

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583914

Luminaire Tested: **HCC8W15D010MB-HM80520927-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583914  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W15D010MB-HM80520927-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1180.4 lumens  
Efficiency: N/A  
Efficacy: 84.3 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583914  
CATALOG NUMBER: HCC8W15D010MB-HM80520927-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583914

CATALOG NUMBER: HCC8W15D010MB-HM80520927-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	19723	19723	19723
5°	20417	19613	18832
10°	20869	19266	17773
15°	21166	18618	16594
20°	21104	17714	15407
25°	20581	16563	14144
30°	19502	15236	12979
35°	17742	13785	11794
40°	15578	12261	10655
45°	13589	10789	9502
50°	11820	9451	8371
55°	10548	8306	7279
60°	9578	7277	6204
65°	8610	6333	5633
70°	7673	5401	5085
75°	6720	4551	4337
80°	5700	3694	3853
85°	4316	2760	3078



TEST NUMBER: P583914  
 CATALOG NUMBER: HCC8W15D010MB-HM80520927-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.9	5.1
10°-20°	165.1	14.0
20°-30°	229.1	19.4
30°-40°	236.9	20.1
40°-50°	198.3	16.8
50°-60°	144.0	12.2
60°-70°	90.9	7.7
70°-80°	45.0	3.8
80°-90°	11.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	454.1	38.5
0°-40°	691.0	58.5
0°-60°	1033.3	87.5
0°-90°	1180.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1180.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	640	640	640	640	640	
5°	660	652	634	616	608	63
15°	663	638	583	536	520	187
25°	605	566	487	434	416	277
35°	471	437	366	325	313	293
45°	312	289	247	223	218	241
55°	196	179	154	142	135	177
65°	118	103	87	76	77	118
75°	56	47	38	36	36	60
85°	12	10	8	9	9	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583914

CATALOG NUMBER: HCC8W15D010MB-HM80520927-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6
2.5°	650.0	650.0	650.9	650.0	650.0	650.0	649.1	649.1	648.3	648.3	646.6
5°	659.6	657.8	659.6	657.8	657.8	657.8	657.0	655.3	654.3	652.6	651.8
7.5°	664.0	663.0	663.0	662.1	662.1	661.3	660.5	659.6	656.1	655.3	652.6
10°	666.5	665.6	665.6	664.8	663.0	663.0	661.3	660.5	656.1	654.3	650.9
12.5°	665.6	665.6	665.6	664.8	662.1	661.3	659.6	657.0	653.5	650.0	646.6
15°	663.0	663.0	661.3	660.5	657.8	656.1	655.3	650.9	647.4	643.1	637.9
17.5°	654.3	654.3	653.5	651.8	649.1	647.4	645.6	641.3	637.9	630.9	625.8
20°	643.1	642.3	641.3	638.8	636.1	635.3	632.6	626.6	622.3	617.1	610.1
22.5°	626.6	625.8	624.8	623.1	618.8	617.1	615.3	610.9	603.1	597.9	589.2
25°	604.9	604.9	603.1	600.6	596.2	594.4	591.9	587.6	580.6	572.7	565.9
27.5°	579.7	578.9	576.2	574.5	571.0	568.4	564.1	558.9	552.0	545.9	537.2
30°	547.7	547.7	545.9	543.2	538.9	537.2	533.7	527.7	520.7	512.8	506.8
32.5°	511.2	511.2	508.5	506.8	504.2	499.8	499.0	492.1	486.0	480.0	473.0
35°	471.3	472.1	470.4	466.9	462.6	462.6	460.8	454.8	447.8	441.8	436.6
37.5°	431.3	428.7	427.9	426.1	423.6	420.1	418.3	415.7	409.6	405.2	397.5
40°	387.0	387.9	386.2	384.5	383.6	381.0	380.2	375.7	371.4	366.2	362.7
42.5°	347.2	347.2	347.2	345.4	343.7	341.0	340.2	337.6	332.3	329.0	323.7
45°	311.6	309.0	309.0	308.1	307.3	305.5	302.9	301.1	297.6	295.1	289.0
47.5°	276.8	277.8	276.8	275.9	273.4	272.5	271.6	268.1	264.7	262.1	257.7
50°	246.4	248.2	246.4	246.4	244.7	243.9	242.1	239.6	236.9	232.6	228.2
52.5°	221.4	221.4	220.4	219.6	217.0	215.2	214.4	213.5	209.2	205.7	202.2
55°	196.2	197.0	197.0	194.4	193.5	191.8	190.9	188.3	186.5	181.4	178.8
57.5°	174.5	173.5	174.5	172.7	171.0	169.2	168.3	166.7	164.0	160.5	157.1
60°	155.3	153.6	153.6	152.8	151.0	150.1	148.5	145.8	143.2	139.8	137.1
62.5°	136.3	135.4	134.5	133.6	131.9	131.1	130.1	127.6	125.0	122.3	119.8
65°	118.0	118.0	117.1	115.4	114.6	113.6	112.8	111.1	107.6	105.9	103.3
67.5°	101.6	100.6	100.6	98.9	97.2	96.3	96.3	94.6	91.9	89.4	87.6
70°	85.1	85.9	85.1	84.2	82.4	82.4	80.7	79.9	76.4	75.6	72.9
72.5°	70.3	70.3	69.4	69.4	67.7	66.9	66.9	65.1	63.4	61.6	59.9
75°	56.4	56.4	56.4	55.6	54.7	52.9	52.9	52.1	50.4	48.6	46.9
77.5°	44.2	43.4	43.4	42.5	41.7	40.7	40.7	39.9	38.2	37.4	35.5
80°	32.1	31.2	31.2	31.2	29.5	30.4	29.5	28.7	27.7	26.9	26.0
82.5°	20.8	21.7	21.7	20.8	20.0	20.0	20.0	19.0	19.0	18.2	17.4
85°	12.2	12.2	12.2	12.2	11.3	11.3	11.3	10.4	10.4	10.4	9.5
87.5°	5.2	5.2	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583914

CATALOG NUMBER: HCC8W15D010MB-HM80520927-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6
2.5°	646.6	644.8	644.0	643.1	643.1	642.3	641.3	639.6	639.6	637.9	637.0
5°	650.0	647.4	645.6	644.0	643.1	641.3	639.6	637.0	636.1	633.6	630.9
7.5°	650.9	646.6	644.8	641.3	639.6	637.9	634.4	631.8	628.3	625.8	622.3
10°	647.4	644.0	639.6	635.3	634.4	631.8	626.6	623.1	618.8	615.3	610.1
12.5°	642.3	637.0	632.6	627.4	624.8	622.3	617.1	611.8	605.8	599.7	594.4
15°	633.6	627.4	621.4	615.3	611.8	609.2	603.1	597.1	591.1	583.2	578.0
17.5°	620.5	613.6	607.4	599.7	596.2	593.6	585.8	578.9	571.0	563.2	558.0
20°	604.1	595.4	588.4	579.7	577.1	572.7	565.0	557.2	548.5	539.8	533.7
22.5°	582.4	573.7	565.9	557.2	552.9	548.5	540.7	531.2	522.5	515.5	509.5
25°	557.2	549.4	539.8	532.0	526.8	521.5	512.8	505.1	497.3	486.8	480.8
27.5°	529.4	519.8	512.8	502.5	497.3	493.8	484.3	473.8	466.9	457.3	450.4
30°	498.1	489.5	481.6	471.3	466.1	462.6	453.9	444.3	437.4	427.9	420.9
32.5°	465.1	455.6	446.1	439.1	433.1	429.6	420.1	413.9	405.2	397.5	389.7
35°	429.6	420.1	413.1	403.6	400.1	396.6	388.9	381.0	373.2	366.2	360.2
37.5°	391.4	384.5	376.7	369.7	367.0	363.7	354.0	347.2	341.0	334.1	329.0
40°	354.0	348.0	342.8	335.8	331.5	329.0	322.0	316.0	309.0	304.6	299.4
42.5°	320.3	313.3	308.1	302.9	298.6	295.9	289.8	285.5	280.3	275.9	269.9
45°	284.6	281.1	275.1	270.8	268.1	264.7	260.4	255.1	250.8	247.4	243.0
47.5°	253.4	249.9	245.6	240.4	238.7	236.1	231.7	228.2	224.7	221.4	217.0
50°	224.7	220.4	217.0	213.5	211.7	209.2	204.8	203.0	200.5	197.0	194.4
52.5°	198.7	195.2	191.8	187.5	186.5	184.8	182.2	178.8	176.2	174.5	172.7
55°	175.3	171.8	169.2	165.8	164.8	163.2	159.7	158.0	156.2	154.5	152.8
57.5°	154.5	151.0	147.5	145.8	144.1	142.3	141.5	138.8	137.1	136.3	134.5
60°	135.4	131.9	129.3	126.8	125.8	125.0	123.3	121.5	119.8	118.0	117.1
62.5°	117.1	113.6	111.9	110.3	108.4	108.4	106.8	105.0	103.3	102.4	100.6
65°	100.6	98.9	96.3	93.7	92.9	92.9	90.3	89.4	88.6	86.8	85.1
67.5°	85.1	83.3	80.7	79.9	78.9	78.1	77.2	75.6	73.7	72.9	71.2
70°	71.2	69.4	67.7	66.9	65.9	65.1	63.4	62.5	60.7	59.9	59.0
72.5°	57.2	56.4	54.7	53.9	52.9	52.1	51.2	50.4	48.6	47.7	46.9
75°	46.0	45.2	43.4	42.5	41.7	41.7	40.7	39.0	38.2	38.2	37.4
77.5°	34.7	33.9	33.0	32.1	31.2	31.2	30.4	29.5	28.7	28.7	27.7
80°	25.2	24.3	23.4	23.4	23.4	22.5	21.7	21.7	20.8	20.8	20.0
82.5°	16.5	16.5	15.7	15.7	15.7	14.7	14.7	13.9	13.9	13.9	13.9
85°	9.5	9.5	9.5	8.7	8.7	8.7	8.7	8.7	8.7	7.8	8.7
87.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583914

CATALOG NUMBER: HCC8W15D010MB-HM80520927-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6
2.5°	636.1	635.3	633.6	633.6	631.8	631.8	630.9	630.1	629.3	628.3	627.4
5°	630.1	626.6	624.8	623.9	622.3	621.4	618.8	617.1	616.1	614.4	612.7
7.5°	618.8	615.3	611.8	610.9	610.1	606.6	604.1	601.4	599.7	597.9	596.2
10°	605.8	602.3	597.9	596.2	594.4	590.1	586.7	584.1	580.6	577.1	576.2
12.5°	590.1	584.9	579.7	578.0	575.4	571.0	567.6	563.2	560.7	556.3	555.4
15°	571.9	565.9	561.5	557.2	555.4	551.0	545.0	541.5	536.3	534.5	530.2
17.5°	550.2	544.2	538.0	536.3	533.7	527.7	521.5	517.2	512.0	509.5	506.8
20°	527.7	519.8	513.8	512.0	508.5	503.3	497.3	493.0	488.6	483.4	480.8
22.5°	501.6	493.0	487.8	483.4	482.5	476.5	469.5	466.1	462.6	458.3	454.8
25°	473.0	465.1	459.1	455.6	453.9	448.6	443.4	439.1	433.9	431.3	426.9
27.5°	443.4	438.3	430.4	426.9	424.4	420.1	413.9	411.4	406.2	402.7	400.1
30°	414.9	407.0	402.7	398.4	395.7	391.4	386.2	383.6	379.2	375.7	373.2
32.5°	383.6	378.4	372.3	370.5	367.0	362.7	359.3	355.0	351.5	348.0	347.2
35°	355.0	348.0	342.0	340.2	337.6	333.3	331.5	329.0	324.6	323.7	320.3
37.5°	323.7	320.3	313.3	310.6	309.8	306.3	302.9	301.1	298.6	295.9	295.1
40°	294.3	289.8	286.4	283.8	282.1	279.4	275.9	275.1	273.4	269.9	269.1
42.5°	266.4	262.1	258.6	257.7	255.1	252.6	250.8	248.2	247.4	246.4	244.7
45°	239.6	236.9	233.4	232.6	231.7	228.2	226.5	224.7	223.0	222.2	220.4
47.5°	215.2	212.7	210.0	209.2	207.4	206.5	203.9	203.0	200.5	199.5	198.7
50°	191.8	190.0	188.3	187.5	185.7	184.8	183.2	181.4	179.7	178.8	177.9
52.5°	171.0	169.2	167.5	166.7	165.8	164.0	162.3	160.5	159.7	158.8	158.0
55°	151.0	149.3	148.5	147.5	146.6	145.8	143.2	142.3	141.5	140.6	138.8
57.5°	132.8	131.1	129.3	129.3	128.5	127.6	125.8	124.1	124.1	122.3	120.6
60°	116.3	114.6	112.8	111.9	111.1	109.3	108.4	107.6	106.8	105.9	104.1
62.5°	98.9	98.1	96.3	96.3	94.6	93.7	92.9	91.9	91.1	89.4	88.6
65°	84.2	83.3	81.6	80.7	80.7	79.9	78.1	77.2	76.4	76.4	75.6
67.5°	70.3	69.4	67.7	66.9	66.9	65.9	65.1	65.1	64.2	63.4	64.2
70°	58.2	56.4	56.4	55.6	55.6	54.7	53.9	53.9	53.9	54.7	54.7
72.5°	46.0	45.2	44.2	44.2	44.2	44.2	43.4	43.4	44.2	45.2	45.2
75°	36.4	35.5	35.5	35.5	34.7	34.7	35.5	35.5	36.4	36.4	36.4
77.5°	26.9	26.9	26.9	26.9	26.9	26.9	27.7	27.7	28.7	28.7	28.7
80°	20.0	20.0	20.0	20.0	20.0	20.8	20.8	20.8	20.8	20.8	21.7
82.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	14.7	14.7	14.7	14.7
85°	7.8	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583914

CATALOG NUMBER: HCC8W15D010MB-HM80520927-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	639.6	639.6	639.6	639.6	639.6	639.6	639.6	639.6
2.5°	626.6	626.6	626.6	627.4	625.8	625.8	625.8	625.8
5°	611.8	610.9	610.1	610.9	609.2	609.2	608.4	608.4
7.5°	593.6	592.7	591.9	591.9	590.1	590.1	589.2	588.4
10°	573.7	571.9	572.7	571.0	570.2	569.4	568.4	567.6
12.5°	552.0	550.2	549.4	547.7	545.9	545.0	545.9	544.2
15°	528.5	525.9	525.0	523.3	521.5	520.7	520.7	519.8
17.5°	502.5	500.8	499.8	498.1	497.3	495.5	494.7	493.8
20°	478.1	473.8	474.8	473.0	472.1	468.6	468.6	469.5
22.5°	451.3	448.6	446.9	445.2	444.3	442.6	442.6	441.8
25°	424.4	421.8	420.9	419.2	418.3	416.6	415.7	415.7
27.5°	398.4	394.9	394.9	393.2	391.4	390.5	389.7	388.9
30°	370.5	368.0	367.0	367.0	366.2	366.2	363.7	364.5
32.5°	344.5	342.8	342.0	340.2	340.2	339.3	339.3	336.7
35°	318.5	316.0	316.8	315.0	314.1	313.3	314.1	313.3
37.5°	293.3	291.6	291.6	289.8	289.8	289.0	288.1	289.8
40°	268.1	267.3	266.4	265.6	266.4	265.6	263.8	264.7
42.5°	243.0	243.0	242.1	242.1	241.2	241.2	241.2	241.2
45°	220.4	219.6	219.6	218.7	218.7	218.7	218.7	217.9
47.5°	197.9	197.0	197.0	197.0	196.2	196.2	195.2	196.2
50°	176.2	176.2	175.3	175.3	176.2	175.3	174.5	174.5
52.5°	156.2	156.2	155.3	155.3	154.5	153.6	154.5	154.5
55°	138.0	137.1	136.3	136.3	135.4	134.5	134.5	135.4
57.5°	120.6	119.8	118.9	118.9	117.1	116.3	116.3	116.3
60°	104.1	102.4	102.4	101.6	101.6	100.6	100.6	100.6
62.5°	88.6	87.6	87.6	87.6	87.6	86.8	86.8	86.8
65°	75.6	75.6	75.6	76.4	76.4	77.2	77.2	77.2
67.5°	65.1	65.9	65.9	65.9	66.9	66.9	66.9	65.9
70°	55.6	55.6	55.6	56.4	56.4	56.4	56.4	56.4
72.5°	46.0	46.0	46.0	46.0	46.0	46.0	46.0	46.0
75°	36.4	37.4	37.4	37.4	36.4	37.4	37.4	36.4
77.5°	28.7	28.7	28.7	28.7	28.7	28.7	28.7	28.7
80°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
82.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)