

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583915

Luminaire Tested: **HCC8W15D010SL-HM80520927-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010SL-HM80520927-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1229.0 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583915
CATALOG NUMBER: HCC8W15D010SL-HM80520927-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583915

CATALOG NUMBER: HCC8W15D010SL-HM80520927-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	18844	18844	18844
5°	19535	18780	18136
10°	20084	18615	17394
15°	20534	18289	16626
20°	20565	17573	15952
25°	20173	16597	15386
30°	19131	15389	14713
35°	17384	14015	14049
40°	15196	12579	13244
45°	13174	11203	12337
50°	11533	9954	11245
55°	10268	8817	10172
60°	9257	7925	8943
65°	8362	6961	7793
70°	7519	5869	5788
75°	6624	4647	4349
80°	5540	3853	4155
85°	4316	3361	3680



TEST NUMBER: P583915
 CATALOG NUMBER: HCC8W15D010SL-HM80520927-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.6	4.7
10°-20°	162.4	13.2
20°-30°	232.1	18.9
30°-40°	246.6	20.1
40°-50°	212.3	17.3
50°-60°	158.7	12.9
60°-70°	101.2	8.2
70°-80°	46.1	3.7
80°-90°	12.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.1	36.8
0°-40°	698.6	56.8
0°-60°	1069.6	87.0
0°-90°	1229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1229.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	611	611	611	611	611	
5°	631	622	607	591	586	60
15°	643	622	573	534	521	181
25°	593	556	488	458	452	271
35°	462	430	372	363	373	288
45°	302	286	257	264	283	235
55°	191	175	164	178	189	172
65°	115	102	95	100	107	114
75°	56	48	39	36	36	59
85°	12	10	10	10	10	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583915

CATALOG NUMBER: HCC8W15D010SL-HM80520927-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1
2.5°	622.4	620.6	621.5	620.6	621.5	621.5	619.7	619.7	619.7	619.7	617.2
5°	631.1	630.2	630.2	629.3	628.4	629.3	628.4	627.6	625.9	624.9	622.4
7.5°	636.2	636.2	636.2	636.2	635.4	634.6	633.6	631.9	630.2	628.4	626.7
10°	641.4	642.3	641.4	640.6	639.7	637.9	637.1	635.4	632.7	630.2	628.4
12.5°	644.1	644.1	643.2	643.2	641.4	640.6	637.9	635.4	632.7	630.2	625.9
15°	643.2	643.2	642.3	641.4	638.9	637.9	636.2	633.6	629.3	625.9	621.5
17.5°	637.9	637.1	635.4	635.4	631.9	631.1	629.3	625.9	621.5	616.2	611.1
20°	626.7	626.7	625.9	624.9	621.5	618.9	617.2	612.9	609.4	603.2	598.0
22.5°	611.1	612.9	611.1	609.4	605.0	604.2	601.5	596.4	591.1	584.2	578.0
25°	592.9	592.0	591.1	589.4	585.9	584.2	580.7	575.5	570.3	562.5	555.5
27.5°	569.4	566.0	566.0	562.5	559.8	557.3	555.5	550.3	543.3	537.3	528.6
30°	537.3	538.2	533.8	533.0	528.6	526.8	523.5	518.2	512.1	505.1	498.3
32.5°	502.6	500.0	500.0	496.5	493.1	490.4	489.6	483.4	478.3	471.3	464.4
35°	461.8	461.8	459.2	458.3	454.9	453.1	450.5	447.1	440.9	434.9	429.7
37.5°	421.9	420.1	419.2	417.5	414.9	412.4	412.4	406.2	405.4	398.4	391.5
40°	377.5	379.3	377.5	375.0	374.2	372.3	371.5	368.0	365.5	359.3	355.0
42.5°	340.3	338.5	338.5	337.6	334.1	334.1	332.5	330.7	326.3	324.6	319.4
45°	302.1	303.8	301.2	302.1	298.6	298.6	298.6	295.1	291.6	289.1	285.6
47.5°	269.1	269.9	269.9	267.4	266.4	266.4	264.7	263.1	260.4	256.9	254.4
50°	240.4	241.4	239.6	238.7	237.0	236.1	236.1	232.6	230.9	227.4	225.7
52.5°	214.4	214.4	213.5	213.5	210.9	210.9	209.2	206.5	204.8	203.2	198.8
55°	191.0	191.0	190.1	189.2	189.2	186.7	185.8	183.2	181.5	178.0	175.3
57.5°	168.3	169.3	168.3	167.5	166.7	165.8	164.0	161.5	159.7	157.1	155.3
60°	150.1	150.1	149.3	148.5	146.6	145.8	145.0	143.3	140.6	138.9	136.3
62.5°	132.8	131.9	131.1	130.3	128.5	128.5	126.8	125.0	122.4	120.6	118.9
65°	114.6	114.6	113.8	113.8	112.8	111.1	110.3	109.4	105.9	105.1	101.6
67.5°	98.1	98.9	97.2	97.2	95.4	95.4	94.6	92.1	91.1	89.4	87.7
70°	83.4	83.4	83.4	82.4	80.7	79.9	79.0	77.2	76.4	74.6	72.9
72.5°	68.6	68.6	67.7	67.7	66.9	65.9	65.1	63.4	63.4	61.6	59.9
75°	55.6	55.6	54.7	53.9	52.9	52.9	52.1	51.2	49.5	48.6	47.7
77.5°	42.5	42.5	42.5	41.7	40.8	40.8	40.8	39.0	37.4	37.4	36.5
80°	31.2	31.2	30.4	30.4	29.5	29.5	29.5	28.7	27.8	26.9	26.0
82.5°	20.8	20.8	20.8	20.8	20.0	20.0	20.0	19.0	18.2	18.2	18.2
85°	12.2	12.2	12.2	12.2	11.3	11.3	11.3	11.3	11.3	10.4	10.4
87.5°	5.2	4.3	5.2	4.3	5.2	4.3	5.2	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583915

CATALOG NUMBER: HCC8W15D010SL-HM80520927-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1
2.5°	618.0	617.2	616.2	615.4	615.4	614.6	612.9	611.9	611.1	610.2	610.2
5°	621.5	620.6	618.9	617.2	616.2	614.6	612.9	611.1	609.4	606.7	605.9
7.5°	624.1	621.5	619.7	616.2	615.4	613.7	611.1	608.5	605.0	601.5	598.9
10°	624.1	620.6	618.0	613.7	611.9	610.2	606.7	602.4	598.0	594.5	590.2
12.5°	622.4	618.0	613.7	609.4	606.7	604.2	598.9	594.5	589.4	584.2	580.7
15°	616.2	611.1	605.9	600.7	598.0	594.5	589.4	583.3	578.0	572.9	566.8
17.5°	605.0	599.8	593.7	587.7	584.2	581.5	573.7	569.4	561.7	556.3	551.2
20°	590.2	584.2	576.4	570.3	566.0	563.3	557.3	549.5	543.3	535.5	530.3
22.5°	571.2	563.3	555.5	549.5	545.1	541.6	533.8	526.0	520.8	513.8	507.8
25°	548.6	540.8	533.0	524.3	520.0	516.5	509.5	502.6	495.6	487.8	482.6
27.5°	521.6	513.0	506.1	498.3	493.9	488.6	480.9	473.9	466.9	461.8	454.9
30°	492.1	482.6	475.6	467.9	463.6	459.2	451.4	444.4	438.4	432.2	428.7
32.5°	456.6	449.6	442.7	434.9	431.4	428.7	421.0	414.0	407.0	401.9	399.3
35°	422.7	414.9	408.9	401.9	397.5	395.0	388.0	381.9	378.5	372.3	368.9
37.5°	387.2	381.0	374.2	367.2	364.5	362.0	356.8	350.7	345.5	341.1	339.4
40°	349.8	344.6	338.5	334.1	331.6	329.0	324.6	320.3	316.8	312.5	310.8
42.5°	314.3	310.8	305.6	300.3	297.8	296.9	291.6	288.2	286.4	284.7	282.9
45°	282.1	276.9	273.4	269.9	267.4	265.6	263.1	260.4	258.7	256.9	255.2
47.5°	250.9	246.5	243.0	240.4	237.9	237.0	235.2	232.6	230.9	230.9	230.9
50°	222.2	218.7	215.2	213.5	212.7	210.9	209.2	208.3	207.5	207.5	207.5
52.5°	197.0	193.5	191.0	189.2	189.2	187.5	185.8	184.8	184.8	184.8	184.8
55°	173.6	171.0	169.3	167.5	165.8	165.0	165.0	165.0	164.0	164.0	165.0
57.5°	152.8	151.0	148.5	146.6	145.8	145.8	145.0	144.1	145.0	145.8	146.6
60°	133.6	131.9	131.1	128.5	128.5	128.5	127.6	127.6	127.6	128.5	129.3
62.5°	116.3	115.4	113.8	112.8	111.9	111.9	111.1	111.1	111.1	111.1	111.9
65°	100.7	98.9	97.2	97.2	97.2	96.4	96.4	94.6	95.4	95.4	94.6
67.5°	85.9	84.2	83.4	82.4	81.6	81.6	80.7	79.9	79.0	79.0	79.0
70°	72.1	70.3	70.3	68.6	68.6	67.7	66.9	66.9	65.9	65.1	64.2
72.5°	58.2	57.2	56.4	55.6	55.6	55.6	54.7	53.9	52.9	52.1	50.4
75°	46.0	46.0	44.2	43.4	43.4	42.5	41.7	40.8	39.9	39.0	38.2
77.5°	35.5	34.7	33.0	32.2	32.2	32.2	31.2	30.4	29.5	28.7	27.8
80°	26.0	25.2	24.3	23.4	23.4	23.4	22.5	22.5	21.7	21.7	21.7
82.5°	17.4	17.4	16.5	16.5	16.5	16.5	15.7	15.7	15.7	15.7	15.7
85°	10.4	10.4	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
87.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583915

CATALOG NUMBER: HCC8W15D010SL-HM80520927-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1
2.5°	608.5	608.5	606.7	605.9	605.0	605.9	604.2	603.2	602.4	602.4	601.5
5°	603.2	602.4	598.9	598.0	597.2	596.4	594.5	592.9	591.1	590.2	589.4
7.5°	596.4	593.7	590.2	589.4	588.5	585.9	583.3	581.5	579.0	578.0	576.4
10°	586.7	583.3	580.7	578.0	576.4	573.7	571.2	568.5	565.0	564.2	561.7
12.5°	575.5	571.2	566.0	565.0	562.5	559.0	555.5	553.0	550.3	548.6	546.0
15°	561.7	557.3	552.0	549.5	546.8	544.3	539.8	536.5	533.8	531.2	528.6
17.5°	545.1	539.8	535.5	533.0	531.2	526.8	523.5	519.1	516.5	513.8	511.3
20°	525.1	520.8	514.8	512.1	511.3	507.8	503.4	501.8	498.3	495.6	493.9
22.5°	502.6	498.3	493.1	491.3	487.8	486.1	481.8	480.0	478.3	475.6	474.8
25°	477.4	473.1	468.7	467.9	465.3	463.6	460.9	458.3	458.3	455.7	455.7
27.5°	451.4	447.1	443.6	441.9	440.9	439.2	436.6	435.7	434.9	434.0	434.0
30°	423.6	418.4	416.7	415.7	414.9	413.2	412.4	410.5	411.4	412.4	411.4
32.5°	394.0	392.3	388.9	387.2	388.0	387.2	385.4	387.2	386.2	388.0	388.9
35°	365.5	363.7	362.0	362.0	360.2	360.2	360.2	361.1	362.8	363.7	365.5
37.5°	337.6	335.0	334.1	333.3	334.1	334.1	334.1	336.0	337.6	339.4	342.0
40°	308.1	306.4	306.4	306.4	306.4	309.0	308.1	309.9	311.6	314.3	316.8
42.5°	280.4	280.4	281.2	281.2	281.2	281.2	282.9	285.6	288.2	290.8	293.4
45°	254.4	254.4	254.4	256.1	256.1	256.9	260.4	262.1	263.9	266.4	269.1
47.5°	230.0	230.0	230.9	231.7	232.6	234.4	236.1	238.7	241.4	243.0	245.7
50°	207.5	208.3	210.0	211.8	211.8	212.7	215.2	217.0	218.7	221.4	222.2
52.5°	185.8	187.5	189.2	190.1	191.0	192.7	193.5	196.2	197.0	199.7	200.5
55°	165.8	166.7	169.3	170.1	170.1	171.8	173.6	175.3	178.0	178.0	179.7
57.5°	147.6	148.5	150.1	151.0	150.1	152.8	153.6	155.3	156.3	158.0	158.8
60°	129.3	131.1	131.9	131.9	132.8	133.6	135.4	135.4	137.1	138.9	138.9
62.5°	111.9	112.8	113.8	114.6	115.4	114.6	117.1	117.1	118.9	119.8	121.5
65°	95.4	96.4	96.4	97.2	97.2	98.1	98.1	98.9	99.8	101.6	102.4
67.5°	79.0	79.0	79.0	79.9	79.0	79.9	79.9	80.7	80.7	82.4	83.4
70°	64.2	63.4	62.5	62.5	62.5	62.5	61.6	62.5	62.5	63.4	63.4
72.5°	49.5	48.6	47.7	46.9	46.9	46.0	45.2	46.0	46.0	46.9	46.9
75°	37.4	35.5	35.5	35.5	34.7	34.7	34.7	35.5	35.5	35.5	36.5
77.5°	27.8	27.8	26.9	26.9	26.9	27.8	27.8	28.7	28.7	28.7	28.7
80°	20.8	21.7	21.7	21.7	21.7	22.5	22.5	22.5	22.5	23.4	23.4
82.5°	15.7	15.7	15.7	15.7	16.5	16.5	16.5	16.5	16.5	16.5	16.5
85°	9.5	10.4	10.4	9.5	10.4	10.4	10.4	10.4	10.4	10.4	10.4
87.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583915

CATALOG NUMBER: HCC8W15D010SL-HM80520927-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1
2.5°	600.7	600.7	600.7	600.7	599.8	599.8	599.8	598.9
5°	587.7	587.7	587.7	585.9	586.7	586.7	585.0	585.9
7.5°	574.7	573.7	572.9	572.9	572.0	571.2	570.3	571.2
10°	559.8	557.3	557.3	556.3	556.3	554.7	554.7	555.5
12.5°	543.3	541.6	541.6	540.8	539.8	539.0	538.2	538.2
15°	526.8	525.1	524.3	523.5	522.5	520.8	521.6	520.8
17.5°	510.4	507.8	507.8	506.9	506.1	504.3	504.3	503.4
20°	491.3	490.4	488.6	489.6	488.6	486.9	486.1	486.1
22.5°	472.2	472.2	471.3	471.3	470.4	469.6	468.7	468.7
25°	453.9	453.1	453.9	453.9	451.4	451.4	451.4	452.2
27.5°	433.1	434.0	433.1	433.1	433.1	433.1	434.0	433.1
30°	412.4	412.4	412.4	413.2	414.9	414.0	414.0	413.2
32.5°	389.7	390.7	390.7	391.5	392.3	394.0	394.0	395.0
35°	367.2	368.9	369.8	368.9	371.5	371.5	373.2	373.2
37.5°	343.8	344.6	346.3	347.2	349.0	349.8	350.7	350.7
40°	318.6	322.0	322.9	323.8	326.3	326.3	327.3	329.0
42.5°	295.1	298.6	299.4	300.3	302.1	304.6	303.8	305.6
45°	272.6	275.1	276.1	276.9	279.4	280.4	280.4	282.9
47.5°	248.2	250.0	250.9	252.6	254.4	256.1	257.7	256.9
50°	223.9	226.5	228.2	229.2	231.7	232.6	233.5	234.4
52.5°	202.2	204.0	204.8	205.7	208.3	209.2	210.0	211.8
55°	181.5	182.3	184.0	183.2	185.8	186.7	187.5	189.2
57.5°	160.6	161.5	162.3	162.3	164.0	165.8	166.7	167.5
60°	140.6	142.3	143.3	143.3	143.3	145.0	145.0	145.0
62.5°	122.4	122.4	123.3	123.3	125.0	125.0	125.0	125.0
65°	103.3	104.1	105.1	105.1	106.8	105.9	107.6	106.8
67.5°	83.4	83.4	85.1	85.1	84.2	85.1	85.1	85.1
70°	63.4	63.4	64.2	64.2	64.2	64.2	64.2	64.2
72.5°	46.9	46.9	46.9	47.7	46.9	46.9	47.7	46.9
75°	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5
77.5°	28.7	28.7	29.5	29.5	29.5	29.5	29.5	29.5
80°	23.4	23.4	23.4	23.4	24.3	23.4	23.4	23.4
82.5°	17.4	16.5	17.4	16.5	17.4	17.4	17.4	17.4
85°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
87.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)