

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583930

Luminaire Tested: **HCC8S15D010MW-HM80520930-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010MW-HM80520930-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1197.7 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583930
CATALOG NUMBER: HCC8S15D010MW-HM80520930-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583930

CATALOG NUMBER: HCC8S15D010MW-HM80520930-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	19828	19828	19828
5°	20646	19783	18953
10°	21336	19532	18026
15°	21878	19084	17092
20°	21917	18291	16244
25°	21547	17138	15403
30°	20399	15809	14684
35°	18596	14222	13785
40°	16170	12535	12728
45°	13872	10859	11648
50°	11849	9359	10468
55°	10387	8059	9096
60°	9245	6876	7647
65°	8201	5611	6100
70°	7276	4165	3462
75°	6076	2180	1037
80°	4777	693	178
85°	3397	354	0



TEST NUMBER: P583930
 CATALOG NUMBER: HCC8S15D010MW-HM80520930-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	5.1
10°-20°	169.8	14.2
20°-30°	240.4	20.1
30°-40°	251.5	21.0
40°-50°	209.7	17.5
50°-60°	148.7	12.4
60°-70°	85.7	7.2
70°-80°	27.6	2.3
80°-90°	3.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.8	39.3
0°-40°	722.2	60.3
0°-60°	1080.7	90.2
0°-90°	1197.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1197.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	643	643	643	643	643	
5°	667	658	639	620	612	64
15°	685	657	598	551	535	193
25°	633	586	504	463	453	289
35°	494	451	378	358	366	306
45°	318	292	249	252	267	246
55°	193	173	150	158	169	175
65°	112	94	77	77	84	112
75°	51	38	18	9	9	55
85°	10	5	1	0	0	12
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583930

CATALOG NUMBER: HCC8S15D010MW-HM80520930-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0
2.5°	656.5	655.5	654.6	655.5	654.6	655.5	654.6	654.6	653.6	652.6	652.6
5°	667.0	666.0	666.0	666.0	665.2	664.2	664.2	663.2	661.3	660.3	658.4
7.5°	673.7	674.7	674.7	674.7	672.8	672.8	670.8	668.9	667.0	665.2	662.3
10°	681.4	681.4	680.5	679.5	677.6	676.6	675.6	673.7	670.8	667.0	664.2
12.5°	684.3	684.3	683.4	681.4	680.5	679.5	678.5	675.6	671.8	667.0	663.2
15°	685.3	683.4	682.4	681.4	679.5	676.6	676.6	672.8	667.9	662.3	657.4
17.5°	677.6	678.5	676.6	674.7	671.8	669.9	667.0	664.2	658.4	651.7	646.8
20°	667.9	667.0	666.0	663.2	659.4	658.4	655.5	650.7	645.9	638.2	631.4
22.5°	652.6	651.7	649.7	647.8	644.0	642.0	639.1	633.3	626.6	619.0	611.3
25°	633.3	631.4	628.5	624.8	621.9	620.0	616.1	610.3	602.6	593.9	586.2
27.5°	602.6	605.5	603.6	597.8	594.9	591.1	590.1	582.5	575.7	567.1	558.4
30°	572.9	572.9	570.0	567.1	562.3	559.4	555.5	549.7	543.1	532.5	525.7
32.5°	535.4	534.4	530.6	529.6	525.7	520.0	519.0	511.3	504.5	496.9	488.3
35°	494.0	492.1	488.3	485.4	483.4	480.6	477.7	470.9	464.2	456.6	450.8
37.5°	446.9	446.9	446.0	441.2	439.2	437.3	434.4	427.7	423.8	416.2	410.4
40°	401.7	400.8	397.9	396.9	395.0	392.1	390.2	386.3	380.7	374.9	369.1
42.5°	357.5	358.5	354.6	355.6	351.7	349.8	348.8	343.1	340.3	334.5	329.7
45°	318.1	317.2	315.2	314.3	312.3	310.4	308.5	305.6	300.9	295.1	292.2
47.5°	281.6	278.7	278.7	277.8	276.8	272.9	272.0	269.1	266.2	260.5	256.7
50°	247.0	247.0	247.0	246.1	243.2	242.2	240.3	237.4	234.5	230.6	224.9
52.5°	219.2	219.2	219.2	218.2	214.4	213.4	212.4	208.6	204.7	201.8	198.0
55°	193.2	194.1	193.2	191.2	188.3	188.3	185.4	183.5	179.8	176.9	173.0
57.5°	171.1	171.1	169.2	168.2	166.3	165.3	163.4	161.5	156.6	153.8	148.9
60°	149.9	148.9	148.9	147.0	145.1	143.2	142.2	139.4	137.5	132.7	128.8
62.5°	130.7	130.7	128.8	128.8	125.0	125.0	124.0	121.1	118.2	113.4	111.5
65°	112.4	112.4	111.5	110.5	107.6	106.6	105.7	102.8	100.0	97.1	94.2
67.5°	96.2	96.2	94.2	93.3	91.3	90.4	88.4	86.5	83.6	80.7	77.8
70°	80.7	79.8	78.8	77.8	75.9	75.0	73.0	71.1	68.2	66.3	63.4
72.5°	65.3	65.3	64.3	62.4	61.5	60.5	59.6	57.7	54.8	51.9	50.0
75°	51.0	51.0	51.0	49.0	47.1	46.2	46.2	44.2	42.3	39.4	37.5
77.5°	39.4	38.4	37.5	37.5	35.5	34.6	33.6	32.7	29.8	28.8	26.9
80°	26.9	27.8	26.9	25.9	24.9	24.0	24.0	22.1	21.1	19.3	17.4
82.5°	18.3	17.4	17.4	16.4	16.4	15.4	15.4	13.5	12.5	11.6	10.6
85°	9.6	9.6	8.7	8.7	8.7	7.7	7.7	6.7	6.7	5.8	4.8
87.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583930

CATALOG NUMBER: HCC8S15D010MW-HM80520930-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0
2.5°	651.7	649.7	648.8	648.8	647.8	646.8	645.9	644.9	643.0	643.0	641.1
5°	656.5	654.6	653.6	650.7	648.8	648.8	644.9	644.0	641.1	639.1	637.2
7.5°	660.3	656.5	653.6	650.7	648.8	646.8	643.0	639.1	635.3	631.4	629.5
10°	660.3	656.5	651.7	646.8	644.9	643.0	638.2	632.4	627.6	623.8	619.0
12.5°	658.4	652.6	646.8	643.0	639.1	636.2	630.5	624.8	619.0	611.3	607.4
15°	652.6	644.9	639.1	632.4	629.5	624.8	620.0	611.3	604.5	597.8	593.0
17.5°	641.1	631.4	624.8	618.0	613.2	610.3	602.6	594.9	587.2	579.6	573.8
20°	623.8	615.2	607.4	598.8	594.9	591.1	581.5	573.8	566.1	557.4	551.6
22.5°	602.6	593.9	583.5	576.7	570.9	566.1	557.4	548.8	541.2	533.5	525.7
25°	576.7	568.0	558.4	547.8	544.1	539.2	529.6	520.9	512.2	503.7	496.9
27.5°	548.8	537.3	529.6	518.0	514.2	509.4	498.9	489.2	481.5	474.8	467.1
30°	515.1	506.5	496.0	485.4	481.5	476.7	468.0	459.5	451.8	444.0	436.3
32.5°	478.6	470.0	459.5	451.8	446.0	442.1	433.4	425.7	418.1	410.4	403.7
35°	440.2	430.5	423.0	415.2	410.4	405.6	396.9	390.2	384.4	377.8	371.0
37.5°	400.8	394.0	386.3	377.8	372.9	369.1	362.3	354.6	349.8	344.0	339.3
40°	362.3	354.6	347.9	340.3	336.4	333.5	326.8	321.0	316.2	311.4	308.5
42.5°	322.9	316.2	309.4	304.6	301.9	299.0	294.1	287.4	284.5	279.7	276.8
45°	286.4	280.6	275.8	269.1	267.1	265.2	259.6	254.7	251.8	249.0	247.0
47.5°	251.8	248.0	242.2	238.3	235.5	233.5	229.7	225.8	222.9	221.1	219.2
50°	222.0	217.3	213.4	209.5	207.6	204.7	200.9	198.9	197.0	195.1	195.1
52.5°	194.1	189.3	185.4	182.6	180.8	178.8	175.9	175.0	173.0	173.0	172.1
55°	168.2	165.3	161.5	157.6	156.6	155.7	153.8	151.8	150.9	149.9	150.9
57.5°	146.0	143.2	139.4	136.5	135.6	134.6	133.6	131.7	130.7	130.7	130.7
60°	125.9	123.0	120.1	117.2	117.2	115.3	114.4	113.4	112.4	111.5	111.5
62.5°	107.6	104.7	101.8	100.0	99.1	98.1	96.2	95.2	94.2	94.2	93.3
65°	91.3	87.5	86.5	83.6	82.7	81.7	80.7	78.8	77.8	76.9	75.9
67.5°	75.0	73.0	70.1	68.2	67.2	66.3	65.3	63.4	62.4	61.5	59.6
70°	60.5	58.7	56.8	54.8	53.9	52.9	51.0	49.0	48.1	46.2	43.3
72.5°	47.1	45.2	43.3	41.3	40.4	39.4	37.5	35.5	33.6	31.7	29.8
75°	35.5	33.6	30.7	28.8	27.8	27.8	24.9	23.0	21.1	18.3	16.4
77.5°	24.9	22.1	21.1	19.3	18.3	16.4	14.5	12.5	10.6	9.6	7.7
80°	16.4	14.5	12.5	11.6	10.6	9.6	8.7	6.7	4.8	3.9	2.9
82.5°	9.6	8.7	7.7	6.7	5.8	4.8	3.9	3.9	2.9	1.9	1.0
85°	4.8	3.9	2.9	2.9	1.9	1.9	1.9	1.0	1.0	1.0	1.0
87.5°	1.9	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583930

CATALOG NUMBER: HCC8S15D010MW-HM80520930-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0
2.5°	640.1	639.1	638.2	637.2	637.2	635.3	635.3	634.3	632.4	631.4	631.4
5°	634.3	631.4	629.5	628.5	627.6	624.8	623.8	621.9	620.0	618.0	617.1
7.5°	625.6	620.9	619.0	618.0	615.2	612.3	610.3	607.4	604.5	601.7	600.7
10°	615.2	610.3	605.5	603.6	600.7	598.8	594.9	591.1	588.2	585.3	582.5
12.5°	601.7	595.9	591.1	589.1	586.2	582.5	576.7	574.8	570.0	568.0	564.2
15°	586.2	579.6	574.8	571.9	569.0	563.2	559.4	555.5	550.7	548.8	544.9
17.5°	567.1	559.4	554.5	551.6	549.7	544.9	539.2	534.4	529.6	527.7	524.8
20°	544.1	539.2	532.5	529.6	527.7	521.9	516.1	514.2	510.3	506.5	503.7
22.5°	518.0	513.2	506.5	503.7	502.7	497.9	493.1	490.2	487.3	484.4	481.5
25°	491.2	485.4	479.6	477.7	475.7	471.9	468.0	466.1	463.3	461.4	459.5
27.5°	462.4	456.6	451.8	448.9	446.9	444.0	442.1	440.2	438.3	436.3	435.4
30°	431.5	425.7	422.0	420.1	418.1	417.2	414.3	413.3	412.4	410.4	411.4
32.5°	400.8	396.0	392.1	389.2	389.2	387.3	386.3	386.3	385.4	385.4	385.4
35°	367.2	364.3	361.4	360.4	359.5	358.5	357.5	358.5	357.5	358.5	359.5
37.5°	336.4	333.5	331.6	330.7	329.7	330.7	329.7	329.7	330.7	332.6	333.5
40°	304.6	302.7	300.9	301.9	300.9	300.9	300.9	303.7	304.6	305.6	306.6
42.5°	274.9	272.9	272.0	272.0	272.9	272.0	273.9	274.9	276.8	279.7	281.6
45°	246.1	245.1	245.1	246.1	245.1	247.0	247.0	249.0	251.8	253.8	255.7
47.5°	219.2	219.2	219.2	220.2	220.2	221.1	222.9	223.9	225.8	227.7	229.7
50°	194.1	195.1	196.1	196.1	196.1	198.0	199.9	200.9	201.8	202.8	205.7
52.5°	172.1	173.0	173.0	174.0	175.0	175.9	176.9	178.8	179.8	181.6	182.6
55°	150.9	150.9	152.8	153.8	153.8	153.8	155.7	155.7	157.6	158.6	160.5
57.5°	130.7	131.7	131.7	132.7	132.7	133.6	134.6	135.6	136.5	137.5	138.5
60°	111.5	111.5	111.5	112.4	113.4	114.4	113.4	115.3	115.3	117.2	118.2
62.5°	93.3	94.2	94.2	94.2	94.2	94.2	94.2	95.2	96.2	97.1	98.1
65°	75.9	75.9	75.9	75.0	75.9	75.0	75.9	76.9	76.9	77.8	78.8
67.5°	58.7	58.7	56.8	56.8	57.7	57.7	57.7	57.7	56.8	58.7	58.7
70°	42.3	41.3	40.4	39.4	39.4	38.4	38.4	37.5	37.5	37.5	37.5
72.5°	27.8	25.9	24.0	23.0	22.1	22.1	20.1	19.3	20.1	20.1	20.1
75°	14.5	12.5	11.6	10.6	9.6	9.6	8.7	8.7	8.7	8.7	8.7
77.5°	5.8	4.8	3.9	3.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
80°	1.9	1.9	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
82.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
85°	1.0	0.0	0.0	1.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583930

CATALOG NUMBER: HCC8S15D010MW-HM80520930-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	643.0	643.0	643.0	643.0	643.0	643.0	643.0	643.0
2.5°	630.5	630.5	629.5	630.5	628.5	629.5	628.5	628.5
5°	616.1	614.2	614.2	614.2	613.2	613.2	612.3	612.3
7.5°	598.8	597.8	596.8	595.9	594.9	593.9	593.9	593.9
10°	581.5	579.6	579.6	578.6	576.7	575.7	575.7	575.7
12.5°	561.3	560.3	559.4	559.4	555.5	556.5	555.5	555.5
15°	542.1	541.2	541.2	538.3	536.3	536.3	536.3	535.4
17.5°	521.9	520.9	520.0	518.0	516.1	516.1	515.1	516.1
20°	500.8	499.8	497.9	497.9	496.9	496.0	494.0	495.0
22.5°	479.6	477.7	476.7	476.7	475.7	475.7	473.8	473.8
25°	457.5	456.6	455.6	456.6	454.6	454.6	452.7	452.7
27.5°	434.4	433.4	433.4	433.4	432.5	433.4	432.5	432.5
30°	411.4	411.4	410.4	410.4	411.4	410.4	411.4	412.4
32.5°	386.3	386.3	387.3	387.3	388.3	388.3	388.3	388.3
35°	360.4	362.3	362.3	363.3	364.3	365.2	365.2	366.2
37.5°	336.4	337.4	338.4	339.3	341.3	341.3	341.3	341.3
40°	310.4	311.4	313.3	312.3	316.2	317.2	316.2	316.2
42.5°	283.5	285.5	286.4	288.4	289.3	291.2	292.2	292.2
45°	258.6	259.6	261.5	263.3	264.3	267.1	267.1	267.1
47.5°	232.6	234.5	235.5	237.4	238.3	241.2	242.2	241.2
50°	207.6	209.5	211.5	211.5	214.4	215.3	217.3	218.2
52.5°	183.5	184.5	186.4	187.4	189.3	191.2	192.2	193.2
55°	160.5	161.5	163.4	163.4	166.3	167.3	169.2	169.2
57.5°	139.4	140.4	142.2	141.2	143.2	145.1	145.1	144.1
60°	119.2	119.2	119.2	121.1	122.1	123.0	124.0	124.0
62.5°	98.1	100.0	100.9	100.9	101.8	102.8	102.8	101.8
65°	78.8	80.7	81.7	81.7	82.7	82.7	82.7	83.6
67.5°	59.6	59.6	59.6	60.5	59.6	59.6	59.6	59.6
70°	37.5	37.5	37.5	37.5	36.5	37.5	37.5	38.4
72.5°	20.1	20.1	20.1	20.1	20.1	20.1	20.1	20.1
75°	8.7	8.7	8.7	9.6	8.7	8.7	8.7	8.7
77.5°	3.9	2.9	3.9	3.9	2.9	2.9	2.9	2.9
80°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
82.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
85°	0.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)