

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583948

Luminaire Tested: **HCC8S15D010SL-HM80520935-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010SL-HM80520935-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1380.6 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583948
CATALOG NUMBER: HCC8S15D010SL-HM80520935-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P583948

CATALOG NUMBER: HCC8S15D010SL-HM80520935-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23069	23069	23069
5°	23878	22937	22027
10°	24408	22532	20785
15°	24754	21772	19410
20°	24684	20716	18019
25°	24072	19373	16543
30°	22806	17818	15179
35°	20749	16127	13793
40°	18223	14342	12463
45°	15891	12616	11107
50°	13826	11053	9786
55°	12333	9709	8510
60°	11206	8517	7259
65°	10076	7406	6596
70°	8962	6311	5951
75°	7863	5326	5087
80°	6677	4315	4511
85°	5024	3255	3573



TEST NUMBER: P583948
 CATALOG NUMBER: HCC8S15D010SL-HM80520935-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.1	5.1
10°-20°	193.1	14.0
20°-30°	268.0	19.4
30°-40°	277.1	20.1
40°-50°	232.0	16.8
50°-60°	168.4	12.2
60°-70°	106.3	7.7
70°-80°	52.6	3.8
80°-90°	13.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.1	38.5
0°-40°	808.2	58.5
0°-60°	1208.6	87.5
0°-90°	1380.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1380.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	748	748	748	748	748	
5°	771	762	741	721	712	74
15°	775	746	682	627	608	218
25°	708	662	569	508	486	324
35°	551	511	428	380	366	343
45°	364	338	289	261	255	282
55°	229	209	181	165	158	207
65°	138	121	102	89	90	138
75°	66	55	45	43	43	71
85°	14	11	9	10	10	17
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583948

CATALOG NUMBER: HCC8S15D010SL-HM80520935-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1
2.5°	760.2	760.2	761.2	760.2	760.2	760.2	759.3	759.3	758.2	758.2	756.1
5°	771.4	769.4	771.4	769.4	769.4	769.4	768.3	766.4	765.3	763.2	762.3
7.5°	776.5	775.4	775.4	774.5	774.5	773.5	772.4	771.4	767.3	766.4	763.2
10°	779.5	778.6	778.6	777.5	775.4	775.4	773.5	772.4	767.3	765.3	761.2
12.5°	778.6	778.6	778.6	777.5	774.5	773.5	771.4	768.3	764.3	760.2	756.1
15°	775.4	775.4	773.5	772.4	769.4	767.3	766.4	761.2	757.2	752.2	746.0
17.5°	765.3	765.3	764.3	762.3	759.3	757.2	755.2	750.1	746.0	737.9	731.8
20°	752.2	751.1	750.1	747.1	744.0	743.0	740.0	732.9	727.7	721.7	713.6
22.5°	732.9	731.8	730.8	728.8	723.7	721.7	719.6	714.6	705.4	699.4	689.1
25°	707.5	707.5	705.4	702.4	697.3	695.3	692.3	687.2	679.0	669.9	661.8
27.5°	678.1	677.0	674.0	671.9	667.9	664.8	659.7	653.7	645.5	638.4	628.3
30°	640.5	640.5	638.4	635.4	630.3	628.3	624.2	617.1	609.0	599.8	592.7
32.5°	597.8	597.8	594.8	592.7	589.7	584.7	583.6	575.5	568.4	561.3	553.2
35°	551.2	552.1	550.1	546.1	541.0	541.0	539.0	531.9	523.7	516.6	510.6
37.5°	504.4	501.4	500.4	498.4	495.4	491.3	489.2	486.2	479.1	474.0	464.9
40°	452.7	453.7	451.6	449.7	448.6	445.6	444.5	439.5	434.4	428.4	424.3
42.5°	406.0	406.0	406.0	403.9	402.0	398.9	397.9	394.9	388.7	384.6	378.6
45°	364.4	361.4	361.4	360.3	359.3	357.3	354.3	352.2	348.1	345.1	338.0
47.5°	323.8	324.7	323.8	322.8	319.7	318.7	317.6	313.7	309.6	306.6	301.5
50°	288.2	290.3	288.2	288.2	286.2	285.2	283.2	280.2	277.2	272.0	266.9
52.5°	258.8	258.8	257.9	256.8	253.8	251.7	250.8	249.7	244.6	240.5	236.5
55°	229.4	230.4	230.4	227.4	226.3	224.4	223.3	220.3	218.2	212.1	209.1
57.5°	204.0	203.0	204.0	202.0	199.9	198.0	196.9	194.8	191.8	187.7	183.8
60°	181.7	179.7	179.7	178.6	176.7	175.6	173.5	170.5	167.5	163.4	160.4
62.5°	159.3	158.3	157.4	156.3	154.2	153.3	152.2	149.2	146.2	143.2	140.0
65°	138.1	138.1	137.0	135.0	134.0	132.9	131.9	129.9	125.8	123.9	120.7
67.5°	118.8	117.7	117.7	115.7	113.6	112.7	112.7	110.6	107.6	104.6	102.5
70°	99.4	100.5	99.4	98.4	96.4	96.4	94.4	93.4	89.3	88.3	85.3
72.5°	82.2	82.2	81.2	81.2	79.2	78.2	78.2	76.2	74.1	72.1	70.0
75°	66.0	66.0	66.0	64.9	64.0	61.9	61.9	60.9	58.9	56.9	54.8
77.5°	51.8	50.7	50.7	49.8	48.7	47.7	47.7	46.6	44.7	43.6	41.6
80°	37.6	36.5	36.5	36.5	34.5	35.5	34.5	33.5	32.5	31.5	30.5
82.5°	24.3	25.4	25.4	24.3	23.4	23.4	23.4	22.3	22.3	21.3	20.2
85°	14.2	14.2	14.2	14.2	13.3	13.3	13.3	12.2	12.2	12.2	11.2
87.5°	6.1	6.1	6.1	6.1	6.1	6.1	5.1	5.1	5.1	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583948

CATALOG NUMBER: HCC8S15D010SL-HM80520935-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1
2.5°	756.1	754.1	753.1	752.2	752.2	751.1	750.1	748.1	748.1	746.0	745.1
5°	760.2	757.2	755.2	753.1	752.2	750.1	748.1	745.1	744.0	741.0	737.9
7.5°	761.2	756.1	754.1	750.1	748.1	746.0	741.9	738.9	734.8	731.8	727.7
10°	757.2	753.1	748.1	743.0	741.9	738.9	732.9	728.8	723.7	719.6	713.6
12.5°	751.1	745.1	740.0	733.8	730.8	727.7	721.7	715.5	708.4	701.3	695.3
15°	741.0	733.8	726.7	719.6	715.5	712.5	705.4	698.3	691.2	682.0	676.0
17.5°	725.8	717.6	710.5	701.3	697.3	694.3	685.2	677.0	667.9	658.8	652.6
20°	706.5	696.2	688.2	678.1	674.9	669.9	660.8	651.7	641.4	631.3	624.2
22.5°	681.1	670.9	661.8	651.7	646.6	641.4	632.4	621.2	611.1	602.9	595.8
25°	651.7	642.5	631.3	622.1	616.1	610.0	599.8	590.7	581.7	569.4	562.3
27.5°	619.1	608.0	599.8	587.7	581.7	577.6	566.4	554.2	546.1	534.9	526.8
30°	582.6	572.5	563.3	551.2	545.0	541.0	530.8	519.7	511.5	500.4	492.2
32.5°	544.1	532.9	521.8	513.6	506.5	502.5	491.3	484.2	474.0	464.9	455.7
35°	502.5	491.3	483.1	472.0	467.9	463.8	454.8	445.6	436.5	428.4	421.3
37.5°	457.8	449.7	440.5	432.4	429.3	425.2	414.2	406.0	398.9	390.8	384.6
40°	414.2	407.0	400.9	392.8	387.8	384.6	376.6	369.5	361.4	356.3	350.2
42.5°	374.5	366.4	360.3	354.3	349.2	346.1	339.0	333.9	327.9	322.8	315.7
45°	332.9	328.8	321.7	316.7	313.7	309.6	304.5	298.4	293.3	289.3	284.3
47.5°	296.4	292.3	287.3	281.1	279.1	276.1	271.0	266.9	262.9	258.8	253.8
50°	262.9	257.9	253.8	249.7	247.6	244.6	239.6	237.5	234.5	230.4	227.4
52.5°	232.4	228.3	224.4	219.2	218.2	216.2	213.2	209.1	206.1	204.0	202.0
55°	205.0	201.0	198.0	193.9	192.8	190.9	186.8	184.7	182.7	180.6	178.6
57.5°	180.6	176.7	172.6	170.5	168.5	166.4	165.4	162.4	160.4	159.3	157.4
60°	158.3	154.2	151.2	148.2	147.1	146.2	144.1	142.1	140.0	138.1	137.0
62.5°	137.0	132.9	131.0	128.9	126.9	126.9	124.8	122.8	120.7	119.8	117.7
65°	117.7	115.7	112.7	109.7	108.6	108.6	105.6	104.6	103.5	101.5	99.4
67.5°	99.4	97.5	94.4	93.4	92.4	91.3	90.4	88.3	86.3	85.3	83.3
70°	83.3	81.2	79.2	78.2	77.1	76.2	74.1	73.0	71.1	70.0	69.0
72.5°	67.0	66.0	64.0	62.9	61.9	60.9	59.9	58.9	56.9	55.8	54.8
75°	53.7	52.8	50.7	49.8	48.7	48.7	47.7	45.7	44.7	44.7	43.6
77.5°	40.6	39.6	38.6	37.6	36.5	36.5	35.5	34.5	33.5	33.5	32.5
80°	29.4	28.4	27.4	27.4	27.4	26.4	25.4	25.4	24.3	24.3	23.4
82.5°	19.3	19.3	18.3	18.3	18.3	17.2	17.2	16.3	16.3	16.3	16.3
85°	11.2	11.2	11.2	10.1	10.1	10.1	10.1	10.1	10.1	9.2	10.1
87.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	4.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583948

CATALOG NUMBER: HCC8S15D010SL-HM80520935-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1
2.5°	744.0	743.0	741.0	741.0	738.9	738.9	737.9	736.9	735.9	734.8	733.8
5°	736.9	732.9	730.8	729.7	727.7	726.7	723.7	721.7	720.7	718.7	716.6
7.5°	723.7	719.6	715.5	714.6	713.6	709.5	706.5	703.4	701.3	699.4	697.3
10°	708.4	704.4	699.4	697.3	695.3	690.2	686.1	683.1	679.0	674.9	674.0
12.5°	690.2	684.1	678.1	676.0	673.0	667.9	663.8	658.8	655.6	650.6	649.6
15°	668.9	661.8	656.7	651.7	649.6	644.6	637.4	633.3	627.3	625.3	620.2
17.5°	643.5	636.4	629.3	627.3	624.2	617.1	610.0	604.9	598.9	595.8	592.7
20°	617.1	608.0	600.9	598.9	594.8	588.6	581.7	576.5	571.4	565.4	562.3
22.5°	586.7	576.5	570.4	565.4	564.3	557.2	549.1	545.0	541.0	535.9	531.9
25°	553.2	544.1	536.9	532.9	530.8	524.8	518.6	513.6	507.5	504.4	499.4
27.5°	518.6	512.6	503.4	499.4	496.3	491.3	484.2	481.2	475.0	470.9	467.9
30°	485.1	476.1	470.9	465.9	462.8	457.8	451.6	448.6	443.6	439.5	436.5
32.5°	448.6	442.6	435.5	433.4	429.3	424.3	420.2	415.1	411.0	407.0	406.0
35°	415.1	407.0	399.9	397.9	394.9	389.8	387.8	384.6	379.6	378.6	374.5
37.5°	378.6	374.5	366.4	363.4	362.3	358.2	354.3	352.2	349.2	346.1	345.1
40°	344.0	339.0	335.0	331.9	329.9	326.8	322.8	321.7	319.7	315.7	314.6
42.5°	311.6	306.6	302.5	301.5	298.4	295.3	293.3	290.3	289.3	288.2	286.2
45°	280.2	277.2	273.1	272.0	271.0	266.9	264.9	262.9	260.9	259.8	257.9
47.5°	251.7	248.7	245.6	244.6	242.6	241.6	238.5	237.5	234.5	233.4	232.4
50°	224.4	222.3	220.3	219.2	217.3	216.2	214.1	212.1	210.2	209.1	208.1
52.5°	199.9	198.0	195.9	194.8	193.9	191.8	189.8	187.7	186.8	185.7	184.7
55°	176.7	174.6	173.5	172.6	171.6	170.5	167.5	166.4	165.4	164.5	162.4
57.5°	155.3	153.3	151.2	151.2	150.3	149.2	147.1	145.2	145.2	143.2	141.1
60°	136.0	134.0	131.9	131.0	129.9	127.9	126.9	125.8	124.8	123.9	121.8
62.5°	115.7	114.7	112.7	112.7	110.6	109.7	108.6	107.6	106.5	104.6	103.5
65°	98.4	97.5	95.4	94.4	94.4	93.4	91.3	90.4	89.3	89.3	88.3
67.5°	82.2	81.2	79.2	78.2	78.2	77.1	76.2	76.2	75.1	74.1	75.1
70°	68.0	66.0	66.0	64.9	64.9	64.0	62.9	62.9	62.9	64.0	64.0
72.5°	53.7	52.8	51.8	51.8	51.8	51.8	50.7	50.7	51.8	52.8	52.8
75°	42.7	41.6	41.6	41.6	40.6	40.6	41.6	41.6	42.7	42.7	42.7
77.5°	31.5	31.5	31.5	31.5	31.5	31.5	32.5	32.5	33.5	33.5	33.5
80°	23.4	23.4	23.4	23.4	23.4	24.3	24.3	24.3	24.3	24.3	25.4
82.5°	16.3	16.3	16.3	16.3	16.3	16.3	16.3	17.2	17.2	17.2	17.2
85°	9.2	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1
87.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583948

CATALOG NUMBER: HCC8S15D010SL-HM80520935-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	748.1	748.1	748.1	748.1	748.1	748.1	748.1	748.1
2.5°	732.9	732.9	732.9	733.8	731.8	731.8	731.8	731.8
5°	715.5	714.6	713.6	714.6	712.5	712.5	711.6	711.6
7.5°	694.3	693.2	692.3	692.3	690.2	690.2	689.1	688.2
10°	670.9	668.9	669.9	667.9	666.8	665.9	664.8	663.8
12.5°	645.5	643.5	642.5	640.5	638.4	637.4	638.4	636.4
15°	618.2	615.0	614.1	612.0	610.0	609.0	609.0	608.0
17.5°	587.7	585.6	584.7	582.6	581.7	579.6	578.5	577.6
20°	559.2	554.2	555.3	553.2	552.1	548.2	548.2	549.1
22.5°	527.8	524.8	522.7	520.7	519.7	517.7	517.7	516.6
25°	496.3	493.3	492.2	490.2	489.2	487.2	486.2	486.2
27.5°	465.9	461.9	461.9	459.8	457.8	456.7	455.7	454.8
30°	433.4	430.3	429.3	429.3	428.4	428.4	425.2	426.3
32.5°	403.0	400.9	399.9	397.9	397.9	396.8	396.8	393.8
35°	372.5	369.5	370.4	368.5	367.4	366.4	367.4	366.4
37.5°	343.1	341.0	341.0	339.0	339.0	338.0	337.0	339.0
40°	313.7	312.6	311.6	310.6	311.6	310.6	308.6	309.6
42.5°	284.3	284.3	283.2	283.2	282.2	282.2	282.2	282.2
45°	257.9	256.8	256.8	255.8	255.8	255.8	255.8	254.7
47.5°	231.5	230.4	230.4	230.4	229.4	229.4	228.3	229.4
50°	206.1	206.1	205.0	205.0	206.1	205.0	204.0	204.0
52.5°	182.7	182.7	181.7	181.7	180.6	179.7	180.6	180.6
55°	161.3	160.4	159.3	159.3	158.3	157.4	157.4	158.3
57.5°	141.1	140.0	139.1	139.1	137.0	136.0	136.0	136.0
60°	121.8	119.8	119.8	118.8	118.8	117.7	117.7	117.7
62.5°	103.5	102.5	102.5	102.5	102.5	101.5	101.5	101.5
65°	88.3	88.3	88.3	89.3	89.3	90.4	90.4	90.4
67.5°	76.2	77.1	77.1	77.1	78.2	78.2	78.2	77.1
70°	64.9	64.9	64.9	66.0	66.0	66.0	66.0	66.0
72.5°	53.7	53.7	53.7	53.7	53.7	53.7	53.7	53.7
75°	42.7	43.6	43.6	43.6	42.7	43.6	43.6	42.7
77.5°	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5
80°	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4
82.5°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2
85°	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1
87.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)