

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583940

Luminaire Tested: **HCC8W15D010BZ-HM80520935-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583940  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W15D010BZ-HM80520935-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1445.5 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583940  
CATALOG NUMBER: HCC8W15D010BZ-HM80520935-81RWWC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583940

CATALOG NUMBER: HCC8W15D010BZ-HM80520935-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	23454	23454	23454
5°	23763	23355	23132
10°	24004	23115	22767
15°	24246	22628	22174
20°	24126	21793	21294
25°	23562	20486	20214
30°	22379	19021	18946
35°	20377	17354	17508
40°	17865	15530	16106
45°	15411	13815	14792
50°	13490	12128	13394
55°	11957	10430	11790
60°	10768	8770	9775
65°	9704	7041	7479
70°	8520	5130	4120
75°	7268	2657	1096
80°	5594	728	178
85°	3573	0	0



TEST NUMBER: P583940

CATALOG NUMBER: HCC8W15D010BZ-HM80520935-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.8	5.0
10°-20°	201.7	14.0
20°-30°	286.3	19.8
30°-40°	301.4	20.9
40°-50°	256.4	17.7
50°-60°	185.3	12.8
60°-70°	105.4	7.3
70°-80°	33.2	2.3
80°-90°	4.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.8	38.7
0°-40°	861.2	59.6
0°-60°	1302.9	90.1
0°-90°	1445.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1445.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	761	761	761	761	761	
5°	768	764	754	749	747	73
15°	760	740	709	696	695	214
25°	692	658	602	592	594	317
35°	541	510	461	458	465	337
45°	353	340	317	325	339	275
55°	222	206	194	205	219	200
65°	133	115	96	95	102	132
75°	61	47	22	10	9	66
85°	10	6	0	0	0	13
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583940

CATALOG NUMBER: HCC8W15D010BZ-HM80520935-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6
2.5°	764.7	765.7	763.6	763.6	765.7	763.6	764.7	764.7	763.6	763.6	762.6
5°	767.7	766.6	766.6	766.6	767.7	765.7	764.7	765.7	763.6	763.6	763.6
7.5°	768.7	768.7	767.7	766.6	766.6	766.6	765.7	764.7	763.6	761.6	760.6
10°	766.6	766.6	767.7	765.7	765.7	763.6	763.6	761.6	761.6	759.5	756.5
12.5°	764.7	763.6	763.6	761.6	761.6	759.5	759.5	756.5	755.5	752.4	749.4
15°	759.5	758.5	756.5	755.5	754.5	753.5	751.4	750.5	747.3	743.4	740.2
17.5°	749.4	748.4	747.3	745.3	743.4	742.3	741.3	738.2	734.2	731.2	726.0
20°	735.2	734.2	734.2	731.2	730.1	727.1	726.0	722.0	718.9	712.9	708.8
22.5°	715.9	717.0	714.9	712.9	710.8	707.8	705.8	701.7	696.6	690.5	685.4
25°	692.5	693.6	691.5	689.5	686.5	684.4	682.4	676.2	671.2	664.1	658.1
27.5°	663.1	663.1	663.1	661.1	656.0	654.9	653.0	646.8	639.7	633.7	627.6
30°	628.5	627.6	627.6	624.6	622.5	618.4	615.4	610.3	605.3	598.2	591.1
32.5°	587.0	587.9	584.9	582.9	579.8	579.8	575.7	571.7	565.6	558.5	551.4
35°	541.3	542.2	540.2	539.2	534.2	533.1	532.1	527.1	523.0	517.9	509.7
37.5°	494.5	493.6	492.5	492.5	489.5	487.4	485.4	482.4	476.2	472.2	468.1
40°	443.8	443.8	443.8	442.7	441.8	439.7	438.7	436.7	432.6	428.5	425.5
42.5°	398.0	398.0	397.0	396.1	394.0	395.0	393.0	390.9	386.9	383.8	381.9
45°	353.4	353.4	353.4	354.4	352.3	349.3	349.3	347.3	345.2	343.2	340.2
47.5°	313.8	316.8	314.7	313.8	314.7	310.8	310.8	308.7	306.7	304.6	300.5
50°	281.2	281.2	281.2	279.2	278.2	278.2	275.2	273.2	272.1	270.2	266.1
52.5°	251.8	249.8	249.8	248.8	247.7	245.7	245.7	243.8	239.7	237.6	234.6
55°	222.4	222.4	221.4	220.4	219.3	218.3	217.3	214.2	212.2	209.2	206.2
57.5°	195.9	198.0	197.0	195.0	192.9	192.9	190.9	188.8	185.8	182.8	179.8
60°	174.6	173.6	173.6	172.7	170.6	169.5	168.6	165.6	162.4	159.4	156.4
62.5°	152.3	152.3	152.3	150.3	148.2	147.3	146.3	144.2	140.1	137.1	135.1
65°	133.0	132.1	131.0	130.0	128.9	126.9	125.9	123.9	120.9	117.8	114.7
67.5°	113.8	112.7	112.7	111.7	108.7	107.6	107.6	104.6	101.6	98.4	95.4
70°	94.5	94.5	94.5	92.4	91.3	90.4	89.4	87.4	84.2	81.2	78.2
72.5°	78.2	77.1	77.1	76.2	73.1	72.1	71.1	69.0	66.0	64.0	61.9
75°	61.0	61.0	59.9	58.9	57.8	56.9	55.8	53.9	50.7	47.7	46.8
77.5°	46.8	45.7	45.7	44.7	42.7	41.7	41.7	39.6	36.5	34.6	32.5
80°	31.5	32.5	31.5	30.5	29.4	28.4	27.5	26.4	24.3	22.3	20.4
82.5°	19.3	20.4	19.3	19.3	18.3	17.2	17.2	15.2	14.2	13.3	12.2
85°	10.1	10.1	10.1	10.1	9.2	9.2	9.2	8.1	7.1	6.1	6.1
87.5°	3.0	4.1	3.0	3.0	3.0	3.0	3.0	3.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583940

CATALOG NUMBER: HCC8W15D010BZ-HM80520935-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6
2.5°	763.6	762.6	761.6	761.6	761.6	761.6	761.6	760.6	759.5	759.5	759.5
5°	761.6	761.6	761.6	760.6	759.5	759.5	757.6	756.5	755.5	754.5	753.5
7.5°	759.5	757.6	756.5	755.5	754.5	754.5	752.4	750.5	750.5	748.4	746.4
10°	753.5	752.4	750.5	748.4	747.3	746.4	744.3	741.3	740.2	738.2	736.3
12.5°	746.4	744.3	742.3	738.2	737.2	736.3	732.2	729.1	727.1	726.0	721.0
15°	737.2	733.1	730.1	725.0	724.1	722.0	718.9	715.9	711.8	708.8	706.7
17.5°	721.0	717.0	711.8	706.7	704.7	704.7	699.6	695.6	690.5	688.5	684.4
20°	701.7	696.6	692.5	686.5	683.4	680.3	677.3	671.2	667.2	664.1	659.0
22.5°	679.4	672.3	667.2	661.1	656.0	653.0	647.8	642.7	637.7	634.7	630.6
25°	650.9	644.8	636.7	630.6	627.6	623.5	617.4	612.4	607.2	602.1	600.1
27.5°	619.5	611.3	604.2	597.1	594.1	591.1	583.9	577.8	573.7	568.6	566.6
30°	584.9	576.8	568.6	562.6	559.5	554.4	550.3	543.2	538.2	534.2	529.1
32.5°	545.3	539.2	532.1	523.0	520.9	516.8	510.8	507.8	501.6	498.6	494.5
35°	502.6	498.6	491.5	484.4	481.3	479.3	474.2	468.1	464.0	461.0	459.0
37.5°	462.0	456.9	449.8	444.8	442.7	439.7	433.6	430.5	426.4	424.5	420.4
40°	418.4	413.3	408.3	405.1	402.1	400.1	396.1	393.0	389.0	385.8	384.9
42.5°	375.7	372.7	368.6	364.5	363.5	360.5	358.5	355.4	352.3	351.4	348.2
45°	337.2	334.1	330.0	326.0	325.0	322.9	321.9	318.8	316.8	316.8	316.8
47.5°	298.6	295.5	291.5	289.4	290.4	286.3	286.3	285.3	283.3	283.3	284.4
50°	264.0	259.9	259.0	256.9	254.9	252.8	253.9	250.8	250.8	252.8	251.8
52.5°	231.5	227.5	226.4	224.4	223.4	223.4	222.4	222.4	221.4	222.4	222.4
55°	202.1	199.1	197.0	195.0	194.0	194.0	194.0	192.9	192.0	194.0	195.0
57.5°	175.7	174.6	172.7	169.5	168.6	167.5	166.5	166.5	166.5	166.5	167.5
60°	152.3	150.3	148.2	145.2	145.2	144.2	143.2	142.2	142.2	142.2	142.2
62.5°	132.1	128.9	125.9	123.9	122.9	121.8	120.9	118.8	118.8	118.8	118.8
65°	111.7	108.7	106.6	104.6	102.5	102.5	100.5	99.5	97.5	96.5	94.5
67.5°	92.4	90.4	88.3	85.3	84.2	83.3	81.2	80.3	77.1	76.2	75.2
70°	75.2	72.1	70.0	68.1	67.0	64.9	62.9	61.0	58.9	56.9	54.8
72.5°	58.9	55.8	53.9	51.8	49.8	49.8	46.8	44.7	41.7	39.6	36.5
75°	43.6	40.6	38.6	35.5	34.6	33.5	30.5	28.4	25.4	22.3	20.4
77.5°	29.4	27.5	25.4	22.3	20.4	20.4	17.2	15.2	13.3	10.1	9.2
80°	18.3	16.3	14.2	12.2	12.2	10.1	9.2	7.1	5.1	4.1	3.0
82.5°	10.1	9.2	8.1	6.1	6.1	5.1	4.1	3.0	2.0	1.0	1.0
85°	5.1	4.1	3.0	3.0	2.0	2.0	2.0	1.0	1.0	0.0	0.0
87.5°	2.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583940

CATALOG NUMBER: HCC8W15D010BZ-HM80520935-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6
2.5°	758.5	758.5	757.6	757.6	757.6	756.5	757.6	756.5	756.5	756.5	757.6
5°	754.5	752.4	752.4	751.4	751.4	750.5	751.4	750.5	749.4	748.4	749.4
7.5°	746.4	744.3	743.4	742.3	742.3	742.3	741.3	740.2	741.3	738.2	740.2
10°	735.2	734.2	732.2	731.2	730.1	731.2	730.1	728.1	728.1	728.1	727.1
12.5°	721.0	718.9	717.9	717.0	714.9	714.9	715.9	713.8	713.8	711.8	711.8
15°	703.7	701.7	699.6	699.6	697.6	697.6	696.6	696.6	695.6	694.6	694.6
17.5°	682.4	679.4	677.3	678.3	677.3	676.2	676.2	674.3	673.2	674.3	674.3
20°	657.0	654.9	653.0	654.0	651.9	650.9	651.9	648.9	649.9	649.9	649.9
22.5°	628.5	627.6	624.6	624.6	622.5	621.4	622.5	622.5	623.5	622.5	622.5
25°	597.1	595.0	593.0	593.0	592.0	591.1	592.0	593.0	592.0	593.0	593.0
27.5°	563.6	560.6	560.6	558.5	558.5	559.5	558.5	559.5	560.6	560.6	562.6
30°	527.1	526.0	525.0	523.9	523.9	525.0	525.0	525.0	526.0	528.0	528.0
32.5°	492.5	490.4	488.4	488.4	490.4	489.5	490.4	490.4	492.5	492.5	494.5
35°	454.9	454.9	452.8	453.9	453.9	453.9	453.9	456.0	458.0	459.0	461.0
37.5°	420.4	417.4	418.4	418.4	419.3	418.4	421.4	421.4	423.4	423.4	425.5
40°	382.8	382.8	383.8	382.8	383.8	383.8	385.8	387.9	389.0	390.9	392.0
42.5°	347.3	349.3	347.3	348.2	349.3	350.3	351.4	352.3	356.4	358.5	361.5
45°	314.7	315.8	316.8	317.9	316.8	318.8	319.9	321.9	325.0	326.0	327.0
47.5°	283.3	284.4	285.3	286.3	286.3	288.4	289.4	291.5	293.4	294.5	295.5
50°	252.8	254.9	255.9	255.9	256.9	259.0	261.0	261.0	263.1	266.1	267.0
52.5°	225.5	225.5	227.5	228.5	229.6	229.6	232.6	233.5	234.6	236.7	238.6
55°	195.0	198.0	199.1	199.1	201.1	203.0	204.1	205.1	205.1	209.2	209.2
57.5°	168.6	169.5	171.6	171.6	171.6	174.6	174.6	176.7	177.7	178.7	180.8
60°	142.2	144.2	144.2	145.2	144.2	146.3	147.3	149.3	150.3	151.3	152.3
62.5°	117.8	117.8	118.8	118.8	118.8	118.8	120.9	120.9	122.9	123.9	125.0
65°	94.5	94.5	94.5	94.5	94.5	94.5	94.5	94.5	95.4	95.4	97.5
67.5°	73.1	72.1	70.0	71.1	70.0	70.0	69.0	69.0	70.0	70.0	72.1
70°	52.8	51.8	49.8	49.8	48.8	47.7	46.8	45.7	44.7	44.7	44.7
72.5°	34.6	32.5	29.4	28.4	28.4	26.4	24.3	23.4	23.4	23.4	23.4
75°	17.2	15.2	13.3	12.2	12.2	10.1	11.2	10.1	10.1	10.1	10.1
77.5°	7.1	5.1	4.1	4.1	4.1	3.0	3.0	3.0	3.0	3.0	3.0
80°	2.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
82.5°	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583940

CATALOG NUMBER: HCC8W15D010BZ-HM80520935-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	760.6	760.6	760.6	760.6	760.6	760.6	760.6	760.6
2.5°	756.5	756.5	754.5	755.5	755.5	755.5	755.5	755.5
5°	747.3	748.4	747.3	748.4	748.4	747.3	747.3	747.3
7.5°	738.2	739.3	738.2	739.3	739.3	739.3	738.2	738.2
10°	727.1	727.1	727.1	727.1	727.1	726.0	727.1	727.1
12.5°	711.8	711.8	711.8	712.9	712.9	711.8	711.8	710.8
15°	695.6	693.6	694.6	695.6	694.6	694.6	694.6	694.6
17.5°	673.2	674.3	673.2	673.2	673.2	673.2	674.3	673.2
20°	649.9	649.9	650.9	649.9	649.9	649.9	649.9	648.9
22.5°	623.5	622.5	622.5	623.5	623.5	622.5	623.5	623.5
25°	594.1	595.0	594.1	594.1	595.0	595.0	595.0	594.1
27.5°	562.6	563.6	564.5	563.6	563.6	563.6	564.5	565.6
30°	530.1	532.1	530.1	530.1	532.1	531.0	532.1	532.1
32.5°	495.5	498.6	496.6	498.6	498.6	499.6	498.6	499.6
35°	461.0	464.0	464.0	464.0	465.1	466.1	466.1	465.1
37.5°	428.5	429.6	429.6	431.6	432.6	433.6	433.6	432.6
40°	395.0	397.0	398.0	398.0	398.0	400.1	402.1	400.1
42.5°	362.5	363.5	364.5	364.5	366.6	367.6	368.6	368.6
45°	331.0	333.1	334.1	335.1	336.1	338.1	337.2	339.2
47.5°	298.6	301.6	302.6	303.7	305.7	306.7	307.6	308.7
50°	269.1	271.1	271.1	273.2	276.2	276.2	278.2	279.2
52.5°	239.7	240.6	241.7	242.7	244.7	246.8	246.8	248.8
55°	211.2	212.2	212.2	213.3	214.2	218.3	219.3	219.3
57.5°	181.7	181.7	183.8	184.8	185.8	187.9	187.9	187.9
60°	153.3	154.4	154.4	155.3	156.4	158.5	159.4	158.5
62.5°	125.0	125.9	125.9	126.9	128.9	130.0	128.9	128.9
65°	98.4	99.5	99.5	100.5	102.5	102.5	101.6	102.5
67.5°	72.1	72.1	72.1	72.1	72.1	72.1	72.1	72.1
70°	45.7	44.7	43.6	44.7	44.7	44.7	43.6	45.7
72.5°	22.3	23.4	23.4	23.4	23.4	23.4	23.4	22.3
75°	10.1	10.1	9.2	9.2	9.2	10.1	10.1	9.2
77.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
80°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)