

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593580

Luminaire Tested: **HCC8S15D010MW-HM80520950-81RWWH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593580  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S15D010MW-HM80520950-81RWWH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1446.6 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593580  
CATALOG NUMBER: HCC8S15D010MW-HM80520950-81RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593580

CATALOG NUMBER: HCC8S15D010MW-HM80520950-81RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67			
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	23796	23796	23796
5°	24240	23692	23141
10°	24621	23280	22294
15°	24869	22701	21332
20°	24772	21822	20349
25°	24120	20564	19213
30°	22973	19064	18092
35°	20742	17395	16808
40°	18223	15615	15574
45°	15734	13724	14321
50°	13696	12041	12838
55°	12139	10457	11188
60°	10836	8838	9288
65°	9770	7172	7326
70°	8673	5373	4337
75°	7482	3110	1871
80°	5754	1119	550
85°	3715	389	389



TEST NUMBER: P593580  
 CATALOG NUMBER: HCC8S15D010MW-HM80520950-81RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.4	5.0
10°-20°	201.7	13.9
20°-30°	285.2	19.7
30°-40°	300.6	20.8
40°-50°	255.4	17.7
50°-60°	183.9	12.7
60°-70°	106.1	7.3
70°-80°	36.3	2.5
80°-90°	5.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.3	38.7
0°-40°	859.9	59.4
0°-60°	1299.2	89.8
0°-90°	1446.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1446.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	772	772	772	772	772	
5°	783	778	765	752	748	75
15°	779	755	711	680	668	219
25°	709	672	604	573	565	325
35°	551	519	462	446	446	343
45°	361	344	315	317	328	280
55°	226	208	194	202	208	203
65°	134	115	98	96	100	133
75°	63	47	26	17	16	66
85°	10	6	1	1	1	14
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593580

CATALOG NUMBER: HCC8S15D010MW-HM80520950-81RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	771.7	771.7	771.7	771.7	771.7	771.7	771.7	771.7	771.7	771.7	771.7
2.5°	779.0	780.0	779.0	779.0	777.9	776.9	775.9	774.8	772.8	770.6	770.6
5°	783.1	785.3	783.1	783.1	780.0	777.9	775.9	772.8	768.5	765.4	765.4
7.5°	786.3	786.3	786.3	783.1	781.1	777.9	772.8	767.5	762.3	757.0	754.9
10°	786.3	786.3	785.3	781.1	779.0	772.8	767.5	760.1	752.9	745.5	743.5
12.5°	783.1	784.2	782.2	777.9	772.8	765.4	758.1	748.7	740.4	731.9	727.7
15°	779.0	777.9	775.9	770.6	764.3	754.9	747.6	737.2	725.7	715.2	711.1
17.5°	768.5	768.5	765.4	760.1	751.8	741.3	729.9	718.3	705.8	694.3	689.0
20°	754.9	754.9	750.7	744.4	736.1	722.5	710.0	696.4	681.8	670.2	665.0
22.5°	735.1	736.1	730.8	723.6	714.2	698.4	685.9	669.3	654.6	640.9	636.8
25°	708.9	711.1	705.8	698.4	685.9	672.4	656.6	640.9	624.2	610.7	604.4
27.5°	678.7	679.6	674.4	667.1	654.6	640.0	624.2	607.6	591.8	577.2	570.9
30°	645.2	640.9	638.9	629.5	615.9	603.3	585.5	572.0	555.3	542.7	535.4
32.5°	598.0	600.2	593.9	586.6	576.1	561.5	546.8	531.2	515.5	506.1	500.8
35°	551.0	553.1	550.0	542.7	531.2	518.6	503.9	492.5	478.9	467.4	462.1
37.5°	501.9	501.9	499.8	495.6	487.3	475.7	461.2	449.6	438.1	428.7	425.6
40°	452.7	450.7	449.6	446.5	439.1	428.7	419.3	409.9	398.4	392.1	387.9
42.5°	404.6	404.6	402.6	399.5	392.1	386.9	377.5	367.0	358.6	352.3	352.3
45°	360.8	361.7	358.6	356.6	352.3	344.0	335.6	328.4	321.0	316.8	314.7
47.5°	322.1	322.1	319.0	316.8	312.7	305.3	298.0	291.7	286.5	283.4	282.3
50°	285.5	285.5	285.5	280.3	275.0	269.8	264.5	257.3	254.1	252.0	251.0
52.5°	254.1	253.0	253.0	248.8	243.7	237.4	232.1	225.8	222.7	220.6	221.7
55°	225.8	225.8	224.9	219.6	214.4	208.1	202.8	197.6	195.6	193.4	194.5
56°	214.4	214.4	213.3	209.1	202.8	197.6	191.4	186.2	183.0	184.0	184.0
57°	205.9	203.9	203.9	198.7	193.4	186.2	180.9	175.7	173.5	172.6	172.6
58°	195.6	194.5	193.4	188.2	183.0	176.7	171.5	166.3	163.2	163.2	162.1
59°	185.1	185.1	183.0	178.8	173.5	167.3	162.1	156.9	153.8	152.7	152.7
60°	175.7	176.7	173.5	169.4	165.2	157.9	151.6	147.5	144.2	143.3	143.3
61°	167.3	167.3	165.2	160.0	154.7	149.5	143.3	138.0	135.9	133.9	133.9
62°	160.0	157.9	156.9	151.6	146.4	140.1	134.8	129.7	126.5	124.5	125.4
63°	150.6	149.5	147.5	143.3	138.0	131.7	125.4	121.3	118.2	115.1	116.0
64°	143.3	142.2	139.1	134.8	129.7	123.4	117.1	112.9	110.9	107.7	106.6
65°	133.9	132.8	131.7	126.5	121.3	115.1	109.8	105.6	102.4	100.4	98.3
66°	125.4	126.5	124.5	120.3	114.0	108.7	101.5	97.2	95.2	92.1	89.9
67°	118.2	118.2	116.0	111.8	105.6	100.4	95.2	89.9	86.8	83.6	82.7
67.5°	114.0	114.0	111.8	106.6	102.4	96.2	91.0	86.8	82.7	80.5	78.4
68°	109.8	109.8	108.7	104.6	99.3	93.0	87.8	82.7	78.4	75.3	74.2
69°	102.4	103.5	101.5	97.2	92.1	85.8	80.5	76.3	72.2	69.0	66.9
70°	96.2	95.2	93.0	88.9	83.6	79.4	74.2	69.0	64.8	60.6	59.6
71°	87.8	87.8	85.8	82.7	77.4	72.2	66.9	62.8	58.6	53.4	52.3
72°	81.6	81.6	79.4	75.3	71.1	65.9	60.6	55.4	52.3	47.0	44.9
72.5°	77.4	78.4	76.3	72.2	68.0	61.7	57.5	53.4	48.1	43.9	41.8
73°	75.3	74.2	73.1	69.0	63.7	59.6	54.3	50.2	44.9	40.7	38.7



TEST NUMBER: P593580  
 CATALOG NUMBER: HCC8S15D010MW-HM80520950-81RWWH

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	47.0	47.0	46.0	41.8	37.6	33.5	29.3	25.1	21.0	16.7	14.6
80°	32.4	33.5	31.3	29.3	26.1	21.9	17.8	14.6	10.5	8.3	6.3
82.5°	21.0	21.0	19.9	17.8	15.7	12.5	10.5	7.4	5.2	4.2	3.1
85°	10.5	11.4	10.5	9.4	7.4	6.3	5.2	3.1	2.0	1.1	1.1
87.5°	4.2	4.2	4.2	3.1	3.1	2.0	1.1	1.1	1.1	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593580

CATALOG NUMBER: HCC8S15D010MW-HM80520950-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	771.7	771.7	771.7	771.7	771.7	771.7	771.7	771.7	771.7	771.7
2.5°	768.5	768.5	766.5	765.4	764.3	763.2	762.3	761.2	761.2	762.3
5°	762.3	760.1	756.0	754.9	751.8	750.7	748.7	747.6	748.7	747.6
7.5°	752.9	748.7	743.5	741.3	737.2	735.1	731.9	731.9	729.9	730.8
10°	740.4	734.1	727.7	723.6	720.5	717.3	715.2	713.1	712.0	712.0
12.5°	724.6	717.3	711.1	704.8	699.5	697.5	693.2	693.2	691.2	690.1
15°	706.9	697.5	690.1	683.8	679.6	675.5	672.4	670.2	668.2	668.2
17.5°	683.8	675.5	668.2	660.8	654.6	651.4	648.3	645.2	645.2	643.1
20°	658.8	649.4	643.1	635.8	630.5	625.3	621.1	621.1	619.0	620.1
22.5°	630.5	619.0	612.7	607.6	602.3	598.0	593.9	593.9	592.9	591.8
25°	599.1	589.7	582.4	576.1	573.0	568.8	567.8	565.6	564.7	564.7
27.5°	565.6	558.4	549.0	545.9	541.6	539.6	539.6	538.5	536.3	537.4
30°	530.1	521.8	516.6	514.4	510.3	510.3	509.2	507.2	507.2	508.1
32.5°	495.6	487.3	483.1	482.0	477.9	477.9	476.8	477.9	477.9	478.9
35°	458.0	450.7	449.6	446.5	445.5	445.5	445.5	447.5	449.6	446.5
37.5°	422.5	417.2	414.0	413.1	414.0	414.0	415.1	418.3	417.2	416.2
40°	385.8	381.6	379.6	379.6	381.6	383.8	383.8	386.9	387.9	386.9
42.5°	349.2	346.1	346.1	347.2	349.2	350.3	353.4	356.6	357.6	358.6
45°	314.7	314.7	314.7	315.8	316.8	319.0	323.1	326.2	327.3	328.4
47.5°	281.2	280.3	283.4	284.4	287.5	288.6	291.7	295.9	296.9	298.0
50°	249.9	252.0	253.0	256.2	258.2	258.2	262.4	264.5	267.6	267.6
52.5°	220.6	223.8	224.9	228.0	229.0	230.0	232.1	235.2	237.4	237.4
55°	194.5	195.6	197.6	198.7	201.8	202.8	205.0	205.9	209.1	208.1
56°	183.0	185.1	186.2	188.2	190.3	191.4	193.4	194.5	196.5	197.6
57°	172.6	173.5	176.7	177.7	179.9	179.9	180.9	184.0	184.0	185.1
58°	162.1	164.1	165.2	166.3	168.3	169.4	171.5	172.6	173.5	172.6
59°	152.7	153.8	154.7	154.7	156.9	156.9	160.0	162.1	163.2	163.2
60°	143.3	143.3	144.2	145.3	147.5	148.5	148.5	150.6	150.6	150.6
61°	133.9	133.9	134.8	135.9	137.0	137.0	139.1	139.1	140.1	141.1
62°	125.4	124.5	124.5	125.4	125.4	127.6	128.6	129.7	130.7	129.7
63°	116.0	115.1	115.1	115.1	115.1	117.1	117.1	118.2	120.3	119.2
64°	105.6	105.6	105.6	105.6	106.6	106.6	108.7	109.8	110.9	111.8
65°	98.3	96.2	95.2	95.2	96.2	97.2	98.3	99.3	100.4	100.4
66°	89.9	87.8	86.8	86.8	86.8	86.8	88.9	88.9	91.0	91.0
67°	80.5	78.4	77.4	76.3	76.3	76.3	79.4	78.4	78.4	78.4
67.5°	77.4	74.2	73.1	72.2	71.1	73.1	72.2	73.1	73.1	72.2
68°	73.1	71.1	69.0	66.9	66.9	66.9	68.0	69.0	68.0	66.9
69°	64.8	63.7	60.6	58.6	57.5	58.6	57.5	58.6	57.5	58.6
70°	57.5	54.3	51.2	50.2	49.2	49.2	49.2	48.1	49.2	48.1
71°	50.2	47.0	43.9	41.8	40.7	40.7	39.8	40.7	39.8	40.7
72°	42.9	39.8	35.5	33.5	33.5	33.5	33.5	32.4	33.5	32.4
72.5°	39.8	35.5	32.4	30.4	29.3	29.3	29.3	29.3	28.2	29.3
73°	36.6	32.4	28.2	27.2	27.2	27.2	26.1	25.1	26.1	26.1





TEST NUMBER: P593580  
 CATALOG NUMBER: HCC8S15D010MW-HM80520950-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	12.5	9.4	8.3	8.3	8.3	8.3	8.3	8.3	7.4	7.4
80°	5.2	4.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
82.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
85°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



74°	68.0	68.0	65.9	62.8	57.5	52.3	48.1	43.9	38.7	33.5	31.3
75°	62.8	61.7	59.6	56.5	52.3	47.0	42.9	37.6	33.5	28.2	26.1

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	30.4	25.1	23.0	21.0	21.0	21.0	19.9	19.9	19.9	21.0
75°	24.1	19.9	17.8	15.7	16.7	15.7	16.7	15.7	15.7	15.7

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)