

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583998

Luminaire Tested: **HCC8S20D010MB-HM80520830-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MB-HM80520830-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1804.1 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583998
CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P583998

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	29865	29865	29865
5°	31100	29800	28546
10°	32139	29421	27154
15°	32952	28744	25744
20°	33019	27555	24467
25°	32462	25811	23201
30°	30725	23817	22115
35°	28015	21420	20765
40°	24362	18879	19173
45°	20897	16349	17553
50°	17851	14094	15764
55°	15645	12145	13698
60°	13932	10361	11520
65°	12360	8449	9194
70°	10963	6266	5220
75°	9138	3276	1549
80°	7192	1030	249
85°	5095	495	0



TEST NUMBER: P583998
 CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.3	5.1
10°-20°	255.8	14.2
20°-30°	362.0	20.1
30°-40°	378.8	21.0
40°-50°	315.9	17.5
50°-60°	224.0	12.4
60°-70°	129.0	7.2
70°-80°	41.5	2.3
80°-90°	5.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.1	39.3
0°-40°	1087.9	60.3
0°-60°	1627.8	90.2
0°-90°	1804.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1804.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	968	968	968	968	968	
5°	1005	992	963	934	922	96
15°	1032	990	900	830	806	290
25°	954	883	759	698	682	435
35°	744	679	569	538	552	461
45°	479	440	375	379	402	371
55°	291	261	226	238	255	263
65°	169	142	116	116	126	169
75°	77	56	28	13	13	83
85°	14	7	1	0	0	18
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583998

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5
2.5°	988.9	987.3	985.9	987.3	985.9	987.3	985.9	985.9	984.5	983.1	983.1
5°	1004.7	1003.3	1003.3	1003.3	1001.9	1000.4	1000.4	998.9	996.1	994.7	991.7
7.5°	1014.9	1016.3	1016.3	1016.3	1013.4	1013.4	1010.5	1007.7	1004.7	1001.9	997.5
10°	1026.4	1026.4	1025.0	1023.6	1020.7	1019.2	1017.8	1014.9	1010.5	1004.7	1000.4
12.5°	1030.8	1030.8	1029.4	1026.4	1025.0	1023.6	1022.1	1017.8	1012.0	1004.7	998.9
15°	1032.2	1029.4	1027.9	1026.4	1023.6	1019.2	1019.2	1013.4	1006.2	997.5	990.3
17.5°	1020.7	1022.1	1019.2	1016.3	1012.0	1009.1	1004.7	1000.4	991.7	981.5	974.3
20°	1006.2	1004.7	1003.3	998.9	993.1	991.7	987.3	980.1	972.9	961.3	951.2
22.5°	983.1	981.5	978.7	975.7	969.9	967.1	962.7	954.1	943.9	932.4	920.8
25°	954.1	951.2	946.8	941.0	936.7	933.8	928.0	919.4	907.8	894.7	883.1
27.5°	907.8	912.0	909.2	900.4	896.2	890.4	888.9	877.3	867.2	854.1	841.1
30°	862.9	862.9	858.5	854.1	846.9	842.6	836.9	828.1	817.9	802.1	791.9
32.5°	806.4	804.9	799.2	797.7	791.9	783.2	781.8	770.2	760.0	748.4	735.4
35°	744.2	741.2	735.4	731.1	728.2	723.9	719.5	709.4	699.3	687.7	678.9
37.5°	673.1	673.1	671.7	664.5	661.6	658.7	654.4	644.2	638.4	626.9	618.2
40°	605.2	603.8	599.4	598.0	595.0	590.6	587.8	582.0	573.3	564.6	555.9
42.5°	538.5	540.1	534.3	535.7	529.9	526.9	525.5	516.9	512.5	503.8	496.6
45°	479.2	477.8	474.8	473.4	470.6	467.6	464.8	460.4	453.2	444.4	440.1
47.5°	424.2	419.8	419.8	418.4	417.0	411.2	409.7	405.4	401.1	392.3	386.5
50°	372.1	372.1	372.1	370.7	366.3	364.9	361.9	357.6	353.3	347.5	338.8
52.5°	330.1	330.1	330.1	328.6	322.8	321.4	320.0	314.2	308.4	304.0	298.2
55°	291.0	292.4	291.0	288.1	283.8	283.8	279.4	276.5	270.7	266.4	260.6
57.5°	257.7	257.7	254.8	253.3	250.5	249.0	246.1	243.3	235.9	231.7	224.3
60°	225.9	224.3	224.3	221.5	218.6	215.7	214.3	209.9	207.1	199.8	194.0
62.5°	196.9	196.9	194.0	194.0	188.2	188.2	186.8	182.4	178.1	170.8	168.0
65°	169.4	169.4	168.0	166.5	162.2	160.8	159.2	155.0	150.6	146.2	141.8
67.5°	144.8	144.8	141.8	140.4	137.6	136.0	133.2	130.3	126.0	121.6	117.3
70°	121.6	120.2	118.7	117.3	114.4	112.9	110.0	107.1	102.8	99.9	95.5
72.5°	98.5	98.5	97.0	94.1	92.7	91.3	89.7	86.9	82.5	78.1	75.3
75°	76.7	76.7	76.7	73.9	70.9	69.5	69.5	66.5	63.7	59.3	56.5
77.5°	59.3	57.9	56.5	56.5	53.5	52.1	50.7	49.2	44.9	43.4	40.5
80°	40.5	42.0	40.5	39.1	37.6	36.2	36.2	33.3	31.8	29.0	26.0
82.5°	27.5	26.0	26.0	24.6	24.6	23.2	23.2	20.2	18.8	17.4	16.0
85°	14.4	14.4	13.0	13.0	13.0	11.6	11.6	10.2	10.2	8.6	7.2
87.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583998

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5
2.5°	981.5	978.7	977.3	977.3	975.7	974.3	972.9	971.5	968.5	968.5	965.7
5°	988.9	985.9	984.5	980.1	977.3	977.3	971.5	969.9	965.7	962.7	959.9
7.5°	994.7	988.9	984.5	980.1	977.3	974.3	968.5	962.7	956.9	951.2	948.3
10°	994.7	988.9	981.5	974.3	971.5	968.5	961.3	952.6	945.4	939.6	932.4
12.5°	991.7	983.1	974.3	968.5	962.7	958.4	949.7	941.0	932.4	920.8	915.0
15°	983.1	971.5	962.7	952.6	948.3	941.0	933.8	920.8	910.6	900.4	893.2
17.5°	965.7	951.2	941.0	930.9	923.6	919.4	907.8	896.2	884.6	873.0	864.3
20°	939.6	926.6	915.0	902.0	896.2	890.4	875.9	864.3	852.7	839.7	831.1
22.5°	907.8	894.7	878.8	868.7	859.9	852.7	839.7	826.7	815.1	803.5	791.9
25°	868.7	855.6	841.1	825.3	819.5	812.2	797.7	784.7	771.6	758.6	748.4
27.5°	826.7	809.3	797.7	780.4	774.6	767.4	751.4	736.9	725.3	715.2	703.6
30°	776.0	763.0	747.0	731.1	725.3	718.1	705.1	692.1	680.5	668.9	657.3
32.5°	721.0	707.9	692.1	680.5	671.7	665.9	652.9	641.4	629.8	618.2	608.0
35°	663.1	648.6	637.0	625.4	618.2	611.0	598.0	587.8	579.1	569.0	558.8
37.5°	603.8	593.6	582.0	569.0	561.7	555.9	545.8	534.3	526.9	518.3	511.1
40°	545.8	534.3	524.1	512.5	506.7	502.4	492.2	483.6	476.3	469.0	464.8
42.5°	486.4	476.3	466.2	459.0	454.6	450.2	443.0	432.8	428.5	421.3	417.0
45°	431.4	422.8	415.5	405.4	402.5	399.6	390.9	383.7	379.3	374.9	372.1
47.5°	379.3	373.5	364.9	359.1	354.7	351.8	346.0	340.2	335.9	333.0	330.1
50°	334.4	327.2	321.4	315.6	312.8	308.4	302.6	299.6	296.8	293.8	293.8
52.5°	292.4	285.2	279.4	275.1	272.2	269.3	264.9	263.5	260.6	260.6	259.1
55°	253.3	249.0	243.3	237.5	235.9	234.5	231.7	228.7	227.3	225.9	227.3
57.5°	220.1	215.7	209.9	205.5	204.1	202.7	201.3	198.3	196.9	196.9	196.9
60°	189.7	185.3	181.0	176.6	176.6	173.8	172.3	170.8	169.4	168.0	168.0
62.5°	162.2	157.8	153.4	150.6	149.2	147.6	144.8	143.4	141.8	141.8	140.4
65°	137.6	131.8	130.3	126.0	124.5	123.0	121.6	118.7	117.3	115.8	114.4
67.5°	112.9	110.0	105.7	102.8	101.3	99.9	98.5	95.5	94.1	92.7	89.7
70°	91.3	88.3	85.5	82.5	81.1	79.7	76.7	73.9	72.3	69.5	65.1
72.5°	70.9	68.1	65.1	62.3	60.8	59.3	56.5	53.5	50.7	47.8	44.9
75°	53.5	50.7	46.3	43.4	42.0	42.0	37.6	34.8	31.8	27.5	24.6
77.5°	37.6	33.3	31.8	29.0	27.5	24.6	21.7	18.8	16.0	14.4	11.6
80°	24.6	21.7	18.8	17.4	16.0	14.4	13.0	10.2	7.2	5.8	4.4
82.5°	14.4	13.0	11.6	10.2	8.6	7.2	5.8	5.8	4.4	2.8	1.4
85°	7.2	5.8	4.4	4.4	2.8	2.8	2.8	1.4	1.4	1.4	1.4
87.5°	2.8	1.4	1.4	1.4	1.4	1.4	1.4	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583998

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5
2.5°	964.2	962.7	961.3	959.9	959.9	956.9	956.9	955.5	952.6	951.2	951.2
5°	955.5	951.2	948.3	946.8	945.4	941.0	939.6	936.7	933.8	930.9	929.4
7.5°	942.5	935.2	932.4	930.9	926.6	922.2	919.4	915.0	910.6	906.2	904.8
10°	926.6	919.4	912.0	909.2	904.8	902.0	896.2	890.4	886.0	881.7	877.3
12.5°	906.2	897.6	890.4	887.4	883.1	877.3	868.7	865.7	858.5	855.6	849.9
15°	883.1	873.0	865.7	861.4	857.1	848.3	842.6	836.9	829.5	826.7	820.9
17.5°	854.1	842.6	835.3	831.1	828.1	820.9	812.2	804.9	797.7	794.8	790.5
20°	819.5	812.2	802.1	797.7	794.8	786.1	777.4	774.6	768.8	763.0	758.6
22.5°	780.4	773.1	763.0	758.6	757.2	750.0	742.7	738.4	734.0	729.6	725.3
25°	739.8	731.1	722.4	719.5	716.6	710.9	705.1	702.1	697.9	694.9	692.1
27.5°	696.3	687.7	680.5	676.1	673.1	668.9	665.9	663.1	660.1	657.3	655.8
30°	650.0	641.4	635.6	632.7	629.8	628.4	624.0	622.6	621.1	618.2	619.6
32.5°	603.8	596.4	590.6	586.4	586.4	583.4	582.0	582.0	580.6	580.6	580.6
35°	553.1	548.7	544.3	542.9	541.5	540.1	538.5	540.1	538.5	540.1	541.5
37.5°	506.7	502.4	499.5	498.0	496.6	498.0	496.6	496.6	498.0	500.9	502.4
40°	459.0	456.0	453.2	454.6	453.2	453.2	453.2	457.4	459.0	460.4	461.8
42.5°	414.1	411.2	409.7	409.7	411.2	409.7	412.6	414.1	417.0	421.3	424.2
45°	370.7	369.1	369.1	370.7	369.1	372.1	372.1	374.9	379.3	382.3	385.1
47.5°	330.1	330.1	330.1	331.6	331.6	333.0	335.9	337.3	340.2	343.1	346.0
50°	292.4	293.8	295.4	295.4	295.4	298.2	301.2	302.6	304.0	305.4	309.8
52.5°	259.1	260.6	260.6	262.0	263.5	264.9	266.4	269.3	270.7	273.6	275.1
55°	227.3	227.3	230.1	231.7	231.7	231.7	234.5	234.5	237.5	238.9	241.7
57.5°	196.9	198.3	198.3	199.8	199.8	201.3	202.7	204.1	205.5	207.1	208.5
60°	168.0	168.0	168.0	169.4	170.8	172.3	170.8	173.8	173.8	176.6	178.1
62.5°	140.4	141.8	141.8	141.8	141.8	141.8	141.8	143.4	144.8	146.2	147.6
65°	114.4	114.4	114.4	112.9	114.4	112.9	114.4	115.8	115.8	117.3	118.7
67.5°	88.3	88.3	85.5	85.5	86.9	86.9	86.9	86.9	85.5	88.3	88.3
70°	63.7	62.3	60.8	59.3	59.3	57.9	57.9	56.5	56.5	56.5	56.5
72.5°	42.0	39.1	36.2	34.8	33.3	33.3	30.4	29.0	30.4	30.4	30.4
75°	21.7	18.8	17.4	16.0	14.4	14.4	13.0	13.0	13.0	13.0	13.0
77.5°	8.6	7.2	5.8	5.8	4.4	4.4	4.4	4.4	4.4	4.4	4.4
80°	2.8	2.8	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
85°	1.4	0.0	0.0	1.4	0.0	1.4	1.4	1.4	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583998

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	968.5	968.5	968.5	968.5	968.5	968.5	968.5	968.5
2.5°	949.7	949.7	948.3	949.7	946.8	948.3	946.8	946.8
5°	928.0	925.2	925.2	925.2	923.6	923.6	922.2	922.2
7.5°	902.0	900.4	899.0	897.6	896.2	894.7	894.7	894.7
10°	875.9	873.0	873.0	871.5	868.7	867.2	867.2	867.2
12.5°	845.5	844.1	842.6	842.6	836.9	838.3	836.9	836.9
15°	816.5	815.1	815.1	810.7	807.9	807.9	807.9	806.4
17.5°	786.1	784.7	783.2	780.4	777.4	777.4	776.0	777.4
20°	754.2	752.8	750.0	750.0	748.4	747.0	744.2	745.6
22.5°	722.4	719.5	718.1	718.1	716.6	716.6	713.7	713.7
25°	689.1	687.7	686.3	687.7	684.7	684.7	681.9	681.9
27.5°	654.4	652.9	652.9	652.9	651.5	652.9	651.5	651.5
30°	619.6	619.6	618.2	618.2	619.6	618.2	619.6	621.1
32.5°	582.0	582.0	583.4	583.4	584.9	584.9	584.9	584.9
35°	542.9	545.8	545.8	547.3	548.7	550.1	550.1	551.6
37.5°	506.7	508.1	509.6	511.1	513.9	513.9	513.9	513.9
40°	467.6	469.0	472.0	470.6	476.3	477.8	476.3	476.3
42.5°	427.1	430.0	431.4	434.3	435.8	438.6	440.1	440.1
45°	389.5	390.9	393.8	396.7	398.1	402.5	402.5	402.5
47.5°	350.3	353.3	354.7	357.6	359.1	363.3	364.9	363.3
50°	312.8	315.6	318.5	318.5	322.8	324.3	327.2	328.6
52.5°	276.5	278.0	280.8	282.3	285.2	288.1	289.6	291.0
55°	241.7	243.3	246.1	246.1	250.5	251.9	254.8	254.8
57.5°	209.9	211.3	214.3	212.8	215.7	218.6	218.6	217.1
60°	179.5	179.5	179.5	182.4	183.9	185.3	186.8	186.8
62.5°	147.6	150.6	152.0	152.0	153.4	155.0	155.0	153.4
65°	118.7	121.6	123.0	123.0	124.5	124.5	124.5	126.0
67.5°	89.7	89.7	89.7	91.3	89.7	89.7	89.7	89.7
70°	56.5	56.5	56.5	56.5	55.0	56.5	56.5	57.9
72.5°	30.4	30.4	30.4	30.4	30.4	30.4	30.4	30.4
75°	13.0	13.0	13.0	14.4	13.0	13.0	13.0	13.0
77.5°	5.8	4.4	5.8	5.8	4.4	4.4	4.4	4.4
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
85°	0.0	1.4	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)