

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584000

Luminaire Tested: **HCC8S20D010MW-HM80520830-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584000  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S20D010MW-HM80520830-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2050.3 lumens  
Efficiency: N/A  
Efficacy: 102.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584000  
CATALOG NUMBER: HCC8S20D010MW-HM80520830-81WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P584000

CATALOG NUMBER: HCC8S20D010MW-HM80520830-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	31435	31435	31435
5°	32585	31329	30255
10°	33507	31058	29017
15°	34255	30507	27736
20°	34308	29317	26610
25°	33650	27689	25668
30°	31914	25676	24540
35°	28997	23381	23441
40°	25356	20984	22091
45°	21975	18691	20588
50°	19242	16603	18757
55°	17123	14709	16972
60°	15449	13216	14912
65°	13944	11623	12995
70°	12532	9791	9665
75°	11044	7756	7256
80°	9252	6428	6943
85°	7182	5661	6156



TEST NUMBER: P584000  
 CATALOG NUMBER: HCC8S20D010MW-HM80520830-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.2	4.7
10°-20°	270.9	13.2
20°-30°	387.1	18.9
30°-40°	411.3	20.1
40°-50°	354.1	17.3
50°-60°	264.8	12.9
60°-70°	168.9	8.2
70°-80°	76.9	3.7
80°-90°	20.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.1	36.8
0°-40°	1165.4	56.8
0°-60°	1784.3	87.0
0°-90°	2050.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2050.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1019	1019	1019	1019	1019	
5°	1053	1038	1012	986	977	101
15°	1073	1037	956	890	869	302
25°	989	927	814	764	754	453
35°	770	717	621	605	623	480
45°	504	476	429	440	472	392
55°	318	292	274	297	316	286
65°	191	169	159	166	178	191
75°	93	80	65	59	61	98
85°	20	17	16	17	17	24
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584000

CATALOG NUMBER: HCC8S20D010MW-HM80520830-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4
2.5°	1038.3	1035.3	1036.7	1035.3	1036.7	1036.7	1033.9	1033.9	1033.9	1033.9	1029.5
5°	1052.7	1051.3	1051.3	1049.9	1048.3	1049.9	1048.3	1046.9	1044.1	1042.5	1038.3
7.5°	1061.4	1061.4	1061.4	1061.4	1059.9	1058.5	1057.1	1054.1	1051.3	1048.3	1045.5
10°	1070.1	1071.5	1070.1	1068.6	1067.2	1064.3	1062.9	1059.9	1055.6	1051.3	1048.3
12.5°	1074.4	1074.4	1073.0	1073.0	1070.1	1068.6	1064.3	1059.9	1055.6	1051.3	1044.1
15°	1073.0	1073.0	1071.5	1070.1	1065.7	1064.3	1061.4	1057.1	1049.9	1044.1	1036.7
17.5°	1064.3	1062.9	1059.9	1059.9	1054.1	1052.7	1049.9	1044.1	1036.7	1028.1	1019.4
20°	1045.5	1045.5	1044.1	1042.5	1036.7	1032.5	1029.5	1022.3	1016.5	1006.4	997.7
22.5°	1019.4	1022.3	1019.4	1016.5	1009.3	1007.8	1003.5	994.8	986.1	974.6	964.4
25°	989.0	987.6	986.1	983.2	977.4	974.6	968.8	960.0	951.3	938.3	926.7
27.5°	949.9	944.1	944.1	938.3	933.9	929.6	926.7	918.1	906.5	896.3	881.8
30°	896.3	897.7	890.5	889.1	881.8	878.9	873.1	864.4	854.3	842.8	831.2
32.5°	838.4	834.0	834.0	828.2	822.4	818.1	816.6	806.5	797.8	786.3	774.7
35°	770.3	770.3	765.9	764.5	758.7	755.9	751.5	745.7	735.6	725.4	716.8
37.5°	703.8	700.8	699.4	696.4	692.2	687.8	687.8	677.6	676.2	664.6	653.1
40°	629.9	632.7	629.9	625.5	624.1	621.1	619.7	613.9	609.6	599.5	592.2
42.5°	567.6	564.8	564.8	563.2	557.4	557.4	554.6	551.6	544.4	541.6	532.8
45°	503.9	506.8	502.5	503.9	498.1	498.1	498.1	492.3	486.5	482.1	476.3
47.5°	448.9	450.3	450.3	446.0	444.6	444.6	441.6	438.8	434.4	428.6	424.2
50°	401.1	402.6	399.6	398.2	395.3	393.8	393.8	388.1	385.2	379.4	376.5
52.5°	357.7	357.7	356.3	356.3	351.9	351.9	348.9	344.7	341.7	338.9	331.6
55°	318.5	318.5	317.1	315.7	315.7	311.3	309.9	305.5	302.6	296.8	292.5
57.5°	281.0	282.4	281.0	279.4	278.0	276.6	273.6	269.4	266.4	262.0	259.2
60°	250.5	250.5	249.0	247.6	244.7	243.3	241.8	238.9	234.6	231.7	227.3
62.5°	221.5	220.1	218.7	217.3	214.3	214.3	211.5	208.5	204.1	201.3	198.3
65°	191.1	191.1	189.7	189.7	188.3	185.3	183.9	182.5	176.7	175.2	169.4
67.5°	163.6	165.1	162.2	162.2	159.3	159.3	157.8	153.5	152.0	149.2	146.2
70°	139.0	139.0	139.0	137.6	134.6	133.2	131.8	128.8	127.4	124.6	121.6
72.5°	114.4	114.4	113.0	113.0	111.5	110.0	108.6	105.7	105.7	102.8	99.9
75°	92.7	92.7	91.3	89.8	88.3	88.3	86.9	85.5	82.5	81.1	79.7
77.5°	70.9	70.9	70.9	69.5	68.1	68.1	68.1	65.1	62.3	62.3	60.9
80°	52.1	52.1	50.7	50.7	49.3	49.3	49.3	47.8	46.3	44.9	43.5
82.5°	34.8	34.8	34.8	34.8	33.3	33.3	33.3	31.9	30.4	30.4	30.4
85°	20.3	20.3	20.3	20.3	18.8	18.8	18.8	18.8	18.8	17.4	17.4
87.5°	8.7	7.2	8.7	7.2	8.7	7.2	8.7	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584000

CATALOG NUMBER: HCC8S20D010MW-HM80520830-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4
2.5°	1030.9	1029.5	1028.1	1026.7	1026.7	1025.1	1022.3	1020.9	1019.4	1017.9	1017.9
5°	1036.7	1035.3	1032.5	1029.5	1028.1	1025.1	1022.3	1019.4	1016.5	1012.1	1010.7
7.5°	1041.1	1036.7	1033.9	1028.1	1026.7	1023.7	1019.4	1015.1	1009.3	1003.5	999.1
10°	1041.1	1035.3	1030.9	1023.7	1020.9	1017.9	1012.1	1004.9	997.7	991.9	984.6
12.5°	1038.3	1030.9	1023.7	1016.5	1012.1	1007.8	999.1	991.9	983.2	974.6	968.8
15°	1028.1	1019.4	1010.7	1002.0	997.7	991.9	983.2	973.0	964.4	955.6	945.5
17.5°	1009.3	1000.6	990.4	980.4	974.6	970.2	957.1	949.9	936.9	928.1	919.5
20°	984.6	974.6	961.4	951.3	944.1	939.7	929.6	916.5	906.5	893.4	884.7
22.5°	952.8	939.7	926.7	916.5	909.3	903.5	890.5	877.5	868.8	857.2	847.0
25°	915.1	902.1	889.1	874.6	867.4	861.6	850.0	838.4	826.8	813.8	805.1
27.5°	870.2	855.8	844.2	831.2	823.9	815.2	802.2	790.6	779.1	770.3	758.7
30°	821.0	805.1	793.5	780.5	773.3	765.9	752.9	741.4	731.2	721.1	715.3
32.5°	761.7	750.1	738.5	725.4	719.6	715.3	702.2	690.6	679.1	670.4	666.1
35°	705.2	692.2	682.0	670.4	663.2	658.8	647.3	637.1	631.3	621.1	615.3
37.5°	645.8	635.7	624.1	612.5	608.1	603.8	595.1	585.0	576.3	569.0	566.2
40°	583.6	574.8	564.8	557.4	553.2	548.8	541.6	534.3	528.5	521.3	518.4
42.5°	524.2	518.4	509.7	501.0	496.7	495.3	486.5	480.7	477.9	474.9	472.1
45°	470.6	461.9	456.1	450.3	446.0	443.1	438.8	434.4	431.5	428.6	425.8
47.5°	418.4	411.2	405.4	401.1	396.8	395.3	392.4	388.1	385.2	385.2	385.2
50°	370.7	364.9	359.1	356.3	354.7	351.9	348.9	347.5	346.1	346.1	346.1
52.5°	328.7	322.9	318.5	315.7	315.7	312.8	309.9	308.4	308.4	308.4	308.4
55°	289.6	285.2	282.4	279.4	276.6	275.2	275.2	275.2	273.6	273.6	275.2
57.5°	254.8	252.0	247.6	244.7	243.3	243.3	241.8	240.4	241.8	243.3	244.7
60°	223.0	220.1	218.7	214.3	214.3	214.3	212.9	212.9	212.9	214.3	215.7
62.5°	194.1	192.5	189.7	188.3	186.8	186.8	185.3	185.3	185.3	185.3	186.8
65°	168.0	165.1	162.2	162.2	162.2	160.8	160.8	157.8	159.3	159.3	157.8
67.5°	143.4	140.4	139.0	137.6	136.2	136.2	134.6	133.2	131.8	131.8	131.8
70°	120.2	117.3	117.3	114.4	114.4	113.0	111.5	111.5	110.0	108.6	107.2
72.5°	97.0	95.6	94.1	92.7	92.7	92.7	91.3	89.8	88.3	86.9	84.0
75°	76.7	76.7	73.9	72.5	72.5	70.9	69.5	68.1	66.7	65.1	63.7
77.5°	59.3	57.9	55.1	53.5	53.5	53.5	52.1	50.7	49.3	47.8	46.3
80°	43.5	42.0	40.5	39.1	39.1	39.1	37.7	37.7	36.2	36.2	36.2
82.5°	29.0	29.0	27.5	27.5	27.5	27.5	26.1	26.1	26.1	26.1	26.1
85°	17.4	17.4	16.0	16.0	16.0	16.0	16.0	16.0	16.0	16.0	16.0
87.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584000

CATALOG NUMBER: HCC8S20D010MW-HM80520830-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4
2.5°	1015.1	1015.1	1012.1	1010.7	1009.3	1010.7	1007.8	1006.4	1004.9	1004.9	1003.5
5°	1006.4	1004.9	999.1	997.7	996.2	994.8	991.9	989.0	986.1	984.6	983.2
7.5°	994.8	990.4	984.6	983.2	981.8	977.4	973.0	970.2	965.8	964.4	961.4
10°	978.8	973.0	968.8	964.4	961.4	957.1	952.8	948.4	942.6	941.2	936.9
12.5°	960.0	952.8	944.1	942.6	938.3	932.5	926.7	922.3	918.1	915.1	910.7
15°	936.9	929.6	920.9	916.5	912.3	907.9	900.7	894.9	890.5	886.1	881.8
17.5°	909.3	900.7	893.4	889.1	886.1	878.9	873.1	865.9	861.6	857.2	852.8
20°	876.0	868.8	858.6	854.3	852.8	847.0	839.8	837.0	831.2	826.8	823.9
22.5°	838.4	831.2	822.4	819.6	813.8	810.9	803.6	800.7	797.8	793.5	792.1
25°	796.4	789.1	781.9	780.5	776.1	773.3	768.9	764.5	764.5	760.1	760.1
27.5°	752.9	745.7	739.9	737.0	735.6	732.7	728.3	726.9	725.4	724.0	724.0
30°	706.6	698.0	695.0	693.6	692.2	689.2	687.8	684.9	686.4	687.8	686.4
32.5°	657.4	654.5	648.7	645.8	647.3	645.8	642.9	645.8	644.3	647.3	648.7
35°	609.6	606.7	603.8	603.8	600.9	600.9	600.9	602.3	605.3	606.7	609.6
37.5°	563.2	559.0	557.4	556.0	557.4	557.4	557.4	560.4	563.2	566.2	570.6
40°	514.1	511.1	511.1	511.1	511.1	515.5	514.1	516.9	519.8	524.2	528.5
42.5°	467.7	467.7	469.1	469.1	469.1	469.1	472.1	476.3	480.7	485.1	489.5
45°	424.2	424.2	424.2	427.2	427.2	428.6	434.4	437.3	440.2	444.6	448.9
47.5°	383.7	383.7	385.2	386.6	388.1	391.0	393.8	398.2	402.6	405.4	409.8
50°	346.1	347.5	350.5	353.3	353.3	354.7	359.1	362.0	364.9	369.3	370.7
52.5°	309.9	312.8	315.7	317.1	318.5	321.5	322.9	327.3	328.7	333.1	334.5
55°	276.6	278.0	282.4	283.8	283.8	286.8	289.6	292.5	296.8	296.8	299.8
57.5°	246.2	247.6	250.5	252.0	250.5	254.8	256.3	259.2	260.6	263.6	265.0
60°	215.7	218.7	220.1	220.1	221.5	223.0	225.9	225.9	228.8	231.7	231.7
62.5°	186.8	188.3	189.7	191.1	192.5	191.1	195.5	195.5	198.3	199.9	202.7
65°	159.3	160.8	160.8	162.2	162.2	163.6	163.6	165.1	166.5	169.4	170.9
67.5°	131.8	131.8	131.8	133.2	131.8	133.2	133.2	134.6	134.6	137.6	139.0
70°	107.2	105.7	104.3	104.3	104.3	104.3	102.8	104.3	104.3	105.7	105.7
72.5°	82.5	81.1	79.7	78.2	78.2	76.7	75.3	76.7	76.7	78.2	78.2
75°	62.3	59.3	59.3	59.3	57.9	57.9	57.9	59.3	59.3	59.3	60.9
77.5°	46.3	46.3	44.9	44.9	44.9	46.3	46.3	47.8	47.8	47.8	47.8
80°	34.8	36.2	36.2	36.2	36.2	37.7	37.7	37.7	37.7	39.1	39.1
82.5°	26.1	26.1	26.1	26.1	27.5	27.5	27.5	27.5	27.5	27.5	27.5
85°	16.0	17.4	17.4	16.0	17.4	17.4	17.4	17.4	17.4	17.4	17.4
87.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584000

CATALOG NUMBER: HCC8S20D010MW-HM80520830-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4	1019.4
2.5°	1002.0	1002.0	1002.0	1002.0	1000.6	1000.6	1000.6	999.1
5°	980.4	980.4	980.4	977.4	978.8	978.8	976.0	977.4
7.5°	958.6	957.1	955.6	955.6	954.2	952.8	951.3	952.8
10°	933.9	929.6	929.6	928.1	928.1	925.3	925.3	926.7
12.5°	906.5	903.5	903.5	902.1	900.7	899.1	897.7	897.7
15°	878.9	876.0	874.6	873.1	871.7	868.8	870.2	868.8
17.5°	851.4	847.0	847.0	845.6	844.2	841.2	841.2	839.8
20°	819.6	818.1	815.2	816.6	815.2	812.3	810.9	810.9
22.5°	787.7	787.7	786.3	786.3	784.8	783.3	781.9	781.9
25°	757.3	755.9	757.3	757.3	752.9	752.9	752.9	754.4
27.5°	722.6	724.0	722.6	722.6	722.6	722.6	724.0	722.6
30°	687.8	687.8	687.8	689.2	692.2	690.6	690.6	689.2
32.5°	650.1	651.6	651.6	653.1	654.5	657.4	657.4	658.8
35°	612.5	615.3	616.9	615.3	619.7	619.7	622.7	622.7
37.5°	573.4	574.8	577.8	579.2	582.1	583.6	585.0	585.0
40°	531.4	537.2	538.6	540.1	544.4	544.4	545.8	548.8
42.5°	492.3	498.1	499.5	501.0	503.9	508.3	506.8	509.7
45°	454.7	459.0	460.5	461.9	466.3	467.7	467.7	472.1
47.5°	414.2	417.0	418.4	421.4	424.2	427.2	430.0	428.6
50°	373.6	377.9	380.8	382.3	386.6	388.1	389.5	391.0
52.5°	337.3	340.3	341.7	343.1	347.5	348.9	350.5	353.3
55°	302.6	304.1	307.0	305.5	309.9	311.3	312.8	315.7
57.5°	267.8	269.4	270.8	270.8	273.6	276.6	278.0	279.4
60°	234.6	237.5	238.9	238.9	238.9	241.8	241.8	241.8
62.5°	204.1	204.1	205.7	205.7	208.5	208.5	208.5	208.5
65°	172.3	173.8	175.2	175.2	178.1	176.7	179.5	178.1
67.5°	139.0	139.0	142.0	142.0	140.4	142.0	142.0	142.0
70°	105.7	105.7	107.2	107.2	107.2	107.2	107.2	107.2
72.5°	78.2	78.2	78.2	79.7	78.2	78.2	79.7	78.2
75°	60.9	60.9	60.9	60.9	60.9	60.9	60.9	60.9
77.5°	47.8	47.8	49.3	49.3	49.3	49.3	49.3	49.3
80°	39.1	39.1	39.1	39.1	40.5	39.1	39.1	39.1
82.5°	29.0	27.5	29.0	27.5	29.0	29.0	29.0	29.0
85°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
87.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)