

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584011

Luminaire Tested: **HCC8S20D010SL-HM80520835-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010SL-HM80520835-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1876.8 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584011
CATALOG NUMBER: HCC8S20D010SL-HM80520835-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584011

CATALOG NUMBER: HCC8S20D010SL-HM80520835-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	31074	31074	31074
5°	32353	31004	29697
10°	33435	30607	28250
15°	34280	29910	26781
20°	34351	28664	25452
25°	33769	26852	24137
30°	31961	24775	23005
35°	29144	22282	21604
40°	25340	19640	19946
45°	21744	17012	18259
50°	18570	14670	16397
55°	16274	12634	14252
60°	14493	10774	11983
65°	12856	8785	9566
70°	11405	6519	5437
75°	9508	3407	1620
80°	7494	1065	266
85°	5307	531	0



TEST NUMBER: P584011
 CATALOG NUMBER: HCC8S20D010SL-HM80520835-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	5.1
10°-20°	266.1	14.2
20°-30°	376.6	20.1
30°-40°	394.1	21.0
40°-50°	328.7	17.5
50°-60°	233.1	12.4
60°-70°	134.2	7.2
70°-80°	43.2	2.3
80°-90°	5.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.7	39.3
0°-40°	1131.7	60.3
0°-60°	1693.5	90.2
0°-90°	1876.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1876.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1008	1008	1008	1008	1008	
5°	1045	1032	1002	972	959	100
15°	1074	1030	937	863	839	302
25°	992	919	789	726	709	453
35°	774	706	592	560	574	480
45°	499	458	390	395	419	386
55°	303	271	235	247	265	274
65°	176	148	120	120	131	176
75°	80	59	29	14	14	86
85°	15	8	2	0	0	19
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584011

CATALOG NUMBER: HCC8S20D010SL-HM80520835-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7
2.5°	1028.7	1027.2	1025.6	1027.2	1025.6	1027.2	1025.6	1025.6	1024.2	1022.7	1022.7
5°	1045.2	1043.7	1043.7	1043.7	1042.3	1040.8	1040.8	1039.2	1036.3	1034.7	1031.6
7.5°	1055.8	1057.3	1057.3	1057.3	1054.3	1054.3	1051.3	1048.3	1045.2	1042.3	1037.7
10°	1067.8	1067.8	1066.3	1064.9	1061.8	1060.4	1058.8	1055.8	1051.3	1045.2	1040.8
12.5°	1072.3	1072.3	1070.9	1067.8	1066.3	1064.9	1063.3	1058.8	1052.8	1045.2	1039.2
15°	1073.8	1070.9	1069.4	1067.8	1064.9	1060.4	1060.4	1054.3	1046.8	1037.7	1030.2
17.5°	1061.8	1063.3	1060.4	1057.3	1052.8	1049.7	1045.2	1040.8	1031.6	1021.1	1013.7
20°	1046.8	1045.2	1043.7	1039.2	1033.2	1031.6	1027.2	1019.6	1012.1	1000.1	989.6
22.5°	1022.7	1021.1	1018.2	1015.1	1009.1	1006.1	1001.6	992.5	982.0	969.9	957.9
25°	992.5	989.6	985.0	978.9	974.4	971.5	965.5	956.4	944.3	930.8	918.8
27.5°	944.3	948.9	945.8	936.9	932.2	926.2	924.8	912.7	902.2	888.6	875.0
30°	897.6	897.6	893.1	888.6	881.1	876.6	870.5	861.6	850.9	834.4	823.9
32.5°	838.9	837.4	831.4	829.9	823.9	814.9	813.3	801.3	790.8	778.7	765.1
35°	774.2	771.1	765.1	760.6	757.5	753.1	748.6	738.0	727.4	715.5	706.4
37.5°	700.3	700.3	698.8	691.4	688.3	685.3	680.7	670.2	664.2	652.1	643.1
40°	629.5	628.1	623.5	622.1	619.0	614.5	611.4	605.4	596.4	587.3	578.4
42.5°	560.3	561.8	555.8	557.3	551.3	548.2	546.7	537.7	533.2	524.1	516.7
45°	498.6	497.0	494.0	492.5	489.5	486.5	483.4	478.9	471.4	462.4	457.9
47.5°	441.2	436.7	436.7	435.3	433.8	427.8	426.2	421.7	417.2	408.1	402.1
50°	387.1	387.1	387.1	385.6	381.1	379.5	376.6	372.0	367.5	361.5	352.5
52.5°	343.4	343.4	343.4	341.8	335.9	334.4	332.9	326.8	320.8	316.3	310.3
55°	302.7	304.2	302.7	299.8	295.1	295.1	290.7	287.7	281.7	277.2	271.2
57.5°	268.1	268.1	265.1	263.6	260.5	259.1	256.0	253.1	245.5	241.0	233.4
60°	235.0	233.4	233.4	230.5	227.4	224.5	222.9	218.4	215.4	207.8	201.8
62.5°	204.8	204.8	201.8	201.8	195.7	195.7	194.3	189.8	185.2	177.8	174.7
65°	176.2	176.2	174.7	173.2	168.7	167.1	165.7	161.1	156.6	152.1	147.6
67.5°	150.6	150.6	147.6	146.1	143.1	141.6	138.5	135.6	131.1	126.5	122.0
70°	126.5	125.1	123.5	122.0	119.0	117.5	114.4	111.5	107.0	103.9	99.4
72.5°	102.4	102.4	100.9	97.9	96.5	94.9	93.4	90.4	85.8	81.3	78.4
75°	79.8	79.8	79.8	76.8	73.8	72.3	72.3	69.3	66.3	61.7	58.7
77.5°	61.7	60.3	58.7	58.7	55.7	54.3	52.7	51.2	46.7	45.2	42.2
80°	42.2	43.7	42.2	40.7	39.1	37.7	37.7	34.6	33.1	30.1	27.1
82.5°	28.6	27.1	27.1	25.6	25.6	24.1	24.1	21.0	19.6	18.1	16.5
85°	15.0	15.0	13.6	13.6	13.6	12.1	12.1	10.5	10.5	9.0	7.6
87.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	3.0	3.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584011

CATALOG NUMBER: HCC8S20D010SL-HM80520835-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7
2.5°	1021.1	1018.2	1016.6	1016.6	1015.1	1013.7	1012.1	1010.6	1007.7	1007.7	1004.6
5°	1028.7	1025.6	1024.2	1019.6	1016.6	1016.6	1010.6	1009.1	1004.6	1001.6	998.6
7.5°	1034.7	1028.7	1024.2	1019.6	1016.6	1013.7	1007.7	1001.6	995.6	989.6	986.5
10°	1034.7	1028.7	1021.1	1013.7	1010.6	1007.7	1000.1	991.0	983.5	977.5	969.9
12.5°	1031.6	1022.7	1013.7	1007.7	1001.6	997.0	988.0	978.9	969.9	957.9	951.9
15°	1022.7	1010.6	1001.6	991.0	986.5	978.9	971.5	957.9	947.4	936.9	929.3
17.5°	1004.6	989.6	978.9	968.4	961.0	956.4	944.3	932.2	920.3	908.2	899.1
20°	977.5	963.9	951.9	938.3	932.2	926.2	911.2	899.1	887.1	873.5	864.5
22.5°	944.3	930.8	914.3	903.6	894.7	887.1	873.5	860.0	848.0	835.9	823.9
25°	903.6	890.2	875.0	858.5	852.5	844.9	829.9	816.3	802.8	789.2	778.7
27.5°	860.0	841.9	829.9	811.8	805.8	798.2	781.7	766.6	754.6	744.1	732.0
30°	807.3	793.7	777.2	760.6	754.6	747.0	733.4	720.0	707.9	695.8	683.8
32.5°	750.1	736.5	720.0	707.9	698.8	692.8	679.3	667.2	655.2	643.1	632.6
35°	689.8	674.8	662.7	650.7	643.1	635.6	622.1	611.4	602.5	591.9	581.3
37.5°	628.1	617.5	605.4	591.9	584.4	578.4	567.8	555.8	548.2	539.2	531.7
40°	567.8	555.8	545.3	533.2	527.2	522.7	512.0	503.1	495.5	487.9	483.4
42.5°	506.0	495.5	485.0	477.4	472.9	468.4	460.9	450.3	445.9	438.3	433.8
45°	448.8	439.8	432.3	421.7	418.7	415.7	406.6	399.2	394.6	390.1	387.1
47.5°	394.6	388.5	379.5	373.5	369.0	365.9	359.9	353.9	349.4	346.4	343.4
50°	347.9	340.4	334.4	328.4	325.3	320.8	314.8	311.8	308.7	305.8	305.8
52.5°	304.2	296.7	290.7	286.2	283.2	280.1	275.6	274.1	271.2	271.2	269.6
55°	263.6	259.1	253.1	247.0	245.5	244.0	241.0	237.9	236.5	235.0	236.5
57.5°	229.0	224.5	218.4	213.8	212.4	210.9	209.3	206.4	204.8	204.8	204.8
60°	197.3	192.8	188.3	183.8	183.8	180.7	179.2	177.8	176.2	174.7	174.7
62.5°	168.7	164.2	159.7	156.6	155.1	153.7	150.6	149.1	147.6	147.6	146.1
65°	143.1	137.1	135.6	131.1	129.5	128.0	126.5	123.5	122.0	120.4	119.0
67.5°	117.5	114.4	109.9	107.0	105.4	103.9	102.4	99.4	97.9	96.5	93.4
70°	94.9	91.8	88.9	85.8	84.4	82.9	79.8	76.8	75.3	72.3	67.7
72.5°	73.8	70.8	67.7	64.8	63.2	61.7	58.7	55.7	52.7	49.6	46.7
75°	55.7	52.7	48.2	45.2	43.7	43.7	39.1	36.2	33.1	28.6	25.6
77.5°	39.1	34.6	33.1	30.1	28.6	25.6	22.6	19.6	16.5	15.0	12.1
80°	25.6	22.6	19.6	18.1	16.5	15.0	13.6	10.5	7.6	6.0	4.5
82.5°	15.0	13.6	12.1	10.5	9.0	7.6	6.0	6.0	4.5	3.0	1.5
85°	7.6	6.0	4.5	4.5	3.0	3.0	3.0	1.5	1.5	1.5	1.5
87.5°	3.0	1.5	1.5	1.5	1.5	1.5	1.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584011

CATALOG NUMBER: HCC8S20D010SL-HM80520835-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7
2.5°	1003.0	1001.6	1000.1	998.6	998.6	995.6	995.6	994.1	991.0	989.6	989.6
5°	994.1	989.6	986.5	985.0	983.5	978.9	977.5	974.4	971.5	968.4	967.0
7.5°	980.5	972.9	969.9	968.4	963.9	959.4	956.4	951.9	947.4	942.9	941.3
10°	963.9	956.4	948.9	945.8	941.3	938.3	932.2	926.2	921.7	917.2	912.7
12.5°	942.9	933.8	926.2	923.3	918.8	912.7	903.6	900.7	893.1	890.2	884.1
15°	918.8	908.2	900.7	896.2	891.6	882.6	876.6	870.5	863.0	860.0	854.0
17.5°	888.6	876.6	869.0	864.5	861.6	854.0	844.9	837.4	829.9	826.8	822.3
20°	852.5	844.9	834.4	829.9	826.8	817.8	808.8	805.8	799.7	793.7	789.2
22.5°	811.8	804.2	793.7	789.2	787.7	780.1	772.7	768.2	763.6	759.1	754.6
25°	769.6	760.6	751.5	748.6	745.5	739.5	733.4	730.5	726.0	722.9	720.0
27.5°	724.4	715.5	707.9	703.4	700.3	695.8	692.8	689.8	686.7	683.8	682.3
30°	676.2	667.2	661.2	658.1	655.2	653.6	649.2	647.6	646.1	643.1	644.7
32.5°	628.1	620.6	614.5	610.0	610.0	607.0	605.4	605.4	604.0	604.0	604.0
35°	575.4	570.8	566.3	564.8	563.3	561.8	560.3	561.8	560.3	561.8	563.3
37.5°	527.2	522.7	519.6	518.1	516.7	518.1	516.7	516.7	518.1	521.1	522.7
40°	477.4	474.5	471.4	472.9	471.4	471.4	471.4	476.0	477.4	478.9	480.5
42.5°	430.7	427.8	426.2	426.2	427.8	426.2	429.3	430.7	433.8	438.3	441.2
45°	385.6	384.0	384.0	385.6	384.0	387.1	387.1	390.1	394.6	397.6	400.6
47.5°	343.4	343.4	343.4	344.9	344.9	346.4	349.4	350.9	353.9	357.0	359.9
50°	304.2	305.8	307.2	307.2	307.2	310.3	313.2	314.8	316.3	317.8	322.3
52.5°	269.6	271.2	271.2	272.6	274.1	275.6	277.2	280.1	281.7	284.6	286.2
55°	236.5	236.5	239.5	241.0	241.0	241.0	244.0	244.0	247.0	248.5	251.5
57.5°	204.8	206.4	206.4	207.8	207.8	209.3	210.9	212.4	213.8	215.4	216.9
60°	174.7	174.7	174.7	176.2	177.8	179.2	177.8	180.7	180.7	183.8	185.2
62.5°	146.1	147.6	147.6	147.6	147.6	147.6	147.6	149.1	150.6	152.1	153.7
65°	119.0	119.0	119.0	117.5	119.0	117.5	119.0	120.4	120.4	122.0	123.5
67.5°	91.8	91.8	88.9	88.9	90.4	90.4	90.4	90.4	88.9	91.8	91.8
70°	66.3	64.8	63.2	61.7	61.7	60.3	60.3	58.7	58.7	58.7	58.7
72.5°	43.7	40.7	37.7	36.2	34.6	34.6	31.7	30.1	31.7	31.7	31.7
75°	22.6	19.6	18.1	16.5	15.0	15.0	13.6	13.6	13.6	13.6	13.6
77.5°	9.0	7.6	6.0	6.0	4.5	4.5	4.5	4.5	4.5	4.5	4.5
80°	3.0	3.0	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
82.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
85°	1.5	0.0	0.0	1.5	0.0	1.5	1.5	1.5	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584011

CATALOG NUMBER: HCC8S20D010SL-HM80520835-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7	1007.7
2.5°	988.0	988.0	986.5	988.0	985.0	986.5	985.0	985.0
5°	965.5	962.4	962.4	962.4	961.0	961.0	959.4	959.4
7.5°	938.3	936.9	935.3	933.8	932.2	930.8	930.8	930.8
10°	911.2	908.2	908.2	906.7	903.6	902.2	902.2	902.2
12.5°	879.5	878.1	876.6	876.6	870.5	872.1	870.5	870.5
15°	849.5	848.0	848.0	843.5	840.4	840.4	840.4	838.9
17.5°	817.8	816.3	814.9	811.8	808.8	808.8	807.3	808.8
20°	784.7	783.2	780.1	780.1	778.7	777.2	774.2	775.6
22.5°	751.5	748.6	747.0	747.0	745.5	745.5	742.5	742.5
25°	716.9	715.5	713.9	715.5	712.4	712.4	709.4	709.4
27.5°	680.7	679.3	679.3	679.3	677.8	679.3	677.8	677.8
30°	644.7	644.7	643.1	643.1	644.7	643.1	644.7	646.1
32.5°	605.4	605.4	607.0	607.0	608.5	608.5	608.5	608.5
35°	564.8	567.8	567.8	569.4	570.8	572.3	572.3	573.9
37.5°	527.2	528.7	530.1	531.7	534.6	534.6	534.6	534.6
40°	486.5	487.9	491.0	489.5	495.5	497.0	495.5	495.5
42.5°	444.3	447.3	448.8	451.9	453.3	456.4	457.9	457.9
45°	405.2	406.6	409.7	412.6	414.2	418.7	418.7	418.7
47.5°	364.5	367.5	369.0	372.0	373.5	378.0	379.5	378.0
50°	325.3	328.4	331.3	331.3	335.9	337.3	340.4	341.8
52.5°	287.7	289.2	292.2	293.7	296.7	299.8	301.2	302.7
55°	251.5	253.1	256.0	256.0	260.5	262.0	265.1	265.1
57.5°	218.4	219.9	222.9	221.4	224.5	227.4	227.4	225.9
60°	186.8	186.8	186.8	189.8	191.2	192.8	194.3	194.3
62.5°	153.7	156.6	158.2	158.2	159.7	161.1	161.1	159.7
65°	123.5	126.5	128.0	128.0	129.5	129.5	129.5	131.1
67.5°	93.4	93.4	93.4	94.9	93.4	93.4	93.4	93.4
70°	58.7	58.7	58.7	58.7	57.2	58.7	58.7	60.3
72.5°	31.7	31.7	31.7	31.7	31.7	31.7	31.7	31.7
75°	13.6	13.6	13.6	15.0	13.6	13.6	13.6	13.6
77.5°	6.0	4.5	6.0	6.0	4.5	4.5	4.5	4.5
80°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
82.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
85°	0.0	1.5	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)