

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593598

Luminaire Tested: **HCC8S20D010SL-HM80520850-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010SL-HM80520850-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2016.5 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593598
CATALOG NUMBER: HCC8S20D010SL-HM80520850-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593598

CATALOG NUMBER: HCC8S20D010SL-HM80520850-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	33383	33383	33383
5°	34761	33310	31907
10°	35921	32884	30348
15°	36834	32132	28773
20°	36907	30797	27345
25°	36283	28852	25933
30°	34339	26620	24718
35°	31312	23938	23208
40°	27224	21105	21431
45°	23357	18277	19620
50°	19947	15759	17625
55°	17489	13575	15306
60°	15572	11576	12871
65°	13820	9442	10273
70°	12253	7005	5842
75°	10222	3658	1728
80°	8044	1154	302
85°	5732	601	0



TEST NUMBER: P593598
 CATALOG NUMBER: HCC8S20D010SL-HM80520850-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	5.1
10°-20°	285.9	14.2
20°-30°	404.7	20.1
30°-40°	423.4	21.0
40°-50°	353.1	17.5
50°-60°	250.4	12.4
60°-70°	144.2	7.2
70°-80°	46.4	2.3
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	792.6	39.3
0°-40°	1215.9	60.3
0°-60°	1819.4	90.2
0°-90°	2016.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2016.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1083	1083	1083	1083	1083	
5°	1123	1108	1076	1044	1031	108
15°	1154	1107	1006	927	901	324
25°	1066	987	848	780	762	487
35°	832	759	636	602	616	516
45°	536	492	419	424	450	415
55°	325	291	252	265	285	294
65°	189	159	129	129	141	189
75°	86	63	31	14	14	93
85°	16	8	2	0	0	20
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593598

CATALOG NUMBER: HCC8S20D010SL-HM80520850-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6
2.5°	1105.2	1103.6	1102.0	1103.6	1102.0	1103.6	1102.0	1102.0	1100.3	1098.8	1098.8
5°	1123.0	1121.4	1121.4	1121.4	1119.8	1118.2	1118.2	1116.5	1113.3	1111.7	1108.5
7.5°	1134.4	1135.9	1135.9	1135.9	1132.7	1132.7	1129.5	1126.2	1123.0	1119.8	1114.9
10°	1147.2	1147.2	1145.7	1144.1	1140.7	1139.2	1137.6	1134.4	1129.5	1123.0	1118.2
12.5°	1152.1	1152.1	1150.6	1147.2	1145.7	1144.1	1142.4	1137.6	1131.1	1123.0	1116.5
15°	1153.8	1150.6	1148.9	1147.2	1144.1	1139.2	1139.2	1132.7	1124.7	1114.9	1106.8
17.5°	1140.7	1142.4	1139.2	1135.9	1131.1	1127.9	1123.0	1118.2	1108.5	1097.1	1089.0
20°	1124.7	1123.0	1121.4	1116.5	1110.0	1108.5	1103.6	1095.5	1087.4	1074.4	1063.1
22.5°	1098.8	1097.1	1093.8	1090.6	1084.1	1080.9	1076.1	1066.4	1055.1	1042.1	1029.2
25°	1066.4	1063.1	1058.2	1051.9	1046.9	1043.7	1037.2	1027.5	1014.6	1000.0	987.1
27.5°	1014.6	1019.5	1016.2	1006.5	1001.6	995.1	993.6	980.6	969.2	954.7	940.2
30°	964.4	964.4	959.5	954.7	946.7	941.8	935.3	925.6	914.3	896.4	885.1
32.5°	901.3	899.7	893.2	891.6	885.1	875.4	873.9	860.9	849.5	836.6	822.1
35°	831.8	828.5	822.1	817.1	813.9	809.1	804.2	792.9	781.5	768.7	759.0
37.5°	752.5	752.5	750.8	742.8	739.5	736.3	731.4	720.1	713.6	700.7	691.0
40°	676.3	674.8	670.0	668.3	665.1	660.3	657.0	650.5	640.8	631.1	621.4
42.5°	602.0	603.5	597.1	598.7	592.3	589.0	587.3	577.6	572.8	563.1	555.1
45°	535.6	534.0	530.7	529.2	525.9	522.7	519.5	514.5	506.5	496.8	491.9
47.5°	474.1	469.3	469.3	467.6	466.1	459.6	457.9	453.1	448.2	438.5	432.0
50°	415.8	415.8	415.8	414.3	409.4	407.8	404.6	399.6	394.8	388.4	378.6
52.5°	368.9	368.9	368.9	367.4	360.9	359.2	357.7	351.2	344.7	339.8	333.3
55°	325.3	326.8	325.3	322.0	317.1	317.1	312.3	309.1	302.6	297.7	291.2
57.5°	288.1	288.1	284.7	283.2	279.9	278.4	275.1	271.9	263.7	258.9	250.8
60°	252.5	250.8	250.8	247.6	244.3	241.1	239.5	234.6	231.4	223.3	216.8
62.5°	220.1	220.1	216.8	216.8	210.4	210.4	208.7	203.9	199.0	190.9	187.7
65°	189.4	189.4	187.7	186.0	181.2	179.7	178.0	173.2	168.3	163.5	158.6
67.5°	161.8	161.8	158.6	157.0	153.8	152.1	148.8	145.6	140.8	135.9	131.1
70°	135.9	134.3	132.7	131.1	127.9	126.2	122.9	119.7	114.9	111.7	106.9
72.5°	110.0	110.0	108.4	105.2	103.5	101.9	100.4	97.0	92.2	87.3	84.2
75°	85.8	85.8	85.8	82.5	79.3	77.7	77.7	74.5	71.2	66.3	63.1
77.5°	66.3	64.8	63.1	63.1	59.9	58.3	56.6	55.0	50.1	48.6	45.3
80°	45.3	46.9	45.3	43.7	42.1	40.4	40.4	37.2	35.6	32.4	29.1
82.5°	30.7	29.1	29.1	27.5	27.5	25.9	25.9	22.7	21.0	19.4	17.8
85°	16.2	16.2	14.5	14.5	14.5	13.0	13.0	11.3	11.3	9.7	8.0
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593598

CATALOG NUMBER: HCC8S20D010SL-HM80520850-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6
2.5°	1097.1	1093.8	1092.3	1092.3	1090.6	1089.0	1087.4	1085.8	1082.6	1082.6	1079.3
5°	1105.2	1102.0	1100.3	1095.5	1092.3	1092.3	1085.8	1084.1	1079.3	1076.1	1072.9
7.5°	1111.7	1105.2	1100.3	1095.5	1092.3	1089.0	1082.6	1076.1	1069.6	1063.1	1059.9
10°	1111.7	1105.2	1097.1	1089.0	1085.8	1082.6	1074.4	1064.7	1056.7	1050.2	1042.1
12.5°	1108.5	1098.8	1089.0	1082.6	1076.1	1071.2	1061.6	1051.9	1042.1	1029.2	1022.7
15°	1098.8	1085.8	1076.1	1064.7	1059.9	1051.9	1043.7	1029.2	1017.8	1006.5	998.4
17.5°	1079.3	1063.1	1051.9	1040.5	1032.4	1027.5	1014.6	1001.6	988.7	975.7	966.0
20°	1050.2	1035.7	1022.7	1008.1	1001.6	995.1	978.9	966.0	953.0	938.5	928.8
22.5°	1014.6	1000.0	982.2	970.9	961.2	953.0	938.5	924.0	911.0	898.1	885.1
25°	970.9	956.4	940.2	922.3	915.9	907.8	891.6	877.0	862.5	848.0	836.6
27.5°	924.0	904.6	891.6	872.2	865.7	857.7	839.8	823.6	810.7	799.4	786.4
30°	867.4	852.8	835.0	817.1	810.7	802.6	788.0	773.5	760.5	747.6	734.6
32.5°	805.9	791.2	773.5	760.5	750.8	744.3	729.8	716.9	703.9	691.0	679.6
35°	741.1	724.9	712.0	699.0	691.0	682.8	668.3	657.0	647.3	635.9	624.6
37.5°	674.8	663.5	650.5	635.9	627.9	621.4	610.0	597.1	589.0	579.3	571.3
40°	610.0	597.1	585.8	572.8	566.4	561.4	550.2	540.4	532.4	524.3	519.5
42.5°	543.7	532.4	521.0	513.0	508.1	503.3	495.1	483.8	478.9	470.9	466.1
45°	482.3	472.4	464.4	453.1	449.9	446.6	436.9	428.8	424.0	419.1	415.8
47.5°	424.0	417.5	407.8	401.3	396.4	393.3	386.8	380.2	375.4	372.2	368.9
50°	373.7	365.7	359.2	352.7	349.5	344.7	338.2	335.0	331.7	328.5	328.5
52.5°	326.8	318.8	312.3	307.4	304.2	300.9	296.1	294.6	291.2	291.2	289.7
55°	283.2	278.4	271.9	265.4	263.7	262.2	258.9	255.7	254.0	252.5	254.0
57.5°	246.0	241.1	234.6	229.8	228.1	226.6	224.9	221.7	220.1	220.1	220.1
60°	211.9	207.1	202.2	197.4	197.4	194.2	192.5	190.9	189.4	187.7	187.7
62.5°	181.2	176.4	171.5	168.3	166.7	165.0	161.8	160.2	158.6	158.6	157.0
65°	153.8	147.3	145.6	140.8	139.1	137.6	135.9	132.7	131.1	129.4	127.9
67.5°	126.2	122.9	118.1	114.9	113.2	111.7	110.0	106.9	105.2	103.5	100.4
70°	101.9	98.7	95.5	92.2	90.7	89.0	85.8	82.5	81.0	77.7	72.8
72.5°	79.3	76.0	72.8	69.6	68.0	66.3	63.1	59.9	56.6	53.4	50.1
75°	59.9	56.6	51.8	48.6	46.9	46.9	42.1	38.9	35.6	30.7	27.5
77.5°	42.1	37.2	35.6	32.4	30.7	27.5	24.2	21.0	17.8	16.2	13.0
80°	27.5	24.2	21.0	19.4	17.8	16.2	14.5	11.3	8.0	6.5	4.8
82.5°	16.2	14.5	13.0	11.3	9.7	8.0	6.5	6.5	4.8	3.2	1.7
85°	8.0	6.5	4.8	4.8	3.2	3.2	3.2	1.7	1.7	1.7	1.7
87.5°	3.2	1.7	1.7	1.7	1.7	1.7	1.7	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593598

CATALOG NUMBER: HCC8S20D010SL-HM80520850-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6
2.5°	1077.7	1076.1	1074.4	1072.9	1072.9	1069.6	1069.6	1067.9	1064.7	1063.1	1063.1
5°	1067.9	1063.1	1059.9	1058.2	1056.7	1051.9	1050.2	1046.9	1043.7	1040.5	1038.9
7.5°	1053.4	1045.4	1042.1	1040.5	1035.7	1030.8	1027.5	1022.7	1017.8	1013.0	1011.3
10°	1035.7	1027.5	1019.5	1016.2	1011.3	1008.1	1001.6	995.1	990.3	985.4	980.6
12.5°	1013.0	1003.3	995.1	991.9	987.1	980.6	970.9	967.7	959.5	956.4	949.9
15°	987.1	975.7	967.7	962.9	958.0	948.2	941.8	935.3	927.2	924.0	917.5
17.5°	954.7	941.8	933.7	928.8	925.6	917.5	907.8	899.7	891.6	888.4	883.5
20°	915.9	907.8	896.4	891.6	888.4	878.7	869.0	865.7	859.2	852.8	848.0
22.5°	872.2	864.0	852.8	848.0	846.3	838.2	830.1	825.3	820.4	815.6	810.7
25°	826.9	817.1	807.4	804.2	801.0	794.5	788.0	784.8	780.0	776.7	773.5
27.5°	778.3	768.7	760.5	755.7	752.5	747.6	744.3	741.1	737.9	734.6	733.1
30°	726.6	716.9	710.4	707.2	703.9	702.2	697.4	695.8	694.2	691.0	692.5
32.5°	674.8	666.6	660.3	655.3	655.3	652.1	650.5	650.5	648.9	648.9	648.9
35°	618.2	613.3	608.4	606.8	605.2	603.5	602.0	603.5	602.0	603.5	605.2
37.5°	566.4	561.4	558.3	556.6	555.1	556.6	555.1	555.1	556.6	559.9	561.4
40°	513.0	509.7	506.5	508.1	506.5	506.5	506.5	511.3	513.0	514.5	516.2
42.5°	462.8	459.6	457.9	457.9	459.6	457.9	461.2	462.8	466.1	470.9	474.1
45°	414.3	412.6	412.6	414.3	412.6	415.8	415.8	419.1	424.0	427.2	430.5
47.5°	368.9	368.9	368.9	370.6	370.6	372.2	375.4	377.1	380.2	383.6	386.8
50°	326.8	328.5	330.1	330.1	330.1	333.3	336.6	338.2	339.8	341.5	346.3
52.5°	289.7	291.2	291.2	292.9	294.6	296.1	297.7	300.9	302.6	305.8	307.4
55°	254.0	254.0	257.3	258.9	258.9	258.9	262.2	262.2	265.4	267.0	270.2
57.5°	220.1	221.7	221.7	223.3	223.3	224.9	226.6	228.1	229.8	231.4	233.0
60°	187.7	187.7	187.7	189.4	190.9	192.5	190.9	194.2	194.2	197.4	199.0
62.5°	157.0	158.6	158.6	158.6	158.6	158.6	158.6	160.2	161.8	163.5	165.0
65°	127.9	127.9	127.9	126.2	127.9	126.2	127.9	129.4	129.4	131.1	132.7
67.5°	98.7	98.7	95.5	95.5	97.0	97.0	97.0	97.0	95.5	98.7	98.7
70°	71.2	69.6	68.0	66.3	66.3	64.8	64.8	63.1	63.1	63.1	63.1
72.5°	46.9	43.7	40.4	38.9	37.2	37.2	33.9	32.4	33.9	33.9	33.9
75°	24.2	21.0	19.4	17.8	16.2	16.2	14.5	14.5	14.5	14.5	14.5
77.5°	9.7	8.0	6.5	6.5	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	3.2	3.2	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	1.7	0.0	0.0	1.7	0.0	1.7	1.7	1.7	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593598

CATALOG NUMBER: HCC8S20D010SL-HM80520850-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6
2.5°	1061.6	1061.6	1059.9	1061.6	1058.2	1059.9	1058.2	1058.2
5°	1037.2	1034.0	1034.0	1034.0	1032.4	1032.4	1030.8	1030.8
7.5°	1008.1	1006.5	1004.9	1003.3	1001.6	1000.0	1000.0	1000.0
10°	978.9	975.7	975.7	974.1	970.9	969.2	969.2	969.2
12.5°	945.0	943.4	941.8	941.8	935.3	937.0	935.3	935.3
15°	912.6	911.0	911.0	906.1	902.9	902.9	902.9	901.3
17.5°	878.7	877.0	875.4	872.2	869.0	869.0	867.4	869.0
20°	843.1	841.5	838.2	838.2	836.6	835.0	831.8	833.3
22.5°	807.4	804.2	802.6	802.6	801.0	801.0	797.7	797.7
25°	770.2	768.7	767.0	768.7	765.3	765.3	762.2	762.2
27.5°	731.4	729.8	729.8	729.8	728.2	729.8	728.2	728.2
30°	692.5	692.5	691.0	691.0	692.5	691.0	692.5	694.2
32.5°	650.5	650.5	652.1	652.1	653.8	653.8	653.8	653.8
35°	606.8	610.0	610.0	611.7	613.3	614.9	614.9	616.5
37.5°	566.4	568.0	569.6	571.3	574.5	574.5	574.5	574.5
40°	522.7	524.3	527.5	525.9	532.4	534.0	532.4	532.4
42.5°	477.4	480.6	482.3	485.4	487.1	490.3	491.9	491.9
45°	435.3	436.9	440.2	443.4	445.0	449.9	449.9	449.9
47.5°	391.6	394.8	396.4	399.6	401.3	406.1	407.8	406.1
50°	349.5	352.7	356.0	356.0	360.9	362.5	365.7	367.4
52.5°	309.1	310.6	313.9	315.6	318.8	322.0	323.6	325.3
55°	270.2	271.9	275.1	275.1	279.9	281.6	284.7	284.7
57.5°	234.6	236.3	239.5	237.8	241.1	244.3	244.3	242.8
60°	200.7	200.7	200.7	203.9	205.5	207.1	208.7	208.7
62.5°	165.0	168.3	169.9	169.9	171.5	173.2	173.2	171.5
65°	132.7	135.9	137.6	137.6	139.1	139.1	139.1	140.8
67.5°	100.4	100.4	100.4	101.9	100.4	100.4	100.4	100.4
70°	63.1	63.1	63.1	63.1	61.5	63.1	63.1	64.8
72.5°	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9
75°	14.5	14.5	14.5	16.2	14.5	14.5	14.5	14.5
77.5°	6.5	4.8	6.5	6.5	4.8	4.8	4.8	4.8
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	0.0	1.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)