

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584038

Luminaire Tested: **HCC8S20D010MW-HM80520927-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MW-HM80520927-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1683.1 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584038
CATALOG NUMBER: HCC8S20D010MW-HM80520927-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584038

CATALOG NUMBER: HCC8S20D010MW-HM80520927-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47																			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	27312	27312	27312
5°	27670	27193	26936
10°	27955	26916	26506
15°	28237	26347	25817
20°	28090	25376	24792
25°	27437	23858	23534
30°	26061	22147	22062
35°	23723	20211	20388
40°	20799	18086	18750
45°	17945	16087	17221
50°	15711	14123	15601
55°	13924	12145	13731
60°	12544	10207	11379
65°	11295	8194	8712
70°	9909	5969	4796
75°	8447	3098	1263
80°	6499	835	213
85°	4175	0	0



TEST NUMBER: P584038
 CATALOG NUMBER: HCC8S20D010MW-HM80520927-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	5.0
10°-20°	234.9	14.0
20°-30°	333.4	19.8
30°-40°	351.0	20.9
40°-50°	298.5	17.7
50°-60°	215.8	12.8
60°-70°	122.7	7.3
70°-80°	38.6	2.3
80°-90°	4.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	651.8	38.7
0°-40°	1002.8	59.6
0°-60°	1517.1	90.1
0°-90°	1683.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1683.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	886	886	886	886	886	
5°	894	889	878	873	870	85
15°	884	862	825	810	809	249
25°	806	766	701	689	692	369
35°	630	594	537	533	542	392
45°	412	396	369	378	395	320
55°	259	240	226	239	255	234
65°	155	134	112	111	119	154
75°	71	54	26	12	11	76
85°	12	7	0	0	0	15
90°	0	0	0	0	0	



TEST NUMBER: P584038

CATALOG NUMBER: HCC8S20D010MW-HM80520927-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7
2.5°	890.4	891.6	889.2	889.2	891.6	889.2	890.4	890.4	889.2	889.2	888.0
5°	893.9	892.8	892.8	892.8	893.9	891.6	890.4	891.6	889.2	889.2	889.2
7.5°	895.1	895.1	893.9	892.8	892.8	892.8	891.6	890.4	889.2	886.9	885.7
10°	892.8	892.8	893.9	891.6	891.6	889.2	889.2	886.9	886.9	884.5	880.8
12.5°	890.4	889.2	889.2	886.9	886.9	884.5	884.5	880.8	879.6	876.1	872.6
15°	884.5	883.3	880.8	879.6	878.5	877.3	874.9	873.7	870.2	865.5	861.9
17.5°	872.6	871.4	870.2	867.8	865.5	864.3	863.1	859.6	854.8	851.3	845.4
20°	856.0	854.8	854.8	851.3	850.1	846.5	845.4	840.6	837.1	830.0	825.3
22.5°	833.5	834.7	832.4	830.0	827.6	824.1	821.7	817.0	811.1	804.0	798.1
25°	806.4	807.5	805.2	802.8	799.3	796.9	794.5	787.4	781.5	773.3	766.2
27.5°	772.1	772.1	772.1	769.7	763.8	762.6	760.3	753.2	744.9	737.8	730.7
30°	731.9	730.7	730.7	727.2	724.8	720.1	716.5	710.6	704.7	696.4	688.2
32.5°	683.4	684.6	681.1	678.7	675.2	675.2	670.4	665.7	658.6	650.3	642.1
35°	630.2	631.4	629.1	627.9	622.0	620.8	619.6	613.7	609.0	603.1	593.6
37.5°	575.9	574.7	573.5	573.5	570.0	567.6	565.2	561.7	554.6	549.9	545.1
40°	516.7	516.7	516.7	515.5	514.3	511.9	510.7	508.4	503.7	498.9	495.4
42.5°	463.5	463.5	462.3	461.1	458.7	459.9	457.6	455.2	450.5	446.9	444.6
45°	411.5	411.5	411.5	412.6	410.3	406.7	406.7	404.4	402.0	399.6	396.1
47.5°	365.4	368.9	366.5	365.4	366.5	361.8	361.8	359.4	357.1	354.7	350.0
50°	327.5	327.5	327.5	325.2	324.0	324.0	320.4	318.1	316.9	314.5	309.8
52.5°	293.3	290.9	290.9	289.7	288.5	286.2	286.2	283.8	279.1	276.7	273.2
55°	259.0	259.0	257.8	256.6	255.4	254.2	253.1	249.5	247.2	243.6	240.1
57.5°	228.2	230.6	229.4	227.1	224.7	224.7	222.3	220.0	216.4	212.9	209.3
60°	203.4	202.2	202.2	201.1	198.7	197.5	196.3	192.8	189.2	185.7	182.1
62.5°	177.4	177.4	177.4	174.9	172.6	171.4	170.2	167.8	163.1	159.6	157.2
65°	154.8	153.7	152.5	151.3	150.1	147.8	146.6	144.2	140.7	137.1	133.6
67.5°	132.4	131.2	131.2	130.0	126.5	125.3	125.3	121.7	118.2	114.7	111.1
70°	109.9	109.9	109.9	107.6	106.4	105.2	104.0	101.7	98.1	94.6	91.0
72.5°	91.0	89.8	89.8	88.6	85.1	83.9	82.7	80.4	76.8	74.5	72.1
75°	70.9	70.9	69.7	68.6	67.4	66.2	65.0	62.6	59.1	55.6	54.4
77.5°	54.4	53.2	53.2	52.0	49.6	48.5	48.5	46.1	42.6	40.2	37.8
80°	36.6	37.8	36.6	35.5	34.3	33.1	31.9	30.7	28.4	26.0	23.6
82.5°	22.5	23.6	22.5	22.5	21.3	20.1	20.1	17.7	16.5	15.4	14.2
85°	11.8	11.8	11.8	11.8	10.6	10.6	10.6	9.5	8.3	7.1	7.1
87.5°	3.5	4.7	3.5	3.5	3.5	3.5	3.5	3.5	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584038

CATALOG NUMBER: HCC8S20D010MW-HM80520927-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7
2.5°	889.2	888.0	886.9	886.9	886.9	886.9	886.9	885.7	884.5	884.5	884.5
5°	886.9	886.9	886.9	885.7	884.5	884.5	882.1	880.8	879.6	878.5	877.3
7.5°	884.5	882.1	880.8	879.6	878.5	878.5	876.1	873.7	873.7	871.4	869.0
10°	877.3	876.1	873.7	871.4	870.2	869.0	866.6	863.1	861.9	859.6	857.2
12.5°	869.0	866.6	864.3	859.6	858.4	857.2	852.5	848.9	846.5	845.4	839.5
15°	858.4	853.6	850.1	844.2	843.0	840.6	837.1	833.5	828.8	825.3	822.9
17.5°	839.5	834.7	828.8	822.9	820.5	820.5	814.6	809.9	804.0	801.6	796.9
20°	817.0	811.1	806.4	799.3	795.7	792.2	788.6	781.5	776.8	773.3	767.4
22.5°	791.0	782.7	776.8	769.7	763.8	760.3	754.4	748.4	742.5	739.0	734.3
25°	757.9	750.8	741.4	734.3	730.7	726.0	718.9	713.0	707.1	701.2	698.8
27.5°	721.3	711.8	703.5	695.3	691.7	688.2	679.9	672.8	668.1	662.2	659.8
30°	681.1	671.6	662.2	655.1	651.5	645.6	640.9	632.6	626.7	622.0	616.1
32.5°	635.0	627.9	619.6	609.0	606.6	601.9	594.8	591.2	584.1	580.6	575.9
35°	585.3	580.6	572.3	564.1	560.5	558.1	552.2	545.1	540.4	536.9	534.5
37.5°	538.0	532.1	523.7	517.8	515.5	511.9	504.8	501.3	496.6	494.2	489.5
40°	487.1	481.2	475.3	471.7	468.2	465.8	461.1	457.6	452.8	449.3	448.1
42.5°	437.5	433.9	429.2	424.5	423.3	419.7	417.4	413.8	410.3	409.1	405.5
45°	392.5	389.0	384.3	379.5	378.4	376.0	374.8	371.3	368.9	368.9	368.9
47.5°	347.6	344.1	339.4	337.0	338.2	333.4	333.4	332.3	329.9	329.9	331.1
50°	307.4	302.7	301.5	299.2	296.8	294.4	295.6	292.1	292.1	294.4	293.3
52.5°	269.6	264.9	263.7	261.3	260.2	260.2	259.0	259.0	257.8	259.0	259.0
55°	235.3	231.8	229.4	227.1	225.9	225.9	225.9	224.7	223.5	225.9	227.1
57.5°	204.6	203.4	201.1	197.5	196.3	195.1	194.0	194.0	194.0	194.0	195.1
60°	177.4	174.9	172.6	169.0	169.0	167.8	166.7	165.5	165.5	165.5	165.5
62.5°	153.7	150.1	146.6	144.2	143.0	141.8	140.7	138.3	138.3	138.3	138.3
65°	130.0	126.5	124.1	121.7	119.4	119.4	117.0	115.8	113.5	112.3	109.9
67.5°	107.6	105.2	102.8	99.3	98.1	96.9	94.6	93.4	89.8	88.6	87.5
70°	87.5	83.9	81.6	79.2	78.0	75.6	73.3	70.9	68.6	66.2	63.8
72.5°	68.6	65.0	62.6	60.3	57.9	57.9	54.4	52.0	48.5	46.1	42.6
75°	50.8	47.3	44.9	41.4	40.2	39.0	35.5	33.1	29.6	26.0	23.6
77.5°	34.3	31.9	29.6	26.0	23.6	23.6	20.1	17.7	15.4	11.8	10.6
80°	21.3	18.9	16.5	14.2	14.2	11.8	10.6	8.3	5.9	4.7	3.5
82.5°	11.8	10.6	9.5	7.1	7.1	5.9	4.7	3.5	2.4	1.2	1.2
85°	5.9	4.7	3.5	3.5	2.4	2.4	2.4	1.2	1.2	0.0	0.0
87.5°	2.4	1.2	1.2	1.2	1.2	1.2	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584038

CATALOG NUMBER: HCC8S20D010MW-HM80520927-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7
2.5°	883.3	883.3	882.1	882.1	882.1	880.8	882.1	880.8	880.8	880.8	882.1
5°	878.5	876.1	876.1	874.9	874.9	873.7	874.9	873.7	872.6	871.4	872.6
7.5°	869.0	866.6	865.5	864.3	864.3	864.3	863.1	861.9	863.1	859.6	861.9
10°	856.0	854.8	852.5	851.3	850.1	851.3	850.1	847.7	847.7	847.7	846.5
12.5°	839.5	837.1	835.9	834.7	832.4	832.4	833.5	831.2	831.2	828.8	828.8
15°	819.4	817.0	814.6	814.6	812.3	812.3	811.1	811.1	809.9	808.7	808.7
17.5°	794.5	791.0	788.6	789.8	788.6	787.4	787.4	785.1	783.9	785.1	785.1
20°	765.0	762.6	760.3	761.4	759.1	757.9	759.1	755.5	756.7	756.7	756.7
22.5°	731.9	730.7	727.2	727.2	724.8	723.6	724.8	724.8	726.0	724.8	724.8
25°	695.3	692.9	690.5	690.5	689.3	688.2	689.3	690.5	689.3	690.5	690.5
27.5°	656.2	652.7	652.7	650.3	650.3	651.5	650.3	651.5	652.7	652.7	655.1
30°	613.7	612.5	611.3	610.1	610.1	611.3	611.3	611.3	612.5	614.9	614.9
32.5°	573.5	571.1	568.8	568.8	571.1	570.0	571.1	571.1	573.5	573.5	575.9
35°	529.8	529.8	527.3	528.5	528.5	528.5	528.5	531.0	533.3	534.5	536.9
37.5°	489.5	485.9	487.1	487.1	488.3	487.1	490.6	490.6	493.0	493.0	495.4
40°	445.7	445.7	446.9	445.7	446.9	446.9	449.3	451.6	452.8	455.2	456.4
42.5°	404.4	406.7	404.4	405.5	406.7	407.9	409.1	410.3	415.0	417.4	420.9
45°	366.5	367.7	368.9	370.1	368.9	371.3	372.4	374.8	378.4	379.5	380.7
47.5°	329.9	331.1	332.3	333.4	333.4	335.8	337.0	339.4	341.7	342.9	344.1
50°	294.4	296.8	298.0	298.0	299.2	301.5	303.9	303.9	306.3	309.8	311.0
52.5°	262.5	262.5	264.9	266.1	267.3	267.3	270.8	272.0	273.2	275.5	277.9
55°	227.1	230.6	231.8	231.8	234.2	236.5	237.7	238.9	238.9	243.6	243.6
57.5°	196.3	197.5	199.9	199.9	199.9	203.4	203.4	205.8	207.0	208.2	210.5
60°	165.5	167.8	167.8	169.0	167.8	170.2	171.4	173.8	174.9	176.1	177.4
62.5°	137.1	137.1	138.3	138.3	138.3	138.3	140.7	140.7	143.0	144.2	145.4
65°	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9	111.1	111.1	113.5
67.5°	85.1	83.9	81.6	82.7	81.6	81.6	80.4	80.4	81.6	81.6	83.9
70°	61.5	60.3	57.9	57.9	56.7	55.6	54.4	53.2	52.0	52.0	52.0
72.5°	40.2	37.8	34.3	33.1	33.1	30.7	28.4	27.2	27.2	27.2	27.2
75°	20.1	17.7	15.4	14.2	14.2	11.8	13.0	11.8	11.8	11.8	11.8
77.5°	8.3	5.9	4.7	4.7	4.7	3.5	3.5	3.5	3.5	3.5	3.5
80°	2.4	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
82.5°	1.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584038

CATALOG NUMBER: HCC8S20D010MW-HM80520927-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	885.7	885.7	885.7	885.7	885.7	885.7	885.7	885.7
2.5°	880.8	880.8	878.5	879.6	879.6	879.6	879.6	879.6
5°	870.2	871.4	870.2	871.4	871.4	870.2	870.2	870.2
7.5°	859.6	860.7	859.6	860.7	860.7	860.7	859.6	859.6
10°	846.5	846.5	846.5	846.5	846.5	845.4	846.5	846.5
12.5°	828.8	828.8	828.8	830.0	830.0	828.8	828.8	827.6
15°	809.9	807.5	808.7	809.9	808.7	808.7	808.7	808.7
17.5°	783.9	785.1	783.9	783.9	783.9	783.9	785.1	783.9
20°	756.7	756.7	757.9	756.7	756.7	756.7	756.7	755.5
22.5°	726.0	724.8	724.8	726.0	726.0	724.8	726.0	726.0
25°	691.7	692.9	691.7	691.7	692.9	692.9	692.9	691.7
27.5°	655.1	656.2	657.4	656.2	656.2	656.2	657.4	658.6
30°	617.2	619.6	617.2	617.2	619.6	618.4	619.6	619.6
32.5°	577.1	580.6	578.2	580.6	580.6	581.8	580.6	581.8
35°	536.9	540.4	540.4	540.4	541.6	542.8	542.8	541.6
37.5°	498.9	500.1	500.1	502.5	503.7	504.8	504.8	503.7
40°	459.9	462.3	463.5	463.5	463.5	465.8	468.2	465.8
42.5°	422.1	423.3	424.5	424.5	426.8	428.0	429.2	429.2
45°	385.5	387.8	389.0	390.2	391.4	393.7	392.5	394.9
47.5°	347.6	351.2	352.4	353.5	355.9	357.1	358.3	359.4
50°	313.3	315.7	315.7	318.1	321.6	321.6	324.0	325.2
52.5°	279.1	280.3	281.4	282.6	285.0	287.3	287.3	289.7
55°	246.0	247.2	247.2	248.3	249.5	254.2	255.4	255.4
57.5°	211.7	211.7	214.1	215.2	216.4	218.8	218.8	218.8
60°	178.6	179.8	179.8	181.0	182.1	184.5	185.7	184.5
62.5°	145.4	146.6	146.6	147.8	150.1	151.3	150.1	150.1
65°	114.7	115.8	115.8	117.0	119.4	119.4	118.2	119.4
67.5°	83.9	83.9	83.9	83.9	83.9	83.9	83.9	83.9
70°	53.2	52.0	50.8	52.0	52.0	52.0	50.8	53.2
72.5°	26.0	27.2	27.2	27.2	27.2	27.2	27.2	26.0
75°	11.8	11.8	10.6	10.6	10.6	11.8	11.8	10.6
77.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
80°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)