

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584064

Luminaire Tested: **HCC8W20D010BZ-HM80520930-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584064  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W20D010BZ-HM80520930-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1853.6 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584064  
CATALOG NUMBER: HCC8W20D010BZ-HM80520930-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584064

CATALOG NUMBER: HCC8W20D010BZ-HM80520930-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	28419	28419	28419
5°	29459	28326	27354
10°	30294	28081	26233
15°	30970	27582	25073
20°	31014	26508	24057
25°	30424	25032	23204
30°	28856	23216	22190
35°	26215	21141	21190
40°	22925	18972	19974
45°	19864	16899	18612
50°	17395	15011	16954
55°	15489	13301	15338
60°	13969	11946	13488
65°	12608	10507	11747
70°	11324	8854	8736
75°	9984	7017	6553
80°	8382	5807	6269
85°	6475	5095	5555



TEST NUMBER: P584064  
 CATALOG NUMBER: HCC8W20D010BZ-HM80520930-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.9	4.7
10°-20°	244.9	13.2
20°-30°	350.0	18.9
30°-40°	371.9	20.1
40°-50°	320.2	17.3
50°-60°	239.4	12.9
60°-70°	152.7	8.2
70°-80°	69.5	3.7
80°-90°	18.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.8	36.8
0°-40°	1053.7	56.8
0°-60°	1613.2	87.0
0°-90°	1853.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1853.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	922	922	922	922	922	
5°	952	939	915	892	884	91
15°	970	937	864	805	785	273
25°	894	838	736	691	682	409
35°	696	648	562	547	563	434
45°	456	431	388	398	427	354
55°	288	264	247	268	285	259
65°	173	153	144	151	161	172
75°	84	72	59	54	55	89
85°	18	16	14	16	16	22
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584064

CATALOG NUMBER: HCC8W20D010BZ-HM80520930-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6
2.5°	938.6	936.0	937.3	936.0	937.3	937.3	934.7	934.7	934.7	934.7	930.8
5°	951.7	950.4	950.4	949.1	947.8	949.1	947.8	946.5	943.8	942.5	938.6
7.5°	959.5	959.5	959.5	959.5	958.2	956.9	955.6	953.0	950.4	947.8	945.1
10°	967.5	968.8	967.5	966.2	964.9	962.1	960.8	958.2	954.3	950.4	947.8
12.5°	971.4	971.4	970.1	970.1	967.5	966.2	962.1	958.2	954.3	950.4	943.8
15°	970.1	970.1	968.8	967.5	963.6	962.1	959.5	955.6	949.1	943.8	937.3
17.5°	962.1	960.8	958.2	958.2	953.0	951.7	949.1	943.8	937.3	929.5	921.6
20°	945.1	945.1	943.8	942.5	937.3	933.4	930.8	924.2	919.0	909.8	902.0
22.5°	921.6	924.2	921.6	919.0	912.5	911.1	907.2	899.4	891.5	881.1	871.8
25°	894.2	892.8	891.5	888.9	883.7	881.1	875.7	867.9	860.1	848.3	837.8
27.5°	858.7	853.5	853.5	848.3	844.4	840.4	837.8	830.0	819.5	810.4	797.3
30°	810.4	811.7	805.1	803.8	797.3	794.7	789.3	781.5	772.3	761.9	751.4
32.5°	758.0	754.0	754.0	748.8	743.6	739.7	738.4	729.2	721.4	710.9	700.3
35°	696.4	696.4	692.5	691.2	686.0	683.3	679.4	674.2	665.0	655.9	648.0
37.5°	636.3	633.6	632.3	629.7	625.8	621.9	621.9	612.6	611.3	600.9	590.4
40°	569.5	572.1	569.5	565.6	564.3	561.6	560.3	555.1	551.2	541.9	535.4
42.5°	513.2	510.5	510.5	509.2	504.0	504.0	501.4	498.8	492.2	489.6	481.8
45°	455.5	458.1	454.2	455.5	450.3	450.3	450.3	445.1	439.8	435.9	430.7
47.5°	405.8	407.1	407.1	403.2	401.9	401.9	399.3	396.7	392.8	387.5	383.6
50°	362.6	363.9	361.3	360.0	357.4	356.1	356.1	350.8	348.2	343.0	340.4
52.5°	323.4	323.4	322.1	322.1	318.1	318.1	315.5	311.6	309.0	306.4	299.8
55°	288.1	288.1	286.8	285.3	285.3	281.4	280.1	276.2	273.6	268.3	264.4
57.5°	254.0	255.3	254.0	252.7	251.3	250.0	247.4	243.5	240.9	237.0	234.3
60°	226.5	226.5	225.2	223.9	221.3	220.0	218.7	216.0	212.1	209.5	205.5
62.5°	200.3	198.9	197.6	196.3	193.7	193.7	191.1	188.5	184.6	181.9	179.3
65°	172.8	172.8	171.5	171.5	170.2	167.6	166.3	165.0	159.7	158.4	153.2
67.5°	148.0	149.3	146.6	146.6	144.0	144.0	142.7	138.8	137.5	134.9	132.3
70°	125.6	125.6	125.6	124.3	121.7	120.4	119.1	116.5	115.2	112.5	109.9
72.5°	103.4	103.4	102.1	102.1	100.8	99.5	98.2	95.6	95.6	92.9	90.3
75°	83.8	83.8	82.5	81.2	79.9	79.9	78.6	77.2	74.6	73.3	72.0
77.5°	64.2	64.2	64.2	62.9	61.6	61.6	61.6	58.9	56.3	56.3	55.0
80°	47.2	47.2	45.9	45.9	44.6	44.6	44.6	43.1	41.8	40.5	39.2
82.5°	31.4	31.4	31.4	31.4	30.1	30.1	30.1	28.8	27.5	27.5	27.5
85°	18.3	18.3	18.3	18.3	17.0	17.0	17.0	17.0	17.0	15.7	15.7
87.5°	7.8	6.5	7.8	6.5	7.8	6.5	7.8	6.5	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584064

CATALOG NUMBER: HCC8W20D010BZ-HM80520930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6
2.5°	932.1	930.8	929.5	928.1	928.1	926.8	924.2	922.9	921.6	920.3	920.3
5°	937.3	936.0	933.4	930.8	929.5	926.8	924.2	921.6	919.0	915.1	913.8
7.5°	941.2	937.3	934.7	929.5	928.1	925.5	921.6	917.7	912.5	907.2	903.3
10°	941.2	936.0	932.1	925.5	922.9	920.3	915.1	908.5	902.0	896.8	890.2
12.5°	938.6	932.1	925.5	919.0	915.1	911.1	903.3	896.8	888.9	881.1	875.7
15°	929.5	921.6	913.8	905.9	902.0	896.8	888.9	879.8	871.8	864.0	854.8
17.5°	912.5	904.6	895.5	886.3	881.1	877.2	865.3	858.7	847.0	839.1	831.3
20°	890.2	881.1	869.2	860.1	853.5	849.6	840.4	828.7	819.5	807.8	799.9
22.5°	861.4	849.6	837.8	828.7	822.1	816.9	805.1	793.4	785.4	775.0	765.8
25°	827.4	815.6	803.8	790.8	784.1	778.9	768.4	758.0	747.5	735.7	727.9
27.5°	786.7	773.7	763.2	751.4	744.9	737.0	725.3	714.8	704.4	696.4	686.0
30°	742.3	727.9	717.4	705.7	699.0	692.5	680.7	670.3	661.1	652.0	646.7
32.5°	688.6	678.1	667.6	655.9	650.6	646.7	635.0	624.5	613.9	606.1	602.2
35°	637.6	625.8	616.6	606.1	599.6	595.6	585.2	576.0	570.8	561.6	556.4
37.5°	583.9	574.7	564.3	553.8	549.9	545.8	538.0	528.8	521.0	514.5	511.8
40°	527.5	519.7	510.5	504.0	500.1	496.2	489.6	483.1	477.9	471.3	468.7
42.5°	473.9	468.7	460.9	452.9	449.0	447.7	439.8	434.6	432.0	429.4	426.8
45°	425.5	417.6	412.4	407.1	403.2	400.6	396.7	392.8	390.1	387.5	384.9
47.5°	378.4	371.7	366.5	362.6	358.7	357.4	354.7	350.8	348.2	348.2	348.2
50°	335.1	329.9	324.7	322.1	320.7	318.1	315.5	314.2	312.9	312.9	312.9
52.5°	297.2	292.0	288.1	285.3	285.3	282.7	280.1	278.8	278.8	278.8	278.8
55°	261.8	257.9	255.3	252.7	250.0	248.7	248.7	248.7	247.4	247.4	248.7
57.5°	230.4	227.8	223.9	221.3	220.0	220.0	218.7	217.4	218.7	220.0	221.3
60°	201.6	198.9	197.6	193.7	193.7	193.7	192.4	192.4	192.4	193.7	195.0
62.5°	175.4	174.1	171.5	170.2	168.9	168.9	167.6	167.6	167.6	167.6	168.9
65°	151.9	149.3	146.6	146.6	146.6	145.3	145.3	142.7	144.0	144.0	142.7
67.5°	129.5	126.9	125.6	124.3	123.0	123.0	121.7	120.4	119.1	119.1	119.1
70°	108.6	106.0	106.0	103.4	103.4	102.1	100.8	100.8	99.5	98.2	96.9
72.5°	87.7	86.4	85.1	83.8	83.8	83.8	82.5	81.2	79.9	78.6	75.9
75°	69.4	69.4	66.8	65.5	65.5	64.2	62.9	61.6	60.2	58.9	57.6
77.5°	53.7	52.4	49.8	48.5	48.5	48.5	47.2	45.9	44.6	43.1	41.8
80°	39.2	37.9	36.6	35.3	35.3	35.3	34.0	34.0	32.7	32.7	32.7
82.5°	26.2	26.2	24.8	24.8	24.8	24.8	23.5	23.5	23.5	23.5	23.5
85°	15.7	15.7	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4
87.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584064

CATALOG NUMBER: HCC8W20D010BZ-HM80520930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6
2.5°	917.7	917.7	915.1	913.8	912.5	913.8	911.1	909.8	908.5	908.5	907.2
5°	909.8	908.5	903.3	902.0	900.7	899.4	896.8	894.2	891.5	890.2	888.9
7.5°	899.4	895.5	890.2	888.9	887.6	883.7	879.8	877.2	873.1	871.8	869.2
10°	885.0	879.8	875.7	871.8	869.2	865.3	861.4	857.4	852.2	850.9	847.0
12.5°	867.9	861.4	853.5	852.2	848.3	843.1	837.8	833.9	830.0	827.4	823.4
15°	847.0	840.4	832.6	828.7	824.8	820.8	814.3	809.1	805.1	801.2	797.3
17.5°	822.1	814.3	807.8	803.8	801.2	794.7	789.3	782.8	778.9	775.0	771.0
20°	792.1	785.4	776.3	772.3	771.0	765.8	759.3	756.7	751.4	747.5	744.9
22.5°	758.0	751.4	743.6	741.0	735.7	733.1	726.6	724.0	721.4	717.4	716.1
25°	720.0	713.5	707.0	705.7	701.6	699.0	695.1	691.2	691.2	687.3	687.3
27.5°	680.7	674.2	669.0	666.3	665.0	662.4	658.5	657.2	655.9	654.6	654.6
30°	638.9	631.0	628.4	627.1	625.8	623.2	621.9	619.2	620.6	621.9	620.6
32.5°	594.3	591.7	586.5	583.9	585.2	583.9	581.2	583.9	582.6	585.2	586.5
35°	551.2	548.6	545.8	545.8	543.2	543.2	543.2	544.5	547.3	548.6	551.2
37.5°	509.2	505.3	504.0	502.7	504.0	504.0	504.0	506.6	509.2	511.8	515.8
40°	464.8	462.2	462.2	462.2	462.2	466.1	464.8	467.4	470.0	473.9	477.9
42.5°	422.8	422.8	424.1	424.1	424.1	424.1	426.8	430.7	434.6	438.5	442.4
45°	383.6	383.6	383.6	386.2	386.2	387.5	392.8	395.4	398.0	401.9	405.8
47.5°	346.9	346.9	348.2	349.5	350.8	353.4	356.1	360.0	363.9	366.5	370.4
50°	312.9	314.2	316.8	319.4	319.4	320.7	324.7	327.3	329.9	333.8	335.1
52.5°	280.1	282.7	285.3	286.8	288.1	290.7	292.0	295.9	297.2	301.1	302.4
55°	250.0	251.3	255.3	256.6	256.6	259.2	261.8	264.4	268.3	268.3	271.0
57.5°	222.6	223.9	226.5	227.8	226.5	230.4	231.7	234.3	235.7	238.3	239.6
60°	195.0	197.6	198.9	198.9	200.3	201.6	204.2	204.2	206.8	209.5	209.5
62.5°	168.9	170.2	171.5	172.8	174.1	172.8	176.7	176.7	179.3	180.6	183.3
65°	144.0	145.3	145.3	146.6	146.6	148.0	148.0	149.3	150.6	153.2	154.5
67.5°	119.1	119.1	119.1	120.4	119.1	120.4	120.4	121.7	121.7	124.3	125.6
70°	96.9	95.6	94.2	94.2	94.2	94.2	92.9	94.2	94.2	95.6	95.6
72.5°	74.6	73.3	72.0	70.7	70.7	69.4	68.1	69.4	69.4	70.7	70.7
75°	56.3	53.7	53.7	53.7	52.4	52.4	52.4	53.7	53.7	53.7	55.0
77.5°	41.8	41.8	40.5	40.5	40.5	41.8	41.8	43.1	43.1	43.1	43.1
80°	31.4	32.7	32.7	32.7	32.7	34.0	34.0	34.0	34.0	35.3	35.3
82.5°	23.5	23.5	23.5	23.5	24.8	24.8	24.8	24.8	24.8	24.8	24.8
85°	14.4	15.7	15.7	14.4	15.7	15.7	15.7	15.7	15.7	15.7	15.7
87.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P584064

CATALOG NUMBER: HCC8W20D010BZ-HM80520930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	921.6	921.6	921.6	921.6	921.6	921.6	921.6	921.6
2.5°	905.9	905.9	905.9	905.9	904.6	904.6	904.6	903.3
5°	886.3	886.3	886.3	883.7	885.0	885.0	882.4	883.7
7.5°	866.6	865.3	864.0	864.0	862.7	861.4	860.1	861.4
10°	844.4	840.4	840.4	839.1	839.1	836.5	836.5	837.8
12.5°	819.5	816.9	816.9	815.6	814.3	813.0	811.7	811.7
15°	794.7	792.1	790.8	789.3	788.0	785.4	786.7	785.4
17.5°	769.7	765.8	765.8	764.5	763.2	760.6	760.6	759.3
20°	741.0	739.7	737.0	738.4	737.0	734.4	733.1	733.1
22.5°	712.2	712.2	710.9	710.9	709.6	708.3	707.0	707.0
25°	684.6	683.3	684.6	684.6	680.7	680.7	680.7	682.0
27.5°	653.3	654.6	653.3	653.3	653.3	653.3	654.6	653.3
30°	621.9	621.9	621.9	623.2	625.8	624.5	624.5	623.2
32.5°	587.8	589.1	589.1	590.4	591.7	594.3	594.3	595.6
35°	553.8	556.4	557.7	556.4	560.3	560.3	562.9	562.9
37.5°	518.4	519.7	522.3	523.6	526.2	527.5	528.8	528.8
40°	480.5	485.7	487.0	488.3	492.2	492.2	493.5	496.2
42.5°	445.1	450.3	451.6	452.9	455.5	459.4	458.1	460.9
45°	411.1	415.0	416.3	417.6	421.5	422.8	422.8	426.8
47.5°	374.5	377.1	378.4	381.0	383.6	386.2	388.8	387.5
50°	337.7	341.7	344.3	345.6	349.5	350.8	352.1	353.4
52.5°	305.1	307.7	309.0	310.3	314.2	315.5	316.8	319.4
55°	273.6	274.9	277.5	276.2	280.1	281.4	282.7	285.3
57.5°	242.2	243.5	244.8	244.8	247.4	250.0	251.3	252.7
60°	212.1	214.7	216.0	216.0	216.0	218.7	218.7	218.7
62.5°	184.6	184.6	185.9	185.9	188.5	188.5	188.5	188.5
65°	155.8	157.1	158.4	158.4	161.0	159.7	162.3	161.0
67.5°	125.6	125.6	128.2	128.2	126.9	128.2	128.2	128.2
70°	95.6	95.6	96.9	96.9	96.9	96.9	96.9	96.9
72.5°	70.7	70.7	70.7	72.0	70.7	70.7	72.0	70.7
75°	55.0	55.0	55.0	55.0	55.0	55.0	55.0	55.0
77.5°	43.1	43.1	44.6	44.6	44.6	44.6	44.6	44.6
80°	35.3	35.3	35.3	35.3	36.6	35.3	35.3	35.3
82.5°	26.2	24.8	26.2	24.8	26.2	26.2	26.2	26.2
85°	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7
87.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)