

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584097

Luminaire Tested: **HCC8W20D010SL-HM80520940-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010SL-HM80520940-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1935.9 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584097
CATALOG NUMBER: HCC8W20D010SL-HM80520940-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584097

CATALOG NUMBER: HCC8W20D010SL-HM80520940-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32344	32344	32344
5°	33480	32161	30883
10°	34227	31597	29145
15°	34714	30535	27218
20°	34610	29051	25268
25°	33755	27165	23198
30°	31978	24982	21282
35°	29091	22609	19342
40°	25549	20107	17474
45°	22284	17692	15577
50°	19391	15495	13720
55°	17290	13618	11935
60°	15708	11940	10182
65°	14126	10383	9245
70°	12577	8854	8349
75°	11033	7458	7125
80°	9358	6073	6322
85°	7076	4529	5024



TEST NUMBER: P584097
 CATALOG NUMBER: HCC8W20D010SL-HM80520940-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.2	5.1
10°-20°	270.7	14.0
20°-30°	375.8	19.4
30°-40°	388.5	20.1
40°-50°	325.3	16.8
50°-60°	236.1	12.2
60°-70°	149.0	7.7
70°-80°	73.8	3.8
80°-90°	18.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	744.7	38.5
0°-40°	1133.2	58.5
0°-60°	1694.7	87.5
0°-90°	1935.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1935.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1049	1049	1049	1049	1049	
5°	1082	1069	1039	1010	998	103
15°	1087	1046	956	880	853	306
25°	992	928	798	712	682	455
35°	773	716	601	532	514	481
45°	511	474	406	366	357	395
55°	322	293	253	232	222	290
65°	194	169	142	125	127	193
75°	93	77	63	60	60	99
85°	20	16	13	14	14	24
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584097

CATALOG NUMBER: HCC8W20D010SL-HM80520940-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9
2.5°	1066.0	1066.0	1067.5	1066.0	1066.0	1066.0	1064.6	1064.6	1063.2	1063.2	1060.4
5°	1081.6	1078.8	1081.6	1078.8	1078.8	1078.8	1077.4	1074.6	1073.1	1070.3	1068.9
7.5°	1088.9	1087.4	1087.4	1085.9	1085.9	1084.5	1083.1	1081.6	1076.0	1074.6	1070.3
10°	1093.1	1091.7	1091.7	1090.3	1087.4	1087.4	1084.5	1083.1	1076.0	1073.1	1067.5
12.5°	1091.7	1091.7	1091.7	1090.3	1085.9	1084.5	1081.6	1077.4	1071.7	1066.0	1060.4
15°	1087.4	1087.4	1084.5	1083.1	1078.8	1076.0	1074.6	1067.5	1061.8	1054.7	1046.1
17.5°	1073.1	1073.1	1071.7	1068.9	1064.6	1061.8	1059.0	1051.9	1046.1	1034.7	1026.2
20°	1054.7	1053.3	1051.9	1047.5	1043.2	1041.8	1037.6	1027.6	1020.5	1011.9	1000.6
22.5°	1027.6	1026.2	1024.8	1022.0	1014.7	1011.9	1009.1	1002.0	989.2	980.6	966.4
25°	992.1	992.1	989.2	985.0	977.8	974.9	970.7	963.6	952.2	939.3	928.0
27.5°	950.8	949.4	945.0	942.2	936.5	932.2	925.2	916.6	905.2	895.2	881.1
30°	898.1	898.1	895.2	891.0	883.9	881.1	875.3	865.3	854.0	841.1	831.2
32.5°	838.3	838.3	834.0	831.2	826.9	819.8	818.4	807.0	797.0	787.1	775.6
35°	772.8	774.2	771.4	765.7	758.6	758.6	755.8	745.8	734.4	724.4	715.9
37.5°	707.4	703.1	701.6	698.8	694.5	688.9	686.0	681.8	671.7	664.6	651.9
40°	634.7	636.2	633.3	630.5	629.1	624.8	623.4	616.3	609.2	600.6	594.9
42.5°	569.4	569.4	569.4	566.4	563.6	559.3	557.9	553.6	545.1	539.5	530.8
45°	511.0	506.7	506.7	505.3	503.9	501.0	496.7	493.8	488.2	483.9	474.0
47.5°	454.0	455.4	454.0	452.6	448.3	446.9	445.5	439.8	434.1	429.8	422.7
50°	404.2	407.1	404.2	404.2	401.4	400.0	397.2	392.8	388.5	381.4	374.3
52.5°	363.0	363.0	361.5	360.0	355.8	352.9	351.5	350.1	343.0	337.3	331.7
55°	321.6	323.0	323.0	318.8	317.4	314.5	313.1	308.9	306.0	297.5	293.3
57.5°	286.0	284.6	286.0	283.2	280.4	277.5	276.1	273.3	269.0	263.3	257.6
60°	254.7	251.9	251.9	250.5	247.6	246.2	243.4	239.1	234.9	229.2	224.9
62.5°	223.4	222.0	220.6	219.1	216.3	214.9	213.5	209.2	205.0	200.7	196.4
65°	193.6	193.6	192.2	189.2	187.8	186.4	185.0	182.1	176.5	173.6	169.4
67.5°	166.5	165.1	165.1	162.3	159.5	158.0	158.0	155.1	150.8	146.6	143.7
70°	139.5	140.9	139.5	138.1	135.2	135.2	132.4	131.0	125.3	123.9	119.5
72.5°	115.2	115.2	113.8	113.8	111.0	109.6	109.6	106.7	103.9	101.1	98.2
75°	92.6	92.6	92.6	91.1	89.7	86.9	86.9	85.3	82.5	79.7	76.8
77.5°	72.6	71.2	71.2	69.7	68.3	66.9	66.9	65.5	62.6	61.2	58.4
80°	52.7	51.2	51.2	51.2	48.3	49.8	48.3	46.9	45.5	44.1	42.7
82.5°	34.2	35.6	35.6	34.2	32.7	32.7	32.7	31.3	31.3	29.9	28.5
85°	20.0	20.0	20.0	20.0	18.6	18.6	18.6	17.0	17.0	17.0	15.6
87.5°	8.5	8.5	8.5	8.5	8.5	8.5	7.1	7.1	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584097

CATALOG NUMBER: HCC8W20D010SL-HM80520940-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9
2.5°	1060.4	1057.5	1056.1	1054.7	1054.7	1053.3	1051.9	1048.9	1048.9	1046.1	1044.7
5°	1066.0	1061.8	1059.0	1056.1	1054.7	1051.9	1048.9	1044.7	1043.2	1039.0	1034.7
7.5°	1067.5	1060.4	1057.5	1051.9	1048.9	1046.1	1040.4	1036.1	1030.5	1026.2	1020.5
10°	1061.8	1056.1	1048.9	1041.8	1040.4	1036.1	1027.6	1022.0	1014.7	1009.1	1000.6
12.5°	1053.3	1044.7	1037.6	1029.0	1024.8	1020.5	1011.9	1003.4	993.5	983.5	974.9
15°	1039.0	1029.0	1019.1	1009.1	1003.4	999.1	989.2	979.2	969.2	956.5	947.8
17.5°	1017.7	1006.2	996.3	983.5	977.8	973.5	960.7	949.4	936.5	923.7	915.2
20°	990.6	976.3	965.0	950.8	946.4	939.3	926.6	913.8	899.5	885.3	875.3
22.5°	955.1	940.8	928.0	913.8	906.6	899.5	886.7	871.0	856.8	845.5	835.4
25°	913.8	900.9	885.3	872.4	863.9	855.4	841.1	828.3	815.6	798.4	788.5
27.5°	868.2	852.6	841.1	824.1	815.6	809.8	794.2	777.2	765.7	750.1	738.6
30°	817.0	802.7	789.9	772.8	764.3	758.6	744.4	728.7	717.4	701.6	690.3
32.5°	762.9	747.3	731.5	720.2	710.3	704.5	688.9	678.9	664.6	651.9	639.1
35°	704.5	688.9	677.5	661.8	656.1	650.5	637.6	624.8	612.0	600.6	590.6
37.5°	641.9	630.5	617.7	606.4	602.0	596.3	580.7	569.4	559.3	548.0	539.5
40°	580.7	570.8	562.2	550.8	543.7	539.5	528.0	518.1	506.7	499.5	491.0
42.5°	525.2	513.8	505.3	496.7	489.6	485.3	475.4	468.3	459.7	452.6	442.7
45°	466.9	461.1	451.2	444.1	439.8	434.1	426.9	418.4	411.3	405.7	398.6
47.5°	415.6	409.9	402.8	394.2	391.4	387.1	380.0	374.3	368.7	363.0	355.8
50°	368.7	361.5	355.8	350.1	347.3	343.0	335.9	333.1	328.8	323.0	318.8
52.5°	325.9	320.2	314.5	307.4	306.0	303.2	298.9	293.3	288.9	286.0	283.2
55°	287.5	281.8	277.5	271.9	270.4	267.6	261.9	259.1	256.1	253.3	250.5
57.5°	253.3	247.6	242.0	239.1	236.3	233.4	232.0	227.8	224.9	223.4	220.6
60°	222.0	216.3	212.1	207.8	206.4	205.0	202.1	199.3	196.4	193.6	192.2
62.5°	192.2	186.4	183.6	180.7	177.9	177.9	175.1	172.2	169.4	168.0	165.1
65°	165.1	162.3	158.0	153.7	152.2	152.2	148.0	146.6	145.1	142.3	139.5
67.5°	139.5	136.6	132.4	131.0	129.5	128.1	126.7	123.9	121.0	119.5	116.7
70°	116.7	113.8	111.0	109.6	108.2	106.7	103.9	102.5	99.6	98.2	96.8
72.5°	94.0	92.6	89.7	88.3	86.9	85.3	83.9	82.5	79.7	78.2	76.8
75°	75.4	74.0	71.2	69.7	68.3	68.3	66.9	64.1	62.6	62.6	61.2
77.5°	57.0	55.6	54.1	52.7	51.2	51.2	49.8	48.3	46.9	46.9	45.5
80°	41.3	39.8	38.4	38.4	38.4	37.0	35.6	35.6	34.2	34.2	32.7
82.5°	27.1	27.1	25.6	25.6	25.6	24.2	24.2	22.8	22.8	22.8	22.8
85°	15.6	15.6	15.6	14.2	14.2	14.2	14.2	14.2	14.2	12.8	14.2
87.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	5.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584097

CATALOG NUMBER: HCC8W20D010SL-HM80520940-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9
2.5°	1043.2	1041.8	1039.0	1039.0	1036.1	1036.1	1034.7	1033.3	1031.9	1030.5	1029.0
5°	1033.3	1027.6	1024.8	1023.4	1020.5	1019.1	1014.7	1011.9	1010.5	1007.7	1004.8
7.5°	1014.7	1009.1	1003.4	1002.0	1000.6	994.9	990.6	986.4	983.5	980.6	977.8
10°	993.5	987.8	980.6	977.8	974.9	967.8	962.1	957.9	952.2	946.4	945.0
12.5°	967.8	959.3	950.8	947.8	943.6	936.5	930.8	923.7	919.5	912.3	910.8
15°	937.9	928.0	920.9	913.8	910.8	903.8	893.8	888.2	879.6	876.7	869.6
17.5°	902.3	892.4	882.5	879.6	875.3	865.3	855.4	848.3	839.7	835.4	831.2
20°	865.3	852.6	842.5	839.7	834.0	825.5	815.6	808.4	801.3	792.8	788.5
22.5°	822.7	808.4	799.9	792.8	791.3	781.4	770.0	764.3	758.6	751.5	745.8
25°	775.6	762.9	752.9	747.3	744.4	735.8	727.3	720.2	711.7	707.4	700.2
27.5°	727.3	718.8	705.9	700.2	696.0	688.9	678.9	674.7	666.1	660.4	656.1
30°	680.4	667.5	660.4	653.3	649.0	641.9	633.3	629.1	622.0	616.3	612.0
32.5°	629.1	620.6	610.6	607.8	602.0	594.9	589.2	582.1	576.5	570.8	569.4
35°	582.1	570.8	560.7	557.9	553.6	546.6	543.7	539.5	532.3	530.8	525.2
37.5°	530.8	525.2	513.8	509.6	508.1	502.5	496.7	493.8	489.6	485.3	483.9
40°	482.5	475.4	469.7	465.4	462.5	458.3	452.6	451.2	448.3	442.7	441.2
42.5°	437.0	429.8	424.1	422.7	418.4	414.2	411.3	407.1	405.7	404.2	401.4
45°	392.8	388.5	382.8	381.4	380.0	374.3	371.5	368.7	365.8	364.4	361.5
47.5°	352.9	348.7	344.4	343.0	340.2	338.8	334.5	333.1	328.8	327.3	325.9
50°	314.5	311.7	308.9	307.4	304.6	303.2	300.3	297.5	294.7	293.3	291.7
52.5°	280.4	277.5	274.7	273.3	271.9	269.0	266.2	263.3	261.9	260.5	259.1
55°	247.6	244.8	243.4	242.0	240.5	239.1	234.9	233.4	232.0	230.6	227.8
57.5°	217.7	214.9	212.1	212.1	210.6	209.2	206.4	203.5	203.5	200.7	197.9
60°	190.8	187.8	185.0	183.6	182.1	179.3	177.9	176.5	175.1	173.6	170.8
62.5°	162.3	160.9	158.0	158.0	155.1	153.7	152.2	150.8	149.4	146.6	145.1
65°	138.1	136.6	133.8	132.4	132.4	131.0	128.1	126.7	125.3	125.3	123.9
67.5°	115.2	113.8	111.0	109.6	109.6	108.2	106.7	106.7	105.3	103.9	105.3
70°	95.4	92.6	92.6	91.1	91.1	89.7	88.3	88.3	88.3	89.7	89.7
72.5°	75.4	74.0	72.6	72.6	72.6	72.6	71.2	71.2	72.6	74.0	74.0
75°	59.8	58.4	58.4	58.4	57.0	57.0	58.4	58.4	59.8	59.8	59.8
77.5°	44.1	44.1	44.1	44.1	44.1	44.1	45.5	45.5	46.9	46.9	46.9
80°	32.7	32.7	32.7	32.7	32.7	34.2	34.2	34.2	34.2	34.2	35.6
82.5°	22.8	22.8	22.8	22.8	22.8	22.8	22.8	24.2	24.2	24.2	24.2
85°	12.8	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584097

CATALOG NUMBER: HCC8W20D010SL-HM80520940-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9
2.5°	1027.6	1027.6	1027.6	1029.0	1026.2	1026.2	1026.2	1026.2
5°	1003.4	1002.0	1000.6	1002.0	999.1	999.1	997.7	997.7
7.5°	973.5	972.1	970.7	970.7	967.8	967.8	966.4	965.0
10°	940.8	937.9	939.3	936.5	935.1	933.7	932.2	930.8
12.5°	905.2	902.3	900.9	898.1	895.2	893.8	895.2	892.4
15°	866.8	862.5	861.1	858.3	855.4	854.0	854.0	852.6
17.5°	824.1	821.3	819.8	817.0	815.6	812.7	811.3	809.8
20°	784.3	777.2	778.6	775.6	774.2	768.5	768.5	770.0
22.5°	740.1	735.8	733.0	730.1	728.7	725.9	725.9	724.4
25°	696.0	691.7	690.3	687.5	686.0	683.2	681.8	681.8
27.5°	653.3	647.6	647.6	644.8	641.9	640.5	639.1	637.6
30°	607.8	603.5	602.0	602.0	600.6	600.6	596.3	597.7
32.5°	565.0	562.2	560.7	557.9	557.9	556.5	556.5	552.2
35°	522.3	518.1	519.5	516.7	515.2	513.8	515.2	513.8
37.5°	481.1	478.2	478.2	475.4	475.4	474.0	472.6	475.4
40°	439.8	438.4	437.0	435.6	437.0	435.6	432.7	434.1
42.5°	398.6	398.6	397.2	397.2	395.6	395.6	395.6	395.6
45°	361.5	360.0	360.0	358.6	358.6	358.6	358.6	357.2
47.5°	324.5	323.0	323.0	323.0	321.6	321.6	320.2	321.6
50°	288.9	288.9	287.5	287.5	288.9	287.5	286.0	286.0
52.5°	256.1	256.1	254.7	254.7	253.3	251.9	253.3	253.3
55°	226.4	224.9	223.4	223.4	222.0	220.6	220.6	222.0
57.5°	197.9	196.4	195.0	195.0	192.2	190.8	190.8	190.8
60°	170.8	168.0	168.0	166.5	166.5	165.1	165.1	165.1
62.5°	145.1	143.7	143.7	143.7	143.7	142.3	142.3	142.3
65°	123.9	123.9	123.9	125.3	125.3	126.7	126.7	126.7
67.5°	106.7	108.2	108.2	108.2	109.6	109.6	109.6	108.2
70°	91.1	91.1	91.1	92.6	92.6	92.6	92.6	92.6
72.5°	75.4	75.4	75.4	75.4	75.4	75.4	75.4	75.4
75°	59.8	61.2	61.2	61.2	59.8	61.2	61.2	59.8
77.5°	46.9	46.9	46.9	46.9	46.9	46.9	46.9	46.9
80°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6
82.5°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)