

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584113

Luminaire Tested: **HCC8W25D010MW-HM82555827-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010MW-HM82555827-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2057.5 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584113
CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584113

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34062	34062	34062
5°	35470	33988	32558
10°	36657	33554	30968
15°	37581	32786	29361
20°	37659	31424	27903
25°	37022	29438	26461
30°	35041	27161	25220
35°	31949	24424	23682
40°	27783	21536	21866
45°	23837	18652	20017
50°	20360	16076	17980
55°	17843	13844	15623
60°	15881	11810	13136
65°	14090	9631	10478
70°	12505	7150	5951
75°	10425	3741	1775
80°	8204	1172	284
85°	5838	566	0



TEST NUMBER: P584113
 CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.1	5.1
10°-20°	291.7	14.2
20°-30°	412.9	20.1
30°-40°	432.0	21.0
40°-50°	360.3	17.5
50°-60°	255.5	12.4
60°-70°	147.2	7.2
70°-80°	47.3	2.3
80°-90°	6.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.7	39.3
0°-40°	1240.7	60.3
0°-60°	1856.5	90.2
0°-90°	2057.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2057.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1105	1105	1105	1105	1105	
5°	1146	1131	1098	1065	1052	110
15°	1177	1129	1027	946	920	331
25°	1088	1007	865	796	778	497
35°	849	774	649	614	629	526
45°	547	502	428	433	459	424
55°	332	297	258	271	291	300
65°	193	162	132	132	144	193
75°	88	64	31	15	15	95
85°	16	8	2	0	0	21
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584113

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6
2.5°	1127.7	1126.1	1124.4	1126.1	1124.4	1126.1	1124.4	1124.4	1122.8	1121.1	1121.1
5°	1145.9	1144.3	1144.3	1144.3	1142.5	1140.9	1140.9	1139.2	1136.0	1134.3	1131.0
7.5°	1157.4	1159.1	1159.1	1159.1	1155.8	1155.8	1152.5	1149.2	1145.9	1142.5	1137.6
10°	1170.7	1170.7	1169.0	1167.4	1164.1	1162.3	1160.7	1157.4	1152.5	1145.9	1140.9
12.5°	1175.6	1175.6	1173.9	1170.7	1169.0	1167.4	1165.7	1160.7	1154.1	1145.9	1139.2
15°	1177.2	1173.9	1172.3	1170.7	1167.4	1162.3	1162.3	1155.8	1147.6	1137.6	1129.4
17.5°	1164.1	1165.7	1162.3	1159.1	1154.1	1150.8	1145.9	1140.9	1131.0	1119.4	1111.2
20°	1147.6	1145.9	1144.3	1139.2	1132.7	1131.0	1126.1	1117.8	1109.6	1096.3	1084.8
22.5°	1121.1	1119.4	1116.1	1112.8	1106.3	1103.0	1098.0	1088.1	1076.5	1063.4	1050.1
25°	1088.1	1084.8	1079.8	1073.2	1068.3	1065.0	1058.3	1048.5	1035.2	1020.4	1007.2
27.5°	1035.2	1040.3	1036.9	1027.0	1022.1	1015.4	1013.8	1000.6	989.0	974.1	959.3
30°	984.1	984.1	979.2	974.1	965.9	961.0	954.3	944.5	932.8	914.7	903.2
32.5°	919.7	918.1	911.4	909.7	903.2	893.2	891.6	878.4	866.8	853.6	838.8
35°	848.7	845.4	838.8	833.9	830.5	825.5	820.6	809.0	797.5	784.3	774.4
37.5°	767.7	767.7	766.1	757.9	754.6	751.2	746.3	734.8	728.1	715.0	705.0
40°	690.2	688.5	683.5	681.9	678.6	673.7	670.4	663.7	653.9	643.9	634.0
42.5°	614.2	615.9	609.3	610.9	604.3	601.0	599.3	589.5	584.5	574.6	566.4
45°	546.6	544.8	541.5	539.9	536.6	533.3	530.0	525.0	516.8	506.9	501.9
47.5°	483.7	478.8	478.8	477.2	475.5	468.9	467.3	462.3	457.3	447.5	440.8
50°	424.4	424.4	424.4	422.6	417.7	416.1	412.8	407.8	402.9	396.2	386.4
52.5°	376.4	376.4	376.4	374.8	368.2	366.6	364.9	358.3	351.7	346.8	340.2
55°	331.9	333.5	331.9	328.6	323.6	323.6	318.6	315.3	308.8	303.8	297.2
57.5°	293.9	293.9	290.6	288.9	285.7	284.0	280.7	277.3	269.1	264.2	255.9
60°	257.5	255.9	255.9	252.6	249.3	246.0	244.4	239.4	236.1	227.8	221.3
62.5°	224.6	224.6	221.3	221.3	214.6	214.6	213.0	208.0	203.1	194.8	191.5
65°	193.1	193.1	191.5	189.9	184.9	183.3	181.6	176.7	171.7	166.8	161.8
67.5°	165.1	165.1	161.8	160.2	156.9	155.3	151.9	148.6	143.6	138.7	133.8
70°	138.7	137.1	135.4	133.8	130.4	128.8	125.5	122.2	117.3	114.0	108.9
72.5°	112.2	112.2	110.6	107.3	105.7	104.0	102.4	99.1	94.2	89.1	85.8
75°	87.5	87.5	87.5	84.2	80.9	79.3	79.3	76.0	72.7	67.7	64.4
77.5°	67.7	66.0	64.4	64.4	61.1	59.5	57.8	56.2	51.1	49.5	46.2
80°	46.2	47.8	46.2	44.6	42.9	41.3	41.3	38.0	36.3	33.1	29.7
82.5°	31.4	29.7	29.7	28.0	28.0	26.4	26.4	23.1	21.5	19.8	18.2
85°	16.5	16.5	14.9	14.9	14.9	13.2	13.2	11.6	11.6	10.0	8.2
87.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	3.3	3.3	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584113

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6
2.5°	1119.4	1116.1	1114.5	1114.5	1112.8	1111.2	1109.6	1107.9	1104.6	1104.6	1101.2
5°	1127.7	1124.4	1122.8	1117.8	1114.5	1114.5	1107.9	1106.3	1101.2	1098.0	1094.7
7.5°	1134.3	1127.7	1122.8	1117.8	1114.5	1111.2	1104.6	1098.0	1091.4	1084.8	1081.4
10°	1134.3	1127.7	1119.4	1111.2	1107.9	1104.6	1096.3	1086.5	1078.1	1071.6	1063.4
12.5°	1131.0	1121.1	1111.2	1104.6	1098.0	1093.0	1083.2	1073.2	1063.4	1050.1	1043.5
15°	1121.1	1107.9	1098.0	1086.5	1081.4	1073.2	1065.0	1050.1	1038.5	1027.0	1018.7
17.5°	1101.2	1084.8	1073.2	1061.7	1053.4	1048.5	1035.2	1022.1	1008.8	995.6	985.7
20°	1071.6	1056.7	1043.5	1028.6	1022.1	1015.4	999.0	985.7	972.5	957.6	947.7
22.5°	1035.2	1020.4	1002.3	990.7	980.8	972.5	957.6	942.8	929.6	916.3	903.2
25°	990.7	975.8	959.3	941.2	934.5	926.3	909.7	894.9	880.1	865.2	853.6
27.5°	942.8	923.0	909.7	889.9	883.4	875.0	857.0	840.4	827.2	815.7	802.4
30°	885.0	870.1	851.9	833.9	827.2	819.0	804.1	789.2	776.1	762.8	749.6
32.5°	822.3	807.4	789.2	776.1	766.1	759.5	744.6	731.5	718.2	705.0	693.5
35°	756.2	739.7	726.5	713.3	705.0	696.8	681.9	670.4	660.4	648.8	637.3
37.5°	688.5	677.0	663.7	648.8	640.6	634.0	622.4	609.3	601.0	591.1	582.8
40°	622.4	609.3	597.7	584.5	577.9	573.0	561.4	551.5	543.2	535.0	530.0
42.5°	554.8	543.2	531.7	523.4	518.4	513.5	505.3	493.7	488.8	480.4	475.5
45°	492.0	482.1	473.9	462.3	459.0	455.7	445.8	437.5	432.6	427.7	424.4
47.5°	432.6	426.0	416.1	409.5	404.6	401.2	394.6	388.0	383.1	379.7	376.4
50°	381.5	373.1	366.6	359.9	356.6	351.7	345.1	341.8	338.4	335.1	335.1
52.5°	333.5	325.3	318.6	313.7	310.4	307.1	302.2	300.5	297.2	297.2	295.5
55°	288.9	284.0	277.3	270.8	269.1	267.5	264.2	260.9	259.3	257.5	259.3
57.5°	251.0	246.0	239.4	234.4	232.8	231.1	229.5	226.2	224.6	224.6	224.6
60°	216.2	211.3	206.4	201.5	201.5	198.2	196.5	194.8	193.1	191.5	191.5
62.5°	184.9	180.0	175.1	171.7	170.0	168.4	165.1	163.5	161.8	161.8	160.2
65°	156.9	150.2	148.6	143.6	142.0	140.4	138.7	135.4	133.8	132.0	130.4
67.5°	128.8	125.5	120.5	117.3	115.6	114.0	112.2	108.9	107.3	105.7	102.4
70°	104.0	100.7	97.4	94.2	92.4	90.8	87.5	84.2	82.6	79.3	74.3
72.5°	80.9	77.6	74.3	71.0	69.3	67.7	64.4	61.1	57.8	54.5	51.1
75°	61.1	57.8	52.9	49.5	47.8	47.8	42.9	39.6	36.3	31.4	28.0
77.5°	42.9	38.0	36.3	33.1	31.4	28.0	24.7	21.5	18.2	16.5	13.2
80°	28.0	24.7	21.5	19.8	18.2	16.5	14.9	11.6	8.2	6.6	4.9
82.5°	16.5	14.9	13.2	11.6	10.0	8.2	6.6	6.6	4.9	3.3	1.6
85°	8.2	6.6	4.9	4.9	3.3	3.3	3.3	1.6	1.6	1.6	1.6
87.5°	3.3	1.6	1.6	1.6	1.6	1.6	1.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584113

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6
2.5°	1099.6	1098.0	1096.3	1094.7	1094.7	1091.4	1091.4	1089.7	1086.5	1084.8	1084.8
5°	1089.7	1084.8	1081.4	1079.8	1078.1	1073.2	1071.6	1068.3	1065.0	1061.7	1060.0
7.5°	1074.9	1066.6	1063.4	1061.7	1056.7	1051.8	1048.5	1043.5	1038.5	1033.6	1031.9
10°	1056.7	1048.5	1040.3	1036.9	1031.9	1028.6	1022.1	1015.4	1010.5	1005.5	1000.6
12.5°	1033.6	1023.7	1015.4	1012.1	1007.2	1000.6	990.7	987.4	979.2	975.8	969.2
15°	1007.2	995.6	987.4	982.4	977.4	967.6	961.0	954.3	946.1	942.8	936.1
17.5°	974.1	961.0	952.7	947.7	944.5	936.1	926.3	918.1	909.7	906.5	901.5
20°	934.5	926.3	914.7	909.7	906.5	896.6	886.6	883.4	876.8	870.1	865.2
22.5°	889.9	881.7	870.1	865.2	863.5	855.3	847.0	842.1	837.1	832.1	827.2
25°	843.7	833.9	823.9	820.6	817.3	810.7	804.1	800.8	795.9	792.5	789.2
27.5°	794.2	784.3	776.1	771.0	767.7	762.8	759.5	756.2	753.0	749.6	747.9
30°	741.4	731.5	724.8	721.5	718.2	716.6	711.7	709.9	708.3	705.0	706.6
32.5°	688.5	680.3	673.7	668.8	668.8	665.4	663.7	663.7	662.1	662.1	662.1
35°	630.8	625.7	620.8	619.2	617.5	615.9	614.2	615.9	614.2	615.9	617.5
37.5°	577.9	573.0	569.7	568.0	566.4	568.0	566.4	566.4	568.0	571.3	573.0
40°	523.4	520.1	516.8	518.4	516.8	516.8	516.8	521.7	523.4	525.0	526.7
42.5°	472.2	468.9	467.3	467.3	468.9	467.3	470.6	472.2	475.5	480.4	483.7
45°	422.6	421.0	421.0	422.6	421.0	424.4	424.4	427.7	432.6	435.9	439.2
47.5°	376.4	376.4	376.4	378.1	378.1	379.7	383.1	384.7	388.0	391.3	394.6
50°	333.5	335.1	336.8	336.8	336.8	340.2	343.5	345.1	346.8	348.4	353.3
52.5°	295.5	297.2	297.2	298.9	300.5	302.2	303.8	307.1	308.8	312.0	313.7
55°	259.3	259.3	262.6	264.2	264.2	264.2	267.5	267.5	270.8	272.4	275.7
57.5°	224.6	226.2	226.2	227.8	227.8	229.5	231.1	232.8	234.4	236.1	237.8
60°	191.5	191.5	191.5	193.1	194.8	196.5	194.8	198.2	198.2	201.5	203.1
62.5°	160.2	161.8	161.8	161.8	161.8	161.8	161.8	163.5	165.1	166.8	168.4
65°	130.4	130.4	130.4	128.8	130.4	128.8	130.4	132.0	132.0	133.8	135.4
67.5°	100.7	100.7	97.4	97.4	99.1	99.1	99.1	99.1	97.4	100.7	100.7
70°	72.7	71.0	69.3	67.7	67.7	66.0	66.0	64.4	64.4	64.4	64.4
72.5°	47.8	44.6	41.3	39.6	38.0	38.0	34.7	33.1	34.7	34.7	34.7
75°	24.7	21.5	19.8	18.2	16.5	16.5	14.9	14.9	14.9	14.9	14.9
77.5°	10.0	8.2	6.6	6.6	4.9	4.9	4.9	4.9	4.9	4.9	4.9
80°	3.3	3.3	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	1.6	0.0	0.0	1.6	0.0	1.6	1.6	1.6	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584113

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6
2.5°	1083.2	1083.2	1081.4	1083.2	1079.8	1081.4	1079.8	1079.8
5°	1058.3	1055.0	1055.0	1055.0	1053.4	1053.4	1051.8	1051.8
7.5°	1028.6	1027.0	1025.4	1023.7	1022.1	1020.4	1020.4	1020.4
10°	999.0	995.6	995.6	993.9	990.7	989.0	989.0	989.0
12.5°	964.3	962.6	961.0	961.0	954.3	956.0	954.3	954.3
15°	931.2	929.6	929.6	924.6	921.3	921.3	921.3	919.7
17.5°	896.6	894.9	893.2	889.9	886.6	886.6	885.0	886.6
20°	860.3	858.6	855.3	855.3	853.6	851.9	848.7	850.3
22.5°	823.9	820.6	819.0	819.0	817.3	817.3	813.9	813.9
25°	785.9	784.3	782.6	784.3	781.0	781.0	777.7	777.7
27.5°	746.3	744.6	744.6	744.6	743.0	744.6	743.0	743.0
30°	706.6	706.6	705.0	705.0	706.6	705.0	706.6	708.3
32.5°	663.7	663.7	665.4	665.4	667.0	667.0	667.0	667.0
35°	619.2	622.4	622.4	624.1	625.7	627.4	627.4	629.1
37.5°	577.9	579.5	581.2	582.8	586.1	586.1	586.1	586.1
40°	533.3	535.0	538.2	536.6	543.2	544.8	543.2	543.2
42.5°	487.1	490.4	492.0	495.3	497.0	500.3	501.9	501.9
45°	444.2	445.8	449.1	452.4	454.1	459.0	459.0	459.0
47.5°	399.5	402.9	404.6	407.8	409.5	414.4	416.1	414.4
50°	356.6	359.9	363.3	363.3	368.2	369.9	373.1	374.8
52.5°	315.3	317.0	320.4	322.0	325.3	328.6	330.2	331.9
55°	275.7	277.3	280.7	280.7	285.7	287.3	290.6	290.6
57.5°	239.4	241.1	244.4	242.7	246.0	249.3	249.3	247.7
60°	204.7	204.7	204.7	208.0	209.7	211.3	213.0	213.0
62.5°	168.4	171.7	173.3	173.3	175.1	176.7	176.7	175.1
65°	135.4	138.7	140.4	140.4	142.0	142.0	142.0	143.6
67.5°	102.4	102.4	102.4	104.0	102.4	102.4	102.4	102.4
70°	64.4	64.4	64.4	64.4	62.7	64.4	64.4	66.0
72.5°	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7
75°	14.9	14.9	14.9	16.5	14.9	14.9	14.9	14.9
77.5°	6.6	4.9	6.6	6.6	4.9	4.9	4.9	4.9
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	0.0	1.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)