

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584131

Luminaire Tested: **HCC8S25D010SL-HM82555830-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584131  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S25D010SL-HM82555830-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2193.0 lumens  
Efficiency: N/A  
Efficacy: 81.8 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584131  
CATALOG NUMBER: HCC8S25D010SL-HM82555830-81WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P584131

CATALOG NUMBER: HCC8S25D010SL-HM82555830-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	36640	36640	36640
5°	37931	36433	34984
10°	38774	35796	33019
15°	39324	34590	30832
20°	39208	32910	28625
25°	38236	30775	26277
30°	36226	28304	24113
35°	32957	25613	21913
40°	28947	22780	19797
45°	25245	20043	17649
50°	21967	17558	15548
55°	19585	15430	13526
60°	17799	13519	11533
65°	15994	11762	10470
70°	14245	10035	9449
75°	12486	8447	8066
80°	10601	6872	7156
85°	7996	5166	5732



TEST NUMBER: P584131

CATALOG NUMBER: HCC8S25D010SL-HM82555830-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.3	5.1
10°-20°	306.7	14.0
20°-30°	425.7	19.4
30°-40°	440.1	20.1
40°-50°	368.5	16.8
50°-60°	267.5	12.2
60°-70°	168.8	7.7
70°-80°	83.6	3.8
80°-90°	20.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.7	38.5
0°-40°	1283.8	58.5
0°-60°	1919.8	87.5
0°-90°	2193.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2193.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1188	1188	1188	1188	1188	
5°	1225	1211	1177	1145	1130	117
15°	1232	1185	1084	996	966	347
25°	1124	1051	904	806	772	515
35°	876	811	680	603	582	545
45°	579	537	460	414	405	448
55°	364	332	287	263	252	329
65°	219	192	161	142	144	219
75°	105	87	71	68	68	112
85°	23	18	15	16	16	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584131

CATALOG NUMBER: HCC8S25D010SL-HM82555830-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1207.6	1207.6	1209.2	1207.6	1207.6	1207.6	1206.0	1206.0	1204.4	1204.4	1201.2
5°	1225.4	1222.2	1225.4	1222.2	1222.2	1222.2	1220.5	1217.3	1215.7	1212.4	1210.8
7.5°	1233.4	1231.8	1231.8	1230.2	1230.2	1228.6	1227.0	1225.4	1218.9	1217.3	1212.4
10°	1238.3	1236.6	1236.6	1235.0	1231.8	1231.8	1228.6	1227.0	1218.9	1215.7	1209.2
12.5°	1236.6	1236.6	1236.6	1235.0	1230.2	1228.6	1225.4	1220.5	1214.1	1207.6	1201.2
15°	1231.8	1231.8	1228.6	1227.0	1222.2	1218.9	1217.3	1209.2	1202.8	1194.8	1185.0
17.5°	1215.7	1215.7	1214.1	1210.8	1206.0	1202.8	1199.6	1191.6	1185.0	1172.2	1162.4
20°	1194.8	1193.2	1191.6	1186.6	1181.8	1180.2	1175.4	1164.1	1156.0	1146.4	1133.5
22.5°	1164.1	1162.4	1160.8	1157.6	1149.6	1146.4	1143.2	1135.1	1120.6	1110.9	1094.7
25°	1123.8	1123.8	1120.6	1115.7	1107.7	1104.5	1099.6	1091.5	1078.7	1064.1	1051.3
27.5°	1077.1	1075.5	1070.5	1067.3	1060.9	1056.1	1048.0	1038.3	1025.5	1014.1	998.0
30°	1017.4	1017.4	1014.1	1009.3	1001.2	998.0	991.6	980.3	967.4	952.8	941.6
32.5°	949.6	949.6	944.8	941.6	936.8	928.7	927.0	914.2	902.9	891.6	878.7
35°	875.5	877.1	873.9	867.4	859.3	859.3	856.1	844.9	831.9	820.7	811.0
37.5°	801.3	796.5	794.9	791.7	786.8	780.4	777.1	772.3	761.0	753.0	738.4
40°	719.1	720.8	717.4	714.2	712.6	707.8	706.2	698.2	690.0	680.4	674.0
42.5°	644.9	644.9	644.9	641.7	638.5	633.7	632.0	627.2	617.5	611.1	601.4
45°	578.9	573.9	573.9	572.3	570.7	567.5	562.7	559.5	553.0	548.2	536.9
47.5°	514.3	516.0	514.3	512.7	507.9	506.2	504.6	498.2	491.8	487.0	478.8
50°	457.9	461.2	457.9	457.9	454.6	453.0	449.8	445.0	440.2	432.1	424.0
52.5°	411.1	411.1	409.5	407.9	403.1	399.9	398.3	396.6	388.5	382.1	375.7
55°	364.3	366.0	366.0	361.1	359.5	356.3	354.7	349.9	346.7	336.9	332.1
57.5°	324.1	322.5	324.1	320.9	317.6	314.4	312.8	309.6	304.7	298.3	291.8
60°	288.6	285.4	285.4	283.8	280.6	278.9	275.7	270.8	266.0	259.6	254.8
62.5°	253.2	251.6	250.0	248.3	245.0	243.4	241.8	237.0	232.2	227.4	222.5
65°	219.2	219.2	217.6	214.4	212.8	211.2	209.6	206.4	199.9	196.7	191.9
67.5°	188.6	187.0	187.0	183.8	180.6	179.0	179.0	175.7	170.9	166.1	162.9
70°	158.0	159.6	158.0	156.4	153.2	153.2	149.9	148.3	141.9	140.3	135.5
72.5°	130.6	130.6	128.9	128.9	125.7	124.1	124.1	120.9	117.7	114.5	111.3
75°	104.8	104.8	104.8	103.1	101.5	98.3	98.3	96.7	93.5	90.3	87.1
77.5°	82.2	80.6	80.6	79.0	77.4	75.8	75.8	74.2	70.9	69.3	66.1
80°	59.7	58.0	58.0	58.0	54.8	56.4	54.8	53.2	51.6	50.0	48.4
82.5°	38.7	40.3	40.3	38.7	37.1	37.1	37.1	35.5	35.5	33.8	32.2
85°	22.6	22.6	22.6	22.6	21.0	21.0	21.0	19.4	19.4	19.4	17.8
87.5°	9.6	9.6	9.6	9.6	9.6	9.6	8.0	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584131

CATALOG NUMBER: HCC8S25D010SL-HM82555830-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1201.2	1198.0	1196.4	1194.8	1194.8	1193.2	1191.6	1188.2	1188.2	1185.0	1183.4
5°	1207.6	1202.8	1199.6	1196.4	1194.8	1191.6	1188.2	1183.4	1181.8	1177.0	1172.2
7.5°	1209.2	1201.2	1198.0	1191.6	1188.2	1185.0	1178.6	1173.8	1167.4	1162.4	1156.0
10°	1202.8	1196.4	1188.2	1180.2	1178.6	1173.8	1164.1	1157.6	1149.6	1143.2	1133.5
12.5°	1193.2	1183.4	1175.4	1165.7	1160.8	1156.0	1146.4	1136.7	1125.4	1114.1	1104.5
15°	1177.0	1165.7	1154.4	1143.2	1136.7	1131.8	1120.6	1109.3	1098.0	1083.5	1073.9
17.5°	1152.8	1139.9	1128.6	1114.1	1107.7	1102.8	1088.3	1075.5	1060.9	1046.4	1036.7
20°	1122.2	1106.1	1093.1	1077.1	1072.2	1064.1	1049.7	1035.1	1019.0	1002.9	991.6
22.5°	1081.9	1065.7	1051.3	1035.1	1027.1	1019.0	1004.5	986.8	970.6	957.8	946.4
25°	1035.1	1020.6	1002.9	988.4	978.7	969.0	952.8	938.4	923.8	904.5	893.2
27.5°	983.5	965.8	952.8	933.6	923.8	917.4	899.7	880.3	867.4	849.7	836.8
30°	925.4	909.4	894.8	875.5	865.8	859.3	843.3	825.5	812.6	794.9	782.0
32.5°	864.2	846.5	828.7	815.9	804.5	798.1	780.4	769.1	753.0	738.4	724.0
35°	798.1	780.4	767.5	749.7	743.3	736.8	722.4	707.8	693.3	680.4	669.1
37.5°	727.2	714.2	699.8	686.8	682.0	675.6	657.8	644.9	633.7	620.7	611.1
40°	657.8	646.5	636.9	623.9	615.9	611.1	598.1	586.9	573.9	565.9	556.3
42.5°	594.9	582.1	572.3	562.7	554.7	549.8	538.5	530.5	520.8	512.7	501.4
45°	528.8	522.4	511.1	503.0	498.2	491.8	483.7	474.0	466.0	459.6	451.4
47.5°	470.8	464.4	456.2	446.6	443.4	438.6	430.5	424.0	417.6	411.1	403.1
50°	417.6	409.5	403.1	396.6	393.4	388.5	380.5	377.3	372.5	366.0	361.1
52.5°	369.3	362.7	356.3	348.3	346.7	343.5	338.5	332.1	327.3	324.1	320.9
55°	325.7	319.3	314.4	307.9	306.3	303.1	296.7	293.4	290.2	287.0	283.8
57.5°	287.0	280.6	274.1	270.8	267.6	264.4	262.8	258.0	254.8	253.2	250.0
60°	251.6	245.0	240.2	235.4	233.8	232.2	229.0	225.8	222.5	219.2	217.6
62.5°	217.6	211.2	208.0	204.8	201.6	201.6	198.3	195.1	191.9	190.2	187.0
65°	187.0	183.8	179.0	174.1	172.5	172.5	167.7	166.1	164.5	161.2	158.0
67.5°	158.0	154.8	149.9	148.3	146.7	145.1	143.5	140.3	137.1	135.5	132.3
70°	132.3	128.9	125.7	124.1	122.5	120.9	117.7	116.1	112.9	111.3	109.7
72.5°	106.5	104.8	101.5	99.9	98.3	96.7	95.1	93.5	90.3	88.7	87.1
75°	85.5	83.9	80.6	79.0	77.4	77.4	75.8	72.5	70.9	70.9	69.3
77.5°	64.5	62.9	61.3	59.7	58.0	58.0	56.4	54.8	53.2	53.2	51.6
80°	46.8	45.2	43.5	43.5	43.5	41.9	40.3	40.3	38.7	38.7	37.1
82.5°	30.6	30.6	29.0	29.0	29.0	27.4	27.4	25.8	25.8	25.8	25.8
85°	17.8	17.8	17.8	16.2	16.2	16.2	16.2	16.2	16.2	14.6	16.2
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584131

CATALOG NUMBER: HCC8S25D010SL-HM82555830-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1181.8	1180.2	1177.0	1177.0	1173.8	1173.8	1172.2	1170.6	1169.0	1167.4	1165.7
5°	1170.6	1164.1	1160.8	1159.2	1156.0	1154.4	1149.6	1146.4	1144.8	1141.5	1138.3
7.5°	1149.6	1143.2	1136.7	1135.1	1133.5	1127.0	1122.2	1117.3	1114.1	1110.9	1107.7
10°	1125.4	1118.9	1110.9	1107.7	1104.5	1096.4	1089.9	1085.1	1078.7	1072.2	1070.5
12.5°	1096.4	1086.7	1077.1	1073.9	1068.9	1060.9	1054.5	1046.4	1041.5	1033.5	1031.9
15°	1062.5	1051.3	1043.1	1035.1	1031.9	1023.8	1012.5	1006.1	996.4	993.2	985.1
17.5°	1022.2	1010.9	999.6	996.4	991.6	980.3	969.0	961.0	951.2	946.4	941.6
20°	980.3	965.8	954.5	951.2	944.8	935.2	923.8	915.8	907.8	898.1	893.2
22.5°	932.0	915.8	906.1	898.1	896.4	885.2	872.3	865.8	859.3	851.3	844.9
25°	878.7	864.2	852.9	846.5	843.3	833.5	823.9	815.9	806.1	801.3	793.3
27.5°	823.9	814.3	799.7	793.3	788.4	780.4	769.1	764.2	754.6	748.1	743.3
30°	770.7	756.2	748.1	740.0	735.2	727.2	717.4	712.6	704.6	698.2	693.3
32.5°	712.6	703.0	691.6	688.4	682.0	674.0	667.5	659.4	653.0	646.5	644.9
35°	659.4	646.5	635.3	632.0	627.2	619.1	615.9	611.1	603.1	601.4	594.9
37.5°	601.4	594.9	582.1	577.2	575.6	569.1	562.7	559.5	554.7	549.8	548.2
40°	546.6	538.5	532.1	527.2	524.0	519.2	512.7	511.1	507.9	501.4	499.8
42.5°	495.0	487.0	480.4	478.8	474.0	469.2	466.0	461.2	459.6	457.9	454.6
45°	445.0	440.2	433.7	432.1	430.5	424.0	420.8	417.6	414.4	412.8	409.5
47.5°	399.9	395.0	390.2	388.5	385.3	383.7	378.9	377.3	372.5	370.9	369.3
50°	356.3	353.1	349.9	348.3	345.1	343.5	340.2	336.9	333.7	332.1	330.5
52.5°	317.6	314.4	311.2	309.6	307.9	304.7	301.5	298.3	296.7	295.1	293.4
55°	280.6	277.3	275.7	274.1	272.5	270.8	266.0	264.4	262.8	261.2	258.0
57.5°	246.6	243.4	240.2	240.2	238.6	237.0	233.8	230.6	230.6	227.4	224.2
60°	216.0	212.8	209.6	208.0	206.4	203.2	201.6	199.9	198.3	196.7	193.5
62.5°	183.8	182.2	179.0	179.0	175.7	174.1	172.5	170.9	169.3	166.1	164.5
65°	156.4	154.8	151.5	149.9	149.9	148.3	145.1	143.5	141.9	141.9	140.3
67.5°	130.6	128.9	125.7	124.1	124.1	122.5	120.9	120.9	119.3	117.7	119.3
70°	108.1	104.8	104.8	103.1	103.1	101.5	99.9	99.9	99.9	101.5	101.5
72.5°	85.5	83.9	82.2	82.2	82.2	82.2	80.6	80.6	82.2	83.9	83.9
75°	67.7	66.1	66.1	66.1	64.5	64.5	66.1	66.1	67.7	67.7	67.7
77.5°	50.0	50.0	50.0	50.0	50.0	50.0	51.6	51.6	53.2	53.2	53.2
80°	37.1	37.1	37.1	37.1	37.1	38.7	38.7	38.7	38.7	38.7	40.3
82.5°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	27.4	27.4	27.4	27.4
85°	14.6	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2
87.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584131

CATALOG NUMBER: HCC8S25D010SL-HM82555830-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1164.1	1164.1	1164.1	1165.7	1162.4	1162.4	1162.4	1162.4
5°	1136.7	1135.1	1133.5	1135.1	1131.8	1131.8	1130.2	1130.2
7.5°	1102.8	1101.2	1099.6	1099.6	1096.4	1096.4	1094.7	1093.1
10°	1065.7	1062.5	1064.1	1060.9	1059.3	1057.7	1056.1	1054.5
12.5°	1025.5	1022.2	1020.6	1017.4	1014.1	1012.5	1014.1	1010.9
15°	981.9	977.0	975.4	972.2	969.0	967.4	967.4	965.8
17.5°	933.6	930.3	928.7	925.4	923.8	920.6	919.0	917.4
20°	888.4	880.3	881.9	878.7	877.1	870.7	870.7	872.3
22.5°	838.5	833.5	830.3	827.1	825.5	822.3	822.3	820.7
25°	788.4	783.6	782.0	778.7	777.1	773.9	772.3	772.3
27.5°	740.0	733.6	733.6	730.4	727.2	725.6	724.0	722.4
30°	688.4	683.6	682.0	682.0	680.4	680.4	675.6	677.2
32.5°	640.1	636.9	635.3	632.0	632.0	630.4	630.4	625.6
35°	591.7	586.9	588.5	585.3	583.7	582.1	583.7	582.1
37.5°	545.0	541.7	541.7	538.5	538.5	536.9	535.3	538.5
40°	498.2	496.6	495.0	493.4	495.0	493.4	490.2	491.8
42.5°	451.4	451.4	449.8	449.8	448.2	448.2	448.2	448.2
45°	409.5	407.9	407.9	406.3	406.3	406.3	406.3	404.7
47.5°	367.7	366.0	366.0	366.0	364.3	364.3	362.7	364.3
50°	327.3	327.3	325.7	325.7	327.3	325.7	324.1	324.1
52.5°	290.2	290.2	288.6	288.6	287.0	285.4	287.0	287.0
55°	256.4	254.8	253.2	253.2	251.6	250.0	250.0	251.6
57.5°	224.2	222.5	220.8	220.8	217.6	216.0	216.0	216.0
60°	193.5	190.2	190.2	188.6	188.6	187.0	187.0	187.0
62.5°	164.5	162.9	162.9	162.9	162.9	161.2	161.2	161.2
65°	140.3	140.3	140.3	141.9	141.9	143.5	143.5	143.5
67.5°	120.9	122.5	122.5	122.5	124.1	124.1	124.1	122.5
70°	103.1	103.1	103.1	104.8	104.8	104.8	104.8	104.8
72.5°	85.5	85.5	85.5	85.5	85.5	85.5	85.5	85.5
75°	67.7	69.3	69.3	69.3	67.7	69.3	69.3	67.7
77.5°	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2
80°	40.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3
82.5°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4
85°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2
87.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)