

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584130

Luminaire Tested: **HCC8W25D010SL-HM82555830-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010SL-HM82555830-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2009.2 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584130
CATALOG NUMBER: HCC8W25D010SL-HM82555830-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P584130

CATALOG NUMBER: HCC8W25D010SL-HM82555830-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67																			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59																			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47																			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43																			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39																			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	33263	33263	33263
5°	34638	33189	31793
10°	35796	32765	30241
15°	36700	32017	28671
20°	36773	30689	27247
25°	36151	28747	25838
30°	34218	26523	24626
35°	31196	23855	23125
40°	27131	21029	21355
45°	23274	18211	19546
50°	19880	15701	17558
55°	17424	13526	15258
60°	15517	11533	12828
65°	13761	9405	10237
70°	12217	6978	5815
75°	10187	3646	1739
80°	8027	1137	284
85°	5732	566	0



TEST NUMBER: P584130
 CATALOG NUMBER: HCC8W25D010SL-HM82555830-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.6	5.1
10°-20°	284.9	14.2
20°-30°	403.2	20.1
30°-40°	421.8	21.0
40°-50°	351.8	17.5
50°-60°	249.5	12.4
60°-70°	143.7	7.2
70°-80°	46.2	2.3
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	789.7	39.3
0°-40°	1211.6	60.3
0°-60°	1812.9	90.2
0°-90°	2009.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2009.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1079	1079	1079	1079	1079	
5°	1119	1104	1072	1040	1027	107
15°	1150	1103	1003	924	898	323
25°	1062	984	845	777	759	485
35°	829	756	634	600	614	514
45°	534	490	418	422	448	414
55°	324	290	252	264	284	293
65°	189	158	129	129	140	188
75°	86	63	31	15	15	93
85°	16	8	2	0	0	20
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584130

CATALOG NUMBER: HCC8W25D010SL-HM82555830-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7
2.5°	1101.2	1099.6	1098.0	1099.6	1098.0	1099.6	1098.0	1098.0	1096.4	1094.8	1094.8
5°	1119.0	1117.4	1117.4	1117.4	1115.7	1114.1	1114.1	1112.5	1109.3	1107.7	1104.5
7.5°	1130.2	1131.8	1131.8	1131.8	1128.6	1128.6	1125.4	1122.2	1119.0	1115.7	1110.9
10°	1143.2	1143.2	1141.6	1139.9	1136.7	1135.1	1133.5	1130.2	1125.4	1119.0	1114.1
12.5°	1148.0	1148.0	1146.4	1143.2	1141.6	1139.9	1138.3	1133.5	1127.0	1119.0	1112.5
15°	1149.6	1146.4	1144.8	1143.2	1139.9	1135.1	1135.1	1128.6	1120.6	1110.9	1102.8
17.5°	1136.7	1138.3	1135.1	1131.8	1127.0	1123.8	1119.0	1114.1	1104.5	1093.1	1085.1
20°	1120.6	1119.0	1117.4	1112.5	1106.1	1104.5	1099.6	1091.5	1083.5	1070.6	1059.3
22.5°	1094.8	1093.1	1089.9	1086.7	1080.3	1077.1	1072.2	1062.5	1051.3	1038.3	1025.5
25°	1062.5	1059.3	1054.5	1048.1	1043.1	1039.9	1033.5	1023.9	1010.9	996.4	983.5
27.5°	1010.9	1015.8	1012.5	1002.9	998.0	991.6	990.0	977.1	965.8	951.2	936.8
30°	961.0	961.0	956.2	951.2	943.2	938.4	932.0	922.2	911.0	893.2	881.9
32.5°	898.1	896.4	890.0	888.4	881.9	872.3	870.7	857.7	846.5	833.5	819.1
35°	828.7	825.5	819.1	814.3	811.0	806.1	801.3	790.1	778.7	765.9	756.2
37.5°	749.7	749.7	748.1	740.0	736.8	733.6	728.8	717.5	711.0	698.2	688.4
40°	674.0	672.4	667.5	665.9	662.7	657.8	654.6	648.2	638.5	628.8	619.1
42.5°	599.8	601.4	594.9	596.5	590.1	586.9	585.3	575.6	570.7	561.1	553.1
45°	533.7	532.1	528.8	527.2	524.0	520.8	517.6	512.7	504.6	495.0	490.2
47.5°	472.4	467.6	467.6	466.0	464.4	457.9	456.2	451.4	446.6	437.0	430.5
50°	414.4	414.4	414.4	412.8	407.9	406.3	403.1	398.3	393.4	386.9	377.3
52.5°	367.7	367.7	367.7	366.0	359.5	357.9	356.3	349.9	343.5	338.5	332.1
55°	324.1	325.7	324.1	320.9	316.0	316.0	311.2	307.9	301.5	296.7	290.2
57.5°	287.0	287.0	283.8	282.2	278.9	277.3	274.1	270.9	262.8	258.0	250.0
60°	251.6	250.0	250.0	246.6	243.4	240.2	238.6	233.8	230.6	222.5	216.0
62.5°	219.2	219.2	216.0	216.0	209.6	209.6	208.0	203.2	198.3	190.2	187.0
65°	188.6	188.6	187.0	185.4	180.6	179.0	177.4	172.5	167.7	162.9	158.0
67.5°	161.2	161.2	158.0	156.4	153.2	151.5	148.3	145.1	140.3	135.5	130.6
70°	135.5	133.9	132.3	130.6	127.3	125.7	122.5	119.3	114.5	111.3	106.5
72.5°	109.7	109.7	108.1	104.8	103.1	101.5	99.9	96.7	91.9	87.1	83.9
75°	85.5	85.5	85.5	82.2	79.0	77.4	77.4	74.2	70.9	66.1	62.9
77.5°	66.1	64.5	62.9	62.9	59.7	58.0	56.4	54.8	50.0	48.4	45.2
80°	45.2	46.8	45.2	43.5	41.9	40.3	40.3	37.1	35.5	32.2	29.0
82.5°	30.6	29.0	29.0	27.4	27.4	25.8	25.8	22.6	21.0	19.4	17.8
85°	16.2	16.2	14.6	14.6	14.6	12.9	12.9	11.2	11.2	9.6	8.0
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584130

CATALOG NUMBER: HCC8W25D010SL-HM82555830-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7
2.5°	1093.1	1089.9	1088.3	1088.3	1086.7	1085.1	1083.5	1081.9	1078.7	1078.7	1075.5
5°	1101.2	1098.0	1096.4	1091.5	1088.3	1088.3	1081.9	1080.3	1075.5	1072.2	1068.9
7.5°	1107.7	1101.2	1096.4	1091.5	1088.3	1085.1	1078.7	1072.2	1065.7	1059.3	1056.1
10°	1107.7	1101.2	1093.1	1085.1	1081.9	1078.7	1070.6	1060.9	1052.9	1046.4	1038.3
12.5°	1104.5	1094.8	1085.1	1078.7	1072.2	1067.3	1057.7	1048.1	1038.3	1025.5	1019.0
15°	1094.8	1081.9	1072.2	1060.9	1056.1	1048.1	1039.9	1025.5	1014.1	1002.9	994.8
17.5°	1075.5	1059.3	1048.1	1036.7	1028.7	1023.9	1010.9	998.0	985.1	972.2	962.6
20°	1046.4	1031.9	1019.0	1004.5	998.0	991.6	975.4	962.6	949.6	935.2	925.4
22.5°	1010.9	996.4	978.7	967.4	957.8	949.6	935.2	920.6	907.8	894.8	881.9
25°	967.4	952.9	936.8	919.0	912.6	904.5	888.4	873.9	859.4	844.9	833.5
27.5°	920.6	901.3	888.4	869.1	862.6	854.5	836.8	820.7	807.7	796.5	783.6
30°	864.2	849.7	831.9	814.3	807.7	799.7	785.2	770.7	757.8	744.9	732.0
32.5°	802.9	788.5	770.7	757.8	748.1	741.7	727.2	714.2	701.4	688.4	677.2
35°	738.4	722.4	709.4	696.6	688.4	680.4	665.9	654.6	644.9	633.7	622.3
37.5°	672.4	661.0	648.2	633.7	625.6	619.1	607.9	594.9	586.9	577.3	569.1
40°	607.9	594.9	583.7	570.7	564.3	559.5	548.2	538.5	530.5	522.4	517.6
42.5°	541.7	530.5	519.2	511.1	506.3	501.4	493.4	482.0	477.2	469.2	464.4
45°	480.4	470.8	462.8	451.4	448.2	445.0	435.4	427.3	422.4	417.6	414.4
47.5°	422.4	416.0	406.3	399.9	395.0	391.8	385.3	378.9	374.1	370.9	367.7
50°	372.5	364.3	357.9	351.5	348.3	343.5	336.9	333.7	330.5	327.3	327.3
52.5°	325.7	317.7	311.2	306.3	303.1	299.9	295.1	293.4	290.2	290.2	288.6
55°	282.2	277.3	270.9	264.4	262.8	261.2	258.0	254.8	253.2	251.6	253.2
57.5°	245.0	240.2	233.8	229.0	227.4	225.8	224.2	220.8	219.2	219.2	219.2
60°	211.2	206.4	201.6	196.7	196.7	193.5	191.9	190.2	188.6	187.0	187.0
62.5°	180.6	175.7	170.9	167.7	166.1	164.5	161.2	159.6	158.0	158.0	156.4
65°	153.2	146.7	145.1	140.3	138.7	137.1	135.5	132.3	130.6	128.9	127.3
67.5°	125.7	122.5	117.7	114.5	112.9	111.3	109.7	106.5	104.8	103.1	99.9
70°	101.5	98.3	95.1	91.9	90.3	88.7	85.5	82.2	80.6	77.4	72.5
72.5°	79.0	75.8	72.5	69.3	67.7	66.1	62.9	59.7	56.4	53.2	50.0
75°	59.7	56.4	51.6	48.4	46.8	46.8	41.9	38.7	35.5	30.6	27.4
77.5°	41.9	37.1	35.5	32.2	30.6	27.4	24.2	21.0	17.8	16.2	12.9
80°	27.4	24.2	21.0	19.4	17.8	16.2	14.6	11.2	8.0	6.4	4.8
82.5°	16.2	14.6	12.9	11.2	9.6	8.0	6.4	6.4	4.8	3.2	1.6
85°	8.0	6.4	4.8	4.8	3.2	3.2	3.2	1.6	1.6	1.6	1.6
87.5°	3.2	1.6	1.6	1.6	1.6	1.6	1.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584130

CATALOG NUMBER: HCC8W25D010SL-HM82555830-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7
2.5°	1073.9	1072.2	1070.6	1068.9	1068.9	1065.7	1065.7	1064.1	1060.9	1059.3	1059.3
5°	1064.1	1059.3	1056.1	1054.5	1052.9	1048.1	1046.4	1043.1	1039.9	1036.7	1035.1
7.5°	1049.7	1041.5	1038.3	1036.7	1031.9	1027.1	1023.9	1019.0	1014.1	1009.3	1007.7
10°	1031.9	1023.9	1015.8	1012.5	1007.7	1004.5	998.0	991.6	986.8	981.9	977.1
12.5°	1009.3	999.7	991.6	988.4	983.5	977.1	967.4	964.2	956.2	952.9	946.4
15°	983.5	972.2	964.2	959.4	954.5	944.8	938.4	932.0	923.8	920.6	914.2
17.5°	951.2	938.4	930.4	925.4	922.2	914.2	904.5	896.4	888.4	885.2	880.3
20°	912.6	904.5	893.2	888.4	885.2	875.5	865.8	862.6	856.1	849.7	844.9
22.5°	869.1	861.0	849.7	844.9	843.3	835.2	827.1	822.3	817.5	812.7	807.7
25°	823.9	814.3	804.5	801.3	798.1	791.7	785.2	782.0	777.1	773.9	770.7
27.5°	775.5	765.9	757.8	753.0	749.7	744.9	741.7	738.4	735.2	732.0	730.4
30°	724.0	714.2	707.8	704.6	701.4	699.8	695.0	693.3	691.6	688.4	690.0
32.5°	672.4	664.3	657.8	653.0	653.0	649.8	648.2	648.2	646.5	646.5	646.5
35°	615.9	611.1	606.3	604.7	603.1	601.4	599.8	601.4	599.8	601.4	603.1
37.5°	564.3	559.5	556.3	554.7	553.1	554.7	553.1	553.1	554.7	557.9	559.5
40°	511.1	507.9	504.6	506.3	504.6	504.6	504.6	509.5	511.1	512.7	514.3
42.5°	461.2	457.9	456.2	456.2	457.9	456.2	459.6	461.2	464.4	469.2	472.4
45°	412.8	411.1	411.1	412.8	411.1	414.4	414.4	417.6	422.4	425.6	428.9
47.5°	367.7	367.7	367.7	369.3	369.3	370.9	374.1	375.7	378.9	382.1	385.3
50°	325.7	327.3	328.9	328.9	328.9	332.1	335.3	336.9	338.5	340.2	345.1
52.5°	288.6	290.2	290.2	291.8	293.4	295.1	296.7	299.9	301.5	304.7	306.3
55°	253.2	253.2	256.4	258.0	258.0	258.0	261.2	261.2	264.4	266.0	269.2
57.5°	219.2	220.8	220.8	222.5	222.5	224.2	225.8	227.4	229.0	230.6	232.2
60°	187.0	187.0	187.0	188.6	190.2	191.9	190.2	193.5	193.5	196.7	198.3
62.5°	156.4	158.0	158.0	158.0	158.0	158.0	158.0	159.6	161.2	162.9	164.5
65°	127.3	127.3	127.3	125.7	127.3	125.7	127.3	128.9	128.9	130.6	132.3
67.5°	98.3	98.3	95.1	95.1	96.7	96.7	96.7	96.7	95.1	98.3	98.3
70°	70.9	69.3	67.7	66.1	66.1	64.5	64.5	62.9	62.9	62.9	62.9
72.5°	46.8	43.5	40.3	38.7	37.1	37.1	33.8	32.2	33.8	33.8	33.8
75°	24.2	21.0	19.4	17.8	16.2	16.2	14.6	14.6	14.6	14.6	14.6
77.5°	9.6	8.0	6.4	6.4	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	3.2	3.2	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	1.6	0.0	0.0	1.6	0.0	1.6	1.6	1.6	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584130

CATALOG NUMBER: HCC8W25D010SL-HM82555830-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7
2.5°	1057.7	1057.7	1056.1	1057.7	1054.5	1056.1	1054.5	1054.5
5°	1033.5	1030.3	1030.3	1030.3	1028.7	1028.7	1027.1	1027.1
7.5°	1004.5	1002.9	1001.3	999.7	998.0	996.4	996.4	996.4
10°	975.4	972.2	972.2	970.6	967.4	965.8	965.8	965.8
12.5°	941.6	940.0	938.4	938.4	932.0	933.6	932.0	932.0
15°	909.4	907.8	907.8	902.9	899.7	899.7	899.7	898.1
17.5°	875.5	873.9	872.3	869.1	865.8	865.8	864.2	865.8
20°	840.1	838.5	835.2	835.2	833.5	831.9	828.7	830.3
22.5°	804.5	801.3	799.7	799.7	798.1	798.1	794.9	794.9
25°	767.5	765.9	764.2	765.9	762.6	762.6	759.4	759.4
27.5°	728.8	727.2	727.2	727.2	725.6	727.2	725.6	725.6
30°	690.0	690.0	688.4	688.4	690.0	688.4	690.0	691.6
32.5°	648.2	648.2	649.8	649.8	651.4	651.4	651.4	651.4
35°	604.7	607.9	607.9	609.5	611.1	612.7	612.7	614.3
37.5°	564.3	565.9	567.5	569.1	572.3	572.3	572.3	572.3
40°	520.8	522.4	525.6	524.0	530.5	532.1	530.5	530.5
42.5°	475.6	478.8	480.4	483.7	485.4	488.6	490.2	490.2
45°	433.7	435.4	438.6	441.8	443.4	448.2	448.2	448.2
47.5°	390.2	393.4	395.0	398.3	399.9	404.7	406.3	404.7
50°	348.3	351.5	354.7	354.7	359.5	361.1	364.3	366.0
52.5°	307.9	309.6	312.8	314.4	317.7	320.9	322.5	324.1
55°	269.2	270.9	274.1	274.1	278.9	280.6	283.8	283.8
57.5°	233.8	235.4	238.6	237.0	240.2	243.4	243.4	241.8
60°	200.0	200.0	200.0	203.2	204.8	206.4	208.0	208.0
62.5°	164.5	167.7	169.3	169.3	170.9	172.5	172.5	170.9
65°	132.3	135.5	137.1	137.1	138.7	138.7	138.7	140.3
67.5°	99.9	99.9	99.9	101.5	99.9	99.9	99.9	99.9
70°	62.9	62.9	62.9	62.9	61.3	62.9	62.9	64.5
72.5°	33.8	33.8	33.8	33.8	33.8	33.8	33.8	33.8
75°	14.6	14.6	14.6	16.2	14.6	14.6	14.6	14.6
77.5°	6.4	4.8	6.4	6.4	4.8	4.8	4.8	4.8
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	0.0	1.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)