

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584147

Luminaire Tested: **HCC8W25D010BZ-HM82555835-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584147
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010BZ-HM82555835-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2129.8 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584147
CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584147

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35258	35258	35258
5°	36715	35182	33700
10°	37944	34731	32057
15°	38903	33935	30392
20°	38978	32527	28884
25°	38321	30472	27389
30°	36269	28115	26107
35°	33070	25282	24514
40°	28757	22289	22635
45°	24670	19306	20719
50°	21070	16647	18613
55°	18472	14333	16171
60°	16442	12230	13599
65°	14593	9974	10850
70°	12947	7402	6167
75°	10794	3860	1835
80°	8488	1208	302
85°	6050	601	0



TEST NUMBER: P584147
 CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.7	5.1
10°-20°	302.0	14.2
20°-30°	427.4	20.1
30°-40°	447.2	21.0
40°-50°	373.0	17.5
50°-60°	264.5	12.4
60°-70°	152.3	7.2
70°-80°	49.0	2.3
80°-90°	6.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	837.1	39.3
0°-40°	1284.3	60.3
0°-60°	1921.7	90.2
0°-90°	2129.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2129.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1143	1143	1143	1143	1143	
5°	1186	1171	1137	1102	1089	114
15°	1219	1169	1063	979	952	343
25°	1126	1042	896	824	805	514
35°	878	802	672	636	651	545
45°	566	520	443	448	475	438
55°	344	308	267	280	301	310
65°	200	168	137	137	149	200
75°	91	67	32	15	15	98
85°	17	9	2	0	0	21
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584147

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4
2.5°	1167.4	1165.7	1163.9	1165.7	1163.9	1165.7	1163.9	1163.9	1162.2	1160.5	1160.5
5°	1186.1	1184.4	1184.4	1184.4	1182.7	1181.0	1181.0	1179.2	1175.8	1174.1	1170.7
7.5°	1198.1	1199.8	1199.8	1199.8	1196.4	1196.4	1192.9	1189.5	1186.1	1182.7	1177.5
10°	1211.8	1211.8	1210.1	1208.4	1204.9	1203.2	1201.5	1198.1	1192.9	1186.1	1181.0
12.5°	1216.9	1216.9	1215.2	1211.8	1210.1	1208.4	1206.6	1201.5	1194.7	1186.1	1179.2
15°	1218.6	1215.2	1213.5	1211.8	1208.4	1203.2	1203.2	1196.4	1187.8	1177.5	1169.0
17.5°	1204.9	1206.6	1203.2	1199.8	1194.7	1191.2	1186.1	1181.0	1170.7	1158.8	1150.2
20°	1187.8	1186.1	1184.4	1179.2	1172.4	1170.7	1165.7	1157.1	1148.5	1134.8	1122.9
22.5°	1160.5	1158.8	1155.4	1152.0	1145.1	1141.7	1136.6	1126.3	1114.3	1100.7	1087.0
25°	1126.3	1122.9	1117.7	1110.9	1105.7	1102.4	1095.6	1085.3	1071.6	1056.2	1042.5
27.5°	1071.6	1076.7	1073.3	1063.0	1057.9	1051.1	1049.3	1035.8	1023.8	1008.4	993.0
30°	1018.6	1018.6	1013.5	1008.4	999.8	994.7	987.8	977.7	965.7	946.8	934.9
32.5°	952.0	950.3	943.4	941.7	934.9	924.6	922.9	909.3	897.3	883.6	868.2
35°	878.5	875.0	868.2	863.1	859.6	854.5	849.5	837.5	825.5	811.8	801.5
37.5°	794.7	794.7	793.0	784.5	781.1	777.7	772.5	760.6	753.7	740.0	729.7
40°	714.4	712.7	707.6	705.9	702.5	697.3	693.9	687.0	676.8	666.5	656.3
42.5°	635.8	637.5	630.7	632.4	625.5	622.1	620.4	610.1	605.0	594.8	586.3
45°	565.7	564.0	560.6	558.9	555.4	552.0	548.6	543.5	535.0	524.7	519.6
47.5°	500.8	495.6	495.6	493.9	492.2	485.4	483.6	478.5	473.5	463.2	456.4
50°	439.2	439.2	439.2	437.5	432.4	430.7	427.3	422.1	417.0	410.2	400.0
52.5°	389.7	389.7	389.7	388.0	381.1	379.4	377.7	370.9	364.0	358.9	352.0
55°	343.6	345.3	343.6	340.2	335.0	335.0	329.9	326.5	319.6	314.5	307.6
57.5°	304.2	304.2	300.8	299.1	295.6	293.9	290.5	287.1	278.6	273.5	264.9
60°	266.6	264.9	264.9	261.5	258.1	254.7	252.9	247.8	244.4	235.8	229.0
62.5°	232.4	232.4	229.0	229.0	222.1	222.1	220.5	215.4	210.3	201.7	198.3
65°	200.0	200.0	198.3	196.6	191.4	189.7	188.0	182.9	177.7	172.6	167.5
67.5°	170.9	170.9	167.5	165.7	162.3	160.6	157.3	153.9	148.7	143.6	138.5
70°	143.6	141.9	140.2	138.5	135.0	133.3	129.9	126.5	121.3	117.9	112.8
72.5°	116.2	116.2	114.5	111.1	109.4	107.6	105.9	102.5	97.4	92.3	88.9
75°	90.6	90.6	90.6	87.2	83.8	82.1	82.1	78.6	75.2	70.1	66.7
77.5°	70.1	68.4	66.7	66.7	63.2	61.5	59.8	58.1	53.0	51.3	47.8
80°	47.8	49.5	47.8	46.1	44.4	42.7	42.7	39.3	37.6	34.1	30.8
82.5°	32.4	30.8	30.8	29.1	29.1	27.4	27.4	24.0	22.3	20.5	18.8
85°	17.1	17.1	15.4	15.4	15.4	13.7	13.7	12.0	12.0	10.3	8.6
87.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584147

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4
2.5°	1158.8	1155.4	1153.7	1153.7	1152.0	1150.2	1148.5	1146.8	1143.4	1143.4	1140.0
5°	1167.4	1163.9	1162.2	1157.1	1153.7	1153.7	1146.8	1145.1	1140.0	1136.6	1133.1
7.5°	1174.1	1167.4	1162.2	1157.1	1153.7	1150.2	1143.4	1136.6	1129.7	1122.9	1119.4
10°	1174.1	1167.4	1158.8	1150.2	1146.8	1143.4	1134.8	1124.6	1116.0	1109.2	1100.7
12.5°	1170.7	1160.5	1150.2	1143.4	1136.6	1131.4	1121.1	1110.9	1100.7	1087.0	1080.2
15°	1160.5	1146.8	1136.6	1124.6	1119.4	1110.9	1102.4	1087.0	1075.0	1063.0	1054.5
17.5°	1140.0	1122.9	1110.9	1099.0	1090.4	1085.3	1071.6	1057.9	1044.2	1030.6	1020.4
20°	1109.2	1093.9	1080.2	1064.8	1057.9	1051.1	1034.0	1020.4	1006.7	991.2	981.0
22.5°	1071.6	1056.2	1037.5	1025.5	1015.2	1006.7	991.2	975.9	962.3	948.6	934.9
25°	1025.5	1010.1	993.0	974.2	967.4	958.8	941.7	926.3	911.0	895.6	883.6
27.5°	975.9	955.4	941.7	921.2	914.4	905.9	887.0	869.9	856.2	844.3	830.6
30°	916.0	900.7	881.9	863.1	856.2	847.8	832.4	816.9	803.2	789.6	776.0
32.5°	851.2	835.8	816.9	803.2	793.0	786.2	770.8	757.1	743.4	729.7	717.9
35°	782.8	765.7	752.0	738.3	729.7	721.3	705.9	693.9	683.6	671.6	659.8
37.5°	712.7	700.7	687.0	671.6	663.1	656.3	644.4	630.7	622.1	611.8	603.3
40°	644.4	630.7	618.7	605.0	598.2	593.1	581.1	570.8	562.3	553.7	548.6
42.5°	574.3	562.3	550.3	541.7	536.6	531.6	523.0	511.0	505.9	497.3	492.2
45°	509.3	499.0	490.5	478.5	475.1	471.8	461.5	452.9	447.8	442.7	439.2
47.5°	447.8	440.9	430.7	423.8	418.7	415.3	408.5	401.7	396.5	393.1	389.7
50°	394.8	386.3	379.4	372.6	369.2	364.0	357.2	353.7	350.3	347.0	347.0
52.5°	345.3	336.7	329.9	324.7	321.3	317.9	312.8	311.0	307.6	307.6	305.9
55°	299.1	293.9	287.1	280.3	278.6	276.9	273.5	270.1	268.4	266.6	268.4
57.5°	259.8	254.7	247.8	242.7	241.0	239.3	237.5	234.1	232.4	232.4	232.4
60°	223.8	218.8	213.7	208.5	208.5	205.1	203.4	201.7	200.0	198.3	198.3
62.5°	191.4	186.3	181.2	177.7	176.0	174.3	170.9	169.2	167.5	167.5	165.7
65°	162.3	155.6	153.9	148.7	147.0	145.3	143.6	140.2	138.5	136.7	135.0
67.5°	133.3	129.9	124.8	121.3	119.6	117.9	116.2	112.8	111.1	109.4	105.9
70°	107.6	104.2	100.8	97.4	95.7	94.1	90.6	87.2	85.5	82.1	76.9
72.5°	83.8	80.4	76.9	73.5	71.8	70.1	66.7	63.2	59.8	56.4	53.0
75°	63.2	59.8	54.7	51.3	49.5	49.5	44.4	41.0	37.6	32.4	29.1
77.5°	44.4	39.3	37.6	34.1	32.4	29.1	25.7	22.3	18.8	17.1	13.7
80°	29.1	25.7	22.3	20.5	18.8	17.1	15.4	12.0	8.6	6.8	5.1
82.5°	17.1	15.4	13.7	12.0	10.3	8.6	6.8	6.8	5.1	3.4	1.7
85°	8.6	6.8	5.1	5.1	3.4	3.4	3.4	1.7	1.7	1.7	1.7
87.5°	3.4	1.7	1.7	1.7	1.7	1.7	1.7	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584147

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4
2.5°	1138.3	1136.6	1134.8	1133.1	1133.1	1129.7	1129.7	1128.0	1124.6	1122.9	1122.9
5°	1128.0	1122.9	1119.4	1117.7	1116.0	1110.9	1109.2	1105.7	1102.4	1099.0	1097.3
7.5°	1112.6	1104.1	1100.7	1099.0	1093.9	1088.7	1085.3	1080.2	1075.0	1069.9	1068.2
10°	1093.9	1085.3	1076.7	1073.3	1068.2	1064.8	1057.9	1051.1	1045.9	1040.9	1035.8
12.5°	1069.9	1059.6	1051.1	1047.6	1042.5	1035.8	1025.5	1022.1	1013.5	1010.1	1003.2
15°	1042.5	1030.6	1022.1	1016.9	1011.8	1001.5	994.7	987.8	979.3	975.9	969.1
17.5°	1008.4	994.7	986.1	981.0	977.7	969.1	958.8	950.3	941.7	938.3	933.1
20°	967.4	958.8	946.8	941.7	938.3	928.0	917.7	914.4	907.6	900.7	895.6
22.5°	921.2	912.7	900.7	895.6	893.9	885.3	876.8	871.6	866.5	861.4	856.2
25°	873.3	863.1	852.8	849.5	846.0	839.2	832.4	828.9	823.8	820.4	816.9
27.5°	822.1	811.8	803.2	798.1	794.7	789.6	786.2	782.8	779.4	776.0	774.3
30°	767.4	757.1	750.3	746.9	743.4	741.7	736.6	734.9	733.2	729.7	731.5
32.5°	712.7	704.2	697.3	692.2	692.2	688.8	687.0	687.0	685.3	685.3	685.3
35°	652.9	647.8	642.6	640.9	639.2	637.5	635.8	637.5	635.8	637.5	639.2
37.5°	598.2	593.1	589.7	588.0	586.3	588.0	586.3	586.3	588.0	591.4	593.1
40°	541.7	538.3	535.0	536.6	535.0	535.0	535.0	540.0	541.7	543.5	545.2
42.5°	488.8	485.4	483.6	483.6	485.4	483.6	487.1	488.8	492.2	497.3	500.8
45°	437.5	435.8	435.8	437.5	435.8	439.2	439.2	442.7	447.8	451.2	454.6
47.5°	389.7	389.7	389.7	391.4	391.4	393.1	396.5	398.3	401.7	405.1	408.5
50°	345.3	347.0	348.6	348.6	348.6	352.0	355.5	357.2	358.9	360.6	365.7
52.5°	305.9	307.6	307.6	309.3	311.0	312.8	314.5	317.9	319.6	323.0	324.7
55°	268.4	268.4	271.8	273.5	273.5	273.5	276.9	276.9	280.3	282.1	285.4
57.5°	232.4	234.1	234.1	235.8	235.8	237.5	239.3	241.0	242.7	244.4	246.1
60°	198.3	198.3	198.3	200.0	201.7	203.4	201.7	205.1	205.1	208.5	210.3
62.5°	165.7	167.5	167.5	167.5	167.5	167.5	167.5	169.2	170.9	172.6	174.3
65°	135.0	135.0	135.0	133.3	135.0	133.3	135.0	136.7	136.7	138.5	140.2
67.5°	104.2	104.2	100.8	100.8	102.5	102.5	102.5	102.5	100.8	104.2	104.2
70°	75.2	73.5	71.8	70.1	70.1	68.4	68.4	66.7	66.7	66.7	66.7
72.5°	49.5	46.1	42.7	41.0	39.3	39.3	35.8	34.1	35.8	35.8	35.8
75°	25.7	22.3	20.5	18.8	17.1	17.1	15.4	15.4	15.4	15.4	15.4
77.5°	10.3	8.6	6.8	6.8	5.1	5.1	5.1	5.1	5.1	5.1	5.1
80°	3.4	3.4	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	1.7	0.0	0.0	1.7	0.0	1.7	1.7	1.7	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584147

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4	1143.4
2.5°	1121.1	1121.1	1119.4	1121.1	1117.7	1119.4	1117.7	1117.7
5°	1095.6	1092.1	1092.1	1092.1	1090.4	1090.4	1088.7	1088.7
7.5°	1064.8	1063.0	1061.3	1059.6	1057.9	1056.2	1056.2	1056.2
10°	1034.0	1030.6	1030.6	1028.9	1025.5	1023.8	1023.8	1023.8
12.5°	998.1	996.4	994.7	994.7	987.8	989.5	987.8	987.8
15°	964.0	962.3	962.3	957.1	953.7	953.7	953.7	952.0
17.5°	928.0	926.3	924.6	921.2	917.7	917.7	916.0	917.7
20°	890.5	888.7	885.3	885.3	883.6	881.9	878.5	880.2
22.5°	852.8	849.5	847.8	847.8	846.0	846.0	842.6	842.6
25°	813.5	811.8	810.1	811.8	808.4	808.4	805.0	805.0
27.5°	772.5	770.8	770.8	770.8	769.1	770.8	769.1	769.1
30°	731.5	731.5	729.7	729.7	731.5	729.7	731.5	733.2
32.5°	687.0	687.0	688.8	688.8	690.5	690.5	690.5	690.5
35°	640.9	644.4	644.4	646.1	647.8	649.5	649.5	651.2
37.5°	598.2	599.8	601.6	603.3	606.7	606.7	606.7	606.7
40°	552.0	553.7	557.1	555.4	562.3	564.0	562.3	562.3
42.5°	504.2	507.6	509.3	512.7	514.5	517.9	519.6	519.6
45°	459.8	461.5	464.9	468.3	470.1	475.1	475.1	475.1
47.5°	413.6	417.0	418.7	422.1	423.8	429.0	430.7	429.0
50°	369.2	372.6	376.0	376.0	381.1	382.8	386.3	388.0
52.5°	326.5	328.2	331.6	333.3	336.7	340.2	341.9	343.6
55°	285.4	287.1	290.5	290.5	295.6	297.4	300.8	300.8
57.5°	247.8	249.5	252.9	251.2	254.7	258.1	258.1	256.4
60°	212.0	212.0	212.0	215.4	217.1	218.8	220.5	220.5
62.5°	174.3	177.7	179.4	179.4	181.2	182.9	182.9	181.2
65°	140.2	143.6	145.3	145.3	147.0	147.0	147.0	148.7
67.5°	105.9	105.9	105.9	107.6	105.9	105.9	105.9	105.9
70°	66.7	66.7	66.7	66.7	64.9	66.7	66.7	68.4
72.5°	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.8
75°	15.4	15.4	15.4	17.1	15.4	15.4	15.4	15.4
77.5°	6.8	5.1	6.8	6.8	5.1	5.1	5.1	5.1
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	0.0	1.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)