

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584174

Luminaire Tested: **HCC8S25D010SL-HM82555927-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584174
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010SL-HM82555927-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1896.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584174
CATALOG NUMBER: HCC8S25D010SL-HM82555927-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584174

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	30762	30762	30762
5°	31168	30629	30341
10°	31487	30316	29859
15°	31806	29677	29083
20°	31644	28585	27929
25°	30904	26872	26512
30°	29354	24942	24850
35°	26720	22763	22963
40°	23432	20373	21121
45°	20213	18124	19397
50°	17697	15908	17572
55°	15682	13672	15467
60°	14129	11502	12816
65°	12732	9237	9814
70°	11171	6726	5401
75°	9519	3491	1430
80°	7334	959	231
85°	4706	0	0



TEST NUMBER: P584174
 CATALOG NUMBER: HCC8S25D010SL-HM82555927-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	5.0
10°-20°	264.6	14.0
20°-30°	375.6	19.8
30°-40°	395.3	20.9
40°-50°	336.3	17.7
50°-60°	243.0	12.8
60°-70°	138.2	7.3
70°-80°	43.5	2.3
80°-90°	5.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	734.3	38.7
0°-40°	1129.6	59.6
0°-60°	1708.9	90.1
0°-90°	1896.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1896.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	998	998	998	998	998	
5°	1007	1002	990	983	980	96
15°	996	971	930	912	911	281
25°	908	863	790	776	779	416
35°	710	669	605	601	610	442
45°	464	446	416	426	445	360
55°	292	270	254	269	288	263
65°	174	150	127	125	134	173
75°	80	61	29	13	12	86
85°	13	8	0	0	0	17
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584174

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6
2.5°	1002.9	1004.2	1001.5	1001.5	1004.2	1001.5	1002.9	1002.9	1001.5	1001.5	1000.2
5°	1006.9	1005.6	1005.6	1005.6	1006.9	1004.2	1002.9	1004.2	1001.5	1001.5	1001.5
7.5°	1008.3	1008.3	1006.9	1005.6	1005.6	1005.6	1004.2	1002.9	1001.5	999.0	997.6
10°	1005.6	1005.6	1006.9	1004.2	1004.2	1001.5	1001.5	999.0	999.0	996.3	992.2
12.5°	1002.9	1001.5	1001.5	999.0	999.0	996.3	996.3	992.2	990.9	987.0	982.9
15°	996.3	994.9	992.2	990.9	989.5	988.3	985.6	984.3	980.2	975.0	970.9
17.5°	982.9	981.6	980.2	977.6	975.0	973.6	972.3	968.2	962.9	958.9	952.3
20°	964.3	962.9	962.9	958.9	957.6	953.6	952.3	947.0	943.0	935.0	929.6
22.5°	938.9	940.3	937.6	935.0	932.3	928.3	925.7	920.3	913.7	905.6	899.0
25°	908.3	909.7	907.0	904.4	900.3	897.7	895.1	887.0	880.4	871.1	863.1
27.5°	869.7	869.7	869.7	867.0	860.4	859.1	856.4	848.4	839.1	831.1	823.2
30°	824.4	823.2	823.2	819.1	816.4	811.1	807.1	800.5	793.8	784.5	775.1
32.5°	769.9	771.1	767.2	764.5	760.4	760.4	755.2	749.9	741.8	732.5	723.2
35°	709.8	711.2	708.6	707.3	700.5	699.2	697.9	691.2	685.9	679.2	668.6
37.5°	648.6	647.2	646.0	646.0	642.0	639.3	636.7	632.7	624.7	619.3	614.0
40°	582.1	582.1	582.1	580.7	579.4	576.7	575.3	572.7	567.4	562.1	558.0
42.5°	522.1	522.1	520.8	519.4	516.8	518.1	515.4	512.7	507.4	503.4	500.8
45°	463.5	463.5	463.5	464.8	462.1	458.2	458.2	455.5	452.8	450.1	446.2
47.5°	411.5	415.6	412.9	411.5	412.9	407.6	407.6	404.9	402.2	399.5	394.2
50°	368.9	368.9	368.9	366.3	365.0	365.0	360.9	358.2	357.0	354.3	348.9
52.5°	330.3	327.6	327.6	326.4	325.0	322.3	322.3	319.6	314.4	311.7	307.6
55°	291.7	291.7	290.4	289.0	287.7	286.3	285.0	281.0	278.4	274.3	270.4
57.5°	257.0	259.7	258.4	255.7	253.1	253.1	250.4	247.7	243.7	239.8	235.7
60°	229.1	227.8	227.8	226.4	223.7	222.5	221.1	217.1	213.1	209.1	205.1
62.5°	199.8	199.8	199.8	197.1	194.4	193.1	191.7	189.2	183.8	179.8	177.2
65°	174.5	173.1	171.8	170.5	169.2	166.5	165.1	162.5	158.5	154.5	150.5
67.5°	149.2	147.9	147.9	146.5	142.5	141.1	141.1	137.2	133.2	129.1	125.2
70°	123.9	123.9	123.9	121.2	119.8	118.6	117.2	114.5	110.5	106.6	102.5
72.5°	102.5	101.2	101.2	99.9	95.9	94.6	93.2	90.5	86.6	83.9	81.2
75°	79.9	79.9	78.5	77.3	76.0	74.6	73.3	70.6	66.6	62.6	61.3
77.5°	61.3	59.9	59.9	58.6	56.0	54.6	54.6	51.9	47.9	45.3	42.6
80°	41.3	42.6	41.3	39.9	38.6	37.3	36.0	34.7	32.0	29.3	26.6
82.5°	25.4	26.6	25.4	25.4	24.0	22.7	22.7	20.0	18.6	17.3	15.9
85°	13.3	13.3	13.3	13.3	12.0	12.0	12.0	10.7	9.3	8.0	8.0
87.5°	4.0	5.4	4.0	4.0	4.0	4.0	4.0	4.0	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584174

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6
2.5°	1001.5	1000.2	999.0	999.0	999.0	999.0	999.0	997.6	996.3	996.3	996.3
5°	999.0	999.0	999.0	997.6	996.3	996.3	993.6	992.2	990.9	989.5	988.3
7.5°	996.3	993.6	992.2	990.9	989.5	989.5	987.0	984.3	984.3	981.6	978.9
10°	988.3	987.0	984.3	981.6	980.2	978.9	976.3	972.3	970.9	968.2	965.6
12.5°	978.9	976.3	973.6	968.2	967.0	965.6	960.3	956.3	953.6	952.3	945.7
15°	967.0	961.6	957.6	950.9	949.6	947.0	943.0	938.9	933.7	929.6	926.9
17.5°	945.7	940.3	933.7	926.9	924.4	924.4	917.6	912.3	905.6	903.0	897.7
20°	920.3	913.7	908.3	900.3	896.3	892.4	888.3	880.4	875.0	871.1	864.3
22.5°	891.0	881.7	875.0	867.0	860.4	856.4	849.7	843.1	836.4	832.5	827.1
25°	853.8	845.7	835.1	827.1	823.2	817.8	809.8	803.1	796.5	789.8	787.1
27.5°	812.5	801.8	792.4	783.1	779.2	775.1	765.8	757.9	752.5	745.9	743.2
30°	767.2	756.5	745.9	737.9	733.9	727.2	721.9	712.5	705.9	700.5	693.9
32.5°	715.2	707.3	697.9	685.9	683.3	678.0	669.9	666.0	657.9	654.0	648.6
35°	659.2	654.0	644.7	635.3	631.3	628.6	622.0	614.0	608.6	604.7	602.0
37.5°	606.0	599.3	590.0	583.4	580.7	576.7	568.7	564.7	559.4	556.7	551.4
40°	548.7	542.1	535.4	531.5	527.4	524.7	519.4	515.4	510.1	506.1	504.8
42.5°	492.8	488.8	483.4	478.2	476.8	472.8	470.2	466.2	462.1	460.8	456.8
45°	442.2	438.2	432.8	427.6	426.2	423.5	422.2	418.2	415.6	415.6	415.6
47.5°	391.6	387.6	382.2	379.6	380.9	375.6	375.6	374.3	371.6	371.6	372.9
50°	346.3	341.0	339.6	336.9	334.3	331.6	333.0	329.0	329.0	331.6	330.3
52.5°	303.7	298.3	297.0	294.4	293.0	293.0	291.7	291.7	290.4	291.7	291.7
55°	265.0	261.1	258.4	255.7	254.3	254.3	254.3	253.1	251.8	254.3	255.7
57.5°	230.4	229.1	226.4	222.5	221.1	219.8	218.4	218.4	218.4	218.4	219.8
60°	199.8	197.1	194.4	190.5	190.5	189.2	187.8	186.5	186.5	186.5	186.5
62.5°	173.1	169.2	165.1	162.5	161.1	159.9	158.5	155.8	155.8	155.8	155.8
65°	146.5	142.5	139.8	137.2	134.5	134.5	131.8	130.5	127.9	126.6	123.9
67.5°	121.2	118.6	115.9	111.9	110.5	109.2	106.6	105.2	101.2	99.9	98.5
70°	98.5	94.6	91.9	89.2	88.0	85.3	82.6	79.9	77.3	74.6	71.9
72.5°	77.3	73.3	70.6	67.9	65.3	65.3	61.3	58.6	54.6	51.9	47.9
75°	57.2	53.3	50.6	46.7	45.3	44.0	39.9	37.3	33.3	29.3	26.6
77.5°	38.6	36.0	33.3	29.3	26.6	26.6	22.7	20.0	17.3	13.3	12.0
80°	24.0	21.3	18.6	15.9	15.9	13.3	12.0	9.3	6.6	5.4	4.0
82.5°	13.3	12.0	10.7	8.0	8.0	6.6	5.4	4.0	2.7	1.3	1.3
85°	6.6	5.4	4.0	4.0	2.7	2.7	2.7	1.3	1.3	0.0	0.0
87.5°	2.7	1.3	1.3	1.3	1.3	1.3	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584174

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6
2.5°	994.9	994.9	993.6	993.6	993.6	992.2	993.6	992.2	992.2	992.2	993.6
5°	989.5	987.0	987.0	985.6	985.6	984.3	985.6	984.3	982.9	981.6	982.9
7.5°	978.9	976.3	975.0	973.6	973.6	973.6	972.3	970.9	972.3	968.2	970.9
10°	964.3	962.9	960.3	958.9	957.6	958.9	957.6	955.0	955.0	955.0	953.6
12.5°	945.7	943.0	941.6	940.3	937.6	937.6	938.9	936.4	936.4	933.7	933.7
15°	923.0	920.3	917.6	917.6	915.0	915.0	913.7	913.7	912.3	911.0	911.0
17.5°	895.1	891.0	888.3	889.7	888.3	887.0	887.0	884.4	883.1	884.4	884.4
20°	861.7	859.1	856.4	857.7	855.0	853.8	855.0	851.1	852.4	852.4	852.4
22.5°	824.4	823.2	819.1	819.1	816.4	815.1	816.4	816.4	817.8	816.4	816.4
25°	783.1	780.5	777.8	777.8	776.5	775.1	776.5	777.8	776.5	777.8	777.8
27.5°	739.2	735.2	735.2	732.5	732.5	733.9	732.5	733.9	735.2	735.2	737.9
30°	691.2	689.9	688.5	687.3	687.3	688.5	688.5	688.5	689.9	692.6	692.6
32.5°	646.0	643.3	640.6	640.6	643.3	642.0	643.3	643.3	646.0	646.0	648.6
35°	596.6	596.6	594.1	595.3	595.3	595.3	595.3	598.0	600.7	602.0	604.7
37.5°	551.4	547.4	548.7	548.7	550.1	548.7	552.8	552.8	555.4	555.4	558.0
40°	502.2	502.2	503.4	502.2	503.4	503.4	506.1	508.8	510.1	512.7	514.1
42.5°	455.5	458.2	455.5	456.8	458.2	459.5	460.8	462.1	467.5	470.2	474.1
45°	412.9	414.2	415.6	416.9	415.6	418.2	419.5	422.2	426.2	427.6	428.9
47.5°	371.6	372.9	374.3	375.6	375.6	378.2	379.6	382.2	384.9	386.3	387.6
50°	331.6	334.3	335.7	335.7	336.9	339.6	342.3	342.3	345.0	348.9	350.3
52.5°	295.6	295.6	298.3	299.7	301.0	301.0	305.0	306.3	307.6	310.3	313.0
55°	255.7	259.7	261.1	261.1	263.8	266.3	267.7	269.0	269.0	274.3	274.3
57.5°	221.1	222.5	225.1	225.1	225.1	229.1	229.1	231.8	233.0	234.4	237.1
60°	186.5	189.2	189.2	190.5	189.2	191.7	193.1	195.8	197.1	198.5	199.8
62.5°	154.5	154.5	155.8	155.8	155.8	155.8	158.5	158.5	161.1	162.5	163.8
65°	123.9	123.9	123.9	123.9	123.9	123.9	123.9	123.9	125.2	125.2	127.9
67.5°	95.9	94.6	91.9	93.2	91.9	91.9	90.5	90.5	91.9	91.9	94.6
70°	69.2	67.9	65.3	65.3	63.9	62.6	61.3	59.9	58.6	58.6	58.6
72.5°	45.3	42.6	38.6	37.3	37.3	34.7	32.0	30.6	30.6	30.6	30.6
75°	22.7	20.0	17.3	15.9	15.9	13.3	14.7	13.3	13.3	13.3	13.3
77.5°	9.3	6.6	5.4	5.4	5.4	4.0	4.0	4.0	4.0	4.0	4.0
80°	2.7	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
82.5°	1.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584174

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	997.6	997.6	997.6	997.6	997.6	997.6	997.6	997.6
2.5°	992.2	992.2	989.5	990.9	990.9	990.9	990.9	990.9
5°	980.2	981.6	980.2	981.6	981.6	980.2	980.2	980.2
7.5°	968.2	969.6	968.2	969.6	969.6	969.6	968.2	968.2
10°	953.6	953.6	953.6	953.6	953.6	952.3	953.6	953.6
12.5°	933.7	933.7	933.7	935.0	935.0	933.7	933.7	932.3
15°	912.3	909.7	911.0	912.3	911.0	911.0	911.0	911.0
17.5°	883.1	884.4	883.1	883.1	883.1	883.1	884.4	883.1
20°	852.4	852.4	853.8	852.4	852.4	852.4	852.4	851.1
22.5°	817.8	816.4	816.4	817.8	817.8	816.4	817.8	817.8
25°	779.2	780.5	779.2	779.2	780.5	780.5	780.5	779.2
27.5°	737.9	739.2	740.5	739.2	739.2	739.2	740.5	741.8
30°	695.3	697.9	695.3	695.3	697.9	696.6	697.9	697.9
32.5°	649.9	654.0	651.3	654.0	654.0	655.3	654.0	655.3
35°	604.7	608.6	608.6	608.6	610.0	611.3	611.3	610.0
37.5°	562.1	563.4	563.4	566.0	567.4	568.7	568.7	567.4
40°	518.1	520.8	522.1	522.1	522.1	524.7	527.4	524.7
42.5°	475.5	476.8	478.2	478.2	480.9	482.1	483.4	483.4
45°	434.2	436.9	438.2	439.6	440.8	443.5	442.2	444.8
47.5°	391.6	395.6	396.9	398.3	400.9	402.2	403.6	404.9
50°	353.0	355.6	355.6	358.2	362.3	362.3	365.0	366.3
52.5°	314.4	315.7	316.9	318.3	321.0	323.7	323.7	326.4
55°	277.0	278.4	278.4	279.7	281.0	286.3	287.7	287.7
57.5°	238.4	238.4	241.1	242.4	243.7	246.4	246.4	246.4
60°	201.2	202.4	202.4	203.7	205.1	207.8	209.1	207.8
62.5°	163.8	165.1	165.1	166.5	169.2	170.5	169.2	169.2
65°	129.1	130.5	130.5	131.8	134.5	134.5	133.2	134.5
67.5°	94.6	94.6	94.6	94.6	94.6	94.6	94.6	94.6
70°	59.9	58.6	57.2	58.6	58.6	58.6	57.2	59.9
72.5°	29.3	30.6	30.6	30.6	30.6	30.6	30.6	29.3
75°	13.3	13.3	12.0	12.0	12.0	13.3	13.3	12.0
77.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)