

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584183

Luminaire Tested: **HCC8S25D010SL-HM82555927-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584183
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010SL-HM82555927-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1885.3 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584183
CATALOG NUMBER: HCC8S25D010SL-HM82555927-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584183

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	28906	28906	28906
5°	29964	28809	27822
10°	30811	28560	26681
15°	31496	28055	25504
20°	31549	26958	24470
25°	30942	25464	23603
30°	29347	23611	22568
35°	26663	21502	21555
40°	23315	19298	20312
45°	20208	17186	18931
50°	17692	15265	17246
55°	15752	13532	15607
60°	14209	12156	13710
65°	12827	10689	11952
70°	11531	8998	8881
75°	10151	7137	6672
80°	8506	5913	6393
85°	6581	5201	5626



TEST NUMBER: P584183
 CATALOG NUMBER: HCC8S25D010SL-HM82555927-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	4.7
10°-20°	249.1	13.2
20°-30°	356.0	18.9
30°-40°	378.2	20.1
40°-50°	325.6	17.3
50°-60°	243.5	12.9
60°-70°	155.3	8.2
70°-80°	70.7	3.7
80°-90°	18.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	693.5	36.8
0°-40°	1071.7	56.8
0°-60°	1640.8	87.0
0°-90°	1885.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1885.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	937	937	937	937	937	
5°	968	955	931	907	899	93
15°	987	953	879	819	799	278
25°	909	852	748	703	694	416
35°	708	659	571	557	573	441
45°	463	438	394	405	434	360
55°	293	269	252	273	290	263
65°	176	156	146	153	164	175
75°	85	73	60	55	56	91
85°	19	16	15	16	16	22
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584183

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4
2.5°	954.7	952.0	953.4	952.0	953.4	953.4	950.7	950.7	950.7	950.7	946.7
5°	968.0	966.6	966.6	965.4	964.0	965.4	964.0	962.7	960.0	958.7	954.7
7.5°	975.9	975.9	975.9	975.9	974.7	973.4	972.0	969.3	966.6	964.0	961.4
10°	984.0	985.4	984.0	982.7	981.3	978.6	977.3	974.7	970.7	966.6	964.0
12.5°	987.9	987.9	986.6	986.6	984.0	982.7	978.6	974.7	970.7	966.6	960.0
15°	986.6	986.6	985.4	984.0	980.0	978.6	975.9	972.0	965.4	960.0	953.4
17.5°	978.6	977.3	974.7	974.7	969.3	968.0	965.4	960.0	953.4	945.3	937.4
20°	961.4	961.4	960.0	958.7	953.4	949.4	946.7	940.0	934.8	925.4	917.4
22.5°	937.4	940.0	937.4	934.8	928.0	926.7	922.8	914.7	906.7	896.1	886.8
25°	909.4	908.1	906.7	904.0	898.8	896.1	890.8	882.8	874.8	862.8	852.1
27.5°	873.4	868.1	868.1	862.8	858.8	854.8	852.1	844.1	833.5	824.2	810.8
30°	824.2	825.5	818.9	817.6	810.8	808.2	802.9	794.9	785.6	774.9	764.3
32.5°	770.9	767.0	767.0	761.6	756.3	752.3	750.9	741.6	733.7	723.0	712.4
35°	708.3	708.3	704.4	703.0	697.7	695.1	691.0	685.8	676.5	667.0	659.1
37.5°	647.1	644.5	643.1	640.5	636.4	632.5	632.5	623.2	621.8	611.2	600.5
40°	579.2	581.9	579.2	575.2	573.8	571.2	569.9	564.5	560.6	551.3	544.6
42.5°	521.9	519.3	519.3	518.0	512.6	512.6	510.0	507.3	500.7	498.0	490.0
45°	463.4	466.0	462.0	463.4	458.1	458.1	458.1	452.7	447.4	443.4	438.1
47.5°	412.8	414.1	414.1	410.1	408.7	408.7	406.1	403.5	399.4	394.1	390.1
50°	368.8	370.1	367.5	366.2	363.5	362.2	362.2	356.8	354.2	348.8	346.1
52.5°	328.9	328.9	327.5	327.5	323.6	323.6	320.9	316.9	314.3	311.6	305.0
55°	293.0	293.0	291.6	290.3	290.3	286.2	284.9	281.0	278.3	273.0	269.0
57.5°	258.3	259.7	258.3	257.0	255.6	254.3	251.7	247.7	245.0	241.0	238.3
60°	230.4	230.4	229.0	227.7	225.0	223.7	222.3	219.7	215.7	213.0	209.1
62.5°	203.7	202.3	201.1	199.8	197.1	197.1	194.4	191.7	187.8	185.1	182.4
65°	175.8	175.8	174.4	174.4	173.1	170.5	169.1	167.8	162.4	161.1	155.8
67.5°	150.4	151.8	149.2	149.2	146.5	146.5	145.1	141.1	139.8	137.2	134.5
70°	127.9	127.9	127.9	126.5	123.8	122.5	121.1	118.6	117.2	114.5	111.8
72.5°	105.2	105.2	103.9	103.9	102.5	101.2	99.8	97.2	97.2	94.6	91.9
75°	85.2	85.2	83.9	82.6	81.2	81.2	79.9	78.5	75.9	74.6	73.2
77.5°	65.3	65.3	65.3	63.9	62.6	62.6	62.6	59.9	57.2	57.2	56.0
80°	47.9	47.9	46.7	46.7	45.3	45.3	45.3	44.0	42.6	41.3	39.9
82.5°	32.0	32.0	32.0	32.0	30.6	30.6	30.6	29.3	27.9	27.9	27.9
85°	18.6	18.6	18.6	18.6	17.3	17.3	17.3	17.3	17.3	15.9	15.9
87.5°	8.0	6.6	8.0	6.6	8.0	6.6	8.0	6.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584183

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4
2.5°	948.0	946.7	945.3	944.1	944.1	942.7	940.0	938.7	937.4	936.0	936.0
5°	953.4	952.0	949.4	946.7	945.3	942.7	940.0	937.4	934.8	930.7	929.4
7.5°	957.3	953.4	950.7	945.3	944.1	941.4	937.4	933.4	928.0	922.8	918.7
10°	957.3	952.0	948.0	941.4	938.7	936.0	930.7	924.1	917.4	912.1	905.4
12.5°	954.7	948.0	941.4	934.8	930.7	926.7	918.7	912.1	904.0	896.1	890.8
15°	945.3	937.4	929.4	921.4	917.4	912.1	904.0	894.7	886.8	878.8	869.5
17.5°	928.0	920.1	910.8	901.5	896.1	892.1	880.1	873.4	861.5	853.5	845.5
20°	905.4	896.1	884.1	874.8	868.1	864.1	854.8	842.8	833.5	821.5	813.5
22.5°	876.1	864.1	852.1	842.8	836.2	830.9	818.9	806.9	798.9	788.3	779.0
25°	841.6	829.6	817.6	804.2	797.6	792.2	781.6	770.9	760.3	748.4	740.3
27.5°	800.3	786.9	776.3	764.3	757.7	749.6	737.7	727.0	716.4	708.3	697.7
30°	755.0	740.3	729.6	717.6	711.0	704.4	692.4	681.7	672.4	663.1	657.7
32.5°	700.4	689.7	679.0	667.0	661.8	657.7	645.7	635.2	624.5	616.5	612.5
35°	648.4	636.4	627.1	616.5	609.8	605.8	595.1	585.8	580.6	571.2	565.9
37.5°	593.8	584.5	573.8	563.2	559.2	555.2	547.2	537.9	530.0	523.2	520.7
40°	536.6	528.6	519.3	512.6	508.7	504.6	498.0	491.3	486.0	479.4	476.7
42.5°	482.0	476.7	468.7	460.7	456.7	455.4	447.4	442.0	439.4	436.8	434.1
45°	432.7	424.8	419.4	414.1	410.1	407.5	403.5	399.4	396.8	394.1	391.5
47.5°	384.8	378.1	372.8	368.8	364.9	363.5	360.8	356.8	354.2	354.2	354.2
50°	340.9	335.6	330.2	327.5	326.2	323.6	320.9	319.6	318.2	318.2	318.2
52.5°	302.3	296.9	293.0	290.3	290.3	287.6	284.9	283.7	283.7	283.7	283.7
55°	266.3	262.3	259.7	257.0	254.3	252.9	252.9	252.9	251.7	251.7	252.9
57.5°	234.3	231.7	227.7	225.0	223.7	223.7	222.3	221.1	222.3	223.7	225.0
60°	205.0	202.3	201.1	197.1	197.1	197.1	195.7	195.7	195.7	197.1	198.4
62.5°	178.4	177.1	174.4	173.1	171.7	171.7	170.5	170.5	170.5	170.5	171.7
65°	154.5	151.8	149.2	149.2	149.2	147.8	147.8	145.1	146.5	146.5	145.1
67.5°	131.8	129.1	127.9	126.5	125.2	125.2	123.8	122.5	121.1	121.1	121.1
70°	110.5	107.9	107.9	105.2	105.2	103.9	102.5	102.5	101.2	99.8	98.5
72.5°	89.2	87.8	86.6	85.2	85.2	85.2	83.9	82.6	81.2	79.9	77.3
75°	70.6	70.6	67.9	66.6	66.6	65.3	63.9	62.6	61.2	59.9	58.6
77.5°	54.6	53.3	50.6	49.2	49.2	49.2	47.9	46.7	45.3	44.0	42.6
80°	39.9	38.6	37.2	36.0	36.0	36.0	34.7	34.7	33.3	33.3	33.3
82.5°	26.6	26.6	25.3	25.3	25.3	25.3	24.0	24.0	24.0	24.0	24.0
85°	15.9	15.9	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584183

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4
2.5°	933.4	933.4	930.7	929.4	928.0	929.4	926.7	925.4	924.1	924.1	922.8
5°	925.4	924.1	918.7	917.4	916.0	914.7	912.1	909.4	906.7	905.4	904.0
7.5°	914.7	910.8	905.4	904.0	902.8	898.8	894.7	892.1	888.1	886.8	884.1
10°	900.1	894.7	890.8	886.8	884.1	880.1	876.1	872.2	866.8	865.5	861.5
12.5°	882.8	876.1	868.1	866.8	862.8	857.5	852.1	848.2	844.1	841.6	837.5
15°	861.5	854.8	846.8	842.8	838.9	834.8	828.2	822.8	818.9	814.9	810.8
17.5°	836.2	828.2	821.5	817.6	814.9	808.2	802.9	796.2	792.2	788.3	784.3
20°	805.6	798.9	789.6	785.6	784.3	779.0	772.3	769.7	764.3	760.3	757.7
22.5°	770.9	764.3	756.3	753.6	748.4	745.7	738.9	736.4	733.7	729.6	728.3
25°	732.3	725.7	719.0	717.6	713.7	711.0	707.1	703.0	703.0	699.0	699.0
27.5°	692.4	685.8	680.4	677.7	676.5	673.8	669.7	668.4	667.0	665.8	665.8
30°	649.8	641.8	639.1	637.8	636.4	633.8	632.5	629.8	631.1	632.5	631.1
32.5°	604.6	601.9	596.5	593.8	595.1	593.8	591.2	593.8	592.6	595.1	596.5
35°	560.6	557.9	555.2	555.2	552.5	552.5	552.5	553.9	556.6	557.9	560.6
37.5°	518.0	513.9	512.6	511.2	512.6	512.6	512.6	515.3	518.0	520.7	524.6
40°	472.7	470.1	470.1	470.1	470.1	474.0	472.7	475.4	478.0	482.0	486.0
42.5°	430.0	430.0	431.4	431.4	431.4	431.4	434.1	438.1	442.0	446.1	450.0
45°	390.1	390.1	390.1	392.8	392.8	394.1	399.4	402.1	404.8	408.7	412.8
47.5°	352.9	352.9	354.2	355.6	356.8	359.5	362.2	366.2	370.1	372.8	376.9
50°	318.2	319.6	322.2	324.9	324.9	326.2	330.2	332.9	335.6	339.5	340.9
52.5°	284.9	287.6	290.3	291.6	293.0	295.6	296.9	300.9	302.3	306.2	307.6
55°	254.3	255.6	259.7	261.0	261.0	263.6	266.3	269.0	273.0	273.0	275.6
57.5°	226.3	227.7	230.4	231.7	230.4	234.3	235.7	238.3	239.7	242.4	243.6
60°	198.4	201.1	202.3	202.3	203.7	205.0	207.7	207.7	210.4	213.0	213.0
62.5°	171.7	173.1	174.4	175.8	177.1	175.8	179.8	179.8	182.4	183.7	186.4
65°	146.5	147.8	147.8	149.2	149.2	150.4	150.4	151.8	153.1	155.8	157.1
67.5°	121.1	121.1	121.1	122.5	121.1	122.5	122.5	123.8	123.8	126.5	127.9
70°	98.5	97.2	95.9	95.9	95.9	95.9	94.6	95.9	95.9	97.2	97.2
72.5°	75.9	74.6	73.2	71.9	71.9	70.6	69.2	70.6	70.6	71.9	71.9
75°	57.2	54.6	54.6	54.6	53.3	53.3	53.3	54.6	54.6	54.6	56.0
77.5°	42.6	42.6	41.3	41.3	41.3	42.6	42.6	44.0	44.0	44.0	44.0
80°	32.0	33.3	33.3	33.3	33.3	34.7	34.7	34.7	34.7	36.0	36.0
82.5°	24.0	24.0	24.0	24.0	25.3	25.3	25.3	25.3	25.3	25.3	25.3
85°	14.7	15.9	15.9	14.7	15.9	15.9	15.9	15.9	15.9	15.9	15.9
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584183

CATALOG NUMBER: HCC8S25D010SL-HM82555927-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4
2.5°	921.4	921.4	921.4	921.4	920.1	920.1	920.1	918.7
5°	901.5	901.5	901.5	898.8	900.1	900.1	897.4	898.8
7.5°	881.5	880.1	878.8	878.8	877.5	876.1	874.8	876.1
10°	858.8	854.8	854.8	853.5	853.5	850.9	850.9	852.1
12.5°	833.5	830.9	830.9	829.6	828.2	826.9	825.5	825.5
15°	808.2	805.6	804.2	802.9	801.5	798.9	800.3	798.9
17.5°	782.9	779.0	779.0	777.6	776.3	773.6	773.6	772.3
20°	753.6	752.3	749.6	750.9	749.6	747.0	745.7	745.7
22.5°	724.4	724.4	723.0	723.0	721.7	720.3	719.0	719.0
25°	696.4	695.1	696.4	696.4	692.4	692.4	692.4	693.7
27.5°	664.5	665.8	664.5	664.5	664.5	664.5	665.8	664.5
30°	632.5	632.5	632.5	633.8	636.4	635.2	635.2	633.8
32.5°	597.8	599.2	599.2	600.5	601.9	604.6	604.6	605.8
35°	563.2	565.9	567.2	565.9	569.9	569.9	572.6	572.6
37.5°	527.3	528.6	531.3	532.6	535.2	536.6	537.9	537.9
40°	488.7	494.0	495.3	496.7	500.7	500.7	501.9	504.6
42.5°	452.7	458.1	459.4	460.7	463.4	467.4	466.0	468.7
45°	418.0	422.1	423.4	424.8	428.7	430.0	430.0	434.1
47.5°	380.8	383.5	384.8	387.4	390.1	392.8	395.5	394.1
50°	343.6	347.5	350.2	351.5	355.6	356.8	358.1	359.5
52.5°	310.2	312.9	314.3	315.5	319.6	320.9	322.2	324.9
55°	278.3	279.6	282.3	281.0	284.9	286.2	287.6	290.3
57.5°	246.3	247.7	249.0	249.0	251.7	254.3	255.6	257.0
60°	215.7	218.4	219.7	219.7	219.7	222.3	222.3	222.3
62.5°	187.8	187.8	189.1	189.1	191.7	191.7	191.7	191.7
65°	158.5	159.8	161.1	161.1	163.8	162.4	165.1	163.8
67.5°	127.9	127.9	130.5	130.5	129.1	130.5	130.5	130.5
70°	97.2	97.2	98.5	98.5	98.5	98.5	98.5	98.5
72.5°	71.9	71.9	71.9	73.2	71.9	71.9	73.2	71.9
75°	56.0	56.0	56.0	56.0	56.0	56.0	56.0	56.0
77.5°	44.0	44.0	45.3	45.3	45.3	45.3	45.3	45.3
80°	36.0	36.0	36.0	36.0	37.2	36.0	36.0	36.0
82.5°	26.6	25.3	26.6	25.3	26.6	26.6	26.6	26.6
85°	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)