

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584195

Luminaire Tested: **HCC8W25D010BZ-HM82555930-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584195  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W25D010BZ-HM82555930-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2522.5 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584195  
CATALOG NUMBER: HCC8W25D010BZ-HM82555930-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584195  
 CATALOG NUMBER: HCC8W25D010BZ-HM82555930-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |   |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 92  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  | 92  | 89  | 86  | 89  | 87  | 85  | 83  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 75  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 76  | 72  | 79  | 74  | 71  | 77  | 73  | 70  | 68  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 87  | 78  | 71  | 66  | 86  | 77  | 70  | 66  | 75  | 69  | 65  | 73  | 68  | 64  | 71  | 67  | 64  | 62  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 82  | 72  | 65  | 60  | 80  | 71  | 64  | 60  | 69  | 64  | 59  | 68  | 63  | 59  | 66  | 62  | 58  | 57  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 77  | 67  | 60  | 55  | 76  | 66  | 59  | 55  | 64  | 59  | 54  | 63  | 58  | 54  | 62  | 57  | 54  | 52  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 73  | 62  | 55  | 50  | 71  | 61  | 55  | 50  | 60  | 54  | 50  | 59  | 54  | 50  | 58  | 53  | 49  | 48  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 69  | 58  | 51  | 46  | 67  | 57  | 51  | 46  | 56  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 46  | 44  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 65  | 54  | 47  | 43  | 64  | 53  | 47  | 43  | 53  | 47  | 43  | 52  | 46  | 43  | 51  | 46  | 42  | 41  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 57750 |
| 5°  | 56448 |
| 10° | 54718 |
| 15° | 53613 |
| 20° | 53128 |
| 25° | 52336 |
| 30° | 49575 |
| 35° | 41190 |
| 40° | 24257 |
| 45° | 16044 |
| 50° | 12626 |
| 55° | 9290  |
| 60° | 6451  |
| 65° | 3933  |
| 70° | 1713  |
| 75° | 751   |
| 80° | 568   |
| 85° | 0     |



TEST NUMBER: P584195  
 CATALOG NUMBER: HCC8W25D010BZ-HM82555930-81WDH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 171.7  | 6.8       |
| 10°-20°   | 474.8  | 18.8      |
| 20°-30°   | 703.4  | 27.9      |
| 30°-40°   | 650.0  | 25.8      |
| 40°-50°   | 299.7  | 11.9      |
| 50°-60°   | 157.6  | 6.2       |
| 60°-70°   | 55.7   | 2.2       |
| 70°-80°   | 8.7    | 0.3       |
| 80°-90°   | 0.9    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1349.9 | 53.5      |
| 0°-40°    | 1999.9 | 79.3      |
| 0°-60°    | 2457.2 | 97.4      |
| 0°-90°    | 2522.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2522.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1873 |      |
| 5°  | 1824 | 172  |
| 15° | 1679 | 475  |
| 25° | 1538 | 703  |
| 35° | 1094 | 650  |
| 45° | 368  | 300  |
| 55° | 173  | 158  |
| 65° | 54   | 56   |
| 75° | 6    | 9    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P584195  
CATALOG NUMBER: HCC8W25D010BZ-HM82555930-81WDH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1872.8 |
| 2.5°  | 1856.9 |
| 5°    | 1823.6 |
| 7.5°  | 1787.1 |
| 10°   | 1747.5 |
| 12.5° | 1709.4 |
| 15°   | 1679.4 |
| 17.5° | 1652.4 |
| 20°   | 1619.0 |
| 22.5° | 1582.6 |
| 25°   | 1538.2 |
| 27.5° | 1477.9 |
| 30°   | 1392.3 |
| 32.5° | 1270.2 |
| 35°   | 1094.2 |
| 37.5° | 840.5  |
| 40°   | 602.6  |
| 42.5° | 452.0  |
| 45°   | 367.9  |
| 47.5° | 312.4  |
| 50°   | 263.2  |
| 52.5° | 215.7  |
| 55°   | 172.8  |
| 57.5° | 136.4  |
| 60°   | 104.6  |
| 62.5° | 79.3   |
| 65°   | 53.9   |
| 67.5° | 31.7   |
| 70°   | 19.0   |
| 72.5° | 11.1   |
| 75°   | 6.3    |
| 77.5° | 4.7    |
| 80°   | 3.2    |
| 82.5° | 1.6    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)