

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584198

Luminaire Tested: **HCC8S25D010MB-HM82555930-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MB-HM82555930-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1975.5 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584198
CATALOG NUMBER: HCC8S25D010MB-HM82555930-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584198

CATALOG NUMBER: HCC8S25D010MB-HM82555930-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59				59
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53				53
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47				47
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43				43
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39				39
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35				35
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32705	32705	32705
5°	34056	32635	31261
10°	35192	32214	29734
15°	36084	31477	28189
20°	36156	30174	26790
25°	35545	28264	25402
30°	33641	26078	24216
35°	30672	23456	22737
40°	26676	20674	20992
45°	22882	17906	19219
50°	19549	15442	17261
55°	17128	13295	15005
60°	15252	11342	12612
65°	13528	9252	10062
70°	12009	6861	5725
75°	10008	3598	1692
80°	7885	1119	284
85°	5590	566	0



TEST NUMBER: P584198
 CATALOG NUMBER: HCC8S25D010MB-HM82555930-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	5.1
10°-20°	280.1	14.2
20°-30°	396.4	20.1
30°-40°	414.8	21.0
40°-50°	345.9	17.5
50°-60°	245.3	12.4
60°-70°	141.3	7.2
70°-80°	45.5	2.3
80°-90°	6.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.5	39.3
0°-40°	1191.2	60.3
0°-60°	1782.5	90.2
0°-90°	1975.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1975.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1061	1061	1061	1061	1061	
5°	1100	1086	1054	1022	1010	106
15°	1130	1084	986	908	883	318
25°	1045	967	831	764	747	477
35°	815	744	623	590	604	505
45°	525	482	411	415	441	407
55°	319	285	247	260	279	288
65°	185	155	127	127	138	185
75°	84	62	30	14	14	91
85°	16	8	2	0	0	20
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584198

CATALOG NUMBER: HCC8S25D010MB-HM82555930-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6
2.5°	1082.7	1081.1	1079.6	1081.1	1079.6	1081.1	1079.6	1079.6	1078.0	1076.4	1076.4
5°	1100.2	1098.6	1098.6	1098.6	1097.1	1095.5	1095.5	1093.9	1090.7	1089.0	1085.9
7.5°	1111.3	1112.9	1112.9	1112.9	1109.7	1109.7	1106.5	1103.4	1100.2	1097.1	1092.3
10°	1123.9	1123.9	1122.4	1120.8	1117.6	1116.0	1114.5	1111.3	1106.5	1100.2	1095.5
12.5°	1128.7	1128.7	1127.1	1123.9	1122.4	1120.8	1119.2	1114.5	1108.1	1100.2	1093.9
15°	1130.3	1127.1	1125.5	1123.9	1120.8	1116.0	1116.0	1109.7	1101.8	1092.3	1084.3
17.5°	1117.6	1119.2	1116.0	1112.9	1108.1	1105.0	1100.2	1095.5	1085.9	1074.8	1066.9
20°	1101.8	1100.2	1098.6	1093.9	1087.5	1085.9	1081.1	1073.2	1065.3	1052.7	1041.5
22.5°	1076.4	1074.8	1071.7	1068.5	1062.2	1059.0	1054.3	1044.7	1033.6	1020.9	1008.3
25°	1044.7	1041.5	1036.8	1030.4	1025.7	1022.5	1016.2	1006.7	994.0	979.7	967.1
27.5°	994.0	998.7	995.5	986.0	981.3	975.0	973.4	960.6	949.6	935.3	921.1
30°	944.8	944.8	940.1	935.3	927.4	922.7	916.3	906.8	895.7	878.3	867.1
32.5°	883.0	881.5	875.0	873.5	867.1	857.6	856.1	843.4	832.2	819.6	805.3
35°	814.8	811.7	805.3	800.6	797.4	792.7	787.8	776.8	765.7	753.1	743.5
37.5°	737.1	737.1	735.6	727.6	724.5	721.3	716.6	705.5	699.1	686.4	676.9
40°	662.7	661.0	656.3	654.7	651.5	646.8	643.6	637.3	627.8	618.2	608.7
42.5°	589.7	591.3	585.0	586.6	580.3	577.1	575.4	565.9	561.2	551.7	543.8
45°	524.7	523.1	520.0	518.4	515.2	512.1	508.9	504.1	496.2	486.6	481.9
47.5°	464.5	459.8	459.8	458.2	456.6	450.3	448.7	443.8	439.1	429.6	423.3
50°	407.5	407.5	407.5	405.9	401.0	399.5	396.3	391.6	386.8	380.5	371.0
52.5°	361.4	361.4	361.4	359.8	353.5	351.9	350.3	344.0	337.7	332.9	326.6
55°	318.6	320.3	318.6	315.4	310.7	310.7	305.9	302.8	296.5	291.7	285.4
57.5°	282.2	282.2	279.1	277.5	274.2	272.6	269.5	266.3	258.4	253.7	245.7
60°	247.3	245.7	245.7	242.6	239.4	236.3	234.7	229.8	226.7	218.8	212.4
62.5°	215.6	215.6	212.4	212.4	206.1	206.1	204.5	199.8	195.0	187.0	183.9
65°	185.4	185.4	183.9	182.3	177.5	176.0	174.4	169.6	164.9	160.1	155.4
67.5°	158.6	158.6	155.4	153.8	150.7	149.1	145.8	142.6	137.9	133.2	128.4
70°	133.2	131.6	130.0	128.4	125.2	123.7	120.5	117.3	112.6	109.4	104.6
72.5°	107.7	107.7	106.3	103.0	101.4	99.8	98.3	95.1	90.4	85.6	82.4
75°	84.0	84.0	84.0	80.9	77.7	76.1	76.1	73.0	69.8	64.9	61.8
77.5°	64.9	63.5	61.8	61.8	58.6	57.0	55.5	53.9	49.1	47.5	44.4
80°	44.4	46.0	44.4	42.8	41.2	39.6	39.6	36.5	34.9	31.7	28.6
82.5°	30.2	28.6	28.6	27.0	27.0	25.4	25.4	22.1	20.7	19.0	17.4
85°	15.8	15.8	14.2	14.2	14.2	12.7	12.7	11.1	11.1	9.5	7.9
87.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584198

CATALOG NUMBER: HCC8S25D010MB-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6
2.5°	1074.8	1071.7	1070.1	1070.1	1068.5	1066.9	1065.3	1063.7	1060.6	1060.6	1057.4
5°	1082.7	1079.6	1078.0	1073.2	1070.1	1070.1	1063.7	1062.2	1057.4	1054.3	1051.1
7.5°	1089.0	1082.7	1078.0	1073.2	1070.1	1066.9	1060.6	1054.3	1047.9	1041.5	1038.3
10°	1089.0	1082.7	1074.8	1066.9	1063.7	1060.6	1052.7	1043.1	1035.2	1028.8	1020.9
12.5°	1085.9	1076.4	1066.9	1060.6	1054.3	1049.5	1039.9	1030.4	1020.9	1008.3	1001.9
15°	1076.4	1063.7	1054.3	1043.1	1038.3	1030.4	1022.5	1008.3	997.1	986.0	978.1
17.5°	1057.4	1041.5	1030.4	1019.4	1011.5	1006.7	994.0	981.3	968.6	955.9	946.4
20°	1028.8	1014.6	1001.9	987.6	981.3	975.0	959.1	946.4	933.8	919.5	909.9
22.5°	994.0	979.7	962.3	951.2	941.7	933.8	919.5	905.2	892.5	879.9	867.1
25°	951.2	936.9	921.1	903.6	897.3	889.4	873.5	859.2	845.0	830.7	819.6
27.5°	905.2	886.2	873.5	854.5	848.1	840.2	822.7	806.9	794.3	783.1	770.5
30°	849.7	835.5	818.0	800.6	794.3	786.3	772.0	757.8	745.0	732.4	719.7
32.5°	789.4	775.2	757.8	745.0	735.6	729.2	715.0	702.2	689.6	676.9	665.9
35°	726.1	710.3	697.5	684.8	676.9	669.0	654.7	643.6	634.1	623.1	611.9
37.5°	661.0	650.0	637.3	623.1	615.1	608.7	597.7	585.0	577.1	567.5	559.6
40°	597.7	585.0	573.8	561.2	554.9	550.1	539.0	529.4	521.5	513.6	508.9
42.5°	532.6	521.5	510.5	502.6	497.8	493.1	485.1	474.0	469.2	461.3	456.6
45°	472.4	462.9	455.0	443.8	440.7	437.5	428.0	420.1	415.4	410.6	407.5
47.5°	415.4	409.0	399.5	393.1	388.4	385.2	378.9	372.6	367.8	364.7	361.4
50°	366.2	358.2	351.9	345.6	342.4	337.7	331.4	328.2	325.0	321.9	321.9
52.5°	320.3	312.3	305.9	301.2	298.0	294.9	290.1	288.5	285.4	285.4	283.8
55°	277.5	272.6	266.3	260.0	258.4	256.8	253.7	250.5	248.9	247.3	248.9
57.5°	241.0	236.3	229.8	225.1	223.5	221.9	220.3	217.2	215.6	215.6	215.6
60°	207.7	202.9	198.2	193.5	193.5	190.2	188.6	187.0	185.4	183.9	183.9
62.5°	177.5	172.8	168.0	164.9	163.3	161.7	158.6	157.0	155.4	155.4	153.8
65°	150.7	144.2	142.6	137.9	136.3	134.7	133.2	130.0	128.4	126.8	125.2
67.5°	123.7	120.5	115.8	112.6	111.0	109.4	107.7	104.6	103.0	101.4	98.3
70°	99.8	96.7	93.5	90.4	88.8	87.2	84.0	80.9	79.3	76.1	71.4
72.5°	77.7	74.5	71.4	68.2	66.6	64.9	61.8	58.6	55.5	52.3	49.1
75°	58.6	55.5	50.7	47.5	46.0	46.0	41.2	38.1	34.9	30.2	27.0
77.5°	41.2	36.5	34.9	31.7	30.2	27.0	23.8	20.7	17.4	15.8	12.7
80°	27.0	23.8	20.7	19.0	17.4	15.8	14.2	11.1	7.9	6.3	4.7
82.5°	15.8	14.2	12.7	11.1	9.5	7.9	6.3	6.3	4.7	3.2	1.6
85°	7.9	6.3	4.7	4.7	3.2	3.2	3.2	1.6	1.6	1.6	1.6
87.5°	3.2	1.6	1.6	1.6	1.6	1.6	1.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584198

CATALOG NUMBER: HCC8S25D010MB-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6
2.5°	1055.8	1054.3	1052.7	1051.1	1051.1	1047.9	1047.9	1046.2	1043.1	1041.5	1041.5
5°	1046.2	1041.5	1038.3	1036.8	1035.2	1030.4	1028.8	1025.7	1022.5	1019.4	1017.8
7.5°	1032.0	1024.1	1020.9	1019.4	1014.6	1009.9	1006.7	1001.9	997.1	992.4	990.8
10°	1014.6	1006.7	998.7	995.5	990.8	987.6	981.3	975.0	970.2	965.5	960.6
12.5°	992.4	982.9	975.0	971.8	967.1	960.6	951.2	948.0	940.1	936.9	930.6
15°	967.1	955.9	948.0	943.2	938.5	929.0	922.7	916.3	908.3	905.2	898.9
17.5°	935.3	922.7	914.7	909.9	906.8	898.9	889.4	881.5	873.5	870.3	865.5
20°	897.3	889.4	878.3	873.5	870.3	860.8	851.3	848.1	841.8	835.5	830.7
22.5°	854.5	846.6	835.5	830.7	829.1	821.2	813.3	808.5	803.8	799.0	794.3
25°	810.1	800.6	791.1	787.8	784.7	778.4	772.0	768.9	764.1	761.0	757.8
27.5°	762.5	753.1	745.0	740.3	737.1	732.4	729.2	726.1	722.9	719.7	718.2
30°	711.8	702.2	695.9	692.8	689.6	688.0	683.3	681.7	680.1	676.9	678.5
32.5°	661.0	653.1	646.8	642.0	642.0	638.9	637.3	637.3	635.7	635.7	635.7
35°	605.6	600.8	596.1	594.5	592.9	591.3	589.7	591.3	589.7	591.3	592.9
37.5°	554.9	550.1	546.9	545.4	543.8	545.4	543.8	543.8	545.4	548.5	550.1
40°	502.6	499.4	496.2	497.8	496.2	496.2	496.2	501.0	502.6	504.1	505.7
42.5°	453.4	450.3	448.7	448.7	450.3	448.7	451.9	453.4	456.6	461.3	464.5
45°	405.9	404.2	404.2	405.9	404.2	407.5	407.5	410.6	415.4	418.5	421.7
47.5°	361.4	361.4	361.4	363.1	363.1	364.7	367.8	369.4	372.6	375.7	378.9
50°	320.3	321.9	323.4	323.4	323.4	326.6	329.8	331.4	332.9	334.5	339.3
52.5°	283.8	285.4	285.4	287.0	288.5	290.1	291.7	294.9	296.5	299.6	301.2
55°	248.9	248.9	252.1	253.7	253.7	253.7	256.8	256.8	260.0	261.6	264.7
57.5°	215.6	217.2	217.2	218.8	218.8	220.3	221.9	223.5	225.1	226.7	228.2
60°	183.9	183.9	183.9	185.4	187.0	188.6	187.0	190.2	190.2	193.5	195.0
62.5°	153.8	155.4	155.4	155.4	155.4	155.4	155.4	157.0	158.6	160.1	161.7
65°	125.2	125.2	125.2	123.7	125.2	123.7	125.2	126.8	126.8	128.4	130.0
67.5°	96.7	96.7	93.5	93.5	95.1	95.1	95.1	95.1	93.5	96.7	96.7
70°	69.8	68.2	66.6	64.9	64.9	63.5	63.5	61.8	61.8	61.8	61.8
72.5°	46.0	42.8	39.6	38.1	36.5	36.5	33.3	31.7	33.3	33.3	33.3
75°	23.8	20.7	19.0	17.4	15.8	15.8	14.2	14.2	14.2	14.2	14.2
77.5°	9.5	7.9	6.3	6.3	4.7	4.7	4.7	4.7	4.7	4.7	4.7
80°	3.2	3.2	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	1.6	0.0	0.0	1.6	0.0	1.6	1.6	1.6	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584198

CATALOG NUMBER: HCC8S25D010MB-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6	1060.6
2.5°	1039.9	1039.9	1038.3	1039.9	1036.8	1038.3	1036.8	1036.8
5°	1016.2	1013.0	1013.0	1013.0	1011.5	1011.5	1009.9	1009.9
7.5°	987.6	986.0	984.5	982.9	981.3	979.7	979.7	979.7
10°	959.1	955.9	955.9	954.3	951.2	949.6	949.6	949.6
12.5°	925.8	924.3	922.7	922.7	916.3	917.8	916.3	916.3
15°	894.1	892.5	892.5	887.8	884.6	884.6	884.6	883.0
17.5°	860.8	859.2	857.6	854.5	851.3	851.3	849.7	851.3
20°	825.9	824.3	821.2	821.2	819.6	818.0	814.8	816.4
22.5°	791.1	787.8	786.3	786.3	784.7	784.7	781.5	781.5
25°	754.6	753.1	751.5	753.1	749.9	749.9	746.6	746.6
27.5°	716.6	715.0	715.0	715.0	713.4	715.0	713.4	713.4
30°	678.5	678.5	676.9	676.9	678.5	676.9	678.5	680.1
32.5°	637.3	637.3	638.9	638.9	640.5	640.5	640.5	640.5
35°	594.5	597.7	597.7	599.2	600.8	602.4	602.4	604.0
37.5°	554.9	556.4	558.0	559.6	562.8	562.8	562.8	562.8
40°	512.1	513.6	516.8	515.2	521.5	523.1	521.5	521.5
42.5°	467.7	470.8	472.4	475.6	477.2	480.3	481.9	481.9
45°	426.4	428.0	431.2	434.4	435.9	440.7	440.7	440.7
47.5°	383.6	386.8	388.4	391.6	393.1	397.9	399.5	397.9
50°	342.4	345.6	348.7	348.7	353.5	355.1	358.2	359.8
52.5°	302.8	304.4	307.5	309.1	312.3	315.4	317.0	318.6
55°	264.7	266.3	269.5	269.5	274.2	275.8	279.1	279.1
57.5°	229.8	231.4	234.7	233.0	236.3	239.4	239.4	237.8
60°	196.6	196.6	196.6	199.8	201.4	202.9	204.5	204.5
62.5°	161.7	164.9	166.5	166.5	168.0	169.6	169.6	168.0
65°	130.0	133.2	134.7	134.7	136.3	136.3	136.3	137.9
67.5°	98.3	98.3	98.3	99.8	98.3	98.3	98.3	98.3
70°	61.8	61.8	61.8	61.8	60.2	61.8	61.8	63.5
72.5°	33.3	33.3	33.3	33.3	33.3	33.3	33.3	33.3
75°	14.2	14.2	14.2	15.8	14.2	14.2	14.2	14.2
77.5°	6.3	4.7	6.3	6.3	4.7	4.7	4.7	4.7
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	0.0	1.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)