

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584200

Luminaire Tested: **HCC8S25D010SL-HM82555930-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584200  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S25D010SL-HM82555930-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2245.0 lumens  
Efficiency: N/A  
Efficacy: 83.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584200  
CATALOG NUMBER: HCC8S25D010SL-HM82555930-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584200

CATALOG NUMBER: HCC8S25D010SL-HM82555930-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	34419	34419	34419
5°	35681	34306	33127
10°	36691	34011	31775
15°	37508	33409	30369
20°	37567	32103	29137
25°	36845	30319	28104
30°	34948	28119	26876
35°	31753	25606	25666
40°	27763	22977	24189
45°	24064	20466	22542
50°	21070	18182	20537
55°	18752	16112	18580
60°	16917	14475	16331
65°	15272	12725	14235
70°	13731	10720	10585
75°	12081	8507	7935
80°	10122	7032	7600
85°	7819	6156	6722

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584200

CATALOG NUMBER: HCC8S25D010SL-HM82555930-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.3	4.7
10°-20°	296.6	13.2
20°-30°	423.9	18.9
30°-40°	450.4	20.1
40°-50°	387.8	17.3
50°-60°	289.9	12.9
60°-70°	184.9	8.2
70°-80°	84.2	3.7
80°-90°	22.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	825.8	36.8
0°-40°	1276.2	56.8
0°-60°	1953.9	87.0
0°-90°	2245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2245.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1116	1116	1116	1116	1116	
5°	1153	1137	1108	1080	1070	110
15°	1175	1135	1046	975	951	331
25°	1083	1015	891	837	826	496
35°	844	785	680	663	682	525
45°	552	522	469	482	517	429
55°	349	320	300	325	346	314
65°	209	186	174	182	195	209
75°	101	87	71	65	67	108
85°	22	19	17	19	19	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584200

CATALOG NUMBER: HCC8S25D010SL-HM82555930-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2
2.5°	1136.9	1133.7	1135.3	1133.7	1135.3	1135.3	1132.1	1132.1	1132.1	1132.1	1127.4
5°	1152.7	1151.1	1151.1	1149.5	1148.0	1149.5	1148.0	1146.4	1143.2	1141.6	1136.9
7.5°	1162.2	1162.2	1162.2	1162.2	1160.6	1159.0	1157.4	1154.3	1151.1	1148.0	1144.8
10°	1171.8	1173.4	1171.8	1170.2	1168.5	1165.4	1163.8	1160.6	1155.9	1151.1	1148.0
12.5°	1176.5	1176.5	1174.9	1174.9	1171.8	1170.2	1165.4	1160.6	1155.9	1151.1	1143.2
15°	1174.9	1174.9	1173.4	1171.8	1166.9	1165.4	1162.2	1157.4	1149.5	1143.2	1135.3
17.5°	1165.4	1163.8	1160.6	1160.6	1154.3	1152.7	1149.5	1143.2	1135.3	1125.7	1116.2
20°	1144.8	1144.8	1143.2	1141.6	1135.3	1130.6	1127.4	1119.4	1113.1	1102.0	1092.5
22.5°	1116.2	1119.4	1116.2	1113.1	1105.1	1103.6	1098.8	1089.3	1079.7	1067.1	1056.0
25°	1082.9	1081.3	1079.7	1076.6	1070.2	1067.1	1060.7	1051.3	1041.8	1027.4	1014.8
27.5°	1040.1	1033.8	1033.8	1027.4	1022.7	1017.9	1014.8	1005.3	992.5	981.5	965.6
30°	981.5	983.0	975.1	973.5	965.6	962.5	956.0	946.6	935.5	922.8	910.1
32.5°	918.1	913.2	913.2	906.9	900.6	895.8	894.3	883.2	873.7	860.9	848.3
35°	843.5	843.5	838.8	837.2	830.9	827.6	822.9	816.5	805.5	794.4	784.8
37.5°	770.6	767.4	765.8	762.7	757.9	753.2	753.2	742.0	740.4	727.8	715.1
40°	689.7	692.9	689.7	685.0	683.4	680.2	678.6	672.3	667.6	656.4	648.5
42.5°	621.6	618.4	618.4	616.7	610.4	610.4	607.2	604.1	596.2	593.0	583.5
45°	551.8	554.9	550.2	551.8	545.5	545.5	545.5	539.1	532.8	528.0	521.6
47.5°	491.6	493.2	493.2	488.3	486.7	486.7	483.6	480.4	475.7	469.3	464.6
50°	439.2	440.8	437.6	436.0	432.8	431.3	431.3	424.9	421.8	415.4	412.3
52.5°	391.6	391.6	390.0	390.0	385.3	385.3	382.1	377.4	374.2	371.1	363.1
55°	348.8	348.8	347.2	345.6	345.6	340.9	339.3	334.6	331.4	325.1	320.3
57.5°	307.6	309.2	307.6	306.0	304.4	302.8	299.7	294.9	291.8	287.0	283.8
60°	274.3	274.3	272.7	271.1	267.9	266.3	264.8	261.6	256.9	253.7	248.9
62.5°	242.6	241.0	239.5	237.9	234.7	234.7	231.4	228.3	223.5	220.4	217.2
65°	209.3	209.3	207.7	207.7	206.1	203.0	201.4	199.8	193.5	191.9	185.5
67.5°	179.1	180.7	177.6	177.6	174.4	174.4	172.8	168.1	166.5	163.3	160.2
70°	152.3	152.3	152.3	150.7	147.4	145.8	144.2	141.1	139.5	136.3	133.2
72.5°	125.3	125.3	123.7	123.7	122.1	120.5	118.9	115.8	115.8	112.6	109.4
75°	101.4	101.4	99.9	98.3	96.7	96.7	95.1	93.5	90.4	88.8	87.2
77.5°	77.7	77.7	77.7	76.1	74.5	74.5	74.5	71.4	68.2	68.2	66.6
80°	57.0	57.0	55.5	55.5	53.9	53.9	53.9	52.3	50.7	49.1	47.6
82.5°	38.1	38.1	38.1	38.1	36.5	36.5	36.5	34.9	33.3	33.3	33.3
85°	22.1	22.1	22.1	22.1	20.7	20.7	20.7	20.7	20.7	19.0	19.0
87.5°	9.5	7.9	9.5	7.9	9.5	7.9	9.5	7.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584200

CATALOG NUMBER: HCC8S25D010SL-HM82555930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2
2.5°	1129.0	1127.4	1125.7	1124.1	1124.1	1122.5	1119.4	1117.8	1116.2	1114.6	1114.6
5°	1135.3	1133.7	1130.6	1127.4	1125.7	1122.5	1119.4	1116.2	1113.1	1108.3	1106.7
7.5°	1140.0	1135.3	1132.1	1125.7	1124.1	1121.0	1116.2	1111.5	1105.1	1098.8	1094.1
10°	1140.0	1133.7	1129.0	1121.0	1117.8	1114.6	1108.3	1100.4	1092.5	1086.2	1078.1
12.5°	1136.9	1129.0	1121.0	1113.1	1108.3	1103.6	1094.1	1086.2	1076.6	1067.1	1060.7
15°	1125.7	1116.2	1106.7	1097.2	1092.5	1086.2	1076.6	1065.5	1056.0	1046.5	1035.3
17.5°	1105.1	1095.6	1084.6	1073.4	1067.1	1062.3	1048.1	1040.1	1025.8	1016.4	1006.9
20°	1078.1	1067.1	1052.8	1041.8	1033.8	1029.0	1017.9	1003.7	992.5	978.3	968.8
22.5°	1043.2	1029.0	1014.8	1003.7	995.7	989.4	975.1	960.9	951.3	938.6	927.6
25°	1002.1	987.8	973.5	957.6	949.7	943.4	930.7	918.1	905.3	891.1	881.6
27.5°	952.9	937.1	924.4	910.1	902.2	892.7	878.4	865.7	853.0	843.5	830.9
30°	899.0	881.6	868.8	854.6	846.7	838.8	824.5	811.8	800.7	789.7	783.2
32.5°	834.0	821.3	808.6	794.4	788.1	783.2	769.0	756.3	743.7	734.1	729.3
35°	772.2	757.9	746.8	734.1	726.2	721.4	708.8	697.6	691.3	680.2	673.9
37.5°	707.2	696.0	683.4	670.7	666.0	661.2	651.6	640.6	631.1	623.2	620.0
40°	639.0	629.5	618.4	610.4	605.7	600.9	593.0	585.1	578.8	570.8	567.6
42.5°	573.9	567.6	558.1	548.6	543.9	542.3	532.8	526.4	523.2	520.0	516.9
45°	515.3	505.8	499.5	493.2	488.3	485.1	480.4	475.7	472.5	469.3	466.2
47.5°	458.3	450.3	443.9	439.2	434.4	432.8	429.7	424.9	421.8	421.8	421.8
50°	406.0	399.5	393.2	390.0	388.5	385.3	382.1	380.5	379.0	379.0	379.0
52.5°	359.9	353.5	348.8	345.6	345.6	342.5	339.3	337.7	337.7	337.7	337.7
55°	317.1	312.3	309.2	306.0	302.8	301.2	301.2	301.2	299.7	299.7	301.2
57.5°	279.1	275.8	271.1	267.9	266.3	266.3	264.8	263.2	264.8	266.3	267.9
60°	244.2	241.0	239.5	234.7	234.7	234.7	233.0	233.0	233.0	234.7	236.3
62.5°	212.5	210.9	207.7	206.1	204.6	204.6	203.0	203.0	203.0	203.0	204.6
65°	183.9	180.7	177.6	177.6	177.6	176.0	176.0	172.8	174.4	174.4	172.8
67.5°	157.0	153.8	152.3	150.7	149.1	149.1	147.4	145.8	144.2	144.2	144.2
70°	131.6	128.4	128.4	125.3	125.3	123.7	122.1	122.1	120.5	118.9	117.4
72.5°	106.3	104.6	103.0	101.4	101.4	101.4	99.9	98.3	96.7	95.1	91.9
75°	84.0	84.0	80.9	79.3	79.3	77.7	76.1	74.5	73.0	71.4	69.8
77.5°	65.1	63.5	60.2	58.6	58.6	58.6	57.0	55.5	53.9	52.3	50.7
80°	47.6	46.0	44.4	42.8	42.8	42.8	41.2	41.2	39.6	39.6	39.6
82.5°	31.7	31.7	30.2	30.2	30.2	30.2	28.6	28.6	28.6	28.6	28.6
85°	19.0	19.0	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
87.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584200

CATALOG NUMBER: HCC8S25D010SL-HM82555930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2
2.5°	1111.5	1111.5	1108.3	1106.7	1105.1	1106.7	1103.6	1102.0	1100.4	1100.4	1098.8
5°	1102.0	1100.4	1094.1	1092.5	1090.9	1089.3	1086.2	1082.9	1079.7	1078.1	1076.6
7.5°	1089.3	1084.6	1078.1	1076.6	1075.0	1070.2	1065.5	1062.3	1057.6	1056.0	1052.8
10°	1071.8	1065.5	1060.7	1056.0	1052.8	1048.1	1043.2	1038.5	1032.2	1030.6	1025.8
12.5°	1051.3	1043.2	1033.8	1032.2	1027.4	1021.1	1014.8	1010.0	1005.3	1002.1	997.3
15°	1025.8	1017.9	1008.4	1003.7	999.0	994.1	986.2	979.9	975.1	970.4	965.6
17.5°	995.7	986.2	978.3	973.5	970.4	962.5	956.0	948.1	943.4	938.6	933.9
20°	959.3	951.3	940.2	935.5	933.9	927.6	919.7	916.5	910.1	905.3	902.2
22.5°	918.1	910.1	900.6	897.4	891.1	887.9	880.0	876.9	873.7	868.8	867.3
25°	872.0	864.1	856.2	854.6	849.9	846.7	842.0	837.2	837.2	832.5	832.5
27.5°	824.5	816.5	810.2	807.1	805.5	802.3	797.6	796.0	794.4	792.8	792.8
30°	773.7	764.2	761.1	759.5	757.9	754.8	753.2	750.0	751.6	753.2	751.6
32.5°	719.9	716.7	710.4	707.2	708.8	707.2	704.0	707.2	705.6	708.8	710.4
35°	667.6	664.4	661.2	661.2	658.1	658.1	658.1	659.5	662.8	664.4	667.6
37.5°	616.7	612.0	610.4	608.8	610.4	610.4	610.4	613.6	616.7	620.0	624.7
40°	562.9	559.7	559.7	559.7	559.7	564.4	562.9	566.0	569.2	573.9	578.8
42.5°	512.1	512.1	513.7	513.7	513.7	513.7	516.9	521.6	526.4	531.1	536.0
45°	464.6	464.6	464.6	467.7	467.7	469.3	475.7	478.8	482.0	486.7	491.6
47.5°	420.2	420.2	421.8	423.4	424.9	428.1	431.3	436.0	440.8	443.9	448.8
50°	379.0	380.5	383.7	386.9	386.9	388.5	393.2	396.4	399.5	404.4	406.0
52.5°	339.3	342.5	345.6	347.2	348.8	352.0	353.5	358.3	359.9	364.7	366.3
55°	302.8	304.4	309.2	310.7	310.7	313.9	317.1	320.3	325.1	325.1	328.2
57.5°	269.5	271.1	274.3	275.8	274.3	279.1	280.7	283.8	285.4	288.6	290.2
60°	236.3	239.5	241.0	241.0	242.6	244.2	247.4	247.4	250.5	253.7	253.7
62.5°	204.6	206.1	207.7	209.3	210.9	209.3	214.0	214.0	217.2	218.8	222.0
65°	174.4	176.0	176.0	177.6	177.6	179.1	179.1	180.7	182.3	185.5	187.1
67.5°	144.2	144.2	144.2	145.8	144.2	145.8	145.8	147.4	147.4	150.7	152.3
70°	117.4	115.8	114.2	114.2	114.2	114.2	112.6	114.2	114.2	115.8	115.8
72.5°	90.4	88.8	87.2	85.6	85.6	84.0	82.5	84.0	84.0	85.6	85.6
75°	68.2	65.1	65.1	65.1	63.5	63.5	63.5	65.1	65.1	65.1	66.6
77.5°	50.7	50.7	49.1	49.1	49.1	50.7	50.7	52.3	52.3	52.3	52.3
80°	38.1	39.6	39.6	39.6	39.6	41.2	41.2	41.2	41.2	42.8	42.8
82.5°	28.6	28.6	28.6	28.6	30.2	30.2	30.2	30.2	30.2	30.2	30.2
85°	17.4	19.0	19.0	17.4	19.0	19.0	19.0	19.0	19.0	19.0	19.0
87.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584200

CATALOG NUMBER: HCC8S25D010SL-HM82555930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2	1116.2
2.5°	1097.2	1097.2	1097.2	1097.2	1095.6	1095.6	1095.6	1094.1
5°	1073.4	1073.4	1073.4	1070.2	1071.8	1071.8	1068.7	1070.2
7.5°	1049.7	1048.1	1046.5	1046.5	1044.9	1043.2	1041.8	1043.2
10°	1022.7	1017.9	1017.9	1016.4	1016.4	1013.2	1013.2	1014.8
12.5°	992.5	989.4	989.4	987.8	986.2	984.6	983.0	983.0
15°	962.5	959.3	957.6	956.0	954.5	951.3	952.9	951.3
17.5°	932.3	927.6	927.6	926.0	924.4	921.2	921.2	919.7
20°	897.4	895.8	892.7	894.3	892.7	889.5	887.9	887.9
22.5°	862.5	862.5	860.9	860.9	859.4	857.8	856.2	856.2
25°	829.2	827.6	829.2	829.2	824.5	824.5	824.5	826.0
27.5°	791.2	792.8	791.2	791.2	791.2	791.2	792.8	791.2
30°	753.2	753.2	753.2	754.8	757.9	756.3	756.3	754.8
32.5°	711.9	713.5	713.5	715.1	716.7	719.9	719.9	721.4
35°	670.7	673.9	675.5	673.9	678.6	678.6	681.8	681.8
37.5°	627.9	629.5	632.7	634.2	637.4	639.0	640.6	640.6
40°	581.9	588.3	589.8	591.4	596.2	596.2	597.8	600.9
42.5°	539.1	545.5	547.0	548.6	551.8	556.5	554.9	558.1
45°	497.9	502.6	504.2	505.8	510.6	512.1	512.1	516.9
47.5°	453.5	456.7	458.3	461.4	464.6	467.7	470.9	469.3
50°	409.1	413.9	417.0	418.6	423.4	424.9	426.5	428.1
52.5°	369.5	372.6	374.2	375.8	380.5	382.1	383.7	386.9
55°	331.4	333.0	336.1	334.6	339.3	340.9	342.5	345.6
57.5°	293.3	294.9	296.5	296.5	299.7	302.8	304.4	306.0
60°	256.9	260.0	261.6	261.6	261.6	264.8	264.8	264.8
62.5°	223.5	223.5	225.1	225.1	228.3	228.3	228.3	228.3
65°	188.6	190.2	191.9	191.9	195.1	193.5	196.6	195.1
67.5°	152.3	152.3	155.4	155.4	153.8	155.4	155.4	155.4
70°	115.8	115.8	117.4	117.4	117.4	117.4	117.4	117.4
72.5°	85.6	85.6	85.6	87.2	85.6	85.6	87.2	85.6
75°	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6
77.5°	52.3	52.3	53.9	53.9	53.9	53.9	53.9	53.9
80°	42.8	42.8	42.8	42.8	44.4	42.8	42.8	42.8
82.5°	31.7	30.2	31.7	30.2	31.7	31.7	31.7	31.7
85°	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0
87.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)