

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584191

Luminaire Tested: **HCC8W25D010SL-HM82555930-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584191  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W25D010SL-HM82555930-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2257.7 lumens  
Efficiency: N/A  
Efficacy: 84.2 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584191  
CATALOG NUMBER: HCC8W25D010SL-HM82555930-81RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P584191

CATALOG NUMBER: HCC8W25D010SL-HM82555930-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	36630	36630	36630
5°	37114	36476	36133
10°	37493	36103	35558
15°	37872	35340	34634
20°	37679	34039	33258
25°	36804	32000	31568
30°	34955	29707	29593
35°	31821	27104	27345
40°	27896	24261	25155
45°	24068	21582	23104
50°	21074	18944	20921
55°	18671	16284	18419
60°	16818	13691	15258
65°	15162	10996	11689
70°	13289	8006	6437
75°	11330	4158	1692
80°	8719	1119	284
85°	5590	0	0



TEST NUMBER: P584191  
 CATALOG NUMBER: HCC8W25D010SL-HM82555930-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.1	5.0
10°-20°	315.1	14.0
20°-30°	447.2	19.8
30°-40°	470.7	20.9
40°-50°	400.5	17.7
50°-60°	289.4	12.8
60°-70°	164.6	7.3
70°-80°	51.9	2.3
80°-90°	6.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	874.4	38.7
0°-40°	1345.1	59.6
0°-60°	2034.9	90.1
0°-90°	2257.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2257.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1188	1188	1188	1188	1188	
5°	1199	1193	1178	1170	1167	114
15°	1186	1156	1107	1086	1085	334
25°	1082	1028	940	925	928	495
35°	845	796	720	715	726	526
45°	552	531	495	508	530	429
55°	347	322	303	320	343	313
65°	208	179	151	149	160	206
75°	95	73	35	16	14	102
85°	16	10	0	0	0	20
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584191

CATALOG NUMBER: HCC8W25D010SL-HM82555930-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9
2.5°	1194.2	1195.8	1192.7	1192.7	1195.8	1192.7	1194.2	1194.2	1192.7	1192.7	1191.1
5°	1199.0	1197.4	1197.4	1197.4	1199.0	1195.8	1194.2	1195.8	1192.7	1192.7	1192.7
7.5°	1200.6	1200.6	1199.0	1197.4	1197.4	1197.4	1195.8	1194.2	1192.7	1189.5	1187.9
10°	1197.4	1197.4	1199.0	1195.8	1195.8	1192.7	1192.7	1189.5	1189.5	1186.3	1181.6
12.5°	1194.2	1192.7	1192.7	1189.5	1189.5	1186.3	1186.3	1181.6	1180.0	1175.2	1170.5
15°	1186.3	1184.7	1181.6	1180.0	1178.4	1176.8	1173.7	1172.1	1167.3	1161.0	1156.2
17.5°	1170.5	1168.9	1167.3	1164.2	1161.0	1159.3	1157.7	1153.0	1146.7	1141.9	1134.0
20°	1148.2	1146.7	1146.7	1141.9	1140.3	1135.6	1134.0	1127.7	1122.9	1113.3	1107.0
22.5°	1118.2	1119.8	1116.5	1113.3	1110.2	1105.4	1102.3	1095.9	1088.0	1078.5	1070.5
25°	1081.7	1083.3	1080.1	1076.8	1072.1	1068.9	1065.8	1056.3	1048.4	1037.3	1027.7
27.5°	1035.7	1035.7	1035.7	1032.4	1024.5	1023.0	1019.8	1010.3	999.2	989.6	980.1
30°	981.7	980.1	980.1	975.4	972.2	965.9	961.1	953.2	945.2	934.1	923.1
32.5°	916.7	918.3	913.6	910.4	905.6	905.6	899.2	892.9	883.4	872.3	861.2
35°	845.3	846.9	843.8	842.2	834.3	832.7	831.1	823.2	816.8	808.8	796.2
37.5°	772.4	770.8	769.2	769.2	764.4	761.3	758.1	753.4	743.9	737.4	731.1
40°	693.0	693.0	693.0	691.5	689.9	686.7	685.1	682.0	675.6	669.3	664.6
42.5°	621.7	621.7	620.2	618.6	615.4	617.0	613.8	610.6	604.2	599.5	596.3
45°	551.9	551.9	551.9	553.5	550.3	545.6	545.6	542.4	539.3	536.1	531.4
47.5°	490.1	494.9	491.7	490.1	491.7	485.4	485.4	482.1	478.9	475.8	469.4
50°	439.3	439.3	439.3	436.1	434.5	434.5	429.8	426.6	425.0	421.9	415.5
52.5°	393.3	390.1	390.1	388.6	387.0	383.8	383.8	380.6	374.3	371.1	366.4
55°	347.3	347.3	345.7	344.1	342.6	341.0	339.4	334.7	331.5	326.7	322.0
57.5°	306.1	309.2	307.7	304.5	301.3	301.3	298.2	295.0	290.3	285.5	280.8
60°	272.7	271.2	271.2	269.6	266.4	264.8	263.3	258.5	253.8	249.0	244.3
62.5°	237.9	237.9	237.9	234.8	231.5	229.9	228.3	225.2	218.9	214.1	210.9
65°	207.8	206.2	204.6	203.0	201.4	198.3	196.7	193.5	188.7	183.9	179.2
67.5°	177.6	176.0	176.0	174.4	169.7	168.1	168.1	163.4	158.6	153.9	149.1
70°	147.4	147.4	147.4	144.3	142.7	141.1	139.5	136.4	131.6	126.9	122.1
72.5°	122.1	120.6	120.6	119.0	114.2	112.6	111.1	107.9	103.0	99.9	96.7
75°	95.1	95.1	93.6	92.0	90.4	88.8	87.2	84.1	79.3	74.6	73.0
77.5°	73.0	71.4	71.4	69.8	66.7	65.1	65.1	61.8	57.1	53.9	50.7
80°	49.1	50.7	49.1	47.6	46.0	44.4	42.8	41.2	38.1	34.9	31.7
82.5°	30.2	31.7	30.2	30.2	28.6	27.0	27.0	23.8	22.3	20.7	19.0
85°	15.8	15.8	15.8	15.8	14.2	14.2	14.2	12.7	11.1	9.5	9.5
87.5°	4.7	6.3	4.7	4.7	4.7	4.7	4.7	4.7	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584191

CATALOG NUMBER: HCC8W25D010SL-HM82555930-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9
2.5°	1192.7	1191.1	1189.5	1189.5	1189.5	1189.5	1189.5	1187.9	1186.3	1186.3	1186.3
5°	1189.5	1189.5	1189.5	1187.9	1186.3	1186.3	1183.2	1181.6	1180.0	1178.4	1176.8
7.5°	1186.3	1183.2	1181.6	1180.0	1178.4	1178.4	1175.2	1172.1	1172.1	1168.9	1165.8
10°	1176.8	1175.2	1172.1	1168.9	1167.3	1165.8	1162.6	1157.7	1156.2	1153.0	1149.8
12.5°	1165.8	1162.6	1159.3	1153.0	1151.4	1149.8	1143.5	1138.8	1135.6	1134.0	1126.1
15°	1151.4	1145.1	1140.3	1132.4	1130.8	1127.7	1122.9	1118.2	1111.8	1107.0	1103.8
17.5°	1126.1	1119.8	1111.8	1103.8	1100.7	1100.7	1092.8	1086.4	1078.5	1075.4	1068.9
20°	1095.9	1088.0	1081.7	1072.1	1067.4	1062.6	1057.9	1048.4	1042.0	1037.3	1029.3
22.5°	1061.0	1049.9	1042.0	1032.4	1024.5	1019.8	1011.9	1004.0	996.1	991.2	984.9
25°	1016.6	1007.1	994.5	984.9	980.1	973.8	964.3	956.4	948.4	940.5	937.3
27.5°	967.5	954.8	943.6	932.6	927.8	923.1	912.0	902.4	896.1	888.2	885.0
30°	913.6	900.8	888.2	878.7	873.9	866.0	859.6	848.5	840.6	834.3	826.4
32.5°	851.7	842.2	831.1	816.8	813.6	807.3	797.8	793.0	783.5	778.7	772.4
35°	785.1	778.7	767.6	756.5	751.8	748.6	740.7	731.1	724.8	720.0	716.9
37.5°	721.6	713.7	702.6	694.6	691.5	686.7	677.2	672.5	666.1	663.0	656.7
40°	653.4	645.5	637.6	632.8	628.1	624.9	618.6	613.8	607.4	602.7	601.1
42.5°	586.8	582.1	575.8	569.3	567.7	563.0	559.8	555.1	550.3	548.8	544.0
45°	526.5	521.8	515.4	509.1	507.5	504.4	502.8	498.0	494.9	494.9	494.9
47.5°	466.3	461.5	455.2	452.0	453.6	447.3	447.3	445.7	442.4	442.4	444.0
50°	412.4	406.1	404.5	401.2	398.0	394.9	396.5	391.7	391.7	394.9	393.3
52.5°	361.7	355.2	353.6	350.5	348.9	348.9	347.3	347.3	345.7	347.3	347.3
55°	315.7	310.8	307.7	304.5	302.9	302.9	302.9	301.3	299.7	302.9	304.5
57.5°	274.3	272.7	269.6	264.8	263.3	261.7	260.1	260.1	260.1	260.1	261.7
60°	237.9	234.8	231.5	226.8	226.8	225.2	223.6	222.0	222.0	222.0	222.0
62.5°	206.2	201.4	196.7	193.5	192.0	190.4	188.7	185.5	185.5	185.5	185.5
65°	174.4	169.7	166.5	163.4	160.2	160.2	157.0	155.5	152.3	150.7	147.4
67.5°	144.3	141.1	138.0	133.2	131.6	130.0	126.9	125.3	120.6	119.0	117.4
70°	117.4	112.6	109.5	106.3	104.6	101.5	98.3	95.1	92.0	88.8	85.6
72.5°	92.0	87.2	84.1	80.9	77.7	77.7	73.0	69.8	65.1	61.8	57.1
75°	68.2	63.5	60.2	55.5	53.9	52.3	47.6	44.4	39.7	34.9	31.7
77.5°	46.0	42.8	39.7	34.9	31.7	31.7	27.0	23.8	20.7	15.8	14.2
80°	28.6	25.4	22.3	19.0	19.0	15.8	14.2	11.1	7.9	6.3	4.7
82.5°	15.8	14.2	12.7	9.5	9.5	7.9	6.3	4.7	3.2	1.6	1.6
85°	7.9	6.3	4.7	4.7	3.2	3.2	3.2	1.6	1.6	0.0	0.0
87.5°	3.2	1.6	1.6	1.6	1.6	1.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584191

CATALOG NUMBER: HCC8W25D010SL-HM82555930-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9
2.5°	1184.7	1184.7	1183.2	1183.2	1183.2	1181.6	1183.2	1181.6	1181.6	1181.6	1183.2
5°	1178.4	1175.2	1175.2	1173.7	1173.7	1172.1	1173.7	1172.1	1170.5	1168.9	1170.5
7.5°	1165.8	1162.6	1161.0	1159.3	1159.3	1159.3	1157.7	1156.2	1157.7	1153.0	1156.2
10°	1148.2	1146.7	1143.5	1141.9	1140.3	1141.9	1140.3	1137.2	1137.2	1137.2	1135.6
12.5°	1126.1	1122.9	1121.3	1119.8	1116.5	1116.5	1118.2	1114.9	1114.9	1111.8	1111.8
15°	1099.1	1095.9	1092.8	1092.8	1089.6	1089.6	1088.0	1088.0	1086.4	1084.9	1084.9
17.5°	1065.8	1061.0	1057.9	1059.4	1057.9	1056.3	1056.3	1053.1	1051.5	1053.1	1053.1
20°	1026.1	1023.0	1019.8	1021.4	1018.2	1016.6	1018.2	1013.5	1015.0	1015.0	1015.0
22.5°	981.7	980.1	975.4	975.4	972.2	970.6	972.2	972.2	973.8	972.2	972.2
25°	932.6	929.4	926.2	926.2	924.7	923.1	924.7	926.2	924.7	926.2	926.2
27.5°	880.2	875.5	875.5	872.3	872.3	873.9	872.3	873.9	875.5	875.5	878.7
30°	823.2	821.5	819.9	818.3	818.3	819.9	819.9	819.9	821.5	824.8	824.8
32.5°	769.2	766.0	762.9	762.9	766.0	764.4	766.0	766.0	769.2	769.2	772.4
35°	710.5	710.5	707.4	709.0	709.0	709.0	709.0	712.1	715.3	716.9	720.0
37.5°	656.7	651.8	653.4	653.4	655.1	653.4	658.2	658.2	661.4	661.4	664.6
40°	597.9	597.9	599.5	597.9	599.5	599.5	602.7	605.8	607.4	610.6	612.1
42.5°	542.4	545.6	542.4	544.0	545.6	547.2	548.8	550.3	556.7	559.8	564.6
45°	491.7	493.3	494.9	496.4	494.9	498.0	499.6	502.8	507.5	509.1	510.7
47.5°	442.4	444.0	445.7	447.3	447.3	450.5	452.0	455.2	458.4	460.0	461.5
50°	394.9	398.0	399.6	399.6	401.2	404.5	407.6	407.6	410.8	415.5	417.1
52.5°	352.1	352.1	355.2	356.8	358.5	358.5	363.2	364.8	366.4	369.6	372.7
55°	304.5	309.2	310.8	310.8	314.0	317.1	318.8	320.4	320.4	326.7	326.7
57.5°	263.3	264.8	268.0	268.0	268.0	272.7	272.7	276.0	277.6	279.2	282.3
60°	222.0	225.2	225.2	226.8	225.2	228.3	229.9	233.2	234.8	236.4	237.9
62.5°	183.9	183.9	185.5	185.5	185.5	185.5	188.7	188.7	192.0	193.5	195.1
65°	147.4	147.4	147.4	147.4	147.4	147.4	147.4	147.4	149.1	149.1	152.3
67.5°	114.2	112.6	109.5	111.1	109.5	109.5	107.9	107.9	109.5	109.5	112.6
70°	82.5	80.9	77.7	77.7	76.1	74.6	73.0	71.4	69.8	69.8	69.8
72.5°	53.9	50.7	46.0	44.4	44.4	41.2	38.1	36.5	36.5	36.5	36.5
75°	27.0	23.8	20.7	19.0	19.0	15.8	17.4	15.8	15.8	15.8	15.8
77.5°	11.1	7.9	6.3	6.3	6.3	4.7	4.7	4.7	4.7	4.7	4.7
80°	3.2	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P584191

CATALOG NUMBER: HCC8W25D010SL-HM82555930-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9	1187.9
2.5°	1181.6	1181.6	1178.4	1180.0	1180.0	1180.0	1180.0	1180.0
5°	1167.3	1168.9	1167.3	1168.9	1168.9	1167.3	1167.3	1167.3
7.5°	1153.0	1154.6	1153.0	1154.6	1154.6	1154.6	1153.0	1153.0
10°	1135.6	1135.6	1135.6	1135.6	1135.6	1134.0	1135.6	1135.6
12.5°	1111.8	1111.8	1111.8	1113.3	1113.3	1111.8	1111.8	1110.2
15°	1086.4	1083.3	1084.9	1086.4	1084.9	1084.9	1084.9	1084.9
17.5°	1051.5	1053.1	1051.5	1051.5	1051.5	1051.5	1053.1	1051.5
20°	1015.0	1015.0	1016.6	1015.0	1015.0	1015.0	1015.0	1013.5
22.5°	973.8	972.2	972.2	973.8	973.8	972.2	973.8	973.8
25°	927.8	929.4	927.8	927.8	929.4	929.4	929.4	927.8
27.5°	878.7	880.2	881.8	880.2	880.2	880.2	881.8	883.4
30°	827.9	831.1	827.9	827.9	831.1	829.5	831.1	831.1
32.5°	773.9	778.7	775.5	778.7	778.7	780.4	778.7	780.4
35°	720.0	724.8	724.8	724.8	726.4	728.0	728.0	726.4
37.5°	669.3	670.9	670.9	674.1	675.6	677.2	677.2	675.6
40°	617.0	620.2	621.7	621.7	621.7	624.9	628.1	624.9
42.5°	566.2	567.7	569.3	569.3	572.6	574.2	575.8	575.8
45°	517.0	520.2	521.8	523.3	524.9	528.2	526.5	529.8
47.5°	466.3	471.0	472.6	474.2	477.4	478.9	480.5	482.1
50°	420.3	423.5	423.5	426.6	431.4	431.4	434.5	436.1
52.5°	374.3	375.9	377.5	379.1	382.2	385.4	385.4	388.6
55°	329.9	331.5	331.5	333.1	334.7	341.0	342.6	342.6
57.5°	283.9	283.9	287.1	288.7	290.3	293.4	293.4	293.4
60°	239.5	241.1	241.1	242.7	244.3	247.4	249.0	247.4
62.5°	195.1	196.7	196.7	198.3	201.4	203.0	201.4	201.4
65°	153.9	155.5	155.5	157.0	160.2	160.2	158.6	160.2
67.5°	112.6	112.6	112.6	112.6	112.6	112.6	112.6	112.6
70°	71.4	69.8	68.2	69.8	69.8	69.8	68.2	71.4
72.5°	34.9	36.5	36.5	36.5	36.5	36.5	36.5	34.9
75°	15.8	15.8	14.2	14.2	14.2	15.8	15.8	14.2
77.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)