

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584215

Luminaire Tested: **HCC8S25D010MB-HM82555935-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MB-HM82555935-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1986.1 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584215
CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P584215

CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32881	32881	32881
5°	34241	32808	31428
10°	35383	32389	29894
15°	36279	31650	28342
20°	36350	30334	26935
25°	35736	28414	25542
30°	33823	26221	24344
35°	30838	23580	22858
40°	26817	20787	21109
45°	23004	18002	19323
50°	19650	15524	17357
55°	17225	13370	15085
60°	15338	11403	12686
65°	13608	9303	10120
70°	12072	6897	5752
75°	10056	3610	1704
80°	7920	1137	284
85°	5626	566	0



TEST NUMBER: P584215
 CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.5	5.1
10°-20°	281.6	14.2
20°-30°	398.6	20.1
30°-40°	417.0	21.0
40°-50°	347.8	17.5
50°-60°	246.6	12.4
60°-70°	142.1	7.2
70°-80°	45.7	2.3
80°-90°	6.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	780.7	39.3
0°-40°	1197.6	60.3
0°-60°	1792.1	90.2
0°-90°	1986.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1986.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1066	1066	1066	1066	1066	
5°	1106	1092	1060	1028	1015	106
15°	1136	1090	991	913	888	320
25°	1050	972	835	768	751	479
35°	819	748	626	593	607	508
45°	528	484	413	418	443	409
55°	320	287	249	261	281	289
65°	186	156	128	128	139	186
75°	84	62	30	14	14	92
85°	16	8	2	0	0	20
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584215

CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3
2.5°	1088.6	1087.0	1085.4	1087.0	1085.4	1087.0	1085.4	1085.4	1083.8	1082.2	1082.2
5°	1106.2	1104.6	1104.6	1104.6	1103.0	1101.4	1101.4	1099.7	1096.5	1094.9	1091.8
7.5°	1117.3	1118.9	1118.9	1118.9	1115.7	1115.7	1112.5	1109.3	1106.2	1103.0	1098.1
10°	1130.0	1130.0	1128.4	1126.8	1123.6	1122.1	1120.5	1117.3	1112.5	1106.2	1101.4
12.5°	1134.8	1134.8	1133.2	1130.0	1128.4	1126.8	1125.2	1120.5	1114.1	1106.2	1099.7
15°	1136.4	1133.2	1131.6	1130.0	1126.8	1122.1	1122.1	1115.7	1107.7	1098.1	1090.2
17.5°	1123.6	1125.2	1122.1	1118.9	1114.1	1110.9	1106.2	1101.4	1091.8	1080.6	1072.7
20°	1107.7	1106.2	1104.6	1099.7	1093.3	1091.8	1087.0	1079.0	1071.1	1058.3	1047.1
22.5°	1082.2	1080.6	1077.4	1074.3	1067.9	1064.6	1059.9	1050.3	1039.2	1026.5	1013.7
25°	1050.3	1047.1	1042.4	1036.0	1031.2	1028.1	1021.6	1012.1	999.4	985.0	972.2
27.5°	999.4	1004.1	1000.9	991.4	986.5	980.2	978.6	965.9	954.7	940.3	926.0
30°	949.9	949.9	945.1	940.3	932.4	927.6	921.3	911.6	900.5	883.0	871.8
32.5°	887.8	886.2	879.8	878.3	871.8	862.3	860.7	847.9	836.7	824.0	809.7
35°	819.2	816.1	809.7	804.9	801.8	796.9	792.1	781.0	769.9	757.0	747.5
37.5°	741.1	741.1	739.6	731.6	728.3	725.2	720.4	709.3	702.9	690.2	680.5
40°	666.2	664.6	659.9	658.3	655.1	650.2	647.1	640.7	631.2	621.6	612.0
42.5°	592.9	594.5	588.1	589.7	583.4	580.2	578.5	569.0	564.2	554.7	546.7
45°	527.5	526.0	522.8	521.2	518.0	514.8	511.7	506.9	498.8	489.3	484.5
47.5°	466.9	462.2	462.2	460.6	459.0	452.6	451.0	446.3	441.5	432.0	425.5
50°	409.6	409.6	409.6	408.0	403.3	401.7	398.5	393.7	388.9	382.5	373.0
52.5°	363.4	363.4	363.4	361.8	355.5	353.8	352.2	345.8	339.5	334.7	328.4
55°	320.4	322.0	320.4	317.1	312.4	312.4	307.6	304.4	298.0	293.3	286.9
57.5°	283.7	283.7	280.6	278.9	275.7	274.1	270.9	267.7	259.8	255.0	247.1
60°	248.7	247.1	247.1	243.9	240.6	237.4	235.9	231.1	227.9	220.0	213.6
62.5°	216.8	216.8	213.6	213.6	207.2	207.2	205.7	200.8	196.0	188.1	184.9
65°	186.5	186.5	184.9	183.3	178.5	176.9	175.4	170.6	165.7	160.9	156.2
67.5°	159.4	159.4	156.2	154.6	151.4	149.8	146.6	143.5	138.7	133.9	129.1
70°	133.9	132.3	130.6	129.1	125.9	124.3	121.1	117.9	113.2	110.0	105.2
72.5°	108.4	108.4	106.8	103.6	102.0	100.4	98.9	95.7	90.8	86.0	82.9
75°	84.4	84.4	84.4	81.3	78.1	76.5	76.5	73.3	70.1	65.4	62.2
77.5°	65.4	63.8	62.2	62.2	59.0	57.4	55.7	54.1	49.4	47.8	44.6
80°	44.6	46.2	44.6	43.0	41.4	39.8	39.8	36.7	35.1	31.9	28.7
82.5°	30.3	28.7	28.7	27.1	27.1	25.5	25.5	22.4	20.8	19.2	17.5
85°	15.9	15.9	14.3	14.3	14.3	12.7	12.7	11.1	11.1	9.5	7.9
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584215

CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3
2.5°	1080.6	1077.4	1075.9	1075.9	1074.3	1072.7	1071.1	1069.5	1066.3	1066.3	1063.0
5°	1088.6	1085.4	1083.8	1079.0	1075.9	1075.9	1069.5	1067.9	1063.0	1059.9	1056.7
7.5°	1094.9	1088.6	1083.8	1079.0	1075.9	1072.7	1066.3	1059.9	1053.5	1047.1	1044.0
10°	1094.9	1088.6	1080.6	1072.7	1069.5	1066.3	1058.3	1048.7	1040.8	1034.4	1026.5
12.5°	1091.8	1082.2	1072.7	1066.3	1059.9	1055.1	1045.6	1036.0	1026.5	1013.7	1007.3
15°	1082.2	1069.5	1059.9	1048.7	1044.0	1036.0	1028.1	1013.7	1002.5	991.4	983.4
17.5°	1063.0	1047.1	1036.0	1024.8	1016.8	1012.1	999.4	986.5	973.8	961.1	951.6
20°	1034.4	1020.0	1007.3	993.0	986.5	980.2	964.3	951.6	938.8	924.4	914.8
22.5°	999.4	985.0	967.5	956.3	946.7	938.8	924.4	910.0	897.3	884.6	871.8
25°	956.3	941.9	926.0	908.5	902.1	894.1	878.3	863.8	849.5	835.1	824.0
27.5°	910.0	891.0	878.3	859.1	852.7	844.8	827.2	811.3	798.5	787.3	774.6
30°	854.3	840.0	822.4	804.9	798.5	790.5	776.2	761.8	749.1	736.4	723.6
32.5°	793.7	779.4	761.8	749.1	739.6	733.2	718.8	706.1	693.4	680.5	669.4
35°	730.0	714.0	701.3	688.5	680.5	672.6	658.3	647.1	637.5	626.4	615.2
37.5°	664.6	653.4	640.7	626.4	618.5	612.0	600.9	588.1	580.2	570.6	562.6
40°	600.9	588.1	576.9	564.2	557.8	553.1	542.0	532.3	524.4	516.4	511.7
42.5°	535.5	524.4	513.2	505.3	500.4	495.7	487.7	476.6	471.8	463.8	459.0
45°	475.0	465.4	457.4	446.3	443.1	439.9	430.4	422.3	417.6	412.8	409.6
47.5°	417.6	411.2	401.7	395.3	390.4	387.3	380.9	374.5	369.8	366.6	363.4
50°	368.2	360.2	353.8	347.4	344.2	339.5	333.1	329.9	326.8	323.6	323.6
52.5°	322.0	313.9	307.6	302.8	299.6	296.5	291.7	290.1	286.9	286.9	285.3
55°	278.9	274.1	267.7	261.4	259.8	258.2	255.0	251.9	250.3	248.7	250.3
57.5°	242.2	237.4	231.1	226.3	224.7	223.1	221.5	218.4	216.8	216.8	216.8
60°	208.8	204.0	199.2	194.4	194.4	191.2	189.7	188.1	186.5	184.9	184.9
62.5°	178.5	173.8	169.0	165.7	164.1	162.5	159.4	157.8	156.2	156.2	154.6
65°	151.4	145.1	143.5	138.7	137.1	135.5	133.9	130.6	129.1	127.5	125.9
67.5°	124.3	121.1	116.3	113.2	111.6	110.0	108.4	105.2	103.6	102.0	98.9
70°	100.4	97.3	94.1	90.8	89.2	87.6	84.4	81.3	79.7	76.5	71.7
72.5°	78.1	74.9	71.7	68.6	67.0	65.4	62.2	59.0	55.7	52.6	49.4
75°	59.0	55.7	51.0	47.8	46.2	46.2	41.4	38.2	35.1	30.3	27.1
77.5°	41.4	36.7	35.1	31.9	30.3	27.1	23.9	20.8	17.5	15.9	12.7
80°	27.1	23.9	20.8	19.2	17.5	15.9	14.3	11.1	7.9	6.4	4.8
82.5°	15.9	14.3	12.7	11.1	9.5	7.9	6.4	6.4	4.8	3.2	1.6
85°	7.9	6.4	4.8	4.8	3.2	3.2	3.2	1.6	1.6	1.6	1.6
87.5°	3.2	1.6	1.6	1.6	1.6	1.6	1.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584215

CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3
2.5°	1061.5	1059.9	1058.3	1056.7	1056.7	1053.5	1053.5	1051.9	1048.7	1047.1	1047.1
5°	1051.9	1047.1	1044.0	1042.4	1040.8	1036.0	1034.4	1031.2	1028.1	1024.8	1023.2
7.5°	1037.6	1029.7	1026.5	1024.8	1020.0	1015.3	1012.1	1007.3	1002.5	997.8	996.2
10°	1020.0	1012.1	1004.1	1000.9	996.2	993.0	986.5	980.2	975.4	970.6	965.9
12.5°	997.8	988.1	980.2	977.0	972.2	965.9	956.3	953.2	945.1	941.9	935.6
15°	972.2	961.1	953.2	948.3	943.5	934.0	927.6	921.3	913.2	910.0	903.7
17.5°	940.3	927.6	919.7	914.8	911.6	903.7	894.1	886.2	878.3	875.0	870.2
20°	902.1	894.1	883.0	878.3	875.0	865.4	855.9	852.7	846.4	840.0	835.1
22.5°	859.1	851.1	840.0	835.1	833.5	825.6	817.6	812.9	808.1	803.2	798.5
25°	814.5	804.9	795.3	792.1	788.9	782.6	776.2	773.0	768.3	765.1	761.8
27.5°	766.7	757.0	749.1	744.3	741.1	736.4	733.2	730.0	726.7	723.6	722.0
30°	715.6	706.1	699.7	696.5	693.4	691.8	686.9	685.3	683.7	680.5	682.1
32.5°	664.6	656.7	650.2	645.5	645.5	642.3	640.7	640.7	639.1	639.1	639.1
35°	608.8	604.0	599.3	597.7	596.1	594.5	592.9	594.5	592.9	594.5	596.1
37.5°	557.8	553.1	549.9	548.3	546.7	548.3	546.7	546.7	548.3	551.5	553.1
40°	505.3	502.0	498.8	500.4	498.8	498.8	498.8	503.6	505.3	506.9	508.5
42.5°	455.8	452.6	451.0	451.0	452.6	451.0	454.2	455.8	459.0	463.8	466.9
45°	408.0	406.4	406.4	408.0	406.4	409.6	409.6	412.8	417.6	420.7	423.9
47.5°	363.4	363.4	363.4	365.0	365.0	366.6	369.8	371.4	374.5	377.7	380.9
50°	322.0	323.6	325.2	325.2	325.2	328.4	331.5	333.1	334.7	336.3	341.1
52.5°	285.3	286.9	286.9	288.5	290.1	291.7	293.3	296.5	298.0	301.2	302.8
55°	250.3	250.3	253.4	255.0	255.0	255.0	258.2	258.2	261.4	263.0	266.2
57.5°	216.8	218.4	218.4	220.0	220.0	221.5	223.1	224.7	226.3	227.9	229.5
60°	184.9	184.9	184.9	186.5	188.1	189.7	188.1	191.2	191.2	194.4	196.0
62.5°	154.6	156.2	156.2	156.2	156.2	156.2	156.2	157.8	159.4	160.9	162.5
65°	125.9	125.9	125.9	124.3	125.9	124.3	125.9	127.5	127.5	129.1	130.6
67.5°	97.3	97.3	94.1	94.1	95.7	95.7	95.7	95.7	94.1	97.3	97.3
70°	70.1	68.6	67.0	65.4	65.4	63.8	63.8	62.2	62.2	62.2	62.2
72.5°	46.2	43.0	39.8	38.2	36.7	36.7	33.5	31.9	33.5	33.5	33.5
75°	23.9	20.8	19.2	17.5	15.9	15.9	14.3	14.3	14.3	14.3	14.3
77.5°	9.5	7.9	6.4	6.4	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	3.2	3.2	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	1.6	0.0	0.0	1.6	0.0	1.6	1.6	1.6	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584215

CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3	1066.3
2.5°	1045.6	1045.6	1044.0	1045.6	1042.4	1044.0	1042.4	1042.4
5°	1021.6	1018.4	1018.4	1018.4	1016.8	1016.8	1015.3	1015.3
7.5°	993.0	991.4	989.8	988.1	986.5	985.0	985.0	985.0
10°	964.3	961.1	961.1	959.5	956.3	954.7	954.7	954.7
12.5°	930.8	929.2	927.6	927.6	921.3	922.9	921.3	921.3
15°	898.9	897.3	897.3	892.6	889.4	889.4	889.4	887.8
17.5°	865.4	863.8	862.3	859.1	855.9	855.9	854.3	855.9
20°	830.4	828.8	825.6	825.6	824.0	822.4	819.2	820.8
22.5°	795.3	792.1	790.5	790.5	788.9	788.9	785.8	785.8
25°	758.6	757.0	755.5	757.0	753.9	753.9	750.7	750.7
27.5°	720.4	718.8	718.8	718.8	717.2	718.8	717.2	717.2
30°	682.1	682.1	680.5	680.5	682.1	680.5	682.1	683.7
32.5°	640.7	640.7	642.3	642.3	643.9	643.9	643.9	643.9
35°	597.7	600.9	600.9	602.5	604.0	605.6	605.6	607.2
37.5°	557.8	559.4	561.0	562.6	565.8	565.8	565.8	565.8
40°	514.8	516.4	519.6	518.0	524.4	526.0	524.4	524.4
42.5°	470.2	473.4	475.0	478.2	479.8	482.9	484.5	484.5
45°	428.7	430.4	433.6	436.7	438.3	443.1	443.1	443.1
47.5°	385.7	388.9	390.4	393.7	395.3	400.1	401.7	400.1
50°	344.2	347.4	350.6	350.6	355.5	357.1	360.2	361.8
52.5°	304.4	306.0	309.2	310.8	313.9	317.1	318.8	320.4
55°	266.2	267.7	270.9	270.9	275.7	277.3	280.6	280.6
57.5°	231.1	232.7	235.9	234.3	237.4	240.6	240.6	239.0
60°	197.6	197.6	197.6	200.8	202.4	204.0	205.7	205.7
62.5°	162.5	165.7	167.3	167.3	169.0	170.6	170.6	169.0
65°	130.6	133.9	135.5	135.5	137.1	137.1	137.1	138.7
67.5°	98.9	98.9	98.9	100.4	98.9	98.9	98.9	98.9
70°	62.2	62.2	62.2	62.2	60.6	62.2	62.2	63.8
72.5°	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5
75°	14.3	14.3	14.3	15.9	14.3	14.3	14.3	14.3
77.5°	6.4	4.8	6.4	6.4	4.8	4.8	4.8	4.8
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	0.0	1.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)