

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584216

Luminaire Tested: **HCC8W25D010SL-HM82555935-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584216  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W25D010SL-HM82555935-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2167.8 lumens  
Efficiency: N/A  
Efficacy: 80.9 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584216  
CATALOG NUMBER: HCC8W25D010SL-HM82555935-81WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P584216

CATALOG NUMBER: HCC8W25D010SL-HM82555935-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	36220	36220	36220
5°	37495	36015	34585
10°	38329	35383	32640
15°	38874	34194	30478
20°	38758	32533	28293
25°	37797	30421	25974
30°	35810	27980	23835
35°	32577	25319	21657
40°	28613	22518	19567
45°	24949	19807	17448
50°	21712	17357	15370
55°	19365	15252	13370
60°	17595	13371	11403
65°	15819	11631	10354
70°	14083	9918	9341
75°	12343	8352	7983
80°	10477	6784	7068
85°	7925	5059	5626



TEST NUMBER: P584216  
 CATALOG NUMBER: HCC8W25D010SL-HM82555935-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.0	5.1
10°-20°	303.2	14.0
20°-30°	420.8	19.4
30°-40°	435.1	20.1
40°-50°	364.3	16.8
50°-60°	264.4	12.2
60°-70°	166.9	7.7
70°-80°	82.7	3.8
80°-90°	20.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	834.0	38.5
0°-40°	1269.0	58.5
0°-60°	1897.8	87.5
0°-90°	2167.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2167.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1175	1175	1175	1175	1175	
5°	1211	1197	1164	1132	1117	116
15°	1218	1171	1071	985	955	343
25°	1111	1039	894	797	763	509
35°	865	802	673	596	575	539
45°	572	531	454	410	400	443
55°	360	328	284	260	249	325
65°	217	190	159	140	142	216
75°	104	86	70	67	67	111
85°	22	18	14	16	16	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584216

CATALOG NUMBER: HCC8W25D010SL-HM82555935-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6
2.5°	1193.8	1193.8	1195.4	1193.8	1193.8	1193.8	1192.2	1192.2	1190.6	1190.6	1187.4
5°	1211.3	1208.1	1211.3	1208.1	1208.1	1208.1	1206.5	1203.3	1201.7	1198.5	1197.0
7.5°	1219.3	1217.7	1217.7	1216.1	1216.1	1214.4	1213.0	1211.3	1204.9	1203.3	1198.5
10°	1224.1	1222.5	1222.5	1220.9	1217.7	1217.7	1214.4	1213.0	1204.9	1201.7	1195.4
12.5°	1222.5	1222.5	1222.5	1220.9	1216.1	1214.4	1211.3	1206.5	1200.1	1193.8	1187.4
15°	1217.7	1217.7	1214.4	1213.0	1208.1	1204.9	1203.3	1195.4	1189.0	1181.1	1171.4
17.5°	1201.7	1201.7	1200.1	1197.0	1192.2	1189.0	1185.8	1177.9	1171.4	1158.7	1149.2
20°	1181.1	1179.5	1177.9	1173.0	1168.2	1166.7	1161.9	1150.8	1142.8	1133.2	1120.5
22.5°	1150.8	1149.2	1147.6	1144.4	1136.4	1133.2	1130.0	1122.0	1107.7	1098.1	1082.2
25°	1110.9	1110.9	1107.7	1103.0	1094.9	1091.7	1087.0	1079.0	1066.3	1051.9	1039.2
27.5°	1064.6	1063.0	1058.3	1055.1	1048.7	1044.0	1036.0	1026.5	1013.7	1002.5	986.5
30°	1005.7	1005.7	1002.5	997.8	989.8	986.5	980.2	969.0	956.3	941.9	930.8
32.5°	938.7	938.7	934.0	930.8	926.0	918.1	916.5	903.7	892.6	881.4	868.6
35°	865.4	867.0	863.8	857.5	849.5	849.5	846.4	835.1	822.4	811.3	801.6
37.5°	792.1	787.3	785.8	782.6	777.8	771.4	768.3	763.4	752.3	744.3	730.0
40°	710.8	712.4	709.3	706.1	704.5	699.7	698.1	690.2	682.1	672.6	666.2
42.5°	637.5	637.5	637.5	634.3	631.2	626.4	624.8	620.0	610.4	604.0	594.5
45°	572.1	567.4	567.4	565.8	564.2	561.0	556.3	553.1	546.7	541.8	530.7
47.5°	508.5	510.1	508.5	506.9	502.0	500.4	498.8	492.5	486.1	481.3	473.4
50°	452.6	455.8	452.6	452.6	449.5	447.9	444.7	439.9	435.1	427.1	419.2
52.5°	406.4	406.4	404.8	403.3	398.5	395.3	393.7	392.0	384.1	377.7	371.4
55°	360.2	361.8	361.8	357.1	355.5	352.2	350.6	345.8	342.7	333.1	328.3
57.5°	320.4	318.8	320.4	317.1	313.9	310.8	309.2	306.0	301.2	294.9	288.5
60°	285.3	282.2	282.2	280.6	277.3	275.7	272.5	267.7	263.0	256.6	251.8
62.5°	250.3	248.7	247.1	245.5	242.2	240.6	239.0	234.3	229.5	224.7	220.0
65°	216.8	216.8	215.2	212.0	210.4	208.8	207.2	204.0	197.6	194.4	189.7
67.5°	186.5	184.9	184.9	181.7	178.5	176.9	176.9	173.8	169.0	164.1	160.9
70°	156.2	157.8	156.2	154.6	151.4	151.4	148.2	146.6	140.3	138.7	133.9
72.5°	129.1	129.1	127.5	127.5	124.3	122.7	122.7	119.5	116.3	113.2	110.0
75°	103.6	103.6	103.6	102.0	100.4	97.3	97.3	95.7	92.4	89.2	86.0
77.5°	81.3	79.7	79.7	78.1	76.5	74.9	74.9	73.3	70.1	68.6	65.4
80°	59.0	57.4	57.4	57.4	54.1	55.7	54.1	52.6	51.0	49.4	47.8
82.5°	38.2	39.8	39.8	38.2	36.7	36.7	36.7	35.1	35.1	33.5	31.9
85°	22.4	22.4	22.4	22.4	20.8	20.8	20.8	19.2	19.2	19.2	17.5
87.5°	9.5	9.5	9.5	9.5	9.5	9.5	7.9	7.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584216

CATALOG NUMBER: HCC8W25D010SL-HM82555935-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6
2.5°	1187.4	1184.2	1182.6	1181.1	1181.1	1179.5	1177.9	1174.6	1174.6	1171.4	1169.8
5°	1193.8	1189.0	1185.8	1182.6	1181.1	1177.9	1174.6	1169.8	1168.2	1163.5	1158.7
7.5°	1195.4	1187.4	1184.2	1177.9	1174.6	1171.4	1165.1	1160.3	1153.9	1149.2	1142.8
10°	1189.0	1182.6	1174.6	1166.7	1165.1	1160.3	1150.8	1144.4	1136.4	1130.0	1120.5
12.5°	1179.5	1169.8	1161.9	1152.3	1147.6	1142.8	1133.2	1123.6	1112.5	1101.4	1091.7
15°	1163.5	1152.3	1141.2	1130.0	1123.6	1118.9	1107.7	1096.5	1085.4	1071.1	1061.4
17.5°	1139.6	1126.8	1115.7	1101.4	1094.9	1090.2	1075.8	1063.0	1048.7	1034.4	1024.8
20°	1109.3	1093.3	1080.6	1064.6	1059.9	1051.9	1037.6	1023.2	1007.3	991.4	980.2
22.5°	1069.5	1053.5	1039.2	1023.2	1015.2	1007.3	993.0	975.4	959.5	946.7	935.6
25°	1023.2	1008.9	991.4	977.0	967.5	957.9	941.9	927.6	913.2	894.1	883.0
27.5°	972.2	954.7	941.9	922.9	913.2	906.9	889.4	870.2	857.5	840.0	827.2
30°	914.8	898.9	884.6	865.4	855.9	849.5	833.5	816.1	803.2	785.8	773.0
32.5°	854.3	836.7	819.2	806.5	795.3	788.9	771.4	760.2	744.3	730.0	715.6
35°	788.9	771.4	758.6	741.1	734.8	728.3	714.0	699.7	685.3	672.6	661.5
37.5°	718.8	706.1	691.8	679.0	674.2	667.8	650.2	637.5	626.4	613.6	604.0
40°	650.2	639.1	629.6	616.9	608.8	604.0	591.3	580.2	567.4	559.4	549.9
42.5°	588.1	575.3	565.8	556.3	548.3	543.5	532.3	524.4	514.8	506.9	495.7
45°	522.8	516.4	505.3	497.2	492.5	486.1	478.2	468.6	460.6	454.2	446.3
47.5°	465.3	459.0	451.0	441.5	438.3	433.6	425.5	419.2	412.8	406.4	398.5
50°	412.8	404.8	398.5	392.0	388.9	384.1	376.1	373.0	368.2	361.8	357.1
52.5°	365.0	358.6	352.2	344.2	342.7	339.5	334.7	328.3	323.6	320.4	317.1
55°	322.0	315.5	310.8	304.4	302.8	299.6	293.3	290.1	286.9	283.7	280.6
57.5°	283.7	277.3	270.9	267.7	264.6	261.4	259.8	255.0	251.8	250.3	247.1
60°	248.7	242.2	237.4	232.7	231.1	229.5	226.3	223.1	220.0	216.8	215.2
62.5°	215.2	208.8	205.7	202.4	199.2	199.2	196.0	192.8	189.7	188.1	184.9
65°	184.9	181.7	176.9	172.2	170.6	170.6	165.7	164.1	162.5	159.4	156.2
67.5°	156.2	153.0	148.2	146.6	145.0	143.5	141.9	138.7	135.5	133.9	130.6
70°	130.6	127.5	124.3	122.7	121.1	119.5	116.3	114.7	111.6	110.0	108.4
72.5°	105.2	103.6	100.4	98.9	97.3	95.7	94.1	92.4	89.2	87.6	86.0
75°	84.4	82.9	79.7	78.1	76.5	76.5	74.9	71.7	70.1	70.1	68.6
77.5°	63.8	62.2	60.6	59.0	57.4	57.4	55.7	54.1	52.6	52.6	51.0
80°	46.2	44.6	43.0	43.0	43.0	41.4	39.8	39.8	38.2	38.2	36.7
82.5°	30.3	30.3	28.7	28.7	28.7	27.1	27.1	25.5	25.5	25.5	25.5
85°	17.5	17.5	17.5	15.9	15.9	15.9	15.9	15.9	15.9	14.3	15.9
87.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584216

CATALOG NUMBER: HCC8W25D010SL-HM82555935-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6
2.5°	1168.2	1166.7	1163.5	1163.5	1160.3	1160.3	1158.7	1157.1	1155.5	1153.9	1152.3
5°	1157.1	1150.8	1147.6	1146.0	1142.8	1141.2	1136.4	1133.2	1131.6	1128.4	1125.2
7.5°	1136.4	1130.0	1123.6	1122.0	1120.5	1114.1	1109.3	1104.6	1101.4	1098.1	1094.9
10°	1112.5	1106.2	1098.1	1094.9	1091.7	1083.8	1077.4	1072.7	1066.3	1059.9	1058.3
12.5°	1083.8	1074.3	1064.6	1061.4	1056.7	1048.7	1042.4	1034.4	1029.7	1021.6	1020.0
15°	1050.3	1039.2	1031.2	1023.2	1020.0	1012.1	1000.9	994.6	984.9	981.8	973.8
17.5°	1010.5	999.4	988.1	984.9	980.2	969.0	957.9	949.9	940.3	935.6	930.8
20°	969.0	954.7	943.5	940.3	934.0	924.4	913.2	905.3	897.3	887.8	883.0
22.5°	921.3	905.3	895.7	887.8	886.2	875.0	862.2	855.9	849.5	841.6	835.1
25°	868.6	854.3	843.2	836.7	833.5	824.0	814.5	806.5	796.9	792.1	784.2
27.5°	814.5	804.9	790.5	784.2	779.4	771.4	760.2	755.4	745.9	739.6	734.8
30°	761.8	747.5	739.6	731.6	726.7	718.8	709.3	704.5	696.5	690.2	685.3
32.5°	704.5	694.9	683.7	680.5	674.2	666.2	659.9	651.8	645.5	639.1	637.5
35°	651.8	639.1	628.0	624.8	620.0	612.0	608.8	604.0	596.1	594.5	588.1
37.5°	594.5	588.1	575.3	570.6	569.0	562.6	556.3	553.1	548.3	543.5	541.8
40°	540.4	532.3	526.0	521.2	518.0	513.2	506.9	505.3	502.0	495.7	494.1
42.5°	489.3	481.3	475.0	473.4	468.6	463.8	460.6	455.8	454.2	452.6	449.5
45°	439.9	435.1	428.7	427.1	425.5	419.2	416.0	412.8	409.6	408.0	404.8
47.5°	395.3	390.4	385.7	384.1	380.9	379.3	374.5	373.0	368.2	366.6	365.0
50°	352.2	349.0	345.8	344.2	341.1	339.5	336.3	333.1	329.9	328.3	326.8
52.5°	313.9	310.8	307.6	306.0	304.4	301.2	298.0	294.9	293.3	291.7	290.1
55°	277.3	274.1	272.5	270.9	269.3	267.7	263.0	261.4	259.8	258.2	255.0
57.5°	243.9	240.6	237.4	237.4	235.9	234.3	231.1	227.9	227.9	224.7	221.5
60°	213.6	210.4	207.2	205.7	204.0	200.8	199.2	197.6	196.0	194.4	191.2
62.5°	181.7	180.1	176.9	176.9	173.8	172.2	170.6	169.0	167.3	164.1	162.5
65°	154.6	153.0	149.8	148.2	148.2	146.6	143.5	141.9	140.3	140.3	138.7
67.5°	129.1	127.5	124.3	122.7	122.7	121.1	119.5	119.5	117.9	116.3	117.9
70°	106.8	103.6	103.6	102.0	102.0	100.4	98.9	98.9	98.9	100.4	100.4
72.5°	84.4	82.9	81.3	81.3	81.3	81.3	79.7	79.7	81.3	82.9	82.9
75°	67.0	65.4	65.4	65.4	63.8	63.8	65.4	65.4	67.0	67.0	67.0
77.5°	49.4	49.4	49.4	49.4	49.4	49.4	51.0	51.0	52.6	52.6	52.6
80°	36.7	36.7	36.7	36.7	36.7	38.2	38.2	38.2	38.2	38.2	39.8
82.5°	25.5	25.5	25.5	25.5	25.5	25.5	25.5	27.1	27.1	27.1	27.1
85°	14.3	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9
87.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584216

CATALOG NUMBER: HCC8W25D010SL-HM82555935-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6	1174.6
2.5°	1150.8	1150.8	1150.8	1152.3	1149.2	1149.2	1149.2	1149.2
5°	1123.6	1122.0	1120.5	1122.0	1118.9	1118.9	1117.3	1117.3
7.5°	1090.2	1088.6	1087.0	1087.0	1083.8	1083.8	1082.2	1080.6
10°	1053.5	1050.3	1051.9	1048.7	1047.1	1045.5	1044.0	1042.4
12.5°	1013.7	1010.5	1008.9	1005.7	1002.5	1000.9	1002.5	999.4
15°	970.6	965.9	964.3	961.1	957.9	956.3	956.3	954.7
17.5°	922.9	919.7	918.1	914.8	913.2	910.0	908.4	906.9
20°	878.1	870.2	871.8	868.6	867.0	860.7	860.7	862.2
22.5°	828.8	824.0	820.8	817.6	816.1	812.9	812.9	811.3
25°	779.4	774.6	773.0	769.9	768.3	765.1	763.4	763.4
27.5°	731.6	725.1	725.1	722.0	718.8	717.2	715.6	714.0
30°	680.5	675.8	674.2	674.2	672.6	672.6	667.8	669.4
32.5°	632.8	629.6	628.0	624.8	624.8	623.2	623.2	618.4
35°	585.0	580.2	581.8	578.5	576.9	575.3	576.9	575.3
37.5°	538.7	535.5	535.5	532.3	532.3	530.7	529.1	532.3
40°	492.5	490.9	489.3	487.7	489.3	487.7	484.5	486.1
42.5°	446.3	446.3	444.7	444.7	443.1	443.1	443.1	443.1
45°	404.8	403.3	403.3	401.7	401.7	401.7	401.7	400.1
47.5°	363.4	361.8	361.8	361.8	360.2	360.2	358.6	360.2
50°	323.6	323.6	322.0	322.0	323.6	322.0	320.4	320.4
52.5°	286.9	286.9	285.3	285.3	283.7	282.2	283.7	283.7
55°	253.4	251.8	250.3	250.3	248.7	247.1	247.1	248.7
57.5°	221.5	220.0	218.4	218.4	215.2	213.6	213.6	213.6
60°	191.2	188.1	188.1	186.5	186.5	184.9	184.9	184.9
62.5°	162.5	160.9	160.9	160.9	160.9	159.4	159.4	159.4
65°	138.7	138.7	138.7	140.3	140.3	141.9	141.9	141.9
67.5°	119.5	121.1	121.1	121.1	122.7	122.7	122.7	121.1
70°	102.0	102.0	102.0	103.6	103.6	103.6	103.6	103.6
72.5°	84.4	84.4	84.4	84.4	84.4	84.4	84.4	84.4
75°	67.0	68.6	68.6	68.6	67.0	68.6	68.6	67.0
77.5°	52.6	52.6	52.6	52.6	52.6	52.6	52.6	52.6
80°	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8
82.5°	27.1	27.1	27.1	27.1	27.1	27.1	27.1	27.1
85°	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9
87.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)