

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584234

Luminaire Tested: **HCC8S25D010MW-HM82555940-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584234  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S25D010MW-HM82555940-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2494.9 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584234  
CATALOG NUMBER: HCC8S25D010MW-HM82555940-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584234

CATALOG NUMBER: HCC8S25D010MW-HM82555940-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	38252	38252	38252
5°	39652	38126	36817
10°	40775	37794	35311
15°	41683	37128	33753
20°	41748	35677	32382
25°	40948	33694	31238
30°	38840	31245	29867
35°	35288	28459	28523
40°	30855	25533	26882
45°	26741	22742	25053
50°	23416	20206	22821
55°	20843	17903	20650
60°	18798	16084	18144
65°	16972	14141	15819
70°	15255	11910	11757
75°	13439	9448	8817
80°	11276	7831	8453
85°	8739	6864	7501



TEST NUMBER: P584234

CATALOG NUMBER: HCC8S25D010MW-HM82555940-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.0	4.7
10°-20°	329.6	13.2
20°-30°	471.1	18.9
30°-40°	500.5	20.1
40°-50°	430.9	17.3
50°-60°	322.2	12.9
60°-70°	205.5	8.2
70°-80°	93.5	3.7
80°-90°	24.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	917.7	36.8
0°-40°	1418.2	56.8
0°-60°	2171.4	87.0
0°-90°	2494.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2494.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1240	1240	1240	1240	1240	
5°	1281	1263	1232	1200	1189	123
15°	1306	1262	1163	1084	1057	368
25°	1204	1128	990	930	918	551
35°	937	872	756	737	758	584
45°	613	580	522	536	574	477
55°	388	356	333	361	384	349
65°	233	206	194	203	217	232
75°	113	97	79	72	74	120
85°	25	21	19	21	21	30
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584234

CATALOG NUMBER: HCC8S25D010MW-HM82555940-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5
2.5°	1263.3	1259.8	1261.6	1259.8	1261.6	1261.6	1258.1	1258.1	1258.1	1258.1	1252.9
5°	1281.0	1279.3	1279.3	1277.5	1275.8	1277.5	1275.8	1273.9	1270.4	1268.7	1263.3
7.5°	1291.6	1291.6	1291.6	1291.6	1289.8	1288.1	1286.4	1282.8	1279.3	1275.8	1272.2
10°	1302.2	1303.9	1302.2	1300.4	1298.7	1295.1	1293.3	1289.8	1284.5	1279.3	1275.8
12.5°	1307.4	1307.4	1305.7	1305.7	1302.2	1300.4	1295.1	1289.8	1284.5	1279.3	1270.4
15°	1305.7	1305.7	1303.9	1302.2	1296.8	1295.1	1291.6	1286.4	1277.5	1270.4	1261.6
17.5°	1295.1	1293.3	1289.8	1289.8	1282.8	1281.0	1277.5	1270.4	1261.6	1251.0	1240.5
20°	1272.2	1272.2	1270.4	1268.7	1261.6	1256.4	1252.9	1244.0	1236.9	1224.6	1214.0
22.5°	1240.5	1244.0	1240.5	1236.9	1228.1	1226.4	1221.1	1210.5	1200.0	1185.9	1173.6
25°	1203.5	1201.7	1200.0	1196.5	1189.4	1185.9	1178.8	1168.2	1157.6	1141.8	1127.7
27.5°	1155.9	1148.9	1148.9	1141.8	1136.6	1131.2	1127.7	1117.2	1103.1	1090.8	1073.1
30°	1090.8	1092.5	1083.7	1081.9	1073.1	1069.6	1062.5	1051.9	1039.6	1025.5	1011.5
32.5°	1020.2	1014.9	1014.9	1007.9	1000.9	995.5	993.8	981.5	970.9	956.8	942.7
35°	937.4	937.4	932.1	930.4	923.3	919.8	914.5	907.5	895.2	882.8	872.3
37.5°	856.3	852.8	851.1	847.5	842.3	837.0	837.0	824.6	822.8	808.8	794.7
40°	766.5	770.0	766.5	761.2	759.5	756.0	754.1	747.1	741.8	729.5	720.6
42.5°	690.7	687.2	687.2	685.4	678.4	678.4	674.8	671.3	662.5	659.0	648.4
45°	613.2	616.7	611.4	613.2	606.2	606.2	606.2	599.1	592.0	586.8	579.7
47.5°	546.2	547.9	547.9	542.7	541.0	541.0	537.5	533.9	528.6	521.5	516.3
50°	488.1	489.8	486.3	484.6	481.1	479.3	479.3	472.2	468.7	461.7	458.2
52.5°	435.3	435.3	433.5	433.5	428.2	428.2	424.7	419.3	415.8	412.3	403.5
55°	387.7	387.7	385.8	384.1	384.1	378.9	377.1	371.8	368.3	361.2	355.9
57.5°	341.9	343.6	341.9	340.0	338.3	336.5	333.0	327.7	324.2	319.0	315.4
60°	304.8	304.8	303.0	301.3	297.8	296.1	294.2	290.7	285.5	281.9	276.6
62.5°	269.6	267.8	266.1	264.3	260.8	260.8	257.2	253.7	248.5	244.9	241.4
65°	232.6	232.6	230.8	230.8	229.1	225.6	223.7	222.0	215.0	213.3	206.2
67.5°	199.1	200.8	197.3	197.3	193.8	193.8	192.1	186.8	185.0	181.5	177.9
70°	169.2	169.2	169.2	167.3	163.9	162.1	160.4	156.9	155.0	151.5	148.0
72.5°	139.2	139.2	137.4	137.4	135.7	134.0	132.1	128.6	128.6	125.1	121.6
75°	112.8	112.8	111.0	109.2	107.5	107.5	105.7	104.0	100.5	98.7	96.9
77.5°	86.3	86.3	86.3	84.5	82.8	82.8	82.8	79.3	75.8	75.8	74.0
80°	63.5	63.5	61.6	61.6	59.9	59.9	59.9	58.1	56.4	54.7	52.9
82.5°	42.3	42.3	42.3	42.3	40.6	40.6	40.6	38.7	37.0	37.0	37.0
85°	24.7	24.7	24.7	24.7	22.9	22.9	22.9	22.9	22.9	21.2	21.2
87.5°	10.6	8.8	10.6	8.8	10.6	8.8	10.6	8.8	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584234

CATALOG NUMBER: HCC8S25D010MW-HM82555940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5
2.5°	1254.6	1252.9	1251.0	1249.3	1249.3	1247.5	1244.0	1242.3	1240.5	1238.7	1238.7
5°	1261.6	1259.8	1256.4	1252.9	1251.0	1247.5	1244.0	1240.5	1236.9	1231.7	1230.0
7.5°	1266.9	1261.6	1258.1	1251.0	1249.3	1245.8	1240.5	1235.2	1228.1	1221.1	1215.8
10°	1266.9	1259.8	1254.6	1245.8	1242.3	1238.7	1231.7	1222.9	1214.0	1207.0	1198.2
12.5°	1263.3	1254.6	1245.8	1236.9	1231.7	1226.4	1215.8	1207.0	1196.5	1185.9	1178.8
15°	1251.0	1240.5	1230.0	1219.4	1214.0	1207.0	1196.5	1184.1	1173.6	1163.0	1150.6
17.5°	1228.1	1217.6	1205.2	1192.9	1185.9	1180.5	1164.7	1155.9	1140.1	1129.5	1118.9
20°	1198.2	1185.9	1170.0	1157.6	1148.9	1143.6	1131.2	1115.4	1103.1	1087.2	1076.6
22.5°	1159.5	1143.6	1127.7	1115.4	1106.6	1099.5	1083.7	1067.8	1057.3	1043.1	1030.8
25°	1113.7	1097.7	1081.9	1064.3	1055.4	1048.4	1034.4	1020.2	1006.1	990.3	979.7
27.5°	1059.0	1041.3	1027.3	1011.5	1002.6	992.0	976.2	962.0	948.0	937.4	923.3
30°	999.1	979.7	965.6	949.7	941.0	932.1	916.2	902.2	889.8	877.5	870.4
32.5°	926.8	912.7	898.7	882.8	875.8	870.4	854.6	840.5	826.4	815.9	810.5
35°	858.1	842.3	829.9	815.9	807.0	801.8	787.6	775.3	768.3	756.0	748.9
37.5°	785.9	773.5	759.5	745.4	740.0	734.8	724.2	711.9	701.3	692.5	689.0
40°	710.2	699.6	687.2	678.4	673.1	667.8	659.0	650.2	643.2	634.3	630.8
42.5°	637.8	630.8	620.3	609.7	604.3	602.6	592.0	585.0	581.4	577.9	574.5
45°	572.7	562.1	555.0	547.9	542.7	539.2	533.9	528.6	525.0	521.5	518.1
47.5°	509.2	500.4	493.4	488.1	482.8	481.1	477.5	472.2	468.7	468.7	468.7
50°	451.1	444.0	437.0	433.5	431.7	428.2	424.7	422.9	421.2	421.2	421.2
52.5°	400.0	392.9	387.7	384.1	384.1	380.6	377.1	375.4	375.4	375.4	375.4
55°	352.5	347.1	343.6	340.0	336.5	334.8	334.8	334.8	333.0	333.0	334.8
57.5°	310.1	306.6	301.3	297.8	296.1	296.1	294.2	292.5	294.2	296.1	297.8
60°	271.4	267.8	266.1	260.8	260.8	260.8	259.0	259.0	259.0	260.8	262.6
62.5°	236.1	234.3	230.8	229.1	227.3	227.3	225.6	225.6	225.6	225.6	227.3
65°	204.4	200.8	197.3	197.3	197.3	195.6	195.6	192.1	193.8	193.8	192.1
67.5°	174.4	170.9	169.2	167.3	165.6	165.6	163.9	162.1	160.4	160.4	160.4
70°	146.3	142.7	142.7	139.2	139.2	137.4	135.7	135.7	134.0	132.1	130.4
72.5°	118.0	116.3	114.5	112.8	112.8	112.8	111.0	109.2	107.5	105.7	102.2
75°	93.4	93.4	89.9	88.1	88.1	86.3	84.5	82.8	81.1	79.3	77.6
77.5°	72.2	70.5	67.0	65.2	65.2	65.2	63.5	61.6	59.9	58.1	56.4
80°	52.9	51.1	49.3	47.6	47.6	47.6	45.8	45.8	44.1	44.1	44.1
82.5°	35.2	35.2	33.5	33.5	33.5	33.5	31.7	31.7	31.7	31.7	31.7
85°	21.2	21.2	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584234

CATALOG NUMBER: HCC8S25D010MW-HM82555940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5
2.5°	1235.2	1235.2	1231.7	1230.0	1228.1	1230.0	1226.4	1224.6	1222.9	1222.9	1221.1
5°	1224.6	1222.9	1215.8	1214.0	1212.3	1210.5	1207.0	1203.5	1200.0	1198.2	1196.5
7.5°	1210.5	1205.2	1198.2	1196.5	1194.7	1189.4	1184.1	1180.5	1175.3	1173.6	1170.0
10°	1191.1	1184.1	1178.8	1173.6	1170.0	1164.7	1159.5	1154.1	1147.1	1145.3	1140.1
12.5°	1168.2	1159.5	1148.9	1147.1	1141.8	1134.7	1127.7	1122.4	1117.2	1113.7	1108.3
15°	1140.1	1131.2	1120.7	1115.4	1110.1	1104.8	1096.0	1088.9	1083.7	1078.3	1073.1
17.5°	1106.6	1096.0	1087.2	1081.9	1078.3	1069.6	1062.5	1053.7	1048.4	1043.1	1037.9
20°	1066.0	1057.3	1044.9	1039.6	1037.9	1030.8	1022.0	1018.4	1011.5	1006.1	1002.6
22.5°	1020.2	1011.5	1000.9	997.3	990.3	986.8	978.0	974.4	970.9	965.6	963.9
25°	969.1	960.3	951.6	949.7	944.5	941.0	935.6	930.4	930.4	925.1	925.1
27.5°	916.2	907.5	900.4	896.9	895.2	891.6	886.3	884.6	882.8	881.0	881.0
30°	859.9	849.3	845.8	844.0	842.3	838.8	837.0	833.4	835.2	837.0	835.2
32.5°	799.9	796.4	789.4	785.9	787.6	785.9	782.4	785.9	784.1	787.6	789.4
35°	741.8	738.3	734.8	734.8	731.2	731.2	731.2	733.1	736.6	738.3	741.8
37.5°	685.4	680.2	678.4	676.7	678.4	678.4	678.4	681.9	685.4	689.0	694.2
40°	625.5	622.0	622.0	622.0	622.0	627.3	625.5	629.1	632.6	637.8	643.2
42.5°	569.1	569.1	571.0	571.0	571.0	571.0	574.5	579.7	585.0	590.3	595.6
45°	516.3	516.3	516.3	519.8	519.8	521.5	528.6	532.1	535.6	541.0	546.2
47.5°	466.9	466.9	468.7	470.5	472.2	475.7	479.3	484.6	489.8	493.4	498.6
50°	421.2	422.9	426.4	429.9	429.9	431.7	437.0	440.5	444.0	449.3	451.1
52.5°	377.1	380.6	384.1	385.8	387.7	391.2	392.9	398.3	400.0	405.3	407.0
55°	336.5	338.3	343.6	345.4	345.4	348.9	352.5	355.9	361.2	361.2	364.8
57.5°	299.6	301.3	304.8	306.6	304.8	310.1	311.9	315.4	317.1	320.7	322.5
60°	262.6	266.1	267.8	267.8	269.6	271.4	274.9	274.9	278.4	281.9	281.9
62.5°	227.3	229.1	230.8	232.6	234.3	232.6	237.9	237.9	241.4	243.2	246.6
65°	193.8	195.6	195.6	197.3	197.3	199.1	199.1	200.8	202.7	206.2	207.9
67.5°	160.4	160.4	160.4	162.1	160.4	162.1	162.1	163.9	163.9	167.3	169.2
70°	130.4	128.6	126.9	126.9	126.9	126.9	125.1	126.9	126.9	128.6	128.6
72.5°	100.5	98.7	96.9	95.1	95.1	93.4	91.6	93.4	93.4	95.1	95.1
75°	75.8	72.2	72.2	72.2	70.5	70.5	70.5	72.2	72.2	72.2	74.0
77.5°	56.4	56.4	54.7	54.7	54.7	56.4	56.4	58.1	58.1	58.1	58.1
80°	42.3	44.1	44.1	44.1	44.1	45.8	45.8	45.8	45.8	47.6	47.6
82.5°	31.7	31.7	31.7	31.7	33.5	33.5	33.5	33.5	33.5	33.5	33.5
85°	19.4	21.2	21.2	19.4	21.2	21.2	21.2	21.2	21.2	21.2	21.2
87.5°	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584234

CATALOG NUMBER: HCC8S25D010MW-HM82555940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5	1240.5
2.5°	1219.4	1219.4	1219.4	1219.4	1217.6	1217.6	1217.6	1215.8
5°	1192.9	1192.9	1192.9	1189.4	1191.1	1191.1	1187.6	1189.4
7.5°	1166.5	1164.7	1163.0	1163.0	1161.2	1159.5	1157.6	1159.5
10°	1136.6	1131.2	1131.2	1129.5	1129.5	1126.0	1126.0	1127.7
12.5°	1103.1	1099.5	1099.5	1097.7	1096.0	1094.3	1092.5	1092.5
15°	1069.6	1066.0	1064.3	1062.5	1060.8	1057.3	1059.0	1057.3
17.5°	1036.1	1030.8	1030.8	1029.0	1027.3	1023.8	1023.8	1022.0
20°	997.3	995.5	992.0	993.8	992.0	988.5	986.8	986.8
22.5°	958.5	958.5	956.8	956.8	955.1	953.3	951.6	951.6
25°	921.6	919.8	921.6	921.6	916.2	916.2	916.2	918.1
27.5°	879.2	881.0	879.2	879.2	879.2	879.2	881.0	879.2
30°	837.0	837.0	837.0	838.8	842.3	840.5	840.5	838.8
32.5°	791.2	793.0	793.0	794.7	796.4	799.9	799.9	801.8
35°	745.4	748.9	750.6	748.9	754.1	754.1	757.7	757.7
37.5°	697.7	699.6	703.1	704.8	708.3	710.2	711.9	711.9
40°	646.7	653.8	655.5	657.2	662.5	662.5	664.3	667.8
42.5°	599.1	606.2	607.9	609.7	613.2	618.5	616.7	620.3
45°	553.3	558.5	560.4	562.1	567.4	569.1	569.1	574.5
47.5°	504.0	507.5	509.2	512.7	516.3	519.8	523.3	521.5
50°	454.6	459.9	463.4	465.2	470.5	472.2	474.0	475.7
52.5°	410.6	414.1	415.8	417.6	422.9	424.7	426.4	429.9
55°	368.3	370.0	373.5	371.8	377.1	378.9	380.6	384.1
57.5°	326.0	327.7	329.5	329.5	333.0	336.5	338.3	340.0
60°	285.5	289.0	290.7	290.7	290.7	294.2	294.2	294.2
62.5°	248.5	248.5	250.2	250.2	253.7	253.7	253.7	253.7
65°	209.7	211.4	213.3	213.3	216.8	215.0	218.5	216.8
67.5°	169.2	169.2	172.7	172.7	170.9	172.7	172.7	172.7
70°	128.6	128.6	130.4	130.4	130.4	130.4	130.4	130.4
72.5°	95.1	95.1	95.1	96.9	95.1	95.1	96.9	95.1
75°	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0
77.5°	58.1	58.1	59.9	59.9	59.9	59.9	59.9	59.9
80°	47.6	47.6	47.6	47.6	49.3	47.6	47.6	47.6
82.5°	35.2	33.5	35.2	33.5	35.2	35.2	35.2	35.2
85°	21.2	21.2	21.2	21.2	21.2	21.2	21.2	21.2
87.5°	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)