

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584232

Luminaire Tested: **HCC8W25D010MW-HM82555940-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584232  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W25D010MW-HM82555940-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2195.4 lumens  
Efficiency: N/A  
Efficacy: 81.9 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584232  
CATALOG NUMBER: HCC8W25D010MW-HM82555940-81WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P584232

CATALOG NUMBER: HCC8W25D010MW-HM82555940-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	36344	36344	36344
5°	37848	36263	34737
10°	39112	35802	33044
15°	40103	34982	31327
20°	40179	33531	29773
25°	39502	31411	28233
30°	37387	28980	26908
35°	34087	26065	25267
40°	29643	22977	23331
45°	25433	19894	21355
50°	21722	17155	19189
55°	19037	14779	16671
60°	16954	12606	14018
65°	15038	10281	11178
70°	13344	7618	6356
75°	11128	3991	1882
80°	8755	1261	302
85°	6262	601	0



TEST NUMBER: P584232  
 CATALOG NUMBER: HCC8W25D010MW-HM82555940-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.1	5.1
10°-20°	311.3	14.2
20°-30°	440.6	20.1
30°-40°	460.9	21.0
40°-50°	384.4	17.5
50°-60°	272.6	12.4
60°-70°	157.0	7.2
70°-80°	50.5	2.3
80°-90°	6.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.9	39.3
0°-40°	1323.8	60.3
0°-60°	1980.9	90.2
0°-90°	2195.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2195.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1179	1179	1179	1179	1179	
5°	1223	1207	1172	1136	1122	117
15°	1256	1205	1096	1009	981	353
25°	1161	1075	923	849	830	530
35°	906	826	692	655	671	561
45°	583	536	456	462	490	452
55°	354	317	275	289	310	320
65°	206	173	141	141	153	206
75°	93	69	34	16	16	101
85°	18	9	2	0	0	22
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584232

CATALOG NUMBER: HCC8W25D010MW-HM82555940-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6
2.5°	1203.3	1201.5	1199.8	1201.5	1199.8	1201.5	1199.8	1199.8	1198.0	1196.3	1196.3
5°	1222.7	1220.9	1220.9	1220.9	1219.2	1217.3	1217.3	1215.6	1212.1	1210.3	1206.9
7.5°	1235.0	1236.7	1236.7	1236.7	1233.3	1233.3	1229.8	1226.2	1222.7	1219.2	1213.8
10°	1249.1	1249.1	1247.3	1245.6	1242.1	1240.2	1238.5	1235.0	1229.8	1222.7	1217.3
12.5°	1254.4	1254.4	1252.6	1249.1	1247.3	1245.6	1243.8	1238.5	1231.5	1222.7	1215.6
15°	1256.2	1252.6	1250.8	1249.1	1245.6	1240.2	1240.2	1233.3	1224.4	1213.8	1205.0
17.5°	1242.1	1243.8	1240.2	1236.7	1231.5	1227.9	1222.7	1217.3	1206.9	1194.4	1185.7
20°	1224.4	1222.7	1220.9	1215.6	1208.6	1206.9	1201.5	1192.7	1183.8	1169.8	1157.5
22.5°	1196.3	1194.4	1190.9	1187.4	1180.4	1176.9	1171.5	1161.0	1148.6	1134.5	1120.5
25°	1161.0	1157.5	1152.2	1145.1	1139.9	1136.3	1129.3	1118.7	1104.7	1088.7	1074.7
27.5°	1104.7	1109.9	1106.4	1095.8	1090.5	1083.5	1081.8	1067.6	1055.3	1039.4	1023.6
30°	1050.0	1050.0	1044.7	1039.4	1030.6	1025.4	1018.3	1007.7	995.4	976.1	963.6
32.5°	981.3	979.6	972.5	970.7	963.6	953.2	951.3	937.2	924.9	910.8	894.9
35°	905.5	902.0	894.9	889.7	886.2	880.9	875.6	863.3	851.0	836.8	826.3
37.5°	819.2	819.2	817.5	808.6	805.2	801.6	796.3	784.0	776.9	762.8	752.3
40°	736.4	734.7	729.4	727.6	724.1	718.8	715.3	708.2	697.6	687.0	676.6
42.5°	655.4	657.1	650.1	651.8	644.8	641.3	639.5	628.9	623.7	613.1	604.3
45°	583.2	581.3	577.9	576.1	572.6	569.0	565.5	560.3	551.5	540.9	535.5
47.5°	516.2	510.9	510.9	509.1	507.4	500.3	498.6	493.3	488.0	477.4	470.4
50°	452.8	452.8	452.8	451.0	445.8	443.9	440.4	435.2	429.8	422.9	412.3
52.5°	401.7	401.7	401.7	400.0	392.9	391.1	389.4	382.3	375.2	370.0	362.9
55°	354.1	355.9	354.1	350.6	345.3	345.3	340.0	336.5	329.5	324.2	317.1
57.5°	313.6	313.6	310.1	308.3	304.7	303.0	299.5	296.0	287.2	281.8	273.1
60°	274.9	273.1	273.1	269.5	266.0	262.5	260.8	255.4	251.9	243.1	236.0
62.5°	239.6	239.6	236.0	236.0	229.0	229.0	227.3	222.0	216.7	207.9	204.4
65°	206.1	206.1	204.4	202.6	197.3	195.6	193.8	188.5	183.2	177.9	172.7
67.5°	176.2	176.2	172.7	170.9	167.3	165.6	162.1	158.6	153.2	148.0	142.7
70°	148.0	146.3	144.5	142.7	139.2	137.4	133.9	130.3	125.1	121.6	116.3
72.5°	119.8	119.8	118.0	114.5	112.8	111.0	109.2	105.7	100.5	95.1	91.6
75°	93.4	93.4	93.4	89.9	86.3	84.5	84.5	81.0	77.5	72.2	68.7
77.5°	72.2	70.5	68.7	68.7	65.2	63.5	61.6	59.9	54.6	52.9	49.3
80°	49.3	51.0	49.3	47.6	45.8	44.1	44.1	40.6	38.7	35.2	31.7
82.5°	33.5	31.7	31.7	30.0	30.0	28.1	28.1	24.7	22.9	21.2	19.4
85°	17.7	17.7	15.8	15.8	15.8	14.1	14.1	12.3	12.3	10.6	8.8
87.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584232

CATALOG NUMBER: HCC8W25D010MW-HM82555940-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6
2.5°	1194.4	1190.9	1189.2	1189.2	1187.4	1185.7	1183.8	1182.1	1178.6	1178.6	1175.1
5°	1203.3	1199.8	1198.0	1192.7	1189.2	1189.2	1182.1	1180.4	1175.1	1171.5	1168.0
7.5°	1210.3	1203.3	1198.0	1192.7	1189.2	1185.7	1178.6	1171.5	1164.5	1157.5	1154.0
10°	1210.3	1203.3	1194.4	1185.7	1182.1	1178.6	1169.8	1159.2	1150.5	1143.4	1134.5
12.5°	1206.9	1196.3	1185.7	1178.6	1171.5	1166.3	1155.7	1145.1	1134.5	1120.5	1113.4
15°	1196.3	1182.1	1171.5	1159.2	1154.0	1145.1	1136.3	1120.5	1108.1	1095.8	1087.0
17.5°	1175.1	1157.5	1145.1	1132.8	1124.0	1118.7	1104.7	1090.5	1076.4	1062.3	1051.8
20°	1143.4	1127.6	1113.4	1097.6	1090.5	1083.5	1065.8	1051.8	1037.7	1021.8	1011.3
22.5°	1104.7	1088.7	1069.4	1057.1	1046.5	1037.7	1021.8	1006.0	991.9	977.8	963.6
25°	1057.1	1041.2	1023.6	1004.2	997.1	988.4	970.7	954.9	939.0	923.2	910.8
27.5°	1006.0	984.8	970.7	949.6	942.6	933.7	914.3	896.8	882.6	870.3	856.2
30°	944.3	928.4	909.1	889.7	882.6	873.9	857.9	842.1	828.1	813.9	799.8
32.5°	877.4	861.5	842.1	828.1	817.5	810.4	794.6	780.5	766.3	752.3	739.9
35°	806.9	789.2	775.2	761.1	752.3	743.4	727.6	715.3	704.7	692.4	680.0
37.5°	734.7	722.4	708.2	692.4	683.5	676.6	664.1	650.1	641.3	630.7	621.9
40°	664.1	650.1	637.7	623.7	616.6	611.3	599.0	588.4	579.6	570.8	565.5
42.5°	591.9	579.6	567.3	558.4	553.2	547.9	539.1	526.8	521.5	512.6	507.4
45°	525.0	514.5	505.6	493.3	489.7	486.2	475.7	466.8	461.6	456.2	452.8
47.5°	461.6	454.5	443.9	436.9	431.6	428.1	421.0	414.0	408.7	405.2	401.7
50°	406.9	398.1	391.1	384.0	380.5	375.2	368.2	364.7	361.1	357.6	357.6
52.5°	355.9	347.1	340.0	334.7	331.2	327.6	322.4	320.7	317.1	317.1	315.3
55°	308.3	303.0	296.0	288.9	287.2	285.4	281.8	278.3	276.6	274.9	276.6
57.5°	267.8	262.5	255.4	250.2	248.5	246.6	244.9	241.4	239.6	239.6	239.6
60°	230.8	225.6	220.2	215.0	215.0	211.4	209.6	207.9	206.1	204.4	204.4
62.5°	197.3	192.1	186.7	183.2	181.5	179.7	176.2	174.4	172.7	172.7	170.9
65°	167.3	160.3	158.6	153.2	151.5	149.8	148.0	144.5	142.7	140.9	139.2
67.5°	137.4	133.9	128.6	125.1	123.4	121.6	119.8	116.3	114.5	112.8	109.2
70°	111.0	107.4	103.9	100.5	98.7	96.9	93.4	89.9	88.1	84.5	79.3
72.5°	86.3	82.8	79.3	75.8	74.0	72.2	68.7	65.2	61.6	58.1	54.6
75°	65.2	61.6	56.4	52.9	51.0	51.0	45.8	42.3	38.7	33.5	30.0
77.5°	45.8	40.6	38.7	35.2	33.5	30.0	26.4	22.9	19.4	17.7	14.1
80°	30.0	26.4	22.9	21.2	19.4	17.7	15.8	12.3	8.8	7.1	5.2
82.5°	17.7	15.8	14.1	12.3	10.6	8.8	7.1	7.1	5.2	3.5	1.7
85°	8.8	7.1	5.2	5.2	3.5	3.5	3.5	1.7	1.7	1.7	1.7
87.5°	3.5	1.7	1.7	1.7	1.7	1.7	1.7	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584232

CATALOG NUMBER: HCC8W25D010MW-HM82555940-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6
2.5°	1173.4	1171.5	1169.8	1168.0	1168.0	1164.5	1164.5	1162.8	1159.2	1157.5	1157.5
5°	1162.8	1157.5	1154.0	1152.2	1150.5	1145.1	1143.4	1139.9	1136.3	1132.8	1131.1
7.5°	1146.9	1138.1	1134.5	1132.8	1127.6	1122.2	1118.7	1113.4	1108.1	1102.8	1101.1
10°	1127.6	1118.7	1109.9	1106.4	1101.1	1097.6	1090.5	1083.5	1078.2	1072.9	1067.6
12.5°	1102.8	1092.3	1083.5	1080.0	1074.7	1067.6	1057.1	1053.5	1044.7	1041.2	1034.2
15°	1074.7	1062.3	1053.5	1048.3	1042.9	1032.3	1025.4	1018.3	1009.4	1006.0	999.0
17.5°	1039.4	1025.4	1016.5	1011.3	1007.7	999.0	988.4	979.6	970.7	967.2	961.9
20°	997.1	988.4	976.1	970.7	967.2	956.7	946.1	942.6	935.5	928.4	923.2
22.5°	949.6	940.7	928.4	923.2	921.4	912.6	903.8	898.5	893.2	887.9	882.6
25°	900.3	889.7	879.1	875.6	872.0	865.0	857.9	854.5	849.2	845.6	842.1
27.5°	847.4	836.8	828.1	822.7	819.2	813.9	810.4	806.9	803.4	799.8	798.1
30°	791.1	780.5	773.4	769.9	766.3	764.6	759.3	757.6	755.7	752.3	754.0
32.5°	734.7	725.9	718.8	713.5	713.5	709.9	708.2	708.2	706.4	706.4	706.4
35°	673.0	667.7	662.4	660.6	658.9	657.1	655.4	657.1	655.4	657.1	658.9
37.5°	616.6	611.3	607.8	606.0	604.3	606.0	604.3	604.3	606.0	609.6	611.3
40°	558.4	554.9	551.5	553.2	551.5	551.5	551.5	556.7	558.4	560.3	562.0
42.5°	503.9	500.3	498.6	498.6	500.3	498.6	502.2	503.9	507.4	512.6	516.2
45°	451.0	449.3	449.3	451.0	449.3	452.8	452.8	456.2	461.6	465.1	468.7
47.5°	401.7	401.7	401.7	403.4	403.4	405.2	408.7	410.5	414.0	417.5	421.0
50°	355.9	357.6	359.4	359.4	359.4	362.9	366.5	368.2	370.0	371.7	377.1
52.5°	315.3	317.1	317.1	318.9	320.7	322.4	324.2	327.6	329.5	333.0	334.7
55°	276.6	276.6	280.1	281.8	281.8	281.8	285.4	285.4	288.9	290.7	294.2
57.5°	239.6	241.4	241.4	243.1	243.1	244.9	246.6	248.5	250.2	251.9	253.7
60°	204.4	204.4	204.4	206.1	207.9	209.6	207.9	211.4	211.4	215.0	216.7
62.5°	170.9	172.7	172.7	172.7	172.7	172.7	172.7	174.4	176.2	177.9	179.7
65°	139.2	139.2	139.2	137.4	139.2	137.4	139.2	140.9	140.9	142.7	144.5
67.5°	107.4	107.4	103.9	103.9	105.7	105.7	105.7	105.7	103.9	107.4	107.4
70°	77.5	75.8	74.0	72.2	72.2	70.5	70.5	68.7	68.7	68.7	68.7
72.5°	51.0	47.6	44.1	42.3	40.6	40.6	37.0	35.2	37.0	37.0	37.0
75°	26.4	22.9	21.2	19.4	17.7	17.7	15.8	15.8	15.8	15.8	15.8
77.5°	10.6	8.8	7.1	7.1	5.2	5.2	5.2	5.2	5.2	5.2	5.2
80°	3.5	3.5	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	1.7	0.0	0.0	1.7	0.0	1.7	1.7	1.7	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584232

CATALOG NUMBER: HCC8W25D010MW-HM82555940-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6	1178.6
2.5°	1155.7	1155.7	1154.0	1155.7	1152.2	1154.0	1152.2	1152.2
5°	1129.3	1125.7	1125.7	1125.7	1124.0	1124.0	1122.2	1122.2
7.5°	1097.6	1095.8	1094.1	1092.3	1090.5	1088.7	1088.7	1088.7
10°	1065.8	1062.3	1062.3	1060.6	1057.1	1055.3	1055.3	1055.3
12.5°	1028.9	1027.1	1025.4	1025.4	1018.3	1020.0	1018.3	1018.3
15°	993.6	991.9	991.9	986.5	983.0	983.0	983.0	981.3
17.5°	956.7	954.9	953.2	949.6	946.1	946.1	944.3	946.1
20°	917.8	916.1	912.6	912.6	910.8	909.1	905.5	907.3
22.5°	879.1	875.6	873.9	873.9	872.0	872.0	868.5	868.5
25°	838.6	836.8	835.0	836.8	833.3	833.3	829.8	829.8
27.5°	796.3	794.6	794.6	794.6	792.8	794.6	792.8	792.8
30°	754.0	754.0	752.3	752.3	754.0	752.3	754.0	755.7
32.5°	708.2	708.2	709.9	709.9	711.8	711.8	711.8	711.8
35°	660.6	664.1	664.1	666.0	667.7	669.5	669.5	671.2
37.5°	616.6	618.4	620.2	621.9	625.4	625.4	625.4	625.4
40°	569.0	570.8	574.4	572.6	579.6	581.3	579.6	579.6
42.5°	519.7	523.2	525.0	528.6	530.3	533.8	535.5	535.5
45°	473.9	475.7	479.1	482.7	484.5	489.7	489.7	489.7
47.5°	426.4	429.8	431.6	435.2	436.9	442.2	443.9	442.2
50°	380.5	384.0	387.6	387.6	392.9	394.6	398.1	400.0
52.5°	336.5	338.2	341.8	343.6	347.1	350.6	352.4	354.1
55°	294.2	296.0	299.5	299.5	304.7	306.6	310.1	310.1
57.5°	255.4	257.2	260.8	258.9	262.5	266.0	266.0	264.3
60°	218.5	218.5	218.5	222.0	223.7	225.6	227.3	227.3
62.5°	179.7	183.2	185.0	185.0	186.7	188.5	188.5	186.7
65°	144.5	148.0	149.8	149.8	151.5	151.5	151.5	153.2
67.5°	109.2	109.2	109.2	111.0	109.2	109.2	109.2	109.2
70°	68.7	68.7	68.7	68.7	67.0	68.7	68.7	70.5
72.5°	37.0	37.0	37.0	37.0	37.0	37.0	37.0	37.0
75°	15.8	15.8	15.8	17.7	15.8	15.8	15.8	15.8
77.5°	7.1	5.2	7.1	7.1	5.2	5.2	5.2	5.2
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	0.0	1.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)