

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584284

Luminaire Tested: **HCC8S30D010SL-HM82555835-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584284
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010SL-HM82555835-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3127.8 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584284
CATALOG NUMBER: HCC8S30D010SL-HM82555835-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584284

CATALOG NUMBER: HCC8S30D010SL-HM82555835-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66																			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51																			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41																			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38																			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34																			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52261	52261	52261
5°	54098	51963	49898
10°	55297	51051	47093
15°	56087	49332	43975
20°	55917	46939	40826
25°	54534	43895	37478
30°	51669	40367	34389
35°	47006	36534	31252
40°	41284	32493	28234
45°	35999	28581	25167
50°	31331	25042	22173
55°	27940	22010	19284
60°	25384	19285	16448
65°	22816	16782	14929
70°	20313	14299	13479
75°	17812	12057	11497
80°	15112	9802	10211
85°	11393	7324	8102



TEST NUMBER: P584284
 CATALOG NUMBER: HCC8S30D010SL-HM82555835-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	5.1
10°-20°	437.4	14.0
20°-30°	607.1	19.4
30°-40°	627.7	20.1
40°-50°	525.6	16.8
50°-60°	381.5	12.2
60°-70°	240.8	7.7
70°-80°	119.3	3.8
80°-90°	29.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1203.3	38.5
0°-40°	1831.0	58.5
0°-60°	2738.1	87.5
0°-90°	3127.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3127.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1695	1695	1695	1695	1695	
5°	1748	1727	1679	1633	1612	167
15°	1757	1690	1545	1421	1378	494
25°	1603	1499	1290	1150	1102	734
35°	1249	1157	970	860	830	778
45°	826	766	655	591	577	639
55°	520	474	409	375	359	469
65°	313	274	230	202	205	312
75°	150	124	101	96	96	160
85°	32	25	21	23	23	39
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584284

CATALOG NUMBER: HCC8S30D010SL-HM82555835-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1722.4	1722.4	1724.6	1722.4	1722.4	1722.4	1720.1	1720.1	1717.7	1717.7	1713.2
5°	1747.7	1743.1	1747.7	1743.1	1743.1	1743.1	1740.8	1736.2	1733.9	1729.3	1727.0
7.5°	1759.1	1756.9	1756.9	1754.6	1754.6	1752.2	1750.0	1747.7	1738.4	1736.2	1729.3
10°	1766.0	1763.8	1763.8	1761.5	1756.9	1756.9	1752.2	1750.0	1738.4	1733.9	1724.6
12.5°	1763.8	1763.8	1763.8	1761.5	1754.6	1752.2	1747.7	1740.8	1731.5	1722.4	1713.2
15°	1756.9	1756.9	1752.2	1750.0	1743.1	1738.4	1736.2	1724.6	1715.5	1704.0	1690.2
17.5°	1733.9	1733.9	1731.5	1727.0	1720.1	1715.5	1710.9	1699.4	1690.2	1671.9	1657.9
20°	1704.0	1701.7	1699.4	1692.5	1685.6	1683.3	1676.4	1660.3	1648.8	1635.0	1616.6
22.5°	1660.3	1657.9	1655.7	1651.0	1639.6	1635.0	1630.4	1618.9	1598.3	1584.5	1561.4
25°	1602.8	1602.8	1598.3	1591.4	1579.8	1575.2	1568.3	1556.8	1538.4	1517.8	1499.3
27.5°	1536.1	1533.8	1526.9	1522.3	1513.1	1506.2	1494.7	1480.9	1462.6	1446.4	1423.5
30°	1451.1	1451.1	1446.4	1439.5	1428.0	1423.5	1414.2	1398.1	1379.7	1359.0	1343.0
32.5°	1354.5	1354.5	1347.6	1343.0	1336.1	1324.5	1322.3	1303.9	1287.8	1271.6	1253.3
35°	1248.7	1250.9	1246.4	1237.2	1225.6	1225.6	1221.1	1204.9	1186.6	1170.5	1156.7
37.5°	1142.9	1136.0	1133.7	1129.1	1122.2	1113.0	1108.4	1101.5	1085.4	1073.9	1053.2
40°	1025.6	1027.9	1023.4	1018.7	1016.4	1009.5	1007.2	995.7	984.3	970.5	961.2
42.5°	919.8	919.8	919.8	915.3	910.7	903.8	901.4	894.5	880.7	871.5	857.7
45°	825.5	818.6	818.6	816.4	814.1	809.5	802.6	797.9	788.8	781.9	765.7
47.5°	733.6	735.9	733.6	731.2	724.3	722.1	719.8	710.5	701.4	694.5	683.0
50°	653.1	657.6	653.1	653.1	648.5	646.2	641.6	634.7	627.8	616.3	604.8
52.5°	586.4	586.4	584.0	581.8	574.9	570.2	568.0	565.7	554.2	545.0	535.8
55°	519.7	522.0	522.0	515.1	512.8	508.2	505.9	499.0	494.4	480.6	473.7
57.5°	462.2	459.9	462.2	457.6	453.0	448.4	446.1	441.5	434.6	425.4	416.3
60°	411.6	407.0	407.0	404.7	400.1	397.8	393.2	386.3	379.4	370.3	363.4
62.5°	361.0	358.7	356.5	354.1	349.6	347.2	344.9	338.0	331.1	324.2	317.3
65°	312.7	312.7	310.4	305.8	303.6	301.3	298.9	294.4	285.1	280.6	273.7
67.5°	269.1	266.7	266.7	262.2	257.5	255.3	255.3	250.6	243.7	236.8	232.2
70°	225.3	227.7	225.3	223.1	218.4	218.4	213.9	211.5	202.4	200.1	193.2
72.5°	186.3	186.3	183.9	183.9	179.4	177.0	177.0	172.5	167.9	163.2	158.6
75°	149.5	149.5	149.5	147.2	144.8	140.3	140.3	137.9	133.4	128.8	124.1
77.5°	117.2	115.0	115.0	112.7	110.3	108.1	108.1	105.8	101.2	98.9	94.3
80°	85.1	82.8	82.8	82.8	78.2	80.5	78.2	75.9	73.6	71.3	69.0
82.5°	55.2	57.5	57.5	55.2	52.9	52.9	52.9	50.5	50.5	48.3	46.0
85°	32.2	32.2	32.2	32.2	29.8	29.8	29.8	27.6	27.6	27.6	25.3
87.5°	13.8	13.8	13.8	13.8	13.8	13.8	11.5	11.5	11.5	11.5	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584284

CATALOG NUMBER: HCC8S30D010SL-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1713.2	1708.6	1706.3	1704.0	1704.0	1701.7	1699.4	1694.8	1694.8	1690.2	1687.9
5°	1722.4	1715.5	1710.9	1706.3	1704.0	1699.4	1694.8	1687.9	1685.6	1678.7	1671.9
7.5°	1724.6	1713.2	1708.6	1699.4	1694.8	1690.2	1681.0	1674.1	1664.8	1657.9	1648.8
10°	1715.5	1706.3	1694.8	1683.3	1681.0	1674.1	1660.3	1651.0	1639.6	1630.4	1616.6
12.5°	1701.7	1687.9	1676.4	1662.6	1655.7	1648.8	1635.0	1621.2	1605.2	1589.0	1575.2
15°	1678.7	1662.6	1646.5	1630.4	1621.2	1614.3	1598.3	1582.1	1566.0	1545.3	1531.6
17.5°	1644.1	1625.8	1609.7	1589.0	1579.8	1572.9	1552.2	1533.8	1513.1	1492.4	1478.6
20°	1600.5	1577.6	1559.1	1536.1	1529.2	1517.8	1497.1	1476.4	1453.3	1430.4	1414.2
22.5°	1543.0	1520.0	1499.3	1476.4	1464.8	1453.3	1432.6	1407.3	1384.4	1365.9	1349.9
25°	1476.4	1455.7	1430.4	1409.7	1395.9	1382.1	1359.0	1338.3	1317.6	1290.1	1274.0
27.5°	1402.8	1377.5	1359.0	1331.4	1317.6	1308.5	1283.2	1255.6	1237.2	1211.8	1193.5
30°	1319.9	1297.0	1276.3	1248.7	1234.9	1225.6	1202.7	1177.3	1159.0	1133.7	1115.3
32.5°	1232.5	1207.3	1182.0	1163.6	1147.5	1138.3	1113.0	1096.9	1073.9	1053.2	1032.5
35°	1138.3	1113.0	1094.6	1069.3	1060.1	1051.0	1030.3	1009.5	988.8	970.5	954.3
37.5°	1037.2	1018.7	998.0	979.6	972.7	963.6	938.2	919.8	903.8	885.3	871.5
40°	938.2	922.2	908.3	890.0	878.4	871.5	853.1	837.1	818.6	807.2	793.3
42.5°	848.6	830.2	816.4	802.6	791.0	784.1	768.1	756.6	742.8	731.2	715.2
45°	754.3	745.0	729.0	717.4	710.5	701.4	689.9	676.1	664.5	655.4	643.8
47.5°	671.4	662.3	650.7	636.9	632.4	625.5	614.0	604.8	595.6	586.4	574.9
50°	595.6	584.0	574.9	565.7	561.1	554.2	542.7	538.1	531.2	522.0	515.1
52.5°	526.6	517.5	508.2	496.8	494.4	489.9	482.9	473.7	466.8	462.2	457.6
55°	464.5	455.3	448.4	439.2	437.0	432.3	423.2	418.5	413.9	409.4	404.7
57.5°	409.4	400.1	390.9	386.3	381.8	377.2	374.8	367.9	363.4	361.0	356.5
60°	358.7	349.6	342.7	335.8	333.4	331.1	326.5	322.0	317.3	312.7	310.4
62.5°	310.4	301.3	296.7	292.0	287.5	287.5	282.9	278.2	273.7	271.3	266.7
65°	266.7	262.2	255.3	248.4	246.0	246.0	239.1	236.8	234.6	230.0	225.3
67.5°	225.3	220.8	213.9	211.5	209.3	207.0	204.6	200.1	195.5	193.2	188.6
70°	188.6	183.9	179.4	177.0	174.8	172.5	167.9	165.6	161.0	158.6	156.4
72.5°	151.7	149.5	144.8	142.6	140.3	137.9	135.7	133.4	128.8	126.5	124.1
75°	121.9	119.6	115.0	112.7	110.3	110.3	108.1	103.4	101.2	101.2	98.9
77.5°	92.0	89.7	87.4	85.1	82.8	82.8	80.5	78.2	75.9	75.9	73.6
80°	66.7	64.4	62.1	62.1	62.1	59.8	57.5	57.5	55.2	55.2	52.9
82.5°	43.6	43.6	41.4	41.4	41.4	39.1	39.1	36.7	36.7	36.7	36.7
85°	25.3	25.3	25.3	22.9	22.9	22.9	22.9	22.9	22.9	20.7	22.9
87.5°	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584284

CATALOG NUMBER: HCC8S30D010SL-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1685.6	1683.3	1678.7	1678.7	1674.1	1674.1	1671.9	1669.5	1667.2	1664.8	1662.6
5°	1669.5	1660.3	1655.7	1653.4	1648.8	1646.5	1639.6	1635.0	1632.7	1628.1	1623.5
7.5°	1639.6	1630.4	1621.2	1618.9	1616.6	1607.4	1600.5	1593.6	1589.0	1584.5	1579.8
10°	1605.2	1595.9	1584.5	1579.8	1575.2	1563.8	1554.5	1547.6	1538.4	1529.2	1526.9
12.5°	1563.8	1549.9	1536.1	1531.6	1524.7	1513.1	1504.0	1492.4	1485.5	1474.0	1471.7
15°	1515.4	1499.3	1487.8	1476.4	1471.7	1460.2	1444.2	1434.9	1421.1	1416.6	1405.0
17.5°	1458.0	1441.8	1425.7	1421.1	1414.2	1398.1	1382.1	1370.6	1356.8	1349.9	1343.0
20°	1398.1	1377.5	1361.4	1356.8	1347.6	1333.7	1317.6	1306.1	1294.7	1280.9	1274.0
22.5°	1329.2	1306.1	1292.3	1280.9	1278.5	1262.5	1244.1	1234.9	1225.6	1214.2	1204.9
25°	1253.3	1232.5	1216.5	1207.3	1202.7	1188.9	1175.1	1163.6	1149.8	1142.9	1131.5
27.5°	1175.1	1161.3	1140.6	1131.5	1124.4	1113.0	1096.9	1090.0	1076.2	1067.0	1060.1
30°	1099.2	1078.5	1067.0	1055.5	1048.6	1037.2	1023.4	1016.4	1004.9	995.7	988.8
32.5°	1016.4	1002.6	986.5	981.9	972.7	961.2	952.0	940.5	931.3	922.2	919.8
35°	940.5	922.2	906.0	901.4	894.5	883.1	878.4	871.5	860.0	857.7	848.6
37.5°	857.7	848.6	830.2	823.3	821.0	811.7	802.6	797.9	791.0	784.1	781.9
40°	779.5	768.1	758.8	751.9	747.4	740.5	731.2	729.0	724.3	715.2	712.9
42.5°	706.0	694.5	685.2	683.0	676.1	669.2	664.5	657.6	655.4	653.1	648.5
45°	634.7	627.8	618.6	616.3	614.0	604.8	600.2	595.6	590.9	588.7	584.0
47.5°	570.2	563.3	556.5	554.2	549.6	547.3	540.4	538.1	531.2	528.9	526.6
50°	508.2	503.7	499.0	496.8	492.1	489.9	485.2	480.6	476.0	473.7	471.4
52.5°	453.0	448.4	443.9	441.5	439.2	434.6	430.1	425.4	423.2	420.8	418.5
55°	400.1	395.6	393.2	390.9	388.7	386.3	379.4	377.2	374.8	372.5	367.9
57.5°	351.8	347.2	342.7	342.7	340.3	338.0	333.4	328.9	328.9	324.2	319.6
60°	308.2	303.6	298.9	296.7	294.4	289.8	287.5	285.1	282.9	280.6	276.0
62.5°	262.2	259.8	255.3	255.3	250.6	248.4	246.0	243.7	241.5	236.8	234.6
65°	223.1	220.8	216.2	213.9	213.9	211.5	207.0	204.6	202.4	202.4	200.1
67.5°	186.3	183.9	179.4	177.0	177.0	174.8	172.5	172.5	170.1	167.9	170.1
70°	154.1	149.5	149.5	147.2	147.2	144.8	142.6	142.6	142.6	144.8	144.8
72.5°	121.9	119.6	117.2	117.2	117.2	117.2	115.0	115.0	117.2	119.6	119.6
75°	96.5	94.3	94.3	94.3	92.0	92.0	94.3	94.3	96.5	96.5	96.5
77.5°	71.3	71.3	71.3	71.3	71.3	71.3	73.6	73.6	75.9	75.9	75.9
80°	52.9	52.9	52.9	52.9	52.9	55.2	55.2	55.2	55.2	55.2	57.5
82.5°	36.7	36.7	36.7	36.7	36.7	36.7	36.7	39.1	39.1	39.1	39.1
85°	20.7	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584284

CATALOG NUMBER: HCC8S30D010SL-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1660.3	1660.3	1660.3	1662.6	1657.9	1657.9	1657.9	1657.9
5°	1621.2	1618.9	1616.6	1618.9	1614.3	1614.3	1612.0	1612.0
7.5°	1572.9	1570.7	1568.3	1568.3	1563.8	1563.8	1561.4	1559.1
10°	1520.0	1515.4	1517.8	1513.1	1510.9	1508.5	1506.2	1504.0
12.5°	1462.6	1458.0	1455.7	1451.1	1446.4	1444.2	1446.4	1441.8
15°	1400.4	1393.5	1391.2	1386.6	1382.1	1379.7	1379.7	1377.5
17.5°	1331.4	1326.8	1324.5	1319.9	1317.6	1313.0	1310.8	1308.5
20°	1267.1	1255.6	1257.8	1253.3	1250.9	1241.8	1241.8	1244.1
22.5°	1195.8	1188.9	1184.2	1179.7	1177.3	1172.8	1172.8	1170.5
25°	1124.4	1117.5	1115.3	1110.6	1108.4	1103.7	1101.5	1101.5
27.5°	1055.5	1046.3	1046.3	1041.7	1037.2	1034.8	1032.5	1030.3
30°	981.9	975.0	972.7	972.7	970.5	970.5	963.6	965.8
32.5°	912.9	908.3	906.0	901.4	901.4	899.1	899.1	892.2
35°	844.0	837.1	839.3	834.8	832.4	830.2	832.4	830.2
37.5°	777.2	772.6	772.6	768.1	768.1	765.7	763.5	768.1
40°	710.5	708.3	706.0	703.7	706.0	703.7	699.1	701.4
42.5°	643.8	643.8	641.6	641.6	639.3	639.3	639.3	639.3
45°	584.0	581.8	581.8	579.5	579.5	579.5	579.5	577.1
47.5°	524.3	522.0	522.0	522.0	519.7	519.7	517.5	519.7
50°	466.8	466.8	464.5	464.5	466.8	464.5	462.2	462.2
52.5°	413.9	413.9	411.6	411.6	409.4	407.0	409.4	409.4
55°	365.6	363.4	361.0	361.0	358.7	356.5	356.5	358.7
57.5°	319.6	317.3	315.1	315.1	310.4	308.2	308.2	308.2
60°	276.0	271.3	271.3	269.1	269.1	266.7	266.7	266.7
62.5°	234.6	232.2	232.2	232.2	232.2	230.0	230.0	230.0
65°	200.1	200.1	200.1	202.4	202.4	204.6	204.6	204.6
67.5°	172.5	174.8	174.8	174.8	177.0	177.0	177.0	174.8
70°	147.2	147.2	147.2	149.5	149.5	149.5	149.5	149.5
72.5°	121.9	121.9	121.9	121.9	121.9	121.9	121.9	121.9
75°	96.5	98.9	98.9	98.9	96.5	98.9	98.9	96.5
77.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9
80°	57.5	57.5	57.5	57.5	57.5	57.5	57.5	57.5
82.5°	39.1	39.1	39.1	39.1	39.1	39.1	39.1	39.1
85°	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)