

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584335

Luminaire Tested: **HCC8S30D010SL-HM82555930-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584335  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S30D010SL-HM82555930-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2901.2 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584335  
CATALOG NUMBER: HCC8S30D010SL-HM82555930-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584335

CATALOG NUMBER: HCC8S30D010SL-HM82555930-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	48475	48475	48475
5°	50180	48199	46286
10°	51292	47353	43677
15°	52024	45757	40789
20°	51865	43536	37866
25°	50584	40713	34762
30°	47923	37444	31900
35°	43599	33884	28986
40°	38294	30138	26189
45°	33392	26510	23348
50°	29062	23228	20571
55°	25913	20408	17892
60°	23547	17891	15258
65°	21167	15563	13856
70°	18843	13271	12496
75°	16513	11176	10663
80°	14011	9092	9465
85°	10543	6758	7536



TEST NUMBER: P584335

CATALOG NUMBER: HCC8S30D010SL-HM82555930-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.2	5.1
10°-20°	405.7	14.0
20°-30°	563.1	19.4
30°-40°	582.2	20.1
40°-50°	487.5	16.8
50°-60°	353.9	12.2
60°-70°	223.3	7.7
70°-80°	110.6	3.8
80°-90°	27.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1116.1	38.5
0°-40°	1698.3	58.5
0°-60°	2539.8	87.5
0°-90°	2901.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2901.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1572	1572	1572	1572	1572	
5°	1621	1602	1557	1514	1495	155
15°	1630	1568	1433	1318	1278	459
25°	1487	1391	1197	1066	1022	681
35°	1158	1073	900	798	770	721
45°	766	710	608	548	535	592
55°	482	440	380	348	333	435
65°	290	254	213	188	190	289
75°	139	115	94	90	90	149
85°	30	23	19	21	21	36
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584335

CATALOG NUMBER: HCC8S30D010SL-HM82555930-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0
2.5°	1597.7	1597.7	1599.8	1597.7	1597.7	1597.7	1595.5	1595.5	1593.4	1593.4	1589.1
5°	1621.1	1616.8	1621.1	1616.8	1616.8	1616.8	1614.7	1610.4	1608.2	1604.0	1601.9
7.5°	1631.8	1629.6	1629.6	1627.5	1627.5	1625.4	1623.2	1621.1	1612.5	1610.4	1604.0
10°	1638.1	1636.1	1636.1	1633.9	1629.6	1629.6	1625.4	1623.2	1612.5	1608.2	1599.8
12.5°	1636.1	1636.1	1636.1	1633.9	1627.5	1625.4	1621.1	1614.7	1606.1	1597.7	1589.1
15°	1629.6	1629.6	1625.4	1623.2	1616.8	1612.5	1610.4	1599.8	1591.2	1580.5	1567.7
17.5°	1608.2	1608.2	1606.1	1601.9	1595.5	1591.2	1587.0	1576.3	1567.7	1550.7	1537.9
20°	1580.5	1578.4	1576.3	1569.8	1563.5	1561.4	1555.0	1540.0	1529.4	1516.6	1499.4
22.5°	1540.0	1537.9	1535.7	1531.6	1520.8	1516.6	1512.3	1501.6	1482.4	1469.6	1448.3
25°	1486.7	1486.7	1482.4	1476.0	1465.3	1461.2	1454.7	1444.0	1426.9	1407.8	1390.8
27.5°	1424.9	1422.8	1416.3	1412.1	1403.5	1397.1	1386.5	1373.7	1356.5	1341.7	1320.4
30°	1345.9	1345.9	1341.7	1335.2	1324.5	1320.4	1311.8	1296.8	1279.8	1260.6	1245.7
32.5°	1256.3	1256.3	1250.0	1245.7	1239.3	1228.6	1226.5	1209.5	1194.5	1179.6	1162.5
35°	1158.2	1160.3	1156.1	1147.5	1136.9	1136.9	1132.6	1117.7	1100.7	1085.7	1073.0
37.5°	1060.1	1053.7	1051.6	1047.3	1040.9	1032.4	1028.1	1021.7	1006.7	996.1	976.9
40°	951.3	953.5	949.2	944.9	942.8	936.3	934.2	923.6	912.9	900.1	891.6
42.5°	853.2	853.2	853.2	848.9	844.7	838.2	836.1	829.7	817.0	808.4	795.6
45°	765.7	759.3	759.3	757.3	755.1	750.9	744.4	740.2	731.6	725.2	710.3
47.5°	680.5	682.6	680.5	678.3	671.9	669.8	667.6	659.1	650.6	644.2	633.5
50°	605.8	610.1	605.8	605.8	601.5	599.4	595.1	588.7	582.3	571.7	561.0
52.5°	544.0	544.0	541.8	539.7	533.3	529.0	526.8	524.7	514.0	505.6	497.0
55°	482.0	484.2	484.2	477.7	475.6	471.4	469.3	462.9	458.6	445.8	439.5
57.5°	428.8	426.6	428.8	424.5	420.2	415.9	413.8	409.5	403.2	394.6	386.1
60°	381.8	377.5	377.5	375.4	371.1	369.1	364.8	358.4	351.9	343.4	337.0
62.5°	334.8	332.8	330.7	328.5	324.2	322.1	320.0	313.5	307.1	300.7	294.4
65°	290.1	290.1	288.0	283.7	281.6	279.4	277.3	273.0	264.4	260.3	253.9
67.5°	249.6	247.4	247.4	243.2	238.9	236.7	236.7	232.4	226.1	219.7	215.4
70°	209.0	211.2	209.0	206.9	202.6	202.6	198.3	196.2	187.7	185.6	179.2
72.5°	172.8	172.8	170.6	170.6	166.3	164.2	164.2	159.9	155.8	151.5	147.2
75°	138.6	138.6	138.6	136.5	134.4	130.1	130.1	127.9	123.7	119.5	115.2
77.5°	108.8	106.7	106.7	104.5	102.4	100.2	100.2	98.1	93.8	91.7	87.5
80°	78.9	76.8	76.8	76.8	72.5	74.7	72.5	70.4	68.2	66.1	64.0
82.5°	51.2	53.3	53.3	51.2	49.1	49.1	49.1	47.0	47.0	44.8	42.7
85°	29.8	29.8	29.8	29.8	27.7	27.7	27.7	25.6	25.6	25.6	23.4
87.5°	12.8	12.8	12.8	12.8	12.8	12.8	10.7	10.7	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584335

CATALOG NUMBER: HCC8S30D010SL-HM82555930-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0
2.5°	1589.1	1584.8	1582.7	1580.5	1580.5	1578.4	1576.3	1572.0	1572.0	1567.7	1565.7
5°	1597.7	1591.2	1587.0	1582.7	1580.5	1576.3	1572.0	1565.7	1563.5	1557.1	1550.7
7.5°	1599.8	1589.1	1584.8	1576.3	1572.0	1567.7	1559.3	1552.8	1544.3	1537.9	1529.4
10°	1591.2	1582.7	1572.0	1561.4	1559.3	1552.8	1540.0	1531.6	1520.8	1512.3	1499.4
12.5°	1578.4	1565.7	1555.0	1542.1	1535.7	1529.4	1516.6	1503.7	1488.9	1473.9	1461.2
15°	1557.1	1542.1	1527.3	1512.3	1503.7	1497.3	1482.4	1467.5	1452.6	1433.3	1420.6
17.5°	1525.1	1508.0	1493.1	1473.9	1465.3	1459.0	1439.8	1422.8	1403.5	1384.4	1371.5
20°	1484.6	1463.2	1446.2	1424.9	1418.5	1407.8	1388.6	1369.4	1348.1	1326.7	1311.8
22.5°	1431.2	1409.9	1390.8	1369.4	1358.7	1348.1	1328.8	1305.4	1284.1	1267.0	1252.0
25°	1369.4	1350.2	1326.7	1307.5	1294.7	1282.0	1260.6	1241.4	1222.2	1196.6	1181.6
27.5°	1301.1	1277.7	1260.6	1235.0	1222.2	1213.7	1190.2	1164.6	1147.5	1124.1	1107.1
30°	1224.3	1203.0	1183.8	1158.2	1145.4	1136.9	1115.5	1092.1	1075.0	1051.6	1034.5
32.5°	1143.3	1119.8	1096.4	1079.3	1064.4	1055.8	1032.4	1017.4	996.1	976.9	957.7
35°	1055.8	1032.4	1015.3	991.9	983.3	974.7	955.6	936.3	917.2	900.1	885.2
37.5°	962.0	944.9	925.8	908.6	902.2	893.8	870.2	853.2	838.2	821.2	808.4
40°	870.2	855.4	842.5	825.5	814.8	808.4	791.4	776.4	759.3	748.7	735.9
42.5°	787.1	770.0	757.3	744.4	733.7	727.3	712.4	701.7	688.9	678.3	663.3
45°	699.6	691.0	676.2	665.5	659.1	650.6	639.9	627.1	616.5	607.9	597.2
47.5°	622.8	614.4	603.7	590.8	586.5	580.2	569.5	561.0	552.4	544.0	533.3
50°	552.4	541.8	533.3	524.7	520.4	514.0	503.4	499.1	492.7	484.2	477.7
52.5°	488.4	479.9	471.4	460.7	458.6	454.3	447.9	439.5	433.0	428.8	424.5
55°	430.9	422.3	415.9	407.4	405.2	401.0	392.5	388.2	383.9	379.6	375.4
57.5°	379.6	371.1	362.6	358.4	354.1	349.8	347.7	341.2	337.0	334.8	330.7
60°	332.8	324.2	317.8	311.4	309.3	307.1	302.8	298.7	294.4	290.1	288.0
62.5°	288.0	279.4	275.1	270.9	266.6	266.6	262.4	258.1	253.9	251.7	247.4
65°	247.4	243.2	236.7	230.3	228.3	228.3	221.9	219.7	217.6	213.3	209.0
67.5°	209.0	204.7	198.3	196.2	194.0	192.0	189.9	185.6	181.3	179.2	174.9
70°	174.9	170.6	166.3	164.2	162.1	159.9	155.8	153.6	149.3	147.2	145.1
72.5°	140.8	138.6	134.4	132.2	130.1	127.9	125.8	123.7	119.5	117.4	115.2
75°	113.1	110.9	106.7	104.5	102.4	102.4	100.2	96.0	93.8	93.8	91.7
77.5°	85.4	83.2	81.1	78.9	76.8	76.8	74.7	72.5	70.4	70.4	68.2
80°	61.8	59.7	57.5	57.5	57.5	55.4	53.3	53.3	51.2	51.2	49.1
82.5°	40.5	40.5	38.4	38.4	38.4	36.3	36.3	34.1	34.1	34.1	34.1
85°	23.4	23.4	23.4	21.3	21.3	21.3	21.3	21.3	21.3	19.1	21.3
87.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584335

CATALOG NUMBER: HCC8S30D010SL-HM82555930-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0
2.5°	1563.5	1561.4	1557.1	1557.1	1552.8	1552.8	1550.7	1548.6	1546.4	1544.3	1542.1
5°	1548.6	1540.0	1535.7	1533.6	1529.4	1527.3	1520.8	1516.6	1514.4	1510.1	1505.9
7.5°	1520.8	1512.3	1503.7	1501.6	1499.4	1491.0	1484.6	1478.2	1473.9	1469.6	1465.3
10°	1488.9	1480.3	1469.6	1465.3	1461.2	1450.5	1441.9	1435.5	1426.9	1418.5	1416.3
12.5°	1450.5	1437.6	1424.9	1420.6	1414.2	1403.5	1394.9	1384.4	1377.9	1367.2	1365.1
15°	1405.6	1390.8	1380.1	1369.4	1365.1	1354.5	1339.5	1331.0	1318.2	1314.0	1303.3
17.5°	1352.4	1337.4	1322.4	1318.2	1311.8	1296.8	1282.0	1271.3	1258.4	1252.0	1245.7
20°	1296.8	1277.7	1262.7	1258.4	1250.0	1237.2	1222.2	1211.6	1200.9	1188.0	1181.6
22.5°	1232.9	1211.6	1198.7	1188.0	1185.9	1171.0	1153.9	1145.4	1136.9	1126.2	1117.7
25°	1162.5	1143.3	1128.4	1119.8	1115.5	1102.8	1090.0	1079.3	1066.5	1060.1	1049.4
27.5°	1090.0	1077.1	1058.0	1049.4	1043.0	1032.4	1017.4	1011.0	998.3	989.7	983.3
30°	1019.6	1000.4	989.7	979.0	972.6	962.0	949.2	942.8	932.2	923.6	917.2
32.5°	942.8	930.0	915.1	910.8	902.2	891.6	883.1	872.4	863.8	855.4	853.2
35°	872.4	855.4	840.4	836.1	829.7	819.1	814.8	808.4	797.7	795.6	787.1
37.5°	795.6	787.1	770.0	763.6	761.4	753.0	744.4	740.2	733.7	727.3	725.2
40°	723.0	712.4	703.9	697.5	693.2	686.9	678.3	676.2	671.9	663.3	661.2
42.5°	654.8	644.2	635.6	633.5	627.1	620.7	616.5	610.1	607.9	605.8	601.5
45°	588.7	582.3	573.8	571.7	569.5	561.0	556.7	552.4	548.1	546.0	541.8
47.5°	529.0	522.6	516.1	514.0	509.8	507.7	501.3	499.1	492.7	490.6	488.4
50°	471.4	467.2	462.9	460.7	456.5	454.3	450.0	445.8	441.5	439.5	437.3
52.5°	420.2	415.9	411.6	409.5	407.4	403.2	398.9	394.6	392.5	390.3	388.2
55°	371.1	366.9	364.8	362.6	360.5	358.4	351.9	349.8	347.7	345.5	341.2
57.5°	326.4	322.1	317.8	317.8	315.7	313.5	309.3	305.0	305.0	300.7	296.5
60°	285.8	281.6	277.3	275.1	273.0	268.7	266.6	264.4	262.4	260.3	256.0
62.5°	243.2	241.0	236.7	236.7	232.4	230.3	228.3	226.1	224.0	219.7	217.6
65°	206.9	204.7	200.5	198.3	198.3	196.2	192.0	189.9	187.7	187.7	185.6
67.5°	172.8	170.6	166.3	164.2	164.2	162.1	159.9	159.9	157.9	155.8	157.9
70°	142.9	138.6	138.6	136.5	136.5	134.4	132.2	132.2	132.2	134.4	134.4
72.5°	113.1	110.9	108.8	108.8	108.8	108.8	106.7	106.7	108.8	110.9	110.9
75°	89.5	87.5	87.5	87.5	85.4	85.4	87.5	87.5	89.5	89.5	89.5
77.5°	66.1	66.1	66.1	66.1	66.1	66.1	68.2	68.2	70.4	70.4	70.4
80°	49.1	49.1	49.1	49.1	49.1	51.2	51.2	51.2	51.2	51.2	53.3
82.5°	34.1	34.1	34.1	34.1	34.1	34.1	34.1	36.3	36.3	36.3	36.3
85°	19.1	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584335

CATALOG NUMBER: HCC8S30D010SL-HM82555930-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0
2.5°	1540.0	1540.0	1540.0	1542.1	1537.9	1537.9	1537.9	1537.9
5°	1503.7	1501.6	1499.4	1501.6	1497.3	1497.3	1495.3	1495.3
7.5°	1459.0	1456.9	1454.7	1454.7	1450.5	1450.5	1448.3	1446.2
10°	1409.9	1405.6	1407.8	1403.5	1401.4	1399.2	1397.1	1394.9
12.5°	1356.5	1352.4	1350.2	1345.9	1341.7	1339.5	1341.7	1337.4
15°	1299.0	1292.6	1290.4	1286.1	1282.0	1279.8	1279.8	1277.7
17.5°	1235.0	1230.7	1228.6	1224.3	1222.2	1217.9	1215.8	1213.7
20°	1175.3	1164.6	1166.8	1162.5	1160.3	1151.8	1151.8	1153.9
22.5°	1109.2	1102.8	1098.5	1094.2	1092.1	1087.8	1087.8	1085.7
25°	1043.0	1036.7	1034.5	1030.3	1028.1	1023.8	1021.7	1021.7
27.5°	979.0	970.5	970.5	966.3	962.0	959.9	957.7	955.6
30°	910.8	904.4	902.2	902.2	900.1	900.1	893.8	895.9
32.5°	846.8	842.5	840.4	836.1	836.1	834.0	834.0	827.7
35°	782.8	776.4	778.6	774.3	772.1	770.0	772.1	770.0
37.5°	721.0	716.7	716.7	712.4	712.4	710.3	708.2	712.4
40°	659.1	656.9	654.8	652.6	654.8	652.6	648.5	650.6
42.5°	597.2	597.2	595.1	595.1	593.0	593.0	593.0	593.0
45°	541.8	539.7	539.7	537.5	537.5	537.5	537.5	535.4
47.5°	486.3	484.2	484.2	484.2	482.0	482.0	479.9	482.0
50°	433.0	433.0	430.9	430.9	433.0	430.9	428.8	428.8
52.5°	383.9	383.9	381.8	381.8	379.6	377.5	379.6	379.6
55°	339.1	337.0	334.8	334.8	332.8	330.7	330.7	332.8
57.5°	296.5	294.4	292.3	292.3	288.0	285.8	285.8	285.8
60°	256.0	251.7	251.7	249.6	249.6	247.4	247.4	247.4
62.5°	217.6	215.4	215.4	215.4	215.4	213.3	213.3	213.3
65°	185.6	185.6	185.6	187.7	187.7	189.9	189.9	189.9
67.5°	159.9	162.1	162.1	162.1	164.2	164.2	164.2	162.1
70°	136.5	136.5	136.5	138.6	138.6	138.6	138.6	138.6
72.5°	113.1	113.1	113.1	113.1	113.1	113.1	113.1	113.1
75°	89.5	91.7	91.7	91.7	89.5	91.7	91.7	89.5
77.5°	70.4	70.4	70.4	70.4	70.4	70.4	70.4	70.4
80°	53.3	53.3	53.3	53.3	53.3	53.3	53.3	53.3
82.5°	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3
85°	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)