

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584454

Luminaire Tested: **HCC8S35D010SL-HM82555927-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584454  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S35D010SL-HM82555927-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2927.9 lumens  
Efficiency: N/A  
Efficacy: 86.9 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584454  
CATALOG NUMBER: HCC8S35D010SL-HM82555927-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584454

CATALOG NUMBER: HCC8S35D010SL-HM82555927-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	48922	48922	48922
5°	50641	48641	46710
10°	51765	47792	44081
15°	52502	46181	41163
20°	52344	43936	38217
25°	51050	41088	35082
30°	48365	37786	32192
35°	44002	34196	29253
40°	38648	30416	26427
45°	33701	26754	23562
50°	29326	23444	20758
55°	26155	20596	18053
60°	23762	18058	15400
65°	21364	15709	13980
70°	19024	13398	12613
75°	16668	11295	10770
80°	14153	9163	9554
85°	10685	6864	7642



TEST NUMBER: P584454  
 CATALOG NUMBER: HCC8S35D010SL-HM82555927-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.6	5.1
10°-20°	409.4	14.0
20°-30°	568.3	19.4
30°-40°	587.6	20.1
40°-50°	492.0	16.8
50°-60°	357.2	12.2
60°-70°	225.4	7.7
70°-80°	111.6	3.8
80°-90°	27.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1126.4	38.5
0°-40°	1714.0	58.5
0°-60°	2563.1	87.5
0°-90°	2927.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2927.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1586	1586	1586	1586	1586	
5°	1636	1617	1571	1528	1509	156
15°	1645	1582	1447	1330	1289	463
25°	1500	1404	1208	1076	1031	688
35°	1169	1083	908	805	777	728
45°	773	717	614	553	540	598
55°	486	444	383	351	336	439
65°	293	256	215	189	192	292
75°	140	116	95	90	90	150
85°	30	24	19	22	22	37
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584454

CATALOG NUMBER: HCC8S35D010SL-HM82555927-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5
2.5°	1612.3	1612.3	1614.4	1612.3	1612.3	1612.3	1610.1	1610.1	1608.0	1608.0	1603.8
5°	1636.0	1631.7	1636.0	1631.7	1631.7	1631.7	1629.5	1625.2	1623.1	1618.7	1616.6
7.5°	1646.8	1644.6	1644.6	1642.5	1642.5	1640.3	1638.1	1636.0	1627.4	1625.2	1618.7
10°	1653.2	1651.1	1651.1	1648.9	1644.6	1644.6	1640.3	1638.1	1627.4	1623.1	1614.4
12.5°	1651.1	1651.1	1651.1	1648.9	1642.5	1640.3	1636.0	1629.5	1620.9	1612.3	1603.8
15°	1644.6	1644.6	1640.3	1638.1	1631.7	1627.4	1625.2	1614.4	1605.8	1595.1	1582.2
17.5°	1623.1	1623.1	1620.9	1616.6	1610.1	1605.8	1601.6	1590.8	1582.2	1564.9	1552.0
20°	1595.1	1593.0	1590.8	1584.4	1577.9	1575.7	1569.3	1554.2	1543.4	1530.6	1513.3
22.5°	1554.2	1552.0	1549.9	1545.5	1534.9	1530.6	1526.3	1515.5	1496.1	1483.1	1461.7
25°	1500.4	1500.4	1496.1	1489.6	1478.8	1474.5	1468.0	1457.4	1440.1	1420.7	1403.5
27.5°	1438.0	1435.8	1429.3	1425.0	1416.4	1409.9	1399.3	1386.3	1369.1	1354.0	1332.4
30°	1358.3	1358.3	1354.0	1347.5	1336.7	1332.4	1323.9	1308.8	1291.6	1272.2	1257.2
32.5°	1267.8	1267.8	1261.5	1257.2	1250.7	1239.9	1237.8	1220.5	1205.4	1190.5	1173.2
35°	1168.9	1171.0	1166.7	1158.1	1147.3	1147.3	1143.0	1127.9	1110.8	1095.7	1082.8
37.5°	1069.8	1063.3	1061.2	1057.0	1050.5	1041.9	1037.6	1031.1	1016.0	1005.2	986.0
40°	960.1	962.2	957.9	953.6	951.5	945.0	942.8	932.0	921.4	908.4	899.8
42.5°	861.0	861.0	861.0	856.7	852.5	846.0	843.9	837.4	824.5	815.8	802.9
45°	772.8	766.4	766.4	764.2	762.0	757.7	751.3	747.0	738.3	731.9	716.9
47.5°	686.7	688.8	686.7	684.5	678.1	675.9	673.8	665.1	656.5	650.0	639.4
50°	611.3	615.7	611.3	611.3	607.0	604.9	600.6	594.1	587.6	577.0	566.2
52.5°	548.9	548.9	546.8	544.6	538.1	533.8	531.7	529.5	518.7	510.2	501.6
55°	486.5	488.7	488.7	482.2	480.0	475.7	473.6	467.1	462.8	449.8	443.5
57.5°	432.7	430.6	432.7	428.4	424.1	419.8	417.6	413.3	406.8	398.2	389.6
60°	385.3	381.0	381.0	378.8	374.6	372.5	368.1	361.7	355.2	346.6	340.1
62.5°	338.0	335.8	333.6	331.5	327.2	325.0	322.9	316.4	309.9	303.6	297.1
65°	292.8	292.8	290.6	286.3	284.2	282.0	279.9	275.5	266.9	262.6	256.1
67.5°	251.8	249.7	249.7	245.4	241.0	239.0	239.0	234.7	228.2	221.7	217.4
70°	211.0	213.1	211.0	208.8	204.5	204.5	200.2	198.0	189.4	187.2	180.8
72.5°	174.3	174.3	172.2	172.2	168.0	165.8	165.8	161.5	157.2	152.9	148.6
75°	139.9	139.9	139.9	137.8	135.6	131.3	131.3	129.1	124.8	120.5	116.2
77.5°	109.7	107.6	107.6	105.4	103.3	101.2	101.2	99.1	94.8	92.6	88.3
80°	79.7	77.5	77.5	77.5	73.2	75.4	73.2	71.0	68.9	66.7	64.6
82.5°	51.6	53.8	53.8	51.6	49.5	49.5	49.5	47.3	47.3	45.2	43.0
85°	30.2	30.2	30.2	30.2	28.0	28.0	28.0	25.9	25.9	25.9	23.7
87.5°	12.9	12.9	12.9	12.9	12.9	12.9	10.8	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584454

CATALOG NUMBER: HCC8S35D010SL-HM82555927-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5
2.5°	1603.8	1599.4	1597.3	1595.1	1595.1	1593.0	1590.8	1586.5	1586.5	1582.2	1580.0
5°	1612.3	1605.8	1601.6	1597.3	1595.1	1590.8	1586.5	1580.0	1577.9	1571.4	1564.9
7.5°	1614.4	1603.8	1599.4	1590.8	1586.5	1582.2	1573.6	1567.1	1558.5	1552.0	1543.4
10°	1605.8	1597.3	1586.5	1575.7	1573.6	1567.1	1554.2	1545.5	1534.9	1526.3	1513.3
12.5°	1593.0	1580.0	1569.3	1556.3	1549.9	1543.4	1530.6	1517.6	1502.5	1487.4	1474.5
15°	1571.4	1556.3	1541.2	1526.3	1517.6	1511.2	1496.1	1481.0	1466.0	1446.6	1433.6
17.5°	1539.1	1521.9	1506.8	1487.4	1478.8	1472.3	1453.1	1435.8	1416.4	1397.1	1384.2
20°	1498.2	1476.7	1459.5	1438.0	1431.5	1420.7	1401.3	1382.0	1360.4	1338.9	1323.9
22.5°	1444.4	1422.9	1403.5	1382.0	1371.2	1360.4	1341.0	1317.4	1295.9	1278.6	1263.5
25°	1382.0	1362.6	1338.9	1319.6	1306.7	1293.7	1272.2	1252.9	1233.5	1207.6	1192.6
27.5°	1313.1	1289.4	1272.2	1246.4	1233.5	1224.8	1201.1	1175.4	1158.1	1134.4	1117.3
30°	1235.6	1214.1	1194.8	1168.9	1156.0	1147.3	1125.9	1102.2	1084.9	1061.2	1044.1
32.5°	1153.8	1130.1	1106.5	1089.2	1074.1	1065.5	1041.9	1026.8	1005.2	986.0	966.5
35°	1065.5	1041.9	1024.6	1000.9	992.3	983.8	964.4	945.0	925.6	908.4	893.3
37.5°	970.9	953.6	934.2	917.1	910.6	902.0	878.3	861.0	846.0	828.8	815.8
40°	878.3	863.2	850.3	833.1	822.3	815.8	798.6	783.6	766.4	755.6	742.6
42.5°	794.3	777.1	764.2	751.3	740.5	734.0	718.9	708.3	695.3	684.5	669.4
45°	706.1	697.5	682.4	671.6	665.1	656.5	645.8	632.9	622.1	613.5	602.7
47.5°	628.6	620.0	609.2	596.2	591.9	585.5	574.8	566.2	557.5	548.9	538.1
50°	557.5	546.8	538.1	529.5	525.2	518.7	508.1	503.8	497.3	488.7	482.2
52.5°	493.0	484.4	475.7	464.9	462.8	458.5	452.0	443.5	437.0	432.7	428.4
55°	434.9	426.2	419.8	411.2	409.0	404.7	396.1	391.7	387.4	383.1	378.8
57.5°	383.1	374.6	366.0	361.7	357.4	353.1	350.9	344.4	340.1	338.0	333.6
60°	335.8	327.2	320.7	314.2	312.1	309.9	305.7	301.4	297.1	292.8	290.6
62.5°	290.6	282.0	277.7	273.4	269.1	269.1	264.8	260.4	256.1	254.0	249.7
65°	249.7	245.4	239.0	232.5	230.4	230.4	223.9	221.7	219.6	215.3	211.0
67.5°	211.0	206.7	200.2	198.0	195.9	193.7	191.6	187.2	182.9	180.8	176.5
70°	176.5	172.2	168.0	165.8	163.6	161.5	157.2	155.0	150.7	148.6	146.4
72.5°	142.1	139.9	135.6	133.5	131.3	129.1	127.0	124.8	120.5	118.4	116.2
75°	114.0	111.9	107.6	105.4	103.3	103.3	101.2	96.9	94.8	94.8	92.6
77.5°	86.1	84.0	81.8	79.7	77.5	77.5	75.4	73.2	71.0	71.0	68.9
80°	62.4	60.3	58.1	58.1	58.1	55.9	53.8	53.8	51.6	51.6	49.5
82.5°	40.9	40.9	38.7	38.7	38.7	36.5	36.5	34.4	34.4	34.4	34.4
85°	23.7	23.7	23.7	21.6	21.6	21.6	21.6	21.6	21.6	19.4	21.6
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584454

CATALOG NUMBER: HCC8S35D010SL-HM82555927-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5
2.5°	1577.9	1575.7	1571.4	1571.4	1567.1	1567.1	1564.9	1562.8	1560.6	1558.5	1556.3
5°	1562.8	1554.2	1549.9	1547.7	1543.4	1541.2	1534.9	1530.6	1528.4	1524.1	1519.8
7.5°	1534.9	1526.3	1517.6	1515.5	1513.3	1504.7	1498.2	1491.7	1487.4	1483.1	1478.8
10°	1502.5	1493.9	1483.1	1478.8	1474.5	1463.8	1455.2	1448.7	1440.1	1431.5	1429.3
12.5°	1463.8	1450.9	1438.0	1433.6	1427.2	1416.4	1407.8	1397.1	1390.6	1379.9	1377.7
15°	1418.6	1403.5	1392.8	1382.0	1377.7	1366.9	1351.8	1343.2	1330.4	1326.1	1315.3
17.5°	1364.8	1349.7	1334.6	1330.4	1323.9	1308.8	1293.7	1282.9	1270.0	1263.5	1257.2
20°	1308.8	1289.4	1274.3	1270.0	1261.5	1248.6	1233.5	1222.7	1211.9	1199.0	1192.6
22.5°	1244.2	1222.7	1209.7	1199.0	1196.8	1181.8	1164.6	1156.0	1147.3	1136.5	1127.9
25°	1173.2	1153.8	1138.7	1130.1	1125.9	1112.9	1100.0	1089.2	1076.3	1069.8	1059.0
27.5°	1100.0	1087.1	1067.7	1059.0	1052.7	1041.9	1026.8	1020.3	1007.4	998.8	992.3
30°	1029.0	1009.6	998.8	988.1	981.6	970.9	957.9	951.5	940.7	932.0	925.6
32.5°	951.5	938.5	923.4	919.2	910.6	899.8	891.2	880.4	871.8	863.2	861.0
35°	880.4	863.2	848.2	843.9	837.4	826.6	822.3	815.8	805.1	802.9	794.3
37.5°	802.9	794.3	777.1	770.7	768.5	759.9	751.3	747.0	740.5	734.0	731.9
40°	729.7	718.9	710.4	703.9	699.6	693.2	684.5	682.4	678.1	669.4	667.3
42.5°	660.8	650.0	641.5	639.4	632.9	626.4	622.1	615.7	613.5	611.3	607.0
45°	594.1	587.6	579.1	577.0	574.8	566.2	561.9	557.5	553.2	551.1	546.8
47.5°	533.8	527.4	520.9	518.7	514.4	512.3	505.9	503.8	497.3	495.1	493.0
50°	475.7	471.4	467.1	464.9	460.6	458.5	454.2	449.8	445.5	443.5	441.3
52.5°	424.1	419.8	415.5	413.3	411.2	406.8	402.5	398.2	396.1	393.9	391.7
55°	374.6	370.3	368.1	366.0	363.8	361.7	355.2	353.1	350.9	348.7	344.4
57.5°	329.3	325.0	320.7	320.7	318.5	316.4	312.1	307.8	307.8	303.6	299.3
60°	288.5	284.2	279.9	277.7	275.5	271.2	269.1	266.9	264.8	262.6	258.3
62.5°	245.4	243.2	239.0	239.0	234.7	232.5	230.4	228.2	226.1	221.7	219.6
65°	208.8	206.7	202.3	200.2	200.2	198.0	193.7	191.6	189.4	189.4	187.2
67.5°	174.3	172.2	168.0	165.8	165.8	163.6	161.5	161.5	159.3	157.2	159.3
70°	144.2	139.9	139.9	137.8	137.8	135.6	133.5	133.5	133.5	135.6	135.6
72.5°	114.0	111.9	109.7	109.7	109.7	109.7	107.6	107.6	109.7	111.9	111.9
75°	90.4	88.3	88.3	88.3	86.1	86.1	88.3	88.3	90.4	90.4	90.4
77.5°	66.7	66.7	66.7	66.7	66.7	66.7	68.9	68.9	71.0	71.0	71.0
80°	49.5	49.5	49.5	49.5	49.5	51.6	51.6	51.6	51.6	51.6	53.8
82.5°	34.4	34.4	34.4	34.4	34.4	34.4	34.4	36.5	36.5	36.5	36.5
85°	19.4	21.6	21.6	21.6	21.6	21.6	21.6	21.6	21.6	21.6	21.6
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584454

CATALOG NUMBER: HCC8S35D010SL-HM82555927-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5	1586.5
2.5°	1554.2	1554.2	1554.2	1556.3	1552.0	1552.0	1552.0	1552.0
5°	1517.6	1515.5	1513.3	1515.5	1511.2	1511.2	1509.0	1509.0
7.5°	1472.3	1470.2	1468.0	1468.0	1463.8	1463.8	1461.7	1459.5
10°	1422.9	1418.6	1420.7	1416.4	1414.2	1412.1	1409.9	1407.8
12.5°	1369.1	1364.8	1362.6	1358.3	1354.0	1351.8	1354.0	1349.7
15°	1311.0	1304.5	1302.3	1298.0	1293.7	1291.6	1291.6	1289.4
17.5°	1246.4	1242.1	1239.9	1235.6	1233.5	1229.1	1227.0	1224.8
20°	1186.1	1175.4	1177.5	1173.2	1171.0	1162.4	1162.4	1164.6
22.5°	1119.4	1112.9	1108.6	1104.3	1102.2	1097.8	1097.8	1095.7
25°	1052.7	1046.2	1044.1	1039.7	1037.6	1033.3	1031.1	1031.1
27.5°	988.1	979.5	979.5	975.2	970.9	968.7	966.5	964.4
30°	919.2	912.8	910.6	910.6	908.4	908.4	902.0	904.1
32.5°	854.5	850.3	848.2	843.9	843.9	841.7	841.7	835.2
35°	790.0	783.6	785.6	781.5	779.3	777.1	779.3	777.1
37.5°	727.5	723.2	723.2	718.9	718.9	716.9	714.7	718.9
40°	665.1	663.0	660.8	658.7	660.8	658.7	654.3	656.5
42.5°	602.7	602.7	600.6	600.6	598.4	598.4	598.4	598.4
45°	546.8	544.6	544.6	542.5	542.5	542.5	542.5	540.3
47.5°	490.8	488.7	488.7	488.7	486.5	486.5	484.4	486.5
50°	437.0	437.0	434.9	434.9	437.0	434.9	432.7	432.7
52.5°	387.4	387.4	385.3	385.3	383.1	381.0	383.1	383.1
55°	342.3	340.1	338.0	338.0	335.8	333.6	333.6	335.8
57.5°	299.3	297.1	294.9	294.9	290.6	288.5	288.5	288.5
60°	258.3	254.0	254.0	251.8	251.8	249.7	249.7	249.7
62.5°	219.6	217.4	217.4	217.4	217.4	215.3	215.3	215.3
65°	187.2	187.2	187.2	189.4	189.4	191.6	191.6	191.6
67.5°	161.5	163.6	163.6	163.6	165.8	165.8	165.8	163.6
70°	137.8	137.8	137.8	139.9	139.9	139.9	139.9	139.9
72.5°	114.0	114.0	114.0	114.0	114.0	114.0	114.0	114.0
75°	90.4	92.6	92.6	92.6	90.4	92.6	92.6	90.4
77.5°	71.0	71.0	71.0	71.0	71.0	71.0	71.0	71.0
80°	53.8	53.8	53.8	53.8	53.8	53.8	53.8	53.8
82.5°	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5
85°	21.6	21.6	21.6	21.6	21.6	21.6	21.6	21.6
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)