

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584455

Luminaire Tested: **HCC8W35D010SL-HM82555927-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584455  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W35D010SL-HM82555927-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3048.5 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584455  
CATALOG NUMBER: HCC8W35D010SL-HM82555927-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584455

CATALOG NUMBER: HCC8W35D010SL-HM82555927-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	46739	46739	46739
5°	48449	46583	44986
10°	49821	46182	43145
15°	50932	45361	41240
20°	51011	43595	39565
25°	50032	41169	38165
30°	47453	38178	36493
35°	43118	34772	34851
40°	37702	31201	32847
45°	32672	27792	30609
50°	28611	24682	27887
55°	25467	21881	25236
60°	22973	19655	22171
65°	20737	17278	19328
70°	18636	14561	14362
75°	16418	11545	10770
80°	13762	9554	10317
85°	10685	8385	9164



TEST NUMBER: P584455  
 CATALOG NUMBER: HCC8W35D010SL-HM82555927-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.0	4.7
10°-20°	402.7	13.2
20°-30°	575.6	18.9
30°-40°	611.6	20.1
40°-50°	526.6	17.3
50°-60°	393.7	12.9
60°-70°	251.1	8.2
70°-80°	114.3	3.7
80°-90°	30.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1121.3	36.8
0°-40°	1732.9	56.8
0°-60°	2653.1	87.0
0°-90°	3048.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3048.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1516	1516	1516	1516	1516	
5°	1565	1544	1505	1466	1453	150
15°	1595	1542	1421	1324	1292	449
25°	1470	1378	1210	1137	1122	673
35°	1145	1066	924	900	926	713
45°	749	708	637	654	702	582
55°	474	435	407	441	469	426
65°	284	252	237	248	265	283
75°	138	118	97	88	90	146
85°	30	26	24	26	26	36
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584455

CATALOG NUMBER: HCC8W35D010SL-HM82555927-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7
2.5°	1543.7	1539.4	1541.6	1539.4	1541.6	1541.6	1537.3	1537.3	1537.3	1537.3	1530.8
5°	1565.2	1563.0	1563.0	1560.9	1558.7	1560.9	1558.7	1556.7	1552.4	1550.2	1543.7
7.5°	1578.1	1578.1	1578.1	1578.1	1576.0	1573.8	1571.7	1567.3	1563.0	1558.7	1554.5
10°	1591.1	1593.2	1591.1	1588.9	1586.8	1582.4	1580.3	1576.0	1569.5	1563.0	1558.7
12.5°	1597.5	1597.5	1595.4	1595.4	1591.1	1588.9	1582.4	1576.0	1569.5	1563.0	1552.4
15°	1595.4	1595.4	1593.2	1591.1	1584.6	1582.4	1578.1	1571.7	1560.9	1552.4	1541.6
17.5°	1582.4	1580.3	1576.0	1576.0	1567.3	1565.2	1560.9	1552.4	1541.6	1528.6	1515.7
20°	1554.5	1554.5	1552.4	1550.2	1541.6	1535.1	1530.8	1520.0	1511.4	1496.3	1483.4
22.5°	1515.7	1520.0	1515.7	1511.4	1500.6	1498.5	1492.0	1479.2	1466.2	1449.0	1433.9
25°	1470.5	1468.4	1466.2	1461.9	1453.3	1449.0	1440.4	1427.4	1414.5	1395.2	1377.9
27.5°	1412.3	1403.8	1403.8	1395.2	1388.7	1382.3	1377.9	1365.0	1347.8	1332.7	1311.2
30°	1332.7	1334.8	1324.1	1322.0	1311.2	1306.9	1298.3	1285.3	1270.2	1253.1	1235.9
32.5°	1246.6	1240.2	1240.2	1231.5	1222.9	1216.4	1214.3	1199.2	1186.3	1169.1	1151.9
35°	1145.4	1145.4	1138.9	1136.8	1128.2	1123.8	1117.4	1108.7	1093.8	1078.7	1065.7
37.5°	1046.3	1042.0	1039.9	1035.6	1029.1	1022.7	1022.7	1007.6	1005.5	988.2	971.0
40°	936.6	940.9	936.6	930.1	928.0	923.7	921.5	912.9	906.4	891.3	880.5
42.5°	844.0	839.7	839.7	837.5	828.9	828.9	824.6	820.3	809.5	805.2	792.4
45°	749.2	753.5	747.1	749.2	740.6	740.6	740.6	732.0	723.4	717.0	708.4
47.5°	667.4	669.6	669.6	663.1	660.9	660.9	656.6	652.3	646.0	637.3	630.9
50°	596.4	598.5	594.2	592.1	587.7	585.6	585.6	577.0	572.6	564.1	559.8
52.5°	531.8	531.8	529.6	529.6	523.2	523.2	518.9	512.4	508.1	503.8	493.1
55°	473.7	473.7	471.5	469.4	469.4	462.9	460.8	454.3	450.0	441.3	434.9
57.5°	417.7	419.8	417.7	415.6	413.4	411.3	407.0	400.5	396.2	389.7	385.4
60°	372.5	372.5	370.3	368.1	363.8	361.7	359.5	355.2	348.7	344.4	338.1
62.5°	329.4	327.3	325.1	323.0	318.7	318.7	314.4	310.0	303.6	299.3	294.9
65°	284.2	284.2	282.0	282.0	279.9	275.5	273.4	271.2	262.7	260.6	251.9
67.5°	243.3	245.5	241.2	241.2	236.8	236.8	234.7	228.2	226.1	221.7	217.4
70°	206.7	206.7	206.7	204.5	200.2	198.0	195.9	191.6	189.5	185.2	180.9
72.5°	170.1	170.1	168.0	168.0	165.8	163.6	161.5	157.2	157.2	152.9	148.6
75°	137.8	137.8	135.6	133.5	131.3	131.3	129.1	127.0	122.7	120.5	118.4
77.5°	105.5	105.5	105.5	103.4	101.2	101.2	101.2	96.9	92.6	92.6	90.4
80°	77.5	77.5	75.4	75.4	73.2	73.2	73.2	71.0	68.9	66.7	64.6
82.5°	51.6	51.6	51.6	51.6	49.5	49.5	49.5	47.3	45.2	45.2	45.2
85°	30.2	30.2	30.2	30.2	28.0	28.0	28.0	28.0	28.0	25.9	25.9
87.5°	12.9	10.8	12.9	10.8	12.9	10.8	12.9	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584455

CATALOG NUMBER: HCC8W35D010SL-HM82555927-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7
2.5°	1533.0	1530.8	1528.6	1526.5	1526.5	1524.3	1520.0	1517.9	1515.7	1513.6	1513.6
5°	1541.6	1539.4	1535.1	1530.8	1528.6	1524.3	1520.0	1515.7	1511.4	1504.9	1502.8
7.5°	1548.1	1541.6	1537.3	1528.6	1526.5	1522.2	1515.7	1509.2	1500.6	1492.0	1485.5
10°	1548.1	1539.4	1533.0	1522.2	1517.9	1513.6	1504.9	1494.1	1483.4	1474.9	1464.1
12.5°	1543.7	1533.0	1522.2	1511.4	1504.9	1498.5	1485.5	1474.9	1461.9	1449.0	1440.4
15°	1528.6	1515.7	1502.8	1489.8	1483.4	1474.9	1461.9	1446.8	1433.9	1420.9	1405.9
17.5°	1500.6	1487.7	1472.7	1457.6	1449.0	1442.5	1423.1	1412.3	1393.0	1380.1	1367.2
20°	1464.1	1449.0	1429.6	1414.5	1403.8	1397.3	1382.3	1362.8	1347.8	1328.5	1315.5
22.5°	1416.6	1397.3	1377.9	1362.8	1352.1	1343.4	1324.1	1304.7	1291.8	1274.6	1259.5
25°	1360.7	1341.3	1322.0	1300.4	1289.6	1281.0	1263.8	1246.6	1229.4	1210.0	1197.0
27.5°	1294.0	1272.4	1255.1	1235.9	1225.1	1212.1	1192.7	1175.6	1158.3	1145.4	1128.2
30°	1220.8	1197.0	1179.8	1160.5	1149.7	1138.9	1119.5	1102.3	1087.3	1072.2	1063.6
32.5°	1132.5	1115.2	1098.1	1078.7	1070.1	1063.6	1044.2	1026.9	1009.8	996.9	990.4
35°	1048.5	1029.1	1014.1	996.9	986.1	979.6	962.4	947.4	938.8	923.7	915.0
37.5°	960.2	945.2	928.0	910.7	904.3	897.8	884.8	869.9	856.9	846.1	841.8
40°	867.7	854.8	839.7	828.9	822.4	816.0	805.2	794.5	785.9	775.1	770.8
42.5°	779.4	770.8	757.9	744.9	738.4	736.3	723.4	714.8	710.5	706.2	701.9
45°	699.8	686.8	678.2	669.6	663.1	658.8	652.3	646.0	641.6	637.3	633.0
47.5°	622.2	611.5	602.8	596.4	589.9	587.7	583.4	577.0	572.6	572.6	572.6
50°	551.2	542.6	533.9	529.6	527.5	523.2	518.9	516.7	514.5	514.5	514.5
52.5°	488.8	480.2	473.7	469.4	469.4	465.1	460.8	458.6	458.6	458.6	458.6
55°	430.6	424.1	419.8	415.6	411.3	409.1	409.1	409.1	407.0	407.0	409.1
57.5°	378.9	374.6	368.1	363.8	361.7	361.7	359.5	357.4	359.5	361.7	363.8
60°	331.6	327.3	325.1	318.7	318.7	318.7	316.5	316.5	316.5	318.7	320.8
62.5°	288.5	286.3	282.0	279.9	277.7	277.7	275.5	275.5	275.5	275.5	277.7
65°	249.8	245.5	241.2	241.2	241.2	239.0	239.0	234.7	236.8	236.8	234.7
67.5°	213.1	208.8	206.7	204.5	202.3	202.3	200.2	198.0	195.9	195.9	195.9
70°	178.7	174.4	174.4	170.1	170.1	168.0	165.8	165.8	163.6	161.5	159.3
72.5°	144.2	142.1	139.9	137.8	137.8	137.8	135.6	133.5	131.3	129.1	124.8
75°	114.0	114.0	109.9	107.7	107.7	105.5	103.4	101.2	99.1	96.9	94.8
77.5°	88.3	86.1	81.8	79.7	79.7	79.7	77.5	75.4	73.2	71.0	68.9
80°	64.6	62.4	60.3	58.1	58.1	58.1	55.9	55.9	53.8	53.8	53.8
82.5°	43.0	43.0	40.9	40.9	40.9	40.9	38.7	38.7	38.7	38.7	38.7
85°	25.9	25.9	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584455

CATALOG NUMBER: HCC8W35D010SL-HM82555927-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7
2.5°	1509.2	1509.2	1504.9	1502.8	1500.6	1502.8	1498.5	1496.3	1494.1	1494.1	1492.0
5°	1496.3	1494.1	1485.5	1483.4	1481.3	1479.2	1474.9	1470.5	1466.2	1464.1	1461.9
7.5°	1479.2	1472.7	1464.1	1461.9	1459.8	1453.3	1446.8	1442.5	1436.0	1433.9	1429.6
10°	1455.5	1446.8	1440.4	1433.9	1429.6	1423.1	1416.6	1410.2	1401.7	1399.5	1393.0
12.5°	1427.4	1416.6	1403.8	1401.7	1395.2	1386.6	1377.9	1371.5	1365.0	1360.7	1354.2
15°	1393.0	1382.3	1369.3	1362.8	1356.4	1349.9	1339.1	1330.5	1324.1	1317.7	1311.2
17.5°	1352.1	1339.1	1328.5	1322.0	1317.7	1306.9	1298.3	1287.5	1281.0	1274.6	1268.1
20°	1302.6	1291.8	1276.7	1270.2	1268.1	1259.5	1248.8	1244.5	1235.9	1229.4	1225.1
22.5°	1246.6	1235.9	1222.9	1218.6	1210.0	1205.7	1194.9	1190.6	1186.3	1179.8	1177.8
25°	1184.1	1173.4	1162.7	1160.5	1154.0	1149.7	1143.3	1136.8	1136.8	1130.3	1130.3
27.5°	1119.5	1108.7	1100.2	1095.9	1093.8	1089.5	1083.0	1080.8	1078.7	1076.5	1076.5
30°	1050.6	1037.7	1033.4	1031.2	1029.1	1024.9	1022.7	1018.4	1020.6	1022.7	1020.6
32.5°	977.4	973.1	964.5	960.2	962.4	960.2	955.9	960.2	958.0	962.4	964.5
35°	906.4	902.1	897.8	897.8	893.5	893.5	893.5	895.6	899.9	902.1	906.4
37.5°	837.5	831.1	828.9	826.7	828.9	828.9	828.9	833.2	837.5	841.8	848.3
40°	764.3	760.0	760.0	760.0	760.0	766.5	764.3	768.6	772.9	779.4	785.9
42.5°	695.4	695.4	697.6	697.6	697.6	697.6	701.9	708.4	714.8	721.3	727.7
45°	630.9	630.9	630.9	635.2	635.2	637.3	646.0	650.2	654.5	660.9	667.4
47.5°	570.5	570.5	572.6	574.8	577.0	581.3	585.6	592.1	598.5	602.8	609.3
50°	514.5	516.7	521.0	525.3	525.3	527.5	533.9	538.3	542.6	549.0	551.2
52.5°	460.8	465.1	469.4	471.5	473.7	478.0	480.2	486.6	488.8	495.1	497.3
55°	411.3	413.4	419.8	421.9	421.9	426.2	430.6	434.9	441.3	441.3	445.7
57.5°	366.0	368.1	372.5	374.6	372.5	378.9	381.1	385.4	387.6	391.9	394.0
60°	320.8	325.1	327.3	327.3	329.4	331.6	335.9	335.9	340.2	344.4	344.4
62.5°	277.7	279.9	282.0	284.2	286.3	284.2	290.6	290.6	294.9	297.1	301.4
65°	236.8	239.0	239.0	241.2	241.2	243.3	243.3	245.5	247.6	251.9	254.1
67.5°	195.9	195.9	195.9	198.0	195.9	198.0	198.0	200.2	200.2	204.5	206.7
70°	159.3	157.2	155.0	155.0	155.0	155.0	152.9	155.0	155.0	157.2	157.2
72.5°	122.7	120.5	118.4	116.2	116.2	114.0	112.0	114.0	114.0	116.2	116.2
75°	92.6	88.3	88.3	88.3	86.1	86.1	86.1	88.3	88.3	88.3	90.4
77.5°	68.9	68.9	66.7	66.7	66.7	68.9	68.9	71.0	71.0	71.0	71.0
80°	51.6	53.8	53.8	53.8	53.8	55.9	55.9	55.9	55.9	58.1	58.1
82.5°	38.7	38.7	38.7	38.7	40.9	40.9	40.9	40.9	40.9	40.9	40.9
85°	23.7	25.9	25.9	23.7	25.9	25.9	25.9	25.9	25.9	25.9	25.9
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584455

CATALOG NUMBER: HCC8W35D010SL-HM82555927-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7	1515.7
2.5°	1489.8	1489.8	1489.8	1489.8	1487.7	1487.7	1487.7	1485.5
5°	1457.6	1457.6	1457.6	1453.3	1455.5	1455.5	1451.1	1453.3
7.5°	1425.3	1423.1	1420.9	1420.9	1418.8	1416.6	1414.5	1416.6
10°	1388.7	1382.3	1382.3	1380.1	1380.1	1375.8	1375.8	1377.9
12.5°	1347.8	1343.4	1343.4	1341.3	1339.1	1337.0	1334.8	1334.8
15°	1306.9	1302.6	1300.4	1298.3	1296.1	1291.8	1294.0	1291.8
17.5°	1265.9	1259.5	1259.5	1257.3	1255.1	1251.0	1251.0	1248.8
20°	1218.6	1216.4	1212.1	1214.3	1212.1	1207.8	1205.7	1205.7
22.5°	1171.3	1171.3	1169.1	1169.1	1167.0	1164.8	1162.7	1162.7
25°	1126.0	1123.8	1126.0	1126.0	1119.5	1119.5	1119.5	1121.7
27.5°	1074.4	1076.5	1074.4	1074.4	1074.4	1074.4	1076.5	1074.4
30°	1022.7	1022.7	1022.7	1024.9	1029.1	1026.9	1026.9	1024.9
32.5°	966.7	968.8	968.8	971.0	973.1	977.4	977.4	979.6
35°	910.7	915.0	917.2	915.0	921.5	921.5	925.8	925.8
37.5°	852.6	854.8	859.1	861.2	865.6	867.7	869.9	869.9
40°	790.2	798.7	800.9	803.0	809.5	809.5	811.6	816.0
42.5°	732.0	740.6	742.8	744.9	749.2	755.7	753.5	757.9
45°	676.0	682.5	684.7	686.8	693.3	695.4	695.4	701.9
47.5°	615.8	620.1	622.2	626.6	630.9	635.2	639.5	637.3
50°	555.5	562.0	566.3	568.5	574.8	577.0	579.1	581.3
52.5°	501.6	505.9	508.1	510.2	516.7	518.9	521.0	525.3
55°	450.0	452.1	456.4	454.3	460.8	462.9	465.1	469.4
57.5°	398.3	400.5	402.6	402.6	407.0	411.3	413.4	415.6
60°	348.7	353.1	355.2	355.2	355.2	359.5	359.5	359.5
62.5°	303.6	303.6	305.7	305.7	310.0	310.0	310.0	310.0
65°	256.3	258.4	260.6	260.6	264.9	262.7	266.9	264.9
67.5°	206.7	206.7	211.0	211.0	208.8	211.0	211.0	211.0
70°	157.2	157.2	159.3	159.3	159.3	159.3	159.3	159.3
72.5°	116.2	116.2	116.2	118.4	116.2	116.2	118.4	116.2
75°	90.4	90.4	90.4	90.4	90.4	90.4	90.4	90.4
77.5°	71.0	71.0	73.2	73.2	73.2	73.2	73.2	73.2
80°	58.1	58.1	58.1	58.1	60.3	58.1	58.1	58.1
82.5°	43.0	40.9	43.0	40.9	43.0	43.0	43.0	43.0
85°	25.9	25.9	25.9	25.9	25.9	25.9	25.9	25.9
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)