

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584555

Luminaire Tested: **HCC8S40D010MB-HM82555835-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584555  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S40D010MB-HM82555835-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3990.1 lumens  
Efficiency: N/A  
Efficacy: 97.3 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584555  
CATALOG NUMBER: HCC8S40D010MB-HM82555835-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584555

CATALOG NUMBER: HCC8S40D010MB-HM82555835-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	66054	66054	66054
5°	68786	65911	63137
10°	71085	65069	60053
15°	72883	63580	56937
20°	73024	60941	54112
25°	71794	57086	51312
30°	67952	52673	48909
35°	61955	47371	45926
40°	53876	41759	42404
45°	46217	36165	38816
50°	39477	31182	34871
55°	34601	26859	30300
60°	30812	22905	25471
65°	27333	18694	20328
70°	24244	13857	11540
75°	20218	7244	3431
80°	15911	2291	568
85°	11322	1132	0



TEST NUMBER: P584555  
 CATALOG NUMBER: HCC8S40D010MB-HM82555835-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	201.8	5.1
10°-20°	565.7	14.2
20°-30°	800.7	20.1
30°-40°	837.7	21.0
40°-50°	698.7	17.5
50°-60°	495.5	12.4
60°-70°	285.4	7.2
70°-80°	91.8	2.3
80°-90°	12.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1568.3	39.3
0°-40°	2406.0	60.3
0°-60°	3600.2	90.2
0°-90°	3990.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3990.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2142	2142	2142	2142	2142	
5°	2222	2193	2129	2065	2040	213
15°	2283	2190	1992	1835	1784	642
25°	2110	1953	1678	1543	1508	963
35°	1646	1502	1258	1191	1220	1020
45°	1060	973	829	839	890	821
55°	644	576	500	525	564	581
65°	375	314	256	256	279	374
75°	170	125	61	29	29	184
85°	32	16	3	0	0	40
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584555

CATALOG NUMBER: HCC8S40D010MB-HM82555835-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1
2.5°	2187.0	2183.8	2180.6	2183.8	2180.6	2183.8	2180.6	2180.6	2177.3	2174.1	2174.1
5°	2222.2	2219.0	2219.0	2219.0	2215.8	2212.6	2212.6	2209.4	2202.9	2199.7	2193.3
7.5°	2244.6	2247.8	2247.8	2247.8	2241.4	2241.4	2234.9	2228.5	2222.2	2215.8	2206.1
10°	2270.2	2270.2	2267.0	2263.7	2257.4	2254.2	2251.0	2244.6	2234.9	2222.2	2212.6
12.5°	2279.8	2279.8	2276.6	2270.2	2267.0	2263.7	2260.5	2251.0	2238.2	2222.2	2209.4
15°	2283.0	2276.6	2273.4	2270.2	2263.7	2254.2	2254.2	2241.4	2225.3	2206.1	2190.2
17.5°	2257.4	2260.5	2254.2	2247.8	2238.2	2231.7	2222.2	2212.6	2193.3	2170.9	2155.0
20°	2225.3	2222.2	2219.0	2209.4	2196.5	2193.3	2183.8	2167.7	2151.8	2126.1	2103.7
22.5°	2174.1	2170.9	2164.5	2158.1	2145.3	2138.9	2129.3	2110.1	2087.6	2062.0	2036.4
25°	2110.1	2103.7	2094.0	2081.3	2071.7	2065.2	2052.5	2033.2	2007.6	1978.9	1953.1
27.5°	2007.6	2017.3	2010.9	1991.6	1982.1	1969.2	1966.0	1940.4	1917.9	1889.1	1860.3
30°	1908.4	1908.4	1898.8	1889.1	1873.2	1863.5	1850.7	1831.5	1809.2	1773.9	1751.4
32.5°	1783.5	1780.2	1767.5	1764.3	1751.4	1732.3	1729.1	1703.5	1681.0	1655.4	1626.6
35°	1645.8	1639.3	1626.6	1617.0	1610.5	1601.0	1591.4	1569.0	1546.5	1520.9	1501.7
37.5°	1488.9	1488.9	1485.7	1469.6	1463.3	1456.9	1447.3	1424.9	1412.1	1386.5	1367.2
40°	1338.4	1335.2	1325.7	1322.4	1316.0	1306.4	1300.0	1287.2	1267.9	1248.8	1229.5
42.5°	1191.1	1194.3	1181.6	1184.8	1171.9	1165.5	1162.3	1143.1	1133.5	1114.3	1098.3
45°	1059.8	1056.6	1050.3	1047.1	1040.7	1034.2	1027.8	1018.2	1002.2	983.1	973.4
47.5°	938.2	928.6	928.6	925.3	922.1	909.4	906.2	896.5	886.9	867.7	854.9
50°	822.9	822.9	822.9	819.7	810.2	806.9	800.5	790.9	781.2	768.5	749.2
52.5°	730.1	730.1	730.1	726.9	714.0	710.8	707.6	694.8	682.0	672.5	659.6
55°	643.6	646.8	643.6	637.2	627.6	627.6	618.0	611.5	598.8	589.2	576.3
57.5°	569.9	569.9	563.6	560.4	553.9	550.7	544.3	537.9	521.9	512.3	496.3
60°	499.6	496.3	496.3	489.9	483.5	477.1	473.9	464.3	457.9	441.8	429.1
62.5°	435.4	435.4	429.1	429.1	416.3	416.3	413.0	403.4	393.9	377.8	371.4
65°	374.6	374.6	371.4	368.2	358.7	355.5	352.2	342.6	333.0	323.4	313.8
67.5°	320.2	320.2	313.8	310.6	304.2	301.0	294.5	288.2	278.6	268.9	259.3
70°	268.9	265.7	262.5	259.3	253.0	249.8	243.4	236.9	227.3	221.0	211.3
72.5°	217.8	217.8	214.6	208.1	204.9	201.7	198.5	192.1	182.5	172.9	166.5
75°	169.7	169.7	169.7	163.3	156.8	153.7	153.7	147.3	140.9	131.3	124.8
77.5°	131.3	128.0	124.8	124.8	118.5	115.3	112.1	108.9	99.2	96.0	89.6
80°	89.6	92.8	89.6	86.4	83.3	80.1	80.1	73.7	70.4	64.0	57.6
82.5°	60.8	57.6	57.6	54.4	54.4	51.3	51.3	44.9	41.6	38.4	35.2
85°	32.0	32.0	28.8	28.8	28.8	25.6	25.6	22.4	22.4	19.2	16.1
87.5°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584555

CATALOG NUMBER: HCC8S40D010MB-HM82555835-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1
2.5°	2170.9	2164.5	2161.3	2161.3	2158.1	2155.0	2151.8	2148.5	2142.1	2142.1	2135.7
5°	2187.0	2180.6	2177.3	2167.7	2161.3	2161.3	2148.5	2145.3	2135.7	2129.3	2122.8
7.5°	2199.7	2187.0	2177.3	2167.7	2161.3	2155.0	2142.1	2129.3	2116.5	2103.7	2097.3
10°	2199.7	2187.0	2170.9	2155.0	2148.5	2142.1	2126.1	2106.9	2090.8	2078.1	2062.0
12.5°	2193.3	2174.1	2155.0	2142.1	2129.3	2119.7	2100.5	2081.3	2062.0	2036.4	2023.6
15°	2174.1	2148.5	2129.3	2106.9	2097.3	2081.3	2065.2	2036.4	2014.1	1991.6	1975.6
17.5°	2135.7	2103.7	2081.3	2058.8	2042.9	2033.2	2007.6	1982.1	1956.4	1930.8	1911.6
20°	2078.1	2049.3	2023.6	1994.8	1982.1	1969.2	1937.2	1911.6	1885.9	1857.1	1838.0
22.5°	2007.6	1978.9	1943.6	1921.1	1902.0	1885.9	1857.1	1828.3	1802.7	1777.0	1751.4
25°	1921.1	1892.3	1860.3	1825.1	1812.3	1796.3	1764.3	1735.5	1706.7	1677.8	1655.4
27.5°	1828.3	1789.9	1764.3	1725.9	1713.0	1697.1	1661.8	1629.8	1604.2	1581.7	1556.2
30°	1716.2	1687.4	1652.2	1617.0	1604.2	1588.2	1559.4	1530.6	1504.9	1479.3	1453.7
32.5°	1594.6	1565.8	1530.6	1504.9	1485.7	1472.9	1444.1	1418.5	1392.9	1367.2	1344.8
35°	1466.4	1434.4	1408.8	1383.3	1367.2	1351.2	1322.4	1300.0	1280.8	1258.4	1235.9
37.5°	1335.2	1312.8	1287.2	1258.4	1242.4	1229.5	1207.1	1181.6	1165.5	1146.3	1130.3
40°	1207.1	1181.6	1159.1	1133.5	1120.7	1111.1	1088.6	1069.5	1053.4	1037.4	1027.8
42.5°	1075.9	1053.4	1031.0	1015.1	1005.4	995.8	979.8	957.4	947.8	931.8	922.1
45°	954.1	935.0	918.9	896.5	890.1	883.7	864.5	848.5	839.0	829.3	822.9
47.5°	839.0	826.1	806.9	794.1	784.4	778.0	765.3	752.4	742.8	736.5	730.1
50°	739.7	723.6	710.8	698.1	691.6	682.0	669.3	662.8	656.4	650.0	650.0
52.5°	646.8	630.8	618.0	608.3	602.0	595.6	586.0	582.7	576.3	576.3	573.1
55°	560.4	550.7	537.9	525.1	521.9	518.7	512.3	505.9	502.7	499.6	502.7
57.5°	486.7	477.1	464.3	454.7	451.5	448.3	445.1	438.6	435.4	435.4	435.4
60°	419.5	409.8	400.2	390.7	390.7	384.3	381.0	377.8	374.6	371.4	371.4
62.5°	358.7	349.0	339.4	333.0	329.7	326.7	320.2	317.0	313.8	313.8	310.6
65°	304.2	291.4	288.2	278.6	275.4	272.2	268.9	262.5	259.3	256.2	253.0
67.5°	249.8	243.4	233.7	227.3	224.2	221.0	217.8	211.3	208.1	204.9	198.5
70°	201.7	195.3	189.0	182.5	179.3	176.1	169.7	163.3	160.1	153.7	144.1
72.5°	156.8	150.5	144.1	137.7	134.5	131.3	124.8	118.5	112.1	105.7	99.2
75°	118.5	112.1	102.5	96.0	92.8	92.8	83.3	76.9	70.4	60.8	54.4
77.5°	83.3	73.7	70.4	64.0	60.8	54.4	48.1	41.6	35.2	32.0	25.6
80°	54.4	48.1	41.6	38.4	35.2	32.0	28.8	22.4	16.1	12.9	9.6
82.5°	32.0	28.8	25.6	22.4	19.2	16.1	12.9	12.9	9.6	6.4	3.2
85°	16.1	12.9	9.6	9.6	6.4	6.4	6.4	3.2	3.2	3.2	3.2
87.5°	6.4	3.2	3.2	3.2	3.2	3.2	3.2	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584555

CATALOG NUMBER: HCC8S40D010MB-HM82555835-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1
2.5°	2132.5	2129.3	2126.1	2122.8	2122.8	2116.5	2116.5	2113.3	2106.9	2103.7	2103.7
5°	2113.3	2103.7	2097.3	2094.0	2090.8	2081.3	2078.1	2071.7	2065.2	2058.8	2055.6
7.5°	2084.5	2068.5	2062.0	2058.8	2049.3	2039.7	2033.2	2023.6	2014.1	2004.4	2001.2
10°	2049.3	2033.2	2017.3	2010.9	2001.2	1994.8	1982.1	1969.2	1959.6	1949.9	1940.4
12.5°	2004.4	1985.2	1969.2	1962.8	1953.1	1940.4	1921.1	1914.7	1898.8	1892.3	1879.6
15°	1953.1	1930.8	1914.7	1905.2	1895.6	1876.4	1863.5	1850.7	1834.7	1828.3	1815.5
17.5°	1889.1	1863.5	1847.5	1838.0	1831.5	1815.5	1796.3	1780.2	1764.3	1757.9	1748.2
20°	1812.3	1796.3	1773.9	1764.3	1757.9	1738.7	1719.4	1713.0	1700.3	1687.4	1677.8
22.5°	1725.9	1709.8	1687.4	1677.8	1674.6	1658.6	1642.6	1633.0	1623.4	1613.8	1604.2
25°	1636.2	1617.0	1597.8	1591.4	1585.0	1572.1	1559.4	1552.9	1543.3	1536.9	1530.6
27.5°	1540.1	1520.9	1504.9	1495.4	1488.9	1479.3	1472.9	1466.4	1460.1	1453.7	1450.5
30°	1437.6	1418.5	1405.6	1399.2	1392.9	1389.7	1380.0	1376.8	1373.6	1367.2	1370.4
32.5°	1335.2	1319.2	1306.4	1296.7	1296.7	1290.4	1287.2	1287.2	1284.0	1284.0	1284.0
35°	1223.2	1213.6	1203.9	1200.7	1197.5	1194.3	1191.1	1194.3	1191.1	1194.3	1197.5
37.5°	1120.7	1111.1	1104.7	1101.5	1098.3	1101.5	1098.3	1098.3	1101.5	1107.9	1111.1
40°	1015.1	1008.6	1002.2	1005.4	1002.2	1002.2	1002.2	1011.9	1015.1	1018.2	1021.4
42.5°	915.7	909.4	906.2	906.2	909.4	906.2	912.6	915.7	922.1	931.8	938.2
45°	819.7	816.5	816.5	819.7	816.5	822.9	822.9	829.3	839.0	845.3	851.7
47.5°	730.1	730.1	730.1	733.3	733.3	736.5	742.8	746.0	752.4	758.9	765.3
50°	646.8	650.0	653.2	653.2	653.2	659.6	666.0	669.3	672.5	675.6	685.2
52.5°	573.1	576.3	576.3	579.5	582.7	586.0	589.2	595.6	598.8	605.1	608.3
55°	502.7	502.7	509.1	512.3	512.3	512.3	518.7	518.7	525.1	528.4	534.8
57.5°	435.4	438.6	438.6	441.8	441.8	445.1	448.3	451.5	454.7	457.9	461.1
60°	371.4	371.4	371.4	374.6	377.8	381.0	377.8	384.3	384.3	390.7	393.9
62.5°	310.6	313.8	313.8	313.8	313.8	313.8	313.8	317.0	320.2	323.4	326.7
65°	253.0	253.0	253.0	249.8	253.0	249.8	253.0	256.2	256.2	259.3	262.5
67.5°	195.3	195.3	189.0	189.0	192.1	192.1	192.1	192.1	189.0	195.3	195.3
70°	140.9	137.7	134.5	131.3	131.3	128.0	128.0	124.8	124.8	124.8	124.8
72.5°	92.8	86.4	80.1	76.9	73.7	73.7	67.2	64.0	67.2	67.2	67.2
75°	48.1	41.6	38.4	35.2	32.0	32.0	28.8	28.8	28.8	28.8	28.8
77.5°	19.2	16.1	12.9	12.9	9.6	9.6	9.6	9.6	9.6	9.6	9.6
80°	6.4	6.4	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
85°	3.2	0.0	0.0	3.2	0.0	3.2	3.2	3.2	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584555

CATALOG NUMBER: HCC8S40D010MB-HM82555835-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1	2142.1
2.5°	2100.5	2100.5	2097.3	2100.5	2094.0	2097.3	2094.0	2094.0
5°	2052.5	2046.1	2046.1	2046.1	2042.9	2042.9	2039.7	2039.7
7.5°	1994.8	1991.6	1988.4	1985.2	1982.1	1978.9	1978.9	1978.9
10°	1937.2	1930.8	1930.8	1927.6	1921.1	1917.9	1917.9	1917.9
12.5°	1870.0	1866.8	1863.5	1863.5	1850.7	1853.9	1850.7	1850.7
15°	1805.9	1802.7	1802.7	1793.1	1786.7	1786.7	1786.7	1783.5
17.5°	1738.7	1735.5	1732.3	1725.9	1719.4	1719.4	1716.2	1719.4
20°	1668.3	1665.0	1658.6	1658.6	1655.4	1652.2	1645.8	1649.0
22.5°	1597.8	1591.4	1588.2	1588.2	1585.0	1585.0	1578.5	1578.5
25°	1524.2	1520.9	1517.7	1520.9	1514.5	1514.5	1508.1	1508.1
27.5°	1447.3	1444.1	1444.1	1444.1	1440.9	1444.1	1440.9	1440.9
30°	1370.4	1370.4	1367.2	1367.2	1370.4	1367.2	1370.4	1373.6
32.5°	1287.2	1287.2	1290.4	1290.4	1293.6	1293.6	1293.6	1293.6
35°	1200.7	1207.1	1207.1	1210.3	1213.6	1216.8	1216.8	1220.0
37.5°	1120.7	1123.8	1127.0	1130.3	1136.7	1136.7	1136.7	1136.7
40°	1034.2	1037.4	1043.9	1040.7	1053.4	1056.6	1053.4	1053.4
42.5°	944.6	950.9	954.1	960.6	963.8	970.2	973.4	973.4
45°	861.3	864.5	871.0	877.4	880.5	890.1	890.1	890.1
47.5°	774.9	781.2	784.4	790.9	794.1	803.7	806.9	803.7
50°	691.6	698.1	704.5	704.5	714.0	717.2	723.6	726.9
52.5°	611.5	614.8	621.2	624.4	630.8	637.2	640.3	643.6
55°	534.8	537.9	544.3	544.3	553.9	557.2	563.6	563.6
57.5°	464.3	467.4	473.9	470.6	477.1	483.5	483.5	480.3
60°	397.0	397.0	397.0	403.4	406.6	409.8	413.0	413.0
62.5°	326.7	333.0	336.2	336.2	339.4	342.6	342.6	339.4
65°	262.5	268.9	272.2	272.2	275.4	275.4	275.4	278.6
67.5°	198.5	198.5	198.5	201.7	198.5	198.5	198.5	198.5
70°	124.8	124.8	124.8	124.8	121.6	124.8	124.8	128.0
72.5°	67.2	67.2	67.2	67.2	67.2	67.2	67.2	67.2
75°	28.8	28.8	28.8	32.0	28.8	28.8	28.8	28.8
77.5°	12.9	9.6	12.9	12.9	9.6	9.6	9.6	9.6
80°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
85°	0.0	3.2	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)