

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584574

Luminaire Tested: **HCC8W40D010BZ-HM82555840-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010BZ-HM82555840-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4911.1 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584574
CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584574

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	75296	75296	75296
5°	78054	75048	72470
10°	80262	74397	69506
15°	82051	73081	66437
20°	82176	70228	63737
25°	80600	66323	61485
30°	76448	61503	58787
35°	69461	56015	56143
40°	60735	50265	52918
45°	52636	44769	49309
50°	46092	39769	44927
55°	41020	35246	40649
60°	37004	31663	35727
65°	33403	27836	31127
70°	30023	23450	23144
75°	26438	18598	17359
80°	22162	15414	16639
85°	17195	13515	14718



TEST NUMBER: P584574
 CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.4	4.7
10°-20°	648.8	13.2
20°-30°	927.3	18.9
30°-40°	985.3	20.1
40°-50°	848.3	17.3
50°-60°	634.2	12.9
60°-70°	404.5	8.2
70°-80°	184.1	3.7
80°-90°	48.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1806.4	36.8
0°-40°	2791.7	56.8
0°-60°	4274.2	87.0
0°-90°	4911.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4911.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2442	2442	2442	2442	2442	
5°	2522	2487	2424	2362	2341	242
15°	2570	2483	2289	2133	2081	724
25°	2369	2220	1949	1831	1807	1084
35°	1845	1717	1488	1450	1491	1149
45°	1207	1141	1027	1054	1131	938
55°	763	701	656	711	756	686
65°	458	406	382	399	427	457
75°	222	191	156	142	146	236
85°	49	42	38	42	42	59
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584574

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8
2.5°	2486.9	2480.0	2483.4	2480.0	2483.4	2483.4	2476.5	2476.5	2476.5	2476.5	2466.0
5°	2521.6	2518.2	2518.2	2514.7	2511.1	2514.7	2511.1	2507.7	2500.8	2497.3	2486.9
7.5°	2542.4	2542.4	2542.4	2542.4	2539.0	2535.4	2532.0	2525.1	2518.2	2511.1	2504.2
10°	2563.3	2566.7	2563.3	2559.7	2556.2	2549.3	2545.9	2539.0	2528.5	2518.2	2511.1
12.5°	2573.6	2573.6	2570.2	2570.2	2563.3	2559.7	2549.3	2539.0	2528.5	2518.2	2500.8
15°	2570.2	2570.2	2566.7	2563.3	2552.8	2549.3	2542.4	2532.0	2514.7	2500.8	2483.4
17.5°	2549.3	2545.9	2539.0	2539.0	2525.1	2521.6	2514.7	2500.8	2483.4	2462.6	2441.8
20°	2504.2	2504.2	2500.8	2497.3	2483.4	2473.1	2466.0	2448.8	2434.9	2410.6	2389.8
22.5°	2441.8	2448.8	2441.8	2434.9	2417.5	2414.0	2403.7	2382.9	2362.0	2334.3	2310.0
25°	2368.9	2365.5	2362.0	2355.1	2341.2	2334.3	2320.4	2299.6	2278.8	2247.6	2219.8
27.5°	2275.3	2261.5	2261.5	2247.6	2237.2	2226.7	2219.8	2199.0	2171.3	2147.0	2112.2
30°	2147.0	2150.4	2133.1	2129.6	2112.2	2105.3	2091.5	2070.7	2046.4	2018.7	1990.9
32.5°	2008.2	1997.9	1997.9	1984.0	1970.0	1959.7	1956.2	1932.0	1911.1	1883.4	1855.7
35°	1845.2	1845.2	1834.9	1831.4	1817.5	1810.6	1800.1	1786.3	1762.0	1737.8	1716.9
37.5°	1685.6	1678.7	1675.3	1668.4	1657.9	1647.6	1647.6	1623.3	1619.8	1592.0	1564.3
40°	1508.8	1515.7	1508.8	1498.3	1494.9	1488.0	1484.5	1470.6	1460.2	1436.0	1418.6
42.5°	1359.7	1352.7	1352.7	1349.2	1335.4	1335.4	1328.4	1321.5	1304.1	1297.2	1276.4
45°	1207.0	1213.9	1203.6	1207.0	1193.2	1193.2	1193.2	1179.3	1165.4	1155.0	1141.1
47.5°	1075.3	1078.7	1078.7	1068.3	1064.8	1064.8	1057.9	1051.0	1040.5	1026.6	1016.3
50°	960.8	964.3	957.4	953.8	946.9	943.4	943.4	929.5	922.6	908.7	901.8
52.5°	856.7	856.7	853.2	853.2	842.9	842.9	835.9	825.5	818.6	811.6	794.3
55°	763.0	763.0	759.6	756.1	756.1	745.8	742.2	731.8	724.9	711.0	700.7
57.5°	672.9	676.4	672.9	669.4	665.9	662.5	655.6	645.1	638.2	627.8	620.8
60°	600.0	600.0	596.5	593.1	586.2	582.7	579.3	572.3	561.9	555.0	544.5
62.5°	530.6	527.2	523.7	520.3	513.4	513.4	506.3	499.4	489.1	482.1	475.2
65°	457.8	457.8	454.3	454.3	450.9	444.0	440.5	437.1	423.2	419.7	405.8
67.5°	392.0	395.4	388.4	388.4	381.5	381.5	378.1	367.7	364.1	357.2	350.3
70°	333.0	333.0	333.0	329.5	322.6	319.2	315.6	308.7	305.2	298.3	291.3
72.5°	274.1	274.1	270.5	270.5	267.0	263.6	260.1	253.2	253.2	246.2	239.3
75°	221.9	221.9	218.5	215.0	211.6	211.6	208.1	204.7	197.7	194.2	190.8
77.5°	169.9	169.9	169.9	166.5	163.0	163.0	163.0	156.1	149.1	149.1	145.7
80°	124.8	124.8	121.4	121.4	117.9	117.9	117.9	114.5	111.0	107.6	104.0
82.5°	83.3	83.3	83.3	83.3	79.7	79.7	79.7	76.3	72.8	72.8	72.8
85°	48.6	48.6	48.6	48.6	45.1	45.1	45.1	45.1	45.1	41.6	41.6
87.5°	20.8	17.4	20.8	17.4	20.8	17.4	20.8	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584574

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8
2.5°	2469.6	2466.0	2462.6	2459.1	2459.1	2455.7	2448.8	2445.3	2441.8	2438.3	2438.3
5°	2483.4	2480.0	2473.1	2466.0	2462.6	2455.7	2448.8	2441.8	2434.9	2424.5	2421.1
7.5°	2493.9	2483.4	2476.5	2462.6	2459.1	2452.2	2441.8	2431.4	2417.5	2403.7	2393.2
10°	2493.9	2480.0	2469.6	2452.2	2445.3	2438.3	2424.5	2407.1	2389.8	2376.0	2358.6
12.5°	2486.9	2469.6	2452.2	2434.9	2424.5	2414.0	2393.2	2376.0	2355.1	2334.3	2320.4
15°	2462.6	2441.8	2421.1	2400.2	2389.8	2376.0	2355.1	2330.9	2310.0	2289.2	2264.9
17.5°	2417.5	2396.8	2372.5	2348.1	2334.3	2323.8	2292.7	2275.3	2244.1	2223.3	2202.5
20°	2358.6	2334.3	2303.1	2278.8	2261.5	2251.0	2226.7	2195.5	2171.3	2140.1	2119.3
22.5°	2282.3	2251.0	2219.8	2195.5	2178.2	2164.4	2133.1	2101.9	2081.1	2053.3	2029.1
25°	2192.1	2160.9	2129.6	2095.0	2077.6	2063.7	2036.0	2008.2	1980.5	1949.3	1928.5
27.5°	2084.5	2049.9	2022.2	1990.9	1973.6	1952.8	1921.5	1893.8	1866.0	1845.2	1817.5
30°	1966.6	1928.5	1900.8	1869.5	1852.1	1834.9	1803.6	1775.8	1751.6	1727.3	1713.5
32.5°	1824.4	1796.7	1768.9	1737.8	1723.8	1713.5	1682.2	1654.5	1626.7	1605.9	1595.6
35°	1689.2	1657.9	1633.6	1605.9	1588.5	1578.2	1550.5	1526.2	1512.3	1488.0	1474.1
37.5°	1547.0	1522.7	1494.9	1467.2	1456.8	1446.3	1425.5	1401.2	1380.4	1363.1	1356.1
40°	1397.8	1376.9	1352.7	1335.4	1324.9	1314.6	1297.2	1279.8	1266.0	1248.7	1241.8
42.5°	1255.6	1241.8	1220.9	1200.1	1189.6	1186.2	1165.4	1151.6	1144.5	1137.6	1130.7
45°	1127.3	1106.5	1092.5	1078.7	1068.3	1061.4	1051.0	1040.5	1033.6	1026.6	1019.7
47.5°	1002.3	985.1	971.2	960.8	950.3	946.9	940.0	929.5	922.6	922.6	922.6
50°	888.0	874.1	860.1	853.2	849.8	842.9	835.9	832.4	829.0	829.0	829.0
52.5°	787.3	773.5	763.0	756.1	756.1	749.2	742.2	738.8	738.8	738.8	738.8
55°	693.7	683.3	676.4	669.4	662.5	659.0	659.0	659.0	655.6	655.6	659.0
57.5°	610.5	603.6	593.1	586.2	582.7	582.7	579.3	575.7	579.3	582.7	586.2
60°	534.2	527.2	523.7	513.4	513.4	513.4	509.9	509.9	509.9	513.4	516.8
62.5°	464.8	461.4	454.3	450.9	447.4	447.4	444.0	444.0	444.0	444.0	447.4
65°	402.3	395.4	388.4	388.4	388.4	385.0	385.0	378.1	381.5	381.5	378.1
67.5°	343.4	336.4	333.0	329.5	326.1	326.1	322.6	319.2	315.6	315.6	315.6
70°	287.9	281.0	281.0	274.1	274.1	270.5	267.0	267.0	263.6	260.1	256.7
72.5°	232.4	229.0	225.5	221.9	221.9	221.9	218.5	215.0	211.6	208.1	201.2
75°	183.9	183.9	176.8	173.4	173.4	169.9	166.5	163.0	159.6	156.1	152.6
77.5°	142.2	138.8	131.9	128.3	128.3	128.3	124.8	121.4	117.9	114.5	111.0
80°	104.0	100.6	97.1	93.7	93.7	93.7	90.2	90.2	86.8	86.8	86.8
82.5°	69.4	69.4	65.9	65.9	65.9	65.9	62.5	62.5	62.5	62.5	62.5
85°	41.6	41.6	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584574

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8
2.5°	2431.4	2431.4	2424.5	2421.1	2417.5	2421.1	2414.0	2410.6	2407.1	2407.1	2403.7
5°	2410.6	2407.1	2393.2	2389.8	2386.3	2382.9	2376.0	2368.9	2362.0	2358.6	2355.1
7.5°	2382.9	2372.5	2358.6	2355.1	2351.7	2341.2	2330.9	2323.8	2313.5	2310.0	2303.1
10°	2344.7	2330.9	2320.4	2310.0	2303.1	2292.7	2282.3	2271.8	2258.0	2254.6	2244.1
12.5°	2299.6	2282.3	2261.5	2258.0	2247.6	2233.7	2219.8	2209.5	2199.0	2192.1	2181.6
15°	2244.1	2226.7	2205.9	2195.5	2185.2	2174.7	2157.4	2143.5	2133.1	2122.7	2112.2
17.5°	2178.2	2157.4	2140.1	2129.6	2122.7	2105.3	2091.5	2074.2	2063.7	2053.3	2043.0
20°	2098.4	2081.1	2056.8	2046.4	2043.0	2029.1	2011.7	2004.8	1990.9	1980.5	1973.6
22.5°	2008.2	1990.9	1970.0	1963.1	1949.3	1942.3	1925.1	1918.0	1911.1	1900.8	1897.2
25°	1907.7	1890.3	1872.9	1869.5	1859.1	1852.1	1841.8	1831.4	1831.4	1820.9	1820.9
27.5°	1803.6	1786.3	1772.4	1765.5	1762.0	1755.0	1744.7	1741.2	1737.8	1734.2	1734.2
30°	1692.7	1671.8	1664.9	1661.4	1657.9	1651.0	1647.6	1640.7	1644.1	1647.6	1644.1
32.5°	1574.7	1567.7	1553.9	1547.0	1550.5	1547.0	1540.0	1547.0	1543.4	1550.5	1553.9
35°	1460.2	1453.3	1446.3	1446.3	1439.4	1439.4	1439.4	1442.9	1449.8	1453.3	1460.2
37.5°	1349.2	1338.9	1335.4	1331.8	1335.4	1335.4	1335.4	1342.3	1349.2	1356.1	1366.6
40°	1231.3	1224.4	1224.4	1224.4	1224.4	1234.7	1231.3	1238.2	1245.2	1255.6	1266.0
42.5°	1120.3	1120.3	1123.8	1123.8	1123.8	1123.8	1130.7	1141.1	1151.6	1161.9	1172.4
45°	1016.3	1016.3	1016.3	1023.2	1023.2	1026.6	1040.5	1047.4	1054.5	1064.8	1075.3
47.5°	919.2	919.2	922.6	926.1	929.5	936.5	943.4	953.8	964.3	971.2	981.6
50°	829.0	832.4	839.4	846.3	846.3	849.8	860.1	867.2	874.1	884.4	888.0
52.5°	742.2	749.2	756.1	759.6	763.0	770.0	773.5	783.9	787.3	797.8	801.2
55°	662.5	665.9	676.4	679.8	679.8	686.7	693.7	700.7	711.0	711.0	717.9
57.5°	589.6	593.1	600.0	603.6	600.0	610.5	613.9	620.8	624.3	631.3	634.7
60°	516.8	523.7	527.2	527.2	530.6	534.2	541.1	541.1	548.0	555.0	555.0
62.5°	447.4	450.9	454.3	457.8	461.4	457.8	468.3	468.3	475.2	478.6	485.6
65°	381.5	385.0	385.0	388.4	388.4	392.0	392.0	395.4	398.9	405.8	409.2
67.5°	315.6	315.6	315.6	319.2	315.6	319.2	319.2	322.6	322.6	329.5	333.0
70°	256.7	253.2	249.8	249.8	249.8	249.8	246.2	249.8	249.8	253.2	253.2
72.5°	197.7	194.2	190.8	187.3	187.3	183.9	180.4	183.9	183.9	187.3	187.3
75°	149.1	142.2	142.2	142.2	138.8	138.8	138.8	142.2	142.2	142.2	145.7
77.5°	111.0	111.0	107.6	107.6	107.6	111.0	111.0	114.5	114.5	114.5	114.5
80°	83.3	86.8	86.8	86.8	86.8	90.2	90.2	90.2	90.2	93.7	93.7
82.5°	62.5	62.5	62.5	62.5	65.9	65.9	65.9	65.9	65.9	65.9	65.9
85°	38.2	41.6	41.6	38.2	41.6	41.6	41.6	41.6	41.6	41.6	41.6
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584574

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8	2441.8
2.5°	2400.2	2400.2	2400.2	2400.2	2396.8	2396.8	2396.8	2393.2
5°	2348.1	2348.1	2348.1	2341.2	2344.7	2344.7	2337.8	2341.2
7.5°	2296.1	2292.7	2289.2	2289.2	2285.8	2282.3	2278.8	2282.3
10°	2237.2	2226.7	2226.7	2223.3	2223.3	2216.4	2216.4	2219.8
12.5°	2171.3	2164.4	2164.4	2160.9	2157.4	2153.9	2150.4	2150.4
15°	2105.3	2098.4	2095.0	2091.5	2088.0	2081.1	2084.5	2081.1
17.5°	2039.4	2029.1	2029.1	2025.6	2022.2	2015.1	2015.1	2011.7
20°	1963.1	1959.7	1952.8	1956.2	1952.8	1945.8	1942.3	1942.3
22.5°	1886.9	1886.9	1883.4	1883.4	1880.0	1876.4	1872.9	1872.9
25°	1814.0	1810.6	1814.0	1814.0	1803.6	1803.6	1803.6	1807.1
27.5°	1730.7	1734.2	1730.7	1730.7	1730.7	1730.7	1734.2	1730.7
30°	1647.6	1647.6	1647.6	1651.0	1657.9	1654.5	1654.5	1651.0
32.5°	1557.4	1560.8	1560.8	1564.3	1567.7	1574.7	1574.7	1578.2
35°	1467.2	1474.1	1477.6	1474.1	1484.5	1484.5	1491.4	1491.4
37.5°	1373.5	1376.9	1384.0	1387.4	1394.3	1397.8	1401.2	1401.2
40°	1272.9	1286.9	1290.3	1293.8	1304.1	1304.1	1307.6	1314.6
42.5°	1179.3	1193.2	1196.7	1200.1	1207.0	1217.5	1213.9	1220.9
45°	1089.1	1099.6	1103.0	1106.5	1116.8	1120.3	1120.3	1130.7
47.5°	992.0	998.9	1002.3	1009.4	1016.3	1023.2	1030.2	1026.6
50°	894.9	905.2	912.3	915.7	926.1	929.5	933.1	936.5
52.5°	808.1	815.2	818.6	822.1	832.4	835.9	839.4	846.3
55°	724.9	728.4	735.3	731.8	742.2	745.8	749.2	756.1
57.5°	641.6	645.1	648.6	648.6	655.6	662.5	665.9	669.4
60°	561.9	568.8	572.3	572.3	572.3	579.3	579.3	579.3
62.5°	489.1	489.1	492.5	492.5	499.4	499.4	499.4	499.4
65°	412.7	416.3	419.7	419.7	426.6	423.2	430.1	426.6
67.5°	333.0	333.0	339.9	339.9	336.4	339.9	339.9	339.9
70°	253.2	253.2	256.7	256.7	256.7	256.7	256.7	256.7
72.5°	187.3	187.3	187.3	190.8	187.3	187.3	190.8	187.3
75°	145.7	145.7	145.7	145.7	145.7	145.7	145.7	145.7
77.5°	114.5	114.5	117.9	117.9	117.9	117.9	117.9	117.9
80°	93.7	93.7	93.7	93.7	97.1	93.7	93.7	93.7
82.5°	69.4	65.9	69.4	65.9	69.4	69.4	69.4	69.4
85°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)