

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593734

Luminaire Tested: **HCC8S40D010SL-HM82555850-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593734  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S40D010SL-HM82555850-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4321.5 lumens  
Efficiency: N/A  
Efficacy: 105.4 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593734  
CATALOG NUMBER: HCC8S40D010SL-HM82555850-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593734

CATALOG NUMBER: HCC8S40D010SL-HM82555850-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59				59
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53				53
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47				47
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43				43
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39				39
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35				35
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32				32

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	71540	71540	71540
5°	74500	71383	68378
10°	76990	70471	65044
15°	78936	68860	61665
20°	79091	66001	58608
25°	77759	61825	55575
30°	73596	57049	52972
35°	67101	51305	49739
40°	58348	45229	45930
45°	50059	39170	42039
50°	42753	33773	37764
55°	37477	29085	32816
60°	33365	24805	27586
65°	29609	20240	22014
70°	26263	15012	12514
75°	21910	7851	3717
80°	17243	2468	622
85°	12242	1238	0



TEST NUMBER: P593734  
 CATALOG NUMBER: HCC8S40D010SL-HM82555850-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	218.6	5.1
10°-20°	612.7	14.2
20°-30°	867.2	20.1
30°-40°	907.3	21.0
40°-50°	756.8	17.5
50°-60°	536.6	12.4
60°-70°	309.1	7.2
70°-80°	99.5	2.3
80°-90°	13.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1698.6	39.3
0°-40°	2605.9	60.3
0°-60°	3899.3	90.2
0°-90°	4321.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4321.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2320	2320	2320	2320	2320	
5°	2407	2376	2306	2237	2209	231
15°	2473	2372	2157	1987	1932	695
25°	2285	2116	1817	1672	1633	1043
35°	1782	1626	1363	1290	1321	1105
45°	1148	1054	898	909	964	889
55°	697	624	541	569	610	630
65°	406	340	277	277	302	405
75°	184	135	66	31	31	199
85°	35	17	4	0	0	43
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593734

CATALOG NUMBER: HCC8S40D010SL-HM82555850-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0
2.5°	2368.6	2365.1	2361.7	2365.1	2361.7	2365.1	2361.7	2361.7	2358.2	2354.7	2354.7
5°	2406.8	2403.2	2403.2	2403.2	2399.8	2396.3	2396.3	2392.9	2386.0	2382.5	2375.5
7.5°	2431.1	2434.5	2434.5	2434.5	2427.5	2427.5	2420.6	2413.7	2406.8	2399.8	2389.4
10°	2458.8	2458.8	2455.3	2451.8	2444.9	2441.4	2438.0	2431.1	2420.6	2406.8	2396.3
12.5°	2469.1	2469.1	2465.7	2458.8	2455.3	2451.8	2448.3	2438.0	2424.0	2406.8	2392.9
15°	2472.6	2465.7	2462.2	2458.8	2451.8	2441.4	2441.4	2427.5	2410.2	2389.4	2372.0
17.5°	2444.9	2448.3	2441.4	2434.5	2424.0	2417.1	2406.8	2396.3	2375.5	2351.2	2333.9
20°	2410.2	2406.8	2403.2	2392.9	2378.9	2375.5	2365.1	2347.8	2330.4	2302.6	2278.4
22.5°	2354.7	2351.2	2344.3	2337.4	2323.5	2316.6	2306.1	2285.4	2261.1	2233.3	2205.5
25°	2285.4	2278.4	2268.0	2254.1	2243.7	2236.8	2222.9	2202.1	2174.4	2143.2	2115.5
27.5°	2174.4	2184.7	2177.8	2157.0	2146.6	2132.7	2129.3	2101.5	2077.3	2046.1	2014.8
30°	2066.9	2066.9	2056.4	2046.1	2028.7	2018.4	2004.4	1983.6	1959.3	1921.3	1897.0
32.5°	1931.6	1928.2	1914.2	1910.8	1897.0	1876.2	1872.7	1845.0	1820.7	1792.9	1761.7
35°	1782.5	1775.6	1761.7	1751.3	1744.3	1733.9	1723.6	1699.3	1675.0	1647.2	1626.5
37.5°	1612.6	1612.6	1609.1	1591.7	1584.8	1577.9	1567.5	1543.2	1529.4	1501.5	1480.8
40°	1449.5	1446.1	1435.7	1432.3	1425.3	1414.9	1408.0	1394.1	1373.3	1352.4	1331.7
42.5°	1290.1	1293.5	1279.6	1283.2	1269.3	1262.4	1258.9	1238.1	1227.6	1206.8	1189.5
45°	1147.9	1144.4	1137.5	1134.0	1127.0	1120.1	1113.2	1102.8	1085.4	1064.7	1054.2
47.5°	1016.1	1005.7	1005.7	1002.2	998.8	984.8	981.4	971.0	960.6	939.7	925.9
50°	891.2	891.2	891.2	887.7	877.4	873.9	866.9	856.6	846.2	832.3	811.5
52.5°	790.6	790.6	790.6	787.2	773.4	769.9	766.4	752.6	738.6	728.3	714.4
55°	697.1	700.6	697.1	690.1	679.7	679.7	669.3	662.4	648.6	638.1	624.3
57.5°	617.3	617.3	610.4	606.9	600.0	596.4	589.5	582.6	565.2	554.9	537.5
60°	541.0	537.5	537.5	530.6	523.6	516.7	513.2	502.9	495.9	478.6	464.7
62.5°	471.6	471.6	464.7	464.7	450.8	450.8	447.3	437.0	426.5	409.2	402.2
65°	405.8	405.8	402.2	398.8	388.4	385.0	381.5	371.0	360.7	350.2	339.9
67.5°	346.8	346.8	339.9	336.4	329.4	325.9	319.0	312.1	301.7	291.3	281.0
70°	291.3	287.9	284.4	281.0	273.9	270.5	263.6	256.7	246.2	239.3	228.8
72.5°	235.9	235.9	232.4	225.4	221.9	218.5	215.0	208.1	197.7	187.3	180.3
75°	183.9	183.9	183.9	176.8	169.9	166.5	166.5	159.6	152.6	142.2	135.3
77.5°	142.2	138.8	135.3	135.3	128.3	124.8	121.4	117.9	107.5	104.0	97.1
80°	97.1	100.6	97.1	93.7	90.2	86.8	86.8	79.7	76.3	69.4	62.5
82.5°	65.9	62.5	62.5	58.9	58.9	55.5	55.5	48.6	45.1	41.6	38.2
85°	34.6	34.6	31.2	31.2	31.2	27.7	27.7	24.3	24.3	20.8	17.4
87.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	6.9	6.9	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593734

CATALOG NUMBER: HCC8S40D010SL-HM82555850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0
2.5°	2351.2	2344.3	2340.8	2340.8	2337.4	2333.9	2330.4	2326.9	2320.0	2320.0	2313.1
5°	2368.6	2361.7	2358.2	2347.8	2340.8	2340.8	2326.9	2323.5	2313.1	2306.1	2299.2
7.5°	2382.5	2368.6	2358.2	2347.8	2340.8	2333.9	2320.0	2306.1	2292.3	2278.4	2271.5
10°	2382.5	2368.6	2351.2	2333.9	2326.9	2320.0	2302.6	2281.8	2264.6	2250.6	2233.3
12.5°	2375.5	2354.7	2333.9	2320.0	2306.1	2295.7	2274.9	2254.1	2233.3	2205.5	2191.7
15°	2354.7	2326.9	2306.1	2281.8	2271.5	2254.1	2236.8	2205.5	2181.3	2157.0	2139.7
17.5°	2313.1	2278.4	2254.1	2229.8	2212.6	2202.1	2174.4	2146.6	2118.9	2091.2	2070.4
20°	2250.6	2219.5	2191.7	2160.4	2146.6	2132.7	2098.1	2070.4	2042.6	2011.3	1990.5
22.5°	2174.4	2143.2	2105.0	2080.7	2059.9	2042.6	2011.3	1980.2	1952.4	1924.7	1897.0
25°	2080.7	2049.5	2014.8	1976.7	1962.8	1945.5	1910.8	1879.6	1848.4	1817.1	1792.9
27.5°	1980.2	1938.5	1910.8	1869.3	1855.3	1838.0	1799.9	1765.1	1737.4	1713.1	1685.4
30°	1858.8	1827.6	1789.4	1751.3	1737.4	1720.0	1688.8	1657.7	1629.9	1602.2	1574.4
32.5°	1727.0	1695.8	1657.7	1629.9	1609.1	1595.2	1564.0	1536.3	1508.6	1480.8	1456.6
35°	1588.3	1553.7	1525.8	1498.1	1480.8	1463.5	1432.3	1408.0	1387.2	1362.9	1338.6
37.5°	1446.1	1421.8	1394.1	1362.9	1345.5	1331.7	1307.5	1279.6	1262.4	1241.5	1224.2
40°	1307.5	1279.6	1255.3	1227.6	1213.8	1203.3	1179.1	1158.2	1141.0	1123.6	1113.2
42.5°	1165.2	1141.0	1116.7	1099.3	1089.0	1078.5	1061.1	1036.8	1026.5	1009.1	998.8
45°	1033.4	1012.6	995.3	971.0	964.0	957.1	936.3	919.0	908.6	898.2	891.2
47.5°	908.6	894.8	873.9	860.0	849.7	842.8	828.8	814.9	804.6	797.7	790.6
50°	801.1	783.7	769.9	756.0	749.1	738.6	724.8	717.8	710.9	704.0	704.0
52.5°	700.6	683.2	669.3	658.9	652.0	645.0	634.6	631.2	624.3	624.3	620.7
55°	606.9	596.4	582.6	568.7	565.2	561.8	554.9	547.9	544.4	541.0	544.4
57.5°	527.2	516.7	502.9	492.4	489.0	485.5	482.1	475.0	471.6	471.6	471.6
60°	454.3	443.9	433.5	423.0	423.0	416.1	412.7	409.2	405.8	402.2	402.2
62.5°	388.4	377.9	367.6	360.7	357.2	353.7	346.8	343.3	339.9	339.9	336.4
65°	329.4	315.6	312.1	301.7	298.2	294.8	291.3	284.4	281.0	277.4	273.9
67.5°	270.5	263.6	253.1	246.2	242.8	239.3	235.9	228.8	225.4	221.9	215.0
70°	218.5	211.6	204.6	197.7	194.2	190.8	183.9	176.8	173.4	166.5	156.0
72.5°	169.9	163.0	156.0	149.1	145.7	142.2	135.3	128.3	121.4	114.5	107.5
75°	128.3	121.4	111.0	104.0	100.6	100.6	90.2	83.2	76.3	65.9	58.9
77.5°	90.2	79.7	76.3	69.4	65.9	58.9	52.0	45.1	38.2	34.6	27.7
80°	58.9	52.0	45.1	41.6	38.2	34.6	31.2	24.3	17.4	13.9	10.4
82.5°	34.6	31.2	27.7	24.3	20.8	17.4	13.9	13.9	10.4	6.9	3.5
85°	17.4	13.9	10.4	10.4	6.9	6.9	6.9	3.5	3.5	3.5	3.5
87.5°	6.9	3.5	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593734

CATALOG NUMBER: HCC8S40D010SL-HM82555850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0
2.5°	2309.7	2306.1	2302.6	2299.2	2299.2	2292.3	2292.3	2288.8	2281.8	2278.4	2278.4
5°	2288.8	2278.4	2271.5	2268.0	2264.6	2254.1	2250.6	2243.7	2236.8	2229.8	2226.4
7.5°	2257.5	2240.3	2233.3	2229.8	2219.5	2209.0	2202.1	2191.7	2181.3	2170.9	2167.5
10°	2219.5	2202.1	2184.7	2177.8	2167.5	2160.4	2146.6	2132.7	2122.4	2111.9	2101.5
12.5°	2170.9	2150.1	2132.7	2125.8	2115.5	2101.5	2080.7	2073.8	2056.4	2049.5	2035.6
15°	2115.5	2091.2	2073.8	2063.3	2053.0	2032.2	2018.4	2004.4	1987.1	1980.2	1966.4
17.5°	2046.1	2018.4	2001.0	1990.5	1983.6	1966.4	1945.5	1928.2	1910.8	1903.9	1893.5
20°	1962.8	1945.5	1921.3	1910.8	1903.9	1883.1	1862.2	1855.3	1841.4	1827.6	1817.1
22.5°	1869.3	1851.9	1827.6	1817.1	1813.7	1796.4	1779.0	1768.6	1758.2	1747.9	1737.4
25°	1772.1	1751.3	1730.5	1723.6	1716.6	1702.8	1688.8	1681.9	1671.5	1664.6	1657.7
27.5°	1668.0	1647.2	1629.9	1619.5	1612.6	1602.2	1595.2	1588.3	1581.4	1574.4	1570.9
30°	1557.1	1536.3	1522.4	1515.5	1508.6	1505.1	1494.6	1491.2	1487.7	1480.8	1484.3
32.5°	1446.1	1428.7	1414.9	1404.6	1404.6	1397.5	1394.1	1394.1	1390.6	1390.6	1390.6
35°	1324.7	1314.4	1303.9	1300.4	1297.0	1293.5	1290.1	1293.5	1290.1	1293.5	1297.0
37.5°	1213.8	1203.3	1196.4	1193.0	1189.5	1193.0	1189.5	1189.5	1193.0	1199.9	1203.3
40°	1099.3	1092.4	1085.4	1089.0	1085.4	1085.4	1085.4	1095.9	1099.3	1102.8	1106.2
42.5°	991.9	984.8	981.4	981.4	984.8	981.4	988.3	991.9	998.8	1009.1	1016.1
45°	887.7	884.3	884.3	887.7	884.3	891.2	891.2	898.2	908.6	915.5	922.5
47.5°	790.6	790.6	790.6	794.2	794.2	797.7	804.6	808.0	814.9	821.9	828.8
50°	700.6	704.0	707.5	707.5	707.5	714.4	721.4	724.8	728.3	731.7	742.1
52.5°	620.7	624.3	624.3	627.7	631.2	634.6	638.1	645.0	648.6	655.5	658.9
55°	544.4	544.4	551.4	554.9	554.9	554.9	561.8	561.8	568.7	572.2	579.2
57.5°	471.6	475.0	475.0	478.6	478.6	482.1	485.5	489.0	492.4	495.9	499.3
60°	402.2	402.2	402.2	405.8	409.2	412.7	409.2	416.1	416.1	423.0	426.5
62.5°	336.4	339.9	339.9	339.9	339.9	339.9	339.9	343.3	346.8	350.2	353.7
65°	273.9	273.9	273.9	270.5	273.9	270.5	273.9	277.4	277.4	281.0	284.4
67.5°	211.6	211.6	204.6	204.6	208.1	208.1	208.1	208.1	204.6	211.6	211.6
70°	152.6	149.1	145.7	142.2	142.2	138.8	138.8	135.3	135.3	135.3	135.3
72.5°	100.6	93.7	86.8	83.2	79.7	79.7	72.8	69.4	72.8	72.8	72.8
75°	52.0	45.1	41.6	38.2	34.6	34.6	31.2	31.2	31.2	31.2	31.2
77.5°	20.8	17.4	13.9	13.9	10.4	10.4	10.4	10.4	10.4	10.4	10.4
80°	6.9	6.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	3.5	0.0	0.0	3.5	0.0	3.5	3.5	3.5	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593734

CATALOG NUMBER: HCC8S40D010SL-HM82555850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0	2320.0
2.5°	2274.9	2274.9	2271.5	2274.9	2268.0	2271.5	2268.0	2268.0
5°	2222.9	2216.0	2216.0	2216.0	2212.6	2212.6	2209.0	2209.0
7.5°	2160.4	2157.0	2153.5	2150.1	2146.6	2143.2	2143.2	2143.2
10°	2098.1	2091.2	2091.2	2087.6	2080.7	2077.3	2077.3	2077.3
12.5°	2025.3	2021.8	2018.4	2018.4	2004.4	2007.9	2004.4	2004.4
15°	1955.9	1952.4	1952.4	1942.1	1935.1	1935.1	1935.1	1931.6
17.5°	1883.1	1879.6	1876.2	1869.3	1862.2	1862.2	1858.8	1862.2
20°	1806.8	1803.3	1796.4	1796.4	1792.9	1789.4	1782.5	1786.0
22.5°	1730.5	1723.6	1720.0	1720.0	1716.6	1716.6	1709.7	1709.7
25°	1650.8	1647.2	1643.7	1647.2	1640.3	1640.3	1633.4	1633.4
27.5°	1567.5	1564.0	1564.0	1564.0	1560.6	1564.0	1560.6	1560.6
30°	1484.3	1484.3	1480.8	1480.8	1484.3	1480.8	1484.3	1487.7
32.5°	1394.1	1394.1	1397.5	1397.5	1401.0	1401.0	1401.0	1401.0
35°	1300.4	1307.5	1307.5	1310.9	1314.4	1317.8	1317.8	1321.3
37.5°	1213.8	1217.3	1220.7	1224.2	1231.1	1231.1	1231.1	1231.1
40°	1120.1	1123.6	1130.5	1127.0	1141.0	1144.4	1141.0	1141.0
42.5°	1023.0	1029.9	1033.4	1040.4	1043.9	1050.8	1054.2	1054.2
45°	932.8	936.3	943.3	950.2	953.7	964.0	964.0	964.0
47.5°	839.2	846.2	849.7	856.6	860.0	870.5	873.9	870.5
50°	749.1	756.0	762.9	762.9	773.4	776.8	783.7	787.2
52.5°	662.4	665.8	672.8	676.3	683.2	690.1	693.5	697.1
55°	579.2	582.6	589.5	589.5	600.0	603.4	610.4	610.4
57.5°	502.9	506.3	513.2	509.8	516.7	523.6	523.6	520.1
60°	430.1	430.1	430.1	437.0	440.4	443.9	447.3	447.3
62.5°	353.7	360.7	364.1	364.1	367.6	371.0	371.0	367.6
65°	284.4	291.3	294.8	294.8	298.2	298.2	298.2	301.7
67.5°	215.0	215.0	215.0	218.5	215.0	215.0	215.0	215.0
70°	135.3	135.3	135.3	135.3	131.7	135.3	135.3	138.8
72.5°	72.8	72.8	72.8	72.8	72.8	72.8	72.8	72.8
75°	31.2	31.2	31.2	34.6	31.2	31.2	31.2	31.2
77.5°	13.9	10.4	13.9	13.9	10.4	10.4	10.4	10.4
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	0.0	3.5	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)