

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584608

Luminaire Tested: **HCC8W40D010MB-HM82555930-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584608  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W40D010MB-HM82555930-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4206.0 lumens  
Efficiency: N/A  
Efficacy: 102.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584608  
CATALOG NUMBER: HCC8W40D010MB-HM82555930-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584608

CATALOG NUMBER: HCC8W40D010MB-HM82555930-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	64485	64485	64485
5°	66848	64273	62069
10°	68736	63714	59527
15°	70268	62587	56898
20°	70379	60144	54588
25°	69028	56803	52656
30°	65474	52673	50348
35°	59489	47974	48083
40°	52016	43044	45322
45°	45083	38346	42231
50°	39477	34061	38479
55°	35133	30182	34816
60°	31687	27111	30596
65°	28610	23845	26654
70°	25704	20088	19817
75°	22661	15917	14857
80°	19001	13194	14242
85°	14683	11569	12631

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584608

CATALOG NUMBER: HCC8W40D010MB-HM82555930-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	197.3	4.7
10°-20°	555.7	13.2
20°-30°	794.1	18.9
30°-40°	843.8	20.1
40°-50°	726.5	17.3
50°-60°	543.2	12.9
60°-70°	346.4	8.2
70°-80°	157.7	3.7
80°-90°	41.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1547.1	36.8
0°-40°	2390.9	56.8
0°-60°	3660.5	87.0
0°-90°	4206.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4206.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2091	2091	2091	2091	2091	
5°	2160	2130	2076	2023	2005	207
15°	2201	2127	1960	1827	1782	620
25°	2029	1901	1670	1568	1548	929
35°	1580	1470	1274	1242	1277	984
45°	1034	977	879	903	968	804
55°	654	600	561	609	648	588
65°	392	348	327	342	365	391
75°	190	163	134	122	125	202
85°	42	36	33	36	36	50
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584608

CATALOG NUMBER: HCC8W40D010MB-HM82555930-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2
2.5°	2129.9	2123.9	2126.9	2123.9	2126.9	2126.9	2120.9	2120.9	2120.9	2120.9	2112.0
5°	2159.6	2156.6	2156.6	2153.7	2150.7	2153.7	2150.7	2147.7	2141.8	2138.8	2129.9
7.5°	2177.3	2177.3	2177.3	2177.3	2174.4	2171.4	2168.4	2162.6	2156.6	2150.7	2144.7
10°	2195.2	2198.2	2195.2	2192.2	2189.2	2183.3	2180.3	2174.4	2165.6	2156.6	2150.7
12.5°	2204.1	2204.1	2201.1	2201.1	2195.2	2192.2	2183.3	2174.4	2165.6	2156.6	2141.8
15°	2201.1	2201.1	2198.2	2195.2	2186.3	2183.3	2177.3	2168.4	2153.7	2141.8	2126.9
17.5°	2183.3	2180.3	2174.4	2174.4	2162.6	2159.6	2153.7	2141.8	2126.9	2109.0	2091.2
20°	2144.7	2144.7	2141.8	2138.8	2126.9	2118.0	2112.0	2097.1	2085.4	2064.5	2046.7
22.5°	2091.2	2097.1	2091.2	2085.4	2070.5	2067.5	2058.6	2040.7	2022.9	1999.2	1978.4
25°	2028.8	2025.9	2022.9	2016.9	2005.2	1999.2	1987.3	1969.4	1951.6	1924.9	1901.1
27.5°	1948.6	1936.7	1936.7	1924.9	1916.0	1907.1	1901.1	1883.3	1859.5	1838.8	1809.0
30°	1838.8	1841.8	1826.9	1823.9	1809.0	1803.1	1791.2	1773.3	1752.6	1728.8	1705.0
32.5°	1719.9	1711.0	1711.0	1699.1	1687.3	1678.4	1675.4	1654.6	1636.7	1613.0	1589.2
35°	1580.3	1580.3	1571.4	1568.4	1556.5	1550.6	1541.6	1529.9	1509.0	1488.2	1470.4
37.5°	1443.7	1437.8	1434.8	1428.8	1419.9	1411.0	1411.0	1390.2	1387.2	1363.5	1339.7
40°	1292.2	1298.2	1292.2	1283.3	1280.3	1274.4	1271.4	1259.5	1250.6	1229.7	1215.0
42.5°	1164.4	1158.5	1158.5	1155.5	1143.6	1143.6	1137.8	1131.8	1116.9	1111.0	1093.1
45°	1033.8	1039.7	1030.8	1033.8	1021.9	1021.9	1021.9	1010.0	998.1	989.1	977.3
47.5°	920.8	923.8	923.8	914.9	911.9	911.9	905.9	900.1	891.2	879.3	870.4
50°	822.9	825.9	819.9	816.9	811.0	808.0	808.0	796.1	790.2	778.3	772.3
52.5°	733.8	733.8	730.8	730.8	721.9	721.9	715.9	707.0	701.0	695.1	680.2
55°	653.5	653.5	650.6	647.6	647.6	638.7	635.7	626.8	620.8	608.9	600.0
57.5°	576.3	579.3	576.3	573.3	570.4	567.4	561.4	552.5	546.6	537.6	531.7
60°	513.8	513.8	511.0	508.0	502.1	499.1	496.1	490.2	481.2	475.3	466.4
62.5°	454.5	451.5	448.5	445.5	439.6	439.6	433.6	427.8	418.9	412.9	407.0
65°	392.1	392.1	389.1	389.1	386.2	380.2	377.2	374.3	362.4	359.4	347.6
67.5°	335.7	338.7	332.7	332.7	326.8	326.8	323.8	314.9	311.9	305.9	300.0
70°	285.1	285.1	285.1	282.1	276.2	273.3	270.4	264.4	261.4	255.5	249.5
72.5°	234.7	234.7	231.7	231.7	228.7	225.7	222.8	216.8	216.8	210.9	204.9
75°	190.2	190.2	187.2	184.2	181.2	181.2	178.3	175.3	169.3	166.4	163.4
77.5°	145.5	145.5	145.5	142.6	139.6	139.6	139.6	133.6	127.7	127.7	124.7
80°	107.0	107.0	104.0	104.0	101.0	101.0	101.0	98.1	95.1	92.1	89.1
82.5°	71.3	71.3	71.3	71.3	68.3	68.3	68.3	65.3	62.4	62.4	62.4
85°	41.5	41.5	41.5	41.5	38.7	38.7	38.7	38.7	38.7	35.7	35.7
87.5°	17.8	14.9	17.8	14.9	17.8	14.9	17.8	14.9	14.9	14.9	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584608

CATALOG NUMBER: HCC8W40D010MB-HM82555930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2
2.5°	2115.0	2112.0	2109.0	2106.1	2106.1	2103.1	2097.1	2094.2	2091.2	2088.2	2088.2
5°	2126.9	2123.9	2118.0	2112.0	2109.0	2103.1	2097.1	2091.2	2085.4	2076.4	2073.5
7.5°	2135.8	2126.9	2120.9	2109.0	2106.1	2100.1	2091.2	2082.4	2070.5	2058.6	2049.7
10°	2135.8	2123.9	2115.0	2100.1	2094.2	2088.2	2076.4	2061.6	2046.7	2034.8	2019.9
12.5°	2129.9	2115.0	2100.1	2085.4	2076.4	2067.5	2049.7	2034.8	2016.9	1999.2	1987.3
15°	2109.0	2091.2	2073.5	2055.6	2046.7	2034.8	2016.9	1996.2	1978.4	1960.5	1939.7
17.5°	2070.5	2052.6	2031.8	2011.0	1999.2	1990.3	1963.5	1948.6	1922.0	1904.1	1886.3
20°	2019.9	1999.2	1972.4	1951.6	1936.7	1927.9	1907.1	1880.3	1859.5	1832.8	1815.0
22.5°	1954.6	1927.9	1901.1	1880.3	1865.4	1853.5	1826.9	1800.1	1782.3	1758.6	1737.8
25°	1877.3	1850.7	1823.9	1794.2	1779.3	1767.5	1743.7	1719.9	1696.1	1669.5	1651.6
27.5°	1785.2	1755.6	1731.8	1705.0	1690.3	1672.4	1645.7	1621.9	1598.2	1580.3	1556.5
30°	1684.3	1651.6	1627.8	1601.1	1586.3	1571.4	1544.6	1520.9	1500.1	1479.3	1467.4
32.5°	1562.5	1538.7	1515.0	1488.2	1476.3	1467.4	1440.7	1416.9	1393.1	1375.4	1366.5
35°	1446.7	1419.9	1399.1	1375.4	1360.5	1351.6	1327.8	1307.0	1295.2	1274.4	1262.5
37.5°	1324.8	1304.0	1280.3	1256.5	1247.6	1238.7	1220.9	1200.1	1182.3	1167.4	1161.4
40°	1197.1	1179.3	1158.5	1143.6	1134.8	1125.9	1111.0	1096.1	1084.2	1069.3	1063.4
42.5°	1075.3	1063.4	1045.7	1027.8	1018.9	1015.9	998.1	986.2	980.3	974.4	968.4
45°	965.4	947.6	935.7	923.8	914.9	908.9	900.1	891.2	885.2	879.3	873.3
47.5°	858.5	843.6	831.7	822.9	814.0	811.0	805.0	796.1	790.2	790.2	790.2
50°	760.4	748.5	736.7	730.8	727.8	721.9	715.9	712.9	710.0	710.0	710.0
52.5°	674.3	662.5	653.5	647.6	647.6	641.6	635.7	632.7	632.7	632.7	632.7
55°	594.0	585.2	579.3	573.3	567.4	564.4	564.4	564.4	561.4	561.4	564.4
57.5°	522.8	516.8	508.0	502.1	499.1	499.1	496.1	493.1	496.1	499.1	502.1
60°	457.4	451.5	448.5	439.6	439.6	439.6	436.6	436.6	436.6	439.6	442.6
62.5°	398.1	395.1	389.1	386.2	383.2	383.2	380.2	380.2	380.2	380.2	383.2
65°	344.6	338.7	332.7	332.7	332.7	329.7	329.7	323.8	326.8	326.8	323.8
67.5°	294.0	288.1	285.1	282.1	279.2	279.2	276.2	273.3	270.4	270.4	270.4
70°	246.6	240.6	240.6	234.7	234.7	231.7	228.7	228.7	225.7	222.8	219.8
72.5°	199.0	196.1	193.1	190.2	190.2	190.2	187.2	184.2	181.2	178.3	172.3
75°	157.4	157.4	151.5	148.5	148.5	145.5	142.6	139.6	136.6	133.6	130.7
77.5°	121.7	118.8	112.9	110.0	110.0	110.0	107.0	104.0	101.0	98.1	95.1
80°	89.1	86.2	83.2	80.2	80.2	80.2	77.2	77.2	74.3	74.3	74.3
82.5°	59.4	59.4	56.4	56.4	56.4	56.4	53.4	53.4	53.4	53.4	53.4
85°	35.7	35.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7
87.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584608

CATALOG NUMBER: HCC8W40D010MB-HM82555930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2
2.5°	2082.4	2082.4	2076.4	2073.5	2070.5	2073.5	2067.5	2064.5	2061.6	2061.6	2058.6
5°	2064.5	2061.6	2049.7	2046.7	2043.7	2040.7	2034.8	2028.8	2022.9	2019.9	2016.9
7.5°	2040.7	2031.8	2019.9	2016.9	2014.0	2005.2	1996.2	1990.3	1981.4	1978.4	1972.4
10°	2008.1	1996.2	1987.3	1978.4	1972.4	1963.5	1954.6	1945.6	1933.8	1930.8	1922.0
12.5°	1969.4	1954.6	1936.7	1933.8	1924.9	1913.0	1901.1	1892.2	1883.3	1877.3	1868.4
15°	1922.0	1907.1	1889.2	1880.3	1871.4	1862.5	1847.7	1835.8	1826.9	1818.0	1809.0
17.5°	1865.4	1847.7	1832.8	1823.9	1818.0	1803.1	1791.2	1776.3	1767.5	1758.6	1749.7
20°	1797.1	1782.3	1761.6	1752.6	1749.7	1737.8	1722.9	1716.9	1705.0	1696.1	1690.3
22.5°	1719.9	1705.0	1687.3	1681.4	1669.5	1663.5	1648.6	1642.7	1636.7	1627.8	1624.8
25°	1633.8	1618.9	1604.1	1601.1	1592.2	1586.3	1577.3	1568.4	1568.4	1559.5	1559.5
27.5°	1544.6	1529.9	1518.0	1512.0	1509.0	1503.1	1494.2	1491.2	1488.2	1485.2	1485.2
30°	1449.7	1431.8	1425.9	1422.9	1419.9	1414.0	1411.0	1405.0	1408.0	1411.0	1408.0
32.5°	1348.6	1342.7	1330.8	1324.8	1327.8	1324.8	1318.9	1324.8	1321.9	1327.8	1330.8
35°	1250.6	1244.6	1238.7	1238.7	1232.7	1232.7	1232.7	1235.7	1241.6	1244.6	1250.6
37.5°	1155.5	1146.6	1143.6	1140.7	1143.6	1143.6	1143.6	1149.5	1155.5	1161.4	1170.4
40°	1054.6	1048.6	1048.6	1048.6	1048.6	1057.6	1054.6	1060.5	1066.4	1075.3	1084.2
42.5°	959.5	959.5	962.5	962.5	962.5	962.5	968.4	977.3	986.2	995.1	1004.0
45°	870.4	870.4	870.4	876.3	876.3	879.3	891.2	897.1	903.1	911.9	920.8
47.5°	787.2	787.2	790.2	793.1	796.1	802.1	808.0	816.9	825.9	831.7	840.6
50°	710.0	712.9	718.9	724.8	724.8	727.8	736.7	742.7	748.5	757.4	760.4
52.5°	635.7	641.6	647.6	650.6	653.5	659.5	662.5	671.3	674.3	683.2	686.2
55°	567.4	570.4	579.3	582.3	582.3	588.2	594.0	600.0	608.9	608.9	614.9
57.5°	505.0	508.0	513.8	516.8	513.8	522.8	525.7	531.7	534.7	540.6	543.6
60°	442.6	448.5	451.5	451.5	454.5	457.4	463.4	463.4	469.3	475.3	475.3
62.5°	383.2	386.2	389.1	392.1	395.1	392.1	401.0	401.0	407.0	410.0	415.9
65°	326.8	329.7	329.7	332.7	332.7	335.7	335.7	338.7	341.6	347.6	350.6
67.5°	270.4	270.4	270.4	273.3	270.4	273.3	273.3	276.2	276.2	282.1	285.1
70°	219.8	216.8	213.8	213.8	213.8	213.8	210.9	213.8	213.8	216.8	216.8
72.5°	169.3	166.4	163.4	160.4	160.4	157.4	154.5	157.4	157.4	160.4	160.4
75°	127.7	121.7	121.7	121.7	118.8	118.8	118.8	121.7	121.7	121.7	124.7
77.5°	95.1	95.1	92.1	92.1	92.1	95.1	95.1	98.1	98.1	98.1	98.1
80°	71.3	74.3	74.3	74.3	74.3	77.2	77.2	77.2	77.2	80.2	80.2
82.5°	53.4	53.4	53.4	53.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4
85°	32.7	35.7	35.7	32.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7
87.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584608

CATALOG NUMBER: HCC8W40D010MB-HM82555930-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2	2091.2
2.5°	2055.6	2055.6	2055.6	2055.6	2052.6	2052.6	2052.6	2049.7
5°	2011.0	2011.0	2011.0	2005.2	2008.1	2008.1	2002.2	2005.2
7.5°	1966.5	1963.5	1960.5	1960.5	1957.6	1954.6	1951.6	1954.6
10°	1916.0	1907.1	1907.1	1904.1	1904.1	1898.2	1898.2	1901.1
12.5°	1859.5	1853.5	1853.5	1850.7	1847.7	1844.7	1841.8	1841.8
15°	1803.1	1797.1	1794.2	1791.2	1788.2	1782.3	1785.2	1782.3
17.5°	1746.7	1737.8	1737.8	1734.8	1731.8	1725.9	1725.9	1722.9
20°	1681.4	1678.4	1672.4	1675.4	1672.4	1666.5	1663.5	1663.5
22.5°	1615.9	1615.9	1613.0	1613.0	1610.1	1607.1	1604.1	1604.1
25°	1553.5	1550.6	1553.5	1553.5	1544.6	1544.6	1544.6	1547.6
27.5°	1482.3	1485.2	1482.3	1482.3	1482.3	1482.3	1485.2	1482.3
30°	1411.0	1411.0	1411.0	1414.0	1419.9	1416.9	1416.9	1414.0
32.5°	1333.8	1336.7	1336.7	1339.7	1342.7	1348.6	1348.6	1351.6
35°	1256.5	1262.5	1265.4	1262.5	1271.4	1271.4	1277.3	1277.3
37.5°	1176.3	1179.3	1185.2	1188.2	1194.2	1197.1	1200.1	1200.1
40°	1090.2	1102.1	1105.0	1108.0	1116.9	1116.9	1119.9	1125.9
42.5°	1010.0	1021.9	1024.8	1027.8	1033.8	1042.7	1039.7	1045.7
45°	932.7	941.6	944.6	947.6	956.5	959.5	959.5	968.4
47.5°	849.5	855.5	858.5	864.4	870.4	876.3	882.3	879.3
50°	766.4	775.3	781.2	784.2	793.1	796.1	799.1	802.1
52.5°	692.1	698.1	701.0	704.0	712.9	715.9	718.9	724.8
55°	620.8	623.8	629.7	626.8	635.7	638.7	641.6	647.6
57.5°	549.5	552.5	555.5	555.5	561.4	567.4	570.4	573.3
60°	481.2	487.2	490.2	490.2	490.2	496.1	496.1	496.1
62.5°	418.9	418.9	421.9	421.9	427.8	427.8	427.8	427.8
65°	353.5	356.4	359.4	359.4	365.3	362.4	368.3	365.3
67.5°	285.1	285.1	291.1	291.1	288.1	291.1	291.1	291.1
70°	216.8	216.8	219.8	219.8	219.8	219.8	219.8	219.8
72.5°	160.4	160.4	160.4	163.4	160.4	160.4	163.4	160.4
75°	124.7	124.7	124.7	124.7	124.7	124.7	124.7	124.7
77.5°	98.1	98.1	101.0	101.0	101.0	101.0	101.0	101.0
80°	80.2	80.2	80.2	80.2	83.2	80.2	80.2	80.2
82.5°	59.4	56.4	59.4	56.4	59.4	59.4	59.4	59.4
85°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7
87.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)