

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584624

Luminaire Tested: **HCC8W40D010MW-HM82555935-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584624
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010MW-HM82555935-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4061.4 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584624
CATALOG NUMBER: HCC8W40D010MW-HM82555935-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584624

CATALOG NUMBER: HCC8W40D010MW-HM82555935-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	67861	67861	67861
5°	70244	67471	64793
10°	71805	66288	61146
15°	72825	64059	57099
20°	72607	60945	53010
25°	70811	56997	48665
30°	67087	52413	44654
35°	61036	47435	40577
40°	53606	42186	36659
45°	46749	37111	32685
50°	40681	32516	28793
55°	36278	28574	25042
60°	32964	25045	21363
65°	29631	21787	19387
70°	26381	18573	17500
75°	23126	15655	14940
80°	19605	12715	13247
85°	14789	9517	10579

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584624

CATALOG NUMBER: HCC8W40D010MW-HM82555935-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.1	5.1
10°-20°	567.9	14.0
20°-30°	788.3	19.4
30°-40°	815.1	20.1
40°-50°	682.5	16.8
50°-60°	495.4	12.2
60°-70°	312.7	7.7
70°-80°	154.9	3.8
80°-90°	38.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1562.4	38.5
0°-40°	2377.5	58.5
0°-60°	3555.4	87.5
0°-90°	4061.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4061.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2201	2201	2201	2201	2201	
5°	2269	2242	2180	2120	2093	217
15°	2281	2195	2007	1845	1789	642
25°	2081	1947	1675	1493	1430	954
35°	1621	1502	1260	1117	1078	1010
45°	1072	994	851	767	750	829
55°	675	615	532	487	466	609
65°	406	355	299	263	266	405
75°	194	161	131	125	125	208
85°	42	33	27	30	30	51
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584624

CATALOG NUMBER: HCC8W40D010MW-HM82555935-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7
2.5°	2236.5	2236.5	2239.5	2236.5	2236.5	2236.5	2233.5	2233.5	2230.5	2230.5	2224.6
5°	2269.3	2263.4	2269.3	2263.4	2263.4	2263.4	2260.4	2254.5	2251.5	2245.4	2242.4
7.5°	2284.3	2281.2	2281.2	2278.3	2278.3	2275.3	2272.3	2269.3	2257.4	2254.5	2245.4
10°	2293.2	2290.3	2290.3	2287.3	2281.2	2281.2	2275.3	2272.3	2257.4	2251.5	2239.5
12.5°	2290.3	2290.3	2290.3	2287.3	2278.3	2275.3	2269.3	2260.4	2248.4	2236.5	2224.6
15°	2281.2	2281.2	2275.3	2272.3	2263.4	2257.4	2254.5	2239.5	2227.6	2212.6	2194.7
17.5°	2251.5	2251.5	2248.4	2242.4	2233.5	2227.6	2221.6	2206.6	2194.7	2170.8	2152.9
20°	2212.6	2209.6	2206.6	2197.7	2188.8	2185.8	2176.7	2155.9	2140.9	2123.1	2099.2
22.5°	2155.9	2152.9	2149.9	2143.9	2129.0	2123.1	2117.0	2102.1	2075.2	2057.4	2027.5
25°	2081.2	2081.2	2075.2	2066.3	2051.3	2045.4	2036.4	2021.5	1997.7	1970.8	1946.8
27.5°	1994.7	1991.7	1982.7	1976.7	1964.8	1955.8	1940.9	1922.9	1899.1	1878.2	1848.3
30°	1884.1	1884.1	1878.2	1869.3	1854.3	1848.3	1836.4	1815.5	1791.5	1764.8	1743.8
32.5°	1758.7	1758.7	1749.8	1743.8	1734.9	1719.9	1716.9	1693.0	1672.2	1651.2	1627.3
35°	1621.4	1624.4	1618.4	1606.5	1591.5	1591.5	1585.6	1564.6	1540.8	1519.9	1501.9
37.5°	1484.0	1475.1	1472.0	1466.1	1457.2	1445.3	1439.2	1430.3	1409.4	1394.4	1367.5
40°	1331.7	1334.7	1328.8	1322.8	1319.8	1310.9	1307.8	1292.9	1277.9	1260.1	1248.2
42.5°	1194.4	1194.4	1194.4	1188.5	1182.5	1173.5	1170.5	1161.6	1143.6	1131.7	1113.7
45°	1072.0	1063.0	1063.0	1060.1	1057.1	1051.0	1042.1	1036.1	1024.2	1015.2	994.4
47.5°	952.5	955.6	952.5	949.5	940.6	937.6	934.6	922.7	910.7	901.8	886.8
50°	848.0	853.9	848.0	848.0	842.0	839.1	833.1	824.1	815.2	800.3	785.3
52.5°	761.5	761.5	758.4	755.4	746.5	740.5	737.6	734.6	719.6	707.7	695.7
55°	674.8	677.8	677.8	668.9	665.9	659.9	656.9	648.0	642.0	624.0	615.1
57.5°	600.2	597.1	600.2	594.2	588.2	582.3	579.3	573.3	564.3	552.4	540.5
60°	534.5	528.5	528.5	525.5	519.6	516.6	510.6	501.7	492.7	480.8	471.8
62.5°	468.7	465.8	462.8	459.8	453.9	450.9	447.9	439.0	429.9	421.0	412.1
65°	406.1	406.1	403.1	397.1	394.1	391.2	388.2	382.2	370.2	364.3	355.3
67.5°	349.4	346.4	346.4	340.5	334.4	331.4	331.4	325.5	316.5	307.6	301.5
70°	292.6	295.6	292.6	289.6	283.7	283.7	277.7	274.7	262.8	259.8	250.9
72.5°	241.8	241.8	238.8	238.8	232.9	229.9	229.9	224.0	218.0	212.1	206.0
75°	194.1	194.1	194.1	191.1	188.1	182.2	182.2	179.2	173.1	167.2	161.2
77.5°	152.3	149.3	149.3	146.4	143.3	140.3	140.3	137.3	131.4	128.4	122.5
80°	110.4	107.5	107.5	107.5	101.5	104.5	101.5	98.5	95.6	92.6	89.6
82.5°	71.6	74.6	74.6	71.6	68.7	68.7	68.7	65.7	65.7	62.7	59.7
85°	41.8	41.8	41.8	41.8	38.8	38.8	38.8	35.8	35.8	35.8	32.8
87.5°	18.0	18.0	18.0	18.0	18.0	18.0	14.9	14.9	14.9	14.9	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584624

CATALOG NUMBER: HCC8W40D010MW-HM82555935-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7
2.5°	2224.6	2218.6	2215.5	2212.6	2212.6	2209.6	2206.6	2200.7	2200.7	2194.7	2191.7
5°	2236.5	2227.6	2221.6	2215.5	2212.6	2206.6	2200.7	2191.7	2188.8	2179.7	2170.8
7.5°	2239.5	2224.6	2218.6	2206.6	2200.7	2194.7	2182.7	2173.8	2161.9	2152.9	2140.9
10°	2227.6	2215.5	2200.7	2185.8	2182.7	2173.8	2155.9	2143.9	2129.0	2117.0	2099.2
12.5°	2209.6	2191.7	2176.7	2158.9	2149.9	2140.9	2123.1	2105.1	2084.2	2063.3	2045.4
15°	2179.7	2158.9	2138.0	2117.0	2105.1	2096.2	2075.2	2054.3	2033.5	2006.6	1988.6
17.5°	2135.0	2111.1	2090.2	2063.3	2051.3	2042.4	2015.5	1991.7	1964.8	1937.9	1919.9
20°	2078.2	2048.3	2024.5	1994.7	1985.6	1970.8	1943.9	1917.0	1887.1	1857.2	1836.4
22.5°	2003.6	1973.7	1946.8	1917.0	1902.1	1887.1	1860.2	1827.4	1797.6	1773.7	1752.8
25°	1917.0	1890.1	1857.2	1830.5	1812.5	1794.5	1764.8	1737.9	1711.0	1675.2	1654.2
27.5°	1821.4	1788.6	1764.8	1728.8	1711.0	1699.1	1666.1	1630.3	1606.5	1573.7	1549.7
30°	1714.0	1684.1	1657.2	1621.4	1603.5	1591.5	1561.6	1528.8	1505.0	1472.0	1448.2
32.5°	1600.4	1567.6	1534.7	1510.9	1490.0	1478.1	1445.3	1424.3	1394.4	1367.5	1340.7
35°	1478.1	1445.3	1421.3	1388.5	1376.6	1364.6	1337.7	1310.9	1284.0	1260.1	1239.1
37.5°	1346.7	1322.8	1295.9	1272.0	1263.1	1251.2	1218.3	1194.4	1173.5	1149.7	1131.7
40°	1218.3	1197.4	1179.4	1155.6	1140.6	1131.7	1107.8	1086.9	1063.0	1048.0	1030.2
42.5°	1101.8	1077.9	1060.1	1042.1	1027.2	1018.2	997.3	982.3	964.5	949.5	928.7
45°	979.4	967.5	946.5	931.7	922.7	910.7	895.8	877.9	863.0	851.0	836.1
47.5°	871.9	860.0	845.0	827.2	821.1	812.2	797.3	785.3	773.4	761.5	746.5
50°	773.4	758.4	746.5	734.6	728.6	719.6	704.7	698.8	689.7	677.8	668.9
52.5°	683.8	671.9	659.9	645.0	642.0	636.1	627.0	615.1	606.2	600.2	594.2
55°	603.2	591.2	582.3	570.4	567.4	561.3	549.4	543.5	537.5	531.5	525.5
57.5°	531.5	519.6	507.7	501.7	495.6	489.7	486.7	477.8	471.8	468.7	462.8
60°	465.8	453.9	444.9	435.9	432.9	429.9	424.0	418.0	412.1	406.1	403.1
62.5°	403.1	391.2	385.2	379.3	373.3	373.3	367.2	361.3	355.3	352.4	346.4
65°	346.4	340.5	331.4	322.5	319.5	319.5	310.6	307.6	304.5	298.6	292.6
67.5°	292.6	286.7	277.7	274.7	271.7	268.7	265.7	259.8	253.8	250.9	244.9
70°	244.9	238.8	232.9	229.9	226.9	224.0	218.0	215.0	209.0	206.0	203.0
72.5°	197.1	194.1	188.1	185.2	182.2	179.2	176.1	173.1	167.2	164.2	161.2
75°	158.3	155.3	149.3	146.4	143.3	143.3	140.3	134.4	131.4	131.4	128.4
77.5°	119.5	116.5	113.5	110.4	107.5	107.5	104.5	101.5	98.5	98.5	95.6
80°	86.6	83.7	80.6	80.6	80.6	77.6	74.6	74.6	71.6	71.6	68.7
82.5°	56.8	56.8	53.8	53.8	53.8	50.8	50.8	47.7	47.7	47.7	47.7
85°	32.8	32.8	32.8	29.9	29.9	29.9	29.9	29.9	29.9	26.9	29.9
87.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584624

CATALOG NUMBER: HCC8W40D010MW-HM82555935-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7
2.5°	2188.8	2185.8	2179.7	2179.7	2173.8	2173.8	2170.8	2167.8	2164.8	2161.9	2158.9
5°	2167.8	2155.9	2149.9	2146.9	2140.9	2138.0	2129.0	2123.1	2120.1	2114.0	2108.1
7.5°	2129.0	2117.0	2105.1	2102.1	2099.2	2087.1	2078.2	2069.3	2063.3	2057.4	2051.3
10°	2084.2	2072.3	2057.4	2051.3	2045.4	2030.5	2018.5	2009.6	1997.7	1985.6	1982.7
12.5°	2030.5	2012.5	1994.7	1988.6	1979.7	1964.8	1952.8	1937.9	1929.0	1914.0	1911.0
15°	1967.8	1946.8	1932.0	1917.0	1911.0	1896.1	1875.2	1863.3	1845.3	1839.4	1824.4
17.5°	1893.2	1872.2	1851.3	1845.3	1836.4	1815.5	1794.5	1779.6	1761.7	1752.8	1743.8
20°	1815.5	1788.6	1767.7	1761.7	1749.8	1731.9	1711.0	1696.0	1681.1	1663.1	1654.2
22.5°	1725.9	1696.0	1678.1	1663.1	1660.2	1639.3	1615.4	1603.5	1591.5	1576.6	1564.6
25°	1627.3	1600.4	1579.6	1567.6	1561.6	1543.8	1525.8	1510.9	1493.0	1484.0	1469.1
27.5°	1525.8	1508.0	1481.1	1469.1	1460.1	1445.3	1424.3	1415.4	1397.4	1385.5	1376.6
30°	1427.3	1400.4	1385.5	1370.5	1361.6	1346.7	1328.8	1319.8	1304.8	1292.9	1284.0
32.5°	1319.8	1301.9	1281.0	1275.0	1263.1	1248.2	1236.2	1221.3	1209.3	1197.4	1194.4
35°	1221.3	1197.4	1176.4	1170.5	1161.6	1146.6	1140.6	1131.7	1116.8	1113.7	1101.8
37.5°	1113.7	1101.8	1077.9	1069.0	1066.0	1054.1	1042.1	1036.1	1027.2	1018.2	1015.2
40°	1012.2	997.3	985.3	976.4	970.4	961.5	949.5	946.5	940.6	928.7	925.7
42.5°	916.7	901.8	889.8	886.8	877.9	868.9	863.0	853.9	851.0	848.0	842.0
45°	824.1	815.2	803.2	800.3	797.3	785.3	779.3	773.4	767.4	764.5	758.4
47.5°	740.5	731.6	722.6	719.6	713.6	710.7	701.7	698.8	689.7	686.7	683.8
50°	659.9	653.9	648.0	645.0	639.0	636.1	630.0	624.0	618.1	615.1	612.1
52.5°	588.2	582.3	576.3	573.3	570.4	564.3	558.3	552.4	549.4	546.4	543.5
55°	519.6	513.6	510.6	507.7	504.7	501.7	492.7	489.7	486.7	483.7	477.8
57.5°	456.8	450.9	444.9	444.9	442.0	439.0	432.9	427.0	427.0	421.0	415.1
60°	400.1	394.1	388.2	385.2	382.2	376.3	373.3	370.2	367.2	364.3	358.3
62.5°	340.5	337.4	331.4	331.4	325.5	322.5	319.5	316.5	313.6	307.6	304.5
65°	289.6	286.7	280.7	277.7	277.7	274.7	268.7	265.7	262.8	262.8	259.8
67.5°	241.8	238.8	232.9	229.9	229.9	226.9	224.0	224.0	221.0	218.0	221.0
70°	200.0	194.1	194.1	191.1	191.1	188.1	185.2	185.2	185.2	188.1	188.1
72.5°	158.3	155.3	152.3	152.3	152.3	152.3	149.3	149.3	152.3	155.3	155.3
75°	125.4	122.5	122.5	122.5	119.5	119.5	122.5	122.5	125.4	125.4	125.4
77.5°	92.6	92.6	92.6	92.6	92.6	92.6	95.6	95.6	98.5	98.5	98.5
80°	68.7	68.7	68.7	68.7	68.7	71.6	71.6	71.6	71.6	71.6	74.6
82.5°	47.7	47.7	47.7	47.7	47.7	47.7	47.7	50.8	50.8	50.8	50.8
85°	26.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584624

CATALOG NUMBER: HCC8W40D010MW-HM82555935-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7	2200.7
2.5°	2155.9	2155.9	2155.9	2158.9	2152.9	2152.9	2152.9	2152.9
5°	2105.1	2102.1	2099.2	2102.1	2096.2	2096.2	2093.2	2093.2
7.5°	2042.4	2039.4	2036.4	2036.4	2030.5	2030.5	2027.5	2024.5
10°	1973.7	1967.8	1970.8	1964.8	1961.8	1958.9	1955.8	1952.8
12.5°	1899.1	1893.2	1890.1	1884.1	1878.2	1875.2	1878.2	1872.2
15°	1818.4	1809.5	1806.5	1800.6	1794.5	1791.5	1791.5	1788.6
17.5°	1728.8	1722.9	1719.9	1714.0	1711.0	1705.0	1702.1	1699.1
20°	1645.3	1630.3	1633.3	1627.3	1624.4	1612.4	1612.4	1615.4
22.5°	1552.7	1543.8	1537.8	1531.8	1528.8	1522.8	1522.8	1519.9
25°	1460.1	1451.2	1448.2	1442.3	1439.2	1433.2	1430.3	1430.3
27.5°	1370.5	1358.6	1358.6	1352.7	1346.7	1343.7	1340.7	1337.7
30°	1275.0	1266.0	1263.1	1263.1	1260.1	1260.1	1251.2	1254.1
32.5°	1185.5	1179.4	1176.4	1170.5	1170.5	1167.5	1167.5	1158.6
35°	1095.9	1086.9	1089.9	1083.9	1080.9	1077.9	1080.9	1077.9
37.5°	1009.2	1003.3	1003.3	997.3	997.3	994.4	991.4	997.3
40°	922.7	919.6	916.7	913.7	916.7	913.7	907.7	910.7
42.5°	836.1	836.1	833.1	833.1	830.1	830.1	830.1	830.1
45°	758.4	755.4	755.4	752.4	752.4	752.4	752.4	749.5
47.5°	680.8	677.8	677.8	677.8	674.8	674.8	671.9	674.8
50°	606.2	606.2	603.2	603.2	606.2	603.2	600.2	600.2
52.5°	537.5	537.5	534.5	534.5	531.5	528.5	531.5	531.5
55°	474.8	471.8	468.7	468.7	465.8	462.8	462.8	465.8
57.5°	415.1	412.1	409.1	409.1	403.1	400.1	400.1	400.1
60°	358.3	352.4	352.4	349.4	349.4	346.4	346.4	346.4
62.5°	304.5	301.5	301.5	301.5	301.5	298.6	298.6	298.6
65°	259.8	259.8	259.8	262.8	262.8	265.7	265.7	265.7
67.5°	224.0	226.9	226.9	226.9	229.9	229.9	229.9	226.9
70°	191.1	191.1	191.1	194.1	194.1	194.1	194.1	194.1
72.5°	158.3	158.3	158.3	158.3	158.3	158.3	158.3	158.3
75°	125.4	128.4	128.4	128.4	125.4	128.4	128.4	125.4
77.5°	98.5	98.5	98.5	98.5	98.5	98.5	98.5	98.5
80°	74.6	74.6	74.6	74.6	74.6	74.6	74.6	74.6
82.5°	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8
85°	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)