

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584651

Luminaire Tested: **HCC8W45D010SL-HM82555827-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010SL-HM82555827-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4557.8 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584651
CATALOG NUMBER: HCC8W45D010SL-HM82555827-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584651

CATALOG NUMBER: HCC8W45D010SL-HM82555827-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77					77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	74972	74972	74972
5°	76379	74646	72912
10°	77572	73345	70249
15°	78351	71516	67203
20°	78055	68755	64108
25°	75996	64785	60529
30°	72378	60061	57006
35°	65358	54817	52954
40°	57422	49202	49070
45°	49562	43247	45114
50°	43142	37927	40460
55°	38251	32945	35246
60°	34130	27839	29257
65°	30769	22597	23072
70°	27327	16932	13668
75°	23554	9805	5886
80°	18149	3516	1758
85°	11676	1168	1168

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584651

CATALOG NUMBER: HCC8W45D010SL-HM82555827-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.2	5.0
10°-20°	635.4	13.9
20°-30°	898.6	19.7
30°-40°	946.9	20.8
40°-50°	804.8	17.7
50°-60°	579.5	12.7
60°-70°	334.3	7.3
70°-80°	114.4	2.5
80°-90°	15.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1762.2	38.7
0°-40°	2709.2	59.4
0°-60°	4093.4	89.8
0°-90°	4557.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4557.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2431	2431	2431	2431	2431	
5°	2468	2451	2412	2369	2356	236
15°	2454	2379	2240	2141	2105	691
25°	2234	2118	1904	1805	1779	1024
35°	1736	1634	1456	1403	1407	1081
45°	1136	1084	992	998	1034	883
55°	712	656	613	636	656	640
65°	422	362	310	303	316	419
75°	198	148	82	53	49	209
85°	33	20	3	3	3	44
90°	0	0	0	0	0	



TEST NUMBER: P584651

CATALOG NUMBER: HCC8W45D010SL-HM82555827-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3
2.5°	2454.3	2457.7	2454.3	2454.3	2451.0	2447.7	2444.4	2441.1	2434.6	2428.0	2428.0
5°	2467.5	2474.1	2467.5	2467.5	2457.7	2451.0	2444.4	2434.6	2421.4	2411.5	2411.5
7.5°	2477.4	2477.4	2477.4	2467.5	2461.0	2451.0	2434.6	2418.1	2401.6	2385.2	2378.6
10°	2477.4	2477.4	2474.1	2461.0	2454.3	2434.6	2418.1	2395.0	2371.9	2348.9	2342.4
12.5°	2467.5	2470.8	2464.2	2451.0	2434.6	2411.5	2388.5	2358.8	2332.4	2306.1	2292.9
15°	2454.3	2451.0	2444.4	2428.0	2408.2	2378.6	2355.5	2322.5	2286.3	2253.3	2240.2
17.5°	2421.4	2421.4	2411.5	2395.0	2368.6	2335.7	2299.4	2263.3	2223.8	2187.5	2171.0
20°	2378.6	2378.6	2365.4	2345.6	2319.3	2276.4	2236.9	2194.1	2148.0	2111.8	2095.2
22.5°	2316.0	2319.3	2302.8	2279.7	2250.0	2200.7	2161.1	2108.5	2062.3	2019.4	2006.3
25°	2233.6	2240.2	2223.8	2200.7	2161.1	2118.3	2068.8	2019.4	1966.8	1924.0	1904.1
27.5°	2138.0	2141.3	2124.9	2101.8	2062.3	2016.2	1966.8	1914.0	1864.6	1818.5	1798.8
30°	2032.7	2019.4	2012.9	1983.2	1940.4	1900.8	1844.9	1802.1	1749.3	1709.8	1686.8
32.5°	1884.4	1891.0	1871.2	1848.2	1815.2	1769.1	1723.0	1673.5	1624.1	1594.5	1578.0
35°	1736.2	1742.7	1732.9	1709.8	1673.5	1634.0	1587.9	1551.6	1508.8	1472.6	1456.2
37.5°	1581.3	1581.3	1574.8	1561.5	1535.2	1499.0	1452.9	1416.6	1380.4	1350.7	1340.9
40°	1426.5	1419.9	1416.6	1406.7	1383.7	1350.7	1321.0	1291.4	1255.1	1235.4	1222.3
42.5°	1274.9	1274.9	1268.4	1258.5	1235.4	1219.0	1189.3	1156.3	1130.0	1110.2	1110.2
45°	1136.5	1139.8	1130.0	1123.4	1110.2	1083.9	1057.5	1034.5	1011.4	998.2	991.7
47.5°	1014.6	1014.6	1004.8	998.2	985.0	962.0	938.9	919.2	902.6	892.8	889.5
50°	899.3	899.3	899.3	882.9	866.4	850.0	833.5	810.4	800.6	794.0	790.6
52.5°	800.6	797.3	797.3	784.0	767.6	747.8	731.4	711.5	701.7	695.1	698.4
55°	711.5	711.5	708.3	691.8	675.3	655.6	639.2	622.6	616.1	609.5	612.8
56°	675.3	675.3	672.0	658.9	639.2	622.6	602.9	586.4	576.5	579.8	579.8
57°	649.0	642.5	642.5	625.9	609.5	586.4	570.0	553.4	546.9	543.6	543.6
58°	616.1	612.8	609.5	593.0	576.5	556.7	540.3	523.9	513.9	513.9	510.6
59°	583.1	583.1	576.5	563.4	546.9	527.1	510.6	494.2	484.3	480.9	480.9
60°	553.4	556.7	546.9	533.7	520.5	497.5	477.6	464.5	454.7	451.4	451.4
61°	527.1	527.1	520.5	504.0	487.6	471.1	451.4	434.8	428.3	421.7	421.7
62°	504.0	497.5	494.2	477.6	461.2	441.4	425.0	408.6	398.6	392.0	395.3
63°	474.4	471.1	464.5	451.4	434.8	415.1	395.3	382.2	372.3	362.3	365.6
64°	451.4	448.1	438.1	425.0	408.6	388.7	369.0	355.8	349.2	339.3	336.1
65°	421.7	418.4	415.1	398.6	382.2	362.3	345.9	332.8	322.8	316.2	309.7
66°	395.3	398.6	392.0	378.9	359.1	342.6	319.5	306.4	299.8	289.8	283.3
67°	372.3	372.3	365.6	352.5	332.8	316.2	299.8	283.3	273.4	263.6	260.3
67.5°	359.1	359.1	352.5	336.1	322.8	303.1	286.6	273.4	260.3	253.7	247.0
68°	345.9	345.9	342.6	329.5	313.0	293.2	276.7	260.3	247.0	237.2	233.9
69°	322.8	326.1	319.5	306.4	289.8	270.1	253.7	240.5	227.3	217.5	210.8
70°	303.1	299.8	293.2	280.0	263.6	250.3	233.9	217.5	204.2	191.1	187.8
71°	276.7	276.7	270.1	260.3	243.7	227.3	210.8	197.7	184.5	168.0	164.7
72°	257.0	257.0	250.3	237.2	224.0	207.5	191.1	174.7	164.7	148.3	141.7
72.5°	243.7	247.0	240.5	227.3	214.2	194.4	181.2	168.0	151.6	138.4	131.7
73°	237.2	233.9	230.6	217.5	200.9	187.8	171.3	158.1	141.7	128.4	121.9



TEST NUMBER: P584651
 CATALOG NUMBER: HCC8W45D010SL-HM82555827-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	148.3	148.3	145.0	131.7	118.6	105.5	92.2	79.1	65.9	52.7	46.1
80°	102.2	105.5	98.9	92.2	82.3	69.2	56.0	46.1	33.0	26.4	19.8
82.5°	65.9	65.9	62.6	56.0	49.4	39.5	33.0	23.1	16.4	13.1	9.9
85°	33.0	36.2	33.0	29.7	23.1	19.8	16.4	9.9	6.6	3.3	3.3
87.5°	13.1	13.1	13.1	9.9	9.9	6.6	3.3	3.3	3.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584651

CATALOG NUMBER: HCC8W45D010SL-HM82555827-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3	2431.3
2.5°	2421.4	2421.4	2414.7	2411.5	2408.2	2404.9	2401.6	2398.3	2398.3	2401.6
5°	2401.6	2395.0	2381.9	2378.6	2368.6	2365.4	2358.8	2355.5	2358.8	2355.5
7.5°	2371.9	2358.8	2342.4	2335.7	2322.5	2316.0	2306.1	2306.1	2299.4	2302.8
10°	2332.4	2312.7	2292.9	2279.7	2269.9	2259.9	2253.3	2246.8	2243.5	2243.5
12.5°	2283.0	2259.9	2240.2	2220.4	2203.9	2197.4	2184.1	2184.1	2177.6	2174.3
15°	2227.1	2197.4	2174.3	2154.6	2141.3	2128.2	2118.3	2111.8	2105.1	2105.1
17.5°	2154.6	2128.2	2105.1	2082.1	2062.3	2052.4	2042.5	2032.7	2032.7	2026.0
20°	2075.5	2045.8	2026.0	2003.0	1986.5	1970.1	1956.9	1956.9	1950.2	1953.6
22.5°	1986.5	1950.2	1930.5	1914.0	1897.6	1884.4	1871.2	1871.2	1867.9	1864.6
25°	1887.7	1858.0	1834.9	1815.2	1805.4	1792.1	1788.8	1782.3	1779.0	1779.0
27.5°	1782.3	1759.1	1729.6	1719.6	1706.5	1699.9	1699.9	1696.6	1690.1	1693.3
30°	1670.2	1644.0	1627.4	1620.9	1607.7	1607.7	1604.3	1597.7	1597.7	1601.0
32.5°	1561.5	1535.2	1522.0	1518.7	1505.5	1505.5	1502.3	1505.5	1505.5	1508.8
35°	1442.9	1419.9	1416.6	1406.7	1403.4	1403.4	1403.4	1409.9	1416.6	1406.7
37.5°	1330.9	1314.5	1304.6	1301.3	1304.6	1304.6	1307.9	1317.7	1314.5	1311.2
40°	1215.6	1202.4	1195.9	1195.9	1202.4	1209.0	1209.0	1219.0	1222.3	1219.0
42.5°	1100.3	1090.4	1090.4	1093.7	1100.3	1103.7	1113.5	1123.4	1126.7	1130.0
45°	991.7	991.7	991.7	994.9	998.2	1004.8	1017.9	1027.9	1031.2	1034.5
47.5°	886.2	882.9	892.8	896.1	905.9	909.3	919.2	932.3	935.6	938.9
50°	787.3	794.0	797.3	807.1	813.7	813.7	826.8	833.5	843.4	843.4
52.5°	695.1	705.0	708.3	718.2	721.5	724.8	731.4	741.2	747.8	747.8
55°	612.8	616.1	622.6	625.9	635.8	639.2	645.7	649.0	658.9	655.6
56°	576.5	583.1	586.4	593.0	599.6	602.9	609.5	612.8	619.3	622.6
57°	543.6	546.9	556.7	560.0	566.7	566.7	570.0	579.8	579.8	583.1
58°	510.6	517.2	520.5	523.9	530.4	533.7	540.3	543.6	546.9	543.6
59°	480.9	484.3	487.6	487.6	494.2	494.2	504.0	510.6	513.9	513.9
60°	451.4	451.4	454.7	457.9	464.5	467.8	467.8	474.4	474.4	474.4
61°	421.7	421.7	425.0	428.3	431.5	431.5	438.1	438.1	441.4	444.8
62°	395.3	392.0	392.0	395.3	395.3	401.9	405.2	408.6	411.8	408.6
63°	365.6	362.3	362.3	362.3	362.3	369.0	369.0	372.3	378.9	375.6
64°	332.8	332.8	332.8	332.8	336.1	336.1	342.6	345.9	349.2	352.5
65°	309.7	303.1	299.8	299.8	303.1	306.4	309.7	313.0	316.2	316.2
66°	283.3	276.7	273.4	273.4	273.4	273.4	280.0	280.0	286.6	286.6
67°	253.7	247.0	243.7	240.5	240.5	240.5	250.3	247.0	247.0	247.0
67.5°	243.7	233.9	230.6	227.3	224.0	230.6	227.3	230.6	230.6	227.3
68°	230.6	224.0	217.5	210.8	210.8	210.8	214.2	217.5	214.2	210.8
69°	204.2	200.9	191.1	184.5	181.2	184.5	181.2	184.5	181.2	184.5
70°	181.2	171.3	161.4	158.1	154.8	154.8	154.8	151.6	154.8	151.6
71°	158.1	148.3	138.4	131.7	128.4	128.4	125.2	128.4	125.2	128.4
72°	135.0	125.2	112.0	105.5	105.5	105.5	105.5	102.2	105.5	102.2
72.5°	125.2	112.0	102.2	95.5	92.2	92.2	92.2	92.2	88.9	92.2
73°	115.3	102.2	88.9	85.6	85.6	85.6	82.3	79.1	82.3	82.3



TEST NUMBER: P584651
CATALOG NUMBER: HCC8W45D010SL-HM82555827-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	39.5	29.7	26.4	26.4	26.4	26.4	26.4	26.4	23.1	23.1
80°	16.4	13.1	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
82.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
85°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	214.2	214.2	207.5	197.7	181.2	164.7	151.6	138.4	121.9	105.5	98.9
75°	197.7	194.4	187.8	177.9	164.7	148.3	135.0	118.6	105.5	88.9	82.3

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	95.5	79.1	72.5	65.9	65.9	65.9	62.6	62.6	62.6	65.9
75°	75.8	62.6	56.0	49.4	52.7	49.4	52.7	49.4	49.4	49.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)