

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584726

Luminaire Tested: **HCC8S45D010MW-HM82555927-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584726  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S45D010MW-HM82555927-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3611.2 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584726  
CATALOG NUMBER: HCC8S45D010MW-HM82555927-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584726

CATALOG NUMBER: HCC8S45D010MW-HM82555927-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	60337	60337	60337
5°	62459	59992	57612
10°	63845	58942	54370
15°	64755	56956	50772
20°	64561	54188	47133
25°	62962	50679	43272
30°	59652	46609	39705
35°	54268	42177	36082
40°	47665	37513	32594
45°	41568	32999	29061
50°	36171	28913	25598
55°	32257	25408	22268
60°	29313	22264	18995
65°	26340	19365	17234
70°	23459	16517	15552
75°	20552	13916	13296
80°	17438	11312	11791
85°	13162	8456	9376



TEST NUMBER: P584726  
 CATALOG NUMBER: HCC8S45D010MW-HM82555927-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.3	5.1
10°-20°	505.0	14.0
20°-30°	701.0	19.4
30°-40°	724.7	20.1
40°-50°	606.8	16.8
50°-60°	440.5	12.2
60°-70°	278.0	7.7
70°-80°	137.7	3.8
80°-90°	34.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1389.2	38.5
0°-40°	2113.9	58.5
0°-60°	3161.3	87.5
0°-90°	3611.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3611.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1957	1957	1957	1957	1957	
5°	2018	1994	1938	1885	1861	193
15°	2028	1951	1784	1641	1590	571
25°	1850	1731	1490	1328	1272	848
35°	1442	1336	1120	993	958	898
45°	953	884	757	682	666	737
55°	600	547	473	433	414	542
65°	361	316	265	234	236	360
75°	172	143	117	112	112	185
85°	37	29	24	26	26	45
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584726

CATALOG NUMBER: HCC8S45D010MW-HM82555927-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7
2.5°	1988.6	1988.6	1991.3	1988.6	1988.6	1988.6	1985.9	1985.9	1983.3	1983.3	1977.9
5°	2017.8	2012.5	2017.8	2012.5	2012.5	2012.5	2009.8	2004.5	2001.8	1996.6	1993.9
7.5°	2031.0	2028.4	2028.4	2025.8	2025.8	2023.1	2020.5	2017.8	2007.1	2004.5	1996.6
10°	2039.0	2036.3	2036.3	2033.7	2028.4	2028.4	2023.1	2020.5	2007.1	2001.8	1991.3
12.5°	2036.3	2036.3	2036.3	2033.7	2025.8	2023.1	2017.8	2009.8	1999.3	1988.6	1977.9
15°	2028.4	2028.4	2023.1	2020.5	2012.5	2007.1	2004.5	1991.3	1980.6	1967.4	1951.4
17.5°	2001.8	2001.8	1999.3	1993.9	1985.9	1980.6	1975.3	1962.1	1951.4	1930.2	1914.2
20°	1967.4	1964.7	1962.1	1954.1	1946.1	1943.4	1935.4	1916.9	1903.7	1887.7	1866.5
22.5°	1916.9	1914.2	1911.6	1906.2	1893.0	1887.7	1882.4	1869.1	1845.2	1829.3	1802.8
25°	1850.5	1850.5	1845.2	1837.3	1824.0	1818.6	1810.6	1797.4	1776.2	1752.3	1731.0
27.5°	1773.6	1770.9	1762.9	1757.6	1746.9	1739.0	1725.7	1709.8	1688.5	1670.0	1643.5
30°	1675.3	1675.3	1670.0	1662.0	1648.8	1643.5	1632.8	1614.3	1592.9	1569.1	1550.5
32.5°	1563.8	1563.8	1555.9	1550.5	1542.5	1529.2	1526.7	1505.4	1486.8	1468.2	1447.0
35°	1441.6	1444.3	1439.0	1428.4	1415.1	1415.1	1409.8	1391.2	1369.9	1351.4	1335.5
37.5°	1319.5	1311.5	1309.0	1303.6	1295.6	1285.0	1279.7	1271.8	1253.1	1239.9	1215.9
40°	1184.1	1186.7	1181.4	1176.2	1173.5	1165.5	1162.9	1149.7	1136.3	1120.4	1109.8
42.5°	1062.0	1062.0	1062.0	1056.6	1051.4	1043.4	1040.8	1032.8	1016.9	1006.2	990.4
45°	953.2	945.2	945.2	942.5	939.8	934.5	926.6	921.3	910.7	902.7	884.1
47.5°	846.9	849.6	846.9	844.3	836.3	833.7	831.0	820.4	809.7	801.9	788.5
50°	754.0	759.3	754.0	754.0	748.7	746.0	740.7	732.8	724.8	711.5	698.3
52.5°	677.1	677.1	674.4	671.7	663.8	658.4	655.8	653.1	639.9	629.2	618.6
55°	600.0	602.7	602.7	594.7	592.0	586.7	584.2	576.2	570.8	554.9	547.0
57.5°	533.6	531.0	533.6	528.3	523.0	517.8	515.1	509.8	501.8	491.1	480.6
60°	475.3	469.9	469.9	467.3	461.9	459.3	454.0	446.1	438.1	427.4	419.5
62.5°	416.9	414.2	411.5	408.9	403.5	400.9	398.2	390.3	382.3	374.3	366.4
65°	361.0	361.0	358.5	353.1	350.5	347.8	345.1	339.8	329.3	323.9	315.9
67.5°	310.6	308.0	308.0	302.6	297.4	294.7	294.7	289.4	281.4	273.4	268.1
70°	260.2	262.9	260.2	257.6	252.2	252.2	246.9	244.2	233.7	231.0	223.0
72.5°	215.0	215.0	212.4	212.4	207.0	204.5	204.5	199.2	193.8	188.5	183.2
75°	172.5	172.5	172.5	170.0	167.3	162.0	162.0	159.3	154.0	148.7	143.3
77.5°	135.4	132.8	132.8	130.1	127.4	124.8	124.8	122.1	116.8	114.1	108.9
80°	98.2	95.6	95.6	95.6	90.3	92.9	90.3	87.6	84.9	82.3	79.6
82.5°	63.7	66.4	66.4	63.7	61.1	61.1	61.1	58.4	58.4	55.7	53.1
85°	37.2	37.2	37.2	37.2	34.5	34.5	34.5	31.9	31.9	31.9	29.2
87.5°	16.0	16.0	16.0	16.0	16.0	16.0	13.3	13.3	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584726

CATALOG NUMBER: HCC8S45D010MW-HM82555927-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7
2.5°	1977.9	1972.6	1970.1	1967.4	1967.4	1964.7	1962.1	1956.7	1956.7	1951.4	1948.7
5°	1988.6	1980.6	1975.3	1970.1	1967.4	1962.1	1956.7	1948.7	1946.1	1938.1	1930.2
7.5°	1991.3	1977.9	1972.6	1962.1	1956.7	1951.4	1940.8	1932.9	1922.2	1914.2	1903.7
10°	1980.6	1970.1	1956.7	1943.4	1940.8	1932.9	1916.9	1906.2	1893.0	1882.4	1866.5
12.5°	1964.7	1948.7	1935.4	1919.5	1911.6	1903.7	1887.7	1871.8	1853.2	1834.6	1818.6
15°	1938.1	1919.5	1901.0	1882.4	1871.8	1863.8	1845.2	1826.6	1808.1	1784.1	1768.2
17.5°	1898.3	1877.0	1858.5	1834.6	1824.0	1816.0	1792.1	1770.9	1746.9	1723.1	1707.2
20°	1847.8	1821.3	1800.1	1773.6	1765.6	1752.3	1728.4	1704.5	1678.0	1651.3	1632.8
22.5°	1781.6	1754.9	1731.0	1704.5	1691.2	1678.0	1654.0	1624.8	1598.3	1577.1	1558.4
25°	1704.5	1680.6	1651.3	1627.5	1611.6	1595.6	1569.1	1545.2	1521.3	1489.5	1470.8
27.5°	1619.6	1590.4	1569.1	1537.2	1521.3	1510.7	1481.5	1449.6	1428.4	1399.2	1377.9
30°	1524.0	1497.5	1473.5	1441.6	1425.8	1415.1	1388.6	1359.4	1338.2	1309.0	1287.7
32.5°	1423.1	1393.9	1364.7	1343.4	1324.8	1314.2	1285.0	1266.4	1239.9	1215.9	1192.1
35°	1314.2	1285.0	1263.8	1234.6	1223.9	1213.4	1189.4	1165.5	1141.7	1120.4	1101.8
37.5°	1197.4	1176.2	1152.2	1131.0	1123.0	1112.5	1083.3	1062.0	1043.4	1022.2	1006.2
40°	1083.3	1064.6	1048.7	1027.4	1014.2	1006.2	985.0	966.4	945.2	931.9	916.0
42.5°	979.7	958.5	942.5	926.6	913.3	905.3	886.8	873.5	857.6	844.3	825.7
45°	870.8	860.2	841.6	828.4	820.4	809.7	796.5	780.5	767.3	756.7	743.4
47.5°	775.2	764.7	751.3	735.5	730.1	722.1	708.8	698.3	687.6	677.1	663.8
50°	687.6	674.4	663.8	653.1	647.8	639.9	626.6	621.2	613.2	602.7	594.7
52.5°	608.0	597.4	586.7	573.5	570.8	565.5	557.5	547.0	539.0	533.6	528.3
55°	536.3	525.7	517.8	507.1	504.4	499.1	488.6	483.2	477.9	472.6	467.3
57.5°	472.6	461.9	451.4	446.1	440.7	435.4	432.7	424.7	419.5	416.9	411.5
60°	414.2	403.5	395.5	387.7	385.0	382.3	377.0	371.7	366.4	361.0	358.5
62.5°	358.5	347.8	342.5	337.2	331.8	331.8	326.6	321.3	315.9	313.3	308.0
65°	308.0	302.6	294.7	286.7	284.1	284.1	276.1	273.4	270.8	265.4	260.2
67.5°	260.2	254.9	246.9	244.2	241.6	238.9	236.2	231.0	225.7	223.0	217.7
70°	217.7	212.4	207.0	204.5	201.8	199.2	193.8	191.2	185.8	183.2	180.5
72.5°	175.2	172.5	167.3	164.6	162.0	159.3	156.6	154.0	148.7	146.0	143.3
75°	140.8	138.1	132.8	130.1	127.4	127.4	124.8	119.5	116.8	116.8	114.1
77.5°	106.2	103.6	100.9	98.2	95.6	95.6	92.9	90.3	87.6	87.6	84.9
80°	76.9	74.4	71.7	71.7	71.7	69.0	66.4	66.4	63.7	63.7	61.1
82.5°	50.4	50.4	47.7	47.7	47.7	45.2	45.2	42.5	42.5	42.5	42.5
85°	29.2	29.2	29.2	26.5	26.5	26.5	26.5	26.5	26.5	23.9	26.5
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584726

CATALOG NUMBER: HCC8S45D010MW-HM82555927-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7
2.5°	1946.1	1943.4	1938.1	1938.1	1932.9	1932.9	1930.2	1927.5	1924.9	1922.2	1919.5
5°	1927.5	1916.9	1911.6	1908.9	1903.7	1901.0	1893.0	1887.7	1885.0	1879.7	1874.5
7.5°	1893.0	1882.4	1871.8	1869.1	1866.5	1855.8	1847.8	1839.9	1834.6	1829.3	1824.0
10°	1853.2	1842.5	1829.3	1824.0	1818.6	1805.4	1794.8	1786.8	1776.2	1765.6	1762.9
12.5°	1805.4	1789.4	1773.6	1768.2	1760.2	1746.9	1736.4	1723.1	1715.2	1701.8	1699.2
15°	1749.6	1731.0	1717.7	1704.5	1699.2	1686.0	1667.3	1656.7	1640.8	1635.5	1622.1
17.5°	1683.3	1664.7	1646.1	1640.8	1632.8	1614.3	1595.6	1582.4	1566.4	1558.4	1550.5
20°	1614.3	1590.4	1571.7	1566.4	1555.9	1539.9	1521.3	1508.0	1494.8	1478.8	1470.8
22.5°	1534.6	1508.0	1492.1	1478.8	1476.2	1457.6	1436.3	1425.8	1415.1	1401.9	1391.2
25°	1447.0	1423.1	1404.4	1393.9	1388.6	1372.6	1356.7	1343.4	1327.5	1319.5	1306.3
27.5°	1356.7	1340.7	1316.9	1306.3	1298.3	1285.0	1266.4	1258.5	1242.6	1231.9	1223.9
30°	1269.1	1245.1	1231.9	1218.6	1210.7	1197.4	1181.4	1173.5	1160.2	1149.7	1141.7
32.5°	1173.5	1157.5	1139.0	1133.7	1123.0	1109.8	1099.2	1085.8	1075.3	1064.6	1062.0
35°	1085.8	1064.6	1046.1	1040.8	1032.8	1019.6	1014.2	1006.2	992.9	990.4	979.7
37.5°	990.4	979.7	958.5	950.5	947.8	937.2	926.6	921.3	913.3	905.3	902.7
40°	900.0	886.8	876.1	868.1	862.9	854.9	844.3	841.6	836.3	825.7	823.1
42.5°	815.1	801.9	791.2	788.5	780.5	772.7	767.3	759.3	756.7	754.0	748.7
45°	732.8	724.8	714.2	711.5	708.8	698.3	693.0	687.6	682.3	679.6	674.4
47.5°	658.4	650.4	642.5	639.9	634.6	631.9	623.9	621.2	613.2	610.7	608.0
50°	586.7	581.5	576.2	573.5	568.2	565.5	560.2	554.9	549.6	547.0	544.3
52.5°	523.0	517.8	512.4	509.8	507.1	501.8	496.5	491.1	488.6	485.9	483.2
55°	461.9	456.6	454.0	451.4	448.7	446.1	438.1	435.4	432.7	430.1	424.7
57.5°	406.2	400.9	395.5	395.5	393.0	390.3	385.0	379.7	379.7	374.3	369.0
60°	355.8	350.5	345.1	342.5	339.8	334.5	331.8	329.3	326.6	323.9	318.6
62.5°	302.6	300.1	294.7	294.7	289.4	286.7	284.1	281.4	278.8	273.4	270.8
65°	257.6	254.9	249.6	246.9	246.9	244.2	238.9	236.2	233.7	233.7	231.0
67.5°	215.0	212.4	207.0	204.5	204.5	201.8	199.2	199.2	196.5	193.8	196.5
70°	177.8	172.5	172.5	170.0	170.0	167.3	164.6	164.6	164.6	167.3	167.3
72.5°	140.8	138.1	135.4	135.4	135.4	135.4	132.8	132.8	135.4	138.1	138.1
75°	111.6	108.9	108.9	108.9	106.2	106.2	108.9	108.9	111.6	111.6	111.6
77.5°	82.3	82.3	82.3	82.3	82.3	82.3	84.9	84.9	87.6	87.6	87.6
80°	61.1	61.1	61.1	61.1	61.1	63.7	63.7	63.7	63.7	63.7	66.4
82.5°	42.5	42.5	42.5	42.5	42.5	42.5	42.5	45.2	45.2	45.2	45.2
85°	23.9	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5
87.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584726

CATALOG NUMBER: HCC8S45D010MW-HM82555927-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7	1956.7
2.5°	1916.9	1916.9	1916.9	1919.5	1914.2	1914.2	1914.2	1914.2
5°	1871.8	1869.1	1866.5	1869.1	1863.8	1863.8	1861.2	1861.2
7.5°	1816.0	1813.3	1810.6	1810.6	1805.4	1805.4	1802.8	1800.1
10°	1754.9	1749.6	1752.3	1746.9	1744.4	1741.7	1739.0	1736.4
12.5°	1688.5	1683.3	1680.6	1675.3	1670.0	1667.3	1670.0	1664.7
15°	1616.9	1608.9	1606.3	1600.9	1595.6	1592.9	1592.9	1590.4
17.5°	1537.2	1531.9	1529.2	1524.0	1521.3	1516.0	1513.3	1510.7
20°	1462.8	1449.6	1452.3	1447.0	1444.3	1433.6	1433.6	1436.3
22.5°	1380.6	1372.6	1367.4	1362.0	1359.4	1354.0	1354.0	1351.4
25°	1298.3	1290.3	1287.7	1282.3	1279.7	1274.3	1271.8	1271.8
27.5°	1218.6	1208.1	1208.1	1202.7	1197.4	1194.7	1192.1	1189.4
30°	1133.7	1125.7	1123.0	1123.0	1120.4	1120.4	1112.5	1115.1
32.5°	1054.1	1048.7	1046.1	1040.8	1040.8	1038.1	1038.1	1030.1
35°	974.4	966.4	969.0	963.7	961.2	958.5	961.2	958.5
37.5°	897.3	892.1	892.1	886.8	886.8	884.1	881.5	886.8
40°	820.4	817.7	815.1	812.4	815.1	812.4	807.1	809.7
42.5°	743.4	743.4	740.7	740.7	738.1	738.1	738.1	738.1
45°	674.4	671.7	671.7	669.1	669.1	669.1	669.1	666.4
47.5°	605.4	602.7	602.7	602.7	600.0	600.0	597.4	600.0
50°	539.0	539.0	536.3	536.3	539.0	536.3	533.6	533.6
52.5°	477.9	477.9	475.3	475.3	472.6	469.9	472.6	472.6
55°	422.2	419.5	416.9	416.9	414.2	411.5	411.5	414.2
57.5°	369.0	366.4	363.7	363.7	358.5	355.8	355.8	355.8
60°	318.6	313.3	313.3	310.6	310.6	308.0	308.0	308.0
62.5°	270.8	268.1	268.1	268.1	268.1	265.4	265.4	265.4
65°	231.0	231.0	231.0	233.7	233.7	236.2	236.2	236.2
67.5°	199.2	201.8	201.8	201.8	204.5	204.5	204.5	201.8
70°	170.0	170.0	170.0	172.5	172.5	172.5	172.5	172.5
72.5°	140.8	140.8	140.8	140.8	140.8	140.8	140.8	140.8
75°	111.6	114.1	114.1	114.1	111.6	114.1	114.1	111.6
77.5°	87.6	87.6	87.6	87.6	87.6	87.6	87.6	87.6
80°	66.4	66.4	66.4	66.4	66.4	66.4	66.4	66.4
82.5°	45.2	45.2	45.2	45.2	45.2	45.2	45.2	45.2
85°	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5
87.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)