

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584786

Luminaire Tested: **HCC8S50D010SL-HM82555827-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010SL-HM82555827-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4939.6 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584786
CATALOG NUMBER: HCC8S50D010SL-HM82555827-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584786

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80144	80144	80144
5°	81199	79806	79054
10°	82031	78991	77795
15°	82859	77323	75769
20°	82442	74471	72765
25°	80518	70011	69069
30°	76480	64989	64744
35°	69623	59301	59828
40°	61041	53079	55031
45°	52662	47211	50539
50°	46111	41448	45780
55°	40859	35628	40300
60°	36806	29961	33390
65°	33163	24057	25574
70°	29103	17518	14083
75°	24805	9091	3717
80°	19090	2468	622
85°	12277	0	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584786

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.2	5.0
10°-20°	689.3	14.0
20°-30°	978.4	19.8
30°-40°	1029.9	20.9
40°-50°	876.2	17.7
50°-60°	633.1	12.8
60°-70°	360.1	7.3
70°-80°	113.5	2.3
80°-90°	13.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1913.0	38.7
0°-40°	2942.9	59.6
0°-60°	4452.2	90.1
0°-90°	4939.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4939.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2599	2599	2599	2599	2599	
5°	2623	2609	2578	2561	2554	250
15°	2596	2530	2422	2377	2373	731
25°	2366	2249	2058	2023	2030	1084
35°	1850	1742	1575	1565	1589	1151
45°	1208	1162	1083	1110	1159	939
55°	760	704	663	701	750	685
65°	454	392	330	326	350	451
75°	208	160	76	35	31	224
85°	35	21	0	0	0	45
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584786

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0
2.5°	2612.8	2616.3	2609.4	2609.4	2616.3	2609.4	2612.8	2612.8	2609.4	2609.4	2605.9
5°	2623.2	2619.8	2619.8	2619.8	2623.2	2616.3	2612.8	2616.3	2609.4	2609.4	2609.4
7.5°	2626.7	2626.7	2623.2	2619.8	2619.8	2619.8	2616.3	2612.8	2609.4	2602.4	2599.0
10°	2619.8	2619.8	2623.2	2616.3	2616.3	2609.4	2609.4	2602.4	2602.4	2595.5	2585.1
12.5°	2612.8	2609.4	2609.4	2602.4	2602.4	2595.5	2595.5	2585.1	2581.6	2571.2	2560.8
15°	2595.5	2592.0	2585.1	2581.6	2578.2	2574.7	2567.8	2564.3	2553.9	2540.0	2529.6
17.5°	2560.8	2557.3	2553.9	2546.9	2540.0	2536.5	2533.1	2522.7	2508.8	2498.4	2481.0
20°	2512.3	2508.8	2508.8	2498.4	2494.9	2484.5	2481.0	2467.2	2456.8	2436.0	2422.1
22.5°	2446.4	2449.8	2442.9	2436.0	2428.9	2418.5	2411.6	2397.7	2380.4	2359.6	2342.2
25°	2366.5	2370.0	2363.0	2356.1	2345.7	2338.7	2331.8	2311.0	2293.7	2269.4	2248.6
27.5°	2265.9	2265.9	2265.9	2259.0	2241.6	2238.2	2231.2	2210.3	2186.0	2165.2	2144.4
30°	2147.9	2144.4	2144.4	2134.0	2127.1	2113.2	2102.8	2085.5	2068.1	2043.8	2019.6
32.5°	2005.7	2009.2	1998.6	1991.7	1981.3	1981.3	1967.4	1953.6	1932.8	1908.5	1884.2
35°	1849.5	1853.0	1846.0	1842.6	1825.2	1821.8	1818.3	1801.0	1787.1	1769.6	1741.9
37.5°	1689.9	1686.4	1682.9	1682.9	1672.5	1665.6	1658.7	1648.2	1627.4	1613.6	1599.7
40°	1516.4	1516.4	1516.4	1512.9	1509.4	1502.5	1499.0	1492.1	1478.2	1464.3	1453.9
42.5°	1360.2	1360.2	1356.7	1353.2	1346.3	1349.8	1342.8	1335.9	1322.0	1311.6	1304.7
45°	1207.6	1207.6	1207.6	1211.0	1204.1	1193.7	1193.7	1186.8	1179.8	1172.9	1162.5
47.5°	1072.2	1082.6	1075.7	1072.2	1075.7	1061.8	1061.8	1054.9	1047.9	1041.0	1027.1
50°	961.2	961.2	961.2	954.3	950.7	950.7	940.3	933.4	929.9	923.0	909.1
52.5°	860.5	853.6	853.6	850.1	846.7	839.7	839.7	832.8	818.9	812.0	801.6
55°	760.0	760.0	756.5	753.0	749.6	746.1	742.5	732.1	725.2	714.8	704.4
57.5°	669.7	676.6	673.2	666.2	659.3	659.3	652.3	645.4	635.0	624.6	614.2
60°	596.8	593.4	593.4	589.9	583.0	579.5	576.0	565.6	555.2	544.8	534.3
62.5°	520.4	520.4	520.4	513.5	506.6	503.1	499.6	492.7	478.8	468.4	461.5
65°	454.5	451.1	447.6	444.1	440.7	433.7	430.3	423.3	412.9	402.5	392.1
67.5°	388.7	385.2	385.2	381.7	371.3	367.8	367.8	357.4	347.0	336.6	326.2
70°	322.8	322.8	322.8	315.7	312.2	308.8	305.3	298.4	288.0	277.6	267.2
72.5°	267.2	263.7	263.7	260.2	249.8	246.4	242.9	235.9	225.5	218.6	211.7
75°	208.2	208.2	204.7	201.3	197.8	194.3	190.9	183.9	173.5	163.1	159.6
77.5°	159.6	156.2	156.2	152.7	145.8	142.3	142.3	135.4	125.0	118.0	111.1
80°	107.5	111.1	107.5	104.0	100.7	97.1	93.6	90.2	83.2	76.3	69.4
82.5°	65.9	69.4	65.9	65.9	62.4	59.0	59.0	52.0	48.6	45.1	41.6
85°	34.7	34.7	34.7	34.7	31.2	31.2	31.2	27.7	24.3	20.8	20.8
87.5°	10.4	13.9	10.4	10.4	10.4	10.4	10.4	10.4	6.9	6.9	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584786

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0
2.5°	2609.4	2605.9	2602.4	2602.4	2602.4	2602.4	2602.4	2599.0	2595.5	2595.5	2595.5
5°	2602.4	2602.4	2602.4	2599.0	2595.5	2595.5	2588.6	2585.1	2581.6	2578.2	2574.7
7.5°	2595.5	2588.6	2585.1	2581.6	2578.2	2578.2	2571.2	2564.3	2564.3	2557.3	2550.4
10°	2574.7	2571.2	2564.3	2557.3	2553.9	2550.4	2543.5	2533.1	2529.6	2522.7	2515.7
12.5°	2550.4	2543.5	2536.5	2522.7	2519.2	2515.7	2501.9	2491.4	2484.5	2481.0	2463.7
15°	2519.2	2505.3	2494.9	2477.6	2474.1	2467.2	2456.8	2446.4	2432.5	2422.1	2415.0
17.5°	2463.7	2449.8	2432.5	2415.0	2408.1	2408.1	2390.8	2376.9	2359.6	2352.6	2338.7
20°	2397.7	2380.4	2366.5	2345.7	2335.3	2324.9	2314.5	2293.7	2279.8	2269.4	2252.0
22.5°	2321.4	2297.1	2279.8	2259.0	2241.6	2231.2	2213.9	2196.4	2179.1	2168.7	2154.8
25°	2224.3	2203.4	2175.6	2154.8	2144.4	2130.5	2109.7	2092.4	2075.1	2057.7	2050.8
27.5°	2116.7	2088.9	2064.6	2040.4	2030.0	2019.6	1995.2	1974.4	1960.5	1943.2	1936.2
30°	1998.6	1970.9	1943.2	1922.3	1911.9	1894.6	1880.7	1856.4	1839.1	1825.2	1807.9
32.5°	1863.4	1842.6	1818.3	1787.1	1780.0	1766.2	1745.4	1735.0	1714.1	1703.7	1689.9
35°	1717.6	1703.7	1679.5	1655.2	1644.8	1637.8	1620.5	1599.7	1585.7	1575.3	1568.4
37.5°	1578.9	1561.4	1537.2	1519.8	1512.9	1502.5	1481.7	1471.3	1457.4	1450.5	1436.6
40°	1429.6	1412.3	1395.0	1384.6	1374.2	1367.1	1353.2	1342.8	1329.0	1318.6	1315.1
42.5°	1283.9	1273.5	1259.6	1245.7	1242.3	1231.9	1224.9	1214.5	1204.1	1200.6	1190.2
45°	1152.0	1141.6	1127.7	1113.8	1110.4	1103.4	1100.0	1089.6	1082.6	1082.6	1082.6
47.5°	1020.2	1009.8	995.9	989.0	992.4	978.6	978.6	975.1	968.2	968.2	971.6
50°	902.2	888.3	884.8	877.9	870.9	864.0	867.5	857.1	857.1	864.0	860.5
52.5°	791.2	777.3	773.8	766.9	763.4	763.4	760.0	760.0	756.5	760.0	760.0
55°	690.5	680.1	673.2	666.2	662.7	662.7	662.7	659.3	655.8	662.7	666.2
57.5°	600.3	596.8	589.9	579.5	576.0	572.6	569.1	569.1	569.1	569.1	572.6
60°	520.4	513.5	506.6	496.2	496.2	492.7	489.2	485.8	485.8	485.8	485.8
62.5°	451.1	440.7	430.3	423.3	419.9	416.4	412.9	406.0	406.0	406.0	406.0
65°	381.7	371.3	364.4	357.4	350.5	350.5	343.6	340.1	333.2	329.7	322.8
67.5°	315.7	308.8	301.8	291.4	288.0	284.5	277.6	274.1	263.7	260.2	256.8
70°	256.8	246.4	239.4	232.5	229.0	222.1	215.1	208.2	201.3	194.3	187.4
72.5°	201.3	190.9	183.9	177.0	170.0	170.0	159.6	152.7	142.3	135.4	125.0
75°	149.2	138.8	131.9	121.5	118.0	114.6	104.0	97.1	86.7	76.3	69.4
77.5°	100.7	93.6	86.7	76.3	69.4	69.4	59.0	52.0	45.1	34.7	31.2
80°	62.4	55.5	48.6	41.6	41.6	34.7	31.2	24.3	17.3	13.9	10.4
82.5°	34.7	31.2	27.7	20.8	20.8	17.3	13.9	10.4	6.9	3.5	3.5
85°	17.3	13.9	10.4	10.4	6.9	6.9	6.9	3.5	3.5	0.0	0.0
87.5°	6.9	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584786

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0
2.5°	2592.0	2592.0	2588.6	2588.6	2588.6	2585.1	2588.6	2585.1	2585.1	2585.1	2588.6
5°	2578.2	2571.2	2571.2	2567.8	2567.8	2564.3	2567.8	2564.3	2560.8	2557.3	2560.8
7.5°	2550.4	2543.5	2540.0	2536.5	2536.5	2536.5	2533.1	2529.6	2533.1	2522.7	2529.6
10°	2512.3	2508.8	2501.9	2498.4	2494.9	2498.4	2494.9	2488.0	2488.0	2488.0	2484.5
12.5°	2463.7	2456.8	2453.3	2449.8	2442.9	2442.9	2446.4	2439.4	2439.4	2432.5	2432.5
15°	2404.6	2397.7	2390.8	2390.8	2383.8	2383.8	2380.4	2380.4	2376.9	2373.4	2373.4
17.5°	2331.8	2321.4	2314.5	2317.9	2314.5	2311.0	2311.0	2304.1	2300.6	2304.1	2304.1
20°	2245.1	2238.2	2231.2	2234.7	2227.8	2224.3	2227.8	2217.4	2220.7	2220.7	2220.7
22.5°	2147.9	2144.4	2134.0	2134.0	2127.1	2123.6	2127.1	2127.1	2130.5	2127.1	2127.1
25°	2040.4	2033.4	2026.5	2026.5	2023.0	2019.6	2023.0	2026.5	2023.0	2026.5	2026.5
27.5°	1925.8	1915.4	1915.4	1908.5	1908.5	1911.9	1908.5	1911.9	1915.4	1915.4	1922.3
30°	1801.0	1797.5	1793.9	1790.4	1790.4	1793.9	1793.9	1793.9	1797.5	1804.4	1804.4
32.5°	1682.9	1676.0	1669.1	1669.1	1676.0	1672.5	1676.0	1676.0	1682.9	1682.9	1689.9
35°	1554.5	1554.5	1547.6	1551.0	1551.0	1551.0	1551.0	1558.0	1564.9	1568.4	1575.3
37.5°	1436.6	1426.2	1429.6	1429.6	1433.1	1429.6	1440.0	1440.0	1447.0	1447.0	1453.9
40°	1308.2	1308.2	1311.6	1308.2	1311.6	1311.6	1318.6	1325.5	1329.0	1335.9	1339.4
42.5°	1186.8	1193.7	1186.8	1190.2	1193.7	1197.2	1200.6	1204.1	1218.0	1224.9	1235.3
45°	1075.7	1079.1	1082.6	1086.1	1082.6	1089.6	1093.0	1100.0	1110.4	1113.8	1117.3
47.5°	968.2	971.6	975.1	978.6	978.6	985.5	989.0	995.9	1002.8	1006.3	1009.8
50°	864.0	870.9	874.4	874.4	877.9	884.8	891.8	891.8	898.7	909.1	912.6
52.5°	770.4	770.4	777.3	780.8	784.2	784.2	794.6	798.1	801.6	808.5	815.5
55°	666.2	676.6	680.1	680.1	687.0	694.0	697.4	700.9	700.9	714.8	714.8
57.5°	576.0	579.5	586.4	586.4	586.4	596.8	596.8	603.8	607.3	610.7	617.7
60°	485.8	492.7	492.7	496.2	492.7	499.6	503.1	510.0	513.5	517.0	520.4
62.5°	402.5	402.5	406.0	406.0	406.0	406.0	412.9	412.9	419.9	423.3	426.8
65°	322.8	322.8	322.8	322.8	322.8	322.8	322.8	322.8	326.2	326.2	333.2
67.5°	249.8	246.4	239.4	242.9	239.4	239.4	235.9	235.9	239.4	239.4	246.4
70°	180.5	177.0	170.0	170.0	166.6	163.1	159.6	156.2	152.7	152.7	152.7
72.5°	118.0	111.1	100.7	97.1	97.1	90.2	83.2	79.8	79.8	79.8	79.8
75°	59.0	52.0	45.1	41.6	41.6	34.7	38.2	34.7	34.7	34.7	34.7
77.5°	24.3	17.3	13.9	13.9	13.9	10.4	10.4	10.4	10.4	10.4	10.4
80°	6.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584786

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0	2599.0
2.5°	2585.1	2585.1	2578.2	2581.6	2581.6	2581.6	2581.6	2581.6
5°	2553.9	2557.3	2553.9	2557.3	2557.3	2553.9	2553.9	2553.9
7.5°	2522.7	2526.1	2522.7	2526.1	2526.1	2526.1	2522.7	2522.7
10°	2484.5	2484.5	2484.5	2484.5	2484.5	2481.0	2484.5	2484.5
12.5°	2432.5	2432.5	2432.5	2436.0	2436.0	2432.5	2432.5	2428.9
15°	2376.9	2370.0	2373.4	2376.9	2373.4	2373.4	2373.4	2373.4
17.5°	2300.6	2304.1	2300.6	2300.6	2300.6	2300.6	2304.1	2300.6
20°	2220.7	2220.7	2224.3	2220.7	2220.7	2220.7	2220.7	2217.4
22.5°	2130.5	2127.1	2127.1	2130.5	2130.5	2127.1	2130.5	2130.5
25°	2030.0	2033.4	2030.0	2030.0	2033.4	2033.4	2033.4	2030.0
27.5°	1922.3	1925.8	1929.3	1925.8	1925.8	1925.8	1929.3	1932.8
30°	1811.4	1818.3	1811.4	1811.4	1818.3	1814.8	1818.3	1818.3
32.5°	1693.3	1703.7	1696.8	1703.7	1703.7	1707.2	1703.7	1707.2
35°	1575.3	1585.7	1585.7	1585.7	1589.3	1592.8	1592.8	1589.3
37.5°	1464.3	1467.8	1467.8	1474.7	1478.2	1481.7	1481.7	1478.2
40°	1349.8	1356.7	1360.2	1360.2	1360.2	1367.1	1374.2	1367.1
42.5°	1238.8	1242.3	1245.7	1245.7	1252.7	1256.1	1259.6	1259.6
45°	1131.2	1138.1	1141.6	1145.0	1148.5	1155.4	1152.0	1158.9
47.5°	1020.2	1030.6	1034.1	1037.5	1044.5	1047.9	1051.4	1054.9
50°	919.5	926.4	926.4	933.4	943.9	943.9	950.7	954.3
52.5°	818.9	822.4	825.9	829.3	836.3	843.2	843.2	850.1
55°	721.7	725.2	725.2	728.6	732.1	746.1	749.6	749.6
57.5°	621.1	621.1	628.1	631.5	635.0	641.9	641.9	641.9
60°	523.9	527.5	527.5	531.0	534.3	541.4	544.8	541.4
62.5°	426.8	430.3	430.3	433.7	440.7	444.1	440.7	440.7
65°	336.6	340.1	340.1	343.6	350.5	350.5	347.0	350.5
67.5°	246.4	246.4	246.4	246.4	246.4	246.4	246.4	246.4
70°	156.2	152.7	149.2	152.7	152.7	152.7	149.2	156.2
72.5°	76.3	79.8	79.8	79.8	79.8	79.8	79.8	76.3
75°	34.7	34.7	31.2	31.2	31.2	34.7	34.7	31.2
77.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)