

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584811

Luminaire Tested: **HCC8S50D010MB-HM82555830-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584811  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S50D010MB-HM82555830-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4606.8 lumens  
Efficiency: N/A  
Efficacy: 96.0 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584811  
CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584811

CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	76974	76974	76974
5°	79676	76531	73491
10°	81446	75193	69356
15°	82607	72659	64768
20°	82357	69132	60128
25°	80321	64649	55197
30°	76099	59456	50654
35°	69231	53805	46028
40°	60808	47854	41582
45°	53024	42092	37072
50°	46145	36886	32660
55°	41154	32413	28408
60°	37386	28406	24231
65°	33608	24713	21999
70°	29924	21070	19844
75°	26223	17752	16954
80°	22251	14419	15023
85°	16806	10791	11994



TEST NUMBER: P584811  
 CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	233.8	5.1
10°-20°	644.2	14.0
20°-30°	894.2	19.4
30°-40°	924.5	20.1
40°-50°	774.1	16.8
50°-60°	562.0	12.2
60°-70°	354.6	7.7
70°-80°	175.7	3.8
80°-90°	43.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1772.2	38.5
0°-40°	2696.7	58.5
0°-60°	4032.8	87.5
0°-90°	4606.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4606.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2496	2496	2496	2496	2496	
5°	2574	2544	2472	2405	2374	246
15°	2588	2489	2276	2093	2029	728
25°	2361	2208	1900	1693	1622	1082
35°	1839	1704	1429	1267	1223	1145
45°	1216	1128	965	870	850	940
55°	766	698	603	552	528	691
65°	461	403	339	298	302	459
75°	220	183	149	142	142	236
85°	48	37	30	34	34	58
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584811

CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2
2.5°	2536.8	2536.8	2540.2	2536.8	2536.8	2536.8	2533.5	2533.5	2530.1	2530.1	2523.3
5°	2574.0	2567.2	2574.0	2567.2	2567.2	2567.2	2563.9	2557.1	2553.7	2547.0	2543.6
7.5°	2591.0	2587.6	2587.6	2584.2	2584.2	2580.8	2577.4	2574.0	2560.5	2557.1	2547.0
10°	2601.1	2597.8	2597.8	2594.4	2587.6	2587.6	2580.8	2577.4	2560.5	2553.7	2540.2
12.5°	2597.8	2597.8	2597.8	2594.4	2584.2	2580.8	2574.0	2563.9	2550.4	2536.8	2523.3
15°	2587.6	2587.6	2580.8	2577.4	2567.2	2560.5	2557.1	2540.2	2526.7	2509.7	2489.4
17.5°	2553.7	2553.7	2550.4	2543.6	2533.5	2526.7	2519.9	2502.9	2489.4	2462.3	2441.9
20°	2509.7	2506.3	2502.9	2492.8	2482.6	2479.2	2469.0	2445.3	2428.4	2408.1	2381.0
22.5°	2445.3	2441.9	2438.5	2431.8	2414.9	2408.1	2401.4	2384.4	2353.9	2333.6	2299.8
25°	2360.7	2360.7	2353.9	2343.7	2326.8	2320.0	2309.8	2293.0	2265.9	2235.4	2208.2
27.5°	2262.5	2259.1	2248.9	2242.1	2228.6	2218.4	2201.5	2181.1	2154.1	2130.4	2096.5
30°	2137.2	2137.2	2130.4	2120.2	2103.3	2096.5	2082.9	2059.2	2032.2	2001.7	1977.9
32.5°	1994.9	1994.9	1984.7	1977.9	1967.8	1950.8	1947.4	1920.4	1896.7	1873.0	1845.9
35°	1839.1	1842.5	1835.7	1822.1	1805.2	1805.2	1798.5	1774.8	1747.7	1723.9	1703.6
37.5°	1683.2	1673.2	1669.8	1663.0	1652.8	1639.3	1632.5	1622.3	1598.6	1581.7	1551.3
40°	1510.6	1514.0	1507.2	1500.4	1497.0	1486.9	1483.5	1466.5	1449.6	1429.3	1415.8
42.5°	1354.8	1354.8	1354.8	1348.0	1341.2	1331.0	1327.6	1317.5	1297.2	1283.7	1263.3
45°	1215.9	1205.7	1205.7	1202.3	1198.9	1192.1	1182.1	1175.3	1161.8	1151.6	1127.9
47.5°	1080.4	1083.8	1080.4	1077.0	1066.8	1063.4	1060.0	1046.6	1033.0	1022.9	1005.9
50°	961.9	968.6	961.9	961.9	955.1	951.7	944.9	934.7	924.7	907.7	890.8
52.5°	863.7	863.7	860.3	856.9	846.7	839.9	836.5	833.1	816.2	802.8	789.2
55°	765.5	768.9	768.9	758.7	755.3	748.5	745.1	735.0	728.2	707.8	697.7
57.5°	680.8	677.4	680.8	674.0	667.3	660.5	657.1	650.3	640.1	626.6	613.0
60°	606.2	599.5	599.5	596.1	589.3	585.9	579.1	569.0	558.9	545.3	535.2
62.5°	531.8	528.4	525.0	521.6	514.8	511.4	508.0	497.9	487.7	477.5	467.4
65°	460.6	460.6	457.2	450.4	447.0	443.6	440.2	433.6	420.0	413.2	403.1
67.5°	396.3	392.9	392.9	386.1	379.3	376.0	376.0	369.2	359.0	348.8	342.0
70°	331.9	335.3	331.9	328.5	321.7	321.7	314.9	311.5	298.1	294.7	284.5
72.5°	274.4	274.4	271.0	271.0	264.2	260.8	260.8	254.0	247.2	240.5	233.7
75°	220.1	220.1	220.1	216.7	213.3	206.6	206.6	203.2	196.4	189.6	182.9
77.5°	172.8	169.4	169.4	166.0	162.6	159.2	159.2	155.8	149.0	145.7	138.9
80°	125.3	121.9	121.9	121.9	115.1	118.5	115.1	111.8	108.4	105.0	101.6
82.5°	81.2	84.6	84.6	81.2	77.9	77.9	77.9	74.5	74.5	71.1	67.7
85°	47.5	47.5	47.5	47.5	44.1	44.1	44.1	40.7	40.7	40.7	37.3
87.5°	20.3	20.3	20.3	20.3	20.3	20.3	17.0	17.0	17.0	17.0	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584811

CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2
2.5°	2523.3	2516.5	2513.1	2509.7	2509.7	2506.3	2502.9	2496.2	2496.2	2489.4	2486.0
5°	2536.8	2526.7	2519.9	2513.1	2509.7	2502.9	2496.2	2486.0	2482.6	2472.4	2462.3
7.5°	2540.2	2523.3	2516.5	2502.9	2496.2	2489.4	2475.8	2465.7	2452.1	2441.9	2428.4
10°	2526.7	2513.1	2496.2	2479.2	2475.8	2465.7	2445.3	2431.8	2414.9	2401.4	2381.0
12.5°	2506.3	2486.0	2469.0	2448.7	2438.5	2428.4	2408.1	2387.8	2364.1	2340.3	2320.0
15°	2472.4	2448.7	2425.1	2401.4	2387.8	2377.6	2353.9	2330.2	2306.4	2276.0	2255.7
17.5°	2421.7	2394.6	2370.8	2340.3	2326.8	2316.6	2286.2	2259.1	2228.6	2198.1	2177.8
20°	2357.3	2323.4	2296.4	2262.5	2252.3	2235.4	2204.9	2174.5	2140.6	2106.7	2082.9
22.5°	2272.7	2238.8	2208.2	2174.5	2157.5	2140.6	2110.0	2072.8	2039.0	2011.8	1988.1
25°	2174.5	2143.9	2106.7	2076.1	2055.8	2035.6	2001.7	1971.2	1940.7	1900.1	1876.4
27.5°	2066.0	2028.8	2001.7	1961.0	1940.7	1927.2	1889.9	1849.2	1822.1	1784.9	1757.8
30°	1944.0	1910.3	1879.8	1839.1	1818.7	1805.2	1771.4	1734.1	1707.0	1669.8	1642.7
32.5°	1815.3	1778.2	1740.9	1713.8	1690.0	1676.6	1639.3	1615.6	1581.7	1551.3	1520.8
35°	1676.6	1639.3	1612.2	1574.9	1561.3	1547.9	1517.4	1486.9	1456.3	1429.3	1405.6
37.5°	1527.5	1500.4	1469.9	1442.8	1432.6	1419.2	1381.9	1354.8	1331.0	1304.0	1283.7
40°	1381.9	1358.1	1337.8	1310.7	1293.8	1283.7	1256.6	1232.8	1205.7	1188.8	1168.5
42.5°	1249.8	1222.7	1202.3	1182.1	1165.1	1155.0	1131.2	1114.3	1094.0	1077.0	1053.4
45°	1110.9	1097.3	1073.6	1056.8	1046.6	1033.0	1016.1	995.8	978.8	965.2	948.3
47.5°	989.0	975.4	958.5	938.1	931.5	921.3	904.3	890.8	877.2	863.7	846.7
50°	877.2	860.3	846.7	833.1	826.4	816.2	799.4	792.6	782.4	768.9	758.7
52.5°	775.6	762.1	748.5	731.6	728.2	721.4	711.2	697.7	687.5	680.8	674.0
55°	684.2	670.7	660.5	646.9	643.5	636.8	623.2	616.4	609.6	602.9	596.1
57.5°	602.9	589.3	575.7	569.0	562.2	555.5	552.1	541.9	535.2	531.8	525.0
60°	528.4	514.8	504.7	494.5	491.1	487.7	480.9	474.1	467.4	460.6	457.2
62.5°	457.2	443.6	436.9	430.2	423.4	423.4	416.6	409.9	403.1	399.7	392.9
65°	392.9	386.1	376.0	365.8	362.4	362.4	352.2	348.8	345.4	338.7	331.9
67.5°	331.9	325.1	314.9	311.5	308.3	304.9	301.5	294.7	287.9	284.5	277.8
70°	277.8	271.0	264.2	260.8	257.4	254.0	247.2	243.9	237.1	233.7	230.3
72.5°	223.5	220.1	213.3	210.0	206.6	203.2	199.8	196.4	189.6	186.3	182.9
75°	179.6	176.2	169.4	166.0	162.6	162.6	159.2	152.4	149.0	149.0	145.7
77.5°	135.5	132.1	128.7	125.3	121.9	121.9	118.5	115.1	111.8	111.8	108.4
80°	98.2	94.8	91.4	91.4	91.4	88.0	84.6	84.6	81.2	81.2	77.9
82.5°	64.3	64.3	61.0	61.0	61.0	57.6	57.6	54.2	54.2	54.2	54.2
85°	37.3	37.3	37.3	33.9	33.9	33.9	33.9	33.9	33.9	30.5	33.9
87.5°	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	13.6	13.6	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584811

CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2
2.5°	2482.6	2479.2	2472.4	2472.4	2465.7	2465.7	2462.3	2458.9	2455.5	2452.1	2448.7
5°	2458.9	2445.3	2438.5	2435.1	2428.4	2425.1	2414.9	2408.1	2404.7	2398.0	2391.2
7.5°	2414.9	2401.4	2387.8	2384.4	2381.0	2367.5	2357.3	2347.1	2340.3	2333.6	2326.8
10°	2364.1	2350.5	2333.6	2326.8	2320.0	2303.0	2289.6	2279.4	2265.9	2252.3	2248.9
12.5°	2303.0	2282.8	2262.5	2255.7	2245.5	2228.6	2215.0	2198.1	2187.9	2171.1	2167.7
15°	2232.0	2208.2	2191.3	2174.5	2167.7	2150.7	2127.0	2113.4	2093.1	2086.3	2069.4
17.5°	2147.3	2123.6	2099.9	2093.1	2082.9	2059.2	2035.6	2018.6	1998.3	1988.1	1977.9
20°	2059.2	2028.8	2005.1	1998.3	1984.7	1964.4	1940.7	1923.8	1906.9	1886.5	1876.4
22.5°	1957.6	1923.8	1903.5	1886.5	1883.1	1859.4	1832.3	1818.7	1805.2	1788.3	1774.8
25°	1845.9	1815.3	1791.7	1778.2	1771.4	1751.0	1730.7	1713.8	1693.4	1683.2	1666.4
27.5°	1730.7	1710.4	1680.0	1666.4	1656.2	1639.3	1615.6	1605.4	1585.0	1571.5	1561.3
30°	1618.9	1588.4	1571.5	1554.7	1544.5	1527.5	1507.2	1497.0	1480.1	1466.5	1456.3
32.5°	1497.0	1476.7	1453.0	1446.2	1432.6	1415.8	1402.2	1385.3	1371.7	1358.1	1354.8
35°	1385.3	1358.1	1334.4	1327.6	1317.5	1300.6	1293.8	1283.7	1266.7	1263.3	1249.8
37.5°	1263.3	1249.8	1222.7	1212.5	1209.1	1195.5	1182.1	1175.3	1165.1	1155.0	1151.6
40°	1148.2	1131.2	1117.7	1107.5	1100.7	1090.6	1077.0	1073.6	1066.8	1053.4	1050.0
42.5°	1039.8	1022.9	1009.3	1005.9	995.8	985.6	978.8	968.6	965.2	961.9	955.1
45°	934.7	924.7	911.1	907.7	904.3	890.8	884.0	877.2	870.4	867.0	860.3
47.5°	839.9	829.8	819.6	816.2	809.4	806.1	796.0	792.6	782.4	779.0	775.6
50°	748.5	741.7	735.0	731.6	724.8	721.4	714.6	707.8	701.0	697.7	694.3
52.5°	667.3	660.5	653.7	650.3	646.9	640.1	633.4	626.6	623.2	619.8	616.4
55°	589.3	582.5	579.1	575.7	572.3	569.0	558.9	555.5	552.1	548.7	541.9
57.5°	518.2	511.4	504.7	504.7	501.3	497.9	491.1	484.3	484.3	477.5	470.8
60°	453.8	447.0	440.2	436.9	433.6	426.8	423.4	420.0	416.6	413.2	406.5
62.5°	386.1	382.7	376.0	376.0	369.2	365.8	362.4	359.0	355.6	348.8	345.4
65°	328.5	325.1	318.3	314.9	314.9	311.5	304.9	301.5	298.1	298.1	294.7
67.5°	274.4	271.0	264.2	260.8	260.8	257.4	254.0	254.0	250.6	247.2	250.6
70°	226.9	220.1	220.1	216.7	216.7	213.3	210.0	210.0	210.0	213.3	213.3
72.5°	179.6	176.2	172.8	172.8	172.8	172.8	169.4	169.4	172.8	176.2	176.2
75°	142.3	138.9	138.9	138.9	135.5	135.5	138.9	138.9	142.3	142.3	142.3
77.5°	105.0	105.0	105.0	105.0	105.0	105.0	108.4	108.4	111.8	111.8	111.8
80°	77.9	77.9	77.9	77.9	77.9	81.2	81.2	81.2	81.2	81.2	84.6
82.5°	54.2	54.2	54.2	54.2	54.2	54.2	54.2	57.6	57.6	57.6	57.6
85°	30.5	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9
87.5°	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584811

CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2	2496.2
2.5°	2445.3	2445.3	2445.3	2448.7	2441.9	2441.9	2441.9	2441.9
5°	2387.8	2384.4	2381.0	2384.4	2377.6	2377.6	2374.2	2374.2
7.5°	2316.6	2313.2	2309.8	2309.8	2303.0	2303.0	2299.8	2296.4
10°	2238.8	2232.0	2235.4	2228.6	2225.2	2221.8	2218.4	2215.0
12.5°	2154.1	2147.3	2143.9	2137.2	2130.4	2127.0	2130.4	2123.6
15°	2062.6	2052.5	2049.1	2042.4	2035.6	2032.2	2032.2	2028.8
17.5°	1961.0	1954.2	1950.8	1944.0	1940.7	1933.9	1930.5	1927.2
20°	1866.2	1849.2	1852.6	1845.9	1842.5	1828.9	1828.9	1832.3
22.5°	1761.2	1751.0	1744.3	1737.5	1734.1	1727.3	1727.3	1723.9
25°	1656.2	1646.1	1642.7	1635.9	1632.5	1625.7	1622.3	1622.3
27.5°	1554.7	1541.1	1541.1	1534.3	1527.5	1524.1	1520.8	1517.4
30°	1446.2	1436.0	1432.6	1432.6	1429.3	1429.3	1419.2	1422.6
32.5°	1344.6	1337.8	1334.4	1327.6	1327.6	1324.2	1324.2	1314.1
35°	1243.0	1232.8	1236.2	1229.4	1226.0	1222.7	1226.0	1222.7
37.5°	1144.8	1138.0	1138.0	1131.2	1131.2	1127.9	1124.5	1131.2
40°	1046.6	1043.2	1039.8	1036.4	1039.8	1036.4	1029.7	1033.0
42.5°	948.3	948.3	944.9	944.9	941.5	941.5	941.5	941.5
45°	860.3	856.9	856.9	853.5	853.5	853.5	853.5	850.1
47.5°	772.2	768.9	768.9	768.9	765.5	765.5	762.1	765.5
50°	687.5	687.5	684.2	684.2	687.5	684.2	680.8	680.8
52.5°	609.6	609.6	606.2	606.2	602.9	599.5	602.9	602.9
55°	538.6	535.2	531.8	531.8	528.4	525.0	525.0	528.4
57.5°	470.8	467.4	464.0	464.0	457.2	453.8	453.8	453.8
60°	406.5	399.7	399.7	396.3	396.3	392.9	392.9	392.9
62.5°	345.4	342.0	342.0	342.0	342.0	338.7	338.7	338.7
65°	294.7	294.7	294.7	298.1	298.1	301.5	301.5	301.5
67.5°	254.0	257.4	257.4	257.4	260.8	260.8	260.8	257.4
70°	216.7	216.7	216.7	220.1	220.1	220.1	220.1	220.1
72.5°	179.6	179.6	179.6	179.6	179.6	179.6	179.6	179.6
75°	142.3	145.7	145.7	145.7	142.3	145.7	145.7	142.3
77.5°	111.8	111.8	111.8	111.8	111.8	111.8	111.8	111.8
80°	84.6	84.6	84.6	84.6	84.6	84.6	84.6	84.6
82.5°	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6
85°	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9
87.5°	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)