

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584846

Luminaire Tested: **HCC8S50D010SL-HM82555840-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010SL-HM82555840-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5506.6 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584846
CATALOG NUMBER: HCC8S50D010SL-HM82555840-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584846

CATALOG NUMBER: HCC8S50D010SL-HM82555840-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	84427	84427	84427
5°	87517	84149	81258
10°	89991	83415	77936
15°	91999	81943	74492
20°	92142	78744	71465
25°	90375	74366	68940
30°	85716	68963	65915
35°	77886	62806	62952
40°	68102	56360	59334
45°	59021	50198	55288
50°	51676	44591	50371
55°	45998	39520	45584
60°	41493	35499	40056
65°	37453	31222	34906
70°	33666	26299	25948
75°	29655	20850	19456
80°	24861	17278	18646
85°	19282	15143	16487



TEST NUMBER: P584846
 CATALOG NUMBER: HCC8S50D010SL-HM82555840-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.3	4.7
10°-20°	727.5	13.2
20°-30°	1039.7	18.9
30°-40°	1104.7	20.1
40°-50°	951.1	17.3
50°-60°	711.1	12.9
60°-70°	453.6	8.2
70°-80°	206.4	3.7
80°-90°	54.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2025.5	36.8
0°-40°	3130.2	56.8
0°-60°	4792.4	87.0
0°-90°	5506.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5506.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2738	2738	2738	2738	2738	
5°	2827	2788	2718	2648	2625	271
15°	2882	2785	2567	2392	2333	812
25°	2656	2489	2186	2054	2026	1216
35°	2069	1925	1668	1626	1672	1288
45°	1353	1280	1151	1182	1268	1052
55°	856	786	735	797	848	769
65°	513	455	428	447	478	512
75°	249	214	175	160	163	264
85°	54	47	43	47	47	66
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584846

CATALOG NUMBER: HCC8S50D010SL-HM82555840-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9
2.5°	2788.4	2780.7	2784.6	2780.7	2784.6	2784.6	2776.8	2776.8	2776.8	2776.8	2765.2
5°	2827.3	2823.5	2823.5	2819.6	2815.7	2819.6	2815.7	2811.8	2804.0	2800.1	2788.4
7.5°	2850.7	2850.7	2850.7	2850.7	2846.7	2842.9	2839.0	2831.2	2823.5	2815.7	2807.9
10°	2874.0	2878.0	2874.0	2870.1	2866.3	2858.4	2854.6	2846.7	2835.2	2823.5	2815.7
12.5°	2885.7	2885.7	2881.8	2881.8	2874.0	2870.1	2858.4	2846.7	2835.2	2823.5	2804.0
15°	2881.8	2881.8	2878.0	2874.0	2862.4	2858.4	2850.7	2839.0	2819.6	2804.0	2784.6
17.5°	2858.4	2854.6	2846.7	2846.7	2831.2	2827.3	2819.6	2804.0	2784.6	2761.3	2737.9
20°	2807.9	2807.9	2804.0	2800.1	2784.6	2772.9	2765.2	2745.6	2730.1	2703.0	2679.6
22.5°	2737.9	2745.6	2737.9	2730.1	2710.7	2706.8	2695.1	2671.7	2648.5	2617.4	2590.2
25°	2656.2	2652.3	2648.5	2640.7	2625.1	2617.4	2601.8	2578.5	2555.1	2520.1	2489.0
27.5°	2551.2	2535.7	2535.7	2520.1	2508.4	2496.8	2489.0	2465.7	2434.6	2407.3	2368.4
30°	2407.3	2411.2	2391.8	2387.9	2368.4	2360.7	2345.1	2321.8	2294.5	2263.4	2232.3
32.5°	2251.7	2240.2	2240.2	2224.6	2208.9	2197.4	2193.4	2166.2	2142.9	2111.8	2080.7
35°	2069.0	2069.0	2057.3	2053.5	2037.9	2030.1	2018.4	2002.8	1975.6	1948.4	1925.1
37.5°	1890.0	1882.3	1878.5	1870.6	1858.9	1847.3	1847.3	1820.1	1816.2	1785.1	1754.0
40°	1691.8	1699.5	1691.8	1680.1	1676.2	1668.4	1664.5	1649.0	1637.3	1610.1	1590.7
42.5°	1524.5	1516.8	1516.8	1512.8	1497.3	1497.3	1489.5	1481.7	1462.3	1454.5	1431.2
45°	1353.4	1361.2	1349.5	1353.4	1337.8	1337.8	1337.8	1322.3	1306.7	1295.0	1279.5
47.5°	1205.6	1209.4	1209.4	1197.9	1193.9	1193.9	1186.2	1178.4	1166.8	1151.1	1139.5
50°	1077.2	1081.2	1073.4	1069.5	1061.7	1057.8	1057.8	1042.3	1034.4	1018.9	1011.2
52.5°	960.6	960.6	956.7	956.7	945.0	945.0	937.3	925.6	917.8	910.1	890.5
55°	855.6	855.6	851.7	847.9	847.9	836.2	832.2	820.6	812.8	797.3	785.6
57.5°	754.5	758.3	754.5	750.6	746.8	742.8	735.1	723.4	715.5	704.0	696.1
60°	672.8	672.8	668.9	665.0	657.2	653.4	649.5	641.7	630.0	622.3	610.6
62.5°	595.0	591.2	587.3	583.3	575.6	575.6	567.8	560.1	548.4	540.5	532.8
65°	513.3	513.3	509.5	509.5	505.6	497.8	493.9	490.0	474.5	470.5	455.0
67.5°	439.4	443.4	435.6	435.6	427.9	427.9	423.9	412.2	408.3	400.6	392.8
70°	373.4	373.4	373.4	369.4	361.7	357.8	353.9	346.1	342.3	334.5	326.7
72.5°	307.2	307.2	303.4	303.4	299.5	295.5	291.7	284.0	284.0	276.1	268.4
75°	248.9	248.9	245.0	241.2	237.2	237.2	233.3	229.5	221.6	217.8	213.9
77.5°	190.5	190.5	190.5	186.7	182.8	182.8	182.8	175.0	167.3	167.3	163.3
80°	140.0	140.0	136.1	136.1	132.2	132.2	132.2	128.4	124.5	120.5	116.7
82.5°	93.3	93.3	93.3	93.3	89.4	89.4	89.4	85.6	81.7	81.7	81.7
85°	54.5	54.5	54.5	54.5	50.5	50.5	50.5	50.5	50.5	46.6	46.6
87.5°	23.4	19.4	23.4	19.4	23.4	19.4	23.4	19.4	19.4	19.4	19.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584846

CATALOG NUMBER: HCC8S50D010SL-HM82555840-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9
2.5°	2769.0	2765.2	2761.3	2757.3	2757.3	2753.5	2745.6	2741.8	2737.9	2734.1	2734.1
5°	2784.6	2780.7	2772.9	2765.2	2761.3	2753.5	2745.6	2737.9	2730.1	2718.5	2714.5
7.5°	2796.2	2784.6	2776.8	2761.3	2757.3	2749.6	2737.9	2726.2	2710.7	2695.1	2683.4
10°	2796.2	2780.7	2769.0	2749.6	2741.8	2734.1	2718.5	2699.0	2679.6	2664.0	2644.5
12.5°	2788.4	2769.0	2749.6	2730.1	2718.5	2706.8	2683.4	2664.0	2640.7	2617.4	2601.8
15°	2761.3	2737.9	2714.5	2691.3	2679.6	2664.0	2640.7	2613.4	2590.2	2566.8	2539.5
17.5°	2710.7	2687.3	2660.2	2632.9	2617.4	2605.7	2570.6	2551.2	2516.3	2492.9	2469.5
20°	2644.5	2617.4	2582.3	2555.1	2535.7	2524.0	2496.8	2461.8	2434.6	2399.6	2376.2
22.5°	2559.1	2524.0	2489.0	2461.8	2442.4	2426.7	2391.8	2356.8	2333.4	2302.3	2275.1
25°	2457.9	2422.9	2387.9	2349.0	2329.6	2314.0	2282.9	2251.7	2220.6	2185.7	2162.3
27.5°	2337.3	2298.5	2267.3	2232.3	2212.9	2189.5	2154.6	2123.5	2092.3	2069.0	2037.9
30°	2205.1	2162.3	2131.2	2096.3	2076.7	2057.3	2022.4	1991.2	1964.0	1936.8	1921.3
32.5°	2045.6	2014.5	1983.4	1948.4	1932.8	1921.3	1886.2	1855.1	1824.0	1800.6	1788.9
35°	1894.0	1858.9	1831.7	1800.6	1781.2	1769.5	1738.4	1711.2	1695.6	1668.4	1652.8
37.5°	1734.6	1707.3	1676.2	1645.1	1633.4	1621.8	1598.4	1571.1	1547.9	1528.4	1520.6
40°	1567.3	1544.0	1516.8	1497.3	1485.7	1474.0	1454.5	1435.1	1419.5	1400.1	1392.3
42.5°	1407.8	1392.3	1368.9	1345.6	1333.9	1330.1	1306.7	1291.2	1283.4	1275.6	1267.8
45°	1263.9	1240.7	1225.1	1209.4	1197.9	1190.0	1178.4	1166.8	1158.9	1151.1	1143.4
47.5°	1124.0	1104.5	1088.9	1077.2	1065.7	1061.7	1054.0	1042.3	1034.4	1034.4	1034.4
50°	995.6	980.1	964.5	956.7	952.9	945.0	937.3	933.3	929.5	929.5	929.5
52.5°	882.8	867.3	855.6	847.9	847.9	840.0	832.2	828.4	828.4	828.4	828.4
55°	777.9	766.2	758.3	750.6	742.8	738.9	738.9	738.9	735.1	735.1	738.9
57.5°	684.4	676.7	665.0	657.2	653.4	653.4	649.5	645.6	649.5	653.4	657.2
60°	598.9	591.2	587.3	575.6	575.6	575.6	571.6	571.6	571.6	575.6	579.5
62.5°	521.1	517.3	509.5	505.6	501.7	501.7	497.8	497.8	497.8	497.8	501.7
65°	451.1	443.4	435.6	435.6	435.6	431.7	431.7	423.9	427.9	427.9	423.9
67.5°	385.1	377.2	373.4	369.4	365.5	365.5	361.7	357.8	353.9	353.9	353.9
70°	322.8	315.0	315.0	307.2	307.2	303.4	299.5	299.5	295.5	291.7	287.8
72.5°	260.6	256.7	252.7	248.9	248.9	248.9	245.0	241.2	237.2	233.3	225.6
75°	206.1	206.1	198.4	194.4	194.4	190.5	186.7	182.8	178.9	175.0	171.1
77.5°	159.5	155.6	147.8	143.9	143.9	143.9	140.0	136.1	132.2	128.4	124.5
80°	116.7	112.8	109.0	105.0	105.0	105.0	101.1	101.1	97.3	97.3	97.3
82.5°	77.7	77.7	73.9	73.9	73.9	73.9	70.0	70.0	70.0	70.0	70.0
85°	46.6	46.6	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8
87.5°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584846

CATALOG NUMBER: HCC8S50D010SL-HM82555840-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9
2.5°	2726.2	2726.2	2718.5	2714.5	2710.7	2714.5	2706.8	2703.0	2699.0	2699.0	2695.1
5°	2703.0	2699.0	2683.4	2679.6	2675.7	2671.7	2664.0	2656.2	2648.5	2644.5	2640.7
7.5°	2671.7	2660.2	2644.5	2640.7	2636.8	2625.1	2613.4	2605.7	2594.0	2590.2	2582.3
10°	2629.0	2613.4	2601.8	2590.2	2582.3	2570.6	2559.1	2547.4	2531.8	2527.8	2516.3
12.5°	2578.5	2559.1	2535.7	2531.8	2520.1	2504.6	2489.0	2477.3	2465.7	2457.9	2446.2
15°	2516.3	2496.8	2473.5	2461.8	2450.1	2438.4	2419.0	2403.5	2391.8	2380.1	2368.4
17.5°	2442.4	2419.0	2399.6	2387.9	2380.1	2360.7	2345.1	2325.6	2314.0	2302.3	2290.7
20°	2352.8	2333.4	2306.2	2294.5	2290.7	2275.1	2255.7	2247.9	2232.3	2220.6	2212.9
22.5°	2251.7	2232.3	2208.9	2201.2	2185.7	2177.8	2158.4	2150.6	2142.9	2131.2	2127.3
25°	2139.0	2119.5	2100.1	2096.3	2084.6	2076.7	2065.0	2053.5	2053.5	2041.8	2041.8
27.5°	2022.4	2002.8	1987.3	1979.6	1975.6	1967.9	1956.2	1952.3	1948.4	1944.5	1944.5
30°	1897.9	1874.5	1866.8	1862.9	1858.9	1851.2	1847.3	1839.5	1843.4	1847.3	1843.4
32.5°	1765.7	1757.8	1742.3	1734.6	1738.4	1734.6	1726.7	1734.6	1730.6	1738.4	1742.3
35°	1637.3	1629.5	1621.8	1621.8	1613.9	1613.9	1613.9	1617.9	1625.6	1629.5	1637.3
37.5°	1512.8	1501.2	1497.3	1493.4	1497.3	1497.3	1497.3	1505.1	1512.8	1520.6	1532.3
40°	1380.6	1372.9	1372.9	1372.9	1372.9	1384.6	1380.6	1388.4	1396.1	1407.8	1419.5
42.5°	1256.2	1256.2	1260.1	1260.1	1260.1	1260.1	1267.8	1279.5	1291.2	1302.9	1314.5
45°	1139.5	1139.5	1139.5	1147.3	1147.3	1151.1	1166.8	1174.5	1182.3	1193.9	1205.6
47.5°	1030.6	1030.6	1034.4	1038.4	1042.3	1050.0	1057.8	1069.5	1081.2	1088.9	1100.6
50°	929.5	933.3	941.2	948.9	948.9	952.9	964.5	972.3	980.1	991.7	995.6
52.5°	832.2	840.0	847.9	851.7	855.6	863.4	867.3	879.0	882.8	894.5	898.4
55°	742.8	746.8	758.3	762.3	762.3	770.0	777.9	785.6	797.3	797.3	805.1
57.5°	661.2	665.0	672.8	676.7	672.8	684.4	688.3	696.1	700.0	707.8	711.7
60°	579.5	587.3	591.2	591.2	595.0	598.9	606.7	606.7	614.4	622.3	622.3
62.5°	501.7	505.6	509.5	513.3	517.3	513.3	525.0	525.0	532.8	536.7	544.5
65°	427.9	431.7	431.7	435.6	435.6	439.4	439.4	443.4	447.3	455.0	458.9
67.5°	353.9	353.9	353.9	357.8	353.9	357.8	357.8	361.7	361.7	369.4	373.4
70°	287.8	284.0	280.0	280.0	280.0	280.0	276.1	280.0	280.0	284.0	284.0
72.5°	221.6	217.8	213.9	210.0	210.0	206.1	202.2	206.1	206.1	210.0	210.0
75°	167.3	159.5	159.5	159.5	155.6	155.6	155.6	159.5	159.5	159.5	163.3
77.5°	124.5	124.5	120.5	120.5	120.5	124.5	124.5	128.4	128.4	128.4	128.4
80°	93.3	97.3	97.3	97.3	97.3	101.1	101.1	101.1	101.1	105.0	105.0
82.5°	70.0	70.0	70.0	70.0	73.9	73.9	73.9	73.9	73.9	73.9	73.9
85°	42.8	46.6	46.6	42.8	46.6	46.6	46.6	46.6	46.6	46.6	46.6
87.5°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584846

CATALOG NUMBER: HCC8S50D010SL-HM82555840-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9	2737.9
2.5°	2691.3	2691.3	2691.3	2691.3	2687.3	2687.3	2687.3	2683.4
5°	2632.9	2632.9	2632.9	2625.1	2629.0	2629.0	2621.2	2625.1
7.5°	2574.6	2570.6	2566.8	2566.8	2562.9	2559.1	2555.1	2559.1
10°	2508.4	2496.8	2496.8	2492.9	2492.9	2485.1	2485.1	2489.0
12.5°	2434.6	2426.7	2426.7	2422.9	2419.0	2415.2	2411.2	2411.2
15°	2360.7	2352.8	2349.0	2345.1	2341.3	2333.4	2337.3	2333.4
17.5°	2286.8	2275.1	2275.1	2271.3	2267.3	2259.6	2259.6	2255.7
20°	2201.2	2197.4	2189.5	2193.4	2189.5	2181.8	2177.8	2177.8
22.5°	2115.7	2115.7	2111.8	2111.8	2107.8	2104.0	2100.1	2100.1
25°	2033.9	2030.1	2033.9	2033.9	2022.4	2022.4	2022.4	2026.2
27.5°	1940.7	1944.5	1940.7	1940.7	1940.7	1940.7	1944.5	1940.7
30°	1847.3	1847.3	1847.3	1851.2	1858.9	1855.1	1855.1	1851.2
32.5°	1746.1	1750.1	1750.1	1754.0	1757.8	1765.7	1765.7	1769.5
35°	1645.1	1652.8	1656.7	1652.8	1664.5	1664.5	1672.3	1672.3
37.5°	1540.0	1544.0	1551.7	1555.6	1563.4	1567.3	1571.1	1571.1
40°	1427.2	1442.9	1446.8	1450.6	1462.3	1462.3	1466.2	1474.0
42.5°	1322.3	1337.8	1341.8	1345.6	1353.4	1365.0	1361.2	1368.9
45°	1221.1	1232.8	1236.7	1240.7	1252.2	1256.2	1256.2	1267.8
47.5°	1112.3	1120.0	1124.0	1131.7	1139.5	1147.3	1155.1	1151.1
50°	1003.4	1015.0	1022.9	1026.7	1038.4	1042.3	1046.1	1050.0
52.5°	906.2	913.9	917.8	921.8	933.3	937.3	941.2	948.9
55°	812.8	816.7	824.5	820.6	832.2	836.2	840.0	847.9
57.5°	719.5	723.4	727.2	727.2	735.1	742.8	746.8	750.6
60°	630.0	637.8	641.7	641.7	641.7	649.5	649.5	649.5
62.5°	548.4	548.4	552.2	552.2	560.1	560.1	560.1	560.1
65°	462.8	466.7	470.5	470.5	478.4	474.5	482.2	478.4
67.5°	373.4	373.4	381.1	381.1	377.2	381.1	381.1	381.1
70°	284.0	284.0	287.8	287.8	287.8	287.8	287.8	287.8
72.5°	210.0	210.0	210.0	213.9	210.0	210.0	213.9	210.0
75°	163.3	163.3	163.3	163.3	163.3	163.3	163.3	163.3
77.5°	128.4	128.4	132.2	132.2	132.2	132.2	132.2	132.2
80°	105.0	105.0	105.0	105.0	109.0	105.0	105.0	105.0
82.5°	77.7	73.9	77.7	73.9	77.7	77.7	77.7	77.7
85°	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6
87.5°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)