

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584897

Luminaire Tested: **HCC8S50D010SL-HM82555935-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010SL-HM82555935-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4741.4 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584897
CATALOG NUMBER: HCC8S50D010SL-HM82555935-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584897

CATALOG NUMBER: HCC8S50D010SL-HM82555935-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	72694	72694	72694
5°	75355	72454	69969
10°	77488	71823	67105
15°	79213	70555	64142
20°	79338	67800	61535
25°	77817	64033	59358
30°	73809	59378	56754
35°	67059	54080	54208
40°	58638	48526	51090
45°	50822	43225	47604
50°	44500	38393	43372
55°	39606	34026	39246
60°	35733	30571	34487
65°	32251	26880	30047
70°	28986	22639	22341
75°	25532	17955	16751
80°	21398	14863	16053
85°	16594	13020	14223



TEST NUMBER: P584897

CATALOG NUMBER: HCC8S50D010SL-HM82555935-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.4	4.7
10°-20°	626.4	13.2
20°-30°	895.2	18.9
30°-40°	951.2	20.1
40°-50°	819.0	17.3
50°-60°	612.3	12.9
60°-70°	390.5	8.2
70°-80°	177.7	3.7
80°-90°	46.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1744.0	36.8
0°-40°	2695.2	56.8
0°-60°	4126.5	87.0
0°-90°	4741.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4741.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2357	2357	2357	2357	2357	
5°	2434	2401	2341	2280	2260	233
15°	2481	2398	2210	2059	2009	699
25°	2287	2143	1882	1768	1745	1047
35°	1781	1658	1437	1400	1440	1109
45°	1165	1102	991	1018	1092	906
55°	737	676	633	686	730	662
65°	442	392	368	385	412	441
75°	214	184	151	137	141	228
85°	47	40	37	40	40	56
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584897

CATALOG NUMBER: HCC8S50D010SL-HM82555935-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4
2.5°	2401.0	2394.2	2397.6	2394.2	2397.6	2397.6	2391.0	2391.0	2391.0	2391.0	2380.9
5°	2434.4	2431.2	2431.2	2427.8	2424.4	2427.8	2424.4	2421.1	2414.3	2411.1	2401.0
7.5°	2454.5	2454.5	2454.5	2454.5	2451.2	2447.9	2444.5	2437.8	2431.2	2424.4	2417.7
10°	2474.7	2478.0	2474.7	2471.3	2468.0	2461.2	2457.9	2451.2	2441.2	2431.2	2424.4
12.5°	2484.7	2484.7	2481.3	2481.3	2474.7	2471.3	2461.2	2451.2	2441.2	2431.2	2414.3
15°	2481.3	2481.3	2478.0	2474.7	2464.6	2461.2	2454.5	2444.5	2427.8	2414.3	2397.6
17.5°	2461.2	2457.9	2451.2	2451.2	2437.8	2434.4	2427.8	2414.3	2397.6	2377.5	2357.4
20°	2417.7	2417.7	2414.3	2411.1	2397.6	2387.6	2380.9	2364.2	2350.7	2327.4	2307.3
22.5°	2357.4	2364.2	2357.4	2350.7	2334.0	2330.6	2320.6	2300.5	2280.5	2253.6	2230.2
25°	2287.1	2283.8	2280.5	2273.7	2260.4	2253.6	2240.3	2220.2	2200.1	2169.9	2143.1
27.5°	2196.7	2183.3	2183.3	2169.9	2159.8	2149.8	2143.1	2123.0	2096.3	2072.9	2039.3
30°	2072.9	2076.1	2059.4	2056.0	2039.3	2032.7	2019.2	1999.1	1975.7	1949.0	1922.1
32.5°	1938.9	1928.8	1928.8	1915.4	1902.1	1892.0	1888.6	1865.3	1845.1	1818.3	1791.5
35°	1781.4	1781.4	1771.4	1768.1	1754.7	1748.0	1738.0	1724.5	1701.1	1677.6	1657.5
37.5°	1627.5	1620.7	1617.4	1610.6	1600.7	1590.7	1590.7	1567.2	1563.8	1537.0	1510.2
40°	1456.7	1463.4	1456.7	1446.6	1443.2	1436.6	1433.2	1419.9	1409.8	1386.3	1369.6
42.5°	1312.7	1306.0	1306.0	1302.6	1289.2	1289.2	1282.5	1275.8	1259.1	1252.3	1232.4
45°	1165.4	1172.0	1162.0	1165.4	1151.9	1151.9	1151.9	1138.5	1125.2	1115.1	1101.7
47.5°	1038.1	1041.5	1041.5	1031.4	1028.0	1028.0	1021.4	1014.7	1004.6	991.2	981.1
50°	927.6	930.9	924.2	920.8	914.2	910.9	910.9	897.4	890.8	877.3	870.7
52.5°	827.1	827.1	823.8	823.8	813.7	813.7	807.1	797.0	790.2	783.6	766.9
55°	736.7	736.7	733.3	730.0	730.0	720.0	716.6	706.5	699.9	686.4	676.4
57.5°	649.6	653.0	649.6	646.3	643.0	639.6	632.9	622.8	616.2	606.1	599.5
60°	579.4	579.4	576.0	572.6	565.9	562.5	559.2	552.5	542.5	535.8	525.7
62.5°	512.4	509.0	505.6	502.3	495.7	495.7	488.9	482.2	472.2	465.5	458.7
65°	442.0	442.0	438.7	438.7	435.3	428.7	425.3	421.9	408.6	405.2	391.8
67.5°	378.4	381.8	375.0	375.0	368.4	368.4	365.0	354.9	351.6	344.9	338.2
70°	321.5	321.5	321.5	318.1	311.4	308.0	304.8	298.0	294.7	288.0	281.3
72.5°	264.5	264.5	261.2	261.2	257.9	254.5	251.1	244.4	244.4	237.8	231.1
75°	214.3	214.3	211.0	207.6	204.2	204.2	201.0	197.6	190.9	187.5	184.1
77.5°	164.1	164.1	164.1	160.7	157.3	157.3	157.3	150.7	144.0	144.0	140.6
80°	120.5	120.5	117.3	117.3	113.9	113.9	113.9	110.5	107.2	103.8	100.4
82.5°	80.3	80.3	80.3	80.3	77.0	77.0	77.0	73.6	70.4	70.4	70.4
85°	46.9	46.9	46.9	46.9	43.5	43.5	43.5	43.5	43.5	40.2	40.2
87.5°	20.1	16.7	20.1	16.7	20.1	16.7	20.1	16.7	16.7	16.7	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584897

CATALOG NUMBER: HCC8S50D010SL-HM82555935-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4
2.5°	2384.3	2380.9	2377.5	2374.2	2374.2	2370.8	2364.2	2360.8	2357.4	2354.1	2354.1
5°	2397.6	2394.2	2387.6	2380.9	2377.5	2370.8	2364.2	2357.4	2350.7	2340.7	2337.4
7.5°	2407.7	2397.6	2391.0	2377.5	2374.2	2367.5	2357.4	2347.4	2334.0	2320.6	2310.5
10°	2407.7	2394.2	2384.3	2367.5	2360.8	2354.1	2340.7	2324.0	2307.3	2293.8	2277.1
12.5°	2401.0	2384.3	2367.5	2350.7	2340.7	2330.6	2310.5	2293.8	2273.7	2253.6	2240.3
15°	2377.5	2357.4	2337.4	2317.3	2307.3	2293.8	2273.7	2250.3	2230.2	2210.1	2186.6
17.5°	2334.0	2313.9	2290.4	2267.0	2253.6	2243.5	2213.5	2196.7	2166.6	2146.5	2126.4
20°	2277.1	2253.6	2223.6	2200.1	2183.3	2173.3	2149.8	2119.7	2096.3	2066.1	2046.0
22.5°	2203.4	2173.3	2143.1	2119.7	2102.9	2089.6	2059.4	2029.3	2009.2	1982.4	1959.0
25°	2116.4	2086.2	2056.0	2022.6	2005.9	1992.4	1965.7	1938.9	1912.1	1882.0	1861.9
27.5°	2012.6	1979.0	1952.2	1922.1	1905.4	1885.2	1855.2	1828.3	1801.5	1781.4	1754.7
30°	1898.7	1861.9	1835.1	1804.9	1788.2	1771.4	1741.3	1714.5	1691.1	1667.6	1654.3
32.5°	1761.4	1734.6	1707.8	1677.6	1664.3	1654.3	1624.1	1597.3	1570.6	1550.4	1540.4
35°	1630.8	1600.7	1577.2	1550.4	1533.7	1523.7	1496.9	1473.4	1460.0	1436.6	1423.1
37.5°	1493.5	1470.0	1443.2	1416.5	1406.4	1396.4	1376.3	1352.9	1332.8	1316.1	1309.3
40°	1349.5	1329.4	1306.0	1289.2	1279.2	1269.2	1252.3	1235.6	1222.3	1205.5	1198.8
42.5°	1212.3	1198.8	1178.7	1158.6	1148.5	1145.3	1125.2	1111.7	1105.1	1098.4	1091.6
45°	1088.3	1068.2	1054.8	1041.5	1031.4	1024.7	1014.7	1004.6	997.9	991.2	984.5
47.5°	967.8	951.0	937.7	927.6	917.5	914.2	907.5	897.4	890.8	890.8	890.8
50°	857.2	843.9	830.5	823.8	820.4	813.7	807.1	803.7	800.3	800.3	800.3
52.5°	760.2	746.8	736.7	730.0	730.0	723.3	716.6	713.2	713.2	713.2	713.2
55°	669.7	659.7	653.0	646.3	639.6	636.3	636.3	636.3	632.9	632.9	636.3
57.5°	589.4	582.6	572.6	565.9	562.5	562.5	559.2	555.9	559.2	562.5	565.9
60°	515.6	509.0	505.6	495.7	495.7	495.7	492.3	492.3	492.3	495.7	498.9
62.5°	448.7	445.4	438.7	435.3	431.9	431.9	428.7	428.7	428.7	428.7	431.9
65°	388.5	381.8	375.0	375.0	375.0	371.7	371.7	365.0	368.4	368.4	365.0
67.5°	331.5	324.9	321.5	318.1	314.8	314.8	311.4	308.0	304.8	304.8	304.8
70°	278.0	271.2	271.2	264.5	264.5	261.2	257.9	257.9	254.5	251.1	247.8
72.5°	224.3	221.1	217.7	214.3	214.3	214.3	211.0	207.6	204.2	201.0	194.2
75°	177.5	177.5	170.8	167.4	167.4	164.1	160.7	157.3	154.1	150.7	147.3
77.5°	137.2	134.0	127.3	123.9	123.9	123.9	120.5	117.3	113.9	110.5	107.2
80°	100.4	97.1	93.8	90.4	90.4	90.4	87.1	87.1	83.7	83.7	83.7
82.5°	67.0	67.0	63.6	63.6	63.6	63.6	60.3	60.3	60.3	60.3	60.3
85°	40.2	40.2	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8
87.5°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584897

CATALOG NUMBER: HCC8S50D010SL-HM82555935-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4
2.5°	2347.4	2347.4	2340.7	2337.4	2334.0	2337.4	2330.6	2327.4	2324.0	2324.0	2320.6
5°	2327.4	2324.0	2310.5	2307.3	2303.9	2300.5	2293.8	2287.1	2280.5	2277.1	2273.7
7.5°	2300.5	2290.4	2277.1	2273.7	2270.4	2260.4	2250.3	2243.5	2233.6	2230.2	2223.6
10°	2263.7	2250.3	2240.3	2230.2	2223.6	2213.5	2203.4	2193.4	2180.0	2176.7	2166.6
12.5°	2220.2	2203.4	2183.3	2180.0	2169.9	2156.6	2143.1	2133.1	2123.0	2116.4	2106.3
15°	2166.6	2149.8	2129.8	2119.7	2109.7	2099.6	2082.8	2069.5	2059.4	2049.4	2039.3
17.5°	2102.9	2082.8	2066.1	2056.0	2049.4	2032.7	2019.2	2002.5	1992.4	1982.4	1972.3
20°	2025.9	2009.2	1985.8	1975.7	1972.3	1959.0	1942.2	1935.5	1922.1	1912.1	1905.4
22.5°	1938.9	1922.1	1902.1	1895.3	1882.0	1875.2	1858.5	1851.8	1845.1	1835.1	1831.7
25°	1841.8	1825.0	1808.3	1804.9	1794.9	1788.2	1778.2	1768.1	1768.1	1758.1	1758.1
27.5°	1741.3	1724.5	1711.2	1704.5	1701.1	1694.5	1684.4	1681.0	1677.6	1674.4	1674.4
30°	1634.1	1614.0	1607.4	1604.0	1600.7	1593.9	1590.7	1583.9	1587.3	1590.7	1587.3
32.5°	1520.3	1513.6	1500.2	1493.5	1496.9	1493.5	1486.9	1493.5	1490.1	1496.9	1500.2
35°	1409.8	1403.0	1396.4	1396.4	1389.7	1389.7	1389.7	1393.1	1399.8	1403.0	1409.8
37.5°	1302.6	1292.6	1289.2	1285.9	1289.2	1289.2	1289.2	1296.0	1302.6	1309.3	1319.3
40°	1188.8	1182.1	1182.1	1182.1	1182.1	1192.1	1188.8	1195.4	1202.2	1212.3	1222.3
42.5°	1081.6	1081.6	1084.9	1084.9	1084.9	1084.9	1091.6	1101.7	1111.7	1121.8	1131.8
45°	981.1	981.1	981.1	987.8	987.8	991.2	1004.6	1011.3	1018.0	1028.0	1038.1
47.5°	887.4	887.4	890.8	894.1	897.4	904.1	910.9	920.8	930.9	937.7	947.7
50°	800.3	803.7	810.4	817.0	817.0	820.4	830.5	837.1	843.9	854.0	857.2
52.5°	716.6	723.3	730.0	733.3	736.7	743.4	746.8	756.8	760.2	770.1	773.5
55°	639.6	643.0	653.0	656.4	656.4	663.1	669.7	676.4	686.4	686.4	693.2
57.5°	569.3	572.6	579.4	582.6	579.4	589.4	592.7	599.5	602.7	609.4	612.8
60°	498.9	505.6	509.0	509.0	512.4	515.6	522.4	522.4	529.1	535.8	535.8
62.5°	431.9	435.3	438.7	442.0	445.4	442.0	452.1	452.1	458.7	462.1	468.8
65°	368.4	371.7	371.7	375.0	375.0	378.4	378.4	381.8	385.1	391.8	395.1
67.5°	304.8	304.8	304.8	308.0	304.8	308.0	308.0	311.4	311.4	318.1	321.5
70°	247.8	244.4	241.0	241.0	241.0	241.0	237.8	241.0	241.0	244.4	244.4
72.5°	190.9	187.5	184.1	180.8	180.8	177.5	174.2	177.5	177.5	180.8	180.8
75°	144.0	137.2	137.2	137.2	134.0	134.0	134.0	137.2	137.2	137.2	140.6
77.5°	107.2	107.2	103.8	103.8	103.8	107.2	107.2	110.5	110.5	110.5	110.5
80°	80.3	83.7	83.7	83.7	83.7	87.1	87.1	87.1	87.1	90.4	90.4
82.5°	60.3	60.3	60.3	60.3	63.6	63.6	63.6	63.6	63.6	63.6	63.6
85°	36.8	40.2	40.2	36.8	40.2	40.2	40.2	40.2	40.2	40.2	40.2
87.5°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584897

CATALOG NUMBER: HCC8S50D010SL-HM82555935-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4	2357.4
2.5°	2317.3	2317.3	2317.3	2317.3	2313.9	2313.9	2313.9	2310.5
5°	2267.0	2267.0	2267.0	2260.4	2263.7	2263.7	2257.0	2260.4
7.5°	2216.8	2213.5	2210.1	2210.1	2206.7	2203.4	2200.1	2203.4
10°	2159.8	2149.8	2149.8	2146.5	2146.5	2139.7	2139.7	2143.1
12.5°	2096.3	2089.6	2089.6	2086.2	2082.8	2079.5	2076.1	2076.1
15°	2032.7	2025.9	2022.6	2019.2	2015.9	2009.2	2012.6	2009.2
17.5°	1969.1	1959.0	1959.0	1955.6	1952.2	1945.6	1945.6	1942.2
20°	1895.3	1892.0	1885.2	1888.6	1885.2	1878.6	1875.2	1875.2
22.5°	1821.7	1821.7	1818.3	1818.3	1815.0	1811.6	1808.3	1808.3
25°	1751.4	1748.0	1751.4	1751.4	1741.3	1741.3	1741.3	1744.6
27.5°	1671.0	1674.4	1671.0	1671.0	1671.0	1671.0	1674.4	1671.0
30°	1590.7	1590.7	1590.7	1593.9	1600.7	1597.3	1597.3	1593.9
32.5°	1503.6	1506.8	1506.8	1510.2	1513.6	1520.3	1520.3	1523.7
35°	1416.5	1423.1	1426.5	1423.1	1433.2	1433.2	1440.0	1440.0
37.5°	1326.1	1329.4	1336.2	1339.4	1346.1	1349.5	1352.9	1352.9
40°	1229.0	1242.3	1245.7	1249.1	1259.1	1259.1	1262.4	1269.2
42.5°	1138.5	1151.9	1155.3	1158.6	1165.4	1175.4	1172.0	1178.7
45°	1051.5	1061.6	1064.8	1068.2	1078.3	1081.6	1081.6	1091.6
47.5°	957.8	964.4	967.8	974.5	981.1	987.8	994.6	991.2
50°	864.0	873.9	880.7	884.0	894.1	897.4	900.8	904.1
52.5°	780.2	787.0	790.2	793.6	803.7	807.1	810.4	817.0
55°	699.9	703.3	709.9	706.5	716.6	720.0	723.3	730.0
57.5°	619.5	622.8	626.2	626.2	632.9	639.6	643.0	646.3
60°	542.5	549.2	552.5	552.5	552.5	559.2	559.2	559.2
62.5°	472.2	472.2	475.5	475.5	482.2	482.2	482.2	482.2
65°	398.5	401.8	405.2	405.2	411.8	408.6	415.2	411.8
67.5°	321.5	321.5	328.1	328.1	324.9	328.1	328.1	328.1
70°	244.4	244.4	247.8	247.8	247.8	247.8	247.8	247.8
72.5°	180.8	180.8	180.8	184.1	180.8	180.8	184.1	180.8
75°	140.6	140.6	140.6	140.6	140.6	140.6	140.6	140.6
77.5°	110.5	110.5	113.9	113.9	113.9	113.9	113.9	113.9
80°	90.4	90.4	90.4	90.4	93.8	90.4	90.4	90.4
82.5°	67.0	63.6	67.0	63.6	67.0	67.0	67.0	67.0
85°	40.2	40.2	40.2	40.2	40.2	40.2	40.2	40.2
87.5°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)