

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584923

Luminaire Tested: **HCC8W55D010SL-HM82555827-81RWWH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584923  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W55D010SL-HM82555827-81RWWH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5025.3 lumens  
Efficiency: N/A  
Efficacy: 96.6 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584923  
CATALOG NUMBER: HCC8W55D010SL-HM82555827-81RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584923

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77																			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																			
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	82660	82660	82660
5°	84214	82301	80388
10°	85529	80866	77453
15°	86387	78853	74096
20°	86058	75807	70681
25°	83791	71434	66738
30°	79798	66218	62857
35°	72059	60438	58386
40°	63311	54246	54097
45°	54647	47682	49741
50°	47570	41818	44610
55°	42176	36327	38859
60°	37639	30688	32261
65°	33921	24910	25443
70°	30122	18672	15066
75°	25973	10818	6493
80°	19995	3871	1936
85°	12843	1274	1274



TEST NUMBER: P584923  
 CATALOG NUMBER: HCC8W55D010SL-HM82555827-81RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	251.6	5.0
10°-20°	700.5	13.9
20°-30°	990.8	19.7
30°-40°	1044.1	20.8
40°-50°	887.3	17.7
50°-60°	638.9	12.7
60°-70°	368.6	7.3
70°-80°	126.1	2.5
80°-90°	17.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1943.0	38.7
0°-40°	2987.0	59.4
0°-60°	4513.3	89.8
0°-90°	5025.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5025.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2681	2681	2681	2681	2681	
5°	2721	2702	2659	2612	2597	260
15°	2706	2622	2470	2361	2321	762
25°	2463	2336	2100	1990	1962	1129
35°	1914	1802	1606	1547	1551	1192
45°	1253	1195	1093	1101	1141	974
55°	784	723	676	701	723	706
65°	465	400	341	334	349	462
75°	218	164	91	58	54	230
85°	36	22	4	4	4	49
90°	0	0	0	0	0	



TEST NUMBER: P584923

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6
2.5°	2706.0	2709.7	2706.0	2706.0	2702.4	2698.8	2695.1	2691.5	2684.2	2677.0	2677.0
5°	2720.6	2727.8	2720.6	2720.6	2709.7	2702.4	2695.1	2684.2	2669.7	2658.8	2658.8
7.5°	2731.5	2731.5	2731.5	2720.6	2713.3	2702.4	2684.2	2666.1	2647.9	2629.7	2622.5
10°	2731.5	2731.5	2727.8	2713.3	2706.0	2684.2	2666.1	2640.6	2615.2	2589.8	2582.6
12.5°	2720.6	2724.2	2716.9	2702.4	2684.2	2658.8	2633.4	2600.7	2571.7	2542.7	2528.1
15°	2706.0	2702.4	2695.1	2677.0	2655.2	2622.5	2597.0	2560.8	2520.9	2484.5	2470.0
17.5°	2669.7	2669.7	2658.8	2640.6	2611.6	2575.4	2535.4	2495.4	2451.8	2411.9	2393.7
20°	2622.5	2622.5	2607.9	2586.1	2557.2	2510.0	2466.4	2419.1	2368.3	2328.3	2310.1
22.5°	2553.6	2557.2	2539.0	2513.6	2480.9	2426.4	2382.8	2324.7	2273.8	2226.6	2212.0
25°	2462.7	2470.0	2451.8	2426.4	2382.8	2335.6	2281.1	2226.6	2168.4	2121.2	2099.5
27.5°	2357.4	2361.0	2342.8	2317.4	2273.8	2222.9	2168.4	2110.4	2055.9	2005.1	1983.3
30°	2241.1	2226.6	2219.3	2186.6	2139.4	2095.9	2034.1	1986.9	1928.8	1885.2	1859.7
32.5°	2077.7	2085.0	2063.2	2037.8	2001.4	1950.6	1899.7	1845.2	1790.7	1758.0	1739.8
35°	1914.2	1921.5	1910.6	1885.2	1845.2	1801.6	1750.7	1710.8	1663.5	1623.7	1605.5
37.5°	1743.5	1743.5	1736.2	1721.7	1692.6	1652.6	1601.9	1561.9	1522.0	1489.3	1478.4
40°	1572.8	1565.6	1561.9	1551.0	1525.6	1489.3	1456.6	1423.9	1383.9	1362.1	1347.6
42.5°	1405.7	1405.7	1398.4	1387.5	1362.1	1343.9	1311.2	1274.9	1245.8	1224.0	1224.0
45°	1253.1	1256.7	1245.8	1238.6	1224.0	1195.0	1166.0	1140.6	1115.2	1100.6	1093.4
47.5°	1118.8	1118.8	1107.9	1100.6	1086.1	1060.7	1035.2	1013.4	995.3	984.4	980.7
50°	991.6	991.6	991.6	973.5	955.3	937.1	919.0	893.5	882.6	875.4	871.7
52.5°	882.6	879.0	879.0	864.5	846.3	824.5	806.3	784.5	773.6	766.4	770.0
55°	784.5	784.5	780.9	762.7	744.6	722.8	704.6	686.6	679.3	672.0	675.7
56°	744.6	744.6	740.9	726.4	704.6	686.6	664.8	646.6	635.7	639.3	639.3
57°	715.5	708.2	708.2	690.2	672.0	646.6	628.4	610.3	603.0	599.4	599.4
58°	679.3	675.7	672.0	653.9	635.7	613.9	595.7	577.6	566.7	566.7	563.0
59°	643.0	643.0	635.7	621.2	603.0	581.2	563.0	544.9	534.0	530.3	530.3
60°	610.3	613.9	603.0	588.5	573.9	548.5	526.7	512.2	501.3	497.6	497.6
61°	581.2	581.2	573.9	555.8	537.6	519.4	497.6	479.5	472.2	464.9	464.9
62°	555.8	548.5	544.9	526.7	508.5	486.7	468.6	450.4	439.5	432.2	435.9
63°	523.1	519.4	512.2	497.6	479.5	457.7	435.9	421.3	410.4	399.5	403.2
64°	497.6	494.0	483.1	468.6	450.4	428.6	406.8	392.3	385.0	374.1	370.5
65°	464.9	461.3	457.7	439.5	421.3	399.5	381.4	366.8	355.9	348.7	341.4
66°	435.9	439.5	432.2	417.7	395.9	377.7	352.3	337.8	330.5	319.6	312.3
67°	410.4	410.4	403.2	388.6	366.8	348.7	330.5	312.3	301.4	290.5	286.9
67.5°	395.9	395.9	388.6	370.5	355.9	334.1	316.0	301.4	286.9	279.6	272.4
68°	381.4	381.4	377.7	363.2	345.0	323.2	305.1	286.9	272.4	261.5	257.8
69°	355.9	359.6	352.3	337.8	319.6	297.8	279.6	265.1	250.6	239.7	232.5
70°	334.1	330.5	323.2	308.7	290.5	276.0	257.8	239.7	225.3	210.7	207.1
71°	305.1	305.1	297.8	286.9	268.7	250.6	232.5	218.0	203.5	185.3	181.7
72°	283.3	283.3	276.0	261.5	246.9	228.9	210.7	192.6	181.7	163.5	156.2
72.5°	268.7	272.4	265.1	250.6	236.0	214.4	199.8	185.3	167.1	152.6	145.3
73°	261.5	257.8	254.2	239.7	221.6	207.1	188.9	174.4	156.2	141.7	134.4



TEST NUMBER: P584923  
 CATALOG NUMBER: HCC8W55D010SL-HM82555827-81RWWH

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	163.5	163.5	159.9	145.3	130.8	116.3	101.7	87.2	72.7	58.1	50.9
80°	112.6	116.3	109.0	101.7	90.8	76.3	61.8	50.9	36.3	29.1	21.8
82.5°	72.7	72.7	69.0	61.8	54.5	43.6	36.3	25.4	18.2	14.5	10.9
85°	36.3	40.0	36.3	32.7	25.4	21.8	18.2	10.9	7.3	3.6	3.6
87.5°	14.5	14.5	14.5	10.9	10.9	7.3	3.6	3.6	3.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584923

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6	2680.6
2.5°	2669.7	2669.7	2662.4	2658.8	2655.2	2651.5	2647.9	2644.3	2644.3	2647.9
5°	2647.9	2640.6	2626.1	2622.5	2611.6	2607.9	2600.7	2597.0	2600.7	2597.0
7.5°	2615.2	2600.7	2582.6	2575.4	2560.8	2553.6	2542.7	2542.7	2535.4	2539.0
10°	2571.7	2549.9	2528.1	2513.6	2502.7	2491.8	2484.5	2477.3	2473.6	2473.6
12.5°	2517.2	2491.8	2470.0	2448.2	2430.0	2422.8	2408.2	2408.2	2401.0	2397.3
15°	2455.5	2422.8	2397.3	2375.5	2361.0	2346.5	2335.6	2328.3	2321.0	2321.0
17.5°	2375.5	2346.5	2321.0	2295.6	2273.8	2262.9	2252.0	2241.1	2241.1	2233.8
20°	2288.3	2255.6	2233.8	2208.4	2190.2	2172.1	2157.5	2157.5	2150.3	2153.9
22.5°	2190.2	2150.3	2128.5	2110.4	2092.3	2077.7	2063.2	2063.2	2059.6	2055.9
25°	2081.4	2048.7	2023.2	2001.4	1990.5	1976.0	1972.4	1965.1	1961.5	1961.5
27.5°	1965.1	1939.7	1907.0	1896.1	1881.5	1874.3	1874.3	1870.6	1863.4	1867.0
30°	1841.6	1812.5	1794.3	1787.1	1772.5	1772.5	1768.9	1761.6	1761.6	1765.3
32.5°	1721.7	1692.6	1678.1	1674.4	1659.9	1659.9	1656.3	1659.9	1659.9	1663.5
35°	1591.0	1565.6	1561.9	1551.0	1547.4	1547.4	1547.4	1554.7	1561.9	1551.0
37.5°	1467.5	1449.3	1438.4	1434.8	1438.4	1438.4	1442.0	1452.9	1449.3	1445.7
40°	1340.3	1325.8	1318.5	1318.5	1325.8	1333.0	1333.0	1343.9	1347.6	1343.9
42.5°	1213.1	1202.2	1202.2	1205.9	1213.1	1216.8	1227.7	1238.6	1242.2	1245.8
45°	1093.4	1093.4	1093.4	1097.0	1100.6	1107.9	1122.4	1133.3	1137.0	1140.6
47.5°	977.1	973.5	984.4	988.0	998.9	1002.5	1013.4	1028.0	1031.6	1035.2
50°	868.1	875.4	879.0	889.9	897.2	897.2	911.7	919.0	929.9	929.9
52.5°	766.4	777.3	780.9	791.8	795.4	799.1	806.3	817.2	824.5	824.5
55°	675.7	679.3	686.6	690.2	701.1	704.6	711.9	715.5	726.4	722.8
56°	635.7	643.0	646.6	653.9	661.1	664.8	672.0	675.7	682.9	686.6
57°	599.4	603.0	613.9	617.5	624.8	624.8	628.4	639.3	639.3	643.0
58°	563.0	570.3	573.9	577.6	584.8	588.5	595.7	599.4	603.0	599.4
59°	530.3	534.0	537.6	537.6	544.9	544.9	555.8	563.0	566.7	566.7
60°	497.6	497.6	501.3	504.9	512.2	515.8	515.8	523.1	523.1	523.1
61°	464.9	464.9	468.6	472.2	475.8	475.8	483.1	483.1	486.7	490.4
62°	435.9	432.2	432.2	435.9	435.9	443.1	446.8	450.4	454.0	450.4
63°	403.2	399.5	399.5	399.5	399.5	406.8	406.8	410.4	417.7	414.1
64°	366.8	366.8	366.8	366.8	370.5	370.5	377.7	381.4	385.0	388.6
65°	341.4	334.1	330.5	330.5	334.1	337.8	341.4	345.0	348.7	348.7
66°	312.3	305.1	301.4	301.4	301.4	301.4	308.7	308.7	316.0	316.0
67°	279.6	272.4	268.7	265.1	265.1	265.1	276.0	272.4	272.4	272.4
67.5°	268.7	257.8	254.2	250.6	246.9	254.2	250.6	254.2	254.2	250.6
68°	254.2	246.9	239.7	232.5	232.5	232.5	236.0	239.7	236.0	232.5
69°	225.3	221.6	210.7	203.5	199.8	203.5	199.8	203.5	199.8	203.5
70°	199.8	188.9	178.0	174.4	170.8	170.8	170.8	167.1	170.8	167.1
71°	174.4	163.5	152.6	145.3	141.7	141.7	138.1	141.7	138.1	141.7
72°	149.0	138.1	123.5	116.3	116.3	116.3	116.3	112.6	116.3	112.6
72.5°	138.1	123.5	112.6	105.4	101.7	101.7	101.7	101.7	98.1	101.7
73°	127.2	112.6	98.1	94.5	94.5	94.5	90.8	87.2	90.8	90.8





TEST NUMBER: P584923  
 CATALOG NUMBER: HCC8W55D010SL-HM82555827-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	43.6	32.7	29.1	29.1	29.1	29.1	29.1	29.1	25.4	25.4
80°	18.2	14.5	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9
82.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
85°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



74°	236.0	236.0	228.9	218.0	199.8	181.7	167.1	152.6	134.4	116.3	109.0
75°	218.0	214.4	207.1	196.2	181.7	163.5	149.0	130.8	116.3	98.1	90.8

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



74°	105.4	87.2	79.9	72.7	72.7	72.7	69.0	69.0	69.0	72.7
75°	83.6	69.0	61.8	54.5	58.1	54.5	58.1	54.5	54.5	54.5

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)