

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584947

Luminaire Tested: **HCC8W55D010MW-HM82555830-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584947  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W55D010MW-HM82555830-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4822.3 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584947  
CATALOG NUMBER: HCC8W55D010MW-HM82555830-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584947

CATALOG NUMBER: HCC8W55D010MW-HM82555830-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	80572	80572	80572
5°	83403	80112	76927
10°	85256	78706	72603
15°	86470	76056	67797
20°	86206	72364	62940
25°	84074	67671	57780
30°	79656	62233	53018
35°	72469	56323	48177
40°	63654	50092	43527
45°	55506	44063	38808
50°	48304	38609	34185
55°	43079	33929	29735
60°	39137	29739	25366
65°	35184	25866	23020
70°	31330	22053	20773
75°	27450	18586	17752
80°	23281	15112	15734
85°	17584	11286	12560



TEST NUMBER: P584947

CATALOG NUMBER: HCC8W55D010MW-HM82555830-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	244.7	5.1
10°-20°	674.3	14.0
20°-30°	936.0	19.4
30°-40°	967.8	20.1
40°-50°	810.3	16.8
50°-60°	588.2	12.2
60°-70°	371.2	7.7
70°-80°	183.9	3.8
80°-90°	45.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1855.1	38.5
0°-40°	2822.9	58.5
0°-60°	4221.4	87.5
0°-90°	4822.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4822.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2613	2613	2613	2613	2613	
5°	2694	2662	2588	2517	2485	258
15°	2709	2606	2382	2191	2124	762
25°	2471	2312	1989	1773	1698	1132
35°	1925	1783	1496	1326	1280	1199
45°	1273	1181	1010	911	890	984
55°	801	730	631	578	553	723
65°	482	422	354	312	316	481
75°	230	192	156	149	149	247
85°	50	39	32	36	36	60
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584947

CATALOG NUMBER: HCC8W55D010MW-HM82555830-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9
2.5°	2655.4	2655.4	2659.0	2655.4	2655.4	2655.4	2651.9	2651.9	2648.4	2648.4	2641.2
5°	2694.4	2687.4	2694.4	2687.4	2687.4	2687.4	2683.8	2676.7	2673.2	2666.1	2662.5
7.5°	2712.1	2708.6	2708.6	2705.1	2705.1	2701.6	2697.9	2694.4	2680.2	2676.7	2666.1
10°	2722.8	2719.3	2719.3	2715.8	2708.6	2708.6	2701.6	2697.9	2680.2	2673.2	2659.0
12.5°	2719.3	2719.3	2719.3	2715.8	2705.1	2701.6	2694.4	2683.8	2669.6	2655.4	2641.2
15°	2708.6	2708.6	2701.6	2697.9	2687.4	2680.2	2676.7	2659.0	2644.9	2627.0	2605.8
17.5°	2673.2	2673.2	2669.6	2662.5	2651.9	2644.9	2637.7	2620.0	2605.8	2577.5	2556.1
20°	2627.0	2623.5	2620.0	2609.3	2598.7	2595.2	2584.5	2559.8	2542.0	2520.7	2492.4
22.5°	2559.8	2556.1	2552.6	2545.6	2527.8	2520.7	2513.6	2495.9	2464.0	2442.7	2407.3
25°	2471.0	2471.0	2464.0	2453.3	2435.7	2428.5	2418.0	2400.1	2371.8	2339.9	2311.5
27.5°	2368.3	2364.7	2354.1	2347.0	2332.9	2322.2	2304.5	2283.2	2254.8	2230.0	2194.6
30°	2237.1	2237.1	2230.0	2219.4	2201.6	2194.6	2180.4	2155.5	2127.2	2095.3	2070.5
32.5°	2088.2	2088.2	2077.6	2070.5	2059.8	2042.1	2038.6	2010.2	1985.4	1960.5	1932.2
35°	1925.1	1928.6	1921.6	1907.4	1889.6	1889.6	1882.6	1857.7	1829.4	1804.5	1783.3
37.5°	1762.0	1751.4	1747.8	1740.8	1730.1	1715.9	1708.9	1698.2	1673.4	1655.7	1623.8
40°	1581.3	1584.8	1577.6	1570.6	1567.1	1556.4	1552.9	1535.1	1517.4	1496.2	1482.0
42.5°	1418.1	1418.1	1418.1	1411.1	1403.9	1393.3	1389.8	1379.1	1357.9	1343.7	1322.4
45°	1272.8	1262.1	1262.1	1258.6	1255.1	1247.9	1237.3	1230.2	1216.1	1205.4	1180.6
47.5°	1131.0	1134.5	1131.0	1127.5	1116.8	1113.3	1109.6	1095.5	1081.3	1070.7	1052.9
50°	1006.9	1014.0	1006.9	1006.9	999.8	996.2	989.2	978.5	967.8	950.1	932.4
52.5°	904.1	904.1	900.6	896.9	886.4	879.2	875.7	872.2	854.4	840.2	826.0
55°	801.3	804.8	804.8	794.1	790.6	783.5	780.0	769.3	762.3	740.9	730.4
57.5°	712.6	709.1	712.6	705.5	698.4	691.4	687.8	680.7	670.0	655.9	641.7
60°	634.6	627.5	627.5	624.0	616.9	613.3	606.3	595.6	584.9	570.8	560.2
62.5°	556.6	553.1	549.6	546.0	538.9	535.4	531.9	521.2	510.5	499.9	489.3
65°	482.2	482.2	478.6	471.5	468.0	464.5	460.9	453.8	439.6	432.6	421.9
67.5°	414.8	411.3	411.3	404.2	397.1	393.6	393.6	386.4	375.9	365.2	358.0
70°	347.5	351.0	347.5	343.9	336.8	336.8	329.7	326.2	312.0	308.5	297.8
72.5°	287.1	287.1	283.6	283.6	276.6	273.0	273.0	265.9	258.8	251.7	244.6
75°	230.4	230.4	230.4	226.9	223.4	216.2	216.2	212.7	205.7	198.5	191.5
77.5°	180.8	177.3	177.3	173.7	170.2	166.7	166.7	163.1	156.0	152.5	145.3
80°	131.1	127.6	127.6	127.6	120.6	124.1	120.6	117.0	113.4	109.9	106.4
82.5°	85.1	88.6	88.6	85.1	81.6	81.6	81.6	78.1	78.1	74.4	70.9
85°	49.7	49.7	49.7	49.7	46.1	46.1	46.1	42.5	42.5	42.5	39.0
87.5°	21.3	21.3	21.3	21.3	21.3	21.3	17.7	17.7	17.7	17.7	17.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584947

CATALOG NUMBER: HCC8W55D010MW-HM82555830-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9
2.5°	2641.2	2634.2	2630.7	2627.0	2627.0	2623.5	2620.0	2612.9	2612.9	2605.8	2602.3
5°	2655.4	2644.9	2637.7	2630.7	2627.0	2620.0	2612.9	2602.3	2598.7	2588.1	2577.5
7.5°	2659.0	2641.2	2634.2	2620.0	2612.9	2605.8	2591.6	2581.0	2566.8	2556.1	2542.0
10°	2644.9	2630.7	2612.9	2595.2	2591.6	2581.0	2559.8	2545.6	2527.8	2513.6	2492.4
12.5°	2623.5	2602.3	2584.5	2563.3	2552.6	2542.0	2520.7	2499.4	2474.7	2449.8	2428.5
15°	2588.1	2563.3	2538.4	2513.6	2499.4	2488.9	2464.0	2439.2	2414.3	2382.4	2361.2
17.5°	2534.9	2506.6	2481.7	2449.8	2435.7	2425.0	2393.1	2364.7	2332.9	2300.9	2279.7
20°	2467.5	2432.1	2403.8	2368.3	2357.6	2339.9	2308.0	2276.1	2240.6	2205.2	2180.4
22.5°	2378.9	2343.4	2311.5	2276.1	2258.3	2240.6	2208.8	2169.7	2134.3	2106.0	2081.1
25°	2276.1	2244.1	2205.2	2173.2	2152.0	2130.7	2095.3	2063.4	2031.4	1988.9	1964.2
27.5°	2162.7	2123.7	2095.3	2052.8	2031.4	2017.2	1978.3	1935.8	1907.4	1868.4	1840.0
30°	2035.1	1999.5	1967.7	1925.1	1903.8	1889.6	1854.2	1815.2	1786.8	1747.8	1719.4
32.5°	1900.3	1861.3	1822.3	1794.0	1769.1	1755.0	1715.9	1691.1	1655.7	1623.8	1591.8
35°	1755.0	1715.9	1687.6	1648.5	1634.4	1620.2	1588.3	1556.4	1524.5	1496.2	1471.3
37.5°	1599.0	1570.6	1538.7	1510.4	1499.7	1485.5	1446.5	1418.1	1393.3	1364.9	1343.7
40°	1446.5	1421.6	1400.4	1372.1	1354.4	1343.7	1315.3	1290.5	1262.1	1244.4	1223.1
42.5°	1308.2	1279.8	1258.6	1237.3	1219.6	1208.9	1184.2	1166.4	1145.2	1127.5	1102.6
45°	1162.9	1148.7	1123.8	1106.1	1095.5	1081.3	1063.6	1042.4	1024.6	1010.4	992.7
47.5°	1035.2	1021.0	1003.3	982.0	975.0	964.3	946.6	932.4	918.3	904.1	886.4
50°	918.3	900.6	886.4	872.2	865.1	854.4	836.7	829.7	819.0	804.8	794.1
52.5°	811.8	797.7	783.5	765.8	762.3	755.1	744.6	730.4	719.7	712.6	705.5
55°	716.2	702.0	691.4	677.2	673.7	666.5	652.3	645.3	638.2	631.1	624.0
57.5°	631.1	616.9	602.8	595.6	588.6	581.4	577.9	567.2	560.2	556.6	549.6
60°	553.1	538.9	528.2	517.7	514.0	510.5	503.5	496.3	489.3	482.2	478.6
62.5°	478.6	464.5	457.3	450.3	443.1	443.1	436.1	429.0	421.9	418.4	411.3
65°	411.3	404.2	393.6	382.9	379.4	379.4	368.7	365.2	361.7	354.5	347.5
67.5°	347.5	340.3	329.7	326.2	322.7	319.1	315.5	308.5	301.3	297.8	290.8
70°	290.8	283.6	276.6	273.0	269.4	265.9	258.8	255.3	248.2	244.6	241.1
72.5°	234.0	230.4	223.4	219.9	216.2	212.7	209.2	205.7	198.5	195.0	191.5
75°	187.9	184.4	177.3	173.7	170.2	170.2	166.7	159.5	156.0	156.0	152.5
77.5°	141.8	138.3	134.8	131.1	127.6	127.6	124.1	120.6	117.0	117.0	113.4
80°	102.8	99.3	95.8	95.8	95.8	92.2	88.6	88.6	85.1	85.1	81.6
82.5°	67.4	67.4	63.9	63.9	63.9	60.2	60.2	56.7	56.7	56.7	56.7
85°	39.0	39.0	39.0	35.5	35.5	35.5	35.5	35.5	35.5	31.9	35.5
87.5°	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7	14.2	14.2	14.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584947

CATALOG NUMBER: HCC8W55D010MW-HM82555830-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9
2.5°	2598.7	2595.2	2588.1	2588.1	2581.0	2581.0	2577.5	2573.9	2570.3	2566.8	2563.3
5°	2573.9	2559.8	2552.6	2549.1	2542.0	2538.4	2527.8	2520.7	2517.2	2510.1	2503.0
7.5°	2527.8	2513.6	2499.4	2495.9	2492.4	2478.2	2467.5	2456.9	2449.8	2442.7	2435.7
10°	2474.7	2460.5	2442.7	2435.7	2428.5	2410.8	2396.6	2386.0	2371.8	2357.6	2354.1
12.5°	2410.8	2389.6	2368.3	2361.2	2350.6	2332.9	2318.7	2300.9	2290.3	2272.5	2269.0
15°	2336.4	2311.5	2293.8	2276.1	2269.0	2251.3	2226.4	2212.3	2191.1	2183.9	2166.2
17.5°	2247.8	2222.9	2198.1	2191.1	2180.4	2155.5	2130.7	2113.0	2091.8	2081.1	2070.5
20°	2155.5	2123.7	2098.8	2091.8	2077.6	2056.3	2031.4	2013.7	1996.0	1974.7	1964.2
22.5°	2049.2	2013.7	1992.5	1974.7	1971.2	1946.3	1918.0	1903.8	1889.6	1871.9	1857.7
25°	1932.2	1900.3	1875.4	1861.3	1854.2	1832.9	1811.7	1794.0	1772.6	1762.0	1744.3
27.5°	1811.7	1790.3	1758.5	1744.3	1733.6	1715.9	1691.1	1680.5	1659.2	1645.0	1634.4
30°	1694.7	1662.7	1645.0	1627.3	1616.7	1599.0	1577.6	1567.1	1549.3	1535.1	1524.5
32.5°	1567.1	1545.8	1520.9	1513.9	1499.7	1482.0	1467.8	1450.0	1435.8	1421.6	1418.1
35°	1450.0	1421.6	1396.9	1389.8	1379.1	1361.4	1354.4	1343.7	1326.0	1322.4	1308.2
37.5°	1322.4	1308.2	1279.8	1269.3	1265.6	1251.5	1237.3	1230.2	1219.6	1208.9	1205.4
40°	1201.9	1184.2	1170.0	1159.3	1152.2	1141.6	1127.5	1123.8	1116.8	1102.6	1099.1
42.5°	1088.4	1070.7	1056.6	1052.9	1042.4	1031.7	1024.6	1014.0	1010.4	1006.9	999.8
45°	978.5	967.8	953.7	950.1	946.6	932.4	925.3	918.3	911.1	907.6	900.6
47.5°	879.2	868.6	858.0	854.4	847.4	843.8	833.2	829.7	819.0	815.5	811.8
50°	783.5	776.4	769.3	765.8	758.8	755.1	748.1	740.9	733.9	730.4	726.8
52.5°	698.4	691.4	684.2	680.7	677.2	670.0	663.0	655.9	652.3	648.8	645.3
55°	616.9	609.8	606.3	602.8	599.1	595.6	584.9	581.4	577.9	574.4	567.2
57.5°	542.4	535.4	528.2	528.2	524.7	521.2	514.0	507.0	507.0	499.9	492.8
60°	475.1	468.0	460.9	457.3	453.8	446.8	443.1	439.6	436.1	432.6	425.4
62.5°	404.2	400.6	393.6	393.6	386.4	382.9	379.4	375.9	372.2	365.2	361.7
65°	343.9	340.3	333.3	329.7	329.7	326.2	319.1	315.5	312.0	312.0	308.5
67.5°	287.1	283.6	276.6	273.0	273.0	269.4	265.9	265.9	262.4	258.8	262.4
70°	237.6	230.4	230.4	226.9	226.9	223.4	219.9	219.9	219.9	223.4	223.4
72.5°	187.9	184.4	180.8	180.8	180.8	180.8	177.3	177.3	180.8	184.4	184.4
75°	149.0	145.3	145.3	145.3	141.8	141.8	145.3	145.3	149.0	149.0	149.0
77.5°	109.9	109.9	109.9	109.9	109.9	109.9	113.4	113.4	117.0	117.0	117.0
80°	81.6	81.6	81.6	81.6	81.6	85.1	85.1	85.1	85.1	85.1	88.6
82.5°	56.7	56.7	56.7	56.7	56.7	56.7	56.7	60.2	60.2	60.2	60.2
85°	31.9	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5
87.5°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584947

CATALOG NUMBER: HCC8W55D010MW-HM82555830-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9	2612.9
2.5°	2559.8	2559.8	2559.8	2563.3	2556.1	2556.1	2556.1	2556.1
5°	2499.4	2495.9	2492.4	2495.9	2488.9	2488.9	2485.2	2485.2
7.5°	2425.0	2421.5	2418.0	2418.0	2410.8	2410.8	2407.3	2403.8
10°	2343.4	2336.4	2339.9	2332.9	2329.2	2325.7	2322.2	2318.7
12.5°	2254.8	2247.8	2244.1	2237.1	2230.0	2226.4	2230.0	2222.9
15°	2159.1	2148.5	2144.9	2137.8	2130.7	2127.2	2127.2	2123.7
17.5°	2052.8	2045.6	2042.1	2035.1	2031.4	2024.4	2020.9	2017.2
20°	1953.5	1935.8	1939.3	1932.2	1928.6	1914.5	1914.5	1918.0
22.5°	1843.6	1832.9	1825.9	1818.7	1815.2	1808.2	1808.2	1804.5
25°	1733.6	1723.1	1719.4	1712.4	1708.9	1701.7	1698.2	1698.2
27.5°	1627.3	1613.1	1613.1	1606.0	1599.0	1595.4	1591.8	1588.3
30°	1513.9	1503.2	1499.7	1499.7	1496.2	1496.2	1485.5	1489.0
32.5°	1407.5	1400.4	1396.9	1389.8	1389.8	1386.2	1386.2	1375.6
35°	1301.2	1290.5	1294.0	1287.0	1283.5	1279.8	1283.5	1279.8
37.5°	1198.4	1191.2	1191.2	1184.2	1184.2	1180.6	1177.0	1184.2
40°	1095.5	1092.0	1088.4	1084.9	1088.4	1084.9	1077.8	1081.3
42.5°	992.7	992.7	989.2	989.2	985.7	985.7	985.7	985.7
45°	900.6	896.9	896.9	893.4	893.4	893.4	893.4	889.9
47.5°	808.3	804.8	804.8	804.8	801.3	801.3	797.7	801.3
50°	719.7	719.7	716.2	716.2	719.7	716.2	712.6	712.6
52.5°	638.2	638.2	634.6	634.6	631.1	627.5	631.1	631.1
55°	563.7	560.2	556.6	556.6	553.1	549.6	549.6	553.1
57.5°	492.8	489.3	485.7	485.7	478.6	475.1	475.1	475.1
60°	425.4	418.4	418.4	414.8	414.8	411.3	411.3	411.3
62.5°	361.7	358.0	358.0	358.0	358.0	354.5	354.5	354.5
65°	308.5	308.5	308.5	312.0	312.0	315.5	315.5	315.5
67.5°	265.9	269.4	269.4	269.4	273.0	273.0	273.0	269.4
70°	226.9	226.9	226.9	230.4	230.4	230.4	230.4	230.4
72.5°	187.9	187.9	187.9	187.9	187.9	187.9	187.9	187.9
75°	149.0	152.5	152.5	152.5	149.0	152.5	152.5	149.0
77.5°	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0
80°	88.6	88.6	88.6	88.6	88.6	88.6	88.6	88.6
82.5°	60.2	60.2	60.2	60.2	60.2	60.2	60.2	60.2
85°	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5
87.5°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)