

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584964

Luminaire Tested: **HCC8S55D010MW-HM82555835-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010MW-HM82555835-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5111.6 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584964
CATALOG NUMBER: HCC8S55D010MW-HM82555835-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584964

CATALOG NUMBER: HCC8S55D010MW-HM82555835-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	85407	85407	85407
5°	88411	84919	81545
10°	90373	83428	76959
15°	91660	80621	71864
20°	91384	76709	66717
25°	89123	71733	61247
30°	84434	65969	56202
35°	76820	59704	51072
40°	67470	53099	46139
45°	58837	46710	41132
50°	51201	40926	36239
55°	45660	35966	31515
60°	41487	31521	26889
65°	37292	27428	24407
70°	33197	23387	22017
75°	29095	19706	18813
80°	24684	16018	16692
85°	18610	11994	13303



TEST NUMBER: P584964
 CATALOG NUMBER: HCC8S55D010MW-HM82555835-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.4	5.1
10°-20°	714.8	14.0
20°-30°	992.2	19.4
30°-40°	1025.8	20.1
40°-50°	858.9	16.8
50°-60°	623.6	12.2
60°-70°	393.5	7.7
70°-80°	194.9	3.8
80°-90°	48.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1966.4	38.5
0°-40°	2992.3	58.5
0°-60°	4474.7	87.5
0°-90°	5111.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5111.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2770	2770	2770	2770	2770	
5°	2856	2822	2743	2668	2634	273
15°	2871	2762	2525	2323	2251	808
25°	2619	2450	2108	1879	1800	1200
35°	2041	1890	1586	1406	1357	1271
45°	1349	1252	1071	966	943	1043
55°	849	774	669	613	586	767
65°	511	447	376	331	334	510
75°	244	203	165	158	158	262
85°	53	41	34	38	38	64
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584964

CATALOG NUMBER: HCC8S55D010MW-HM82555835-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7
2.5°	2814.8	2814.8	2818.5	2814.8	2814.8	2814.8	2811.0	2811.0	2807.3	2807.3	2799.8
5°	2856.2	2848.7	2856.2	2848.7	2848.7	2848.7	2844.9	2837.4	2833.5	2826.0	2822.3
7.5°	2874.9	2871.2	2871.2	2867.4	2867.4	2863.7	2859.9	2856.2	2841.2	2837.4	2826.0
10°	2886.2	2882.4	2882.4	2878.7	2871.2	2871.2	2863.7	2859.9	2841.2	2833.5	2818.5
12.5°	2882.4	2882.4	2882.4	2878.7	2867.4	2863.7	2856.2	2844.9	2829.8	2814.8	2799.8
15°	2871.2	2871.2	2863.7	2859.9	2848.7	2841.2	2837.4	2818.5	2803.5	2784.8	2762.2
17.5°	2833.5	2833.5	2829.8	2822.3	2811.0	2803.5	2796.0	2777.2	2762.2	2732.2	2709.5
20°	2784.8	2781.0	2777.2	2765.9	2754.7	2750.9	2739.7	2713.3	2694.5	2672.0	2641.9
22.5°	2713.3	2709.5	2705.8	2698.3	2679.5	2672.0	2664.4	2645.7	2611.9	2589.3	2551.8
25°	2619.4	2619.4	2611.9	2600.6	2581.8	2574.3	2563.0	2544.2	2514.2	2480.3	2450.3
27.5°	2510.4	2506.7	2495.4	2487.8	2472.8	2461.6	2442.8	2420.2	2390.2	2363.8	2326.3
30°	2371.3	2371.3	2363.8	2352.6	2333.8	2326.3	2311.2	2284.9	2254.8	2221.1	2194.7
32.5°	2213.6	2213.6	2202.2	2194.7	2183.4	2164.7	2160.9	2130.8	2104.6	2078.2	2048.2
35°	2040.7	2044.4	2036.9	2021.8	2003.1	2003.1	1995.6	1969.2	1939.2	1912.8	1890.3
37.5°	1867.8	1856.4	1852.7	1845.2	1833.9	1818.9	1811.4	1800.1	1773.8	1755.1	1721.2
40°	1676.1	1679.8	1672.3	1664.8	1661.1	1649.8	1646.1	1627.2	1608.5	1586.0	1570.8
42.5°	1503.2	1503.2	1503.2	1495.7	1488.2	1477.0	1473.2	1462.0	1439.3	1424.3	1401.7
45°	1349.2	1337.8	1337.8	1334.1	1330.3	1322.8	1311.6	1304.1	1289.0	1277.7	1251.5
47.5°	1198.8	1202.6	1198.8	1195.1	1183.8	1180.1	1176.3	1161.2	1146.2	1135.0	1116.1
50°	1067.3	1074.8	1067.3	1067.3	1059.7	1056.0	1048.5	1037.2	1026.0	1007.2	988.3
52.5°	958.3	958.3	954.6	950.8	939.5	932.0	928.2	924.5	905.7	890.7	875.6
55°	849.3	853.1	853.1	841.8	838.1	830.5	826.7	815.5	808.0	785.5	774.2
57.5°	755.4	751.6	755.4	747.9	740.4	732.9	729.1	721.6	710.2	695.2	680.2
60°	672.7	665.2	665.2	661.5	653.9	650.1	642.6	631.4	620.1	605.1	593.7
62.5°	590.0	586.2	582.5	578.7	571.2	567.5	563.7	552.5	541.1	529.9	518.6
65°	511.1	511.1	507.4	499.9	496.1	492.4	488.6	481.0	466.0	458.5	447.2
67.5°	439.7	436.0	436.0	428.4	420.9	417.1	417.1	409.6	398.4	387.1	379.6
70°	368.2	372.0	368.2	364.5	357.0	357.0	349.5	345.7	330.7	327.0	315.7
72.5°	304.4	304.4	300.6	300.6	293.1	289.4	289.4	281.9	274.4	266.9	259.4
75°	244.2	244.2	244.2	240.5	236.7	229.2	229.2	225.5	218.0	210.5	203.0
77.5°	191.6	187.9	187.9	184.1	180.4	176.6	176.6	172.9	165.4	161.6	154.1
80°	139.0	135.2	135.2	135.2	127.7	131.5	127.7	124.0	120.2	116.5	112.7
82.5°	90.2	94.0	94.0	90.2	86.5	86.5	86.5	82.6	82.6	78.9	75.1
85°	52.6	52.6	52.6	52.6	48.9	48.9	48.9	45.1	45.1	45.1	41.4
87.5°	22.5	22.5	22.5	22.5	22.5	22.5	18.8	18.8	18.8	18.8	18.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584964

CATALOG NUMBER: HCC8S55D010MW-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7
2.5°	2799.8	2792.3	2788.5	2784.8	2784.8	2781.0	2777.2	2769.7	2769.7	2762.2	2758.4
5°	2814.8	2803.5	2796.0	2788.5	2784.8	2777.2	2769.7	2758.4	2754.7	2743.4	2732.2
7.5°	2818.5	2799.8	2792.3	2777.2	2769.7	2762.2	2747.2	2735.9	2720.8	2709.5	2694.5
10°	2803.5	2788.5	2769.7	2750.9	2747.2	2735.9	2713.3	2698.3	2679.5	2664.4	2641.9
12.5°	2781.0	2758.4	2739.7	2717.0	2705.8	2694.5	2672.0	2649.4	2623.2	2596.8	2574.3
15°	2743.4	2717.0	2690.8	2664.4	2649.4	2638.2	2611.9	2585.5	2559.3	2525.4	2502.9
17.5°	2687.0	2656.9	2630.7	2596.8	2581.8	2570.5	2536.7	2506.7	2472.8	2439.0	2416.4
20°	2615.7	2578.0	2547.9	2510.4	2499.2	2480.3	2446.5	2412.7	2375.1	2337.6	2311.2
22.5°	2521.7	2484.1	2450.3	2412.7	2393.9	2375.1	2341.3	2299.9	2262.3	2232.3	2205.9
25°	2412.7	2378.9	2337.6	2303.7	2281.2	2258.6	2221.1	2187.2	2153.4	2108.3	2081.9
27.5°	2292.4	2251.1	2221.1	2175.9	2153.4	2138.3	2097.1	2051.9	2021.8	1980.6	1950.4
30°	2157.2	2119.6	2085.7	2040.7	2018.1	2003.1	1965.4	1924.2	1894.1	1852.7	1822.7
32.5°	2014.3	1972.9	1931.7	1901.6	1875.3	1860.2	1818.9	1792.6	1755.1	1721.2	1687.3
35°	1860.2	1818.9	1788.8	1747.5	1732.5	1717.4	1683.6	1649.8	1616.0	1586.0	1559.6
37.5°	1694.9	1664.8	1631.0	1601.0	1589.7	1574.6	1533.3	1503.2	1477.0	1446.8	1424.3
40°	1533.3	1507.0	1484.5	1454.3	1435.6	1424.3	1394.2	1368.0	1337.8	1319.1	1296.6
42.5°	1386.7	1356.7	1334.1	1311.6	1292.8	1281.5	1255.2	1236.5	1213.8	1195.1	1168.7
45°	1232.7	1217.6	1191.3	1172.5	1161.2	1146.2	1127.5	1104.8	1086.1	1071.1	1052.2
47.5°	1097.3	1082.3	1063.6	1041.0	1033.5	1022.2	1003.5	988.3	973.3	958.3	939.5
50°	973.3	954.6	939.5	924.5	917.0	905.7	886.9	879.4	868.1	853.1	841.8
52.5°	860.6	845.6	830.5	811.7	808.0	800.5	789.2	774.2	762.9	755.4	747.9
55°	759.1	744.1	732.9	717.8	714.0	706.5	691.5	684.0	676.5	669.0	661.5
57.5°	669.0	653.9	638.9	631.4	623.9	616.4	612.6	601.2	593.7	590.0	582.5
60°	586.2	571.2	560.0	548.7	545.0	541.1	533.6	526.1	518.6	511.1	507.4
62.5°	507.4	492.4	484.7	477.2	469.7	469.7	462.2	454.7	447.2	443.5	436.0
65°	436.0	428.4	417.1	405.9	402.1	402.1	390.9	387.1	383.4	375.9	368.2
67.5°	368.2	360.7	349.5	345.7	342.0	338.2	334.5	327.0	319.5	315.7	308.1
70°	308.1	300.6	293.1	289.4	285.6	281.9	274.4	270.6	263.1	259.4	255.5
72.5°	248.0	244.2	236.7	233.0	229.2	225.5	221.7	218.0	210.5	206.7	203.0
75°	199.1	195.4	187.9	184.1	180.4	180.4	176.6	169.1	165.4	165.4	161.6
77.5°	150.4	146.6	142.7	139.0	135.2	135.2	131.5	127.7	124.0	124.0	120.2
80°	109.0	105.2	101.5	101.5	101.5	97.7	94.0	94.0	90.2	90.2	86.5
82.5°	71.4	71.4	67.6	67.6	67.6	63.9	63.9	60.1	60.1	60.1	60.1
85°	41.4	41.4	41.4	37.6	37.6	37.6	37.6	37.6	37.6	33.9	37.6
87.5°	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8	15.0	15.0	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584964

CATALOG NUMBER: HCC8S55D010MW-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7
2.5°	2754.7	2750.9	2743.4	2743.4	2735.9	2735.9	2732.2	2728.4	2724.7	2720.8	2717.0
5°	2728.4	2713.3	2705.8	2702.0	2694.5	2690.8	2679.5	2672.0	2668.3	2660.7	2653.2
7.5°	2679.5	2664.4	2649.4	2645.7	2641.9	2626.9	2615.7	2604.3	2596.8	2589.3	2581.8
10°	2623.2	2608.2	2589.3	2581.8	2574.3	2555.5	2540.4	2529.2	2514.2	2499.2	2495.4
12.5°	2555.5	2532.9	2510.4	2502.9	2491.6	2472.8	2457.8	2439.0	2427.7	2408.9	2405.2
15°	2476.6	2450.3	2431.4	2412.7	2405.2	2386.4	2360.1	2345.1	2322.6	2314.9	2296.2
17.5°	2382.7	2356.3	2330.1	2322.6	2311.2	2284.9	2258.6	2239.8	2217.3	2205.9	2194.7
20°	2284.9	2251.1	2224.8	2217.3	2202.2	2179.7	2153.4	2134.6	2115.8	2093.3	2081.9
22.5°	2172.2	2134.6	2112.1	2093.3	2089.4	2063.2	2033.1	2018.1	2003.1	1984.3	1969.2
25°	2048.2	2014.3	1988.1	1972.9	1965.4	1942.9	1920.4	1901.6	1879.1	1867.8	1848.9
27.5°	1920.4	1897.8	1864.1	1848.9	1837.7	1818.9	1792.6	1781.3	1758.8	1743.7	1732.5
30°	1796.3	1762.6	1743.7	1724.9	1713.7	1694.9	1672.3	1661.1	1642.3	1627.2	1616.0
32.5°	1661.1	1638.6	1612.2	1604.7	1589.7	1570.8	1555.8	1537.1	1522.1	1507.0	1503.2
35°	1537.1	1507.0	1480.7	1473.2	1462.0	1443.1	1435.6	1424.3	1405.6	1401.7	1386.7
37.5°	1401.7	1386.7	1356.7	1345.3	1341.6	1326.6	1311.6	1304.1	1292.8	1281.5	1277.7
40°	1274.0	1255.2	1240.2	1228.8	1221.3	1210.1	1195.1	1191.3	1183.8	1168.7	1165.0
42.5°	1153.7	1135.0	1120.0	1116.1	1104.8	1093.6	1086.1	1074.8	1071.1	1067.3	1059.7
45°	1037.2	1026.0	1011.0	1007.2	1003.5	988.3	980.8	973.3	965.8	962.1	954.6
47.5°	932.0	920.7	909.5	905.7	898.2	894.5	883.1	879.4	868.1	864.4	860.6
50°	830.5	823.0	815.5	811.7	804.2	800.5	793.0	785.5	778.0	774.2	770.4
52.5°	740.4	732.9	725.4	721.6	717.8	710.2	702.7	695.2	691.5	687.7	684.0
55°	653.9	646.4	642.6	638.9	635.1	631.4	620.1	616.4	612.6	608.9	601.2
57.5°	575.0	567.5	560.0	560.0	556.2	552.5	545.0	537.4	537.4	529.9	522.4
60°	503.6	496.1	488.6	484.7	481.0	473.5	469.7	466.0	462.2	458.5	451.0
62.5°	428.4	424.6	417.1	417.1	409.6	405.9	402.1	398.4	394.6	387.1	383.4
65°	364.5	360.7	353.2	349.5	349.5	345.7	338.2	334.5	330.7	330.7	327.0
67.5°	304.4	300.6	293.1	289.4	289.4	285.6	281.9	281.9	278.1	274.4	278.1
70°	251.7	244.2	244.2	240.5	240.5	236.7	233.0	233.0	233.0	236.7	236.7
72.5°	199.1	195.4	191.6	191.6	191.6	191.6	187.9	187.9	191.6	195.4	195.4
75°	157.9	154.1	154.1	154.1	150.4	150.4	154.1	154.1	157.9	157.9	157.9
77.5°	116.5	116.5	116.5	116.5	116.5	116.5	120.2	120.2	124.0	124.0	124.0
80°	86.5	86.5	86.5	86.5	86.5	90.2	90.2	90.2	90.2	90.2	94.0
82.5°	60.1	60.1	60.1	60.1	60.1	60.1	60.1	63.9	63.9	63.9	63.9
85°	33.9	37.6	37.6	37.6	37.6	37.6	37.6	37.6	37.6	37.6	37.6
87.5°	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584964

CATALOG NUMBER: HCC8S55D010MW-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7	2769.7
2.5°	2713.3	2713.3	2713.3	2717.0	2709.5	2709.5	2709.5	2709.5
5°	2649.4	2645.7	2641.9	2645.7	2638.2	2638.2	2634.4	2634.4
7.5°	2570.5	2566.8	2563.0	2563.0	2555.5	2555.5	2551.8	2547.9
10°	2484.1	2476.6	2480.3	2472.8	2469.1	2465.3	2461.6	2457.8
12.5°	2390.2	2382.7	2378.9	2371.3	2363.8	2360.1	2363.8	2356.3
15°	2288.7	2277.4	2273.7	2266.2	2258.6	2254.8	2254.8	2251.1
17.5°	2175.9	2168.4	2164.7	2157.2	2153.4	2145.8	2142.1	2138.3
20°	2070.7	2051.9	2055.7	2048.2	2044.4	2029.3	2029.3	2033.1
22.5°	1954.2	1942.9	1935.4	1927.9	1924.2	1916.6	1916.6	1912.8
25°	1837.7	1826.4	1822.7	1815.2	1811.4	1803.8	1800.1	1800.1
27.5°	1724.9	1709.9	1709.9	1702.4	1694.9	1691.2	1687.3	1683.6
30°	1604.7	1593.5	1589.7	1589.7	1586.0	1586.0	1574.6	1578.4
32.5°	1492.0	1484.5	1480.7	1473.2	1473.2	1469.5	1469.5	1458.1
35°	1379.2	1368.0	1371.7	1364.2	1360.5	1356.7	1360.5	1356.7
37.5°	1270.2	1262.7	1262.7	1255.2	1255.2	1251.5	1247.7	1255.2
40°	1161.2	1157.5	1153.7	1150.0	1153.7	1150.0	1142.5	1146.2
42.5°	1052.2	1052.2	1048.5	1048.5	1044.7	1044.7	1044.7	1044.7
45°	954.6	950.8	950.8	947.1	947.1	947.1	947.1	943.2
47.5°	856.8	853.1	853.1	853.1	849.3	849.3	845.6	849.3
50°	762.9	762.9	759.1	759.1	762.9	759.1	755.4	755.4
52.5°	676.5	676.5	672.7	672.7	669.0	665.2	669.0	669.0
55°	597.5	593.7	590.0	590.0	586.2	582.5	582.5	586.2
57.5°	522.4	518.6	514.9	514.9	507.4	503.6	503.6	503.6
60°	451.0	443.5	443.5	439.7	439.7	436.0	436.0	436.0
62.5°	383.4	379.6	379.6	379.6	379.6	375.9	375.9	375.9
65°	327.0	327.0	327.0	330.7	330.7	334.5	334.5	334.5
67.5°	281.9	285.6	285.6	285.6	289.4	289.4	289.4	285.6
70°	240.5	240.5	240.5	244.2	244.2	244.2	244.2	244.2
72.5°	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1
75°	157.9	161.6	161.6	161.6	157.9	161.6	161.6	157.9
77.5°	124.0	124.0	124.0	124.0	124.0	124.0	124.0	124.0
80°	94.0	94.0	94.0	94.0	94.0	94.0	94.0	94.0
82.5°	63.9	63.9	63.9	63.9	63.9	63.9	63.9	63.9
85°	37.6	37.6	37.6	37.6	37.6	37.6	37.6	37.6
87.5°	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)