

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584963

Luminaire Tested: **HCC8W55D010SL-HM82555835-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584963  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W55D010SL-HM82555835-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4683.2 lumens  
Efficiency: N/A  
Efficacy: 90.1 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584963  
CATALOG NUMBER: HCC8W55D010SL-HM82555835-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584963

CATALOG NUMBER: HCC8W55D010SL-HM82555835-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	77529	77529	77529
5°	80734	77360	74101
10°	83431	76370	70486
15°	85541	74626	66827
20°	85710	71528	63511
25°	84264	67000	60226
30°	79752	61820	57405
35°	72717	55600	53899
40°	63235	49013	49774
45°	54250	42445	45558
50°	46332	36598	40926
55°	40611	31515	35563
60°	36152	26889	29893
65°	32083	21933	23860
70°	28463	16265	13560
75°	23721	8507	4039
80°	18681	2664	675
85°	13303	1344	0



TEST NUMBER: P584963  
 CATALOG NUMBER: HCC8W55D010SL-HM82555835-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	236.9	5.1
10°-20°	664.0	14.2
20°-30°	939.8	20.1
30°-40°	983.2	21.0
40°-50°	820.1	17.5
50°-60°	581.6	12.4
60°-70°	334.9	7.2
70°-80°	107.8	2.3
80°-90°	14.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1840.7	39.3
0°-40°	2823.9	60.3
0°-60°	4225.6	90.2
0°-90°	4683.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4683.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2514	2514	2514	2514	2514	
5°	2608	2574	2499	2424	2394	250
15°	2680	2570	2338	2153	2093	753
25°	2477	2292	1969	1811	1770	1130
35°	1932	1763	1477	1398	1432	1198
45°	1244	1142	973	985	1045	964
55°	755	676	586	616	662	682
65°	440	368	301	301	327	439
75°	199	147	71	34	34	216
85°	38	19	4	0	0	47
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584963

CATALOG NUMBER: HCC8W55D010SL-HM82555835-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2
2.5°	2566.8	2563.0	2559.3	2563.0	2559.3	2563.0	2559.3	2559.3	2555.5	2551.8	2551.8
5°	2608.2	2604.4	2604.4	2604.4	2600.7	2596.8	2596.8	2593.0	2585.5	2581.8	2574.3
7.5°	2634.4	2638.2	2638.2	2638.2	2630.7	2630.7	2623.2	2615.7	2608.2	2600.7	2589.3
10°	2664.5	2664.5	2660.8	2657.0	2649.4	2645.7	2641.9	2634.4	2623.2	2608.2	2596.8
12.5°	2675.8	2675.8	2672.0	2664.5	2660.8	2657.0	2653.2	2641.9	2626.9	2608.2	2593.0
15°	2679.5	2672.0	2668.3	2664.5	2657.0	2645.7	2645.7	2630.7	2611.9	2589.3	2570.5
17.5°	2649.4	2653.2	2645.7	2638.2	2626.9	2619.4	2608.2	2596.8	2574.3	2548.0	2529.2
20°	2611.9	2608.2	2604.4	2593.0	2578.0	2574.3	2563.0	2544.3	2525.4	2495.4	2469.1
22.5°	2551.8	2548.0	2540.4	2532.9	2517.9	2510.4	2499.2	2476.6	2450.3	2420.2	2390.2
25°	2476.6	2469.1	2457.8	2442.8	2431.5	2423.9	2408.9	2386.4	2356.3	2322.6	2292.4
27.5°	2356.3	2367.6	2360.1	2337.6	2326.3	2311.2	2307.4	2277.4	2251.1	2217.3	2183.4
30°	2239.8	2239.8	2228.6	2217.3	2198.6	2187.2	2172.2	2149.7	2123.3	2081.9	2055.7
32.5°	2093.3	2089.6	2074.4	2070.7	2055.7	2033.2	2029.4	1999.3	1973.1	1942.9	1909.1
35°	1931.7	1924.2	1909.1	1897.8	1890.3	1879.1	1867.8	1841.4	1815.2	1785.1	1762.6
37.5°	1747.6	1747.6	1743.8	1724.9	1717.4	1709.9	1698.7	1672.3	1657.3	1627.3	1604.7
40°	1570.9	1567.1	1555.8	1552.1	1544.6	1533.3	1525.8	1510.7	1488.2	1465.7	1443.1
42.5°	1398.0	1401.8	1386.7	1390.5	1375.5	1368.0	1364.2	1341.6	1330.3	1307.8	1289.1
45°	1244.0	1240.2	1232.7	1229.0	1221.3	1213.8	1206.3	1195.1	1176.3	1153.7	1142.5
47.5°	1101.1	1089.8	1089.8	1086.1	1082.3	1067.3	1063.6	1052.2	1041.0	1018.5	1003.5
50°	965.8	965.8	965.8	962.1	950.8	947.1	939.5	928.2	917.0	902.0	879.4
52.5°	856.8	856.8	856.8	853.1	838.1	834.3	830.6	815.5	800.5	789.2	774.2
55°	755.4	759.1	755.4	747.9	736.6	736.6	725.4	717.8	702.7	691.5	676.5
57.5°	669.0	669.0	661.5	657.7	650.1	646.4	638.9	631.4	612.6	601.4	582.5
60°	586.2	582.5	582.5	575.0	567.5	560.0	556.2	545.0	537.4	518.6	503.6
62.5°	511.1	511.1	503.6	503.6	488.6	488.6	484.7	473.5	462.2	443.5	436.0
65°	439.7	439.7	436.0	432.2	420.9	417.1	413.4	402.1	390.9	379.6	368.2
67.5°	375.9	375.9	368.2	364.5	357.0	353.2	345.7	338.2	327.0	315.7	304.4
70°	315.7	311.9	308.1	304.4	296.9	293.1	285.6	278.1	266.9	259.4	248.0
72.5°	255.5	255.5	251.7	244.2	240.5	236.7	233.0	225.5	214.2	203.0	195.4
75°	199.1	199.1	199.1	191.6	184.1	180.4	180.4	172.9	165.4	154.1	146.6
77.5°	154.1	150.4	146.6	146.6	139.0	135.2	131.5	127.7	116.5	112.7	105.2
80°	105.2	109.0	105.2	101.5	97.7	94.0	94.0	86.5	82.6	75.1	67.6
82.5°	71.4	67.6	67.6	63.9	63.9	60.1	60.1	52.6	48.9	45.1	41.4
85°	37.6	37.6	33.9	33.9	33.9	30.1	30.1	26.3	26.3	22.5	18.8
87.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	7.5	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584963

CATALOG NUMBER: HCC8W55D010SL-HM82555835-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2
2.5°	2548.0	2540.4	2536.7	2536.7	2532.9	2529.2	2525.4	2521.7	2514.2	2514.2	2506.7
5°	2566.8	2559.3	2555.5	2544.3	2536.7	2536.7	2521.7	2517.9	2506.7	2499.2	2491.7
7.5°	2581.8	2566.8	2555.5	2544.3	2536.7	2529.2	2514.2	2499.2	2484.2	2469.1	2461.6
10°	2581.8	2566.8	2548.0	2529.2	2521.7	2514.2	2495.4	2472.8	2454.1	2439.0	2420.2
12.5°	2574.3	2551.8	2529.2	2514.2	2499.2	2487.9	2465.3	2442.8	2420.2	2390.2	2375.2
15°	2551.8	2521.7	2499.2	2472.8	2461.6	2442.8	2423.9	2390.2	2363.8	2337.6	2318.8
17.5°	2506.7	2469.1	2442.8	2416.4	2397.7	2386.4	2356.3	2326.3	2296.2	2266.2	2243.6
20°	2439.0	2405.2	2375.2	2341.3	2326.3	2311.2	2273.7	2243.6	2213.6	2179.7	2157.2
22.5°	2356.3	2322.6	2281.2	2254.8	2232.3	2213.6	2179.7	2145.9	2115.8	2085.8	2055.7
25°	2254.8	2221.1	2183.4	2142.2	2127.1	2108.3	2070.7	2036.9	2003.1	1969.2	1942.9
27.5°	2145.9	2100.8	2070.7	2025.6	2010.6	1991.8	1950.4	1912.9	1882.8	1856.6	1826.4
30°	2014.3	1980.6	1939.2	1897.8	1882.8	1864.1	1830.2	1796.3	1766.3	1736.2	1706.2
32.5°	1871.6	1837.7	1796.3	1766.3	1743.8	1728.7	1694.9	1664.8	1634.8	1604.7	1578.4
35°	1721.2	1683.6	1653.6	1623.5	1604.7	1586.0	1552.1	1525.8	1503.2	1477.0	1450.6
37.5°	1567.1	1540.8	1510.7	1477.0	1458.2	1443.1	1416.8	1386.7	1368.0	1345.5	1326.6
40°	1416.8	1386.7	1360.5	1330.3	1315.3	1304.1	1277.7	1255.2	1236.5	1217.6	1206.3
42.5°	1262.7	1236.5	1210.1	1191.3	1180.1	1168.7	1150.0	1123.7	1112.3	1093.6	1082.3
45°	1120.0	1097.3	1078.6	1052.2	1044.7	1037.2	1014.7	995.8	984.6	973.3	965.8
47.5°	984.6	969.6	947.1	932.0	920.7	913.2	898.2	883.1	871.9	864.4	856.8
50°	868.1	849.3	834.3	819.2	811.7	800.5	785.5	778.0	770.4	762.9	762.9
52.5°	759.1	740.4	725.4	714.1	706.5	699.0	687.7	684.0	676.5	676.5	672.7
55°	657.7	646.4	631.4	616.4	612.6	608.9	601.4	593.7	590.0	586.2	590.0
57.5°	571.2	560.0	545.0	533.6	529.9	526.1	522.4	514.9	511.1	511.1	511.1
60°	492.4	481.0	469.7	458.5	458.5	451.0	447.2	443.5	439.7	436.0	436.0
62.5°	420.9	409.6	398.4	390.9	387.1	383.4	375.9	372.1	368.2	368.2	364.5
65°	357.0	342.0	338.2	327.0	323.2	319.5	315.7	308.1	304.4	300.6	296.9
67.5°	293.1	285.6	274.4	266.9	263.1	259.4	255.5	248.0	244.2	240.5	233.0
70°	236.7	229.2	221.7	214.2	210.5	206.7	199.1	191.6	187.9	180.4	169.1
72.5°	184.1	176.6	169.1	161.6	157.9	154.1	146.6	139.0	131.5	124.0	116.5
75°	139.0	131.5	120.2	112.7	109.0	109.0	97.7	90.2	82.6	71.4	63.9
77.5°	97.7	86.5	82.6	75.1	71.4	63.9	56.4	48.9	41.4	37.6	30.1
80°	63.9	56.4	48.9	45.1	41.4	37.6	33.9	26.3	18.8	15.0	11.3
82.5°	37.6	33.9	30.1	26.3	22.5	18.8	15.0	15.0	11.3	7.5	3.8
85°	18.8	15.0	11.3	11.3	7.5	7.5	7.5	3.8	3.8	3.8	3.8
87.5°	7.5	3.8	3.8	3.8	3.8	3.8	3.8	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584963

CATALOG NUMBER: HCC8W55D010SL-HM82555835-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2
2.5°	2502.9	2499.2	2495.4	2491.7	2491.7	2484.2	2484.2	2480.3	2472.8	2469.1	2469.1
5°	2480.3	2469.1	2461.6	2457.8	2454.1	2442.8	2439.0	2431.5	2423.9	2416.4	2412.7
7.5°	2446.5	2427.8	2420.2	2416.4	2405.2	2393.9	2386.4	2375.2	2363.8	2352.6	2348.8
10°	2405.2	2386.4	2367.6	2360.1	2348.8	2341.3	2326.3	2311.2	2299.9	2288.7	2277.4
12.5°	2352.6	2330.1	2311.2	2303.7	2292.4	2277.4	2254.8	2247.3	2228.6	2221.1	2206.1
15°	2292.4	2266.2	2247.3	2236.1	2224.8	2202.3	2187.2	2172.2	2153.4	2145.9	2130.8
17.5°	2217.3	2187.2	2168.4	2157.2	2149.7	2130.8	2108.3	2089.6	2070.7	2063.2	2051.9
20°	2127.1	2108.3	2081.9	2070.7	2063.2	2040.7	2018.1	2010.6	1995.6	1980.6	1969.2
22.5°	2025.6	2006.8	1980.6	1969.2	1965.4	1946.7	1927.9	1916.7	1905.3	1894.1	1882.8
25°	1920.4	1897.8	1875.3	1867.8	1860.3	1845.2	1830.2	1822.7	1811.4	1803.9	1796.3
27.5°	1807.7	1785.1	1766.3	1755.1	1747.6	1736.2	1728.7	1721.2	1713.7	1706.2	1702.4
30°	1687.4	1664.8	1649.8	1642.3	1634.8	1631.1	1619.7	1616.0	1612.2	1604.7	1608.5
32.5°	1567.1	1548.3	1533.3	1522.1	1522.1	1514.6	1510.7	1510.7	1507.0	1507.0	1507.0
35°	1435.6	1424.3	1413.1	1409.3	1405.6	1401.8	1398.0	1401.8	1398.0	1401.8	1405.6
37.5°	1315.3	1304.1	1296.6	1292.8	1289.1	1292.8	1289.1	1289.1	1292.8	1300.3	1304.1
40°	1191.3	1183.8	1176.3	1180.1	1176.3	1176.3	1176.3	1187.6	1191.3	1195.1	1198.8
42.5°	1074.8	1067.3	1063.6	1063.6	1067.3	1063.6	1071.1	1074.8	1082.3	1093.6	1101.1
45°	962.1	958.3	958.3	962.1	958.3	965.8	965.8	973.3	984.6	992.1	999.7
47.5°	856.8	856.8	856.8	860.6	860.6	864.4	871.9	875.6	883.1	890.7	898.2
50°	759.1	762.9	766.6	766.6	766.6	774.2	781.7	785.5	789.2	793.0	804.2
52.5°	672.7	676.5	676.5	680.2	684.0	687.7	691.5	699.0	702.7	710.2	714.1
55°	590.0	590.0	597.5	601.4	601.4	601.4	608.9	608.9	616.4	620.1	627.6
57.5°	511.1	514.9	514.9	518.6	518.6	522.4	526.1	529.9	533.6	537.4	541.1
60°	436.0	436.0	436.0	439.7	443.5	447.2	443.5	451.0	451.0	458.5	462.2
62.5°	364.5	368.2	368.2	368.2	368.2	368.2	368.2	372.1	375.9	379.6	383.4
65°	296.9	296.9	296.9	293.1	296.9	293.1	296.9	300.6	300.6	304.4	308.1
67.5°	229.2	229.2	221.7	221.7	225.5	225.5	225.5	225.5	221.7	229.2	229.2
70°	165.4	161.6	157.9	154.1	154.1	150.4	150.4	146.6	146.6	146.6	146.6
72.5°	109.0	101.5	94.0	90.2	86.5	86.5	78.9	75.1	78.9	78.9	78.9
75°	56.4	48.9	45.1	41.4	37.6	37.6	33.9	33.9	33.9	33.9	33.9
77.5°	22.5	18.8	15.0	15.0	11.3	11.3	11.3	11.3	11.3	11.3	11.3
80°	7.5	7.5	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
85°	3.8	0.0	0.0	3.8	0.0	3.8	3.8	3.8	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584963

CATALOG NUMBER: HCC8W55D010SL-HM82555835-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2	2514.2
2.5°	2465.3	2465.3	2461.6	2465.3	2457.8	2461.6	2457.8	2457.8
5°	2408.9	2401.4	2401.4	2401.4	2397.7	2397.7	2393.9	2393.9
7.5°	2341.3	2337.6	2333.8	2330.1	2326.3	2322.6	2322.6	2322.6
10°	2273.7	2266.2	2266.2	2262.4	2254.8	2251.1	2251.1	2251.1
12.5°	2194.7	2190.9	2187.2	2187.2	2172.2	2175.9	2172.2	2172.2
15°	2119.6	2115.8	2115.8	2104.6	2097.1	2097.1	2097.1	2093.3
17.5°	2040.7	2036.9	2033.2	2025.6	2018.1	2018.1	2014.3	2018.1
20°	1957.9	1954.2	1946.7	1946.7	1942.9	1939.2	1931.7	1935.4
22.5°	1875.3	1867.8	1864.1	1864.1	1860.3	1860.3	1852.7	1852.7
25°	1788.8	1785.1	1781.3	1785.1	1777.6	1777.6	1770.1	1770.1
27.5°	1698.7	1694.9	1694.9	1694.9	1691.2	1694.9	1691.2	1691.2
30°	1608.5	1608.5	1604.7	1604.7	1608.5	1604.7	1608.5	1612.2
32.5°	1510.7	1510.7	1514.6	1514.6	1518.3	1518.3	1518.3	1518.3
35°	1409.3	1416.8	1416.8	1420.6	1424.3	1428.1	1428.1	1431.8
37.5°	1315.3	1319.1	1322.8	1326.6	1334.1	1334.1	1334.1	1334.1
40°	1213.8	1217.6	1225.1	1221.3	1236.5	1240.2	1236.5	1236.5
42.5°	1108.6	1116.2	1120.0	1127.5	1131.2	1138.7	1142.5	1142.5
45°	1011.0	1014.7	1022.2	1029.7	1033.5	1044.7	1044.7	1044.7
47.5°	909.5	917.0	920.7	928.2	932.0	943.3	947.1	943.3
50°	811.7	819.2	826.7	826.7	838.1	841.8	849.3	853.1
52.5°	717.8	721.6	729.1	732.9	740.4	747.9	751.6	755.4
55°	627.6	631.4	638.9	638.9	650.1	653.9	661.5	661.5
57.5°	545.0	548.7	556.2	552.5	560.0	567.5	567.5	563.7
60°	466.0	466.0	466.0	473.5	477.2	481.0	484.7	484.7
62.5°	383.4	390.9	394.6	394.6	398.4	402.1	402.1	398.4
65°	308.1	315.7	319.5	319.5	323.2	323.2	323.2	327.0
67.5°	233.0	233.0	233.0	236.7	233.0	233.0	233.0	233.0
70°	146.6	146.6	146.6	146.6	142.9	146.6	146.6	150.4
72.5°	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9
75°	33.9	33.9	33.9	37.6	33.9	33.9	33.9	33.9
77.5°	15.0	11.3	15.0	15.0	11.3	11.3	11.3	11.3
80°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
85°	0.0	3.8	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)