

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585015

Luminaire Tested: **HCC8S55D010MW-HM82555930-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585015  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S55D010MW-HM82555930-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4741.3 lumens  
Efficiency: N/A  
Efficacy: 91.2 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585015  
CATALOG NUMBER: HCC8S55D010MW-HM82555930-81WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P585015

CATALOG NUMBER: HCC8S55D010MW-HM82555930-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	79218	79218	79218
5°	82004	78766	75639
10°	83825	77388	71385
15°	85017	74782	66658
20°	84762	71150	61886
25°	82668	66538	56810
30°	78321	61190	52132
35°	71253	55375	47371
40°	62583	49255	42798
45°	54577	43326	38154
50°	47493	37961	33610
55°	42353	33359	29235
60°	38484	29239	24934
65°	34593	25436	22634
70°	30798	21683	20421
75°	26986	18276	17442
80°	22890	14863	15485
85°	17266	11110	12312



TEST NUMBER: P585015  
 CATALOG NUMBER: HCC8S55D010MW-HM82555930-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	240.6	5.1
10°-20°	663.0	14.0
20°-30°	920.3	19.4
30°-40°	951.5	20.1
40°-50°	796.7	16.8
50°-60°	578.4	12.2
60°-70°	365.0	7.7
70°-80°	180.8	3.8
80°-90°	44.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1824.0	38.5
0°-40°	2775.5	58.5
0°-60°	4150.6	87.5
0°-90°	4741.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4741.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2569	2569	2569	2569	2569	
5°	2649	2618	2545	2475	2444	253
15°	2663	2562	2342	2154	2088	750
25°	2430	2273	1956	1743	1670	1113
35°	1893	1753	1471	1304	1258	1179
45°	1252	1161	994	896	875	968
55°	788	718	620	568	544	711
65°	474	415	349	307	310	473
75°	226	188	153	146	146	243
85°	49	38	31	35	35	59
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585015

CATALOG NUMBER: HCC8S55D010MW-HM82555930-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0
2.5°	2610.9	2610.9	2614.4	2610.9	2610.9	2610.9	2607.5	2607.5	2603.9	2603.9	2596.9
5°	2649.2	2642.3	2649.2	2642.3	2642.3	2642.3	2638.8	2631.8	2628.3	2621.4	2617.9
7.5°	2666.7	2663.1	2663.1	2659.7	2659.7	2656.2	2652.7	2649.2	2635.4	2631.8	2621.4
10°	2677.1	2673.7	2673.7	2670.2	2663.1	2663.1	2656.2	2652.7	2635.4	2628.3	2614.4
12.5°	2673.7	2673.7	2673.7	2670.2	2659.7	2656.2	2649.2	2638.8	2624.8	2610.9	2596.9
15°	2663.1	2663.1	2656.2	2652.7	2642.3	2635.4	2631.8	2614.4	2600.4	2583.0	2562.1
17.5°	2628.3	2628.3	2624.8	2617.9	2607.5	2600.4	2593.5	2576.1	2562.1	2534.2	2513.4
20°	2583.0	2579.6	2576.1	2565.6	2555.1	2551.7	2541.1	2516.8	2499.4	2478.4	2450.5
22.5°	2516.8	2513.4	2509.8	2502.8	2485.5	2478.4	2471.5	2454.1	2422.6	2401.8	2366.9
25°	2429.7	2429.7	2422.6	2412.2	2394.7	2387.8	2377.4	2359.9	2332.0	2300.6	2272.7
27.5°	2328.5	2325.0	2314.6	2307.7	2293.7	2283.3	2265.8	2244.8	2217.0	2192.6	2157.8
30°	2199.6	2199.6	2192.6	2182.1	2164.7	2157.8	2143.8	2119.4	2091.6	2060.1	2035.8
32.5°	2053.1	2053.1	2042.7	2035.8	2025.3	2007.9	2004.4	1976.5	1952.1	1927.7	1899.8
35°	1892.8	1896.3	1889.4	1875.4	1858.0	1858.0	1850.9	1826.6	1798.7	1774.3	1753.4
37.5°	1732.5	1722.0	1718.5	1711.6	1701.0	1687.1	1680.2	1669.7	1645.4	1627.9	1596.5
40°	1554.7	1558.2	1551.3	1544.2	1540.7	1530.3	1526.8	1509.4	1492.0	1471.0	1457.0
42.5°	1394.3	1394.3	1394.3	1387.4	1380.4	1370.0	1366.4	1356.0	1335.0	1321.2	1300.2
45°	1251.5	1240.9	1240.9	1237.5	1234.0	1227.0	1216.5	1209.6	1195.7	1185.2	1160.7
47.5°	1112.0	1115.5	1112.0	1108.5	1098.0	1094.5	1091.0	1077.2	1063.2	1052.7	1035.3
50°	990.0	996.9	990.0	990.0	983.0	979.6	972.5	962.1	951.7	934.2	916.7
52.5°	888.8	888.8	885.4	881.9	871.5	864.5	861.0	857.6	840.1	826.1	812.2
55°	787.8	791.3	791.3	780.8	777.4	770.4	766.8	756.4	749.5	728.5	718.1
57.5°	700.6	697.2	700.6	693.7	686.7	679.8	676.2	669.3	658.8	644.8	630.9
60°	624.0	616.9	616.9	613.5	606.5	603.0	596.1	585.6	575.2	561.3	550.7
62.5°	547.3	543.8	540.3	536.8	529.9	526.3	522.8	512.4	502.0	491.5	481.1
65°	474.1	474.1	470.6	463.6	460.1	456.6	453.2	446.2	432.2	425.3	414.8
67.5°	407.9	404.3	404.3	397.4	390.4	386.9	386.9	380.0	369.5	359.1	352.1
70°	341.6	345.2	341.6	338.1	331.2	331.2	324.2	320.7	306.7	303.3	292.8
72.5°	282.3	282.3	278.8	278.8	271.9	268.4	268.4	261.5	254.4	247.5	240.5
75°	226.5	226.5	226.5	223.1	219.6	212.6	212.6	209.2	202.2	195.3	188.2
77.5°	177.8	174.3	174.3	170.8	167.4	163.8	163.8	160.3	153.4	149.9	142.9
80°	128.9	125.5	125.5	125.5	118.5	122.0	118.5	115.1	111.6	108.1	104.5
82.5°	83.7	87.2	87.2	83.7	80.2	80.2	80.2	76.6	76.6	73.2	69.7
85°	48.8	48.8	48.8	48.8	45.4	45.4	45.4	41.8	41.8	41.8	38.3
87.5°	20.9	20.9	20.9	20.9	20.9	20.9	17.5	17.5	17.5	17.5	17.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585015

CATALOG NUMBER: HCC8S55D010MW-HM82555930-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0
2.5°	2596.9	2590.0	2586.5	2583.0	2583.0	2579.6	2576.1	2569.0	2569.0	2562.1	2558.6
5°	2610.9	2600.4	2593.5	2586.5	2583.0	2576.1	2569.0	2558.6	2555.1	2544.6	2534.2
7.5°	2614.4	2596.9	2590.0	2576.1	2569.0	2562.1	2548.2	2537.7	2523.8	2513.4	2499.4
10°	2600.4	2586.5	2569.0	2551.7	2548.2	2537.7	2516.8	2502.8	2485.5	2471.5	2450.5
12.5°	2579.6	2558.6	2541.1	2520.3	2509.8	2499.4	2478.4	2457.6	2433.1	2408.7	2387.8
15°	2544.6	2520.3	2495.9	2471.5	2457.6	2447.0	2422.6	2398.3	2373.9	2342.5	2321.6
17.5°	2492.4	2464.5	2440.1	2408.7	2394.7	2384.3	2352.9	2325.0	2293.7	2262.3	2241.4
20°	2426.2	2391.3	2363.5	2328.5	2318.1	2300.6	2269.3	2237.9	2203.0	2168.2	2143.8
22.5°	2339.0	2304.2	2272.7	2237.9	2220.5	2203.0	2171.7	2133.4	2098.5	2070.6	2046.2
25°	2237.9	2206.5	2168.2	2136.8	2115.9	2095.0	2060.1	2028.7	1997.4	1955.6	1931.1
27.5°	2126.4	2088.0	2060.1	2018.3	1997.4	1983.5	1945.1	1903.3	1875.4	1837.0	1809.1
30°	2000.8	1966.0	1934.6	1892.8	1871.9	1858.0	1823.0	1784.7	1756.8	1718.5	1690.6
32.5°	1868.4	1830.1	1791.8	1763.9	1739.5	1725.5	1687.1	1662.7	1627.9	1596.5	1565.2
35°	1725.5	1687.1	1659.3	1620.9	1606.9	1593.0	1561.7	1530.3	1498.9	1471.0	1446.6
37.5°	1572.1	1544.2	1512.8	1484.9	1474.5	1460.5	1422.2	1394.3	1370.0	1342.1	1321.2
40°	1422.2	1397.8	1376.9	1349.0	1331.6	1321.2	1293.3	1268.8	1240.9	1223.6	1202.6
42.5°	1286.3	1258.4	1237.5	1216.5	1199.2	1188.6	1164.3	1146.8	1125.9	1108.5	1084.1
45°	1143.4	1129.5	1105.0	1087.6	1077.2	1063.2	1045.8	1024.8	1007.5	993.5	976.0
47.5°	1017.9	1003.9	986.5	965.6	958.6	948.1	930.7	916.7	902.8	888.8	871.5
50°	902.8	885.4	871.5	857.6	850.5	840.1	822.6	815.7	805.3	791.3	780.8
52.5°	798.2	784.3	770.4	752.9	749.5	742.5	732.0	718.1	707.7	700.6	693.7
55°	704.1	690.2	679.8	665.8	662.3	655.4	641.4	634.4	627.5	620.5	613.5
57.5°	620.5	606.5	592.6	585.6	578.6	571.7	568.2	557.8	550.7	547.3	540.3
60°	543.8	529.9	519.4	508.9	505.5	502.0	494.9	488.0	481.1	474.1	470.6
62.5°	470.6	456.6	449.7	442.7	435.7	435.7	428.7	421.8	414.8	411.4	404.3
65°	404.3	397.4	386.9	376.4	372.9	372.9	362.5	359.1	355.6	348.6	341.6
67.5°	341.6	334.6	324.2	320.7	317.3	313.7	310.2	303.3	296.3	292.8	285.9
70°	285.9	278.8	271.9	268.4	264.9	261.5	254.4	250.9	244.0	240.5	237.1
72.5°	230.1	226.5	219.6	216.1	212.6	209.2	205.7	202.2	195.3	191.7	188.2
75°	184.7	181.3	174.3	170.8	167.4	167.4	163.8	156.8	153.4	153.4	149.9
77.5°	139.5	136.0	132.4	128.9	125.5	125.5	122.0	118.5	115.1	115.1	111.6
80°	101.1	97.6	94.1	94.1	94.1	90.6	87.2	87.2	83.7	83.7	80.2
82.5°	66.2	66.2	62.7	62.7	62.7	59.3	59.3	55.8	55.8	55.8	55.8
85°	38.3	38.3	38.3	34.8	34.8	34.8	34.8	34.8	34.8	31.4	34.8
87.5°	17.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585015

CATALOG NUMBER: HCC8S55D010MW-HM82555930-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0
2.5°	2555.1	2551.7	2544.6	2544.6	2537.7	2537.7	2534.2	2530.7	2527.3	2523.8	2520.3
5°	2530.7	2516.8	2509.8	2506.3	2499.4	2495.9	2485.5	2478.4	2474.9	2468.0	2461.0
7.5°	2485.5	2471.5	2457.6	2454.1	2450.5	2436.6	2426.2	2415.7	2408.7	2401.8	2394.7
10°	2433.1	2419.1	2401.8	2394.7	2387.8	2370.4	2356.4	2346.0	2332.0	2318.1	2314.6
12.5°	2370.4	2349.5	2328.5	2321.6	2311.1	2293.7	2279.8	2262.3	2251.9	2234.4	2230.9
15°	2297.1	2272.7	2255.4	2237.9	2230.9	2213.6	2189.1	2175.1	2154.3	2147.3	2129.9
17.5°	2210.0	2185.7	2161.3	2154.3	2143.8	2119.4	2095.0	2077.6	2056.6	2046.2	2035.8
20°	2119.4	2088.0	2063.7	2056.6	2042.7	2021.8	1997.4	1980.0	1962.5	1941.7	1931.1
22.5°	2014.8	1980.0	1959.0	1941.7	1938.1	1913.8	1885.9	1871.9	1858.0	1840.5	1826.6
25°	1899.8	1868.4	1844.0	1830.1	1823.0	1802.2	1781.3	1763.9	1742.9	1732.5	1715.0
27.5°	1781.3	1760.3	1728.9	1715.0	1704.6	1687.1	1662.7	1652.3	1631.4	1617.5	1606.9
30°	1666.2	1634.8	1617.5	1600.0	1589.6	1572.1	1551.3	1540.7	1523.4	1509.4	1498.9
32.5°	1540.7	1519.8	1495.5	1488.4	1474.5	1457.0	1443.2	1425.7	1411.8	1397.8	1394.3
35°	1425.7	1397.8	1373.5	1366.4	1356.0	1338.5	1331.6	1321.2	1303.7	1300.2	1286.3
37.5°	1300.2	1286.3	1258.4	1247.9	1244.4	1230.5	1216.5	1209.6	1199.2	1188.6	1185.2
40°	1181.7	1164.3	1150.3	1139.9	1132.9	1122.4	1108.5	1105.0	1098.0	1084.1	1080.6
42.5°	1070.2	1052.7	1038.7	1035.3	1024.8	1014.4	1007.5	996.9	993.5	990.0	983.0
45°	962.1	951.7	937.7	934.2	930.7	916.7	909.8	902.8	895.9	892.4	885.4
47.5°	864.5	854.0	843.6	840.1	833.2	829.7	819.2	815.7	805.3	801.8	798.2
50°	770.4	763.4	756.4	752.9	746.0	742.5	735.5	728.5	721.6	718.1	714.6
52.5°	686.7	679.8	672.7	669.3	665.8	658.8	651.9	644.8	641.4	637.9	634.4
55°	606.5	599.6	596.1	592.6	589.2	585.6	575.2	571.7	568.2	564.7	557.8
57.5°	533.4	526.3	519.4	519.4	515.9	512.4	505.5	498.5	498.5	491.5	484.5
60°	467.2	460.1	453.2	449.7	446.2	439.3	435.7	432.2	428.7	425.3	418.3
62.5°	397.4	393.9	386.9	386.9	380.0	376.4	372.9	369.5	366.0	359.1	355.6
65°	338.1	334.6	327.7	324.2	324.2	320.7	313.7	310.2	306.7	306.7	303.3
67.5°	282.3	278.8	271.9	268.4	268.4	264.9	261.5	261.5	258.0	254.4	258.0
70°	233.6	226.5	226.5	223.1	223.1	219.6	216.1	216.1	216.1	219.6	219.6
72.5°	184.7	181.3	177.8	177.8	177.8	177.8	174.3	174.3	177.8	181.3	181.3
75°	146.4	142.9	142.9	142.9	139.5	139.5	142.9	142.9	146.4	146.4	146.4
77.5°	108.1	108.1	108.1	108.1	108.1	108.1	111.6	111.6	115.1	115.1	115.1
80°	80.2	80.2	80.2	80.2	80.2	83.7	83.7	83.7	83.7	83.7	87.2
82.5°	55.8	55.8	55.8	55.8	55.8	55.8	55.8	59.3	59.3	59.3	59.3
85°	31.4	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585015

CATALOG NUMBER: HCC8S55D010MW-HM82555930-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0	2569.0
2.5°	2516.8	2516.8	2516.8	2520.3	2513.4	2513.4	2513.4	2513.4
5°	2457.6	2454.1	2450.5	2454.1	2447.0	2447.0	2443.6	2443.6
7.5°	2384.3	2380.8	2377.4	2377.4	2370.4	2370.4	2366.9	2363.5
10°	2304.2	2297.1	2300.6	2293.7	2290.2	2286.7	2283.3	2279.8
12.5°	2217.0	2210.0	2206.5	2199.6	2192.6	2189.1	2192.6	2185.7
15°	2122.8	2112.4	2108.9	2102.0	2095.0	2091.6	2091.6	2088.0
17.5°	2018.3	2011.4	2007.9	2000.8	1997.4	1990.4	1986.9	1983.5
20°	1920.7	1903.3	1906.7	1899.8	1896.3	1882.3	1882.3	1885.9
22.5°	1812.6	1802.2	1795.3	1788.2	1784.7	1777.8	1777.8	1774.3
25°	1704.6	1694.1	1690.6	1683.7	1680.2	1673.3	1669.7	1669.7
27.5°	1600.0	1586.1	1586.1	1579.0	1572.1	1568.6	1565.2	1561.7
30°	1488.4	1478.0	1474.5	1474.5	1471.0	1471.0	1460.5	1464.1
32.5°	1383.9	1376.9	1373.5	1366.4	1366.4	1362.9	1362.9	1352.5
35°	1279.4	1268.8	1272.3	1265.4	1261.9	1258.4	1261.9	1258.4
37.5°	1178.2	1171.3	1171.3	1164.3	1164.3	1160.7	1157.4	1164.3
40°	1077.2	1073.7	1070.2	1066.6	1070.2	1066.6	1059.7	1063.2
42.5°	976.0	976.0	972.5	972.5	969.0	969.0	969.0	969.0
45°	885.4	881.9	881.9	878.4	878.4	878.4	878.4	874.9
47.5°	794.7	791.3	791.3	791.3	787.8	787.8	784.3	787.8
50°	707.7	707.7	704.1	704.1	707.7	704.1	700.6	700.6
52.5°	627.5	627.5	624.0	624.0	620.5	616.9	620.5	620.5
55°	554.2	550.7	547.3	547.3	543.8	540.3	540.3	543.8
57.5°	484.5	481.1	477.6	477.6	470.6	467.2	467.2	467.2
60°	418.3	411.4	411.4	407.9	407.9	404.3	404.3	404.3
62.5°	355.6	352.1	352.1	352.1	352.1	348.6	348.6	348.6
65°	303.3	303.3	303.3	306.7	306.7	310.2	310.2	310.2
67.5°	261.5	264.9	264.9	264.9	268.4	268.4	268.4	264.9
70°	223.1	223.1	223.1	226.5	226.5	226.5	226.5	226.5
72.5°	184.7	184.7	184.7	184.7	184.7	184.7	184.7	184.7
75°	146.4	149.9	149.9	149.9	146.4	149.9	149.9	146.4
77.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1
80°	87.2	87.2	87.2	87.2	87.2	87.2	87.2	87.2
82.5°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
85°	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)