

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585007

Luminaire Tested: **HCC8S55D010SL-HM82555930-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585007  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S55D010SL-HM82555930-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4964.4 lumens  
Efficiency: N/A  
Efficacy: 95.5 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585007  
CATALOG NUMBER: HCC8S55D010SL-HM82555930-81RWWC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585007

CATALOG NUMBER: HCC8S55D010SL-HM82555930-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	80544	80544	80544
5°	81610	80208	79453
10°	82445	79388	78189
15°	83277	77710	76152
20°	82859	74845	73126
25°	80926	70362	69413
30°	76864	65317	65068
35°	69973	59602	60125
40°	61351	53345	55313
45°	52924	47451	50800
50°	46342	41655	46006
55°	41063	35805	40493
60°	36991	30115	33550
65°	33330	24173	25698
70°	29239	17608	14146
75°	24925	9150	3741
80°	19196	2468	622
85°	12348	0	0



TEST NUMBER: P585007  
 CATALOG NUMBER: HCC8S55D010SL-HM82555930-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	246.4	5.0
10°-20°	692.8	14.0
20°-30°	983.4	19.8
30°-40°	1035.1	20.9
40°-50°	880.6	17.7
50°-60°	636.3	12.8
60°-70°	361.9	7.3
70°-80°	114.0	2.3
80°-90°	13.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1922.6	38.7
0°-40°	2957.7	59.6
0°-60°	4474.6	90.1
0°-90°	4964.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4964.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2612	2612	2612	2612	2612	
5°	2636	2623	2591	2574	2567	252
15°	2609	2542	2434	2389	2385	735
25°	2378	2260	2068	2033	2040	1089
35°	1859	1751	1583	1573	1597	1157
45°	1214	1168	1088	1116	1165	943
55°	764	708	666	704	753	689
65°	457	394	331	328	352	453
75°	209	160	77	35	31	225
85°	35	21	0	0	0	45
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585007

CATALOG NUMBER: HCC8S55D010SL-HM82555930-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0
2.5°	2626.0	2629.5	2622.6	2622.6	2629.5	2622.6	2626.0	2626.0	2622.6	2622.6	2619.1
5°	2636.5	2633.0	2633.0	2633.0	2636.5	2629.5	2626.0	2629.5	2622.6	2622.6	2622.6
7.5°	2640.0	2640.0	2636.5	2633.0	2633.0	2633.0	2629.5	2626.0	2622.6	2615.6	2612.0
10°	2633.0	2633.0	2636.5	2629.5	2629.5	2622.6	2622.6	2615.6	2615.6	2608.6	2598.1
12.5°	2626.0	2622.6	2622.6	2615.6	2615.6	2608.6	2608.6	2598.1	2594.7	2584.1	2573.7
15°	2608.6	2605.1	2598.1	2594.7	2591.2	2587.7	2580.7	2577.2	2566.8	2552.9	2542.3
17.5°	2573.7	2570.2	2566.8	2559.8	2552.9	2549.3	2545.8	2535.4	2521.4	2511.0	2493.5
20°	2525.0	2521.4	2521.4	2511.0	2507.5	2497.1	2493.5	2479.6	2469.1	2448.2	2434.2
22.5°	2458.6	2462.1	2455.1	2448.2	2441.2	2430.7	2423.8	2409.9	2392.4	2371.4	2354.1
25°	2378.5	2382.0	2374.9	2368.0	2357.5	2350.6	2343.5	2322.7	2305.2	2280.8	2259.9
27.5°	2277.3	2277.3	2277.3	2270.3	2252.9	2249.4	2242.4	2221.5	2197.0	2176.2	2155.2
30°	2158.7	2155.2	2155.2	2144.8	2137.8	2123.9	2113.4	2096.0	2078.5	2054.0	2029.7
32.5°	2015.7	2019.2	2008.8	2001.8	1991.3	1991.3	1977.4	1963.5	1942.5	1918.1	1893.7
35°	1858.8	1862.3	1855.3	1851.9	1834.4	1830.9	1827.4	1810.0	1796.0	1778.6	1750.7
37.5°	1698.3	1694.9	1691.4	1691.4	1681.0	1674.0	1667.1	1656.5	1635.6	1621.7	1607.7
40°	1524.1	1524.1	1524.1	1520.6	1517.0	1510.0	1506.6	1499.6	1485.6	1471.7	1461.2
42.5°	1367.0	1367.0	1363.6	1360.1	1353.1	1356.6	1349.7	1342.6	1328.7	1318.3	1311.2
45°	1213.6	1213.6	1213.6	1217.1	1210.1	1199.7	1199.7	1192.7	1185.7	1178.8	1168.2
47.5°	1077.7	1088.1	1081.1	1077.7	1081.1	1067.1	1067.1	1060.2	1053.2	1046.2	1032.3
50°	966.0	966.0	966.0	959.0	955.5	955.5	945.1	938.1	934.7	927.6	913.7
52.5°	864.9	857.9	857.9	854.4	851.0	844.0	844.0	837.0	823.0	816.1	805.6
55°	763.8	763.8	760.3	756.8	753.2	749.8	746.3	735.9	728.9	718.4	708.0
57.5°	673.1	680.0	676.6	669.6	662.6	662.6	655.6	648.7	638.2	627.7	617.3
60°	599.8	596.3	596.3	592.9	585.9	582.4	579.0	568.4	558.0	547.6	537.0
62.5°	523.1	523.1	523.1	516.1	509.1	505.7	502.2	495.2	481.2	470.8	463.9
65°	456.8	453.3	449.9	446.4	442.9	436.0	432.5	425.4	415.0	404.6	394.0
67.5°	390.6	387.1	387.1	383.6	373.2	369.6	369.6	359.2	348.8	338.2	327.8
70°	324.3	324.3	324.3	317.4	313.9	310.3	306.9	299.9	289.5	279.1	268.5
72.5°	268.5	265.0	265.0	261.6	251.0	247.6	244.1	237.1	226.7	219.8	212.7
75°	209.2	209.2	205.8	202.3	198.8	195.3	191.9	184.8	174.4	164.0	160.4
77.5°	160.4	156.9	156.9	153.4	146.5	143.0	143.0	136.0	125.5	118.6	111.6
80°	108.1	111.6	108.1	104.7	101.1	97.6	94.1	90.7	83.7	76.8	69.7
82.5°	66.2	69.7	66.2	66.2	62.8	59.3	59.3	52.3	48.9	45.4	41.8
85°	34.9	34.9	34.9	34.9	31.4	31.4	31.4	27.9	24.4	21.0	21.0
87.5°	10.4	13.9	10.4	10.4	10.4	10.4	10.4	10.4	7.0	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585007

CATALOG NUMBER: HCC8S55D010SL-HM82555930-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0
2.5°	2622.6	2619.1	2615.6	2615.6	2615.6	2615.6	2615.6	2612.0	2608.6	2608.6	2608.6
5°	2615.6	2615.6	2615.6	2612.0	2608.6	2608.6	2601.6	2598.1	2594.7	2591.2	2587.7
7.5°	2608.6	2601.6	2598.1	2594.7	2591.2	2591.2	2584.1	2577.2	2577.2	2570.2	2563.3
10°	2587.7	2584.1	2577.2	2570.2	2566.8	2563.3	2556.2	2545.8	2542.3	2535.4	2528.4
12.5°	2563.3	2556.2	2549.3	2535.4	2531.9	2528.4	2514.4	2504.0	2497.1	2493.5	2476.1
15°	2531.9	2517.9	2507.5	2490.0	2486.5	2479.6	2469.1	2458.6	2444.7	2434.2	2427.2
17.5°	2476.1	2462.1	2444.7	2427.2	2420.3	2420.3	2402.8	2388.9	2371.4	2364.5	2350.6
20°	2409.9	2392.4	2378.5	2357.5	2347.0	2336.6	2326.1	2305.2	2291.3	2280.8	2263.4
22.5°	2333.1	2308.7	2291.3	2270.3	2252.9	2242.4	2225.0	2207.6	2190.1	2179.7	2165.7
25°	2235.5	2214.5	2186.6	2165.7	2155.2	2141.2	2120.4	2102.9	2085.5	2068.0	2061.1
27.5°	2127.3	2099.4	2075.0	2050.6	2040.1	2029.7	2005.3	1984.3	1970.4	1953.0	1946.0
30°	2008.8	1980.9	1953.0	1932.0	1921.6	1904.1	1890.2	1865.8	1848.4	1834.4	1817.0
32.5°	1872.7	1851.9	1827.4	1796.0	1789.1	1775.1	1754.1	1743.7	1722.8	1712.3	1698.3
35°	1726.2	1712.3	1687.9	1663.5	1653.0	1646.1	1628.6	1607.7	1593.8	1583.3	1576.3
37.5°	1586.8	1569.3	1544.9	1527.5	1520.6	1510.0	1489.1	1478.7	1464.8	1457.7	1443.8
40°	1436.9	1419.4	1401.9	1391.5	1381.0	1374.1	1360.1	1349.7	1335.7	1325.2	1321.8
42.5°	1290.4	1279.9	1266.0	1252.0	1248.5	1238.0	1231.1	1220.6	1210.1	1206.7	1196.1
45°	1157.8	1147.4	1133.4	1119.5	1116.0	1109.1	1105.5	1095.0	1088.1	1088.1	1088.1
47.5°	1025.3	1014.8	1000.9	994.0	997.4	983.4	983.4	980.0	973.0	973.0	976.5
50°	906.8	892.8	889.3	882.3	875.4	868.3	871.9	861.4	861.4	868.3	864.9
52.5°	795.1	781.1	777.7	770.7	767.2	767.2	763.8	763.8	760.3	763.8	763.8
55°	694.1	683.5	676.6	669.6	666.0	666.0	666.0	662.6	659.1	666.0	669.6
57.5°	603.3	599.8	592.9	582.4	579.0	575.5	571.9	571.9	571.9	571.9	575.5
60°	523.1	516.1	509.1	498.7	498.7	495.2	491.8	488.3	488.3	488.3	488.3
62.5°	453.3	442.9	432.5	425.4	422.0	418.5	415.0	408.0	408.0	408.0	408.0
65°	383.6	373.2	366.1	359.2	352.2	352.2	345.3	341.8	334.8	331.3	324.3
67.5°	317.4	310.3	303.4	293.0	289.5	286.0	279.1	275.5	265.0	261.6	258.1
70°	258.1	247.6	240.6	233.7	230.2	223.1	216.2	209.2	202.3	195.3	188.3
72.5°	202.3	191.9	184.8	177.9	170.9	170.9	160.4	153.4	143.0	136.0	125.5
75°	150.0	139.5	132.6	122.0	118.6	115.1	104.7	97.6	87.2	76.8	69.7
77.5°	101.1	94.1	87.2	76.8	69.7	69.7	59.3	52.3	45.4	34.9	31.4
80°	62.8	55.8	48.9	41.8	41.8	34.9	31.4	24.4	17.5	13.9	10.4
82.5°	34.9	31.4	27.9	21.0	21.0	17.5	13.9	10.4	7.0	3.5	3.5
85°	17.5	13.9	10.4	10.4	7.0	7.0	7.0	3.5	3.5	0.0	0.0
87.5°	7.0	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585007

CATALOG NUMBER: HCC8S55D010SL-HM82555930-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0
2.5°	2605.1	2605.1	2601.6	2601.6	2601.6	2598.1	2601.6	2598.1	2598.1	2598.1	2601.6
5°	2591.2	2584.1	2584.1	2580.7	2580.7	2577.2	2580.7	2577.2	2573.7	2570.2	2573.7
7.5°	2563.3	2556.2	2552.9	2549.3	2549.3	2549.3	2545.8	2542.3	2545.8	2535.4	2542.3
10°	2525.0	2521.4	2514.4	2511.0	2507.5	2511.0	2507.5	2500.5	2500.5	2500.5	2497.1
12.5°	2476.1	2469.1	2465.7	2462.1	2455.1	2455.1	2458.6	2451.7	2451.7	2444.7	2444.7
15°	2416.8	2409.9	2402.8	2402.8	2395.9	2395.9	2392.4	2392.4	2388.9	2385.4	2385.4
17.5°	2343.5	2333.1	2326.1	2329.6	2326.1	2322.7	2322.7	2315.6	2312.1	2315.6	2315.6
20°	2256.3	2249.4	2242.4	2245.9	2239.0	2235.5	2239.0	2228.4	2232.0	2232.0	2232.0
22.5°	2158.7	2155.2	2144.8	2144.8	2137.8	2134.3	2137.8	2137.8	2141.2	2137.8	2137.8
25°	2050.6	2043.6	2036.7	2036.7	2033.2	2029.7	2033.2	2036.7	2033.2	2036.7	2036.7
27.5°	1935.6	1925.0	1925.0	1918.1	1918.1	1921.6	1918.1	1921.6	1925.0	1925.0	1932.0
30°	1810.0	1806.5	1803.0	1799.5	1799.5	1803.0	1803.0	1803.0	1806.5	1813.4	1813.4
32.5°	1691.4	1684.4	1677.5	1677.5	1684.4	1681.0	1684.4	1684.4	1691.4	1691.4	1698.3
35°	1562.4	1562.4	1555.4	1558.9	1558.9	1558.9	1558.9	1565.9	1572.8	1576.3	1583.3
37.5°	1443.8	1433.4	1436.9	1436.9	1440.3	1436.9	1447.3	1447.3	1454.2	1454.2	1461.2
40°	1314.7	1314.7	1318.3	1314.7	1318.3	1318.3	1325.2	1332.2	1335.7	1342.6	1346.2
42.5°	1192.7	1199.7	1192.7	1196.1	1199.7	1203.2	1206.7	1210.1	1224.0	1231.1	1241.5
45°	1081.1	1084.6	1088.1	1091.6	1088.1	1095.0	1098.5	1105.5	1116.0	1119.5	1123.0
47.5°	973.0	976.5	980.0	983.4	983.4	990.5	994.0	1000.9	1007.9	1011.3	1014.8
50°	868.3	875.4	878.9	878.9	882.3	889.3	896.2	896.2	903.3	913.7	917.2
52.5°	774.2	774.2	781.1	784.7	788.2	788.2	798.6	802.1	805.6	812.5	819.6
55°	669.6	680.0	683.5	683.5	690.5	697.5	701.0	704.5	704.5	718.4	718.4
57.5°	579.0	582.4	589.4	589.4	589.4	599.8	599.8	606.9	610.3	613.8	620.8
60°	488.3	495.2	495.2	498.7	495.2	502.2	505.7	512.6	516.1	519.7	523.1
62.5°	404.6	404.6	408.0	408.0	408.0	408.0	415.0	415.0	422.0	425.4	429.0
65°	324.3	324.3	324.3	324.3	324.3	324.3	324.3	324.3	327.8	327.8	334.8
67.5°	251.0	247.6	240.6	244.1	240.6	240.6	237.1	237.1	240.6	240.6	247.6
70°	181.3	177.9	170.9	170.9	167.4	164.0	160.4	156.9	153.4	153.4	153.4
72.5°	118.6	111.6	101.1	97.6	97.6	90.7	83.7	80.2	80.2	80.2	80.2
75°	59.3	52.3	45.4	41.8	41.8	34.9	38.3	34.9	34.9	34.9	34.9
77.5°	24.4	17.5	13.9	13.9	13.9	10.4	10.4	10.4	10.4	10.4	10.4
80°	7.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585007

CATALOG NUMBER: HCC8S55D010SL-HM82555930-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0	2612.0
2.5°	2598.1	2598.1	2591.2	2594.7	2594.7	2594.7	2594.7	2594.7
5°	2566.8	2570.2	2566.8	2570.2	2570.2	2566.8	2566.8	2566.8
7.5°	2535.4	2538.9	2535.4	2538.9	2538.9	2538.9	2535.4	2535.4
10°	2497.1	2497.1	2497.1	2497.1	2497.1	2493.5	2497.1	2497.1
12.5°	2444.7	2444.7	2444.7	2448.2	2448.2	2444.7	2444.7	2441.2
15°	2388.9	2382.0	2385.4	2388.9	2385.4	2385.4	2385.4	2385.4
17.5°	2312.1	2315.6	2312.1	2312.1	2312.1	2312.1	2315.6	2312.1
20°	2232.0	2232.0	2235.5	2232.0	2232.0	2232.0	2232.0	2228.4
22.5°	2141.2	2137.8	2137.8	2141.2	2141.2	2137.8	2141.2	2141.2
25°	2040.1	2043.6	2040.1	2040.1	2043.6	2043.6	2043.6	2040.1
27.5°	1932.0	1935.6	1939.1	1935.6	1935.6	1935.6	1939.1	1942.5
30°	1820.5	1827.4	1820.5	1820.5	1827.4	1824.0	1827.4	1827.4
32.5°	1701.9	1712.3	1705.4	1712.3	1712.3	1715.8	1712.3	1715.8
35°	1583.3	1593.8	1593.8	1593.8	1597.2	1600.7	1600.7	1597.2
37.5°	1471.7	1475.2	1475.2	1482.1	1485.6	1489.1	1489.1	1485.6
40°	1356.6	1363.6	1367.0	1367.0	1367.0	1374.1	1381.0	1374.1
42.5°	1245.0	1248.5	1252.0	1252.0	1259.0	1262.5	1266.0	1266.0
45°	1137.0	1143.9	1147.4	1150.9	1154.3	1161.3	1157.8	1164.9
47.5°	1025.3	1035.8	1039.2	1042.7	1049.8	1053.2	1056.7	1060.2
50°	924.1	931.2	931.2	938.1	948.6	948.6	955.5	959.0
52.5°	823.0	826.5	830.0	833.5	840.4	847.5	847.5	854.4
55°	725.4	728.9	728.9	732.4	735.9	749.8	753.2	753.2
57.5°	624.2	624.2	631.2	634.8	638.2	645.2	645.2	645.2
60°	526.6	530.1	530.1	533.6	537.0	544.0	547.6	544.0
62.5°	429.0	432.5	432.5	436.0	442.9	446.4	442.9	442.9
65°	338.2	341.8	341.8	345.3	352.2	352.2	348.8	352.2
67.5°	247.6	247.6	247.6	247.6	247.6	247.6	247.6	247.6
70°	156.9	153.4	150.0	153.4	153.4	153.4	150.0	156.9
72.5°	76.8	80.2	80.2	80.2	80.2	80.2	80.2	76.8
75°	34.9	34.9	31.4	31.4	31.4	34.9	34.9	31.4
77.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)