

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585067

Luminaire Tested: **HCC8W60D010MW-HM86080827-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010MW-HM86080827-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4937.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585067
CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585067

CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	75694	75694	75694
5°	78466	75441	72854
10°	80682	74789	69876
15°	82482	73467	66785
20°	82609	70596	64075
25°	81025	66674	61808
30°	76854	61827	59096
35°	69830	56308	56440
40°	61053	50527	53196
45°	52915	45009	49571
50°	46337	39976	45162
55°	41240	35434	40864
60°	37201	31823	35906
65°	33578	27982	31287
70°	30176	23577	23261
75°	26593	18693	17454
80°	22286	15485	16710
85°	17266	13586	14825



TEST NUMBER: P585067

CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.6	4.7
10°-20°	652.2	13.2
20°-30°	932.1	18.9
30°-40°	990.4	20.1
40°-50°	852.8	17.3
50°-60°	637.6	12.9
60°-70°	406.7	8.2
70°-80°	185.1	3.7
80°-90°	48.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1816.0	36.8
0°-40°	2806.4	56.8
0°-60°	4296.7	87.0
0°-90°	4937.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4937.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2455	2455	2455	2455	2455	
5°	2535	2500	2437	2374	2354	243
15°	2584	2496	2301	2144	2092	728
25°	2381	2232	1960	1841	1817	1090
35°	1855	1726	1496	1457	1499	1155
45°	1213	1147	1032	1060	1137	943
55°	767	704	659	715	760	690
65°	460	408	384	401	429	459
75°	223	192	157	143	146	237
85°	49	42	38	42	42	59
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585067

CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7
2.5°	2500.0	2493.1	2496.5	2493.1	2496.5	2496.5	2489.6	2489.6	2489.6	2489.6	2479.1
5°	2534.9	2531.4	2531.4	2527.9	2524.4	2527.9	2524.4	2521.0	2514.0	2510.5	2500.0
7.5°	2555.8	2555.8	2555.8	2555.8	2552.4	2548.8	2545.3	2538.4	2531.4	2524.4	2517.4
10°	2576.7	2580.3	2576.7	2573.2	2569.8	2562.7	2559.3	2552.4	2541.9	2531.4	2524.4
12.5°	2587.2	2587.2	2583.7	2583.7	2576.7	2573.2	2562.7	2552.4	2541.9	2531.4	2514.0
15°	2583.7	2583.7	2580.3	2576.7	2566.3	2562.7	2555.8	2545.3	2527.9	2514.0	2496.5
17.5°	2562.7	2559.3	2552.4	2552.4	2538.4	2534.9	2527.9	2514.0	2496.5	2475.7	2454.7
20°	2517.4	2517.4	2514.0	2510.5	2496.5	2486.0	2479.1	2461.7	2447.7	2423.3	2402.4
22.5°	2454.7	2461.7	2454.7	2447.7	2430.3	2426.8	2416.4	2395.4	2374.5	2346.6	2322.3
25°	2381.4	2378.0	2374.5	2367.5	2353.6	2346.6	2332.6	2311.8	2290.8	2259.4	2231.6
27.5°	2287.3	2273.4	2273.4	2259.4	2249.0	2238.5	2231.6	2210.6	2182.7	2158.4	2123.4
30°	2158.4	2161.8	2144.4	2140.9	2123.4	2116.5	2102.5	2081.7	2057.2	2029.3	2001.4
32.5°	2018.8	2008.4	2008.4	1994.5	1980.5	1970.0	1966.5	1942.1	1921.2	1893.3	1865.4
35°	1855.0	1855.0	1844.5	1841.1	1827.1	1820.1	1809.7	1795.7	1771.3	1746.8	1725.9
37.5°	1694.6	1687.7	1684.1	1677.2	1666.7	1656.2	1656.2	1631.8	1628.4	1600.5	1572.5
40°	1516.7	1523.8	1516.7	1506.3	1502.8	1495.8	1492.4	1478.4	1467.9	1443.5	1426.1
42.5°	1366.8	1359.9	1359.9	1356.4	1342.4	1342.4	1335.4	1328.5	1311.1	1304.0	1283.2
45°	1213.4	1220.4	1209.9	1213.4	1199.4	1199.4	1199.4	1185.5	1171.5	1161.1	1147.2
47.5°	1080.9	1084.4	1084.4	1073.9	1070.5	1070.5	1063.4	1056.5	1046.0	1032.1	1021.7
50°	965.9	969.3	962.4	958.8	951.9	948.4	948.4	934.5	927.4	913.5	906.6
52.5°	861.2	861.2	857.8	857.8	847.3	847.3	840.4	829.9	822.8	815.9	798.5
55°	767.1	767.1	763.6	760.1	760.1	749.7	746.1	735.8	728.7	714.8	704.4
57.5°	676.5	679.9	676.5	672.9	669.4	666.0	659.1	648.6	641.5	631.1	624.1
60°	603.2	603.2	599.8	596.2	589.3	585.8	582.2	575.3	564.8	557.9	547.4
62.5°	533.4	530.0	526.5	523.1	516.0	516.0	509.1	502.1	491.6	484.7	477.7
65°	460.2	460.2	456.7	456.7	453.3	446.4	442.8	439.3	425.4	421.9	408.0
67.5°	394.0	397.5	390.5	390.5	383.5	383.5	380.0	369.5	366.1	359.2	352.1
70°	334.7	334.7	334.7	331.3	324.2	320.8	317.3	310.4	306.8	299.9	292.8
72.5°	275.4	275.4	272.0	272.0	268.5	265.1	261.5	254.6	254.6	247.5	240.6
75°	223.2	223.2	219.7	216.1	212.7	212.7	209.2	205.8	198.7	195.3	191.8
77.5°	170.8	170.8	170.8	167.4	163.9	163.9	163.9	156.9	149.9	149.9	146.5
80°	125.5	125.5	122.0	122.0	118.6	118.6	118.6	115.1	111.5	108.1	104.6
82.5°	83.7	83.7	83.7	83.7	80.2	80.2	80.2	76.7	73.2	73.2	73.2
85°	48.8	48.8	48.8	48.8	45.3	45.3	45.3	45.3	45.3	41.9	41.9
87.5°	20.9	17.4	20.9	17.4	20.9	17.4	20.9	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585067

CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7
2.5°	2482.6	2479.1	2475.7	2472.1	2472.1	2468.6	2461.7	2458.1	2454.7	2451.2	2451.2
5°	2496.5	2493.1	2486.0	2479.1	2475.7	2468.6	2461.7	2454.7	2447.7	2437.2	2433.8
7.5°	2507.0	2496.5	2489.6	2475.7	2472.1	2465.2	2454.7	2444.3	2430.3	2416.4	2405.9
10°	2507.0	2493.1	2482.6	2465.2	2458.1	2451.2	2437.2	2419.8	2402.4	2388.5	2371.0
12.5°	2500.0	2482.6	2465.2	2447.7	2437.2	2426.8	2405.9	2388.5	2367.5	2346.6	2332.6
15°	2475.7	2454.7	2433.8	2412.8	2402.4	2388.5	2367.5	2343.1	2322.3	2301.3	2276.9
17.5°	2430.3	2409.3	2385.0	2360.5	2346.6	2336.1	2304.7	2287.3	2255.9	2235.1	2214.1
20°	2371.0	2346.6	2315.2	2290.8	2273.4	2263.0	2238.5	2207.1	2182.7	2151.3	2130.4
22.5°	2294.3	2263.0	2231.6	2207.1	2189.7	2175.8	2144.4	2113.0	2092.0	2064.1	2039.8
25°	2203.7	2172.3	2140.9	2106.0	2088.6	2074.6	2046.7	2018.8	1991.0	1959.6	1938.6
27.5°	2095.6	2060.7	2032.8	2001.4	1984.0	1963.1	1931.7	1903.8	1875.9	1855.0	1827.1
30°	1977.0	1938.6	1910.7	1879.3	1861.9	1844.5	1813.1	1785.2	1760.8	1736.4	1722.5
32.5°	1834.0	1806.1	1778.3	1746.8	1733.0	1722.5	1691.1	1663.2	1635.3	1614.4	1603.9
35°	1698.0	1666.7	1642.3	1614.4	1597.0	1586.5	1558.6	1534.1	1520.2	1495.8	1481.9
37.5°	1555.1	1530.7	1502.8	1474.9	1464.5	1454.0	1433.1	1408.6	1387.8	1370.4	1363.3
40°	1405.2	1384.3	1359.9	1342.4	1331.9	1321.5	1304.0	1286.6	1272.7	1255.2	1248.3
42.5°	1262.2	1248.3	1227.3	1206.5	1196.0	1192.5	1171.5	1157.7	1150.6	1143.7	1136.7
45°	1133.2	1112.3	1098.4	1084.4	1073.9	1067.0	1056.5	1046.0	1039.1	1032.1	1025.1
47.5°	1007.7	990.2	976.4	965.9	955.4	951.9	944.9	934.5	927.4	927.4	927.4
50°	892.6	878.7	864.7	857.8	854.2	847.3	840.4	836.8	833.3	833.3	833.3
52.5°	791.5	777.5	767.1	760.1	760.1	753.2	746.1	742.7	742.7	742.7	742.7
55°	697.3	686.8	679.9	672.9	666.0	662.5	662.5	662.5	659.1	659.1	662.5
57.5°	613.7	606.7	596.2	589.3	585.8	585.8	582.2	578.8	582.2	585.8	589.3
60°	536.9	530.0	526.5	516.0	516.0	516.0	512.6	512.6	512.6	516.0	519.5
62.5°	467.2	463.8	456.7	453.3	449.8	449.8	446.4	446.4	446.4	446.4	449.8
65°	404.5	397.5	390.5	390.5	390.5	387.1	387.1	380.0	383.5	383.5	380.0
67.5°	345.2	338.2	334.7	331.3	327.8	327.8	324.2	320.8	317.3	317.3	317.3
70°	289.4	282.5	282.5	275.4	275.4	272.0	268.5	268.5	265.1	261.5	258.0
72.5°	233.6	230.1	226.6	223.2	223.2	223.2	219.7	216.1	212.7	209.2	202.2
75°	184.8	184.8	177.9	174.4	174.4	170.8	167.4	163.9	160.4	156.9	153.4
77.5°	142.9	139.4	132.5	129.1	129.1	129.1	125.5	122.0	118.6	115.1	111.5
80°	104.6	101.2	97.6	94.1	94.1	94.1	90.7	90.7	87.2	87.2	87.2
82.5°	69.8	69.8	66.2	66.2	66.2	66.2	62.7	62.7	62.7	62.7	62.7
85°	41.9	41.9	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585067

CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7
2.5°	2444.3	2444.3	2437.2	2433.8	2430.3	2433.8	2426.8	2423.3	2419.8	2419.8	2416.4
5°	2423.3	2419.8	2405.9	2402.4	2399.0	2395.4	2388.5	2381.4	2374.5	2371.0	2367.5
7.5°	2395.4	2385.0	2371.0	2367.5	2364.0	2353.6	2343.1	2336.1	2325.7	2322.3	2315.2
10°	2357.1	2343.1	2332.6	2322.3	2315.2	2304.7	2294.3	2283.8	2269.9	2266.4	2255.9
12.5°	2311.8	2294.3	2273.4	2269.9	2259.4	2245.4	2231.6	2221.1	2210.6	2203.7	2193.2
15°	2255.9	2238.5	2217.6	2207.1	2196.7	2186.3	2168.7	2154.8	2144.4	2133.9	2123.4
17.5°	2189.7	2168.7	2151.3	2140.9	2133.9	2116.5	2102.5	2085.1	2074.6	2064.1	2053.7
20°	2109.5	2092.0	2067.7	2057.2	2053.7	2039.8	2022.4	2015.3	2001.4	1991.0	1984.0
22.5°	2018.8	2001.4	1980.5	1973.5	1959.6	1952.6	1935.2	1928.1	1921.2	1910.7	1907.3
25°	1917.8	1900.3	1882.8	1879.3	1869.0	1861.9	1851.4	1841.1	1841.1	1830.6	1830.6
27.5°	1813.1	1795.7	1781.8	1774.7	1771.3	1764.4	1753.9	1750.4	1746.8	1743.4	1743.4
30°	1701.5	1680.6	1673.7	1670.1	1666.7	1659.7	1656.2	1649.2	1652.7	1656.2	1652.7
32.5°	1583.0	1576.0	1562.0	1555.1	1558.6	1555.1	1548.1	1555.1	1551.7	1558.6	1562.0
35°	1467.9	1461.0	1454.0	1454.0	1447.1	1447.1	1447.1	1450.5	1457.4	1461.0	1467.9
37.5°	1356.4	1345.9	1342.4	1339.0	1342.4	1342.4	1342.4	1349.4	1356.4	1363.3	1373.8
40°	1237.8	1230.8	1230.8	1230.8	1230.8	1241.3	1237.8	1244.7	1251.8	1262.2	1272.7
42.5°	1126.2	1126.2	1129.8	1129.8	1129.8	1129.8	1136.7	1147.2	1157.7	1168.0	1178.5
45°	1021.7	1021.7	1021.7	1028.6	1028.6	1032.1	1046.0	1053.1	1060.0	1070.5	1080.9
47.5°	924.0	924.0	927.4	931.0	934.5	941.4	948.4	958.8	969.3	976.4	986.7
50°	833.3	836.8	843.8	850.7	850.7	854.2	864.7	871.7	878.7	889.2	892.6
52.5°	746.1	753.2	760.1	763.6	767.1	774.0	777.5	788.0	791.5	802.0	805.4
55°	666.0	669.4	679.9	683.4	683.4	690.4	697.3	704.4	714.8	714.8	721.8
57.5°	592.7	596.2	603.2	606.7	603.2	613.7	617.2	624.1	627.6	634.6	638.1
60°	519.5	526.5	530.0	530.0	533.4	536.9	543.9	543.9	550.9	557.9	557.9
62.5°	449.8	453.3	456.7	460.2	463.8	460.2	470.7	470.7	477.7	481.2	488.1
65°	383.5	387.1	387.1	390.5	390.5	394.0	394.0	397.5	401.0	408.0	411.4
67.5°	317.3	317.3	317.3	320.8	317.3	320.8	320.8	324.2	324.2	331.3	334.7
70°	258.0	254.6	251.1	251.1	251.1	251.1	247.5	251.1	251.1	254.6	254.6
72.5°	198.7	195.3	191.8	188.2	188.2	184.8	181.3	184.8	184.8	188.2	188.2
75°	149.9	142.9	142.9	142.9	139.4	139.4	139.4	142.9	142.9	142.9	146.5
77.5°	111.5	111.5	108.1	108.1	108.1	111.5	111.5	115.1	115.1	115.1	115.1
80°	83.7	87.2	87.2	87.2	87.2	90.7	90.7	90.7	90.7	94.1	94.1
82.5°	62.7	62.7	62.7	62.7	66.2	66.2	66.2	66.2	66.2	66.2	66.2
85°	38.4	41.9	41.9	38.4	41.9	41.9	41.9	41.9	41.9	41.9	41.9
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585067

CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7	2454.7
2.5°	2412.8	2412.8	2412.8	2412.8	2409.3	2409.3	2409.3	2405.9
5°	2360.5	2360.5	2360.5	2353.6	2357.1	2357.1	2350.1	2353.6
7.5°	2308.3	2304.7	2301.3	2301.3	2297.8	2294.3	2290.8	2294.3
10°	2249.0	2238.5	2238.5	2235.1	2235.1	2228.0	2228.0	2231.6
12.5°	2182.7	2175.8	2175.8	2172.3	2168.7	2165.3	2161.8	2161.8
15°	2116.5	2109.5	2106.0	2102.5	2099.1	2092.0	2095.6	2092.0
17.5°	2050.3	2039.8	2039.8	2036.3	2032.8	2025.8	2025.8	2022.4
20°	1973.5	1970.0	1963.1	1966.5	1963.1	1956.1	1952.6	1952.6
22.5°	1896.8	1896.8	1893.3	1893.3	1889.8	1886.4	1882.8	1882.8
25°	1823.6	1820.1	1823.6	1823.6	1813.1	1813.1	1813.1	1816.6
27.5°	1739.9	1743.4	1739.9	1739.9	1739.9	1739.9	1743.4	1739.9
30°	1656.2	1656.2	1656.2	1659.7	1666.7	1663.2	1663.2	1659.7
32.5°	1565.5	1569.1	1569.1	1572.5	1576.0	1583.0	1583.0	1586.5
35°	1474.9	1481.9	1485.3	1481.9	1492.4	1492.4	1499.3	1499.3
37.5°	1380.7	1384.3	1391.2	1394.7	1401.7	1405.2	1408.6	1408.6
40°	1279.7	1293.7	1297.1	1300.6	1311.1	1311.1	1314.5	1321.5
42.5°	1185.5	1199.4	1203.0	1206.5	1213.4	1223.9	1220.4	1227.3
45°	1094.8	1105.3	1108.8	1112.3	1122.7	1126.2	1126.2	1136.7
47.5°	997.2	1004.2	1007.7	1014.6	1021.7	1028.6	1035.5	1032.1
50°	899.5	910.0	917.1	920.5	931.0	934.5	937.9	941.4
52.5°	812.5	819.4	822.8	826.4	836.8	840.4	843.8	850.7
55°	728.7	732.2	739.2	735.8	746.1	749.7	753.2	760.1
57.5°	645.1	648.6	652.0	652.0	659.1	666.0	669.4	672.9
60°	564.8	571.9	575.3	575.3	575.3	582.2	582.2	582.2
62.5°	491.6	491.6	495.2	495.2	502.1	502.1	502.1	502.1
65°	414.9	418.5	421.9	421.9	428.8	425.4	432.4	428.8
67.5°	334.7	334.7	341.8	341.8	338.2	341.8	341.8	341.8
70°	254.6	254.6	258.0	258.0	258.0	258.0	258.0	258.0
72.5°	188.2	188.2	188.2	191.8	188.2	188.2	191.8	188.2
75°	146.5	146.5	146.5	146.5	146.5	146.5	146.5	146.5
77.5°	115.1	115.1	118.6	118.6	118.6	118.6	118.6	118.6
80°	94.1	94.1	94.1	94.1	97.6	94.1	94.1	94.1
82.5°	69.8	66.2	69.8	66.2	69.8	69.8	69.8	69.8
85°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)