

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585076

Luminaire Tested: **HCC8S60D010MW-HM86080830-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010MW-HM86080830-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4790.5 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585076
CATALOG NUMBER: HCC8S60D010MW-HM86080830-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585076

CATALOG NUMBER: HCC8S60D010MW-HM86080830-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88															
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77				77															
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67															
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59															
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52															
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47															
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42															
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38															
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35				35															
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32															

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	78799	78799	78799
5°	80276	78456	76636
10°	81530	77087	73834
15°	82351	75168	70635
20°	82038	72266	67380
25°	79875	68096	63618
30°	76070	63124	59919
35°	68693	57611	55657
40°	60353	51714	51573
45°	52095	45449	47412
50°	45349	39865	42523
55°	40208	34628	37042
60°	35875	29257	30750
65°	32345	23750	24254
70°	28725	17788	14362
75°	24746	10318	6183
80°	19072	3694	1847
85°	12242	1238	1238



TEST NUMBER: P585076
 CATALOG NUMBER: HCC8S60D010MW-HM86080830-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	239.9	5.0
10°-20°	667.8	13.9
20°-30°	944.5	19.7
30°-40°	995.3	20.8
40°-50°	845.8	17.7
50°-60°	609.1	12.7
60°-70°	351.4	7.3
70°-80°	120.2	2.5
80°-90°	16.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1852.2	38.7
0°-40°	2847.5	59.4
0°-60°	4302.4	89.8
0°-90°	4790.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4790.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2555	2555	2555	2555	2555	
5°	2593	2576	2535	2490	2476	248
15°	2580	2500	2355	2251	2213	726
25°	2348	2226	2001	1898	1870	1077
35°	1825	1717	1530	1475	1478	1136
45°	1195	1139	1042	1049	1087	928
55°	748	689	644	668	689	673
65°	443	381	326	319	332	441
75°	208	156	87	55	52	219
85°	35	21	4	4	4	47
90°	0	0	0	0	0	



TEST NUMBER: P585076

CATALOG NUMBER: HCC8S60D010MW-HM86080830-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4
2.5°	2579.6	2583.0	2579.6	2579.6	2576.1	2572.7	2569.2	2565.7	2558.8	2551.9	2551.9
5°	2593.4	2600.3	2593.4	2593.4	2583.0	2576.1	2569.2	2558.8	2545.0	2534.6	2534.6
7.5°	2603.8	2603.8	2603.8	2593.4	2586.5	2576.1	2558.8	2541.5	2524.2	2506.9	2500.0
10°	2603.8	2603.8	2600.3	2586.5	2579.6	2558.8	2541.5	2517.3	2493.1	2468.9	2461.9
12.5°	2593.4	2596.9	2590.0	2576.1	2558.8	2534.6	2510.4	2479.2	2451.4	2423.8	2409.9
15°	2579.6	2576.1	2569.2	2551.9	2531.1	2500.0	2475.8	2441.1	2403.0	2368.4	2354.6
17.5°	2545.0	2545.0	2534.6	2517.3	2489.6	2454.9	2416.8	2378.8	2337.2	2299.2	2281.8
20°	2500.0	2500.0	2486.2	2465.4	2437.6	2392.6	2351.1	2306.1	2257.5	2219.5	2202.2
22.5°	2434.1	2437.6	2420.3	2396.1	2364.9	2313.0	2271.4	2216.0	2167.6	2122.6	2108.6
25°	2347.6	2354.6	2337.2	2313.0	2271.4	2226.4	2174.5	2122.6	2067.1	2022.1	2001.4
27.5°	2247.2	2250.6	2233.3	2209.1	2167.6	2119.1	2067.1	2011.8	1959.9	1911.3	1890.5
30°	2136.4	2122.6	2115.6	2084.4	2039.4	1997.9	1939.0	1894.0	1838.6	1797.1	1772.8
32.5°	1980.6	1987.5	1966.8	1942.4	1907.8	1859.4	1811.0	1758.9	1707.0	1675.9	1658.6
35°	1824.8	1831.7	1821.3	1797.1	1758.9	1717.4	1669.0	1630.9	1585.8	1547.7	1530.4
37.5°	1662.0	1662.0	1655.1	1641.3	1613.6	1575.4	1527.0	1488.9	1450.9	1419.6	1409.2
40°	1499.3	1492.4	1488.9	1478.5	1454.3	1419.6	1388.5	1357.3	1319.3	1298.5	1284.7
42.5°	1340.0	1340.0	1333.1	1322.7	1298.5	1281.2	1249.9	1215.3	1187.7	1166.9	1166.9
45°	1194.6	1198.0	1187.7	1180.7	1166.9	1139.2	1111.5	1087.2	1063.0	1049.1	1042.2
47.5°	1066.4	1066.4	1056.1	1049.1	1035.3	1011.1	986.8	966.1	948.8	938.4	934.9
50°	945.3	945.3	945.3	927.9	910.6	893.3	876.0	851.8	841.4	834.5	831.0
52.5°	841.4	837.9	837.9	824.1	806.8	786.0	768.7	747.9	737.5	730.6	734.0
55°	747.9	747.9	744.4	727.1	709.8	689.0	671.7	654.4	647.5	640.6	644.1
56°	709.8	709.8	706.3	692.5	671.7	654.4	633.7	616.4	606.0	609.5	609.5
57°	682.1	675.2	675.2	657.9	640.6	616.4	599.1	581.7	574.7	571.3	571.3
58°	647.5	644.1	640.6	623.3	606.0	585.1	567.8	550.5	540.1	540.1	536.7
59°	612.9	612.9	606.0	592.0	574.7	554.0	536.7	519.4	509.0	505.5	505.5
60°	581.7	585.1	574.7	560.9	547.1	522.8	502.1	488.2	477.9	474.4	474.4
61°	554.0	554.0	547.1	529.8	512.5	495.2	474.4	457.1	450.2	443.3	443.3
62°	529.8	522.8	519.4	502.1	484.8	464.0	446.7	429.4	418.9	412.0	415.5
63°	498.6	495.2	488.2	474.4	457.1	436.3	415.5	401.6	391.2	380.9	384.3
64°	474.4	470.9	460.6	446.7	429.4	408.5	387.8	373.9	367.0	356.6	353.2
65°	443.3	439.8	436.3	418.9	401.6	380.9	363.6	349.7	339.3	332.4	325.5
66°	415.5	418.9	412.0	398.2	377.4	360.1	335.9	322.0	315.1	304.7	297.8
67°	391.2	391.2	384.3	370.5	349.7	332.4	315.1	297.8	287.4	277.0	273.6
67.5°	377.4	377.4	370.5	353.2	339.3	318.6	301.3	287.4	273.6	266.7	259.7
68°	363.6	363.6	360.1	346.3	328.9	308.2	290.9	273.6	259.7	249.2	245.8
69°	339.3	342.8	335.9	322.0	304.7	284.0	266.7	252.7	238.9	228.5	221.6
70°	318.6	315.1	308.2	294.3	277.0	263.2	245.8	228.5	214.6	200.8	197.3
71°	290.9	290.9	284.0	273.6	256.3	238.9	221.6	207.7	193.9	176.6	173.1
72°	270.1	270.1	263.2	249.2	235.4	218.1	200.8	183.5	173.1	155.8	148.9
72.5°	256.3	259.7	252.7	238.9	225.0	204.3	190.4	176.6	159.3	145.4	138.5
73°	249.2	245.8	242.3	228.5	211.2	197.3	180.0	166.2	148.9	135.1	128.1



TEST NUMBER: P585076

CATALOG NUMBER: HCC8S60D010MW-HM86080830-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	155.8	155.8	152.4	138.5	124.7	110.8	97.0	83.0	69.2	55.4	48.4
80°	107.4	110.8	103.9	97.0	86.6	72.7	58.8	48.4	34.6	27.7	20.8
82.5°	69.2	69.2	65.7	58.8	51.9	41.5	34.6	24.2	17.3	13.8	10.4
85°	34.6	38.1	34.6	31.1	24.2	20.8	17.3	10.4	6.9	3.5	3.5
87.5°	13.8	13.8	13.8	10.4	10.4	6.9	3.5	3.5	3.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585076

CATALOG NUMBER: HCC8S60D010MW-HM86080830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4	2555.4
2.5°	2545.0	2545.0	2538.1	2534.6	2531.1	2527.7	2524.2	2520.8	2520.8	2524.2
5°	2524.2	2517.3	2503.5	2500.0	2489.6	2486.2	2479.2	2475.8	2479.2	2475.8
7.5°	2493.1	2479.2	2461.9	2454.9	2441.1	2434.1	2423.8	2423.8	2416.8	2420.3
10°	2451.4	2430.7	2409.9	2396.1	2385.7	2375.3	2368.4	2361.5	2358.0	2358.0
12.5°	2399.5	2375.3	2354.6	2333.8	2316.5	2309.6	2295.7	2295.7	2288.8	2285.2
15°	2340.7	2309.6	2285.2	2264.5	2250.6	2236.8	2226.4	2219.5	2212.6	2212.6
17.5°	2264.5	2236.8	2212.6	2188.3	2167.6	2157.2	2146.8	2136.4	2136.4	2129.5
20°	2181.4	2150.3	2129.5	2105.2	2087.9	2070.6	2056.7	2056.7	2049.8	2053.3
22.5°	2087.9	2049.8	2029.1	2011.8	1994.5	1980.6	1966.8	1966.8	1963.3	1959.9
25°	1984.1	1952.9	1928.6	1907.8	1897.5	1883.6	1880.2	1873.2	1869.8	1869.8
27.5°	1873.2	1849.0	1817.9	1807.5	1793.7	1786.7	1786.7	1783.3	1776.2	1779.7
30°	1755.5	1727.8	1710.5	1703.6	1689.7	1689.7	1686.3	1679.4	1679.4	1682.8
32.5°	1641.3	1613.6	1599.7	1596.2	1582.3	1582.3	1578.9	1582.3	1582.3	1585.8
35°	1516.6	1492.4	1488.9	1478.5	1475.1	1475.1	1475.1	1482.0	1488.9	1478.5
37.5°	1398.8	1381.5	1371.2	1367.7	1371.2	1371.2	1374.6	1385.0	1381.5	1378.1
40°	1277.7	1263.8	1256.9	1256.9	1263.8	1270.7	1270.7	1281.2	1284.7	1281.2
42.5°	1156.5	1146.1	1146.1	1149.6	1156.5	1160.0	1170.4	1180.7	1184.2	1187.7
45°	1042.2	1042.2	1042.2	1045.7	1049.1	1056.1	1069.9	1080.3	1083.7	1087.2
47.5°	931.4	927.9	938.4	941.9	952.2	955.7	966.1	979.9	983.4	986.8
50°	827.6	834.5	837.9	848.3	855.2	855.2	869.1	876.0	886.4	886.4
52.5°	730.6	740.9	744.4	754.8	758.2	761.7	768.7	779.1	786.0	786.0
55°	644.1	647.5	654.4	657.9	668.3	671.7	678.7	682.1	692.5	689.0
56°	606.0	612.9	616.4	623.3	630.2	633.7	640.6	644.1	651.0	654.4
57°	571.3	574.7	585.1	588.6	595.6	595.6	599.1	609.5	609.5	612.9
58°	536.7	543.6	547.1	550.5	557.4	560.9	567.8	571.3	574.7	571.3
59°	505.5	509.0	512.5	512.5	519.4	519.4	529.8	536.7	540.1	540.1
60°	474.4	474.4	477.9	481.3	488.2	491.7	491.7	498.6	498.6	498.6
61°	443.3	443.3	446.7	450.2	453.6	453.6	460.6	460.6	464.0	467.5
62°	415.5	412.0	412.0	415.5	415.5	422.4	426.0	429.4	432.9	429.4
63°	384.3	380.9	380.9	380.9	380.9	387.8	387.8	391.2	398.2	394.7
64°	349.7	349.7	349.7	349.7	353.2	353.2	360.1	363.6	367.0	370.5
65°	325.5	318.6	315.1	315.1	318.6	322.0	325.5	328.9	332.4	332.4
66°	297.8	290.9	287.4	287.4	287.4	287.4	294.3	294.3	301.3	301.3
67°	266.7	259.7	256.3	252.7	252.7	252.7	263.2	259.7	259.7	259.7
67.5°	256.3	245.8	242.3	238.9	235.4	242.3	238.9	242.3	242.3	238.9
68°	242.3	235.4	228.5	221.6	221.6	221.6	225.0	228.5	225.0	221.6
69°	214.6	211.2	200.8	193.9	190.4	193.9	190.4	193.9	190.4	193.9
70°	190.4	180.0	169.7	166.2	162.7	162.7	162.7	159.3	162.7	159.3
71°	166.2	155.8	145.4	138.5	135.1	135.1	131.6	135.1	131.6	135.1
72°	142.0	131.6	117.8	110.8	110.8	110.8	110.8	107.4	110.8	107.4
72.5°	131.6	117.8	107.4	100.5	97.0	97.0	97.0	97.0	93.5	97.0
73°	121.2	107.4	93.5	90.1	90.1	90.1	86.6	83.0	86.6	86.6



TEST NUMBER: P585076
CATALOG NUMBER: HCC8S60D010MW-HM86080830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	41.5	31.1	27.7	27.7	27.7	27.7	27.7	27.7	24.2	24.2
80°	17.3	13.8	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
82.5°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
85°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	225.0	225.0	218.1	207.7	190.4	173.1	159.3	145.4	128.1	110.8	103.9
75°	207.7	204.3	197.3	187.0	173.1	155.8	142.0	124.7	110.8	93.5	86.6

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	100.5	83.0	76.1	69.2	69.2	69.2	65.7	65.7	65.7	69.2
75°	79.6	65.7	58.8	51.9	55.4	51.9	55.4	51.9	51.9	51.9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)